

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331357

Luminaire Tested: **SA2XXDIP-C675D925U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331357
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6632.4 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331357
CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot



56% Up

44% Dn



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44				38	
2	89	81	76	71	81	75	70	66	63	59	56	51	49	46	41	39	37				33	
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32				28	
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28				24	
5	68	57	49	44	62	53	46	41	45	39	35	37	33	30	30	27	25				22	
6	63	51	44	38	58	48	41	36	40	35	31	33	30	27	27	24	22				19	
7	58	47	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20				17	
8	54	42	35	30	50	39	33	28	33	28	25	28	24	21	23	20	18				15	
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16				14	
10	47	36	28	24	43	33	27	23	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.5	1.9
10°-20°	367.8	5.5
20°-30°	533.7	8.0
30°-40°	563.2	8.5
40°-50°	498.7	7.5
50°-60°	398.0	6.0
60°-70°	270.5	4.1
70°-80°	138.7	2.1
80°-90°	36.5	0.6
90°-100°	42.1	0.6
100°-110°	154.4	2.3
110°-120°	412.7	6.2
120°-130°	681.3	10.3
130°-140°	724.5	10.9
140°-150°	673.4	10.2
150°-160°	541.4	8.2
160°-170°	348.9	5.3
170°-180°	120.1	1.8
0°-30°	1028.0	15.5
0°-40°	1591.2	24.0
0°-60°	2487.8	37.5
0°-90°	2933.5	44.2
90°-120°	609.2	9.2
90°-150°	2688.4	40.5
90°-180°	3699.0	55.8
0°-180°	6632.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	31
90°	25	1	25	1	25	12
95°	39	59	39	59	39	37
105°	69	278	69	278	69	72
115°	75	525	75	525	75	188
125°	781	742	781	742	781	676
135°	949	919	949	919	949	731
145°	1082	1066	1082	1066	1082	677
155°	1174	1174	1174	1174	1174	542
165°	1234	1237	1234	1237	1234	348
175°	1258	1265	1258	1265	1258	120
180°	1262	1262	1262	1262	1262	



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	15.5	15.5	15.8	15.3	15.2	15.5	15.3	14.7	14.9	15.1	15.2
90°	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3	19.3	18.3	16.6
92.5°	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2	21.7	21.2	20.4
95°	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6	36.6	35.6	34.2
97.5°	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3	48.5	47.7	44.4
100°	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3	53.7	52.1	48.6
102.5°	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7	55.6	53.5	82.4
105°	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2	57.9	55.7	111.1
107.5°	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4	75.7	78.0	144.4
110°	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2	139.5	159.8	218.5



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1	329.1	403.1	417.6
115°	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6	469.5	563.5	558.4
117.5°	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7	601.4	624.1	620.7
120°	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3	671.9	669.4	665.8
122.5°	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5	714.0	712.6	708.6
125°	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6	773.2	771.7	767.9
127.5°	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2	827.1	825.1	822.2
130°	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9	861.6	859.4	857.2
132.5°	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6	895.7	893.7	891.5
135°	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7	943.6	941.6	939.8
137.5°	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3	988.3	986.4	984.3
140°	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2	1017.4	1015.6	1013.4
142.5°	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9	1044.3	1042.6	1040.1
145°	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3	1081.8	1080.4	1077.0
147.5°	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8	1114.7	1113.7	1110.3
150°	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8	1134.6	1133.4	1130.2
152.5°	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1	1152.9	1151.7	1148.6
155°	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8	1177.5	1176.3	1173.9
157.5°	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5	1198.2	1196.8	1195.1
160°	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6	1210.4	1209.2	1208.0
162.5°	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9	1221.5	1220.2	1219.1
165°	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9	1233.3
167.5°	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2	1246.8	1245.4	1244.8
170°	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1	1252.6	1251.2	1250.8
172.5°	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4	1257.0	1255.6	1255.2
175°	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2	1261.8	1260.3	1259.9
177.5°	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7	1262.6	1261.4	1261.3
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	15.3	14.9	14.6	15.0	13.4	12.9	10.8	9.2	9.2	9.2	8.9
90°	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9	3.1	5.4	7.6
92.5°	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4	18.2	18.0	17.8
95°	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4	52.7	46.0	39.3
97.5°	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8	98.9	80.1	61.2
100°	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7	133.8	106.0	78.2
102.5°	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9	204.0	198.1	192.2
105°	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6	283.7	289.8	295.9
107.5°	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9	359.8	364.7	369.6
110°	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6	408.9	413.1	417.4



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3	455.1	458.9	462.7
115°	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1	528.6	532.0	535.5
117.5°	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1	594.9	598.8	602.7
120°	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3	642.3	645.4	648.4
122.5°	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2	683.4	686.6	689.8
125°	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5	745.1	747.8	750.4
127.5°	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9	801.9	804.8	807.7
130°	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8	838.0	841.2	844.5
132.5°	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3	874.0	876.8	879.6
135°	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8	922.0	925.3	928.5
137.5°	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8	969.1	971.4	973.6
140°	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2	999.9	1001.5	1003.1
142.5°	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5	1026.0	1027.5	1028.9
145°	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8	1065.6	1065.4	1065.2
147.5°	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8	1101.0	1100.3	1099.5
150°	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2	1123.8	1122.3	1120.9
152.5°	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9	1143.3	1141.7	1140.2
155°	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6	1171.8	1169.9	1168.1
157.5°	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0	1194.5	1193.0	1191.4
160°	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1208.0	1206.8	1205.5
162.5°	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9	1219.7	1218.5	1217.2
165°	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6	1235.4	1234.2	1232.9
167.5°	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3	1247.1	1245.9	1244.6
170°	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9	1253.6	1252.4	1251.2
172.5°	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2	1258.0	1256.8	1255.6
175°	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9	1263.5	1262.1	1260.6
177.5°	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8	1264.7	1263.6	1262.4
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	8.9	8.9	8.8	9.1	9.0	9.0	8.8	9.0	9.2	8.5	8.7
90°	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3	21.3	22.3	23.0
92.5°	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2	22.8	23.3	23.7
95°	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6	38.7	39.7	40.1
97.5°	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3	50.1	50.9	51.4
100°	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3	56.9	58.6	59.6
102.5°	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7	59.9	62.0	63.3
105°	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2	62.4	64.6	66.2
107.5°	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4	71.2	68.9	68.2
110°	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2	98.9	78.6	68.9



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1	181.0	107.0	70.3
115°	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6	281.6	187.6	133.3
117.5°	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7	556.0	533.2	497.8
120°	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3	676.8	679.2	666.7
122.5°	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5	716.9	718.4	716.5
125°	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6	776.0	777.4	778.4
127.5°	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2	831.3	833.4	834.4
130°	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9	866.1	868.3	869.4
132.5°	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6	899.5	901.4	902.2
135°	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7	947.7	949.7	950.5
137.5°	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3	992.3	994.3	995.0
140°	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2	1021.1	1022.9	1023.3
142.5°	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9	1047.6	1049.3	1049.6
145°	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3	1084.7	1086.1	1086.3
147.5°	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8	1116.8	1117.9	1118.0
150°	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8	1137.1	1138.3	1138.4
152.5°	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1	1155.3	1156.5	1156.5
155°	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8	1180.0	1181.2	1181.0
157.5°	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5	1200.9	1202.3	1202.2
160°	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6	1212.9	1214.1	1214.0
162.5°	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9	1224.3	1225.7	1225.5
165°	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5
167.5°	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2	1249.6	1251.1	1250.8
170°	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1	1255.5	1256.9	1256.7
172.5°	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4	1259.9	1261.3	1261.1
175°	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2	1264.6	1266.0	1265.7
177.5°	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7	1264.9	1266.0	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	8.8	8.4	8.5	8.2	8.5	8.4	8.8	8.7	8.5	9.2	9.0
90°	23.4	23.8	24.3	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3
92.5°	23.9	24.2	24.4	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2
95°	39.9	39.7	39.5	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6
97.5°	51.7	51.9	52.2	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3
100°	60.0	60.4	60.8	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3
102.5°	63.9	64.4	65.0	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7
105°	67.0	67.8	68.6	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2
107.5°	69.0	69.8	70.6	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4
110°	69.7	70.5	71.3	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	70.9	71.6	72.2	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1
115°	118.7	104.1	89.5	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6
117.5°	449.8	401.8	353.8	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7
120°	639.3	611.9	584.5	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3
122.5°	711.2	705.8	700.5	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5
125°	779.0	779.6	780.3	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6
127.5°	834.6	834.7	834.8	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2
130°	869.2	868.9	868.7	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9
132.5°	902.0	901.8	901.6	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6
135°	950.1	949.7	949.3	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7
137.5°	994.3	993.6	992.9	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3
140°	1022.3	1021.3	1020.3	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2
142.5°	1048.6	1047.6	1046.6	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9
145°	1085.3	1084.3	1083.3	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3
147.5°	1117.1	1116.3	1115.4	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8
150°	1137.4	1136.3	1135.3	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8
152.5°	1155.1	1153.8	1152.5	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1
155°	1179.4	1177.7	1176.1	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8
157.5°	1200.6	1199.0	1197.4	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5
160°	1212.5	1211.1	1209.7	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6
162.5°	1223.8	1222.0	1220.3	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9
165°	1238.1	1236.7	1235.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7
167.5°	1249.0	1247.2	1245.4	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2
170°	1254.9	1253.0	1251.2	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1
172.5°	1259.2	1257.4	1255.6	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4
175°	1263.7	1261.7	1259.6	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2
177.5°	1264.4	1262.9	1261.4	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	8.8	9.0	9.0	9.1	8.8	8.9	8.9	8.9	9.2	9.2	9.2
90°	19.3	18.3	16.6	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9
92.5°	21.7	21.2	20.4	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4
95°	36.6	35.6	34.2	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4
97.5°	48.5	47.7	44.4	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8
100°	53.7	52.1	48.6	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7
102.5°	55.6	53.5	82.4	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9
105°	57.9	55.7	111.1	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6
107.5°	75.7	78.0	144.4	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9
110°	139.5	159.8	218.5	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.1	403.1	417.6	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3
115°	469.5	563.5	558.4	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1
117.5°	601.4	624.1	620.7	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1
120°	671.9	669.4	665.8	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3
122.5°	714.0	712.6	708.6	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2
125°	773.2	771.7	767.9	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5
127.5°	827.1	825.1	822.2	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9
130°	861.6	859.4	857.2	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8
132.5°	895.7	893.7	891.5	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3
135°	943.6	941.6	939.8	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8
137.5°	988.3	986.4	984.3	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8
140°	1017.4	1015.6	1013.4	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2
142.5°	1044.3	1042.6	1040.1	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5
145°	1081.8	1080.4	1077.0	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8
147.5°	1114.7	1113.7	1110.3	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8
150°	1134.6	1133.4	1130.2	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2
152.5°	1152.9	1151.7	1148.6	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9
155°	1177.5	1176.3	1173.9	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6
157.5°	1198.2	1196.8	1195.1	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0
160°	1210.4	1209.2	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2
162.5°	1221.5	1220.2	1219.1	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9
165°	1235.3	1233.9	1233.3	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6
167.5°	1246.8	1245.4	1244.8	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3
170°	1252.6	1251.2	1250.8	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9
172.5°	1257.0	1255.6	1255.2	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2
175°	1261.8	1260.3	1259.9	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9
177.5°	1262.6	1261.4	1261.3	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	10.8	12.9	13.4	15.0	14.6	14.9	15.3	15.2	15.1	14.9	14.7
90°	3.1	5.4	7.6	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3
92.5°	18.2	18.0	17.8	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2
95°	52.7	46.0	39.3	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6
97.5°	98.9	80.1	61.2	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3
100°	133.8	106.0	78.2	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3
102.5°	204.0	198.1	192.2	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7
105°	283.7	289.8	295.9	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2
107.5°	359.8	364.7	369.6	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4
110°	408.9	413.1	417.4	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.1	458.9	462.7	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1
115°	528.6	532.0	535.5	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6
117.5°	594.9	598.8	602.7	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7
120°	642.3	645.4	648.4	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3
122.5°	683.4	686.6	689.8	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5
125°	745.1	747.8	750.4	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6
127.5°	801.9	804.8	807.7	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2
130°	838.0	841.2	844.5	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9
132.5°	874.0	876.8	879.6	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6
135°	922.0	925.3	928.5	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7
137.5°	969.1	971.4	973.6	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3
140°	999.9	1001.5	1003.1	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2
142.5°	1026.0	1027.5	1028.9	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9
145°	1065.6	1065.4	1065.2	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3
147.5°	1101.0	1100.3	1099.5	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8
150°	1123.8	1122.3	1120.9	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8
152.5°	1143.3	1141.7	1140.2	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1
155°	1171.8	1169.9	1168.1	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8
157.5°	1194.5	1193.0	1191.4	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5
160°	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6
162.5°	1219.7	1218.5	1217.2	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9
165°	1235.4	1234.2	1232.9	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7
167.5°	1247.1	1245.9	1244.6	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2
170°	1253.6	1252.4	1251.2	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1
172.5°	1258.0	1256.8	1255.6	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4
175°	1263.5	1262.1	1260.6	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2
177.5°	1264.7	1263.6	1262.4	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	15.3	15.5	15.2	15.3	15.8	15.5	15.5
90°	21.3	22.3	23.0	23.4	23.8	24.3	24.7
92.5°	22.8	23.3	23.7	23.9	24.2	24.4	24.7
95°	38.7	39.7	40.1	39.9	39.7	39.5	39.3
97.5°	50.1	50.9	51.4	51.7	51.9	52.2	52.4
100°	56.9	58.6	59.6	60.0	60.4	60.8	61.2
102.5°	59.9	62.0	63.3	63.9	64.4	65.0	65.6
105°	62.4	64.6	66.2	67.0	67.8	68.6	69.4
107.5°	71.2	68.9	68.2	69.0	69.8	70.6	71.4
110°	98.9	78.6	68.9	69.7	70.5	71.3	72.2



TEST NUMBER: P331357

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	181.0	107.0	70.3	70.9	71.6	72.2	72.9
115°	281.6	187.6	133.3	118.7	104.1	89.5	74.9
117.5°	556.0	533.2	497.8	449.8	401.8	353.8	305.8
120°	676.8	679.2	666.7	639.3	611.9	584.5	557.1
122.5°	716.9	718.4	716.5	711.2	705.8	700.5	695.2
125°	776.0	777.4	778.4	779.0	779.6	780.3	780.9
127.5°	831.3	833.4	834.4	834.6	834.7	834.8	834.9
130°	866.1	868.3	869.4	869.2	868.9	868.7	868.5
132.5°	899.5	901.4	902.2	902.0	901.8	901.6	901.4
135°	947.7	949.7	950.5	950.1	949.7	949.3	948.9
137.5°	992.3	994.3	995.0	994.3	993.6	992.9	992.2
140°	1021.1	1022.9	1023.3	1022.3	1021.3	1020.3	1019.2
142.5°	1047.6	1049.3	1049.6	1048.6	1047.6	1046.6	1045.5
145°	1084.7	1086.1	1086.3	1085.3	1084.3	1083.3	1082.3
147.5°	1116.8	1117.9	1118.0	1117.1	1116.3	1115.4	1114.6
150°	1137.1	1138.3	1138.4	1137.4	1136.3	1135.3	1134.3
152.5°	1155.3	1156.5	1156.5	1155.1	1153.8	1152.5	1151.1
155°	1180.0	1181.2	1181.0	1179.4	1177.7	1176.1	1174.5
157.5°	1200.9	1202.3	1202.2	1200.6	1199.0	1197.4	1195.9
160°	1212.9	1214.1	1214.0	1212.5	1211.1	1209.7	1208.3
162.5°	1224.3	1225.7	1225.5	1223.8	1222.0	1220.3	1218.5
165°	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9
167.5°	1249.6	1251.1	1250.8	1249.0	1247.2	1245.4	1243.5
170°	1255.5	1256.9	1256.7	1254.9	1253.0	1251.2	1249.4
172.5°	1259.9	1261.3	1261.1	1259.2	1257.4	1255.6	1253.8
175°	1264.6	1266.0	1265.7	1263.7	1261.7	1259.6	1257.6
177.5°	1264.9	1266.0	1265.8	1264.4	1262.9	1261.4	1260.0
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2

(END OF REPORT)