

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331377

Luminaire Tested: **SA2XXDIP-C865D330U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331377
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5089.3 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331377
CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	93	99	95	92	89	86	84	82	78	76	75	71	70	68	65
2	95	88	82	77	91	84	79	74	77	72	69	70	66	63	63	61	59	55
3	88	78	71	65	83	75	68	63	68	63	59	62	58	55	57	53	51	48
4	81	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	41
5	74	63	55	49	71	60	53	47	55	49	44	51	46	42	47	42	39	37
6	69	57	49	43	65	54	47	42	50	44	39	46	41	37	43	38	35	32
7	64	52	44	38	61	50	42	37	46	40	35	42	37	33	39	35	31	29
8	60	47	39	34	57	45	38	33	42	36	32	39	34	30	36	32	28	26
9	56	43	36	31	53	42	35	30	39	33	29	36	31	27	33	29	26	24
10	52	40	33	28	50	39	32	27	36	30	26	34	28	25	31	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.4	3.2
10°-20°	478.0	9.4
20°-30°	693.8	13.6
30°-40°	732.1	14.4
40°-50°	648.2	12.7
50°-60°	517.3	10.2
60°-70°	351.6	6.9
70°-80°	180.3	3.5
80°-90°	45.1	0.9
90°-100°	73.5	1.4
100°-110°	249.3	4.9
110°-120°	264.8	5.2
120°-130°	218.0	4.3
130°-140°	175.1	3.4
140°-150°	132.3	2.6
150°-160°	93.0	1.8
160°-170°	54.7	1.1
170°-180°	17.8	0.4
0°-30°	1336.2	26.3
0°-40°	2068.3	40.6
0°-60°	3233.8	63.5
0°-90°	3810.8	74.9
90°-120°	587.6	11.5
90°-150°	1113.0	21.9
90°-180°	1279.0	25.1
0°-180°	5089.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	39
90°	12	0	12	0	12	8
95°	40	12	40	12	40	52
105°	398	43	398	43	398	385
115°	524	76	524	76	524	513
125°	425	106	425	106	425	384
135°	352	124	352	124	352	274
145°	281	142	281	142	281	179
155°	236	162	236	162	236	110
165°	207	176	207	176	207	59
175°	187	183	187	183	187	18
180°	184	184	184	184	184	



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	16.1	16.1	16.7	16.1	16.1	16.6	16.5	16.1	16.7	17.3	17.7
90°	11.7	11.7	11.7	11.7	11.7	11.3	10.6	11.3	11.7	12.0	11.7
92.5°	19.6	20.1	19.9	21.0	21.3	23.5	26.4	30.8	38.8	45.9	45.3
95°	40.3	39.9	41.0	43.8	48.4	56.2	71.0	92.6	121.2	138.5	122.6
97.5°	79.3	82.3	87.4	96.1	113.0	138.5	176.7	216.0	248.0	236.4	178.1
100°	126.5	132.9	143.1	158.3	187.6	230.4	278.8	322.6	330.0	279.1	192.2
102.5°	222.6	231.2	244.0	269.9	301.8	347.1	382.5	392.4	360.5	280.5	186.8
105°	398.2	403.1	418.3	440.2	462.2	473.8	469.2	429.3	355.8	261.8	176.3
107.5°	508.7	515.2	518.3	519.5	516.7	499.6	462.9	402.7	324.8	241.7	171.1
110°	542.0	542.4	539.2	532.5	517.3	488.3	443.1	379.8	305.3	232.1	170.0



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	541.4	539.5	533.5	522.3	501.2	467.9	419.6	358.9	291.7	225.9	170.2
115°	524.0	520.8	511.6	495.4	470.3	433.9	387.6	333.2	274.9	219.1	171.7
117.5°	492.8	490.1	480.5	463.3	437.7	403.6	361.6	313.8	264.3	215.7	174.3
120°	472.8	469.2	459.0	442.4	417.6	385.5	348.0	304.2	258.6	213.8	176.0
122.5°	451.8	448.9	439.8	423.4	401.2	372.2	336.7	296.6	253.8	212.6	177.9
125°	425.1	422.2	413.4	400.0	379.5	353.0	321.9	285.5	247.0	210.6	180.9
127.5°	401.6	399.3	391.7	379.1	361.2	336.8	307.5	274.5	240.6	209.4	183.9
130°	388.3	385.5	378.4	366.4	349.1	325.8	297.9	267.5	236.4	208.8	186.2
132.5°	374.5	371.9	365.4	353.4	336.4	314.5	288.8	260.7	233.0	208.5	188.5
135°	352.3	350.9	344.5	332.8	317.6	297.9	274.5	251.2	228.2	208.1	191.2
137.5°	330.5	328.4	322.8	312.8	298.9	281.7	263.2	243.7	224.9	208.0	193.6
140°	315.5	313.4	308.1	298.9	287.6	272.1	255.8	238.8	222.9	207.8	194.7
142.5°	300.5	300.1	295.4	287.0	276.3	263.3	249.3	234.9	221.0	207.8	195.5
145°	281.2	280.2	276.7	270.6	262.2	251.9	241.0	229.3	218.4	207.0	196.4
147.5°	265.1	264.4	262.0	257.2	250.2	242.7	234.2	225.0	215.7	205.8	196.7
150°	255.5	255.1	253.0	248.7	243.4	237.1	229.7	221.9	213.4	204.9	196.4
152.5°	247.3	247.2	245.6	242.0	237.8	232.3	226.0	218.8	211.4	203.5	195.9
155°	236.4	237.1	235.7	233.2	229.3	225.4	220.1	214.5	207.8	201.0	195.0
157.5°	227.1	227.1	226.5	224.4	221.7	218.6	214.2	209.5	204.3	198.5	193.4
160°	221.2	221.2	220.8	219.1	216.6	214.1	210.2	206.3	201.7	196.8	192.6
162.5°	215.5	215.8	215.5	214.3	211.8	209.9	206.6	203.2	199.5	195.4	191.7
165°	207.4	207.8	207.8	206.3	204.9	203.5	201.0	198.6	195.7	192.6	190.1
167.5°	199.9	200.3	200.4	199.6	199.0	197.7	196.0	194.1	192.1	190.1	188.5
170°	195.4	196.1	196.4	195.4	195.0	194.3	192.9	191.9	190.1	188.7	187.6
172.5°	191.7	192.1	192.5	192.0	191.6	191.2	190.1	189.3	188.1	187.0	186.5
175°	186.9	187.6	188.0	187.6	187.6	187.3	186.9	186.6	185.5	185.1	184.8
177.5°	184.0	184.6	184.9	184.9	184.9	184.9	184.6	184.6	184.0	183.7	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	17.8	17.3	17.0	17.8	16.1	16.0	13.6	11.7	11.4	11.2	10.3
90°	9.5	7.1	5.3	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	35.3	24.0	16.0	12.7	10.3	8.8	6.2	4.3	6.2	8.8	10.3
95°	81.6	50.9	34.6	26.1	20.5	17.3	13.8	12.4	13.8	17.3	20.5
97.5°	110.0	67.1	46.7	37.1	30.6	25.8	22.0	20.1	22.0	25.8	30.6
100°	115.9	72.8	54.1	44.2	37.1	31.4	28.3	27.2	28.3	31.4	37.1
102.5°	116.2	77.9	60.6	50.7	43.3	37.7	34.5	33.7	34.5	37.7	43.3
105°	118.0	86.6	70.0	60.1	52.3	47.0	44.5	43.1	44.5	47.0	52.3
107.5°	122.9	95.5	79.4	69.4	61.7	56.8	54.4	53.3	54.4	56.8	61.7
110°	126.8	101.4	85.9	75.6	68.2	63.6	61.5	60.1	61.5	63.6	68.2



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	131.1	107.1	92.1	81.5	74.4	70.1	67.7	66.3	67.7	70.1	74.4
115°	137.4	115.9	100.7	91.2	84.1	79.9	77.7	76.0	77.7	79.9	84.1
117.5°	144.2	124.0	110.0	100.1	93.3	89.5	87.4	86.0	87.4	89.5	93.3
120°	148.8	129.7	115.9	106.0	98.9	95.8	93.6	92.2	93.6	95.8	98.9
122.5°	152.7	135.0	122.1	111.9	104.9	101.4	99.3	98.2	99.3	101.4	104.9
125°	159.0	143.1	130.4	120.5	113.4	109.2	107.1	106.0	107.1	109.2	113.4
127.5°	164.9	150.6	138.2	128.0	121.3	116.6	113.6	112.2	113.6	116.6	121.3
130°	168.5	155.1	142.7	132.9	125.8	120.8	117.3	115.9	117.3	120.8	125.8
132.5°	172.2	159.1	147.3	137.4	130.0	124.8	121.0	119.3	121.0	124.8	130.0
135°	177.0	164.7	153.3	143.5	135.3	130.0	125.8	124.4	125.8	130.0	135.3
137.5°	180.7	169.2	158.0	148.8	140.8	135.1	130.9	129.2	130.9	135.1	140.8
140°	182.7	171.7	161.1	151.9	144.2	138.5	134.3	132.9	134.3	138.5	144.2
142.5°	184.4	173.7	163.4	154.8	147.3	141.6	137.7	136.5	137.7	141.6	147.3
145°	186.6	176.7	167.1	159.4	152.3	147.0	143.5	142.0	143.5	147.0	152.3
147.5°	187.8	179.1	170.1	163.2	157.3	152.4	149.0	148.0	149.0	152.4	157.3
150°	188.3	180.2	172.1	165.7	160.4	155.8	153.0	151.9	153.0	155.8	160.4
152.5°	188.6	181.3	174.0	168.3	163.2	159.2	156.4	155.9	156.4	159.2	163.2
155°	189.0	183.0	177.0	171.7	167.8	163.9	161.8	161.5	161.8	163.9	167.8
157.5°	189.0	184.2	179.1	174.7	171.6	168.2	166.5	166.1	166.5	168.2	171.6
160°	189.0	184.8	180.6	176.7	173.8	171.0	169.6	169.2	169.6	171.0	173.8
162.5°	188.7	185.1	181.4	178.4	175.8	173.6	172.1	172.4	172.1	173.6	175.8
165°	188.0	185.5	182.3	180.2	178.4	176.3	175.6	176.0	175.6	176.3	178.4
167.5°	187.5	185.4	183.1	181.8	180.5	179.1	178.5	178.9	178.5	179.1	180.5
170°	186.9	185.1	183.4	182.3	181.6	180.6	180.2	180.9	180.2	180.6	181.6
172.5°	186.1	184.9	183.7	182.9	182.5	181.4	181.6	182.0	181.6	181.4	182.5
175°	185.1	184.4	183.7	183.4	183.4	182.7	183.0	183.4	183.0	182.7	183.4
177.5°	184.6	184.0	183.7	183.7	183.7	183.2	183.4	184.0	183.4	183.2	183.7
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	9.9	9.6	9.4	9.9	9.8	9.3	8.7	8.6	8.5	7.6	7.6
90°	4.2	5.3	7.1	9.5	11.7	12.0	11.7	11.3	10.6	11.3	11.7
92.5°	12.7	16.0	24.0	35.3	45.3	45.9	38.8	30.8	26.4	23.5	21.3
95°	26.1	34.6	50.9	81.6	122.6	138.5	121.2	92.6	71.0	56.2	48.4
97.5°	37.1	46.7	67.1	110.0	178.1	236.4	248.0	216.0	176.7	138.5	113.0
100°	44.2	54.1	72.8	115.9	192.2	279.1	330.0	322.6	278.8	230.4	187.6
102.5°	50.7	60.6	77.9	116.2	186.8	280.5	360.5	392.4	382.5	347.1	301.8
105°	60.1	70.0	86.6	118.0	176.3	261.8	355.8	429.3	469.2	473.8	462.2
107.5°	69.4	79.4	95.5	122.9	171.1	241.7	324.8	402.7	462.9	499.6	516.7
110°	75.6	85.9	101.4	126.8	170.0	232.1	305.3	379.8	443.1	488.3	517.3



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	81.5	92.1	107.1	131.1	170.2	225.9	291.7	358.9	419.6	467.9	501.2
115°	91.2	100.7	115.9	137.4	171.7	219.1	274.9	333.2	387.6	433.9	470.3
117.5°	100.1	110.0	124.0	144.2	174.3	215.7	264.3	313.8	361.6	403.6	437.7
120°	106.0	115.9	129.7	148.8	176.0	213.8	258.6	304.2	348.0	385.5	417.6
122.5°	111.9	122.1	135.0	152.7	177.9	212.6	253.8	296.6	336.7	372.2	401.2
125°	120.5	130.4	143.1	159.0	180.9	210.6	247.0	285.5	321.9	353.0	379.5
127.5°	128.0	138.2	150.6	164.9	183.9	209.4	240.6	274.5	307.5	336.8	361.2
130°	132.9	142.7	155.1	168.5	186.2	208.8	236.4	267.5	297.9	325.8	349.1
132.5°	137.4	147.3	159.1	172.2	188.5	208.5	233.0	260.7	288.8	314.5	336.4
135°	143.5	153.3	164.7	177.0	191.2	208.1	228.2	251.2	274.5	297.9	317.6
137.5°	148.8	158.0	169.2	180.7	193.6	208.0	224.9	243.7	263.2	281.7	298.9
140°	151.9	161.1	171.7	182.7	194.7	207.8	222.9	238.8	255.8	272.1	287.6
142.5°	154.8	163.4	173.7	184.4	195.5	207.8	221.0	234.9	249.3	263.3	276.3
145°	159.4	167.1	176.7	186.6	196.4	207.0	218.4	229.3	241.0	251.9	262.2
147.5°	163.2	170.1	179.1	187.8	196.7	205.8	215.7	225.0	234.2	242.7	250.2
150°	165.7	172.1	180.2	188.3	196.4	204.9	213.4	221.9	229.7	237.1	243.4
152.5°	168.3	174.0	181.3	188.6	195.9	203.5	211.4	218.8	226.0	232.3	237.8
155°	171.7	177.0	183.0	189.0	195.0	201.0	207.8	214.5	220.1	225.4	229.3
157.5°	174.7	179.1	184.2	189.0	193.4	198.5	204.3	209.5	214.2	218.6	221.7
160°	176.7	180.6	184.8	189.0	192.6	196.8	201.7	206.3	210.2	214.1	216.6
162.5°	178.4	181.4	185.1	188.7	191.7	195.4	199.5	203.2	206.6	209.9	211.8
165°	180.2	182.3	185.5	188.0	190.1	192.6	195.7	198.6	201.0	203.5	204.9
167.5°	181.8	183.1	185.4	187.5	188.5	190.1	192.1	194.1	196.0	197.7	199.0
170°	182.3	183.4	185.1	186.9	187.6	188.7	190.1	191.9	192.9	194.3	195.0
172.5°	182.9	183.7	184.9	186.1	186.5	187.0	188.1	189.3	190.1	191.2	191.6
175°	183.4	183.7	184.4	185.1	184.8	185.1	185.5	186.6	186.9	187.3	187.6
177.5°	183.7	183.7	184.0	184.6	184.0	183.7	184.0	184.6	184.6	184.9	184.9
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	7.6	7.1	7.1	6.6	7.1	7.1	7.6	7.6	7.6	8.5	8.6
90°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.3	10.6	11.3
92.5°	21.0	19.9	20.1	19.6	20.1	19.9	21.0	21.3	23.5	26.4	30.8
95°	43.8	41.0	39.9	40.3	39.9	41.0	43.8	48.4	56.2	71.0	92.6
97.5°	96.1	87.4	82.3	79.3	82.3	87.4	96.1	113.0	138.5	176.7	216.0
100°	158.3	143.1	132.9	126.5	132.9	143.1	158.3	187.6	230.4	278.8	322.6
102.5°	269.9	244.0	231.2	222.6	231.2	244.0	269.9	301.8	347.1	382.5	392.4
105°	440.2	418.3	403.1	398.2	403.1	418.3	440.2	462.2	473.8	469.2	429.3
107.5°	519.5	518.3	515.2	508.7	515.2	518.3	519.5	516.7	499.6	462.9	402.7
110°	532.5	539.2	542.4	542.0	542.4	539.2	532.5	517.3	488.3	443.1	379.8



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.3	533.5	539.5	541.4	539.5	533.5	522.3	501.2	467.9	419.6	358.9
115°	495.4	511.6	520.8	524.0	520.8	511.6	495.4	470.3	433.9	387.6	333.2
117.5°	463.3	480.5	490.1	492.8	490.1	480.5	463.3	437.7	403.6	361.6	313.8
120°	442.4	459.0	469.2	472.8	469.2	459.0	442.4	417.6	385.5	348.0	304.2
122.5°	423.4	439.8	448.9	451.8	448.9	439.8	423.4	401.2	372.2	336.7	296.6
125°	400.0	413.4	422.2	425.1	422.2	413.4	400.0	379.5	353.0	321.9	285.5
127.5°	379.1	391.7	399.3	401.6	399.3	391.7	379.1	361.2	336.8	307.5	274.5
130°	366.4	378.4	385.5	388.3	385.5	378.4	366.4	349.1	325.8	297.9	267.5
132.5°	353.4	365.4	371.9	374.5	371.9	365.4	353.4	336.4	314.5	288.8	260.7
135°	332.8	344.5	350.9	352.3	350.9	344.5	332.8	317.6	297.9	274.5	251.2
137.5°	312.8	322.8	328.4	330.5	328.4	322.8	312.8	298.9	281.7	263.2	243.7
140°	298.9	308.1	313.4	315.5	313.4	308.1	298.9	287.6	272.1	255.8	238.8
142.5°	287.0	295.4	300.1	300.5	300.1	295.4	287.0	276.3	263.3	249.3	234.9
145°	270.6	276.7	280.2	281.2	280.2	276.7	270.6	262.2	251.9	241.0	229.3
147.5°	257.2	262.0	264.4	265.1	264.4	262.0	257.2	250.2	242.7	234.2	225.0
150°	248.7	253.0	255.1	255.5	255.1	253.0	248.7	243.4	237.1	229.7	221.9
152.5°	242.0	245.6	247.2	247.3	247.2	245.6	242.0	237.8	232.3	226.0	218.8
155°	233.2	235.7	237.1	236.4	237.1	235.7	233.2	229.3	225.4	220.1	214.5
157.5°	224.4	226.5	227.1	227.1	227.1	226.5	224.4	221.7	218.6	214.2	209.5
160°	219.1	220.8	221.2	221.2	221.2	220.8	219.1	216.6	214.1	210.2	206.3
162.5°	214.3	215.5	215.8	215.5	215.8	215.5	214.3	211.8	209.9	206.6	203.2
165°	206.3	207.8	207.8	207.4	207.8	207.8	206.3	204.9	203.5	201.0	198.6
167.5°	199.6	200.4	200.3	199.9	200.3	200.4	199.6	199.0	197.7	196.0	194.1
170°	195.4	196.4	196.1	195.4	196.1	196.4	195.4	195.0	194.3	192.9	191.9
172.5°	192.0	192.5	192.1	191.7	192.1	192.5	192.0	191.6	191.2	190.1	189.3
175°	187.6	188.0	187.6	186.9	187.6	188.0	187.6	187.6	187.3	186.9	186.6
177.5°	184.9	184.9	184.6	184.0	184.6	184.9	184.9	184.9	184.9	184.6	184.6
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	8.7	9.3	9.8	9.9	9.4	9.6	9.9	10.3	11.2	11.4	11.7
90°	11.7	12.0	11.7	9.5	7.1	5.3	4.2	3.5	2.8	1.4	0.4
92.5°	38.8	45.9	45.3	35.3	24.0	16.0	12.7	10.3	8.8	6.2	4.3
95°	121.2	138.5	122.6	81.6	50.9	34.6	26.1	20.5	17.3	13.8	12.4
97.5°	248.0	236.4	178.1	110.0	67.1	46.7	37.1	30.6	25.8	22.0	20.1
100°	330.0	279.1	192.2	115.9	72.8	54.1	44.2	37.1	31.4	28.3	27.2
102.5°	360.5	280.5	186.8	116.2	77.9	60.6	50.7	43.3	37.7	34.5	33.7
105°	355.8	261.8	176.3	118.0	86.6	70.0	60.1	52.3	47.0	44.5	43.1
107.5°	324.8	241.7	171.1	122.9	95.5	79.4	69.4	61.7	56.8	54.4	53.3
110°	305.3	232.1	170.0	126.8	101.4	85.9	75.6	68.2	63.6	61.5	60.1



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	291.7	225.9	170.2	131.1	107.1	92.1	81.5	74.4	70.1	67.7	66.3
115°	274.9	219.1	171.7	137.4	115.9	100.7	91.2	84.1	79.9	77.7	76.0
117.5°	264.3	215.7	174.3	144.2	124.0	110.0	100.1	93.3	89.5	87.4	86.0
120°	258.6	213.8	176.0	148.8	129.7	115.9	106.0	98.9	95.8	93.6	92.2
122.5°	253.8	212.6	177.9	152.7	135.0	122.1	111.9	104.9	101.4	99.3	98.2
125°	247.0	210.6	180.9	159.0	143.1	130.4	120.5	113.4	109.2	107.1	106.0
127.5°	240.6	209.4	183.9	164.9	150.6	138.2	128.0	121.3	116.6	113.6	112.2
130°	236.4	208.8	186.2	168.5	155.1	142.7	132.9	125.8	120.8	117.3	115.9
132.5°	233.0	208.5	188.5	172.2	159.1	147.3	137.4	130.0	124.8	121.0	119.3
135°	228.2	208.1	191.2	177.0	164.7	153.3	143.5	135.3	130.0	125.8	124.4
137.5°	224.9	208.0	193.6	180.7	169.2	158.0	148.8	140.8	135.1	130.9	129.2
140°	222.9	207.8	194.7	182.7	171.7	161.1	151.9	144.2	138.5	134.3	132.9
142.5°	221.0	207.8	195.5	184.4	173.7	163.4	154.8	147.3	141.6	137.7	136.5
145°	218.4	207.0	196.4	186.6	176.7	167.1	159.4	152.3	147.0	143.5	142.0
147.5°	215.7	205.8	196.7	187.8	179.1	170.1	163.2	157.3	152.4	149.0	148.0
150°	213.4	204.9	196.4	188.3	180.2	172.1	165.7	160.4	155.8	153.0	151.9
152.5°	211.4	203.5	195.9	188.6	181.3	174.0	168.3	163.2	159.2	156.4	155.9
155°	207.8	201.0	195.0	189.0	183.0	177.0	171.7	167.8	163.9	161.8	161.5
157.5°	204.3	198.5	193.4	189.0	184.2	179.1	174.7	171.6	168.2	166.5	166.1
160°	201.7	196.8	192.6	189.0	184.8	180.6	176.7	173.8	171.0	169.6	169.2
162.5°	199.5	195.4	191.7	188.7	185.1	181.4	178.4	175.8	173.6	172.1	172.4
165°	195.7	192.6	190.1	188.0	185.5	182.3	180.2	178.4	176.3	175.6	176.0
167.5°	192.1	190.1	188.5	187.5	185.4	183.1	181.8	180.5	179.1	178.5	178.9
170°	190.1	188.7	187.6	186.9	185.1	183.4	182.3	181.6	180.6	180.2	180.9
172.5°	188.1	187.0	186.5	186.1	184.9	183.7	182.9	182.5	181.4	181.6	182.0
175°	185.5	185.1	184.8	185.1	184.4	183.7	183.4	183.4	182.7	183.0	183.4
177.5°	184.0	183.7	184.0	184.6	184.0	183.7	183.7	183.7	183.2	183.4	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	13.6	16.0	16.1	17.8	17.0	17.3	17.8	17.7	17.3	16.7	16.1
90°	1.4	2.8	3.5	4.2	5.3	7.1	9.5	11.7	12.0	11.7	11.3
92.5°	6.2	8.8	10.3	12.7	16.0	24.0	35.3	45.3	45.9	38.8	30.8
95°	13.8	17.3	20.5	26.1	34.6	50.9	81.6	122.6	138.5	121.2	92.6
97.5°	22.0	25.8	30.6	37.1	46.7	67.1	110.0	178.1	236.4	248.0	216.0
100°	28.3	31.4	37.1	44.2	54.1	72.8	115.9	192.2	279.1	330.0	322.6
102.5°	34.5	37.7	43.3	50.7	60.6	77.9	116.2	186.8	280.5	360.5	392.4
105°	44.5	47.0	52.3	60.1	70.0	86.6	118.0	176.3	261.8	355.8	429.3
107.5°	54.4	56.8	61.7	69.4	79.4	95.5	122.9	171.1	241.7	324.8	402.7
110°	61.5	63.6	68.2	75.6	85.9	101.4	126.8	170.0	232.1	305.3	379.8



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	67.7	70.1	74.4	81.5	92.1	107.1	131.1	170.2	225.9	291.7	358.9
115°	77.7	79.9	84.1	91.2	100.7	115.9	137.4	171.7	219.1	274.9	333.2
117.5°	87.4	89.5	93.3	100.1	110.0	124.0	144.2	174.3	215.7	264.3	313.8
120°	93.6	95.8	98.9	106.0	115.9	129.7	148.8	176.0	213.8	258.6	304.2
122.5°	99.3	101.4	104.9	111.9	122.1	135.0	152.7	177.9	212.6	253.8	296.6
125°	107.1	109.2	113.4	120.5	130.4	143.1	159.0	180.9	210.6	247.0	285.5
127.5°	113.6	116.6	121.3	128.0	138.2	150.6	164.9	183.9	209.4	240.6	274.5
130°	117.3	120.8	125.8	132.9	142.7	155.1	168.5	186.2	208.8	236.4	267.5
132.5°	121.0	124.8	130.0	137.4	147.3	159.1	172.2	188.5	208.5	233.0	260.7
135°	125.8	130.0	135.3	143.5	153.3	164.7	177.0	191.2	208.1	228.2	251.2
137.5°	130.9	135.1	140.8	148.8	158.0	169.2	180.7	193.6	208.0	224.9	243.7
140°	134.3	138.5	144.2	151.9	161.1	171.7	182.7	194.7	207.8	222.9	238.8
142.5°	137.7	141.6	147.3	154.8	163.4	173.7	184.4	195.5	207.8	221.0	234.9
145°	143.5	147.0	152.3	159.4	167.1	176.7	186.6	196.4	207.0	218.4	229.3
147.5°	149.0	152.4	157.3	163.2	170.1	179.1	187.8	196.7	205.8	215.7	225.0
150°	153.0	155.8	160.4	165.7	172.1	180.2	188.3	196.4	204.9	213.4	221.9
152.5°	156.4	159.2	163.2	168.3	174.0	181.3	188.6	195.9	203.5	211.4	218.8
155°	161.8	163.9	167.8	171.7	177.0	183.0	189.0	195.0	201.0	207.8	214.5
157.5°	166.5	168.2	171.6	174.7	179.1	184.2	189.0	193.4	198.5	204.3	209.5
160°	169.6	171.0	173.8	176.7	180.6	184.8	189.0	192.6	196.8	201.7	206.3
162.5°	172.1	173.6	175.8	178.4	181.4	185.1	188.7	191.7	195.4	199.5	203.2
165°	175.6	176.3	178.4	180.2	182.3	185.5	188.0	190.1	192.6	195.7	198.6
167.5°	178.5	179.1	180.5	181.8	183.1	185.4	187.5	188.5	190.1	192.1	194.1
170°	180.2	180.6	181.6	182.3	183.4	185.1	186.9	187.6	188.7	190.1	191.9
172.5°	181.6	181.4	182.5	182.9	183.7	184.9	186.1	186.5	187.0	188.1	189.3
175°	183.0	182.7	183.4	183.4	183.7	184.4	185.1	184.8	185.1	185.5	186.6
177.5°	183.4	183.2	183.7	183.7	183.7	184.0	184.6	184.0	183.7	184.0	184.6
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	16.5	16.6	16.1	16.1	16.7	16.1	16.1
90°	10.6	11.3	11.7	11.7	11.7	11.7	11.7
92.5°	26.4	23.5	21.3	21.0	19.9	20.1	19.6
95°	71.0	56.2	48.4	43.8	41.0	39.9	40.3
97.5°	176.7	138.5	113.0	96.1	87.4	82.3	79.3
100°	278.8	230.4	187.6	158.3	143.1	132.9	126.5
102.5°	382.5	347.1	301.8	269.9	244.0	231.2	222.6
105°	469.2	473.8	462.2	440.2	418.3	403.1	398.2
107.5°	462.9	499.6	516.7	519.5	518.3	515.2	508.7
110°	443.1	488.3	517.3	532.5	539.2	542.4	542.0



TEST NUMBER: P331377

CATALOG NUMBER: SA2XXDIP-C865D330U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	419.6	467.9	501.2	522.3	533.5	539.5	541.4
115°	387.6	433.9	470.3	495.4	511.6	520.8	524.0
117.5°	361.6	403.6	437.7	463.3	480.5	490.1	492.8
120°	348.0	385.5	417.6	442.4	459.0	469.2	472.8
122.5°	336.7	372.2	401.2	423.4	439.8	448.9	451.8
125°	321.9	353.0	379.5	400.0	413.4	422.2	425.1
127.5°	307.5	336.8	361.2	379.1	391.7	399.3	401.6
130°	297.9	325.8	349.1	366.4	378.4	385.5	388.3
132.5°	288.8	314.5	336.4	353.4	365.4	371.9	374.5
135°	274.5	297.9	317.6	332.8	344.5	350.9	352.3
137.5°	263.2	281.7	298.9	312.8	322.8	328.4	330.5
140°	255.8	272.1	287.6	298.9	308.1	313.4	315.5
142.5°	249.3	263.3	276.3	287.0	295.4	300.1	300.5
145°	241.0	251.9	262.2	270.6	276.7	280.2	281.2
147.5°	234.2	242.7	250.2	257.2	262.0	264.4	265.1
150°	229.7	237.1	243.4	248.7	253.0	255.1	255.5
152.5°	226.0	232.3	237.8	242.0	245.6	247.2	247.3
155°	220.1	225.4	229.3	233.2	235.7	237.1	236.4
157.5°	214.2	218.6	221.7	224.4	226.5	227.1	227.1
160°	210.2	214.1	216.6	219.1	220.8	221.2	221.2
162.5°	206.6	209.9	211.8	214.3	215.5	215.8	215.5
165°	201.0	203.5	204.9	206.3	207.8	207.8	207.4
167.5°	196.0	197.7	199.0	199.6	200.4	200.3	199.9
170°	192.9	194.3	195.0	195.4	196.4	196.1	195.4
172.5°	190.1	191.2	191.6	192.0	192.5	192.1	191.7
175°	186.9	187.3	187.6	187.6	188.0	187.6	186.9
177.5°	184.6	184.9	184.9	184.9	184.9	184.6	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7

(END OF REPORT)