

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331703-840

Luminaire Tested: **SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331703-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6235.4 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331703-840
CATALOG NUMBER: SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331703-840

CATALOG NUMBER: SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	38	32
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18392	18392	18392
5°	18462	18162	18263
10°	18321	17864	17713
15°	18111	17336	16836
20°	17819	16579	15747
25°	17521	15720	14694
30°	17107	14838	13340
35°	16703	13878	12151
40°	16297	12886	10777
45°	15819	11768	9533
50°	15330	10643	8312
55°	14829	9433	7139
60°	14247	8157	5926
65°	13589	6854	5398
70°	12798	5646	4961
75°	11834	5147	4629
80°	10451	4603	4212
85°	8207	3631	3631



TEST NUMBER: P331703-840

CATALOG NUMBER: SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	1.7
10°-20°	292.8	4.7
20°-30°	411.1	6.6
30°-40°	448.3	7.2
40°-50°	412.2	6.6
50°-60°	323.8	5.2
60°-70°	211.1	3.4
70°-80°	108.8	1.7
80°-90°	33.8	0.5
90°-100°	88.1	1.4
100°-110°	273.6	4.4
110°-120°	467.6	7.5
120°-130°	614.9	9.9
130°-140°	690.2	11.1
140°-150°	676.7	10.9
150°-160°	567.6	9.1
160°-170°	376.5	6.0
170°-180°	131.6	2.1
0°-30°	810.5	13.0
0°-40°	1258.9	20.2
0°-60°	1994.8	32.0
0°-90°	2348.5	37.7
90°-120°	829.3	13.3
90°-150°	2811.1	45.1
90°-180°	3887.0	62.3
0°-180°	6235.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1121	1129	1127	108
15°	1084	1071	1037	1018	1007	305
25°	984	949	882	842	825	452
35°	847	793	704	642	616	530
45°	693	622	515	445	418	535
55°	527	445	335	276	254	471
65°	356	272	179	146	141	352
75°	190	120	82	76	74	201
85°	44	24	20	20	20	52
90°	1	16	41	39	40	5
95°	61	72	75	75	73	70
105°	252	256	258	260	260	266
115°	469	476	474	473	469	464
125°	683	692	690	686	685	610
135°	883	896	899	897	894	682
145°	1072	1080	1087	1088	1084	670
155°	1226	1229	1233	1238	1235	564
165°	1334	1333	1333	1340	1335	376
175°	1388	1384	1382	1389	1383	132
180°	1390	1390	1390	1390	1390	



TEST NUMBER: P331703-840

CATALOG NUMBER: SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1143.3	1142.4	1141.5	1140.5	1139.6	1138.1	1136.1	1134.1	1132.2	1130.1	1132.0
5°	1139.1	1138.0	1136.9	1135.7	1134.6	1132.6	1129.5	1126.6	1123.6	1120.6	1122.7
7.5°	1127.4	1126.0	1124.6	1123.2	1121.8	1119.2	1115.8	1112.4	1108.8	1105.4	1105.9
10°	1117.5	1115.9	1114.3	1112.7	1111.1	1108.0	1103.4	1098.8	1094.3	1089.6	1089.0
12.5°	1105.1	1103.2	1101.2	1099.2	1097.2	1093.4	1087.5	1081.7	1075.7	1069.9	1068.6
15°	1083.5	1081.0	1078.4	1075.9	1073.4	1068.2	1060.5	1052.7	1044.9	1037.1	1032.8
17.5°	1056.9	1053.1	1049.2	1045.3	1041.5	1034.6	1024.6	1014.6	1004.6	994.6	989.5
20°	1037.1	1032.5	1027.9	1023.4	1018.8	1010.8	999.3	987.8	976.4	964.9	959.2
22.5°	1015.6	1010.6	1005.4	1000.3	995.1	986.1	973.2	960.3	947.4	934.4	927.1
25°	983.5	976.1	968.9	961.5	954.2	942.9	927.9	912.7	897.6	882.4	873.0
27.5°	944.7	936.8	928.8	920.8	912.8	900.3	883.3	866.3	849.2	832.1	821.2
30°	917.6	908.8	900.1	891.4	882.7	869.2	850.8	832.5	814.2	795.9	784.2
32.5°	891.1	880.9	870.8	860.6	850.4	836.0	817.3	798.6	779.9	761.2	747.9
35°	847.4	835.8	824.0	812.3	800.7	784.8	764.6	744.5	724.3	704.1	689.6
37.5°	803.8	790.8	778.0	765.2	752.3	735.2	713.8	692.3	670.8	649.2	633.4
40°	773.2	759.4	745.7	732.0	718.2	700.2	678.0	655.8	633.6	611.4	595.1
42.5°	741.8	727.4	712.9	698.4	684.0	665.2	642.3	619.4	596.3	573.4	556.5
45°	692.8	677.4	662.1	646.7	631.4	611.7	587.6	563.6	539.5	515.4	499.2
47.5°	644.9	628.6	612.4	596.1	579.9	559.4	534.5	509.7	484.8	460.0	443.8
50°	610.3	594.0	577.7	561.5	545.2	524.5	499.3	474.1	448.9	423.7	407.9
52.5°	576.5	559.5	542.5	525.5	508.5	487.7	463.0	438.4	413.7	389.1	373.9
55°	526.8	509.0	491.1	473.2	455.3	434.0	409.3	384.6	359.8	335.1	321.3
57.5°	475.8	457.6	439.2	420.9	402.5	381.5	357.7	334.0	310.1	286.4	273.8
60°	441.2	422.9	404.6	386.3	367.9	347.0	323.4	299.7	276.2	252.6	240.9
62.5°	407.4	389.1	370.7	352.4	334.1	313.7	291.2	268.7	246.2	223.7	212.6
65°	355.7	337.1	318.5	300.0	281.4	261.9	241.3	220.7	200.0	179.4	171.6
67.5°	305.8	287.3	268.9	250.5	232.1	213.6	195.0	176.5	157.9	139.4	135.8
70°	271.1	253.3	235.4	217.5	199.7	182.8	167.0	151.2	135.4	119.6	117.2
72.5°	238.1	221.0	203.9	186.7	169.6	154.7	142.0	129.3	116.6	103.9	102.0
75°	189.7	173.7	157.6	141.6	125.5	113.6	105.8	98.1	90.3	82.5	80.9
77.5°	142.1	127.9	113.9	99.9	85.8	76.9	73.1	69.4	65.6	61.9	60.9
80°	112.4	100.7	89.0	77.4	65.6	58.7	56.4	54.0	51.8	49.5	48.6
82.5°	85.1	76.0	67.0	57.8	48.7	43.3	41.8	40.2	38.7	37.2	36.6
85°	44.3	39.5	34.7	29.9	25.0	22.3	21.6	21.0	20.3	19.6	19.6
87.5°	13.4	12.6	11.7	10.9	10.1	10.2	11.4	12.5	13.6	14.8	14.5
90°	1.2	4.3	7.5	10.6	13.7	18.1	23.8	29.6	35.3	41.1	40.5
92.5°	20.9	23.1	25.4	27.8	30.1	31.9	33.2	34.6	36.0	37.3	37.4
95°	61.0	63.6	66.2	68.8	71.4	73.0	73.5	74.0	74.5	75.0	75.0
97.5°	111.5	113.7	116.0	118.4	120.6	122.3	123.2	124.2	125.2	126.2	126.2
100°	149.0	151.1	153.2	155.2	157.3	158.8	159.6	160.3	161.1	161.9	161.9
102.5°	188.4	190.1	191.8	193.4	195.1	196.4	197.4	198.3	199.3	200.4	200.6
105°	252.2	253.0	253.8	254.6	255.3	256.0	256.5	257.0	257.5	258.0	258.6
107.5°	316.5	317.6	318.8	319.9	321.0	321.6	321.6	321.6	321.6	321.6	321.8
110°	357.8	359.3	360.9	362.4	364.1	364.9	364.9	364.9	364.9	364.9	364.9



TEST NUMBER: P331703-840

CATALOG NUMBER: SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	402.8	404.3	406.0	407.5	409.1	409.8	409.5	409.3	409.1	408.9	408.3
115°	469.2	470.8	472.3	473.9	475.4	475.9	475.4	474.9	474.4	473.9	473.6
117.5°	535.3	537.5	539.6	541.6	543.7	544.0	542.6	541.1	539.7	538.2	537.6
120°	579.5	581.6	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5	579.5
122.5°	619.9	622.4	624.8	627.3	629.9	630.4	628.9	627.4	626.0	624.5	623.9
125°	682.7	685.1	687.4	689.7	692.1	692.9	692.1	691.4	690.5	689.7	688.9
127.5°	744.0	746.9	749.9	752.9	755.8	756.9	755.9	755.0	754.1	753.1	752.1
130°	782.4	785.8	789.2	792.5	796.0	797.4	796.9	796.4	795.9	795.4	794.8
132.5°	825.6	828.4	831.1	833.8	836.7	838.1	838.2	838.3	838.4	838.5	837.4
135°	883.3	886.2	889.1	891.9	894.7	896.5	897.0	897.5	898.1	898.6	898.3
137.5°	944.0	946.4	948.8	951.1	953.4	954.9	955.6	956.3	956.9	957.7	957.5
140°	980.7	983.0	985.3	987.7	990.1	991.9	993.2	994.5	995.8	997.0	997.0
142.5°	1018.2	1020.6	1022.9	1025.2	1027.5	1029.2	1030.1	1031.0	1031.9	1032.8	1033.0
145°	1072.2	1074.0	1075.8	1077.6	1079.4	1081.2	1082.7	1084.3	1085.8	1087.4	1087.6
147.5°	1120.2	1122.5	1124.6	1126.8	1129.0	1130.6	1131.7	1132.8	1133.8	1134.8	1135.4
150°	1153.1	1154.7	1156.2	1157.8	1159.3	1160.6	1161.7	1162.8	1163.8	1164.9	1165.6
152.5°	1182.1	1183.8	1185.3	1186.9	1188.4	1189.8	1191.1	1192.3	1193.7	1194.9	1195.9
155°	1225.9	1226.6	1227.4	1228.2	1229.0	1229.7	1230.5	1231.3	1232.1	1232.8	1234.2
157.5°	1263.1	1263.6	1264.1	1264.7	1265.3	1265.7	1266.2	1266.7	1267.1	1267.6	1269.4
160°	1285.7	1286.2	1286.7	1287.2	1287.8	1288.1	1288.4	1288.7	1288.9	1289.2	1290.7
162.5°	1306.3	1306.4	1306.5	1306.6	1306.8	1306.9	1307.2	1307.4	1307.7	1308.0	1309.7
165°	1333.7	1333.5	1333.2	1332.9	1332.7	1332.6	1332.6	1332.6	1332.6	1332.6	1334.4
167.5°	1356.8	1355.9	1355.1	1354.4	1353.6	1353.2	1353.1	1353.1	1353.0	1353.0	1354.8
170°	1369.0	1368.2	1367.4	1366.5	1365.8	1365.3	1365.0	1364.7	1364.5	1364.2	1366.0
172.5°	1377.4	1376.6	1375.8	1375.0	1374.2	1373.7	1373.5	1373.2	1372.9	1372.7	1374.5
175°	1387.8	1386.9	1386.1	1385.3	1384.6	1383.9	1383.4	1382.9	1382.4	1381.8	1383.7
177.5°	1391.9	1391.3	1390.7	1390.1	1389.5	1388.9	1388.5	1388.1	1387.7	1387.3	1388.5
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331703-840

CATALOG NUMBER: SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1	1139.1
2.5°	1133.8	1135.6	1137.4	1138.1	1137.8	1137.4	1137.1	1136.7
5°	1124.7	1126.8	1128.8	1129.5	1128.8	1128.1	1127.5	1126.8
7.5°	1106.5	1107.1	1107.7	1107.4	1106.2	1105.1	1103.9	1102.7
10°	1088.3	1087.6	1086.9	1085.9	1084.5	1083.2	1081.8	1080.4
12.5°	1067.4	1066.2	1064.9	1063.2	1060.9	1058.6	1056.3	1054.0
15°	1028.4	1024.0	1019.7	1016.3	1014.1	1011.8	1009.5	1007.2
17.5°	984.3	979.1	973.9	969.4	965.4	961.5	957.6	953.6
20°	953.5	947.8	942.0	936.6	931.6	926.6	921.5	916.5
22.5°	919.7	912.3	904.9	899.4	895.5	891.8	888.1	884.3
25°	863.6	854.2	844.9	838.5	835.1	831.6	828.2	824.8
27.5°	810.2	799.3	788.4	780.1	774.7	769.2	763.8	758.3
30°	772.5	760.8	749.1	740.2	734.0	727.8	721.6	715.5
32.5°	734.6	721.2	707.9	698.3	692.5	686.7	680.9	675.1
35°	675.3	660.9	646.4	636.6	631.6	626.5	621.6	616.5
37.5°	617.4	601.6	585.7	574.8	569.1	563.3	557.5	551.8
40°	578.8	562.5	546.2	535.1	529.2	523.2	517.3	511.3
42.5°	539.8	522.9	506.1	494.8	489.1	483.3	477.6	471.7
45°	482.9	466.7	450.4	439.5	434.0	428.5	423.0	417.5
47.5°	427.7	411.5	395.3	384.8	379.7	374.8	369.7	364.8
50°	392.1	376.3	360.5	350.1	345.4	340.5	335.8	330.9
52.5°	358.6	343.3	328.0	318.2	313.8	309.3	304.9	300.4
55°	307.6	293.8	280.0	271.0	266.7	262.3	257.9	253.6
57.5°	261.2	248.6	236.0	227.8	224.2	220.6	216.8	213.2
60°	229.2	217.5	205.8	198.1	194.5	190.9	187.1	183.5
62.5°	201.5	190.3	179.2	172.5	170.3	168.1	165.9	163.7
65°	163.8	156.0	148.2	144.0	143.3	142.6	141.9	141.3
67.5°	132.2	128.7	125.1	122.9	122.2	121.5	120.8	120.0
70°	115.0	112.7	110.4	108.9	107.9	106.9	106.0	105.1
72.5°	100.1	98.2	96.2	95.0	94.4	93.9	93.3	92.8
75°	79.3	77.7	76.0	75.1	74.9	74.7	74.4	74.2
77.5°	60.0	59.1	58.2	57.6	57.2	56.9	56.5	56.0
80°	47.7	46.8	45.8	45.3	45.3	45.3	45.3	45.3
82.5°	36.1	35.4	34.9	34.6	34.6	34.6	34.6	34.6
85°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6
87.5°	14.2	13.9	13.6	13.5	13.6	13.6	13.7	13.7
90°	40.0	39.5	39.0	38.9	39.1	39.4	39.6	39.9
92.5°	37.5	37.6	37.8	37.8	37.9	37.9	38.0	38.0
95°	75.0	75.0	75.0	74.8	74.3	73.8	73.2	72.7
97.5°	126.2	126.2	126.2	126.2	126.1	126.1	126.0	126.0
100°	161.9	161.9	161.9	161.8	161.5	161.3	161.0	160.7
102.5°	200.8	201.0	201.2	201.2	200.9	200.7	200.4	200.2
105°	259.1	259.6	260.1	260.4	260.4	260.4	260.4	260.4
107.5°	322.0	322.2	322.4	321.9	320.8	319.6	318.4	317.2
110°	364.9	364.9	364.9	364.5	363.7	362.8	362.0	361.3



TEST NUMBER: P331703-840

CATALOG NUMBER: SA2XXRDIP-C675D1080U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	407.7	407.1	406.5	405.9	405.3	404.7	404.1	403.5
115°	473.4	473.1	472.8	472.3	471.6	470.8	470.0	469.2
117.5°	536.9	536.3	535.7	535.0	534.2	533.4	532.6	531.9
120°	579.5	579.5	579.5	579.1	578.3	577.5	576.7	575.9
122.5°	623.3	622.7	622.0	621.5	620.9	620.3	619.8	619.1
125°	688.2	687.4	686.6	686.1	685.8	685.6	685.3	685.1
127.5°	751.2	750.2	749.3	748.4	747.6	746.8	746.0	745.1
130°	794.3	793.8	793.2	792.4	791.4	790.3	789.3	788.3
132.5°	836.2	835.1	833.9	832.9	832.1	831.2	830.4	829.6
135°	898.1	897.8	897.5	897.0	896.2	895.4	894.6	893.8
137.5°	957.3	957.0	956.8	956.2	955.1	954.1	953.1	952.0
140°	997.0	997.0	997.0	996.5	995.5	994.5	993.4	992.4
142.5°	1033.2	1033.4	1033.6	1033.2	1032.1	1031.1	1030.1	1029.0
145°	1087.9	1088.2	1088.4	1088.0	1087.0	1086.0	1084.9	1083.9
147.5°	1136.0	1136.5	1137.1	1136.9	1135.9	1134.9	1133.9	1133.0
150°	1166.4	1167.2	1168.0	1168.0	1167.2	1166.4	1165.6	1164.9
152.5°	1196.9	1197.8	1198.8	1198.8	1197.8	1196.9	1195.9	1194.9
155°	1235.5	1236.8	1238.1	1238.3	1237.6	1236.8	1236.0	1235.2
157.5°	1271.1	1272.9	1274.7	1275.0	1273.6	1272.4	1271.2	1269.9
160°	1292.3	1293.8	1295.5	1295.7	1294.6	1293.6	1292.5	1291.5
162.5°	1311.5	1313.2	1315.0	1315.2	1314.0	1312.8	1311.5	1310.3
165°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1334.9
167.5°	1356.7	1358.5	1360.3	1360.5	1359.2	1357.8	1356.5	1355.1
170°	1367.9	1369.7	1371.5	1371.7	1370.1	1368.6	1367.0	1365.4
172.5°	1376.3	1378.2	1380.0	1380.1	1378.6	1377.0	1375.4	1373.8
175°	1385.5	1387.4	1389.2	1389.3	1387.8	1386.1	1384.6	1383.0
177.5°	1389.8	1391.0	1392.2	1392.2	1391.0	1389.8	1388.5	1387.3
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1

(END OF REPORT)