

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331402

Luminaire Tested: **SA2XXDIP-C865D925U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331402  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D925U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7511.0 lumens  
Efficiency: N/A  
Efficacy: 124.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331402  
CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.4	2.2
10°-20°	478.0	6.4
20°-30°	693.8	9.2
30°-40°	732.1	9.7
40°-50°	648.2	8.6
50°-60°	517.3	6.9
60°-70°	351.6	4.7
70°-80°	180.3	2.4
80°-90°	46.6	0.6
90°-100°	42.1	0.6
100°-110°	154.4	2.1
110°-120°	412.7	5.5
120°-130°	681.3	9.1
130°-140°	724.5	9.6
140°-150°	673.4	9.0
150°-160°	541.4	7.2
160°-170°	348.9	4.6
170°-180°	120.1	1.6
0°-30°	1336.2	17.8
0°-40°	2068.3	27.5
0°-60°	3233.8	43.1
0°-90°	3812.2	50.8
90°-120°	609.2	8.1
90°-150°	2688.4	35.8
90°-180°	3699.0	49.2
0°-180°	7511.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	40
90°	25	1	25	1	25	13
95°	39	59	39	59	39	37
105°	69	278	69	278	69	72
115°	75	525	75	525	75	188
125°	781	742	781	742	781	676
135°	949	919	949	919	949	731
145°	1082	1066	1082	1066	1082	677
155°	1174	1174	1174	1174	1174	542
165°	1234	1237	1234	1237	1234	348
175°	1258	1265	1258	1265	1258	120
180°	1262	1262	1262	1262	1262	



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	18.7	18.7	19.1	18.5	18.4	18.8	18.6	17.9	18.2	18.5	18.7
90°	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3	19.3	18.3	16.6
92.5°	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2	21.7	21.2	20.4
95°	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6	36.6	35.6	34.2
97.5°	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3	48.5	47.7	44.4
100°	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3	53.7	52.1	48.6
102.5°	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7	55.6	53.5	48.2
105°	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2	57.9	55.7	48.6
107.5°	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4	75.7	78.0	144.4
110°	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2	139.5	159.8	218.5



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1	329.1	403.1	417.6
115°	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6	469.5	563.5	558.4
117.5°	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7	601.4	624.1	620.7
120°	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3	671.9	669.4	665.8
122.5°	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5	714.0	712.6	708.6
125°	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6	773.2	771.7	767.9
127.5°	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2	827.1	825.1	822.2
130°	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9	861.6	859.4	857.2
132.5°	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6	895.7	893.7	891.5
135°	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7	943.6	941.6	939.8
137.5°	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3	988.3	986.4	984.3
140°	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2	1017.4	1015.6	1013.4
142.5°	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9	1044.3	1042.6	1040.1
145°	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3	1081.8	1080.4	1077.0
147.5°	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8	1114.7	1113.7	1110.3
150°	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8	1134.6	1133.4	1130.2
152.5°	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1	1152.9	1151.7	1148.6
155°	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8	1177.5	1176.3	1173.9
157.5°	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5	1198.2	1196.8	1195.1
160°	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6	1210.4	1209.2	1208.0
162.5°	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9	1221.5	1220.2	1219.1
165°	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9	1233.3
167.5°	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2	1246.8	1245.4	1244.8
170°	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1	1252.6	1251.2	1250.8
172.5°	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4	1257.0	1255.6	1255.2
175°	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2	1261.8	1260.3	1259.9
177.5°	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7	1262.6	1261.4	1261.3
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	18.9	18.6	18.3	19.0	16.9	16.5	13.9	11.9	11.8	11.7	11.1
90°	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9	3.1	5.4	7.6
92.5°	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4	18.2	18.0	17.8
95°	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4	52.7	46.0	39.3
97.5°	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8	98.9	80.1	61.2
100°	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7	133.8	106.0	78.2
102.5°	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9	204.0	198.1	192.2
105°	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6	283.7	289.8	295.9
107.5°	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9	359.8	364.7	369.6
110°	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6	408.9	413.1	417.4





TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3	455.1	458.9	462.7
115°	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1	528.6	532.0	535.5
117.5°	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1	594.9	598.8	602.7
120°	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3	642.3	645.4	648.4
122.5°	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2	683.4	686.6	689.8
125°	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5	745.1	747.8	750.4
127.5°	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9	801.9	804.8	807.7
130°	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8	838.0	841.2	844.5
132.5°	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3	874.0	876.8	879.6
135°	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8	922.0	925.3	928.5
137.5°	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8	969.1	971.4	973.6
140°	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2	999.9	1001.5	1003.1
142.5°	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5	1026.0	1027.5	1028.9
145°	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8	1065.6	1065.4	1065.2
147.5°	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8	1101.0	1100.3	1099.5
150°	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2	1123.8	1122.3	1120.9
152.5°	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9	1143.3	1141.7	1140.2
155°	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6	1171.8	1169.9	1168.1
157.5°	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0	1194.5	1193.0	1191.4
160°	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1208.0	1206.8	1205.5
162.5°	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9	1219.7	1218.5	1217.2
165°	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6	1235.4	1234.2	1232.9
167.5°	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3	1247.1	1245.9	1244.6
170°	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9	1253.6	1252.4	1251.2
172.5°	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2	1258.0	1256.8	1255.6
175°	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9	1263.5	1262.1	1260.6
177.5°	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8	1264.7	1263.6	1262.4
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331402  
 CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	11.0	10.8	10.6	11.0	10.8	10.6	10.2	10.4	10.6	9.8	9.9
90°	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3	21.3	22.3	23.0
92.5°	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2	22.8	23.3	23.7
95°	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6	38.7	39.7	40.1
97.5°	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3	50.1	50.9	51.4
100°	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3	56.9	58.6	59.6
102.5°	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7	59.9	62.0	63.3
105°	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2	62.4	64.6	66.2
107.5°	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4	71.2	68.9	68.2
110°	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2	98.9	78.6	68.9



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1	181.0	107.0	70.3
115°	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6	281.6	187.6	133.3
117.5°	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7	556.0	533.2	497.8
120°	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3	676.8	679.2	666.7
122.5°	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5	716.9	718.4	716.5
125°	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6	776.0	777.4	778.4
127.5°	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2	831.3	833.4	834.4
130°	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9	866.1	868.3	869.4
132.5°	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6	899.5	901.4	902.2
135°	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7	947.7	949.7	950.5
137.5°	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3	992.3	994.3	995.0
140°	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2	1021.1	1022.9	1023.3
142.5°	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9	1047.6	1049.3	1049.6
145°	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3	1084.7	1086.1	1086.3
147.5°	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8	1116.8	1117.9	1118.0
150°	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8	1137.1	1138.3	1138.4
152.5°	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1	1155.3	1156.5	1156.5
155°	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8	1180.0	1181.2	1181.0
157.5°	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5	1200.9	1202.3	1202.2
160°	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6	1212.9	1214.1	1214.0
162.5°	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9	1224.3	1225.7	1225.5
165°	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5
167.5°	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2	1249.6	1251.1	1250.8
170°	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1	1255.5	1256.9	1256.7
172.5°	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4	1259.9	1261.3	1261.1
175°	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2	1264.6	1266.0	1265.7
177.5°	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7	1264.9	1266.0	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	10.0	9.5	9.6	9.2	9.6	9.5	10.0	9.9	9.8	10.6	10.4
90°	23.4	23.8	24.3	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3
92.5°	23.9	24.2	24.4	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2
95°	39.9	39.7	39.5	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6
97.5°	51.7	51.9	52.2	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3
100°	60.0	60.4	60.8	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3
102.5°	63.9	64.4	65.0	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7
105°	67.0	67.8	68.6	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2
107.5°	69.0	69.8	70.6	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4
110°	69.7	70.5	71.3	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	70.9	71.6	72.2	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1
115°	118.7	104.1	89.5	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6
117.5°	449.8	401.8	353.8	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7
120°	639.3	611.9	584.5	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3
122.5°	711.2	705.8	700.5	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5
125°	779.0	779.6	780.3	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6
127.5°	834.6	834.7	834.8	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2
130°	869.2	868.9	868.7	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9
132.5°	902.0	901.8	901.6	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6
135°	950.1	949.7	949.3	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7
137.5°	994.3	993.6	992.9	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3
140°	1022.3	1021.3	1020.3	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2
142.5°	1048.6	1047.6	1046.6	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9
145°	1085.3	1084.3	1083.3	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3
147.5°	1117.1	1116.3	1115.4	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8
150°	1137.4	1136.3	1135.3	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8
152.5°	1155.1	1153.8	1152.5	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1
155°	1179.4	1177.7	1176.1	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8
157.5°	1200.6	1199.0	1197.4	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5
160°	1212.5	1211.1	1209.7	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6
162.5°	1223.8	1222.0	1220.3	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9
165°	1238.1	1236.7	1235.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7
167.5°	1249.0	1247.2	1245.4	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2
170°	1254.9	1253.0	1251.2	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1
172.5°	1259.2	1257.4	1255.6	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4
175°	1263.7	1261.7	1259.6	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2
177.5°	1264.4	1262.9	1261.4	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331402  
 CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	10.2	10.6	10.8	11.0	10.6	10.8	11.0	11.1	11.7	11.8	11.9
90°	19.3	18.3	16.6	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9
92.5°	21.7	21.2	20.4	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4
95°	36.6	35.6	34.2	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4
97.5°	48.5	47.7	44.4	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8
100°	53.7	52.1	48.6	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7
102.5°	55.6	53.5	82.4	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9
105°	57.9	55.7	111.1	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6
107.5°	75.7	78.0	144.4	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9
110°	139.5	159.8	218.5	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.1	403.1	417.6	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3
115°	469.5	563.5	558.4	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1
117.5°	601.4	624.1	620.7	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1
120°	671.9	669.4	665.8	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3
122.5°	714.0	712.6	708.6	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2
125°	773.2	771.7	767.9	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5
127.5°	827.1	825.1	822.2	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9
130°	861.6	859.4	857.2	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8
132.5°	895.7	893.7	891.5	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3
135°	943.6	941.6	939.8	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8
137.5°	988.3	986.4	984.3	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8
140°	1017.4	1015.6	1013.4	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2
142.5°	1044.3	1042.6	1040.1	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5
145°	1081.8	1080.4	1077.0	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8
147.5°	1114.7	1113.7	1110.3	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8
150°	1134.6	1133.4	1130.2	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2
152.5°	1152.9	1151.7	1148.6	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9
155°	1177.5	1176.3	1173.9	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6
157.5°	1198.2	1196.8	1195.1	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0
160°	1210.4	1209.2	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2
162.5°	1221.5	1220.2	1219.1	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9
165°	1235.3	1233.9	1233.3	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6
167.5°	1246.8	1245.4	1244.8	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3
170°	1252.6	1251.2	1250.8	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9
172.5°	1257.0	1255.6	1255.2	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2
175°	1261.8	1260.3	1259.9	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9
177.5°	1262.6	1261.4	1261.3	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	13.9	16.5	16.9	19.0	18.3	18.6	18.9	18.7	18.5	18.2	17.9
90°	3.1	5.4	7.6	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3
92.5°	18.2	18.0	17.8	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2
95°	52.7	46.0	39.3	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6
97.5°	98.9	80.1	61.2	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3
100°	133.8	106.0	78.2	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3
102.5°	204.0	198.1	192.2	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7
105°	283.7	289.8	295.9	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2
107.5°	359.8	364.7	369.6	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4
110°	408.9	413.1	417.4	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2





TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.1	458.9	462.7	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1
115°	528.6	532.0	535.5	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6
117.5°	594.9	598.8	602.7	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7
120°	642.3	645.4	648.4	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3
122.5°	683.4	686.6	689.8	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5
125°	745.1	747.8	750.4	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6
127.5°	801.9	804.8	807.7	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2
130°	838.0	841.2	844.5	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9
132.5°	874.0	876.8	879.6	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6
135°	922.0	925.3	928.5	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7
137.5°	969.1	971.4	973.6	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3
140°	999.9	1001.5	1003.1	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2
142.5°	1026.0	1027.5	1028.9	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9
145°	1065.6	1065.4	1065.2	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3
147.5°	1101.0	1100.3	1099.5	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8
150°	1123.8	1122.3	1120.9	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8
152.5°	1143.3	1141.7	1140.2	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1
155°	1171.8	1169.9	1168.1	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8
157.5°	1194.5	1193.0	1191.4	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5
160°	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6
162.5°	1219.7	1218.5	1217.2	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9
165°	1235.4	1234.2	1232.9	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7
167.5°	1247.1	1245.9	1244.6	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2
170°	1253.6	1252.4	1251.2	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1
172.5°	1258.0	1256.8	1255.6	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4
175°	1263.5	1262.1	1260.6	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2
177.5°	1264.7	1263.6	1262.4	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	18.6	18.8	18.4	18.5	19.1	18.7	18.7
90°	21.3	22.3	23.0	23.4	23.8	24.3	24.7
92.5°	22.8	23.3	23.7	23.9	24.2	24.4	24.7
95°	38.7	39.7	40.1	39.9	39.7	39.5	39.3
97.5°	50.1	50.9	51.4	51.7	51.9	52.2	52.4
100°	56.9	58.6	59.6	60.0	60.4	60.8	61.2
102.5°	59.9	62.0	63.3	63.9	64.4	65.0	65.6
105°	62.4	64.6	66.2	67.0	67.8	68.6	69.4
107.5°	71.2	68.9	68.2	69.0	69.8	70.6	71.4
110°	98.9	78.6	68.9	69.7	70.5	71.3	72.2



TEST NUMBER: P331402

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	181.0	107.0	70.3	70.9	71.6	72.2	72.9
115°	281.6	187.6	133.3	118.7	104.1	89.5	74.9
117.5°	556.0	533.2	497.8	449.8	401.8	353.8	305.8
120°	676.8	679.2	666.7	639.3	611.9	584.5	557.1
122.5°	716.9	718.4	716.5	711.2	705.8	700.5	695.2
125°	776.0	777.4	778.4	779.0	779.6	780.3	780.9
127.5°	831.3	833.4	834.4	834.6	834.7	834.8	834.9
130°	866.1	868.3	869.4	869.2	868.9	868.7	868.5
132.5°	899.5	901.4	902.2	902.0	901.8	901.6	901.4
135°	947.7	949.7	950.5	950.1	949.7	949.3	948.9
137.5°	992.3	994.3	995.0	994.3	993.6	992.9	992.2
140°	1021.1	1022.9	1023.3	1022.3	1021.3	1020.3	1019.2
142.5°	1047.6	1049.3	1049.6	1048.6	1047.6	1046.6	1045.5
145°	1084.7	1086.1	1086.3	1085.3	1084.3	1083.3	1082.3
147.5°	1116.8	1117.9	1118.0	1117.1	1116.3	1115.4	1114.6
150°	1137.1	1138.3	1138.4	1137.4	1136.3	1135.3	1134.3
152.5°	1155.3	1156.5	1156.5	1155.1	1153.8	1152.5	1151.1
155°	1180.0	1181.2	1181.0	1179.4	1177.7	1176.1	1174.5
157.5°	1200.9	1202.3	1202.2	1200.6	1199.0	1197.4	1195.9
160°	1212.9	1214.1	1214.0	1212.5	1211.1	1209.7	1208.3
162.5°	1224.3	1225.7	1225.5	1223.8	1222.0	1220.3	1218.5
165°	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9
167.5°	1249.6	1251.1	1250.8	1249.0	1247.2	1245.4	1243.5
170°	1255.5	1256.9	1256.7	1254.9	1253.0	1251.2	1249.4
172.5°	1259.9	1261.3	1261.1	1259.2	1257.4	1255.6	1253.8
175°	1264.6	1266.0	1265.7	1263.7	1261.7	1259.6	1257.6
177.5°	1264.9	1266.0	1265.8	1264.4	1262.9	1261.4	1260.0
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2

(END OF REPORT)