

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331738

Luminaire Tested: **SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331738  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4793.6 lumens  
Efficiency: N/A  
Efficacy: 96.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331738  
CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331738

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73	
1	104	99	96	92	98	94	91	88	85	83	80	77	75	73	69	68	66	66	66	66	63	
2	95	88	82	77	90	83	78	74	76	71	68	68	65	62	62	59	57	57	57	57	54	
3	87	78	70	65	82	74	68	62	67	62	58	61	57	54	55	52	49	49	49	49	46	
4	80	69	61	55	76	66	59	54	60	55	50	55	50	47	50	46	43	43	43	43	40	
5	74	62	54	48	70	60	52	47	55	48	44	50	45	41	45	41	38	38	38	38	35	
6	68	56	48	42	65	54	47	41	49	43	39	45	40	36	41	37	34	34	34	34	31	
7	64	51	43	38	60	49	42	37	45	39	35	42	36	32	38	34	30	30	30	30	28	
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	28	28	28	28	25	
9	55	43	35	30	53	41	34	30	38	32	28	35	30	27	33	28	25	25	25	25	23	
10	52	40	32	28	49	38	31	27	35	30	26	33	28	24	30	26	23	23	23	23	21	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	27341	27341	27341
5°	27446	27000	27149
10°	27237	26558	26332
15°	26924	25770	25028
20°	26490	24646	23409
25°	26045	23370	21841
30°	25430	22057	19829
35°	24829	20631	18065
40°	24226	19155	16021
45°	23516	17497	14173
50°	22790	15822	12356
55°	22044	14021	10612
60°	21180	12126	8809
65°	20199	10189	8023
70°	19029	8393	7378
75°	17592	7648	6881
80°	15528	6843	6267
85°	12208	5391	5391



TEST NUMBER: P331738

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.5	3.3
10°-20°	435.2	9.1
20°-30°	611.2	12.8
30°-40°	666.5	13.9
40°-50°	612.8	12.8
50°-60°	481.3	10.0
60°-70°	313.8	6.5
70°-80°	161.8	3.4
80°-90°	43.1	0.9
90°-100°	14.9	0.3
100°-110°	54.7	1.1
110°-120°	146.1	3.0
120°-130°	241.2	5.0
130°-140°	256.5	5.4
140°-150°	238.4	5.0
150°-160°	191.7	4.0
160°-170°	123.5	2.6
170°-180°	42.5	0.9
0°-30°	1204.9	25.1
0°-40°	1871.4	39.0
0°-60°	2965.4	61.9
0°-90°	3484.1	72.7
90°-120°	215.7	4.5
90°-150°	951.8	19.9
90°-180°	1309.0	27.3
0°-180°	4793.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1693	1693	1693	1693	1693	
5°	1693	1685	1666	1679	1675	160
15°	1611	1592	1542	1513	1497	454
25°	1462	1410	1312	1251	1226	672
35°	1260	1178	1047	954	916	788
45°	1030	924	766	661	621	795
55°	783	661	498	410	377	700
65°	529	404	267	217	210	524
75°	282	178	123	112	110	298
85°	66	35	29	29	29	78
90°	0	4	6	8	9	4
95°	21	11	13	14	14	26
105°	98	103	20	23	25	105
115°	186	192	200	57	26	183
125°	263	267	273	275	276	234
135°	325	330	333	336	336	251
145°	377	377	382	385	383	236
155°	416	413	416	418	416	191
165°	438	436	437	439	437	124
175°	448	446	446	448	445	43
180°	447	447	447	447	447	



TEST NUMBER: P331738

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1699.6	1698.2	1696.8	1695.5	1694.1	1691.9	1688.9	1686.0	1683.0	1680.0	1682.7
5°	1693.4	1691.7	1690.0	1688.3	1686.6	1683.6	1679.1	1674.7	1670.3	1665.9	1668.9
7.5°	1676.0	1673.9	1671.8	1669.6	1667.5	1663.9	1658.7	1653.5	1648.4	1643.2	1644.1
10°	1661.3	1658.9	1656.5	1654.1	1651.7	1647.1	1640.3	1633.5	1626.7	1619.9	1618.9
12.5°	1642.9	1639.9	1637.0	1634.1	1631.2	1625.3	1616.6	1607.9	1599.2	1590.5	1588.6
15°	1610.7	1606.9	1603.2	1599.4	1595.7	1588.0	1576.5	1564.9	1553.3	1541.7	1535.3
17.5°	1571.1	1565.4	1559.7	1554.0	1548.3	1538.0	1523.1	1508.3	1493.4	1478.6	1470.9
20°	1541.7	1534.9	1528.1	1521.3	1514.5	1502.6	1485.5	1468.5	1451.5	1434.4	1425.9
22.5°	1509.8	1502.2	1494.6	1487.0	1479.3	1465.9	1446.7	1427.5	1408.3	1389.1	1378.1
25°	1462.0	1451.1	1440.2	1429.3	1418.4	1401.8	1379.3	1356.8	1334.3	1311.8	1297.9
27.5°	1404.4	1392.6	1380.7	1368.9	1357.0	1338.4	1313.1	1287.7	1262.4	1237.1	1220.8
30°	1364.0	1351.0	1338.1	1325.1	1312.2	1292.1	1264.8	1237.6	1210.4	1183.1	1165.7
32.5°	1324.7	1309.6	1294.5	1279.4	1264.2	1242.8	1215.0	1187.2	1159.4	1131.6	1111.8
35°	1259.7	1242.4	1225.0	1207.6	1190.3	1166.6	1136.6	1106.7	1076.7	1046.7	1025.3
37.5°	1194.8	1175.7	1156.6	1137.5	1118.5	1093.0	1061.0	1029.1	997.1	965.2	941.6
40°	1149.4	1129.0	1108.5	1088.1	1067.7	1040.9	1007.9	974.9	941.8	908.8	884.6
42.5°	1102.8	1081.3	1059.8	1038.2	1016.7	988.9	954.8	920.6	886.5	852.4	827.4
45°	1029.9	1007.0	984.2	961.4	938.6	909.3	873.5	837.8	802.0	766.3	742.1
47.5°	958.7	934.6	910.4	886.2	862.0	831.5	794.6	757.6	720.7	683.8	659.8
50°	907.3	883.1	858.9	834.7	810.5	779.7	742.3	704.8	667.3	629.9	606.4
52.5°	857.0	831.7	806.5	781.2	755.9	725.0	688.3	651.7	615.0	578.4	555.7
55°	783.1	756.6	730.0	703.4	676.9	645.2	608.4	571.6	534.9	498.1	477.6
57.5°	707.4	680.2	652.9	625.7	598.4	567.1	531.8	496.4	461.1	425.7	407.0
60°	655.9	628.7	601.4	574.2	546.9	515.8	480.7	445.6	410.5	375.5	358.1
62.5°	605.7	578.4	551.2	523.9	496.7	466.3	432.9	399.4	366.0	332.6	316.0
65°	528.7	501.1	473.6	446.0	418.4	389.3	358.6	328.0	297.3	266.7	255.1
67.5°	454.5	427.2	399.8	372.4	345.0	317.5	290.0	262.4	234.8	207.2	201.9
70°	403.1	376.5	349.9	323.4	296.8	271.8	248.3	224.8	201.3	177.8	174.4
72.5°	354.0	328.5	303.1	277.6	252.1	229.9	211.1	192.2	173.3	154.5	151.6
75°	282.0	258.1	234.3	210.5	186.6	168.9	157.3	145.8	134.2	122.6	120.2
77.5°	211.2	190.3	169.4	148.5	127.5	114.3	108.7	103.1	97.5	92.0	90.6
80°	167.0	149.7	132.3	114.9	97.6	87.2	83.8	80.4	77.0	73.6	72.2
82.5°	126.6	113.0	99.5	85.9	72.4	64.4	62.1	59.8	57.5	55.2	54.4
85°	65.9	58.7	51.6	44.4	37.3	33.2	32.2	31.2	30.1	29.1	29.1
87.5°	19.7	17.7	15.6	13.6	11.6	10.6	10.8	10.9	11.0	11.1	10.9
90°	0.3	1.1	1.9	2.7	3.5	4.2	4.7	5.3	5.9	6.5	6.8
92.5°	6.5	6.5	6.4	6.3	6.2	6.4	6.6	6.9	7.2	7.5	7.7
95°	21.0	18.6	16.3	13.9	11.5	10.6	11.1	11.6	12.1	12.6	13.0
97.5°	41.7	35.0	28.3	21.7	15.0	12.2	13.4	14.5	15.7	16.9	17.2
100°	57.2	47.4	37.5	27.7	17.9	13.5	14.8	16.0	17.2	18.4	19.0
102.5°	74.3	72.2	70.1	68.1	66.0	59.8	49.6	39.4	29.2	18.9	19.7
105°	98.3	100.4	102.6	104.8	106.9	98.2	78.6	59.0	39.3	19.7	20.5
107.5°	125.6	127.4	129.1	130.9	132.6	121.7	98.2	74.7	51.1	27.6	26.8
110°	143.2	144.7	146.3	147.8	149.3	139.6	118.9	98.1	77.3	56.6	49.4



TEST NUMBER: P331738

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.8	161.1	162.5	163.8	165.1	163.2	158.1	153.0	147.8	142.7	116.5
115°	185.9	187.1	188.4	189.6	190.8	192.3	194.1	195.9	197.7	199.5	166.2
117.5°	209.3	210.6	212.0	213.4	214.7	216.0	217.3	218.5	219.7	221.0	212.9
120°	226.3	227.4	228.5	229.6	230.6	231.8	233.1	234.4	235.7	237.0	237.9
122.5°	240.8	242.0	243.1	244.2	245.4	246.6	248.0	249.4	250.9	252.3	252.8
125°	262.9	263.8	264.7	265.7	266.6	267.8	269.1	270.5	271.8	273.2	273.7
127.5°	282.8	283.9	284.9	286.0	287.0	288.0	289.0	290.1	291.1	292.1	292.8
130°	295.5	296.7	297.8	299.0	300.1	301.1	301.9	302.7	303.5	304.3	305.0
132.5°	308.5	309.4	310.4	311.4	312.4	313.2	314.0	314.8	315.6	316.4	317.1
135°	325.3	326.4	327.6	328.7	329.9	330.8	331.4	332.1	332.7	333.4	334.1
137.5°	342.3	343.1	343.9	344.7	345.5	346.3	347.0	347.7	348.5	349.2	349.9
140°	353.4	354.0	354.5	355.1	355.7	356.4	357.2	358.0	358.8	359.5	360.2
142.5°	362.7	363.2	363.7	364.3	364.8	365.5	366.4	367.3	368.2	369.1	369.7
145°	377.3	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	383.0
147.5°	390.1	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.6
150°	398.3	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7
152.5°	405.3	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1
155°	415.5	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9
157.5°	423.4	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2
160°	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5
162.5°	432.2	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5
165°	437.8	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3
167.5°	441.9	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4
170°	444.3	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5
172.5°	445.8	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0
175°	447.8	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7
177.5°	448.1	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331738

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1685.4	1688.1	1690.9	1691.9	1691.4	1690.9	1690.3	1689.8
5°	1672.0	1675.1	1678.1	1679.1	1678.1	1677.1	1676.1	1675.1
7.5°	1644.9	1645.8	1646.7	1646.3	1644.5	1642.7	1641.0	1639.2
10°	1617.8	1616.8	1615.8	1614.3	1612.2	1610.2	1608.1	1606.1
12.5°	1586.8	1584.9	1583.1	1580.5	1577.1	1573.7	1570.3	1566.9
15°	1528.8	1522.3	1515.8	1510.9	1507.5	1504.1	1500.7	1497.3
17.5°	1463.2	1455.5	1447.8	1441.0	1435.2	1429.3	1423.4	1417.6
20°	1417.4	1408.9	1400.4	1392.4	1384.9	1377.4	1369.9	1362.4
22.5°	1367.2	1356.2	1345.2	1336.9	1331.4	1325.8	1320.2	1314.6
25°	1283.9	1270.0	1256.0	1246.5	1241.3	1236.2	1231.1	1226.0
27.5°	1204.5	1188.2	1171.9	1159.7	1151.6	1143.5	1135.4	1127.3
30°	1148.4	1131.0	1113.6	1100.4	1091.2	1082.0	1072.8	1063.6
32.5°	1092.0	1072.2	1052.3	1038.1	1029.5	1020.8	1012.1	1003.5
35°	1003.8	982.4	960.9	946.4	938.9	931.4	923.9	916.5
37.5°	917.9	894.3	870.6	854.5	846.0	837.4	828.8	820.2
40°	860.4	836.2	812.1	795.6	786.7	777.8	769.0	760.1
42.5°	802.4	777.4	752.4	735.6	727.0	718.4	709.9	701.3
45°	717.9	693.7	669.5	653.4	645.2	637.0	628.8	620.7
47.5°	635.7	611.7	587.6	571.9	564.5	557.1	549.6	542.2
50°	582.9	559.4	535.9	520.5	513.4	506.2	499.1	491.9
52.5°	533.0	510.3	487.7	473.0	466.4	459.8	453.2	446.6
55°	457.2	436.8	416.3	402.9	396.4	389.9	383.5	377.0
57.5°	388.3	369.5	350.8	338.7	333.3	327.8	322.4	316.9
60°	340.7	323.4	306.0	294.6	289.1	283.7	278.2	272.8
62.5°	299.5	282.9	266.4	256.4	253.2	249.9	246.6	243.4
65°	243.5	231.9	220.3	214.0	213.0	212.0	211.0	210.0
67.5°	196.6	191.3	185.9	182.7	181.7	180.6	179.5	178.4
70°	171.0	167.6	164.2	161.8	160.4	159.0	157.7	156.3
72.5°	148.8	145.9	143.0	141.2	140.4	139.6	138.7	137.9
75°	117.8	115.5	113.1	111.7	111.4	111.0	110.7	110.3
77.5°	89.2	87.9	86.5	85.5	85.0	84.5	83.9	83.4
80°	70.8	69.5	68.1	67.4	67.4	67.4	67.4	67.4
82.5°	53.5	52.7	51.9	51.5	51.5	51.5	51.5	51.5
85°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
87.5°	10.7	10.5	10.3	10.2	10.2	10.3	10.3	10.3
90°	7.2	7.5	7.9	8.2	8.3	8.4	8.6	8.7
92.5°	7.9	8.1	8.2	8.4	8.5	8.6	8.6	8.7
95°	13.3	13.7	14.0	14.2	14.1	14.0	14.0	13.9
97.5°	17.5	17.7	18.0	18.2	18.3	18.4	18.5	18.6
100°	19.6	20.2	20.7	21.1	21.2	21.4	21.5	21.7
102.5°	20.4	21.2	21.9	22.4	22.6	22.8	23.0	23.2
105°	21.3	22.1	22.9	23.4	23.7	24.0	24.3	24.6
107.5°	26.0	25.2	24.4	24.1	24.4	24.7	25.0	25.3
110°	42.2	35.0	27.8	24.4	24.7	25.0	25.3	25.5





TEST NUMBER: P331738

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	90.3	64.1	37.9	24.9	25.1	25.3	25.6	25.8
115°	133.0	99.7	66.4	47.2	42.0	36.9	31.7	26.5
117.5°	204.9	196.8	188.8	176.3	159.3	142.3	125.3	108.3
120°	238.7	239.6	240.4	236.0	226.3	216.6	206.9	197.2
122.5°	253.3	253.8	254.3	253.6	251.8	249.9	248.0	246.1
125°	274.2	274.7	275.2	275.6	275.8	276.0	276.2	276.4
127.5°	293.6	294.3	295.0	295.4	295.5	295.5	295.5	295.6
130°	305.8	306.6	307.4	307.8	307.7	307.6	307.6	307.5
132.5°	317.8	318.4	319.1	319.4	319.3	319.3	319.2	319.1
135°	334.8	335.5	336.2	336.5	336.4	336.2	336.1	335.9
137.5°	350.6	351.3	352.0	352.2	352.0	351.8	351.5	351.3
140°	360.8	361.5	362.1	362.3	361.9	361.6	361.2	360.8
142.5°	370.3	370.9	371.5	371.6	371.2	370.9	370.5	370.1
145°	383.5	384.0	384.5	384.6	384.2	383.9	383.5	383.1
147.5°	395.0	395.4	395.8	395.8	395.5	395.2	394.9	394.6
150°	402.1	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	408.6	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.3	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	424.7	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.0	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	432.9	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	441.9	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.0	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	445.5	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.2	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.4	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)