

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331754

Luminaire Tested: **SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331754  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7122.9 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54	54	54	54	
1	99	95	92	88	92	89	86	83	76	74	72	64	63	61	54	53	52	47	47	47	47	
2	91	84	79	74	84	79	74	69	68	64	61	58	55	53	48	47	45	41	41	41	41	
3	84	75	68	63	78	70	64	59	61	56	52	52	48	46	44	41	39	35	35	35	35	
4	77	67	60	54	71	63	56	51	54	49	45	47	43	40	40	37	35	31	31	31	31	
5	71	60	53	47	66	56	50	44	49	44	40	43	39	35	36	33	31	28	28	28	28	
6	66	54	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28	25	25	25	25	
7	61	50	42	37	57	47	40	35	41	36	32	36	31	28	31	28	25	23	23	23	23	
8	57	45	38	33	53	43	36	31	38	32	28	33	29	26	29	25	23	21	21	21	21	
9	53	42	34	30	50	39	33	28	35	30	26	31	26	23	27	23	21	19	19	19	19	
10	50	38	31	27	47	36	30	26	32	27	24	28	24	21	25	22	19	17	17	17	17	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	35608	35608	35608	35608
5°	39768	35832	31770	35832
10°	44124	35580	27539	35580
15°	46292	35059	21698	35059
20°	40132	34287	18777	34287
25°	26320	33228	16764	33228
30°	17715	31946	15172	31946
35°	14349	30328	13685	30328
40°	12760	28572	12663	28572
45°	11549	26510	11303	26510
50°	10510	24465	10472	24465
55°	9880	22196	9751	22196
60°	8263	20118	8167	20118
65°	6968	18269	7904	18269
70°	6439	16315	7454	16315
75°	6026	14198	6881	14198
80°	5560	11688	6127	11688
85°	5113	9226	5391	9226



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.1	2.9
10°-20°	582.5	8.2
20°-30°	750.7	10.5
30°-40°	713.4	10.0
40°-50°	611.1	8.6
50°-60°	465.4	6.5
60°-70°	294.2	4.1
70°-80°	146.9	2.1
80°-90°	43.0	0.6
90°-100°	74.9	1.1
100°-110°	232.7	3.3
110°-120°	397.8	5.6
120°-130°	523.2	7.3
130°-140°	587.2	8.2
140°-150°	575.7	8.1
150°-160°	482.9	6.8
160°-170°	320.3	4.5
170°-180°	111.9	1.6
0°-30°	1542.3	21.7
0°-40°	2255.7	31.7
0°-60°	3332.1	46.8
0°-90°	3816.2	53.6
90°-120°	705.5	9.9
90°-150°	2391.6	33.6
90°-180°	3307.0	46.4
0°-180°	7122.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2205	2205	2205	2205	2205	
5°	2454	2211	1960	2211	2454	242
15°	2769	2097	1298	2097	2769	747
25°	1477	1865	941	1865	1477	701
35°	728	1539	694	1539	728	466
45°	506	1161	495	1161	506	391
55°	351	788	346	788	351	308
65°	182	478	207	478	182	186
75°	97	228	110	228	97	102
85°	28	50	29	50	28	30
90°	34	1	34	1	34	16
95°	62	52	62	52	62	69
105°	222	215	222	215	222	233
115°	399	399	399	399	399	394
125°	583	581	583	581	583	520
135°	760	752	760	752	760	585
145°	922	912	922	912	922	576
155°	1051	1043	1051	1043	1051	484
165°	1136	1135	1136	1135	1136	320
175°	1177	1181	1177	1181	1177	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2294.9	2296.8	2298.6	2294.3	2294.3	2290.6	2282.7	2276.5	2259.4	2256.9	2256.9
5°	2453.7	2452.2	2455.2	2445.3	2431.5	2428.4	2413.9	2394.7	2374.8	2352.6	2348.0
7.5°	2611.6	2609.3	2603.1	2601.5	2590.9	2567.7	2544.3	2519.3	2486.2	2453.9	2437.6
10°	2691.3	2716.6	2701.2	2674.4	2679.8	2643.8	2624.6	2591.7	2564.1	2515.8	2505.1
12.5°	2769.7	2779.7	2774.8	2759.6	2752.7	2727.7	2701.8	2673.2	2622.3	2578.9	2541.2
15°	2769.4	2784.0	2787.8	2783.2	2787.1	2785.5	2771.7	2748.0	2703.5	2656.0	2614.6
17.5°	2565.0	2575.1	2600.2	2617.2	2638.7	2684.1	2706.4	2715.2	2708.6	2681.5	2652.3
20°	2335.7	2318.8	2389.3	2425.4	2456.0	2532.6	2598.5	2623.8	2664.4	2663.7	2656.0
22.5°	2010.8	2014.8	2081.6	2124.4	2213.9	2290.5	2365.6	2460.8	2539.4	2591.3	2621.7
25°	1477.4	1506.6	1573.2	1631.5	1731.1	1873.6	2003.1	2153.3	2295.1	2407.0	2513.5
27.5°	1109.6	1111.8	1164.6	1218.4	1277.6	1394.4	1557.4	1736.8	1938.9	2105.7	2297.5
30°	950.2	945.6	967.8	1000.8	1051.4	1141.8	1264.4	1440.7	1642.2	1893.5	2117.3
32.5°	837.4	837.7	854.4	878.8	920.8	981.8	1065.8	1208.9	1399.4	1646.5	1908.9
35°	728.0	727.2	739.5	757.1	774.7	813.8	871.3	946.4	1077.4	1308.1	1576.3
37.5°	649.5	652.9	658.9	669.9	689.4	711.1	745.6	796.0	889.4	1025.8	1251.2
40°	605.4	606.9	615.3	624.5	636.0	652.9	681.2	721.9	790.1	898.9	1063.6
42.5°	564.9	566.5	572.4	581.0	590.1	606.9	630.4	665.5	720.8	805.7	941.6
45°	505.8	505.8	511.1	515.0	524.9	540.2	559.4	588.5	626.8	689.7	780.1
47.5°	450.3	450.4	454.0	460.6	466.8	478.8	497.6	521.4	549.3	597.9	675.1
50°	418.4	419.2	421.5	426.8	430.7	441.4	456.0	476.6	505.8	543.3	607.7
52.5°	392.7	392.2	395.1	397.4	400.0	407.7	418.6	436.8	462.8	495.5	548.8
55°	351.0	347.9	352.5	356.3	358.6	361.7	367.8	379.3	401.5	429.1	469.0
57.5°	298.9	297.6	300.9	304.4	311.6	319.9	325.1	332.4	343.9	363.7	403.2
60°	255.9	255.9	262.8	265.1	273.6	284.3	295.0	301.2	312.7	325.7	354.8
62.5°	217.9	218.6	221.8	224.1	228.8	242.0	257.0	270.5	281.4	293.8	313.1
65°	182.4	183.9	183.9	185.4	188.5	191.6	197.7	208.4	227.6	245.2	259.8
67.5°	154.8	155.3	155.7	157.2	158.0	161.4	163.8	168.6	173.0	189.7	207.8
70°	136.4	138.7	137.9	139.5	140.2	141.8	144.8	147.1	154.0	157.9	168.6
72.5°	119.2	120.9	120.8	121.7	123.7	124.0	126.4	128.7	133.2	136.4	142.2
75°	96.6	95.8	96.6	98.1	98.9	99.6	99.6	102.7	105.0	108.0	111.9
77.5°	74.5	75.3	75.1	75.3	75.4	76.8	76.6	78.0	80.3	81.8	83.7
80°	59.8	60.5	59.8	60.5	61.3	62.1	61.3	62.1	64.4	65.9	65.9
82.5°	46.3	46.4	46.9	47.1	47.2	47.4	48.4	48.6	50.3	50.0	50.6
85°	27.6	26.8	26.8	26.8	27.6	28.4	27.6	27.6	28.4	28.4	28.4
87.5°	16.6	17.2	17.1	17.1	17.0	17.1	17.1	17.8	17.3	18.0	16.4
90°	33.9	33.7	33.5	33.3	33.0	33.2	33.6	34.0	34.5	34.9	30.0
92.5°	32.3	32.3	32.2	32.2	32.2	32.1	32.0	31.9	31.8	31.7	30.6
95°	61.9	62.3	62.8	63.2	63.6	63.9	63.9	63.9	63.9	63.9	63.4
97.5°	107.2	107.2	107.3	107.3	107.4	107.4	107.4	107.4	107.4	107.4	106.5
100°	136.7	136.9	137.2	137.4	137.6	137.7	137.7	137.7	137.7	137.7	137.1
102.5°	170.3	170.5	170.7	170.9	171.1	171.2	171.0	170.8	170.6	170.5	169.6
105°	221.5	221.5	221.5	221.5	221.5	221.3	220.9	220.4	220.0	219.5	219.1
107.5°	269.8	270.9	271.9	272.9	273.9	274.3	274.2	274.0	273.8	273.6	273.6
110°	307.4	308.0	308.7	309.4	310.0	310.4	310.4	310.4	310.4	310.4	310.4



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.3	343.8	344.3	344.8	345.2	345.8	346.3	346.8	347.4	347.9	348.1
115°	399.2	399.8	400.5	401.2	401.8	402.3	402.5	402.7	403.0	403.2	403.6
117.5°	452.5	453.1	453.8	454.5	455.1	455.7	456.3	456.8	457.3	457.9	459.1
120°	490.0	490.7	491.3	492.0	492.7	493.0	493.0	493.0	493.0	493.0	494.8
122.5°	526.7	527.2	527.7	528.2	528.7	529.2	529.7	530.2	530.8	531.3	532.6
125°	582.8	583.0	583.2	583.5	583.7	584.1	584.8	585.5	586.1	586.8	587.5
127.5°	633.9	634.6	635.3	636.0	636.7	637.5	638.3	639.1	639.9	640.7	641.5
130°	670.6	671.5	672.4	673.3	674.2	674.8	675.3	675.7	676.2	676.6	677.1
132.5°	705.8	706.5	707.2	707.9	708.6	709.4	710.4	711.4	712.4	713.3	713.2
135°	760.4	761.1	761.8	762.4	763.1	763.5	763.8	764.0	764.2	764.4	764.0
137.5°	809.9	810.8	811.7	812.6	813.5	814.0	814.2	814.4	814.6	814.7	814.2
140°	844.3	845.2	846.0	846.9	847.8	848.3	848.3	848.3	848.3	848.3	847.2
142.5°	875.4	876.3	877.2	878.1	879.0	879.3	879.1	879.0	878.8	878.6	877.8
145°	922.1	923.0	923.9	924.8	925.7	926.0	925.8	925.5	925.3	925.1	923.8
147.5°	963.8	964.7	965.5	966.4	967.2	967.4	966.9	966.4	965.9	965.4	964.5
150°	991.0	991.6	992.3	993.0	993.6	993.6	993.0	992.3	991.6	991.0	990.1
152.5°	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5	1015.4
155°	1050.8	1051.5	1052.2	1052.8	1053.5	1053.3	1052.2	1051.1	1050.0	1048.8	1048.2
157.5°	1080.4	1081.4	1082.5	1083.6	1084.6	1084.4	1082.9	1081.4	1079.9	1078.4	1078.0
160°	1098.7	1099.6	1100.5	1101.4	1102.3	1102.1	1100.7	1099.4	1098.1	1096.7	1096.5
162.5°	1114.7	1115.8	1116.8	1117.9	1119.0	1118.7	1117.2	1115.7	1114.2	1112.7	1112.5
165°	1135.7	1136.8	1137.9	1139.0	1140.1	1139.9	1138.3	1136.8	1135.2	1133.7	1133.7
167.5°	1152.8	1154.0	1155.1	1156.3	1157.4	1157.2	1155.7	1154.1	1152.6	1151.0	1151.1
170°	1161.6	1162.9	1164.3	1165.6	1166.9	1166.8	1165.3	1163.7	1162.2	1160.6	1160.8
172.5°	1168.8	1170.1	1171.5	1172.8	1174.1	1174.0	1172.5	1170.9	1169.4	1167.8	1168.0
175°	1176.6	1177.9	1179.2	1180.6	1181.9	1181.8	1180.2	1178.7	1177.1	1175.6	1176.0
177.5°	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2	1180.5
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2258.2	2253.2	2249.0	2237.9	2232.4	2220.1	2218.3	2217.7	2201.8	2186.4	2182.1
5°	2335.7	2323.4	2305.1	2283.6	2261.4	2238.4	2223.1	2210.8	2180.1	2151.0	2134.2
7.5°	2413.9	2387.5	2355.8	2315.2	2281.3	2243.3	2215.1	2189.8	2146.3	2104.6	2076.5
10°	2472.1	2429.2	2387.0	2331.1	2287.4	2244.5	2204.7	2170.2	2121.1	2066.0	2026.9
12.5°	2508.3	2461.1	2403.0	2348.3	2291.7	2237.2	2183.8	2139.5	2081.9	2024.9	1978.5
15°	2557.2	2506.6	2436.1	2357.9	2285.1	2213.9	2152.6	2097.4	2022.3	1954.1	1897.4
17.5°	2597.2	2527.6	2451.9	2361.5	2277.2	2186.6	2107.7	2037.2	1953.6	1871.3	1804.5
20°	2610.0	2541.1	2453.7	2363.3	2263.7	2157.2	2072.1	1995.5	1905.8	1816.1	1739.5
22.5°	2602.1	2548.4	2451.3	2343.1	2241.0	2129.6	2033.5	1944.6	1845.1	1753.6	1664.7
25°	2548.0	2529.6	2437.6	2319.6	2203.1	2073.6	1962.5	1865.2	1751.8	1653.7	1557.1
27.5°	2421.8	2461.5	2404.5	2278.8	2149.3	2010.5	1885.6	1774.8	1657.1	1546.7	1450.5
30°	2300.5	2391.6	2367.1	2250.6	2105.8	1969.4	1829.2	1713.5	1587.8	1474.4	1379.4
32.5°	2134.3	2285.0	2308.9	2211.4	2061.7	1911.8	1764.8	1649.7	1518.5	1399.0	1306.4
35°	1869.8	2095.1	2198.5	2136.5	1986.3	1824.6	1672.8	1538.7	1406.9	1288.9	1197.0
37.5°	1554.2	1861.1	2033.5	2037.9	1900.0	1731.9	1566.6	1433.5	1298.6	1182.7	1083.3
40°	1349.5	1682.0	1906.6	1956.4	1839.9	1658.3	1491.2	1355.6	1223.8	1110.4	996.2
42.5°	1165.6	1496.9	1772.9	1859.5	1767.0	1586.6	1418.9	1277.1	1149.0	1041.7	925.1
45°	942.6	1232.2	1536.4	1691.2	1639.9	1472.8	1295.8	1161.0	1040.6	947.9	836.0
47.5°	795.1	999.3	1293.7	1503.0	1502.1	1349.6	1175.5	1046.3	934.7	847.8	757.3
50°	711.1	888.9	1138.0	1375.5	1395.4	1267.5	1101.9	974.0	869.8	778.6	705.8
52.5°	635.7	782.2	1006.2	1233.9	1290.6	1179.8	1019.2	901.0	799.9	716.0	653.7
55°	537.2	650.6	820.7	1033.7	1119.6	1041.4	898.9	788.5	706.5	636.0	582.4
57.5°	454.4	539.5	676.0	847.5	947.5	898.3	780.7	691.1	620.9	557.1	514.8
60°	402.3	472.0	587.8	731.1	841.4	806.9	706.5	623.0	563.2	508.1	468.2
62.5°	353.3	413.2	512.4	628.7	729.8	715.6	633.6	563.5	511.1	460.9	427.1
65°	284.3	328.0	405.4	496.6	577.8	584.7	525.7	478.2	431.4	391.6	361.7
67.5°	226.4	254.9	309.4	386.2	447.1	468.8	432.8	396.5	359.4	328.6	302.7
70°	190.8	213.8	253.6	315.7	371.7	394.6	374.0	345.6	313.4	288.1	265.9
72.5°	154.6	177.0	206.4	252.0	299.9	324.8	317.6	297.2	271.1	250.1	229.1
75°	116.5	123.4	143.3	174.0	211.5	233.0	238.3	227.6	206.9	190.8	178.5
77.5°	86.1	90.3	99.8	115.9	140.4	159.5	167.4	166.1	151.9	142.5	131.0
80°	69.0	71.3	75.9	82.8	101.2	120.3	125.7	125.7	115.7	111.9	100.4
82.5°	52.4	54.1	56.9	60.7	69.3	86.0	92.0	93.2	86.9	81.8	72.8
85°	29.9	29.1	30.7	33.0	34.5	39.1	48.3	49.8	48.3	42.1	39.8
87.5°	15.5	15.1	14.1	12.8	12.8	12.9	15.4	18.0	16.1	14.8	14.1
90°	25.2	20.3	15.4	11.6	9.0	6.3	3.7	1.0	3.7	6.3	9.0
92.5°	29.4	28.3	27.1	25.6	23.6	21.7	19.7	17.8	19.7	21.7	23.6
95°	63.0	62.5	62.1	60.8	58.5	56.3	54.1	51.9	54.1	56.3	58.5
97.5°	105.7	104.9	104.0	102.6	100.7	98.7	96.8	94.8	96.8	98.7	100.7
100°	136.4	135.7	135.1	133.8	132.1	130.3	128.5	126.7	128.5	130.3	132.1
102.5°	168.8	167.9	167.1	165.9	164.5	163.1	161.7	160.3	161.7	163.1	164.5
105°	218.7	218.2	217.8	217.2	216.6	215.9	215.2	214.6	215.2	215.9	216.6
107.5°	273.6	273.6	273.6	273.2	272.2	271.2	270.2	269.2	270.2	271.2	272.2
110°	310.4	310.4	310.4	309.7	308.4	307.0	305.7	304.4	305.7	307.0	308.4





TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	348.2	348.4	348.6	348.0	346.7	345.4	344.0	342.7	344.0	345.4	346.7
115°	404.1	404.5	404.9	404.5	403.2	401.8	400.5	399.2	400.5	401.8	403.2
117.5°	460.3	461.6	462.8	462.6	460.8	459.0	457.2	455.5	457.2	459.0	460.8
120°	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0	494.8	496.5	498.3
122.5°	533.8	535.0	536.3	535.8	533.7	531.6	529.4	527.3	529.4	531.6	533.7
125°	588.1	588.8	589.5	588.8	586.8	584.8	582.8	580.8	582.8	584.8	586.8
127.5°	642.3	643.1	643.9	643.0	640.5	638.0	635.4	632.9	635.4	638.0	640.5
130°	677.5	677.9	678.4	677.2	674.3	671.4	668.5	665.6	668.5	671.4	674.3
132.5°	713.2	713.1	713.0	711.8	709.4	707.1	704.7	702.4	704.7	707.1	709.4
135°	763.5	763.1	762.7	761.2	758.8	756.3	753.9	751.5	753.9	756.3	758.8
137.5°	813.6	813.0	812.4	811.1	809.1	807.1	805.1	803.2	805.1	807.1	809.1
140°	846.0	844.9	843.8	842.3	840.3	838.3	836.3	834.3	836.3	838.3	840.3
142.5°	877.1	876.3	875.6	874.2	872.2	870.2	868.2	866.2	868.2	870.2	872.2
145°	922.4	921.1	919.8	918.3	916.8	915.2	913.7	912.1	913.7	915.2	916.8
147.5°	963.6	962.8	961.9	960.5	958.6	956.8	954.9	953.0	954.9	956.8	958.6
150°	989.2	988.3	987.4	986.3	985.0	983.6	982.3	981.0	982.3	983.6	985.0
152.5°	1014.4	1013.3	1012.3	1011.1	1009.7	1008.4	1007.1	1005.7	1007.1	1008.4	1009.7
155°	1047.5	1046.9	1046.2	1045.5	1044.9	1044.2	1043.5	1042.9	1043.5	1044.2	1044.9
157.5°	1077.6	1077.2	1076.8	1076.4	1075.9	1075.5	1075.0	1074.6	1075.0	1075.5	1075.9
160°	1096.3	1096.1	1095.9	1095.5	1095.1	1094.6	1094.2	1093.8	1094.2	1094.6	1095.1
162.5°	1112.3	1112.1	1111.8	1111.7	1111.6	1111.5	1111.4	1111.3	1111.4	1111.5	1111.6
165°	1133.7	1133.7	1133.7	1133.8	1134.0	1134.2	1134.5	1134.7	1134.5	1134.2	1134.0
167.5°	1151.1	1151.2	1151.2	1151.6	1152.2	1152.9	1153.6	1154.2	1153.6	1152.9	1152.2
170°	1161.1	1161.3	1161.5	1161.9	1162.6	1163.3	1163.9	1164.6	1163.9	1163.3	1162.6
172.5°	1168.2	1168.5	1168.7	1169.1	1169.8	1170.5	1171.1	1171.8	1171.1	1170.5	1169.8
175°	1176.5	1176.9	1177.4	1177.9	1178.6	1179.2	1179.9	1180.6	1179.9	1179.2	1178.6
177.5°	1180.9	1181.2	1181.6	1182.0	1182.6	1183.1	1183.6	1184.2	1183.6	1183.1	1182.6
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2174.2	2169.9	2161.9	2149.6	2142.3	2129.4	2120.8	2125.7	2127.0	2125.7	2124.5
5°	2115.8	2099.7	2077.5	2056.0	2036.1	2014.6	2002.4	1997.0	1986.3	1980.1	1977.1
7.5°	2045.1	2017.4	1986.0	1948.6	1916.8	1883.6	1866.6	1858.1	1836.2	1824.3	1813.8
10°	1992.4	1948.7	1917.3	1868.3	1838.4	1794.7	1764.8	1765.6	1735.7	1718.8	1706.6
12.5°	1934.2	1886.2	1833.9	1789.8	1748.3	1713.2	1677.1	1662.6	1630.9	1614.6	1581.5
15°	1837.6	1781.7	1726.5	1666.7	1624.6	1570.2	1518.1	1454.5	1403.1	1358.7	1346.4
17.5°	1732.2	1662.9	1607.6	1537.4	1465.2	1373.7	1313.3	1276.4	1245.4	1222.0	1204.5
20°	1659.8	1589.3	1530.3	1424.6	1327.2	1265.2	1220.7	1192.4	1160.2	1134.9	1121.1
22.5°	1583.8	1510.2	1429.8	1311.8	1235.9	1186.1	1146.5	1113.9	1092.1	1072.4	1059.8
25°	1475.9	1395.4	1262.9	1181.6	1120.3	1068.2	1040.6	1020.7	997.7	970.9	958.7
27.5°	1361.9	1233.9	1138.7	1078.3	1019.8	985.9	961.1	931.4	910.8	898.7	886.0
30°	1276.7	1148.7	1074.4	1008.5	967.1	929.5	900.4	883.6	863.6	842.9	834.5
32.5°	1181.6	1079.4	1008.2	953.3	911.3	879.3	856.3	829.0	814.6	801.9	784.2
35°	1063.6	986.2	921.1	876.7	836.8	810.8	783.9	767.8	741.8	731.1	724.2
37.5°	963.7	896.6	848.0	801.1	769.5	740.7	724.3	698.7	687.4	672.5	658.0
40°	907.3	841.4	794.7	756.3	721.1	699.6	678.9	658.3	641.4	634.5	616.9
42.5°	849.7	796.0	749.3	707.3	683.7	661.0	634.8	619.6	602.2	591.0	580.1
45°	770.1	722.6	682.8	648.3	622.2	598.5	581.6	556.3	546.4	524.2	515.0
47.5°	700.3	656.1	618.1	585.3	559.9	544.4	519.7	499.9	484.0	470.4	458.6
50°	650.6	613.8	577.0	547.9	524.9	502.7	477.4	467.4	442.9	436.0	429.1
52.5°	605.2	570.3	536.6	508.1	485.1	463.5	441.2	428.2	411.7	404.8	399.7
55°	541.8	508.1	475.9	450.6	427.6	405.4	391.6	375.5	367.8	362.5	356.3
57.5°	478.0	447.7	423.0	397.4	374.3	356.6	340.7	331.0	323.1	316.0	308.7
60°	437.6	408.4	386.2	362.5	338.7	324.1	311.9	300.4	291.2	280.5	277.4
62.5°	394.6	369.2	348.8	325.7	305.0	291.7	280.0	269.1	258.1	242.5	238.2
65°	335.6	315.7	294.3	275.1	256.7	243.7	226.8	214.6	210.0	208.4	207.7
67.5°	282.3	263.5	245.1	225.4	208.7	196.6	188.1	186.2	183.0	182.1	179.9
70°	246.8	229.1	210.7	192.3	176.3	174.0	170.9	167.8	164.0	162.5	160.9
72.5°	214.9	196.6	178.2	163.5	156.6	153.7	150.7	147.6	145.0	143.5	142.5
75°	164.8	147.9	135.6	130.3	126.4	124.1	119.5	117.2	115.7	113.4	112.6
77.5°	118.6	109.1	103.5	100.1	96.1	93.6	91.0	88.7	87.1	86.6	85.4
80°	90.4	85.8	82.0	77.4	75.9	72.8	72.0	69.7	70.5	68.2	68.2
82.5°	70.2	64.4	61.2	59.0	57.5	55.0	54.3	53.2	53.3	51.6	51.6
85°	36.0	34.5	33.0	31.4	31.4	29.1	29.9	29.1	29.1	27.6	26.8
87.5°	14.0	14.1	13.9	14.8	15.8	16.2	16.1	15.4	15.3	15.2	14.6
90°	11.6	15.4	20.3	25.2	30.0	34.9	34.5	34.0	33.6	33.2	33.0
92.5°	25.6	27.1	28.3	29.4	30.6	31.7	31.8	31.9	32.0	32.1	32.2
95°	60.8	62.1	62.5	63.0	63.4	63.9	63.9	63.9	63.9	63.9	63.6
97.5°	102.6	104.0	104.9	105.7	106.5	107.4	107.4	107.4	107.4	107.4	107.4
100°	133.8	135.1	135.7	136.4	137.1	137.7	137.7	137.7	137.7	137.7	137.6
102.5°	165.9	167.1	167.9	168.8	169.6	170.5	170.6	170.8	171.0	171.2	171.1
105°	217.2	217.8	218.2	218.7	219.1	219.5	220.0	220.4	220.9	221.3	221.5
107.5°	273.2	273.6	273.6	273.6	273.6	273.6	273.8	274.0	274.2	274.3	273.9
110°	309.7	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.0



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	348.0	348.6	348.4	348.2	348.1	347.9	347.4	346.8	346.3	345.8	345.2
115°	404.5	404.9	404.5	404.1	403.6	403.2	403.0	402.7	402.5	402.3	401.8
117.5°	462.6	462.8	461.6	460.3	459.1	457.9	457.3	456.8	456.3	455.7	455.1
120°	500.1	500.1	498.3	496.5	494.8	493.0	493.0	493.0	493.0	493.0	492.7
122.5°	535.8	536.3	535.0	533.8	532.6	531.3	530.8	530.2	529.7	529.2	528.7
125°	588.8	589.5	588.8	588.1	587.5	586.8	586.1	585.5	584.8	584.1	583.7
127.5°	643.0	643.9	643.1	642.3	641.5	640.7	639.9	639.1	638.3	637.5	636.7
130°	677.2	678.4	677.9	677.5	677.1	676.6	676.2	675.7	675.3	674.8	674.2
132.5°	711.8	713.0	713.1	713.2	713.2	713.3	712.4	711.4	710.4	709.4	708.6
135°	761.2	762.7	763.1	763.5	764.0	764.4	764.2	764.0	763.8	763.5	763.1
137.5°	811.1	812.4	813.0	813.6	814.2	814.7	814.6	814.4	814.2	814.0	813.5
140°	842.3	843.8	844.9	846.0	847.2	848.3	848.3	848.3	848.3	848.3	847.8
142.5°	874.2	875.6	876.3	877.1	877.8	878.6	878.8	879.0	879.1	879.3	879.0
145°	918.3	919.8	921.1	922.4	923.8	925.1	925.3	925.5	925.8	926.0	925.7
147.5°	960.5	961.9	962.8	963.6	964.5	965.4	965.9	966.4	966.9	967.4	967.2
150°	986.3	987.4	988.3	989.2	990.1	991.0	991.6	992.3	993.0	993.6	993.6
152.5°	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9
155°	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0	1051.1	1052.2	1053.3	1053.5
157.5°	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9	1081.4	1082.9	1084.4	1084.6
160°	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1	1099.4	1100.7	1102.1	1102.3
162.5°	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2	1115.7	1117.2	1118.7	1119.0
165°	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2	1136.8	1138.3	1139.9	1140.1
167.5°	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6	1154.1	1155.7	1157.2	1157.4
170°	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2	1163.7	1165.3	1166.8	1166.9
172.5°	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4	1170.9	1172.5	1174.0	1174.1
175°	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1	1178.7	1180.2	1181.8	1181.9
177.5°	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2117.8	2119.0	2117.2	2118.4	2117.2	2119.0	2117.8	2124.5	2125.7	2127.0	2125.7
5°	1973.2	1964.0	1962.5	1960.2	1962.5	1964.0	1973.2	1977.1	1980.1	1986.3	1997.0
7.5°	1800.7	1799.3	1795.5	1790.1	1795.5	1799.3	1800.7	1813.8	1824.3	1836.2	1858.1
10°	1689.7	1685.9	1685.1	1679.7	1685.1	1685.9	1689.7	1706.6	1718.8	1735.7	1765.6
12.5°	1559.7	1535.1	1532.5	1519.1	1532.5	1535.1	1559.7	1581.5	1614.6	1630.9	1662.6
15°	1328.0	1323.4	1308.1	1298.1	1308.1	1323.4	1328.0	1346.4	1358.7	1403.1	1454.5
17.5°	1195.6	1180.6	1175.8	1173.7	1175.8	1180.6	1195.6	1204.5	1222.0	1245.4	1276.4
20°	1110.4	1096.6	1094.3	1092.8	1094.3	1096.6	1110.4	1121.1	1134.9	1160.2	1192.4
22.5°	1051.5	1037.1	1031.1	1026.5	1031.1	1037.1	1051.5	1059.8	1072.4	1092.1	1113.9
25°	951.0	945.6	942.6	941.0	942.6	945.6	951.0	958.7	970.9	997.7	1020.7
27.5°	872.4	860.6	858.3	854.3	858.3	860.6	872.4	886.0	898.7	910.8	931.4
30°	827.6	823.8	818.4	813.8	818.4	823.8	827.6	834.5	842.9	863.6	883.6
32.5°	774.9	771.7	766.9	764.8	766.9	771.7	774.9	784.2	801.9	814.6	829.0
35°	716.5	705.8	701.2	694.3	701.2	705.8	716.5	724.2	731.1	741.8	767.8
37.5°	654.7	649.1	642.6	644.9	642.6	649.1	654.7	658.0	672.5	687.4	698.7
40°	606.9	603.1	601.6	600.8	601.6	603.1	606.9	616.9	634.5	641.4	658.3
42.5°	568.9	558.3	554.3	554.2	554.3	558.3	568.9	580.1	591.0	602.2	619.6
45°	511.1	501.2	494.3	495.0	494.3	501.2	511.1	515.0	524.2	546.4	556.3
47.5°	452.0	451.7	447.4	448.7	447.4	451.7	452.0	458.6	470.4	484.0	499.9
50°	423.8	419.2	416.1	416.9	416.1	419.2	423.8	429.1	436.0	442.9	467.4
52.5°	396.8	392.8	390.4	393.6	390.4	392.8	396.8	399.7	404.8	411.7	428.2
55°	352.5	347.9	347.1	346.4	347.1	347.9	352.5	356.3	362.5	367.8	375.5
57.5°	303.0	299.9	295.3	293.3	295.3	299.9	303.0	308.7	316.0	323.1	331.0
60°	267.4	261.3	253.6	252.9	253.6	261.3	267.4	277.4	280.5	291.2	300.4
62.5°	234.9	233.7	232.2	232.0	232.2	233.7	234.9	238.2	242.5	258.1	269.1
65°	206.1	205.4	206.1	206.9	206.1	205.4	206.1	207.7	208.4	210.0	214.6
67.5°	179.6	178.2	176.9	177.5	176.9	178.2	179.6	179.9	182.1	183.0	186.2
70°	159.4	158.6	157.9	157.9	157.9	158.6	159.4	160.9	162.5	164.0	167.8
72.5°	139.8	139.6	138.9	138.2	138.9	139.6	139.8	142.5	143.5	145.0	147.6
75°	111.9	110.3	110.3	110.3	110.3	110.3	111.9	112.6	113.4	115.7	117.2
77.5°	85.2	84.4	83.7	83.1	83.7	84.4	85.2	85.4	86.6	87.1	88.7
80°	67.4	66.7	65.9	65.9	65.9	66.7	67.4	68.2	68.2	70.5	69.7
82.5°	51.5	50.7	50.6	50.0	50.6	50.7	51.5	51.6	51.6	53.3	53.2
85°	27.6	28.4	27.6	29.1	27.6	28.4	27.6	26.8	27.6	29.1	29.1
87.5°	14.6	14.1	14.7	14.1	14.7	14.1	14.6	14.6	15.2	15.3	15.4
90°	33.3	33.5	33.7	33.9	33.7	33.5	33.3	33.0	33.2	33.6	34.0
92.5°	32.2	32.2	32.3	32.3	32.3	32.2	32.2	32.2	32.1	32.0	31.9
95°	63.2	62.8	62.3	61.9	62.3	62.8	63.2	63.6	63.9	63.9	63.9
97.5°	107.3	107.3	107.2	107.2	107.2	107.3	107.3	107.4	107.4	107.4	107.4
100°	137.4	137.2	136.9	136.7	136.9	137.2	137.4	137.6	137.7	137.7	137.7
102.5°	170.9	170.7	170.5	170.3	170.5	170.7	170.9	171.1	171.2	171.0	170.8
105°	221.5	221.5	221.5	221.5	221.5	221.5	221.5	221.5	221.3	220.9	220.4
107.5°	272.9	271.9	270.9	269.8	270.9	271.9	272.9	273.9	274.3	274.2	274.0
110°	309.4	308.7	308.0	307.4	308.0	308.7	309.4	310.0	310.4	310.4	310.4



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	344.8	344.3	343.8	343.3	343.8	344.3	344.8	345.2	345.8	346.3	346.8
115°	401.2	400.5	399.8	399.2	399.8	400.5	401.2	401.8	402.3	402.5	402.7
117.5°	454.5	453.8	453.1	452.5	453.1	453.8	454.5	455.1	455.7	456.3	456.8
120°	492.0	491.3	490.7	490.0	490.7	491.3	492.0	492.7	493.0	493.0	493.0
122.5°	528.2	527.7	527.2	526.7	527.2	527.7	528.2	528.7	529.2	529.7	530.2
125°	583.5	583.2	583.0	582.8	583.0	583.2	583.5	583.7	584.1	584.8	585.5
127.5°	636.0	635.3	634.6	633.9	634.6	635.3	636.0	636.7	637.5	638.3	639.1
130°	673.3	672.4	671.5	670.6	671.5	672.4	673.3	674.2	674.8	675.3	675.7
132.5°	707.9	707.2	706.5	705.8	706.5	707.2	707.9	708.6	709.4	710.4	711.4
135°	762.4	761.8	761.1	760.4	761.1	761.8	762.4	763.1	763.5	763.8	764.0
137.5°	812.6	811.7	810.8	809.9	810.8	811.7	812.6	813.5	814.0	814.2	814.4
140°	846.9	846.0	845.2	844.3	845.2	846.0	846.9	847.8	848.3	848.3	848.3
142.5°	878.1	877.2	876.3	875.4	876.3	877.2	878.1	879.0	879.3	879.1	879.0
145°	924.8	923.9	923.0	922.1	923.0	923.9	924.8	925.7	926.0	925.8	925.5
147.5°	966.4	965.5	964.7	963.8	964.7	965.5	966.4	967.2	967.4	966.9	966.4
150°	993.0	992.3	991.6	991.0	991.6	992.3	993.0	993.6	993.6	993.0	992.3
152.5°	1019.0	1018.2	1017.4	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2
155°	1052.8	1052.2	1051.5	1050.8	1051.5	1052.2	1052.8	1053.5	1053.3	1052.2	1051.1
157.5°	1083.6	1082.5	1081.4	1080.4	1081.4	1082.5	1083.6	1084.6	1084.4	1082.9	1081.4
160°	1101.4	1100.5	1099.6	1098.7	1099.6	1100.5	1101.4	1102.3	1102.1	1100.7	1099.4
162.5°	1117.9	1116.8	1115.8	1114.7	1115.8	1116.8	1117.9	1119.0	1118.7	1117.2	1115.7
165°	1139.0	1137.9	1136.8	1135.7	1136.8	1137.9	1139.0	1140.1	1139.9	1138.3	1136.8
167.5°	1156.3	1155.1	1154.0	1152.8	1154.0	1155.1	1156.3	1157.4	1157.2	1155.7	1154.1
170°	1165.6	1164.3	1162.9	1161.6	1162.9	1164.3	1165.6	1166.9	1166.8	1165.3	1163.7
172.5°	1172.8	1171.5	1170.1	1168.8	1170.1	1171.5	1172.8	1174.1	1174.0	1172.5	1170.9
175°	1180.6	1179.2	1177.9	1176.6	1177.9	1179.2	1180.6	1181.9	1181.8	1180.2	1178.7
177.5°	1183.4	1182.3	1181.2	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2120.8	2129.4	2142.3	2149.6	2161.9	2169.9	2174.2	2182.1	2186.4	2201.8	2217.7
5°	2002.4	2014.6	2036.1	2056.0	2077.5	2099.7	2115.8	2134.2	2151.0	2180.1	2210.8
7.5°	1866.6	1883.6	1916.8	1948.6	1986.0	2017.4	2045.1	2076.5	2104.6	2146.3	2189.8
10°	1764.8	1794.7	1838.4	1868.3	1917.3	1948.7	1992.4	2026.9	2066.0	2121.1	2170.2
12.5°	1677.1	1713.2	1748.3	1789.8	1833.9	1886.2	1934.2	1978.5	2024.9	2081.9	2139.5
15°	1518.1	1570.2	1624.6	1666.7	1726.5	1781.7	1837.6	1897.4	1954.1	2022.3	2097.4
17.5°	1313.3	1373.7	1465.2	1537.4	1607.6	1662.9	1732.2	1804.5	1871.3	1953.6	2037.2
20°	1220.7	1265.2	1327.2	1424.6	1530.3	1589.3	1659.8	1739.5	1816.1	1905.8	1995.5
22.5°	1146.5	1186.1	1235.9	1311.8	1429.8	1510.2	1583.8	1664.7	1753.6	1845.1	1944.6
25°	1040.6	1068.2	1120.3	1181.6	1262.9	1395.4	1475.9	1557.1	1653.7	1751.8	1865.2
27.5°	961.1	985.9	1019.8	1078.3	1138.7	1233.9	1361.9	1450.5	1546.7	1657.1	1774.8
30°	900.4	929.5	967.1	1008.5	1074.4	1148.7	1276.7	1379.4	1474.4	1587.8	1713.5
32.5°	856.3	879.3	911.3	953.3	1008.2	1079.4	1181.6	1306.4	1399.0	1518.5	1649.7
35°	783.9	810.8	836.8	876.7	921.1	986.2	1063.6	1197.0	1288.9	1406.9	1538.7
37.5°	724.3	740.7	769.5	801.1	848.0	896.6	963.7	1083.3	1182.7	1298.6	1433.5
40°	678.9	699.6	721.1	756.3	794.7	841.4	907.3	996.2	1110.4	1223.8	1355.6
42.5°	634.8	661.0	683.7	707.3	749.3	796.0	849.7	925.1	1041.7	1149.0	1277.1
45°	581.6	598.5	622.2	648.3	682.8	722.6	770.1	836.0	947.9	1040.6	1161.0
47.5°	519.7	544.4	559.9	585.3	618.1	656.1	700.3	757.3	847.8	934.7	1046.3
50°	477.4	502.7	524.9	547.9	577.0	613.8	650.6	705.8	778.6	869.8	974.0
52.5°	441.2	463.5	485.1	508.1	536.6	570.3	605.2	653.7	716.0	799.9	901.0
55°	391.6	405.4	427.6	450.6	475.9	508.1	541.8	582.4	636.0	706.5	788.5
57.5°	340.7	356.6	374.3	397.4	423.0	447.7	478.0	514.8	557.1	620.9	691.1
60°	311.9	324.1	338.7	362.5	386.2	408.4	437.6	468.2	508.1	563.2	623.0
62.5°	280.0	291.7	305.0	325.7	348.8	369.2	394.6	427.1	460.9	511.1	563.5
65°	226.8	243.7	256.7	275.1	294.3	315.7	335.6	361.7	391.6	431.4	478.2
67.5°	188.1	196.6	208.7	225.4	245.1	263.5	282.3	302.7	328.6	359.4	396.5
70°	170.9	174.0	176.3	192.3	210.7	229.1	246.8	265.9	288.1	313.4	345.6
72.5°	150.7	153.7	156.6	163.5	178.2	196.6	214.9	229.1	250.1	271.1	297.2
75°	119.5	124.1	126.4	130.3	135.6	147.9	164.8	178.5	190.8	206.9	227.6
77.5°	91.0	93.6	96.1	100.1	103.5	109.1	118.6	131.0	142.5	151.9	166.1
80°	72.0	72.8	75.9	77.4	82.0	85.8	90.4	100.4	111.9	115.7	125.7
82.5°	54.3	55.0	57.5	59.0	61.2	64.4	70.2	72.8	81.8	86.9	93.2
85°	29.9	29.1	31.4	31.4	33.0	34.5	36.0	39.8	42.1	48.3	49.8
87.5°	16.1	16.2	15.8	14.8	13.9	14.1	14.0	14.1	14.8	16.1	18.0
90°	34.5	34.9	30.0	25.2	20.3	15.4	11.6	9.0	6.3	3.7	1.0
92.5°	31.8	31.7	30.6	29.4	28.3	27.1	25.6	23.6	21.7	19.7	17.8
95°	63.9	63.9	63.4	63.0	62.5	62.1	60.8	58.5	56.3	54.1	51.9
97.5°	107.4	107.4	106.5	105.7	104.9	104.0	102.6	100.7	98.7	96.8	94.8
100°	137.7	137.7	137.1	136.4	135.7	135.1	133.8	132.1	130.3	128.5	126.7
102.5°	170.6	170.5	169.6	168.8	167.9	167.1	165.9	164.5	163.1	161.7	160.3
105°	220.0	219.5	219.1	218.7	218.2	217.8	217.2	216.6	215.9	215.2	214.6
107.5°	273.8	273.6	273.6	273.6	273.6	273.6	273.2	272.2	271.2	270.2	269.2
110°	310.4	310.4	310.4	310.4	310.4	310.4	309.7	308.4	307.0	305.7	304.4



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.4	347.9	348.1	348.2	348.4	348.6	348.0	346.7	345.4	344.0	342.7
115°	403.0	403.2	403.6	404.1	404.5	404.9	404.5	403.2	401.8	400.5	399.2
117.5°	457.3	457.9	459.1	460.3	461.6	462.8	462.6	460.8	459.0	457.2	455.5
120°	493.0	493.0	494.8	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0
122.5°	530.8	531.3	532.6	533.8	535.0	536.3	535.8	533.7	531.6	529.4	527.3
125°	586.1	586.8	587.5	588.1	588.8	589.5	588.8	586.8	584.8	582.8	580.8
127.5°	639.9	640.7	641.5	642.3	643.1	643.9	643.0	640.5	638.0	635.4	632.9
130°	676.2	676.6	677.1	677.5	677.9	678.4	677.2	674.3	671.4	668.5	665.6
132.5°	712.4	713.3	713.2	713.2	713.1	713.0	711.8	709.4	707.1	704.7	702.4
135°	764.2	764.4	764.0	763.5	763.1	762.7	761.2	758.8	756.3	753.9	751.5
137.5°	814.6	814.7	814.2	813.6	813.0	812.4	811.1	809.1	807.1	805.1	803.2
140°	848.3	848.3	847.2	846.0	844.9	843.8	842.3	840.3	838.3	836.3	834.3
142.5°	878.8	878.6	877.8	877.1	876.3	875.6	874.2	872.2	870.2	868.2	866.2
145°	925.3	925.1	923.8	922.4	921.1	919.8	918.3	916.8	915.2	913.7	912.1
147.5°	965.9	965.4	964.5	963.6	962.8	961.9	960.5	958.6	956.8	954.9	953.0
150°	991.6	991.0	990.1	989.2	988.3	987.4	986.3	985.0	983.6	982.3	981.0
152.5°	1017.4	1016.5	1015.4	1014.4	1013.3	1012.3	1011.1	1009.7	1008.4	1007.1	1005.7
155°	1050.0	1048.8	1048.2	1047.5	1046.9	1046.2	1045.5	1044.9	1044.2	1043.5	1042.9
157.5°	1079.9	1078.4	1078.0	1077.6	1077.2	1076.8	1076.4	1075.9	1075.5	1075.0	1074.6
160°	1098.1	1096.7	1096.5	1096.3	1096.1	1095.9	1095.5	1095.1	1094.6	1094.2	1093.8
162.5°	1114.2	1112.7	1112.5	1112.3	1112.1	1111.8	1111.7	1111.6	1111.5	1111.4	1111.3
165°	1135.2	1133.7	1133.7	1133.7	1133.7	1133.7	1133.8	1134.0	1134.2	1134.5	1134.7
167.5°	1152.6	1151.0	1151.1	1151.1	1151.2	1151.2	1151.6	1152.2	1152.9	1153.6	1154.2
170°	1162.2	1160.6	1160.8	1161.1	1161.3	1161.5	1161.9	1162.6	1163.3	1163.9	1164.6
172.5°	1169.4	1167.8	1168.0	1168.2	1168.5	1168.7	1169.1	1169.8	1170.5	1171.1	1171.8
175°	1177.1	1175.6	1176.0	1176.5	1176.9	1177.4	1177.9	1178.6	1179.2	1179.9	1180.6
177.5°	1181.2	1180.2	1180.5	1180.9	1181.2	1181.6	1182.0	1182.6	1183.1	1183.6	1184.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2218.3	2220.1	2232.4	2237.9	2249.0	2253.2	2258.2	2256.9	2256.9	2259.4	2276.5
5°	2223.1	2238.4	2261.4	2283.6	2305.1	2323.4	2335.7	2348.0	2352.6	2374.8	2394.7
7.5°	2215.1	2243.3	2281.3	2315.2	2355.8	2387.5	2413.9	2437.6	2453.9	2486.2	2519.3
10°	2204.7	2244.5	2287.4	2331.1	2387.0	2429.2	2472.1	2505.1	2515.8	2564.1	2591.7
12.5°	2183.8	2237.2	2291.7	2348.3	2403.0	2461.1	2508.3	2541.2	2578.9	2622.3	2673.2
15°	2152.6	2213.9	2285.1	2357.9	2436.1	2506.6	2557.2	2614.6	2656.0	2703.5	2748.0
17.5°	2107.7	2186.6	2277.2	2361.5	2451.9	2527.6	2597.2	2652.3	2681.5	2708.6	2715.2
20°	2072.1	2157.2	2263.7	2363.3	2453.7	2541.1	2610.0	2656.0	2663.7	2664.4	2623.8
22.5°	2033.5	2129.6	2241.0	2343.1	2451.3	2548.4	2602.1	2621.7	2591.3	2539.4	2460.8
25°	1962.5	2073.6	2203.1	2319.6	2437.6	2529.6	2548.0	2513.5	2407.0	2295.1	2153.3
27.5°	1885.6	2010.5	2149.3	2278.8	2404.5	2461.5	2421.8	2297.5	2105.7	1938.9	1736.8
30°	1829.2	1969.4	2105.8	2250.6	2367.1	2391.6	2300.5	2117.3	1893.5	1642.2	1440.7
32.5°	1764.8	1911.8	2061.7	2211.4	2308.9	2285.0	2134.3	1908.9	1646.5	1399.4	1208.9
35°	1672.8	1824.6	1986.3	2136.5	2198.5	2095.1	1869.8	1576.3	1308.1	1077.4	946.4
37.5°	1566.6	1731.9	1900.0	2037.9	2033.5	1861.1	1554.2	1251.2	1025.8	889.4	796.0
40°	1491.2	1658.3	1839.9	1956.4	1906.6	1682.0	1349.5	1063.6	898.9	790.1	721.9
42.5°	1418.9	1586.6	1767.0	1859.5	1772.9	1496.9	1165.6	941.6	805.7	720.8	665.5
45°	1295.8	1472.8	1639.9	1691.2	1536.4	1232.2	942.6	780.1	689.7	626.8	588.5
47.5°	1175.5	1349.6	1502.1	1503.0	1293.7	999.3	795.1	675.1	597.9	549.3	521.4
50°	1101.9	1267.5	1395.4	1375.5	1138.0	888.9	711.1	607.7	543.3	505.8	476.6
52.5°	1019.2	1179.8	1290.6	1233.9	1006.2	782.2	635.7	548.8	495.5	462.8	436.8
55°	898.9	1041.4	1119.6	1033.7	820.7	650.6	537.2	469.0	429.1	401.5	379.3
57.5°	780.7	898.3	947.5	847.5	676.0	539.5	454.4	403.2	363.7	343.9	332.4
60°	706.5	806.9	841.4	731.1	587.8	472.0	402.3	354.8	325.7	312.7	301.2
62.5°	633.6	715.6	729.8	628.7	512.4	413.2	353.3	313.1	293.8	281.4	270.5
65°	525.7	584.7	577.8	496.6	405.4	328.0	284.3	259.8	245.2	227.6	208.4
67.5°	432.8	468.8	447.1	386.2	309.4	254.9	226.4	207.8	189.7	173.0	168.6
70°	374.0	394.6	371.7	315.7	253.6	213.8	190.8	168.6	157.9	154.0	147.1
72.5°	317.6	324.8	299.9	252.0	206.4	177.0	154.6	142.2	136.4	133.2	128.7
75°	238.3	233.0	211.5	174.0	143.3	123.4	116.5	111.9	108.0	105.0	102.7
77.5°	167.4	159.5	140.4	115.9	99.8	90.3	86.1	83.7	81.8	80.3	78.0
80°	125.7	120.3	101.2	82.8	75.9	71.3	69.0	65.9	65.9	64.4	62.1
82.5°	92.0	86.0	69.3	60.7	56.9	54.1	52.4	50.6	50.0	50.3	48.6
85°	48.3	39.1	34.5	33.0	30.7	29.1	29.9	28.4	28.4	28.4	27.6
87.5°	15.4	12.9	12.8	12.8	14.1	15.1	15.5	16.4	18.0	17.3	17.8
90°	3.7	6.3	9.0	11.6	15.4	20.3	25.2	30.0	34.9	34.5	34.0
92.5°	19.7	21.7	23.6	25.6	27.1	28.3	29.4	30.6	31.7	31.8	31.9
95°	54.1	56.3	58.5	60.8	62.1	62.5	63.0	63.4	63.9	63.9	63.9
97.5°	96.8	98.7	100.7	102.6	104.0	104.9	105.7	106.5	107.4	107.4	107.4
100°	128.5	130.3	132.1	133.8	135.1	135.7	136.4	137.1	137.7	137.7	137.7
102.5°	161.7	163.1	164.5	165.9	167.1	167.9	168.8	169.6	170.5	170.6	170.8
105°	215.2	215.9	216.6	217.2	217.8	218.2	218.7	219.1	219.5	220.0	220.4
107.5°	270.2	271.2	272.2	273.2	273.6	273.6	273.6	273.6	273.6	273.8	274.0
110°	305.7	307.0	308.4	309.7	310.4	310.4	310.4	310.4	310.4	310.4	310.4





TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.0	345.4	346.7	348.0	348.6	348.4	348.2	348.1	347.9	347.4	346.8
115°	400.5	401.8	403.2	404.5	404.9	404.5	404.1	403.6	403.2	403.0	402.7
117.5°	457.2	459.0	460.8	462.6	462.8	461.6	460.3	459.1	457.9	457.3	456.8
120°	494.8	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0	493.0	493.0
122.5°	529.4	531.6	533.7	535.8	536.3	535.0	533.8	532.6	531.3	530.8	530.2
125°	582.8	584.8	586.8	588.8	589.5	588.8	588.1	587.5	586.8	586.1	585.5
127.5°	635.4	638.0	640.5	643.0	643.9	643.1	642.3	641.5	640.7	639.9	639.1
130°	668.5	671.4	674.3	677.2	678.4	677.9	677.5	677.1	676.6	676.2	675.7
132.5°	704.7	707.1	709.4	711.8	713.0	713.1	713.2	713.2	713.3	712.4	711.4
135°	753.9	756.3	758.8	761.2	762.7	763.1	763.5	764.0	764.4	764.2	764.0
137.5°	805.1	807.1	809.1	811.1	812.4	813.0	813.6	814.2	814.7	814.6	814.4
140°	836.3	838.3	840.3	842.3	843.8	844.9	846.0	847.2	848.3	848.3	848.3
142.5°	868.2	870.2	872.2	874.2	875.6	876.3	877.1	877.8	878.6	878.8	879.0
145°	913.7	915.2	916.8	918.3	919.8	921.1	922.4	923.8	925.1	925.3	925.5
147.5°	954.9	956.8	958.6	960.5	961.9	962.8	963.6	964.5	965.4	965.9	966.4
150°	982.3	983.6	985.0	986.3	987.4	988.3	989.2	990.1	991.0	991.6	992.3
152.5°	1007.1	1008.4	1009.7	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4	1018.2
155°	1043.5	1044.2	1044.9	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0	1051.1
157.5°	1075.0	1075.5	1075.9	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9	1081.4
160°	1094.2	1094.6	1095.1	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1	1099.4
162.5°	1111.4	1111.5	1111.6	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2	1115.7
165°	1134.5	1134.2	1134.0	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2	1136.8
167.5°	1153.6	1152.9	1152.2	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6	1154.1
170°	1163.9	1163.3	1162.6	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2	1163.7
172.5°	1171.1	1170.5	1169.8	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4	1170.9
175°	1179.9	1179.2	1178.6	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1	1178.7
177.5°	1183.6	1183.1	1182.6	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2	1182.3
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2282.7	2290.6	2294.3	2294.3	2298.6	2296.8	2294.9
5°	2413.9	2428.4	2431.5	2445.3	2455.2	2452.2	2453.7
7.5°	2544.3	2567.7	2590.9	2601.5	2603.1	2609.3	2611.6
10°	2624.6	2643.8	2679.8	2674.4	2701.2	2716.6	2691.3
12.5°	2701.8	2727.7	2752.7	2759.6	2774.8	2779.7	2769.7
15°	2771.7	2785.5	2787.1	2783.2	2787.8	2784.0	2769.4
17.5°	2706.4	2684.1	2638.7	2617.2	2600.2	2575.1	2565.0
20°	2598.5	2532.6	2456.0	2425.4	2389.3	2318.8	2335.7
22.5°	2365.6	2290.5	2213.9	2124.4	2081.6	2014.8	2010.8
25°	2003.1	1873.6	1731.1	1631.5	1573.2	1506.6	1477.4
27.5°	1557.4	1394.4	1277.6	1218.4	1164.6	1111.8	1109.6
30°	1264.4	1141.8	1051.4	1000.8	967.8	945.6	950.2
32.5°	1065.8	981.8	920.8	878.8	854.4	837.7	837.4
35°	871.3	813.8	774.7	757.1	739.5	727.2	728.0
37.5°	745.6	711.1	689.4	669.9	658.9	652.9	649.5
40°	681.2	652.9	636.0	624.5	615.3	606.9	605.4
42.5°	630.4	606.9	590.1	581.0	572.4	566.5	564.9
45°	559.4	540.2	524.9	515.0	511.1	505.8	505.8
47.5°	497.6	478.8	466.8	460.6	454.0	450.4	450.3
50°	456.0	441.4	430.7	426.8	421.5	419.2	418.4
52.5°	418.6	407.7	400.0	397.4	395.1	392.2	392.7
55°	367.8	361.7	358.6	356.3	352.5	347.9	351.0
57.5°	325.1	319.9	311.6	304.4	300.9	297.6	298.9
60°	295.0	284.3	273.6	265.1	262.8	255.9	255.9
62.5°	257.0	242.0	228.8	224.1	221.8	218.6	217.9
65°	197.7	191.6	188.5	185.4	183.9	183.9	182.4
67.5°	163.8	161.4	158.0	157.2	155.7	155.3	154.8
70°	144.8	141.8	140.2	139.5	137.9	138.7	136.4
72.5°	126.4	124.0	123.7	121.7	120.8	120.9	119.2
75°	99.6	99.6	98.9	98.1	96.6	95.8	96.6
77.5°	76.6	76.8	75.4	75.3	75.1	75.3	74.5
80°	61.3	62.1	61.3	60.5	59.8	60.5	59.8
82.5°	48.4	47.4	47.2	47.1	46.9	46.4	46.3
85°	27.6	28.4	27.6	26.8	26.8	26.8	27.6
87.5°	17.1	17.1	17.0	17.1	17.1	17.2	16.6
90°	33.6	33.2	33.0	33.3	33.5	33.7	33.9
92.5°	32.0	32.1	32.2	32.2	32.2	32.3	32.3
95°	63.9	63.9	63.6	63.2	62.8	62.3	61.9
97.5°	107.4	107.4	107.4	107.3	107.3	107.2	107.2
100°	137.7	137.7	137.6	137.4	137.2	136.9	136.7
102.5°	171.0	171.2	171.1	170.9	170.7	170.5	170.3
105°	220.9	221.3	221.5	221.5	221.5	221.5	221.5
107.5°	274.2	274.3	273.9	272.9	271.9	270.9	269.8
110°	310.4	310.4	310.0	309.4	308.7	308.0	307.4



TEST NUMBER: P331754

CATALOG NUMBER: SA2XXRDIP-C1005D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	346.3	345.8	345.2	344.8	344.3	343.8	343.3
115°	402.5	402.3	401.8	401.2	400.5	399.8	399.2
117.5°	456.3	455.7	455.1	454.5	453.8	453.1	452.5
120°	493.0	493.0	492.7	492.0	491.3	490.7	490.0
122.5°	529.7	529.2	528.7	528.2	527.7	527.2	526.7
125°	584.8	584.1	583.7	583.5	583.2	583.0	582.8
127.5°	638.3	637.5	636.7	636.0	635.3	634.6	633.9
130°	675.3	674.8	674.2	673.3	672.4	671.5	670.6
132.5°	710.4	709.4	708.6	707.9	707.2	706.5	705.8
135°	763.8	763.5	763.1	762.4	761.8	761.1	760.4
137.5°	814.2	814.0	813.5	812.6	811.7	810.8	809.9
140°	848.3	848.3	847.8	846.9	846.0	845.2	844.3
142.5°	879.1	879.3	879.0	878.1	877.2	876.3	875.4
145°	925.8	926.0	925.7	924.8	923.9	923.0	922.1
147.5°	966.9	967.4	967.2	966.4	965.5	964.7	963.8
150°	993.0	993.6	993.6	993.0	992.3	991.6	991.0
152.5°	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5
155°	1052.2	1053.3	1053.5	1052.8	1052.2	1051.5	1050.8
157.5°	1082.9	1084.4	1084.6	1083.6	1082.5	1081.4	1080.4
160°	1100.7	1102.1	1102.3	1101.4	1100.5	1099.6	1098.7
162.5°	1117.2	1118.7	1119.0	1117.9	1116.8	1115.8	1114.7
165°	1138.3	1139.9	1140.1	1139.0	1137.9	1136.8	1135.7
167.5°	1155.7	1157.2	1157.4	1156.3	1155.1	1154.0	1152.8
170°	1165.3	1166.8	1166.9	1165.6	1164.3	1162.9	1161.6
172.5°	1172.5	1174.0	1174.1	1172.8	1171.5	1170.1	1168.8
175°	1180.2	1181.8	1181.9	1180.6	1179.2	1177.9	1176.6
177.5°	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6

(END OF REPORT)