

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331630

Luminaire Tested: **SA2XXRDIP-C290D725U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331630
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3932.0 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331630
CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331630

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	29	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22	17
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	15	11
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12	9
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331630

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	1.2
10°-20°	129.0	3.3
20°-30°	181.2	4.6
30°-40°	197.6	5.0
40°-50°	181.6	4.6
50°-60°	142.7	3.6
60°-70°	93.0	2.4
70°-80°	48.0	1.2
80°-90°	14.9	0.4
90°-100°	33.0	0.8
100°-110°	120.9	3.1
110°-120°	323.3	8.2
120°-130°	533.6	13.6
130°-140°	567.5	14.4
140°-150°	527.5	13.4
150°-160°	424.1	10.8
160°-170°	273.3	6.9
170°-180°	94.1	2.4
0°-30°	357.2	9.1
0°-40°	554.7	14.1
0°-60°	879.0	22.4
0°-90°	1034.9	26.3
90°-120°	477.2	12.1
90°-150°	2105.7	53.6
90°-180°	2897.0	73.7
0°-180°	3932.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	8	14	18	19	3
95°	46	24	28	31	31	57
105°	218	227	44	51	54	232
115°	411	424	441	126	59	405
125°	582	591	604	609	612	518
135°	720	731	738	744	743	556
145°	835	835	846	851	848	522
155°	919	914	921	925	920	423
165°	969	965	966	971	966	274
175°	991	986	987	992	985	94
180°	989	989	989	989	989	



TEST NUMBER: P331630

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	6.0	5.7	5.4	5.1	4.8	4.8	5.0	5.3	5.5	5.8	5.8
90°	0.7	2.5	4.2	6.0	7.7	9.2	10.5	11.8	13.0	14.3	15.1
92.5°	14.4	14.3	14.1	14.0	13.8	14.1	14.7	15.3	16.0	16.6	17.0
95°	46.5	41.3	36.0	30.8	25.5	23.4	24.6	25.7	26.8	27.9	28.7
97.5°	92.3	77.5	62.7	47.9	33.1	27.0	29.6	32.2	34.8	37.3	38.0
100°	126.6	104.8	83.1	61.3	39.5	30.0	32.7	35.4	38.1	40.8	42.0
102.5°	164.4	159.8	155.2	150.6	145.9	132.3	109.7	87.1	64.5	41.9	43.6
105°	217.5	222.2	227.0	231.8	236.5	217.2	173.8	130.4	87.0	43.6	45.4
107.5°	278.0	281.8	285.7	289.5	293.4	269.3	217.2	165.2	113.1	61.1	59.3
110°	316.9	320.2	323.6	326.9	330.2	308.9	263.0	217.1	171.1	125.2	109.3



TEST NUMBER: P331630

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.5	356.5	359.4	362.4	365.3	361.1	349.8	338.4	327.1	315.7	257.8
115°	411.3	414.0	416.7	419.4	422.1	425.5	429.4	433.4	437.4	441.4	367.8
117.5°	463.0	466.0	469.0	472.0	475.0	477.9	480.7	483.4	486.1	488.9	471.1
120°	500.7	503.1	505.5	507.9	510.3	512.9	515.8	518.6	521.5	524.3	526.2
122.5°	532.8	535.3	537.8	540.3	542.8	545.6	548.8	551.9	555.0	558.1	559.2
125°	581.6	583.6	585.7	587.8	589.8	592.4	595.4	598.4	601.4	604.5	605.6
127.5°	625.8	628.1	630.4	632.6	634.9	637.2	639.5	641.7	644.0	646.2	647.9
130°	653.8	656.4	658.9	661.4	664.0	666.1	667.9	669.6	671.4	673.1	674.9
132.5°	682.4	684.6	686.8	688.9	691.1	693.0	694.8	696.5	698.3	700.0	701.5
135°	719.6	722.2	724.7	727.3	729.8	731.8	733.2	734.6	736.1	737.5	739.1
137.5°	757.3	759.0	760.8	762.6	764.4	766.1	767.7	769.3	770.9	772.6	774.1
140°	781.9	783.1	784.4	785.7	786.9	788.5	790.2	792.0	793.7	795.5	796.9
142.5°	802.5	803.6	804.8	805.9	807.0	808.6	810.6	812.6	814.6	816.6	817.9
145°	834.8	834.6	834.5	834.3	834.2	835.4	838.1	840.8	843.5	846.2	847.4
147.5°	863.0	862.4	861.8	861.2	860.6	861.6	864.3	866.9	869.6	872.3	873.1
150°	881.3	880.2	879.1	878.0	876.8	877.6	880.1	882.6	885.2	887.7	888.7
152.5°	896.7	895.5	894.3	893.0	891.8	892.4	894.8	897.2	899.6	902.0	903.0
155°	919.2	917.8	916.3	914.9	913.5	913.7	915.6	917.5	919.4	921.3	922.3
157.5°	936.8	935.6	934.4	933.2	932.0	932.0	933.4	934.7	936.0	937.4	938.5
160°	947.1	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	948.1
162.5°	956.3	955.3	954.4	953.4	952.4	952.4	953.2	954.0	954.9	955.7	956.8
165°	968.6	967.6	966.7	965.7	964.7	964.5	965.0	965.5	965.9	966.4	967.5
167.5°	977.7	976.8	975.8	974.9	973.9	973.6	974.1	974.5	975.0	975.4	976.5
170°	982.9	981.9	981.0	980.0	979.1	978.7	979.1	979.4	979.7	980.0	981.1
172.5°	986.3	985.3	984.4	983.4	982.5	982.2	982.5	982.8	983.1	983.4	984.6
175°	990.7	989.6	988.5	987.4	986.3	985.9	986.2	986.5	986.8	987.2	988.3
177.5°	991.5	990.6	989.7	988.8	987.9	987.5	987.6	987.8	987.9	988.0	988.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331630

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	5.9	6.0	6.1	6.2	6.2	6.3	6.3	6.4
90°	15.9	16.7	17.5	18.0	18.4	18.7	19.0	19.3
92.5°	17.4	17.8	18.2	18.6	18.7	18.9	19.1	19.3
95°	29.5	30.3	31.1	31.4	31.2	31.1	30.9	30.8
97.5°	38.6	39.2	39.9	40.3	40.5	40.7	40.9	41.1
100°	43.3	44.6	45.9	46.7	47.0	47.3	47.6	47.9
102.5°	45.2	46.9	48.5	49.6	50.0	50.5	50.9	51.4
105°	47.1	48.9	50.6	51.8	52.5	53.1	53.7	54.4
107.5°	57.5	55.7	54.0	53.4	54.0	54.7	55.3	55.9
110°	93.4	77.5	61.6	54.0	54.6	55.2	55.9	56.5



TEST NUMBER: P331630

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	199.8	141.8	83.8	55.0	55.6	56.1	56.6	57.1
115°	294.2	220.6	147.0	104.4	93.0	81.5	70.1	58.7
117.5°	453.3	435.4	417.6	389.9	352.3	314.7	277.1	239.5
120°	528.2	530.1	532.0	522.2	500.7	479.3	457.8	436.4
122.5°	560.4	561.5	562.7	561.2	557.0	552.8	548.7	544.5
125°	606.7	607.8	608.9	609.7	610.2	610.7	611.1	611.6
127.5°	649.5	651.1	652.7	653.6	653.7	653.8	653.9	654.0
130°	676.6	678.4	680.1	680.9	680.8	680.6	680.4	680.3
132.5°	703.0	704.5	706.0	706.7	706.5	706.4	706.2	706.0
135°	740.7	742.3	743.9	744.5	744.2	743.9	743.5	743.2
137.5°	775.7	777.2	778.8	779.3	778.8	778.2	777.7	777.1
140°	798.3	799.7	801.2	801.5	800.7	799.9	799.1	798.3
142.5°	819.2	820.5	821.8	822.1	821.3	820.5	819.7	818.9
145°	848.5	849.6	850.7	850.8	850.1	849.3	848.5	847.7
147.5°	873.9	874.8	875.6	875.7	875.0	874.3	873.7	873.0
150°	889.6	890.6	891.5	891.6	890.8	890.0	889.2	888.4
152.5°	903.9	904.9	905.9	905.8	904.8	903.7	902.7	901.6
155°	923.3	924.2	925.2	925.0	923.7	922.5	921.2	919.9
157.5°	939.5	940.6	941.7	941.6	940.4	939.1	937.9	936.7
160°	949.0	950.0	950.9	950.8	949.7	948.6	947.5	946.4
162.5°	957.8	958.9	960.0	959.9	958.5	957.1	955.8	954.4
165°	968.6	969.8	970.9	970.9	969.8	968.6	967.5	966.4
167.5°	977.7	978.8	979.9	979.7	978.3	976.9	975.4	974.0
170°	982.2	983.3	984.5	984.3	982.9	981.4	980.0	978.6
172.5°	985.7	986.8	987.9	987.7	986.3	984.9	983.4	982.0
175°	989.4	990.5	991.6	991.4	989.8	988.2	986.6	985.0
177.5°	989.8	990.7	991.6	991.5	990.3	989.2	988.0	986.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6

(END OF REPORT)