

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331449-940

Luminaire Tested: **SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331449-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7147.3 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331449-940  
CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	92	88	92	89	85	83	76	74	72	65	63	62	54	53	52	47
2	91	84	78	73	84	78	73	69	67	64	60	58	55	52	49	47	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	77	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	39	42	37	34	36	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	35	30	37	31	27	32	27	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	26	22	20	17
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28709	28709	28709	28709
5°	32185	28896	25606	28896
10°	36882	28658	22161	28658
15°	40802	28134	19579	28134
20°	40180	27569	17849	27569
25°	36230	26820	16751	26820
30°	29940	25620	15951	25620
35°	21821	24366	15382	24366
40°	17428	22885	15066	22885
45°	15230	21174	14636	21174
50°	14315	19515	14350	19515
55°	13196	17833	13965	17833
60°	12093	16043	13372	16043
65°	11018	14437	12791	14437
70°	10003	12873	11939	12873
75°	8865	11123	10574	11123
80°	7624	9214	8517	9214
85°	6836	6836	5076	6836



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.3	2.4
10°-20°	492.3	6.9
20°-30°	714.5	10.0
30°-40°	754.0	10.5
40°-50°	667.6	9.3
50°-60°	532.7	7.5
60°-70°	362.1	5.1
70°-80°	185.6	2.6
80°-90°	48.9	0.7
90°-100°	185.0	2.6
100°-110°	627.9	8.8
110°-120°	667.1	9.3
120°-130°	549.1	7.7
130°-140°	441.0	6.2
140°-150°	333.2	4.7
150°-160°	234.2	3.3
160°-170°	137.9	1.9
170°-180°	44.9	0.6
0°-30°	1376.1	19.3
0°-40°	2130.1	29.8
0°-60°	3330.4	46.6
0°-90°	3927.0	54.9
90°-120°	1480.0	20.7
90°-150°	2803.4	39.2
90°-180°	3220.0	45.1
0°-180°	7147.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1778	1778	1778	1778	1778	
5°	1986	1783	1580	1783	1986	198
15°	2441	1683	1171	1683	2441	674
25°	2034	1506	940	1506	2034	919
35°	1107	1236	780	1236	1107	720
45°	667	927	641	927	667	524
55°	469	634	496	634	469	420
65°	288	378	335	378	288	287
75°	142	178	170	178	142	152
85°	37	37	27	37	37	41
90°	29	1	29	1	29	18
95°	102	31	102	31	102	132
105°	1003	109	1003	109	1003	970
115°	1320	191	1320	191	1320	1292
125°	1071	267	1071	267	1071	967
135°	887	313	887	313	887	689
145°	708	358	708	358	708	450
155°	595	407	595	407	595	278
165°	522	443	522	443	522	149
175°	471	462	471	462	471	46
180°	463	463	463	463	463	



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1860.1	1860.6	1861.7	1853.0	1851.9	1851.9	1844.2	1837.7	1830.1	1819.6	1820.8
5°	1985.8	1993.3	1996.1	1987.9	1975.6	1974.2	1962.7	1943.5	1925.7	1911.4	1901.1
7.5°	2135.9	2138.9	2132.3	2121.5	2112.3	2095.9	2074.3	2053.1	2023.5	1996.3	1976.0
10°	2249.6	2253.7	2242.1	2226.4	2213.4	2194.3	2162.8	2130.7	2091.8	2054.2	2024.1
12.5°	2336.0	2346.1	2331.2	2329.1	2306.9	2280.6	2243.2	2227.0	2172.1	2119.8	2087.6
15°	2441.0	2440.3	2441.7	2428.7	2412.3	2408.2	2368.6	2325.5	2248.3	2217.5	2164.2
17.5°	2410.7	2421.0	2425.8	2425.6	2425.3	2422.7	2409.9	2382.7	2344.0	2294.2	2232.7
20°	2338.5	2352.2	2354.2	2369.9	2378.8	2390.4	2395.2	2387.6	2363.7	2322.1	2268.8
22.5°	2227.0	2230.8	2237.2	2261.6	2280.9	2310.1	2325.2	2350.5	2341.4	2320.9	2276.4
25°	2033.7	2026.9	2050.8	2063.1	2107.5	2153.9	2187.5	2224.4	2257.2	2277.0	2264.0
27.5°	1801.6	1791.4	1827.2	1859.8	1896.0	1946.2	1998.4	2060.0	2111.3	2175.4	2197.4
30°	1605.9	1612.0	1646.2	1681.1	1735.7	1806.8	1865.5	1933.2	2006.3	2078.1	2128.0
32.5°	1394.9	1418.5	1440.1	1493.5	1541.7	1621.0	1707.0	1791.6	1882.8	1964.4	2041.7
35°	1107.1	1134.3	1164.5	1203.4	1271.0	1349.6	1433.7	1547.8	1672.2	1783.6	1875.2
37.5°	931.8	927.5	944.7	972.9	1027.6	1091.1	1187.8	1300.6	1447.0	1577.9	1707.0
40°	826.9	824.1	836.4	862.4	904.1	950.6	1035.3	1134.3	1270.3	1430.3	1584.0
42.5°	754.7	756.3	763.2	781.5	810.0	848.3	911.8	996.0	1120.6	1271.2	1436.5
45°	667.0	671.7	679.3	688.1	704.5	736.0	771.5	831.7	930.1	1055.8	1218.4
47.5°	603.8	604.0	611.6	619.4	629.1	646.8	675.8	713.5	783.0	885.4	1025.2
50°	569.9	565.2	570.6	576.8	587.0	599.3	618.4	654.0	700.4	783.1	900.0
52.5°	528.3	528.5	533.4	535.7	544.9	557.2	574.7	599.3	641.4	706.1	802.1
55°	468.8	472.2	474.9	479.0	487.2	496.1	509.8	526.2	559.0	607.5	678.6
57.5°	412.8	413.8	416.6	424.4	429.5	437.7	450.8	465.7	487.0	522.9	576.3
60°	374.5	374.5	380.0	383.3	390.2	398.4	408.7	423.0	442.1	471.5	514.6
62.5°	339.5	338.9	341.2	346.7	352.0	359.6	369.8	382.0	400.0	426.1	461.5
65°	288.4	287.0	291.1	292.5	297.9	305.5	313.7	326.6	341.0	360.2	391.6
67.5°	239.2	240.9	243.0	245.6	248.6	256.5	262.0	271.2	283.3	299.2	320.5
70°	211.9	211.9	211.9	213.9	218.0	222.1	227.6	235.1	246.7	260.4	279.5
72.5°	181.2	183.4	185.6	184.4	189.6	192.0	198.6	202.9	213.9	222.7	239.6
75°	142.1	142.1	142.1	145.5	147.6	149.6	153.7	157.8	163.4	174.2	183.2
77.5°	106.0	105.8	106.5	107.3	109.5	111.9	113.2	116.8	121.9	127.0	134.5
80°	82.0	83.4	84.1	85.4	85.4	86.8	87.5	92.3	95.7	99.1	103.9
82.5°	63.4	63.7	63.8	64.1	64.6	65.5	67.2	68.8	70.0	72.9	76.5
85°	36.9	36.2	36.2	37.5	36.9	36.9	38.3	39.6	39.6	40.3	42.4
87.5°	20.1	20.1	20.6	20.1	20.1	20.4	20.1	19.9	20.6	21.4	21.8
90°	29.3	29.3	29.3	29.3	29.3	28.4	26.7	28.4	29.3	30.2	29.3
92.5°	49.3	50.7	50.0	52.9	53.6	59.1	66.6	77.6	97.7	115.7	114.0
95°	101.5	100.6	103.3	110.4	121.9	141.5	178.9	233.2	305.2	348.8	308.8
97.5°	199.7	207.1	220.2	242.1	284.6	348.8	445.1	544.1	624.7	595.6	448.5
100°	318.6	334.7	360.4	398.7	472.6	580.2	702.1	812.5	831.3	703.0	484.1
102.5°	560.7	582.4	614.6	679.9	760.2	874.3	963.5	988.4	908.1	706.6	470.6
105°	1003.0	1015.4	1053.7	1108.8	1164.0	1193.5	1181.9	1081.3	896.2	659.4	444.1
107.5°	1281.2	1297.7	1305.4	1308.4	1301.5	1258.4	1165.8	1014.4	818.1	608.9	430.9
110°	1365.2	1366.1	1358.1	1341.1	1302.9	1229.9	1116.0	956.7	768.9	584.7	428.1



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1363.8	1359.0	1343.8	1315.5	1262.3	1178.7	1056.9	904.0	734.8	569.0	428.7
115°	1319.8	1311.8	1288.6	1247.7	1184.5	1092.9	976.2	839.2	692.4	551.8	432.5
117.5°	1241.3	1234.6	1210.1	1166.9	1102.5	1016.5	910.8	790.4	665.7	543.4	438.9
120°	1190.8	1181.9	1156.0	1114.2	1052.0	970.9	876.6	766.2	651.5	538.4	443.2
122.5°	1138.1	1130.6	1107.6	1066.5	1010.7	937.5	848.1	747.0	639.4	535.6	448.2
125°	1070.6	1063.5	1041.3	1007.5	955.8	889.0	810.7	719.1	622.1	530.4	455.7
127.5°	1011.6	1005.8	986.6	954.9	909.9	848.3	774.5	691.5	606.1	527.4	463.3
130°	978.0	970.9	953.1	922.9	879.3	820.6	750.2	673.7	595.4	525.9	469.0
132.5°	943.2	936.7	920.4	890.1	847.2	792.0	727.5	656.6	586.8	525.2	474.7
135°	887.3	883.7	867.7	838.3	800.0	750.2	691.5	632.8	574.9	524.1	481.4
137.5°	832.5	827.2	813.1	787.8	752.9	709.4	662.8	613.7	566.5	524.0	487.5
140°	794.7	789.4	776.1	752.9	724.4	685.3	644.4	601.6	561.6	523.3	490.4
142.5°	757.0	755.9	744.0	723.0	696.0	663.2	627.9	591.7	556.6	523.3	492.5
145°	708.4	705.7	696.9	681.7	660.3	634.5	607.0	577.6	550.0	521.5	494.8
147.5°	667.6	666.0	660.0	647.9	630.3	611.4	589.9	566.7	543.2	518.4	495.5
150°	643.5	642.6	637.2	626.5	613.1	597.2	578.5	558.9	537.5	516.2	494.8
152.5°	622.8	622.6	618.7	609.4	599.0	585.1	569.2	551.1	532.5	512.6	493.4
155°	595.4	597.2	593.6	587.4	577.6	567.8	554.5	540.2	523.3	506.4	491.2
157.5°	572.0	572.0	570.4	565.3	558.4	550.7	539.5	527.5	514.6	500.0	487.1
160°	557.1	557.1	556.2	551.8	545.5	539.3	529.5	519.7	508.2	495.7	485.0
162.5°	542.9	543.6	542.7	539.7	533.4	528.6	520.2	511.9	502.5	492.1	482.9
165°	522.4	523.3	523.3	519.7	516.2	512.6	506.4	500.2	493.0	485.0	478.8
167.5°	503.5	504.6	504.8	502.8	501.2	498.0	493.7	488.9	483.8	478.8	474.7
170°	492.1	493.9	494.8	492.1	491.2	489.5	485.9	483.2	478.8	475.2	472.6
172.5°	482.9	483.9	484.8	483.6	482.7	481.6	478.8	476.8	473.9	471.0	469.8
175°	470.8	472.6	473.5	472.6	472.6	471.7	470.8	469.9	467.3	466.4	465.5
177.5°	463.5	464.9	465.7	465.7	465.7	465.7	464.9	464.9	463.5	462.8	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1824.6	1820.2	1817.5	1807.7	1798.8	1790.1	1787.4	1788.5	1776.5	1765.0	1760.1
5°	1895.7	1882.0	1869.0	1850.6	1828.7	1804.7	1792.4	1782.9	1759.0	1733.0	1718.0
7.5°	1959.4	1939.8	1914.8	1880.1	1848.2	1810.6	1786.7	1765.5	1730.5	1693.9	1671.5
10°	1998.1	1971.5	1939.4	1897.0	1858.1	1812.3	1780.1	1748.0	1707.0	1663.3	1635.9
12.5°	2031.5	1995.6	1964.0	1909.6	1863.5	1806.2	1768.2	1722.9	1679.7	1627.7	1601.0
15°	2110.9	2044.6	1984.5	1923.0	1866.3	1786.3	1743.9	1683.1	1626.4	1562.2	1531.4
17.5°	2172.3	2097.7	2003.0	1924.9	1858.8	1770.2	1708.0	1635.1	1568.1	1494.7	1452.9
20°	2207.3	2121.8	2020.0	1927.1	1847.8	1746.7	1679.0	1604.5	1526.0	1443.2	1398.2
22.5°	2228.0	2138.2	2037.6	1918.9	1826.0	1727.5	1642.4	1560.8	1481.1	1391.9	1344.6
25°	2234.6	2152.6	2046.0	1912.1	1798.6	1687.2	1584.7	1505.5	1409.1	1325.7	1256.7
27.5°	2202.1	2143.3	2040.8	1899.2	1767.0	1636.8	1522.5	1432.7	1331.1	1240.5	1171.2
30°	2162.1	2128.0	2028.2	1886.1	1741.9	1601.8	1476.0	1374.2	1273.1	1181.5	1110.4
32.5°	2100.4	2093.0	2005.3	1867.5	1715.1	1557.6	1427.5	1324.5	1212.5	1122.5	1054.7
35°	1979.1	2011.8	1956.5	1826.0	1664.6	1494.5	1353.7	1236.2	1120.1	1033.9	970.4
37.5°	1816.4	1897.8	1883.4	1765.1	1596.6	1425.9	1270.5	1147.6	1037.0	950.0	887.7
40°	1704.3	1808.2	1823.2	1718.7	1548.5	1372.9	1208.2	1085.8	977.9	898.7	835.7
42.5°	1584.0	1705.4	1746.7	1662.9	1496.0	1317.1	1152.4	1025.7	918.8	841.8	786.0
45°	1382.4	1543.0	1617.6	1569.7	1408.5	1225.3	1055.8	927.3	830.3	757.9	714.8
47.5°	1194.0	1369.5	1469.6	1452.7	1311.0	1129.6	962.1	838.7	744.3	686.5	648.0
50°	1060.6	1241.0	1361.9	1367.4	1241.0	1061.2	893.1	776.9	690.2	636.2	604.8
52.5°	944.7	1116.9	1248.8	1277.7	1162.8	990.2	831.3	715.8	639.4	589.8	561.6
55°	793.4	939.0	1085.2	1138.4	1046.2	882.3	735.3	633.5	561.7	527.5	502.9
57.5°	659.6	781.0	916.0	974.9	918.0	777.7	639.9	551.4	493.3	463.3	444.4
60°	589.1	684.7	805.0	875.4	826.2	701.2	580.9	496.8	449.0	422.3	404.6
62.5°	523.4	608.2	709.9	774.3	747.4	629.5	521.8	447.6	406.4	381.3	368.5
65°	431.9	498.8	577.5	636.9	619.1	529.6	441.5	377.9	345.1	325.3	315.0
67.5°	355.6	404.0	458.5	510.6	496.2	432.8	362.0	312.5	288.1	271.0	264.8
70°	307.6	344.4	393.0	434.6	423.0	371.0	315.0	272.7	251.5	237.1	231.0
72.5°	261.6	291.9	329.0	363.0	355.2	312.0	265.3	233.3	217.0	203.8	198.8
75°	197.5	220.7	243.3	265.8	263.8	230.3	203.0	178.3	165.4	155.2	153.1
77.5°	145.8	158.8	174.2	187.5	183.8	164.7	143.2	129.1	119.6	112.7	111.6
80°	111.4	118.9	129.8	139.4	134.6	126.4	109.3	99.1	92.3	85.4	82.7
82.5°	80.8	88.3	94.9	100.0	96.4	88.7	78.2	71.2	67.1	62.4	61.3
85°	42.4	46.5	49.2	50.6	49.2	44.4	39.6	36.9	33.5	31.5	30.8
87.5°	21.2	20.0	19.1	19.6	17.7	17.3	14.4	12.2	12.2	12.4	11.6
90°	24.0	17.8	13.4	10.7	8.9	7.1	3.6	0.9	3.6	7.1	8.9
92.5°	88.8	60.5	40.4	32.0	25.9	22.1	15.7	10.9	15.7	22.1	25.9
95°	205.5	128.1	87.2	65.9	51.6	43.6	34.7	31.1	34.7	43.6	51.6
97.5°	277.0	169.1	117.6	93.5	77.0	65.0	55.6	50.7	55.6	65.0	77.0
100°	291.9	183.3	136.2	111.3	93.5	79.2	71.2	68.5	71.2	79.2	93.5
102.5°	292.7	196.2	152.6	127.6	109.1	94.9	86.9	84.9	86.9	94.9	109.1
105°	297.2	218.0	176.2	151.3	131.7	118.3	112.2	108.6	112.2	118.3	131.7
107.5°	309.5	240.5	199.9	174.8	155.4	143.1	137.1	134.2	137.1	143.1	155.4
110°	319.5	255.4	216.2	190.5	171.7	160.2	154.9	151.3	154.9	160.2	171.7





TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	330.2	269.7	231.9	205.4	187.4	176.6	170.5	166.9	170.5	176.6	187.4
115°	346.2	291.9	253.6	229.6	211.8	201.2	195.8	191.4	195.8	201.2	211.8
117.5°	363.3	312.4	277.0	252.0	235.0	225.5	220.2	216.6	220.2	225.5	235.0
120°	374.7	326.6	291.9	267.0	249.1	241.2	235.9	232.3	235.9	241.2	249.1
122.5°	384.6	340.1	307.6	282.0	264.1	255.4	250.0	247.3	250.0	255.4	264.1
125°	400.5	360.4	328.4	303.4	285.7	275.0	269.7	267.0	269.7	275.0	285.7
127.5°	415.3	379.3	348.1	322.5	305.4	293.6	286.2	282.7	286.2	293.6	305.4
130°	424.5	390.7	359.5	334.7	316.8	304.3	295.4	291.9	295.4	304.3	316.8
132.5°	433.7	400.6	371.0	346.0	327.5	314.3	304.7	300.4	304.7	314.3	327.5
135°	445.9	414.7	386.2	361.3	340.8	327.5	316.8	313.3	316.8	327.5	340.8
137.5°	455.1	426.1	398.0	374.9	354.5	340.3	329.7	325.4	329.7	340.3	354.5
140°	460.1	432.5	405.8	382.7	363.1	348.8	338.2	334.7	338.2	348.8	363.1
142.5°	464.4	437.5	411.5	389.8	371.0	356.7	346.7	343.8	346.7	356.7	371.0
145°	469.9	445.0	421.0	401.4	383.6	370.2	361.3	357.8	361.3	370.2	383.6
147.5°	473.0	451.0	428.5	411.0	396.2	383.9	375.4	372.7	375.4	383.9	396.2
150°	474.3	453.9	433.4	417.4	404.0	392.4	385.3	382.7	385.3	392.4	404.0
152.5°	475.0	456.7	438.4	423.8	411.2	401.0	393.9	392.6	393.9	401.0	411.2
155°	476.1	461.0	445.9	432.5	422.8	413.0	407.6	406.7	407.6	413.0	422.8
157.5°	476.1	464.0	451.2	440.0	432.1	423.7	419.4	418.5	419.4	423.7	432.1
160°	476.1	465.5	454.8	445.0	437.8	430.7	427.2	426.3	427.2	430.7	437.8
162.5°	475.4	466.2	456.9	449.2	442.8	437.1	433.5	434.1	433.5	437.1	442.8
165°	473.5	467.3	459.2	453.9	449.4	444.1	442.3	443.2	442.3	444.1	449.4
167.5°	472.3	467.1	461.2	457.8	454.6	451.2	449.6	450.7	449.6	451.2	454.6
170°	470.8	466.4	461.9	459.2	457.4	454.8	453.9	455.7	453.9	454.8	457.4
172.5°	468.7	465.7	462.6	460.7	459.6	456.9	457.4	458.5	457.4	456.9	459.6
175°	466.4	464.6	462.8	461.9	461.9	460.1	461.0	461.9	461.0	460.1	461.9
177.5°	464.9	463.5	462.8	462.8	462.8	461.4	462.1	463.5	462.1	461.4	462.8
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1754.6	1751.3	1739.8	1733.8	1724.0	1714.7	1708.7	1711.5	1713.6	1712.5	1710.8
5°	1704.3	1691.3	1671.5	1654.4	1642.1	1619.6	1610.0	1605.3	1601.2	1596.3	1591.5
7.5°	1644.4	1624.0	1595.5	1571.2	1548.2	1520.2	1504.2	1494.7	1484.8	1474.0	1464.5
10°	1601.8	1573.1	1543.0	1508.9	1481.6	1456.3	1433.7	1418.6	1405.0	1392.0	1382.4
12.5°	1557.0	1523.9	1486.7	1440.0	1409.9	1373.7	1370.3	1343.8	1322.4	1314.4	1303.1
15°	1485.6	1439.1	1392.0	1336.7	1312.8	1280.0	1259.5	1238.9	1220.5	1207.5	1204.1
17.5°	1404.6	1344.4	1297.5	1257.8	1218.6	1185.0	1166.1	1149.7	1134.5	1117.1	1114.8
20°	1342.8	1290.8	1239.7	1204.8	1164.5	1130.2	1107.1	1090.7	1077.6	1067.4	1058.5
22.5°	1284.3	1227.4	1180.5	1142.5	1102.7	1075.0	1056.8	1040.9	1030.1	1018.8	1010.4
25°	1190.4	1146.0	1094.8	1051.7	1018.9	1001.1	986.1	972.4	965.6	958.1	948.5
27.5°	1108.3	1058.9	1010.9	977.6	948.8	933.1	922.4	913.1	906.7	902.3	896.9
30°	1050.3	1000.4	962.9	930.1	906.2	890.5	883.6	878.2	870.6	867.9	865.1
32.5°	994.5	949.6	917.5	889.0	866.2	856.0	849.7	844.8	838.9	836.2	830.7
35°	915.7	878.2	846.7	831.0	812.5	803.6	798.9	792.0	786.6	783.8	783.1
37.5°	841.5	808.9	788.2	767.9	760.2	754.7	748.1	743.5	741.9	741.5	740.7
40°	793.4	766.7	748.3	731.9	728.4	720.2	714.8	710.7	710.7	711.4	710.7
42.5°	749.7	725.8	709.4	695.3	691.3	686.3	680.9	680.6	681.7	684.0	681.7
45°	683.4	666.3	654.7	647.8	640.3	635.5	634.8	636.9	637.6	638.3	640.3
47.5°	622.4	611.1	600.6	593.0	589.8	588.9	588.1	591.7	594.9	596.2	599.3
50°	586.3	573.4	564.5	559.6	557.0	555.5	557.0	561.1	563.7	567.2	569.3
52.5°	545.9	536.7	530.6	526.9	525.8	526.6	526.9	531.5	535.9	537.2	538.1
55°	490.0	483.1	481.8	475.6	478.3	477.7	481.1	483.8	487.9	492.0	492.7
57.5°	434.2	428.7	425.1	425.6	426.4	429.4	432.3	437.1	441.5	445.9	446.2
60°	397.1	394.3	392.3	392.3	393.6	397.7	401.1	405.9	408.7	411.3	413.4
62.5°	363.1	360.4	358.4	359.4	363.0	365.4	369.4	372.0	374.8	377.5	378.4
65°	309.6	308.2	310.2	311.7	312.3	315.8	320.5	322.5	325.3	326.6	331.4
67.5°	260.2	260.5	260.2	262.2	266.1	266.9	271.4	276.3	276.8	279.4	282.5
70°	226.9	228.3	229.6	231.0	234.4	235.8	239.2	241.2	244.0	246.0	248.1
72.5°	196.3	196.5	197.9	197.6	200.5	203.5	206.3	208.4	211.2	213.7	215.8
75°	151.1	151.1	152.4	153.1	156.5	159.9	159.3	160.6	163.4	166.0	167.5
77.5°	110.3	108.8	110.3	111.0	112.1	114.9	115.5	117.4	120.6	119.6	121.1
80°	84.1	82.0	84.1	84.7	84.7	88.2	88.2	89.5	91.6	89.5	91.6
82.5°	60.0	59.0	60.5	60.7	61.8	61.9	63.0	63.3	65.4	64.4	65.4
85°	30.1	29.4	30.1	29.4	30.1	30.8	30.8	30.1	30.1	31.5	29.4
87.5°	11.4	11.4	11.8	13.0	13.6	13.2	12.4	12.2	11.9	11.1	11.3
90°	10.7	13.4	17.8	24.0	29.3	30.2	29.3	28.4	26.7	28.4	29.3
92.5°	32.0	40.4	60.5	88.8	114.0	115.7	97.7	77.6	66.6	59.1	53.6
95°	65.9	87.2	128.1	205.5	308.8	348.8	305.2	233.2	178.9	141.5	121.9
97.5°	93.5	117.6	169.1	277.0	448.5	595.6	624.7	544.1	445.1	348.8	284.6
100°	111.3	136.2	183.3	291.9	484.1	703.0	831.3	812.5	702.1	580.2	472.6
102.5°	127.6	152.6	196.2	292.7	470.6	706.6	908.1	988.4	963.5	874.3	760.2
105°	151.3	176.2	218.0	297.2	444.1	659.4	896.2	1081.3	1181.9	1193.5	1164.0
107.5°	174.8	199.9	240.5	309.5	430.9	608.9	818.1	1014.4	1165.8	1258.4	1301.5
110°	190.5	216.2	255.4	319.5	428.1	584.7	768.9	956.7	1116.0	1229.9	1302.9



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	205.4	231.9	269.7	330.2	428.7	569.0	734.8	904.0	1056.9	1178.7	1262.3
115°	229.6	253.6	291.9	346.2	432.5	551.8	692.4	839.2	976.2	1092.9	1184.5
117.5°	252.0	277.0	312.4	363.3	438.9	543.4	665.7	790.4	910.8	1016.5	1102.5
120°	267.0	291.9	326.6	374.7	443.2	538.4	651.5	766.2	876.6	970.9	1052.0
122.5°	282.0	307.6	340.1	384.6	448.2	535.6	639.4	747.0	848.1	937.5	1010.7
125°	303.4	328.4	360.4	400.5	455.7	530.4	622.1	719.1	810.7	889.0	955.8
127.5°	322.5	348.1	379.3	415.3	463.3	527.4	606.1	691.5	774.5	848.3	909.9
130°	334.7	359.5	390.7	424.5	469.0	525.9	595.4	673.7	750.2	820.6	879.3
132.5°	346.0	371.0	400.6	433.7	474.7	525.2	586.8	656.6	727.5	792.0	847.2
135°	361.3	386.2	414.7	445.9	481.4	524.1	574.9	632.8	691.5	750.2	800.0
137.5°	374.9	398.0	426.1	455.1	487.5	524.0	566.5	613.7	662.8	709.4	752.9
140°	382.7	405.8	432.5	460.1	490.4	523.3	561.6	601.6	644.4	685.3	724.4
142.5°	389.8	411.5	437.5	464.4	492.5	523.3	556.6	591.7	627.9	663.2	696.0
145°	401.4	421.0	445.0	469.9	494.8	521.5	550.0	577.6	607.0	634.5	660.3
147.5°	411.0	428.5	451.0	473.0	495.5	518.4	543.2	566.7	589.9	611.4	630.3
150°	417.4	433.4	453.9	474.3	494.8	516.2	537.5	558.9	578.5	597.2	613.1
152.5°	423.8	438.4	456.7	475.0	493.4	512.6	532.5	551.1	569.2	585.1	599.0
155°	432.5	445.9	461.0	476.1	491.2	506.4	523.3	540.2	554.5	567.8	577.6
157.5°	440.0	451.2	464.0	476.1	487.1	500.0	514.6	527.5	539.5	550.7	558.4
160°	445.0	454.8	465.5	476.1	485.0	495.7	508.2	519.7	529.5	539.3	545.5
162.5°	449.2	456.9	466.2	475.4	482.9	492.1	502.5	511.9	520.2	528.6	533.4
165°	453.9	459.2	467.3	473.5	478.8	485.0	493.0	500.2	506.4	512.6	516.2
167.5°	457.8	461.2	467.1	472.3	474.7	478.8	483.8	488.9	493.7	498.0	501.2
170°	459.2	461.9	466.4	470.8	472.6	475.2	478.8	483.2	485.9	489.5	491.2
172.5°	460.7	462.6	465.7	468.7	469.8	471.0	473.9	476.8	478.8	481.6	482.7
175°	461.9	462.8	464.6	466.4	465.5	466.4	467.3	469.9	470.8	471.7	472.6
177.5°	462.8	462.8	463.5	464.9	463.5	462.8	463.5	464.9	464.9	465.7	465.7
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1705.4	1704.3	1704.3	1699.4	1704.3	1704.3	1705.4	1710.8	1712.5	1713.6	1711.5
5°	1582.0	1579.9	1576.5	1579.9	1576.5	1579.9	1582.0	1591.5	1596.3	1601.2	1605.3
7.5°	1459.9	1451.7	1450.5	1442.4	1450.5	1451.7	1459.9	1464.5	1474.0	1484.8	1494.7
10°	1370.8	1365.4	1364.7	1351.7	1364.7	1365.4	1370.8	1382.4	1392.0	1405.0	1418.6
12.5°	1303.1	1289.9	1292.5	1285.0	1292.5	1289.9	1303.1	1303.1	1314.4	1322.4	1343.8
15°	1185.6	1185.6	1182.9	1171.3	1182.9	1185.6	1185.6	1204.1	1207.5	1220.5	1238.9
17.5°	1101.4	1099.9	1093.4	1096.6	1093.4	1099.9	1101.4	1114.8	1117.1	1134.5	1149.7
20°	1051.0	1047.0	1038.8	1038.8	1038.8	1047.0	1051.0	1058.5	1067.4	1077.6	1090.7
22.5°	1003.4	1003.2	994.4	997.2	994.4	1003.2	1003.4	1010.4	1018.8	1030.1	1040.9
25°	947.8	942.4	938.3	940.3	938.3	942.4	947.8	948.5	958.1	965.6	972.4
27.5°	895.1	892.1	891.8	886.2	891.8	892.1	895.1	896.9	902.3	906.7	913.1
30°	864.4	857.6	859.0	855.6	859.0	857.6	864.4	865.1	867.9	870.6	878.2
32.5°	829.5	827.0	825.6	822.8	825.6	827.0	829.5	830.7	836.2	838.9	844.8
35°	781.8	782.5	779.0	780.4	779.0	782.5	781.8	783.1	783.8	786.6	792.0
37.5°	740.1	742.3	740.7	741.0	740.7	742.3	740.1	740.7	741.5	741.9	743.5
40°	712.7	712.7	712.7	714.8	712.7	712.7	712.7	710.7	711.4	710.7	710.7
42.5°	686.5	685.5	684.3	684.2	684.3	685.5	686.5	681.7	684.0	681.7	680.6
45°	641.7	643.7	644.4	641.0	644.4	643.7	641.7	640.3	638.3	637.6	636.9
47.5°	601.1	601.4	601.1	604.1	601.1	601.4	601.1	599.3	596.2	594.9	591.7
50°	572.7	571.3	572.7	571.3	572.7	571.3	572.7	569.3	567.2	563.7	561.1
52.5°	542.6	542.9	542.1	541.8	542.1	542.9	542.6	538.1	537.2	535.9	531.5
55°	495.4	496.8	496.1	496.1	496.1	496.8	495.4	492.7	492.0	487.9	483.8
57.5°	446.7	447.9	448.8	445.9	448.8	447.9	446.7	446.2	445.9	441.5	437.1
60°	412.8	416.2	415.4	414.1	415.4	416.2	412.8	413.4	411.3	408.7	405.9
62.5°	381.6	382.8	382.7	382.5	382.7	382.8	381.6	378.4	377.5	374.8	372.0
65°	333.5	334.8	332.8	334.8	332.8	334.8	333.5	331.4	326.6	325.3	322.5
67.5°	281.7	282.1	283.6	284.5	283.6	282.1	281.7	282.5	279.4	276.8	276.3
70°	249.4	248.8	250.8	252.9	250.8	248.8	249.4	248.1	246.0	244.0	241.2
72.5°	215.5	217.0	216.3	217.8	216.3	217.0	215.5	215.8	213.7	211.2	208.4
75°	166.0	168.1	167.5	169.5	167.5	168.1	166.0	167.5	166.0	163.4	160.6
77.5°	120.0	120.3	120.0	121.1	120.0	120.3	120.0	121.1	119.6	120.6	117.4
80°	91.6	90.2	88.8	91.6	88.8	90.2	91.6	91.6	89.5	91.6	89.5
82.5°	63.7	64.5	63.1	63.1	63.1	64.5	63.7	65.4	64.4	65.4	63.3
85°	29.4	28.7	27.4	27.4	27.4	28.7	29.4	29.4	31.5	30.1	30.1
87.5°	11.3	10.8	10.8	10.3	10.8	10.8	11.3	11.3	11.1	11.9	12.2
90°	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	28.4	26.7	28.4
92.5°	52.9	50.0	50.7	49.3	50.7	50.0	52.9	53.6	59.1	66.6	77.6
95°	110.4	103.3	100.6	101.5	100.6	103.3	110.4	121.9	141.5	178.9	233.2
97.5°	242.1	220.2	207.1	199.7	207.1	220.2	242.1	284.6	348.8	445.1	544.1
100°	398.7	360.4	334.7	318.6	334.7	360.4	398.7	472.6	580.2	702.1	812.5
102.5°	679.9	614.6	582.4	560.7	582.4	614.6	679.9	760.2	874.3	963.5	988.4
105°	1108.8	1053.7	1015.4	1003.0	1015.4	1053.7	1108.8	1164.0	1193.5	1181.9	1081.3
107.5°	1308.4	1305.4	1297.7	1281.2	1297.7	1305.4	1308.4	1301.5	1258.4	1165.8	1014.4
110°	1341.1	1358.1	1366.1	1365.2	1366.1	1358.1	1341.1	1302.9	1229.9	1116.0	956.7



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1315.5	1343.8	1359.0	1363.8	1359.0	1343.8	1315.5	1262.3	1178.7	1056.9	904.0
115°	1247.7	1288.6	1311.8	1319.8	1311.8	1288.6	1247.7	1184.5	1092.9	976.2	839.2
117.5°	1166.9	1210.1	1234.6	1241.3	1234.6	1210.1	1166.9	1102.5	1016.5	910.8	790.4
120°	1114.2	1156.0	1181.9	1190.8	1181.9	1156.0	1114.2	1052.0	970.9	876.6	766.2
122.5°	1066.5	1107.6	1130.6	1138.1	1130.6	1107.6	1066.5	1010.7	937.5	848.1	747.0
125°	1007.5	1041.3	1063.5	1070.6	1063.5	1041.3	1007.5	955.8	889.0	810.7	719.1
127.5°	954.9	986.6	1005.8	1011.6	1005.8	986.6	954.9	909.9	848.3	774.5	691.5
130°	922.9	953.1	970.9	978.0	970.9	953.1	922.9	879.3	820.6	750.2	673.7
132.5°	890.1	920.4	936.7	943.2	936.7	920.4	890.1	847.2	792.0	727.5	656.6
135°	838.3	867.7	883.7	887.3	883.7	867.7	838.3	800.0	750.2	691.5	632.8
137.5°	787.8	813.1	827.2	832.5	827.2	813.1	787.8	752.9	709.4	662.8	613.7
140°	752.9	776.1	789.4	794.7	789.4	776.1	752.9	724.4	685.3	644.4	601.6
142.5°	723.0	744.0	755.9	757.0	755.9	744.0	723.0	696.0	663.2	627.9	591.7
145°	681.7	696.9	705.7	708.4	705.7	696.9	681.7	660.3	634.5	607.0	577.6
147.5°	647.9	660.0	666.0	667.6	666.0	660.0	647.9	630.3	611.4	589.9	566.7
150°	626.5	637.2	642.6	643.5	642.6	637.2	626.5	613.1	597.2	578.5	558.9
152.5°	609.4	618.7	622.6	622.8	622.6	618.7	609.4	599.0	585.1	569.2	551.1
155°	587.4	593.6	597.2	595.4	597.2	593.6	587.4	577.6	567.8	554.5	540.2
157.5°	565.3	570.4	572.0	572.0	572.0	570.4	565.3	558.4	550.7	539.5	527.5
160°	551.8	556.2	557.1	557.1	557.1	556.2	551.8	545.5	539.3	529.5	519.7
162.5°	539.7	542.7	543.6	542.9	543.6	542.7	539.7	533.4	528.6	520.2	511.9
165°	519.7	523.3	523.3	522.4	523.3	523.3	519.7	516.2	512.6	506.4	500.2
167.5°	502.8	504.8	504.6	503.5	504.6	504.8	502.8	501.2	498.0	493.7	488.9
170°	492.1	494.8	493.9	492.1	493.9	494.8	492.1	491.2	489.5	485.9	483.2
172.5°	483.6	484.8	483.9	482.9	483.9	484.8	483.6	482.7	481.6	478.8	476.8
175°	472.6	473.5	472.6	470.8	472.6	473.5	472.6	472.6	471.7	470.8	469.9
177.5°	465.7	465.7	464.9	463.5	464.9	465.7	465.7	465.7	465.7	464.9	464.9
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331449-940  
 CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1708.7	1714.7	1724.0	1733.8	1739.8	1751.3	1754.6	1760.1	1765.0	1776.5	1788.5
5°	1610.0	1619.6	1642.1	1654.4	1671.5	1691.3	1704.3	1718.0	1733.0	1759.0	1782.9
7.5°	1504.2	1520.2	1548.2	1571.2	1595.5	1624.0	1644.4	1671.5	1693.9	1730.5	1765.5
10°	1433.7	1456.3	1481.6	1508.9	1543.0	1573.1	1601.8	1635.9	1663.3	1707.0	1748.0
12.5°	1370.3	1373.7	1409.9	1440.0	1486.7	1523.9	1557.0	1601.0	1627.7	1679.7	1722.9
15°	1259.5	1280.0	1312.8	1336.7	1392.0	1439.1	1485.6	1531.4	1562.2	1626.4	1683.1
17.5°	1166.1	1185.0	1218.6	1257.8	1297.5	1344.4	1404.6	1452.9	1494.7	1568.1	1635.1
20°	1107.1	1130.2	1164.5	1204.8	1239.7	1290.8	1342.8	1398.2	1443.2	1526.0	1604.5
22.5°	1056.8	1075.0	1102.7	1142.5	1180.5	1227.4	1284.3	1344.6	1391.9	1481.1	1560.8
25°	986.1	1001.1	1018.9	1051.7	1094.8	1146.0	1190.4	1256.7	1325.7	1409.1	1505.5
27.5°	922.4	933.1	948.8	977.6	1010.9	1058.9	1108.3	1171.2	1240.5	1331.1	1432.7
30°	883.6	890.5	906.2	930.1	962.9	1000.4	1050.3	1110.4	1181.5	1273.1	1374.2
32.5°	849.7	856.0	866.2	889.0	917.5	949.6	994.5	1054.7	1122.5	1212.5	1324.5
35°	798.9	803.6	812.5	831.0	846.7	878.2	915.7	970.4	1033.9	1120.1	1236.2
37.5°	748.1	754.7	760.2	767.9	788.2	808.9	841.5	887.7	950.0	1037.0	1147.6
40°	714.8	720.2	728.4	731.9	748.3	766.7	793.4	835.7	898.7	977.9	1085.8
42.5°	680.9	686.3	691.3	695.3	709.4	725.8	749.7	786.0	841.8	918.8	1025.7
45°	634.8	635.5	640.3	647.8	654.7	666.3	683.4	714.8	757.9	830.3	927.3
47.5°	588.1	588.9	589.8	593.0	600.6	611.1	622.4	648.0	686.5	744.3	838.7
50°	557.0	555.5	557.0	559.6	564.5	573.4	586.3	604.8	636.2	690.2	776.9
52.5°	526.9	526.6	525.8	526.9	530.6	536.7	545.9	561.6	589.8	639.4	715.8
55°	481.1	477.7	478.3	475.6	481.8	483.1	490.0	502.9	527.5	561.7	633.5
57.5°	432.3	429.4	426.4	425.6	425.1	428.7	434.2	444.4	463.3	493.3	551.4
60°	401.1	397.7	393.6	392.3	392.3	394.3	397.1	404.6	422.3	449.0	496.8
62.5°	369.4	365.4	363.0	359.4	358.4	360.4	363.1	368.5	381.3	406.4	447.6
65°	320.5	315.8	312.3	311.7	310.2	308.2	309.6	315.0	325.3	345.1	377.9
67.5°	271.4	266.9	266.1	262.2	260.2	260.5	260.2	264.8	271.0	288.1	312.5
70°	239.2	235.8	234.4	231.0	229.6	228.3	226.9	231.0	237.1	251.5	272.7
72.5°	206.3	203.5	200.5	197.6	197.9	196.5	196.3	198.8	203.8	217.0	233.3
75°	159.3	159.9	156.5	153.1	152.4	151.1	151.1	153.1	155.2	165.4	178.3
77.5°	115.5	114.9	112.1	111.0	110.3	108.8	110.3	111.6	112.7	119.6	129.1
80°	88.2	88.2	84.7	84.7	84.1	82.0	84.1	82.7	85.4	92.3	99.1
82.5°	63.0	61.9	61.8	60.7	60.5	59.0	60.0	61.3	62.4	67.1	71.2
85°	30.8	30.8	30.1	29.4	30.1	29.4	30.1	30.8	31.5	33.5	36.9
87.5°	12.4	13.2	13.6	13.0	11.8	11.4	11.4	11.6	12.4	12.2	12.2
90°	29.3	30.2	29.3	24.0	17.8	13.4	10.7	8.9	7.1	3.6	0.9
92.5°	97.7	115.7	114.0	88.8	60.5	40.4	32.0	25.9	22.1	15.7	10.9
95°	305.2	348.8	308.8	205.5	128.1	87.2	65.9	51.6	43.6	34.7	31.1
97.5°	624.7	595.6	448.5	277.0	169.1	117.6	93.5	77.0	65.0	55.6	50.7
100°	831.3	703.0	484.1	291.9	183.3	136.2	111.3	93.5	79.2	71.2	68.5
102.5°	908.1	706.6	470.6	292.7	196.2	152.6	127.6	109.1	94.9	86.9	84.9
105°	896.2	659.4	444.1	297.2	218.0	176.2	151.3	131.7	118.3	112.2	108.6
107.5°	818.1	608.9	430.9	309.5	240.5	199.9	174.8	155.4	143.1	137.1	134.2
110°	768.9	584.7	428.1	319.5	255.4	216.2	190.5	171.7	160.2	154.9	151.3



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	734.8	569.0	428.7	330.2	269.7	231.9	205.4	187.4	176.6	170.5	166.9
115°	692.4	551.8	432.5	346.2	291.9	253.6	229.6	211.8	201.2	195.8	191.4
117.5°	665.7	543.4	438.9	363.3	312.4	277.0	252.0	235.0	225.5	220.2	216.6
120°	651.5	538.4	443.2	374.7	326.6	291.9	267.0	249.1	241.2	235.9	232.3
122.5°	639.4	535.6	448.2	384.6	340.1	307.6	282.0	264.1	255.4	250.0	247.3
125°	622.1	530.4	455.7	400.5	360.4	328.4	303.4	285.7	275.0	269.7	267.0
127.5°	606.1	527.4	463.3	415.3	379.3	348.1	322.5	305.4	293.6	286.2	282.7
130°	595.4	525.9	469.0	424.5	390.7	359.5	334.7	316.8	304.3	295.4	291.9
132.5°	586.8	525.2	474.7	433.7	400.6	371.0	346.0	327.5	314.3	304.7	300.4
135°	574.9	524.1	481.4	445.9	414.7	386.2	361.3	340.8	327.5	316.8	313.3
137.5°	566.5	524.0	487.5	455.1	426.1	398.0	374.9	354.5	340.3	329.7	325.4
140°	561.6	523.3	490.4	460.1	432.5	405.8	382.7	363.1	348.8	338.2	334.7
142.5°	556.6	523.3	492.5	464.4	437.5	411.5	389.8	371.0	356.7	346.7	343.8
145°	550.0	521.5	494.8	469.9	445.0	421.0	401.4	383.6	370.2	361.3	357.8
147.5°	543.2	518.4	495.5	473.0	451.0	428.5	411.0	396.2	383.9	375.4	372.7
150°	537.5	516.2	494.8	474.3	453.9	433.4	417.4	404.0	392.4	385.3	382.7
152.5°	532.5	512.6	493.4	475.0	456.7	438.4	423.8	411.2	401.0	393.9	392.6
155°	523.3	506.4	491.2	476.1	461.0	445.9	432.5	422.8	413.0	407.6	406.7
157.5°	514.6	500.0	487.1	476.1	464.0	451.2	440.0	432.1	423.7	419.4	418.5
160°	508.2	495.7	485.0	476.1	465.5	454.8	445.0	437.8	430.7	427.2	426.3
162.5°	502.5	492.1	482.9	475.4	466.2	456.9	449.2	442.8	437.1	433.5	434.1
165°	493.0	485.0	478.8	473.5	467.3	459.2	453.9	449.4	444.1	442.3	443.2
167.5°	483.8	478.8	474.7	472.3	467.1	461.2	457.8	454.6	451.2	449.6	450.7
170°	478.8	475.2	472.6	470.8	466.4	461.9	459.2	457.4	454.8	453.9	455.7
172.5°	473.9	471.0	469.8	468.7	465.7	462.6	460.7	459.6	456.9	457.4	458.5
175°	467.3	466.4	465.5	466.4	464.6	462.8	461.9	461.9	460.1	461.0	461.9
177.5°	463.5	462.8	463.5	464.9	463.5	462.8	462.8	462.8	461.4	462.1	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1787.4	1790.1	1798.8	1807.7	1817.5	1820.2	1824.6	1820.8	1819.6	1830.1	1837.7
5°	1792.4	1804.7	1828.7	1850.6	1869.0	1882.0	1895.7	1901.1	1911.4	1925.7	1943.5
7.5°	1786.7	1810.6	1848.2	1880.1	1914.8	1939.8	1959.4	1976.0	1996.3	2023.5	2053.1
10°	1780.1	1812.3	1858.1	1897.0	1939.4	1971.5	1998.1	2024.1	2054.2	2091.8	2130.7
12.5°	1768.2	1806.2	1863.5	1909.6	1964.0	1995.6	2031.5	2087.6	2119.8	2172.1	2227.0
15°	1743.9	1786.3	1866.3	1923.0	1984.5	2044.6	2110.9	2164.2	2217.5	2248.3	2325.5
17.5°	1708.0	1770.2	1858.8	1924.9	2003.0	2097.7	2172.3	2232.7	2294.2	2344.0	2382.7
20°	1679.0	1746.7	1847.8	1927.1	2020.0	2121.8	2207.3	2268.8	2322.1	2363.7	2387.6
22.5°	1642.4	1727.5	1826.0	1918.9	2037.6	2138.2	2228.0	2276.4	2320.9	2341.4	2350.5
25°	1584.7	1687.2	1798.6	1912.1	2046.0	2152.6	2234.6	2264.0	2277.0	2257.2	2224.4
27.5°	1522.5	1636.8	1767.0	1899.2	2040.8	2143.3	2202.1	2197.4	2175.4	2111.3	2060.0
30°	1476.0	1601.8	1741.9	1886.1	2028.2	2128.0	2162.1	2128.0	2078.1	2006.3	1933.2
32.5°	1427.5	1557.6	1715.1	1867.5	2005.3	2093.0	2100.4	2041.7	1964.4	1882.8	1791.6
35°	1353.7	1494.5	1664.6	1826.0	1956.5	2011.8	1979.1	1875.2	1783.6	1672.2	1547.8
37.5°	1270.5	1425.9	1596.6	1765.1	1883.4	1897.8	1816.4	1707.0	1577.9	1447.0	1300.6
40°	1208.2	1372.9	1548.5	1718.7	1823.2	1808.2	1704.3	1584.0	1430.3	1270.3	1134.3
42.5°	1152.4	1317.1	1496.0	1662.9	1746.7	1705.4	1584.0	1436.5	1271.2	1120.6	996.0
45°	1055.8	1225.3	1408.5	1569.7	1617.6	1543.0	1382.4	1218.4	1055.8	930.1	831.7
47.5°	962.1	1129.6	1311.0	1452.7	1469.6	1369.5	1194.0	1025.2	885.4	783.0	713.5
50°	893.1	1061.2	1241.0	1367.4	1361.9	1241.0	1060.6	900.0	783.1	700.4	654.0
52.5°	831.3	990.2	1162.8	1277.7	1248.8	1116.9	944.7	802.1	706.1	641.4	599.3
55°	735.3	882.3	1046.2	1138.4	1085.2	939.0	793.4	678.6	607.5	559.0	526.2
57.5°	639.9	777.7	918.0	974.9	916.0	781.0	659.6	576.3	522.9	487.0	465.7
60°	580.9	701.2	826.2	875.4	805.0	684.7	589.1	514.6	471.5	442.1	423.0
62.5°	521.8	629.5	747.4	774.3	709.9	608.2	523.4	461.5	426.1	400.0	382.0
65°	441.5	529.6	619.1	636.9	577.5	498.8	431.9	391.6	360.2	341.0	326.6
67.5°	362.0	432.8	496.2	510.6	458.5	404.0	355.6	320.5	299.2	283.3	271.2
70°	315.0	371.0	423.0	434.6	393.0	344.4	307.6	279.5	260.4	246.7	235.1
72.5°	265.3	312.0	355.2	363.0	329.0	291.9	261.6	239.6	222.7	213.9	202.9
75°	203.0	230.3	263.8	265.8	243.3	220.7	197.5	183.2	174.2	163.4	157.8
77.5°	143.2	164.7	183.8	187.5	174.2	158.8	145.8	134.5	127.0	121.9	116.8
80°	109.3	126.4	134.6	139.4	129.8	118.9	111.4	103.9	99.1	95.7	92.3
82.5°	78.2	88.7	96.4	100.0	94.9	88.3	80.8	76.5	72.9	70.0	68.8
85°	39.6	44.4	49.2	50.6	49.2	46.5	42.4	42.4	40.3	39.6	39.6
87.5°	14.4	17.3	17.7	19.6	19.1	20.0	21.2	21.8	21.4	20.6	19.9
90°	3.6	7.1	8.9	10.7	13.4	17.8	24.0	29.3	30.2	29.3	28.4
92.5°	15.7	22.1	25.9	32.0	40.4	60.5	88.8	114.0	115.7	97.7	77.6
95°	34.7	43.6	51.6	65.9	87.2	128.1	205.5	308.8	348.8	305.2	233.2
97.5°	55.6	65.0	77.0	93.5	117.6	169.1	277.0	448.5	595.6	624.7	544.1
100°	71.2	79.2	93.5	111.3	136.2	183.3	291.9	484.1	703.0	831.3	812.5
102.5°	86.9	94.9	109.1	127.6	152.6	196.2	292.7	470.6	706.6	908.1	988.4
105°	112.2	118.3	131.7	151.3	176.2	218.0	297.2	444.1	659.4	896.2	1081.3
107.5°	137.1	143.1	155.4	174.8	199.9	240.5	309.5	430.9	608.9	818.1	1014.4
110°	154.9	160.2	171.7	190.5	216.2	255.4	319.5	428.1	584.7	768.9	956.7





TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	170.5	176.6	187.4	205.4	231.9	269.7	330.2	428.7	569.0	734.8	904.0
115°	195.8	201.2	211.8	229.6	253.6	291.9	346.2	432.5	551.8	692.4	839.2
117.5°	220.2	225.5	235.0	252.0	277.0	312.4	363.3	438.9	543.4	665.7	790.4
120°	235.9	241.2	249.1	267.0	291.9	326.6	374.7	443.2	538.4	651.5	766.2
122.5°	250.0	255.4	264.1	282.0	307.6	340.1	384.6	448.2	535.6	639.4	747.0
125°	269.7	275.0	285.7	303.4	328.4	360.4	400.5	455.7	530.4	622.1	719.1
127.5°	286.2	293.6	305.4	322.5	348.1	379.3	415.3	463.3	527.4	606.1	691.5
130°	295.4	304.3	316.8	334.7	359.5	390.7	424.5	469.0	525.9	595.4	673.7
132.5°	304.7	314.3	327.5	346.0	371.0	400.6	433.7	474.7	525.2	586.8	656.6
135°	316.8	327.5	340.8	361.3	386.2	414.7	445.9	481.4	524.1	574.9	632.8
137.5°	329.7	340.3	354.5	374.9	398.0	426.1	455.1	487.5	524.0	566.5	613.7
140°	338.2	348.8	363.1	382.7	405.8	432.5	460.1	490.4	523.3	561.6	601.6
142.5°	346.7	356.7	371.0	389.8	411.5	437.5	464.4	492.5	523.3	556.6	591.7
145°	361.3	370.2	383.6	401.4	421.0	445.0	469.9	494.8	521.5	550.0	577.6
147.5°	375.4	383.9	396.2	411.0	428.5	451.0	473.0	495.5	518.4	543.2	566.7
150°	385.3	392.4	404.0	417.4	433.4	453.9	474.3	494.8	516.2	537.5	558.9
152.5°	393.9	401.0	411.2	423.8	438.4	456.7	475.0	493.4	512.6	532.5	551.1
155°	407.6	413.0	422.8	432.5	445.9	461.0	476.1	491.2	506.4	523.3	540.2
157.5°	419.4	423.7	432.1	440.0	451.2	464.0	476.1	487.1	500.0	514.6	527.5
160°	427.2	430.7	437.8	445.0	454.8	465.5	476.1	485.0	495.7	508.2	519.7
162.5°	433.5	437.1	442.8	449.2	456.9	466.2	475.4	482.9	492.1	502.5	511.9
165°	442.3	444.1	449.4	453.9	459.2	467.3	473.5	478.8	485.0	493.0	500.2
167.5°	449.6	451.2	454.6	457.8	461.2	467.1	472.3	474.7	478.8	483.8	488.9
170°	453.9	454.8	457.4	459.2	461.9	466.4	470.8	472.6	475.2	478.8	483.2
172.5°	457.4	456.9	459.6	460.7	462.6	465.7	468.7	469.8	471.0	473.9	476.8
175°	461.0	460.1	461.9	461.9	462.8	464.6	466.4	465.5	466.4	467.3	469.9
177.5°	462.1	461.4	462.8	462.8	462.8	463.5	464.9	463.5	462.8	463.5	464.9
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1	1778.1
2.5°	1844.2	1851.9	1851.9	1853.0	1861.7	1860.6	1860.1
5°	1962.7	1974.2	1975.6	1987.9	1996.1	1993.3	1985.8
7.5°	2074.3	2095.9	2112.3	2121.5	2132.3	2138.9	2135.9
10°	2162.8	2194.3	2213.4	2226.4	2242.1	2253.7	2249.6
12.5°	2243.2	2280.6	2306.9	2329.1	2331.2	2346.1	2336.0
15°	2368.6	2408.2	2412.3	2428.7	2441.7	2440.3	2441.0
17.5°	2409.9	2422.7	2425.3	2425.6	2425.8	2421.0	2410.7
20°	2395.2	2390.4	2378.8	2369.9	2354.2	2352.2	2338.5
22.5°	2325.2	2310.1	2280.9	2261.6	2237.2	2230.8	2227.0
25°	2187.5	2153.9	2107.5	2063.1	2050.8	2026.9	2033.7
27.5°	1998.4	1946.2	1896.0	1859.8	1827.2	1791.4	1801.6
30°	1865.5	1806.8	1735.7	1681.1	1646.2	1612.0	1605.9
32.5°	1707.0	1621.0	1541.7	1493.5	1440.1	1418.5	1394.9
35°	1433.7	1349.6	1271.0	1203.4	1164.5	1134.3	1107.1
37.5°	1187.8	1091.1	1027.6	972.9	944.7	927.5	931.8
40°	1035.3	950.6	904.1	862.4	836.4	824.1	826.9
42.5°	911.8	848.3	810.0	781.5	763.2	756.3	754.7
45°	771.5	736.0	704.5	688.1	679.3	671.7	667.0
47.5°	675.8	646.8	629.1	619.4	611.6	604.0	603.8
50°	618.4	599.3	587.0	576.8	570.6	565.2	569.9
52.5°	574.7	557.2	544.9	535.7	533.4	528.5	528.3
55°	509.8	496.1	487.2	479.0	474.9	472.2	468.8
57.5°	450.8	437.7	429.5	424.4	416.6	413.8	412.8
60°	408.7	398.4	390.2	383.3	380.0	374.5	374.5
62.5°	369.8	359.6	352.0	346.7	341.2	338.9	339.5
65°	313.7	305.5	297.9	292.5	291.1	287.0	288.4
67.5°	262.0	256.5	248.6	245.6	243.0	240.9	239.2
70°	227.6	222.1	218.0	213.9	211.9	211.9	211.9
72.5°	198.6	192.0	189.6	184.4	185.6	183.4	181.2
75°	153.7	149.6	147.6	145.5	142.1	142.1	142.1
77.5°	113.2	111.9	109.5	107.3	106.5	105.8	106.0
80°	87.5	86.8	85.4	85.4	84.1	83.4	82.0
82.5°	67.2	65.5	64.6	64.1	63.8	63.7	63.4
85°	38.3	36.9	36.9	37.5	36.2	36.2	36.9
87.5°	20.1	20.4	20.1	20.1	20.6	20.1	20.1
90°	26.7	28.4	29.3	29.3	29.3	29.3	29.3
92.5°	66.6	59.1	53.6	52.9	50.0	50.7	49.3
95°	178.9	141.5	121.9	110.4	103.3	100.6	101.5
97.5°	445.1	348.8	284.6	242.1	220.2	207.1	199.7
100°	702.1	580.2	472.6	398.7	360.4	334.7	318.6
102.5°	963.5	874.3	760.2	679.9	614.6	582.4	560.7
105°	1181.9	1193.5	1164.0	1108.8	1053.7	1015.4	1003.0
107.5°	1165.8	1258.4	1301.5	1308.4	1305.4	1297.7	1281.2
110°	1116.0	1229.9	1302.9	1341.1	1358.1	1366.1	1365.2



TEST NUMBER: P331449-940

CATALOG NUMBER: SA2XXDIP-C1005D925U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1056.9	1178.7	1262.3	1315.5	1343.8	1359.0	1363.8
115°	976.2	1092.9	1184.5	1247.7	1288.6	1311.8	1319.8
117.5°	910.8	1016.5	1102.5	1166.9	1210.1	1234.6	1241.3
120°	876.6	970.9	1052.0	1114.2	1156.0	1181.9	1190.8
122.5°	848.1	937.5	1010.7	1066.5	1107.6	1130.6	1138.1
125°	810.7	889.0	955.8	1007.5	1041.3	1063.5	1070.6
127.5°	774.5	848.3	909.9	954.9	986.6	1005.8	1011.6
130°	750.2	820.6	879.3	922.9	953.1	970.9	978.0
132.5°	727.5	792.0	847.2	890.1	920.4	936.7	943.2
135°	691.5	750.2	800.0	838.3	867.7	883.7	887.3
137.5°	662.8	709.4	752.9	787.8	813.1	827.2	832.5
140°	644.4	685.3	724.4	752.9	776.1	789.4	794.7
142.5°	627.9	663.2	696.0	723.0	744.0	755.9	757.0
145°	607.0	634.5	660.3	681.7	696.9	705.7	708.4
147.5°	589.9	611.4	630.3	647.9	660.0	666.0	667.6
150°	578.5	597.2	613.1	626.5	637.2	642.6	643.5
152.5°	569.2	585.1	599.0	609.4	618.7	622.6	622.8
155°	554.5	567.8	577.6	587.4	593.6	597.2	595.4
157.5°	539.5	550.7	558.4	565.3	570.4	572.0	572.0
160°	529.5	539.3	545.5	551.8	556.2	557.1	557.1
162.5°	520.2	528.6	533.4	539.7	542.7	543.6	542.9
165°	506.4	512.6	516.2	519.7	523.3	523.3	522.4
167.5°	493.7	498.0	501.2	502.8	504.8	504.6	503.5
170°	485.9	489.5	491.2	492.1	494.8	493.9	492.1
172.5°	478.8	481.6	482.7	483.6	484.8	483.9	482.9
175°	470.8	471.7	472.6	472.6	473.5	472.6	470.8
177.5°	464.9	465.7	465.7	465.7	465.7	464.9	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8

(END OF REPORT)