

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331631

Luminaire Tested: **SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331631
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3626.1 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331631
CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331631

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18				
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	21	20	16				
5	65	54	47	41	58	49	42	38	39	34	31	30	27	24	21	19	18	14				
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	16	12				
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11				
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13	10				
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9				
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331631

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	1.3
10°-20°	129.0	3.6
20°-30°	181.2	5.0
30°-40°	197.6	5.4
40°-50°	181.6	5.0
50°-60°	142.7	3.9
60°-70°	93.0	2.6
70°-80°	48.0	1.3
80°-90°	16.1	0.4
90°-100°	58.7	1.6
100°-110°	182.3	5.0
110°-120°	311.6	8.6
120°-130°	409.8	11.3
130°-140°	459.9	12.7
140°-150°	450.9	12.4
150°-160°	378.2	10.4
160°-170°	250.9	6.9
170°-180°	87.7	2.4
0°-30°	357.2	9.8
0°-40°	554.7	15.3
0°-60°	879.0	24.2
0°-90°	1036.1	28.6
90°-120°	552.6	15.2
90°-150°	1873.2	51.7
90°-180°	2590.0	71.4
0°-180°	3626.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	11	27	26	27	3
95°	41	48	50	50	48	47
105°	168	170	172	173	174	177
115°	313	317	316	315	313	309
125°	455	461	460	457	456	406
135°	589	597	599	598	596	454
145°	714	720	725	725	722	446
155°	817	819	822	825	823	376
165°	889	888	888	893	890	251
175°	925	922	921	926	922	88
180°	926	926	926	926	926	



TEST NUMBER: P331631

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	6.0	5.7	5.5	5.3	5.1	5.3	6.1	6.9	7.6	8.4	8.2
90°	0.8	2.9	5.0	7.0	9.1	12.1	15.9	19.7	23.5	27.4	27.0
92.5°	13.9	15.4	17.0	18.5	20.0	21.2	22.1	23.0	24.0	24.9	24.9
95°	40.6	42.4	44.1	45.9	47.6	48.6	49.0	49.3	49.7	50.0	50.0
97.5°	74.3	75.8	77.3	78.8	80.4	81.5	82.1	82.8	83.4	84.1	84.1
100°	99.3	100.7	102.0	103.4	104.8	105.8	106.3	106.8	107.3	107.9	107.9
102.5°	125.5	126.6	127.8	128.9	130.0	130.9	131.5	132.2	132.8	133.5	133.6
105°	168.1	168.6	169.1	169.6	170.1	170.6	170.9	171.3	171.6	172.0	172.3
107.5°	210.9	211.7	212.4	213.2	213.9	214.3	214.3	214.3	214.3	214.3	214.5
110°	238.4	239.4	240.5	241.5	242.6	243.1	243.1	243.1	243.1	243.1	243.1



TEST NUMBER: P331631

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	268.4	269.5	270.5	271.5	272.6	273.0	272.9	272.8	272.6	272.5	272.1
115°	312.7	313.7	314.7	315.8	316.8	317.2	316.8	316.5	316.1	315.8	315.6
117.5°	356.7	358.1	359.5	360.9	362.3	362.5	361.5	360.6	359.6	358.6	358.2
120°	386.1	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	386.1
122.5°	413.0	414.7	416.4	418.0	419.7	420.0	419.1	418.1	417.1	416.1	415.7
125°	454.9	456.5	458.0	459.6	461.2	461.7	461.2	460.6	460.1	459.6	459.1
127.5°	495.7	497.7	499.7	501.7	503.6	504.3	503.7	503.1	502.4	501.8	501.2
130°	521.4	523.6	525.9	528.1	530.4	531.3	531.0	530.6	530.3	530.0	529.6
132.5°	550.1	552.0	553.8	555.6	557.5	558.4	558.5	558.6	558.6	558.7	558.0
135°	588.6	590.5	592.4	594.3	596.2	597.3	597.7	598.0	598.4	598.7	598.6
137.5°	629.1	630.6	632.2	633.8	635.3	636.3	636.8	637.2	637.7	638.1	638.0
140°	653.5	655.0	656.6	658.1	659.7	660.9	661.8	662.7	663.5	664.4	664.4
142.5°	678.5	680.0	681.6	683.2	684.7	685.8	686.4	687.0	687.6	688.2	688.3
145°	714.4	715.6	716.9	718.1	719.3	720.4	721.5	722.5	723.5	724.6	724.8
147.5°	746.5	747.9	749.4	750.8	752.3	753.4	754.1	754.8	755.5	756.2	756.5
150°	768.4	769.4	770.4	771.5	772.5	773.4	774.1	774.8	775.5	776.2	776.7
152.5°	787.7	788.8	789.8	790.9	791.9	792.8	793.7	794.5	795.3	796.2	796.8
155°	816.8	817.3	817.9	818.4	818.9	819.4	819.9	820.5	821.0	821.5	822.4
157.5°	841.7	842.0	842.4	842.7	843.1	843.4	843.7	844.0	844.3	844.6	845.8
160°	856.7	857.0	857.4	857.7	858.1	858.3	858.5	858.7	858.9	859.0	860.1
162.5°	870.4	870.5	870.6	870.6	870.7	870.8	871.0	871.2	871.4	871.5	872.7
165°	888.7	888.6	888.4	888.2	888.0	887.9	887.9	887.9	887.9	887.9	889.2
167.5°	904.0	903.5	903.0	902.5	902.0	901.7	901.7	901.6	901.6	901.5	902.8
170°	912.2	911.7	911.1	910.6	910.1	909.7	909.6	909.4	909.2	909.0	910.3
172.5°	917.8	917.3	916.8	916.2	915.7	915.4	915.2	915.0	914.9	914.7	915.9
175°	924.7	924.2	923.6	923.1	922.6	922.2	921.8	921.5	921.1	920.8	922.0
177.5°	927.5	927.1	926.7	926.2	925.8	925.5	925.2	924.9	924.6	924.4	925.2
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331631

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	8.1	7.9	7.8	7.7	7.8	7.8	7.8	7.9
90°	26.7	26.3	26.0	25.9	26.1	26.2	26.4	26.6
92.5°	25.0	25.1	25.1	25.2	25.2	25.3	25.3	25.3
95°	50.0	50.0	50.0	49.9	49.5	49.2	48.8	48.5
97.5°	84.1	84.1	84.1	84.1	84.1	84.0	84.0	83.9
100°	107.9	107.9	107.9	107.8	107.6	107.4	107.3	107.1
102.5°	133.8	133.9	134.1	134.0	133.9	133.7	133.5	133.3
105°	172.7	173.0	173.4	173.5	173.5	173.5	173.5	173.5
107.5°	214.6	214.7	214.9	214.6	213.8	213.0	212.2	211.4
110°	243.1	243.1	243.1	242.8	242.3	241.8	241.3	240.7



TEST NUMBER: P331631

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	271.6	271.2	270.8	270.4	270.0	269.6	269.3	268.9
115°	315.4	315.3	315.1	314.7	314.2	313.7	313.2	312.7
117.5°	357.8	357.4	356.9	356.5	356.0	355.4	354.9	354.4
120°	386.1	386.1	386.1	385.9	385.3	384.8	384.3	383.8
122.5°	415.3	414.9	414.5	414.1	413.7	413.3	412.9	412.6
125°	458.6	458.0	457.5	457.2	457.0	456.8	456.7	456.5
127.5°	500.6	499.9	499.3	498.7	498.2	497.6	497.1	496.5
130°	529.3	528.9	528.6	528.0	527.3	526.7	526.0	525.3
132.5°	557.2	556.4	555.7	555.0	554.4	553.9	553.3	552.8
135°	598.4	598.2	598.0	597.7	597.2	596.7	596.1	595.6
137.5°	637.9	637.7	637.6	637.2	636.5	635.8	635.1	634.4
140°	664.4	664.4	664.4	664.0	663.4	662.7	662.0	661.3
142.5°	688.4	688.6	688.7	688.4	687.7	687.0	686.4	685.7
145°	724.9	725.1	725.3	725.0	724.3	723.6	722.9	722.2
147.5°	756.9	757.3	757.7	757.6	756.9	756.2	755.6	754.9
150°	777.2	777.7	778.3	778.3	777.7	777.2	776.7	776.2
152.5°	797.5	798.2	798.8	798.8	798.2	797.5	796.8	796.2
155°	823.2	824.1	825.0	825.2	824.6	824.1	823.6	823.1
157.5°	847.0	848.2	849.4	849.5	848.7	847.9	847.0	846.2
160°	861.1	862.2	863.2	863.4	862.7	862.0	861.3	860.6
162.5°	873.9	875.1	876.3	876.4	875.6	874.8	873.9	873.1
165°	890.4	891.6	892.8	893.0	892.1	891.2	890.4	889.5
167.5°	904.0	905.2	906.4	906.6	905.7	904.8	903.9	903.0
170°	911.5	912.7	913.9	914.0	913.0	911.9	910.9	909.8
172.5°	917.1	918.3	919.5	919.6	918.6	917.5	916.5	915.5
175°	923.2	924.4	925.6	925.7	924.7	923.6	922.6	921.6
177.5°	926.0	926.9	927.7	927.7	926.9	926.0	925.2	924.4
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2

(END OF REPORT)