

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331638

Luminaire Tested: **SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331638
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4648.5 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331638

CATALOG NUMBER: SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331638

CATALOG NUMBER: SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19
2	84	77	71	66	74	68	64	59	52	49	47	38	36	34	24	23	22	16
3	76	68	61	55	68	60	54	50	46	42	39	34	31	29	22	20	19	14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	19	20	17	15	13	12	10	8
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331638

CATALOG NUMBER: SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	1.0
10°-20°	129.0	2.8
20°-30°	181.2	3.9
30°-40°	197.6	4.2
40°-50°	181.6	3.9
50°-60°	142.7	3.1
60°-70°	93.0	2.0
70°-80°	48.0	1.0
80°-90°	17.1	0.4
90°-100°	207.5	4.5
100°-110°	704.2	15.1
110°-120°	748.1	16.1
120°-130°	615.8	13.2
130°-140°	494.5	10.6
140°-150°	373.7	8.0
150°-160°	262.6	5.6
160°-170°	154.6	3.3
170°-180°	50.3	1.1
0°-30°	357.2	7.7
0°-40°	554.7	11.9
0°-60°	879.0	18.9
0°-90°	1037.1	22.3
90°-120°	1659.8	35.7
90°-150°	3143.8	67.6
90°-180°	3611.0	77.7
0°-180°	4648.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	14	34	32	33	3
95°	35	86	391	148	114	37
105°	122	184	740	1322	1125	129
115°	215	271	619	1277	1480	213
125°	299	354	595	1034	1201	266
135°	351	419	588	869	995	271
145°	401	461	585	726	794	252
155°	456	492	568	642	668	210
165°	497	512	544	577	586	140
175°	518	518	523	530	528	49
180°	519	519	519	519	519	



TEST NUMBER: P331638

CATALOG NUMBER: SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	6.0	6.0	6.1	5.9	5.6	5.9	6.9	8.3	9.5	9.7	9.4
90°	1.0	4.0	8.0	10.0	12.0	15.0	20.0	26.9	32.9	33.9	32.9
92.5°	12.2	17.6	24.8	29.1	35.9	45.3	67.9	99.6	127.9	129.7	109.6
95°	34.9	38.9	48.9	57.9	73.9	97.8	143.7	230.5	346.3	391.2	342.3
97.5°	56.9	62.3	72.9	86.4	104.8	131.9	189.6	310.6	503.0	667.9	700.6
100°	76.8	79.8	88.8	104.8	124.8	152.7	205.6	327.4	542.9	788.4	932.2
102.5°	95.2	97.4	106.4	122.4	143.1	171.1	220.0	328.2	527.8	792.4	1018.4
105°	121.8	125.8	132.7	147.7	169.7	197.6	244.5	333.3	498.0	739.5	1005.0
107.5°	150.5	153.7	160.5	174.3	196.0	224.2	269.7	347.1	483.2	682.9	917.4
110°	169.7	173.7	179.6	192.6	213.6	242.5	286.4	358.3	480.1	655.7	862.3



TEST NUMBER: P331638

CATALOG NUMBER: SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.2	191.2	198.0	210.2	230.3	260.1	302.4	370.3	480.8	638.1	824.0
115°	214.6	219.6	225.6	237.5	257.5	284.4	327.4	388.2	485.0	618.8	776.5
117.5°	242.9	246.9	252.9	263.5	282.6	310.6	350.3	407.4	492.2	609.4	746.5
120°	260.5	264.5	270.5	279.4	299.4	327.4	366.3	420.2	497.0	603.8	730.6
122.5°	277.3	280.4	286.4	296.2	316.2	344.9	381.4	431.3	502.6	600.6	717.0
125°	299.4	302.4	308.4	320.4	340.3	368.3	404.2	449.1	511.0	594.8	697.6
127.5°	317.0	321.0	329.3	342.5	361.7	390.4	425.4	465.7	519.6	591.4	679.7
130°	327.4	331.3	341.3	355.3	375.3	403.2	438.1	476.1	526.0	589.8	667.7
132.5°	336.9	341.7	352.5	367.3	388.0	416.0	449.3	486.4	532.3	589.0	658.1
135°	351.3	355.3	367.3	382.2	405.2	433.1	465.1	500.0	539.9	587.8	644.7
137.5°	364.9	369.7	381.6	397.6	420.4	446.3	477.9	510.4	546.7	587.6	635.3
140°	375.3	379.3	391.2	407.2	429.2	455.1	485.0	516.0	549.9	586.8	629.8
142.5°	385.6	388.8	400.0	416.0	437.1	461.5	490.6	520.8	552.3	586.8	624.2
145°	401.2	405.2	415.2	430.2	450.1	472.1	499.0	527.0	554.9	584.8	616.8
147.5°	418.0	421.0	430.5	444.3	460.9	480.5	505.8	530.4	555.7	581.3	609.2
150°	429.2	432.1	440.1	453.1	468.1	486.0	509.0	531.9	554.9	578.9	602.8
152.5°	440.3	441.7	449.7	461.1	475.3	491.6	512.2	532.7	553.3	574.9	597.2
155°	456.1	457.1	463.1	474.1	485.0	500.0	517.0	533.9	550.9	567.9	586.8
157.5°	469.3	470.3	475.1	484.6	493.4	506.0	520.4	533.9	546.3	560.7	577.1
160°	478.1	479.1	483.0	491.0	499.0	510.0	522.0	533.9	543.9	555.9	569.9
162.5°	486.8	486.2	490.2	496.6	503.8	512.4	522.8	533.1	541.5	551.9	563.5
165°	497.0	496.0	498.0	504.0	509.0	515.0	524.0	531.0	536.9	543.9	552.9
167.5°	505.4	504.2	506.0	509.8	513.4	517.2	523.8	529.6	532.3	536.9	542.5
170°	511.0	509.0	510.0	513.0	515.0	518.0	523.0	528.0	530.0	532.9	536.9
172.5°	514.2	513.0	512.4	515.4	516.6	518.8	522.2	525.6	526.8	528.2	531.4
175°	518.0	517.0	516.0	518.0	518.0	519.0	521.0	523.0	522.0	523.0	524.0
177.5°	519.8	518.2	517.4	519.0	519.0	519.0	519.8	521.4	519.8	519.0	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331638

CATALOG NUMBER: SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	9.1	8.7	9.0	9.1	9.1	9.1	9.1	9.1
90°	31.9	29.9	31.9	32.9	32.9	32.9	32.9	32.9
92.5°	87.0	74.7	66.3	60.1	59.3	56.1	56.9	55.3
95°	261.5	200.6	158.7	136.7	123.8	115.8	112.8	113.8
97.5°	610.2	499.2	391.2	319.2	271.5	246.9	232.3	224.0
100°	911.2	787.4	650.7	530.0	447.1	404.2	375.3	357.3
102.5°	1108.4	1080.5	980.5	852.5	762.5	689.2	653.1	628.8
105°	1212.6	1325.4	1338.4	1305.4	1243.5	1181.7	1138.7	1124.8
107.5°	1137.6	1307.4	1411.2	1459.5	1467.3	1463.9	1455.3	1436.8
110°	1072.9	1251.5	1379.3	1461.1	1504.0	1523.0	1532.0	1531.0



TEST NUMBER: P331638

CATALOG NUMBER: SA2XXRDIP-C290D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1013.8	1185.3	1321.8	1415.6	1475.3	1507.0	1524.0	1529.4
115°	941.1	1094.8	1225.6	1328.4	1399.2	1445.1	1471.1	1480.1
117.5°	886.4	1021.4	1139.9	1236.4	1308.6	1357.1	1384.5	1392.0
120°	859.3	983.1	1088.8	1179.7	1249.5	1296.4	1325.4	1335.4
122.5°	837.7	951.1	1051.3	1133.4	1196.0	1242.1	1267.9	1276.3
125°	806.4	909.2	997.0	1071.9	1129.8	1167.7	1192.6	1200.6
127.5°	775.5	868.5	951.3	1020.4	1070.9	1106.4	1128.0	1134.4
130°	755.5	841.3	920.2	986.1	1035.0	1068.9	1088.8	1096.8
132.5°	736.3	815.8	888.2	950.1	998.2	1032.2	1050.5	1057.7
135°	709.6	775.5	841.3	897.2	940.1	973.1	991.0	995.0
137.5°	688.2	743.3	795.6	844.3	883.5	911.8	927.6	933.6
140°	674.7	722.6	768.5	812.4	844.3	870.3	885.3	891.2
142.5°	663.5	704.2	743.7	780.5	810.8	834.4	847.7	848.9
145°	647.7	680.7	711.6	740.5	764.5	781.5	791.4	794.4
147.5°	635.5	661.5	685.6	706.8	726.6	740.1	746.9	748.7
150°	626.8	648.7	669.7	687.6	702.6	714.6	720.6	721.6
152.5°	618.0	638.3	656.1	671.7	683.4	693.8	698.2	698.4
155°	605.8	621.8	636.7	647.7	658.7	665.7	669.7	667.7
157.5°	591.6	605.0	617.6	626.2	633.9	639.7	641.5	641.5
160°	582.8	593.8	604.8	611.8	618.8	623.8	624.8	624.8
162.5°	574.1	583.4	592.8	598.2	605.2	608.6	609.6	608.8
165°	560.9	567.9	574.9	578.9	582.8	586.8	586.8	585.8
167.5°	548.3	553.7	558.5	562.1	563.9	566.1	565.9	564.7
170°	541.9	544.9	548.9	550.9	551.9	554.9	553.9	551.9
172.5°	534.7	536.9	540.1	541.3	542.3	543.7	542.7	541.5
175°	527.0	528.0	529.0	530.0	530.0	531.0	530.0	528.0
177.5°	521.4	521.4	522.2	522.2	522.2	522.2	521.4	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0

(END OF REPORT)