

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331645

Luminaire Tested: **SA2XXRDIP-C485D330U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331645  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3168.0 lumens  
Efficiency: N/A  
Efficacy: 115.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331645  
CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	101	97	93	90	94	90	87	84	79	76	74	68	66	65	58	57	56	51				
2	92	85	80	75	86	80	75	71	70	66	63	61	58	56	52	50	49	44				
3	85	76	69	64	79	71	65	60	63	58	54	55	51	48	47	45	43	39				
4	78	68	61	55	73	64	57	52	56	51	47	49	46	42	43	40	38	34				
5	72	61	54	48	67	58	51	46	51	46	42	45	41	37	39	36	33	31				
6	67	56	48	42	63	52	45	40	47	41	37	41	37	33	36	33	30	27				
7	62	51	43	38	58	48	41	36	43	37	33	38	33	30	33	30	27	25				
8	58	46	39	34	54	44	37	32	39	34	30	35	31	27	31	27	25	23				
9	54	43	35	30	51	40	34	29	36	31	27	32	28	25	29	25	23	21				
10	51	39	32	28	48	37	31	27	34	28	25	30	26	23	27	23	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17354	17354	17354	17354
5°	19379	17462	15483	17462
10°	21502	17339	13421	17339
15°	22559	17085	10574	17085
20°	19557	16708	9149	16708
25°	12827	16192	8170	16192
30°	8634	15567	7394	15567
35°	6993	14781	6668	14781
40°	6218	13923	6171	13923
45°	5628	12919	5507	12919
50°	5122	11921	5102	11921
55°	4814	10818	4752	10818
60°	4027	9804	3978	9804
65°	3396	8902	3851	8902
70°	3139	7950	3630	7950
75°	2938	6918	3356	6918
80°	2706	5690	2985	5690
85°	2482	4502	2631	4502



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.9	3.2
10°-20°	283.9	9.0
20°-30°	365.8	11.5
30°-40°	347.6	11.0
40°-50°	297.8	9.4
50°-60°	226.8	7.2
60°-70°	143.4	4.5
70°-80°	71.6	2.3
80°-90°	19.7	0.6
90°-100°	14.9	0.5
100°-110°	54.7	1.7
110°-120°	146.1	4.6
120°-130°	241.2	7.6
130°-140°	256.5	8.1
140°-150°	238.4	7.5
150°-160°	191.7	6.1
160°-170°	123.5	3.9
170°-180°	42.5	1.3
0°-30°	751.6	23.7
0°-40°	1099.2	34.7
0°-60°	1623.8	51.3
0°-90°	1858.5	58.7
90°-120°	215.7	6.8
90°-150°	951.8	30.0
90°-180°	1309.0	41.3
0°-180°	3168.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1196	1077	955	1077	1196	118
15°	1350	1022	633	1022	1350	364
25°	720	909	459	909	720	342
35°	355	750	338	750	355	227
45°	246	566	241	566	246	191
55°	171	384	169	384	171	150
65°	89	233	101	233	89	90
75°	47	111	54	111	47	50
85°	13	24	14	24	13	15
90°	9	0	9	0	9	4
95°	14	21	14	21	14	13
105°	25	98	25	98	25	26
115°	26	186	26	186	26	66
125°	276	263	276	263	276	239
135°	336	325	336	325	336	259
145°	383	377	383	377	383	240
155°	416	416	416	416	416	192
165°	437	438	437	438	437	123
175°	445	448	445	448	445	42
180°	447	447	447	447	447	



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1118.4	1119.3	1120.2	1118.1	1118.1	1116.3	1112.4	1109.4	1101.0	1099.8	1099.8
5°	1195.7	1195.0	1196.5	1191.6	1184.9	1183.4	1176.3	1167.0	1157.3	1146.4	1144.2
7.5°	1272.7	1271.6	1268.6	1267.7	1262.6	1251.3	1239.9	1227.7	1211.6	1195.8	1187.9
10°	1311.5	1323.8	1316.4	1303.3	1305.9	1288.4	1279.0	1263.0	1249.5	1226.0	1220.8
12.5°	1349.7	1354.6	1352.2	1344.8	1341.5	1329.3	1316.7	1302.7	1277.9	1256.8	1238.4
15°	1349.6	1356.7	1358.6	1356.3	1358.2	1357.4	1350.7	1339.1	1317.5	1294.3	1274.2
17.5°	1250.0	1254.9	1267.1	1275.4	1285.9	1308.0	1318.9	1323.2	1319.9	1306.7	1292.5
20°	1138.2	1130.0	1164.4	1181.9	1196.9	1234.2	1266.3	1278.6	1298.4	1298.1	1294.3
22.5°	979.9	981.8	1014.4	1035.2	1078.9	1116.2	1152.8	1199.2	1237.5	1262.8	1277.6
25°	720.0	734.2	766.7	795.0	843.6	913.1	976.2	1049.4	1118.4	1173.0	1224.9
27.5°	540.7	541.8	567.5	593.8	622.6	679.5	759.0	846.4	944.9	1026.1	1119.6
30°	463.1	460.8	471.7	487.7	512.4	556.4	616.2	702.1	800.3	922.8	1031.8
32.5°	408.1	408.2	416.4	428.3	448.7	478.4	519.4	589.1	682.0	802.4	930.2
35°	354.8	354.4	360.4	369.0	377.5	396.6	424.6	461.2	525.1	637.5	768.2
37.5°	316.5	318.2	321.1	326.5	335.9	346.5	363.4	387.9	433.4	499.9	609.7
40°	295.0	295.8	299.9	304.4	310.0	318.2	332.0	351.8	385.0	438.0	518.3
42.5°	275.3	276.0	279.0	283.1	287.5	295.8	307.2	324.3	351.3	392.6	458.9
45°	246.5	246.5	249.1	250.9	255.8	263.3	272.6	286.8	305.5	336.1	380.2
47.5°	219.4	219.5	221.2	224.4	227.5	233.3	242.5	254.1	267.7	291.4	329.0
50°	203.9	204.3	205.4	208.0	209.9	215.1	222.2	232.3	246.5	264.8	296.1
52.5°	191.3	191.1	192.5	193.7	194.9	198.7	204.0	212.9	225.6	241.5	267.5
55°	171.0	169.5	171.8	173.6	174.8	176.3	179.2	184.9	195.7	209.1	228.5
57.5°	145.6	145.0	146.6	148.3	151.8	155.9	158.4	162.0	167.6	177.2	196.5
60°	124.7	124.7	128.1	129.2	133.3	138.5	143.8	146.8	152.4	158.7	172.9
62.5°	106.2	106.5	108.1	109.2	111.5	117.9	125.3	131.8	137.1	143.2	152.6
65°	88.9	89.6	89.6	90.4	91.9	93.4	96.3	101.6	110.9	119.5	126.6
67.5°	75.4	75.7	75.9	76.6	77.0	78.6	79.8	82.2	84.3	92.5	101.3
70°	66.5	67.6	67.2	68.0	68.3	69.1	70.6	71.7	75.1	76.9	82.2
72.5°	58.1	58.9	58.9	59.3	60.3	60.4	61.6	62.7	64.9	66.5	69.3
75°	47.1	46.7	47.1	47.8	48.2	48.5	48.5	50.0	51.2	52.7	54.5
77.5°	36.3	36.7	36.6	36.7	36.7	37.4	37.3	38.0	39.1	39.9	40.8
80°	29.1	29.5	29.1	29.5	29.9	30.2	29.9	30.2	31.4	32.1	32.1
82.5°	22.6	22.6	22.9	22.9	23.0	23.1	23.6	23.7	24.5	24.3	24.6
85°	13.4	13.1	13.1	13.1	13.4	13.8	13.4	13.4	13.8	13.8	13.8
87.5°	6.5	6.8	6.8	6.7	6.7	6.7	6.6	6.8	6.4	6.7	6.3
90°	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2	6.8	6.5	5.9
92.5°	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9	7.7	7.5	7.2
95°	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3	13.0	12.6	12.1
97.5°	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5	17.2	16.9	15.7
100°	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6	19.0	18.4	17.2
102.5°	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4	19.7	18.9	29.2
105°	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3	20.5	19.7	39.3
107.5°	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0	26.8	27.6	51.1
110°	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2	49.4	56.6	77.3



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3	116.5	142.7	147.8
115°	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0	166.2	199.5	197.7
117.5°	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9	212.9	221.0	219.7
120°	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7	237.9	237.0	235.7
122.5°	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3	252.8	252.3	250.9
125°	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2	273.7	273.2	271.8
127.5°	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6	292.8	292.1	291.1
130°	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8	305.0	304.3	303.5
132.5°	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8	317.1	316.4	315.6
135°	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8	334.1	333.4	332.7
137.5°	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6	349.9	349.2	348.5
140°	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8	360.2	359.5	358.8
142.5°	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3	369.7	369.1	368.2
145°	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5	383.0	382.5	381.3
147.5°	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0	394.6	394.3	393.1
150°	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1	401.7	401.3	400.1
152.5°	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6	408.1	407.7	406.6
155°	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3	416.9	416.4	415.6
157.5°	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7	424.2	423.7	423.1
160°	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0	428.5	428.1	427.7
162.5°	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9	432.5	432.0	431.6
165°	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8	436.6
167.5°	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9	441.4	440.9	440.7
170°	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0	443.5	443.0	442.8
172.5°	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5	445.0	444.5	444.4
175°	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2	446.7	446.2	446.1
177.5°	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4	447.0	446.6	446.5
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1100.4	1098.1	1096.0	1090.6	1087.9	1081.9	1081.0	1080.7	1073.0	1065.5	1063.4
5°	1138.2	1132.3	1123.3	1112.8	1102.0	1090.8	1083.3	1077.4	1062.4	1048.2	1040.0
7.5°	1176.3	1163.5	1148.0	1128.2	1111.7	1093.2	1079.5	1067.1	1045.9	1025.6	1011.9
10°	1204.7	1183.8	1163.3	1136.0	1114.7	1093.8	1074.4	1057.6	1033.7	1006.8	987.7
12.5°	1222.3	1199.3	1171.0	1144.4	1116.8	1090.2	1064.2	1042.6	1014.6	986.8	964.1
15°	1246.2	1221.5	1187.2	1149.1	1113.6	1078.9	1049.0	1022.1	985.5	952.3	924.6
17.5°	1265.7	1231.7	1194.8	1150.8	1109.7	1065.6	1027.1	992.7	952.0	911.9	879.4
20°	1271.9	1238.3	1195.7	1151.7	1103.1	1051.2	1009.8	972.4	928.7	885.0	847.7
22.5°	1268.0	1241.9	1194.5	1141.8	1092.1	1037.8	991.0	947.6	899.2	854.6	811.3
25°	1241.7	1232.7	1187.9	1130.4	1073.6	1010.5	956.4	908.9	853.7	805.9	758.8
27.5°	1180.2	1199.6	1171.8	1110.5	1047.4	979.7	918.9	864.9	807.5	753.7	706.8
30°	1121.1	1165.5	1153.5	1096.8	1026.2	959.7	891.4	835.0	773.8	718.5	672.2
32.5°	1040.1	1113.5	1125.2	1077.7	1004.7	931.6	860.0	803.9	740.0	681.7	636.6
35°	911.2	1021.0	1071.4	1041.1	967.9	889.2	815.2	749.9	685.6	628.1	583.3
37.5°	757.4	906.9	991.0	993.1	925.9	844.0	763.5	698.6	632.8	576.4	527.9
40°	657.6	819.7	929.1	953.4	896.6	808.1	726.7	660.6	596.4	541.1	485.5
42.5°	568.0	729.5	864.0	906.2	861.1	773.2	691.5	622.4	559.9	507.6	450.8
45°	459.3	600.5	748.7	824.2	799.2	717.7	631.5	565.8	507.1	461.9	407.4
47.5°	387.5	487.0	630.4	732.5	732.0	657.7	572.9	509.9	455.5	413.2	369.0
50°	346.5	433.2	554.6	670.3	680.0	617.7	537.0	474.6	423.9	379.4	343.9
52.5°	309.8	381.2	490.3	601.3	628.9	574.9	496.7	439.1	389.8	348.9	318.5
55°	261.8	317.0	400.0	503.8	545.6	507.5	438.0	384.3	344.3	310.0	283.8
57.5°	221.4	262.9	329.4	413.0	461.7	437.7	380.5	336.8	302.6	271.5	250.9
60°	196.1	230.0	286.4	356.3	410.0	393.2	344.3	303.6	274.5	247.6	228.2
62.5°	172.2	201.4	249.7	306.4	355.7	348.7	308.8	274.6	249.1	224.6	208.2
65°	138.5	159.8	197.5	242.0	281.6	284.9	256.2	233.0	210.2	190.8	176.3
67.5°	110.3	124.2	150.8	188.2	217.9	228.5	210.9	193.2	175.1	160.1	147.5
70°	93.0	104.2	123.6	153.9	181.1	192.3	182.2	168.4	152.7	140.4	129.6
72.5°	75.4	86.3	100.6	122.8	146.2	158.3	154.8	144.8	132.1	121.9	111.7
75°	56.8	60.1	69.8	84.8	103.1	113.5	116.1	110.9	100.8	93.0	87.0
77.5°	42.0	44.0	48.6	56.5	68.4	77.7	81.6	81.0	74.0	69.5	63.9
80°	33.6	34.7	37.0	40.3	49.3	58.6	61.2	61.2	56.4	54.5	48.9
82.5°	25.5	26.4	27.7	29.6	33.8	41.9	44.8	45.4	42.3	39.9	35.5
85°	14.6	14.2	14.9	16.1	16.8	19.0	23.5	24.3	23.5	20.5	19.4
87.5°	6.1	6.3	6.2	5.8	5.9	6.1	7.4	8.7	7.7	7.0	6.5
90°	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5	6.5	6.4	6.3
95°	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0	18.6	16.3	13.9
97.5°	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7	35.0	28.3	21.7
100°	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2	47.4	37.5	27.7
102.5°	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3	72.2	70.1	68.1
105°	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3	100.4	102.6	104.8
107.5°	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6	127.4	129.1	130.9
110°	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2	144.7	146.3	147.8





TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8	161.1	162.5	163.8
115°	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9	187.1	188.4	189.6
117.5°	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3	210.6	212.0	213.4
120°	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3	227.4	228.5	229.6
122.5°	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8	242.0	243.1	244.2
125°	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9	263.8	264.7	265.7
127.5°	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8	283.9	284.9	286.0
130°	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5	296.7	297.8	299.0
132.5°	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5	309.4	310.4	311.4
135°	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3	326.4	327.6	328.7
137.5°	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3	343.1	343.9	344.7
140°	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4	354.0	354.5	355.1
142.5°	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7	363.2	363.7	364.3
145°	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3	377.3	377.2	377.1
147.5°	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1	389.8	389.5	389.2
150°	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3	397.8	397.3	396.8
152.5°	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3	404.8	404.2	403.6
155°	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5	414.8	414.2	413.5
157.5°	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4	422.9	422.3	421.8
160°	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	427.7	427.2	426.8
162.5°	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2	431.8	431.4	430.9
165°	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8	437.4	436.9	436.5
167.5°	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9	441.5	441.1	440.6
170°	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3	443.8	443.4	443.0
172.5°	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8	445.4	444.9	444.5
175°	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8	447.3	446.8	446.3
177.5°	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1	447.7	447.3	446.9
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1059.5	1057.4	1053.5	1047.6	1044.0	1037.7	1033.5	1035.9	1036.5	1035.9	1035.3
5°	1031.1	1023.2	1012.4	1001.9	992.2	981.8	975.8	973.2	967.9	965.0	963.5
7.5°	996.6	983.1	967.8	949.6	934.1	917.9	909.6	905.5	894.8	889.0	883.9
10°	970.9	949.6	934.3	910.4	895.9	874.6	860.0	860.4	845.8	837.6	831.6
12.5°	942.6	919.2	893.7	872.2	852.0	834.9	817.3	810.2	794.7	786.8	770.7
15°	895.5	868.2	841.4	812.2	791.7	765.2	739.8	708.8	683.8	662.1	656.1
17.5°	844.1	810.4	783.4	749.2	714.0	669.4	640.0	622.0	606.9	595.5	587.0
20°	808.9	774.5	745.8	694.2	646.8	616.5	594.9	581.1	565.4	553.1	546.3
22.5°	771.8	736.0	696.8	639.2	602.3	578.0	558.7	542.8	532.2	522.6	516.5
25°	719.2	680.0	615.4	575.8	546.0	520.6	507.1	497.4	486.2	473.1	467.2
27.5°	663.7	601.3	554.9	525.5	497.0	480.5	468.4	453.9	443.9	438.0	431.8
30°	622.1	559.8	523.6	491.4	471.3	453.0	438.8	430.6	420.9	410.8	406.7
32.5°	575.8	526.0	491.3	464.6	444.1	428.5	417.3	404.0	397.0	390.8	382.2
35°	518.3	480.6	448.9	427.2	407.8	395.1	382.0	374.2	361.5	356.3	352.9
37.5°	469.6	436.9	413.2	390.4	375.0	361.0	353.0	340.5	335.0	327.7	320.6
40°	442.1	410.0	387.3	368.6	351.4	340.9	330.9	320.8	312.6	309.2	300.6
42.5°	414.1	387.9	365.1	344.7	333.2	322.1	309.4	302.0	293.4	288.0	282.7
45°	375.3	352.2	332.7	315.9	303.2	291.7	283.4	271.1	266.3	255.4	250.9
47.5°	341.2	319.7	301.2	285.2	272.8	265.3	253.3	243.6	235.9	229.2	223.5
50°	317.0	299.1	281.2	267.0	255.8	245.0	232.7	227.8	215.8	212.5	209.1
52.5°	294.9	277.9	261.5	247.6	236.4	225.9	215.0	208.7	200.6	197.2	194.8
55°	264.0	247.6	231.9	219.6	208.4	197.5	190.8	183.0	179.2	176.6	173.6
57.5°	232.9	218.2	206.1	193.7	182.4	173.8	166.0	161.3	157.4	154.0	150.4
60°	213.2	199.0	188.2	176.6	165.1	158.0	152.0	146.4	141.9	136.7	135.2
62.5°	192.3	179.9	170.0	158.7	148.6	142.1	136.5	131.2	125.8	118.2	116.1
65°	163.6	153.9	143.4	134.1	125.1	118.8	110.5	104.6	102.3	101.6	101.2
67.5°	137.6	128.4	119.4	109.9	101.7	95.8	91.6	90.7	89.2	88.7	87.7
70°	120.2	111.7	102.7	93.7	85.9	84.8	83.3	81.8	79.9	79.2	78.4
72.5°	104.7	95.8	86.9	79.7	76.3	74.9	73.4	71.9	70.7	69.9	69.5
75°	80.3	72.1	66.1	63.5	61.6	60.5	58.3	57.1	56.4	55.3	54.9
77.5°	57.8	53.2	50.4	48.8	46.8	45.6	44.4	43.2	42.4	42.2	41.6
80°	44.1	41.8	40.0	37.7	37.0	35.5	35.1	34.0	34.4	33.2	33.2
82.5°	34.2	31.4	29.8	28.8	28.0	26.8	26.4	25.9	26.0	25.2	25.2
85°	17.6	16.8	16.1	15.3	15.3	14.2	14.6	14.2	14.2	13.4	13.1
87.5°	6.4	6.2	5.7	5.8	6.0	5.8	5.8	5.6	5.7	5.8	5.5
90°	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2	7.5	7.9	8.2
92.5°	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9	8.1	8.2	8.4
95°	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3	13.7	14.0	14.2
97.5°	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5	17.7	18.0	18.2
100°	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6	20.2	20.7	21.1
102.5°	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4	21.2	21.9	22.4
105°	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3	22.1	22.9	23.4
107.5°	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0	25.2	24.4	24.1
110°	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2	35.0	27.8	24.4



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3	64.1	37.9	24.9
115°	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0	99.7	66.4	47.2
117.5°	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9	196.8	188.8	176.3
120°	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7	239.6	240.4	236.0
122.5°	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3	253.8	254.3	253.6
125°	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2	274.7	275.2	275.6
127.5°	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6	294.3	295.0	295.4
130°	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8	306.6	307.4	307.8
132.5°	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8	318.4	319.1	319.4
135°	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8	335.5	336.2	336.5
137.5°	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6	351.3	352.0	352.2
140°	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8	361.5	362.1	362.3
142.5°	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3	370.9	371.5	371.6
145°	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5	384.0	384.5	384.6
147.5°	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0	395.4	395.8	395.8
150°	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1	402.5	403.0	403.0
152.5°	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6	409.0	409.4	409.4
155°	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3	417.7	418.2	418.1
157.5°	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7	425.2	425.6	425.6
160°	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0	429.4	429.8	429.8
162.5°	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9	433.4	433.9	433.9
165°	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8	438.3	438.8	438.8
167.5°	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9	442.4	442.9	442.8
170°	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0	444.5	445.0	444.9
172.5°	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5	446.0	446.5	446.5
175°	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2	447.7	448.2	448.1
177.5°	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4	447.8	448.2	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1032.0	1032.6	1031.7	1032.3	1031.7	1032.6	1032.0	1035.3	1035.9	1036.5	1035.9
5°	961.6	957.1	956.4	955.3	956.4	957.1	961.6	963.5	965.0	967.9	973.2
7.5°	877.5	876.8	875.0	872.3	875.0	876.8	877.5	883.9	889.0	894.8	905.5
10°	823.4	821.6	821.2	818.6	821.2	821.6	823.4	831.6	837.6	845.8	860.4
12.5°	760.1	748.1	746.8	740.3	746.8	748.1	760.1	770.7	786.8	794.7	810.2
15°	647.2	644.9	637.5	632.6	637.5	644.9	647.2	656.1	662.1	683.8	708.8
17.5°	582.6	575.3	573.0	572.0	573.0	575.3	582.6	587.0	595.5	606.9	622.0
20°	541.1	534.4	533.3	532.5	533.3	534.4	541.1	546.3	553.1	565.4	581.1
22.5°	512.4	505.4	502.5	500.3	502.5	505.4	512.4	516.5	522.6	532.2	542.8
25°	463.4	460.8	459.3	458.6	459.3	460.8	463.4	467.2	473.1	486.2	497.4
27.5°	425.1	419.4	418.2	416.3	418.2	419.4	425.1	431.8	438.0	443.9	453.9
30°	403.3	401.4	398.8	396.6	398.8	401.4	403.3	406.7	410.8	420.9	430.6
32.5°	377.6	376.1	373.7	372.7	373.7	376.1	377.6	382.2	390.8	397.0	404.0
35°	349.2	343.9	341.7	338.3	341.7	343.9	349.2	352.9	356.3	361.5	374.2
37.5°	319.1	316.3	313.2	314.3	313.2	316.3	319.1	320.6	327.7	335.0	340.5
40°	295.8	293.9	293.1	292.8	293.1	293.9	295.8	300.6	309.2	312.6	320.8
42.5°	277.2	272.1	270.1	270.1	270.1	272.1	277.2	282.7	288.0	293.4	302.0
45°	249.1	244.2	240.9	241.2	240.9	244.2	249.1	250.9	255.4	266.3	271.1
47.5°	220.3	220.1	218.0	218.7	218.0	220.1	220.3	223.5	229.2	235.9	243.6
50°	206.5	204.3	202.8	203.1	202.8	204.3	206.5	209.1	212.5	215.8	227.8
52.5°	193.4	191.4	190.2	191.8	190.2	191.4	193.4	194.8	197.2	200.6	208.7
55°	171.8	169.5	169.2	168.8	169.2	169.5	171.8	173.6	176.6	179.2	183.0
57.5°	147.7	146.2	143.9	143.0	143.9	146.2	147.7	150.4	154.0	157.4	161.3
60°	130.3	127.3	123.6	123.2	123.6	127.3	130.3	135.2	136.7	141.9	146.4
62.5°	114.5	113.9	113.2	113.1	113.2	113.9	114.5	116.1	118.2	125.8	131.2
65°	100.5	100.1	100.5	100.8	100.5	100.1	100.5	101.2	101.6	102.3	104.6
67.5°	87.5	86.9	86.2	86.5	86.2	86.9	87.5	87.7	88.7	89.2	90.7
70°	77.7	77.3	76.9	76.9	76.9	77.3	77.7	78.4	79.2	79.9	81.8
72.5°	68.1	68.0	67.7	67.4	67.7	68.0	68.1	69.5	69.9	70.7	71.9
75°	54.5	53.8	53.8	53.8	53.8	53.8	54.5	54.9	55.3	56.4	57.1
77.5°	41.5	41.2	40.8	40.5	40.8	41.2	41.5	41.6	42.2	42.4	43.2
80°	32.9	32.5	32.1	32.1	32.1	32.5	32.9	33.2	33.2	34.4	34.0
82.5°	25.1	24.7	24.6	24.3	24.6	24.7	25.1	25.2	25.2	26.0	25.9
85°	13.4	13.8	13.4	14.2	13.4	13.8	13.4	13.1	13.4	14.2	14.2
87.5°	5.5	5.3	5.6	5.3	5.6	5.3	5.5	5.5	5.8	5.7	5.6
90°	8.3	8.4	8.6	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2
92.5°	8.5	8.6	8.6	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9
95°	14.1	14.0	14.0	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3
97.5°	18.3	18.4	18.5	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5
100°	21.2	21.4	21.5	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6
102.5°	22.6	22.8	23.0	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4
105°	23.7	24.0	24.3	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3
107.5°	24.4	24.7	25.0	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0
110°	24.7	25.0	25.3	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.1	25.3	25.6	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3
115°	42.0	36.9	31.7	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0
117.5°	159.3	142.3	125.3	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9
120°	226.3	216.6	206.9	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7
122.5°	251.8	249.9	248.0	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3
125°	275.8	276.0	276.2	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2
127.5°	295.5	295.5	295.5	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6
130°	307.7	307.6	307.6	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8
132.5°	319.3	319.3	319.2	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8
135°	336.4	336.2	336.1	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8
137.5°	352.0	351.8	351.5	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6
140°	361.9	361.6	361.2	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8
142.5°	371.2	370.9	370.5	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3
145°	384.2	383.9	383.5	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5
147.5°	395.5	395.2	394.9	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0
150°	402.7	402.3	401.9	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1
152.5°	408.9	408.5	408.0	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6
155°	417.5	417.0	416.4	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3
157.5°	425.0	424.5	423.9	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7
160°	429.3	428.8	428.3	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0
162.5°	433.2	432.6	432.0	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9
165°	438.3	437.8	437.3	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8
167.5°	442.2	441.5	440.9	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9
170°	444.3	443.6	443.0	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0
172.5°	445.8	445.2	444.5	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5
175°	447.4	446.7	445.9	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2
177.5°	447.6	447.1	446.6	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1033.5	1037.7	1044.0	1047.6	1053.5	1057.4	1059.5	1063.4	1065.5	1073.0	1080.7
5°	975.8	981.8	992.2	1001.9	1012.4	1023.2	1031.1	1040.0	1048.2	1062.4	1077.4
7.5°	909.6	917.9	934.1	949.6	967.8	983.1	996.6	1011.9	1025.6	1045.9	1067.1
10°	860.0	874.6	895.9	910.4	934.3	949.6	970.9	987.7	1006.8	1033.7	1057.6
12.5°	817.3	834.9	852.0	872.2	893.7	919.2	942.6	964.1	986.8	1014.6	1042.6
15°	739.8	765.2	791.7	812.2	841.4	868.2	895.5	924.6	952.3	985.5	1022.1
17.5°	640.0	669.4	714.0	749.2	783.4	810.4	844.1	879.4	911.9	952.0	992.7
20°	594.9	616.5	646.8	694.2	745.8	774.5	808.9	847.7	885.0	928.7	972.4
22.5°	558.7	578.0	602.3	639.2	696.8	736.0	771.8	811.3	854.6	899.2	947.6
25°	507.1	520.6	546.0	575.8	615.4	680.0	719.2	758.8	805.9	853.7	908.9
27.5°	468.4	480.5	497.0	525.5	554.9	601.3	663.7	706.8	753.7	807.5	864.9
30°	438.8	453.0	471.3	491.4	523.6	559.8	622.1	672.2	718.5	773.8	835.0
32.5°	417.3	428.5	444.1	464.6	491.3	526.0	575.8	636.6	681.7	740.0	803.9
35°	382.0	395.1	407.8	427.2	448.9	480.6	518.3	583.3	628.1	685.6	749.9
37.5°	353.0	361.0	375.0	390.4	413.2	436.9	469.6	527.9	576.4	632.8	698.6
40°	330.9	340.9	351.4	368.6	387.3	410.0	442.1	485.5	541.1	596.4	660.6
42.5°	309.4	322.1	333.2	344.7	365.1	387.9	414.1	450.8	507.6	559.9	622.4
45°	283.4	291.7	303.2	315.9	332.7	352.2	375.3	407.4	461.9	507.1	565.8
47.5°	253.3	265.3	272.8	285.2	301.2	319.7	341.2	369.0	413.2	455.5	509.9
50°	232.7	245.0	255.8	267.0	281.2	299.1	317.0	343.9	379.4	423.9	474.6
52.5°	215.0	225.9	236.4	247.6	261.5	277.9	294.9	318.5	348.9	389.8	439.1
55°	190.8	197.5	208.4	219.6	231.9	247.6	264.0	283.8	310.0	344.3	384.3
57.5°	166.0	173.8	182.4	193.7	206.1	218.2	232.9	250.9	271.5	302.6	336.8
60°	152.0	158.0	165.1	176.6	188.2	199.0	213.2	228.2	247.6	274.5	303.6
62.5°	136.5	142.1	148.6	158.7	170.0	179.9	192.3	208.2	224.6	249.1	274.6
65°	110.5	118.8	125.1	134.1	143.4	153.9	163.6	176.3	190.8	210.2	233.0
67.5°	91.6	95.8	101.7	109.9	119.4	128.4	137.6	147.5	160.1	175.1	193.2
70°	83.3	84.8	85.9	93.7	102.7	111.7	120.2	129.6	140.4	152.7	168.4
72.5°	73.4	74.9	76.3	79.7	86.9	95.8	104.7	111.7	121.9	132.1	144.8
75°	58.3	60.5	61.6	63.5	66.1	72.1	80.3	87.0	93.0	100.8	110.9
77.5°	44.4	45.6	46.8	48.8	50.4	53.2	57.8	63.9	69.5	74.0	81.0
80°	35.1	35.5	37.0	37.7	40.0	41.8	44.1	48.9	54.5	56.4	61.2
82.5°	26.4	26.8	28.0	28.8	29.8	31.4	34.2	35.5	39.9	42.3	45.4
85°	14.6	14.2	15.3	15.3	16.1	16.8	17.6	19.4	20.5	23.5	24.3
87.5°	5.8	5.8	6.0	5.8	5.7	6.2	6.4	6.5	7.0	7.7	8.7
90°	6.8	6.5	5.9	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.7	7.5	7.2	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5
95°	13.0	12.6	12.1	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0
97.5°	17.2	16.9	15.7	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7
100°	19.0	18.4	17.2	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2
102.5°	19.7	18.9	29.2	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3
105°	20.5	19.7	39.3	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3
107.5°	26.8	27.6	51.1	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6
110°	49.4	56.6	77.3	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	116.5	142.7	147.8	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8
115°	166.2	199.5	197.7	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9
117.5°	212.9	221.0	219.7	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3
120°	237.9	237.0	235.7	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3
122.5°	252.8	252.3	250.9	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8
125°	273.7	273.2	271.8	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9
127.5°	292.8	292.1	291.1	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8
130°	305.0	304.3	303.5	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5
132.5°	317.1	316.4	315.6	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5
135°	334.1	333.4	332.7	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3
137.5°	349.9	349.2	348.5	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3
140°	360.2	359.5	358.8	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4
142.5°	369.7	369.1	368.2	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7
145°	383.0	382.5	381.3	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3
147.5°	394.6	394.3	393.1	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1
150°	401.7	401.3	400.1	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3
152.5°	408.1	407.7	406.6	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3
155°	416.9	416.4	415.6	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5
157.5°	424.2	423.7	423.1	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4
160°	428.5	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1
162.5°	432.5	432.0	431.6	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2
165°	437.3	436.8	436.6	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8
167.5°	441.4	440.9	440.7	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9
170°	443.5	443.0	442.8	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3
172.5°	445.0	444.5	444.4	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8
175°	446.7	446.2	446.1	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8
177.5°	447.0	446.6	446.5	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1081.0	1081.9	1087.9	1090.6	1096.0	1098.1	1100.4	1099.8	1099.8	1101.0	1109.4
5°	1083.3	1090.8	1102.0	1112.8	1123.3	1132.3	1138.2	1144.2	1146.4	1157.3	1167.0
7.5°	1079.5	1093.2	1111.7	1128.2	1148.0	1163.5	1176.3	1187.9	1195.8	1211.6	1227.7
10°	1074.4	1093.8	1114.7	1136.0	1163.3	1183.8	1204.7	1220.8	1226.0	1249.5	1263.0
12.5°	1064.2	1090.2	1116.8	1144.4	1171.0	1199.3	1222.3	1238.4	1256.8	1277.9	1302.7
15°	1049.0	1078.9	1113.6	1149.1	1187.2	1221.5	1246.2	1274.2	1294.3	1317.5	1339.1
17.5°	1027.1	1065.6	1109.7	1150.8	1194.8	1231.7	1265.7	1292.5	1306.7	1319.9	1323.2
20°	1009.8	1051.2	1103.1	1151.7	1195.7	1238.3	1271.9	1294.3	1298.1	1298.4	1278.6
22.5°	991.0	1037.8	1092.1	1141.8	1194.5	1241.9	1268.0	1277.6	1262.8	1237.5	1199.2
25°	956.4	1010.5	1073.6	1130.4	1187.9	1232.7	1241.7	1224.9	1173.0	1118.4	1049.4
27.5°	918.9	979.7	1047.4	1110.5	1171.8	1199.6	1180.2	1119.6	1026.1	944.9	846.4
30°	891.4	959.7	1026.2	1096.8	1153.5	1165.5	1121.1	1031.8	922.8	800.3	702.1
32.5°	860.0	931.6	1004.7	1077.7	1125.2	1113.5	1040.1	930.2	802.4	682.0	589.1
35°	815.2	889.2	967.9	1041.1	1071.4	1021.0	911.2	768.2	637.5	525.1	461.2
37.5°	763.5	844.0	925.9	993.1	991.0	906.9	757.4	609.7	499.9	433.4	387.9
40°	726.7	808.1	896.6	953.4	929.1	819.7	657.6	518.3	438.0	385.0	351.8
42.5°	691.5	773.2	861.1	906.2	864.0	729.5	568.0	458.9	392.6	351.3	324.3
45°	631.5	717.7	799.2	824.2	748.7	600.5	459.3	380.2	336.1	305.5	286.8
47.5°	572.9	657.7	732.0	732.5	630.4	487.0	387.5	329.0	291.4	267.7	254.1
50°	537.0	617.7	680.0	670.3	554.6	433.2	346.5	296.1	264.8	246.5	232.3
52.5°	496.7	574.9	628.9	601.3	490.3	381.2	309.8	267.5	241.5	225.6	212.9
55°	438.0	507.5	545.6	503.8	400.0	317.0	261.8	228.5	209.1	195.7	184.9
57.5°	380.5	437.7	461.7	413.0	329.4	262.9	221.4	196.5	177.2	167.6	162.0
60°	344.3	393.2	410.0	356.3	286.4	230.0	196.1	172.9	158.7	152.4	146.8
62.5°	308.8	348.7	355.7	306.4	249.7	201.4	172.2	152.6	143.2	137.1	131.8
65°	256.2	284.9	281.6	242.0	197.5	159.8	138.5	126.6	119.5	110.9	101.6
67.5°	210.9	228.5	217.9	188.2	150.8	124.2	110.3	101.3	92.5	84.3	82.2
70°	182.2	192.3	181.1	153.9	123.6	104.2	93.0	82.2	76.9	75.1	71.7
72.5°	154.8	158.3	146.2	122.8	100.6	86.3	75.4	69.3	66.5	64.9	62.7
75°	116.1	113.5	103.1	84.8	69.8	60.1	56.8	54.5	52.7	51.2	50.0
77.5°	81.6	77.7	68.4	56.5	48.6	44.0	42.0	40.8	39.9	39.1	38.0
80°	61.2	58.6	49.3	40.3	37.0	34.7	33.6	32.1	32.1	31.4	30.2
82.5°	44.8	41.9	33.8	29.6	27.7	26.4	25.5	24.6	24.3	24.5	23.7
85°	23.5	19.0	16.8	16.1	14.9	14.2	14.6	13.8	13.8	13.8	13.4
87.5°	7.4	6.1	5.9	5.8	6.2	6.3	6.1	6.3	6.7	6.4	6.8
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2
92.5°	6.5	6.4	6.3	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9
95°	18.6	16.3	13.9	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3
97.5°	35.0	28.3	21.7	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5
100°	47.4	37.5	27.7	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6
102.5°	72.2	70.1	68.1	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4
105°	100.4	102.6	104.8	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3
107.5°	127.4	129.1	130.9	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0
110°	144.7	146.3	147.8	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2





TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	161.1	162.5	163.8	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3
115°	187.1	188.4	189.6	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0
117.5°	210.6	212.0	213.4	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9
120°	227.4	228.5	229.6	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7
122.5°	242.0	243.1	244.2	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3
125°	263.8	264.7	265.7	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2
127.5°	283.9	284.9	286.0	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6
130°	296.7	297.8	299.0	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8
132.5°	309.4	310.4	311.4	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8
135°	326.4	327.6	328.7	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8
137.5°	343.1	343.9	344.7	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6
140°	354.0	354.5	355.1	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8
142.5°	363.2	363.7	364.3	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3
145°	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5
147.5°	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0
150°	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1
152.5°	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6
155°	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3
157.5°	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7
160°	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0
162.5°	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9
165°	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8
167.5°	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9
170°	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0
172.5°	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5
175°	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2
177.5°	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1112.4	1116.3	1118.1	1118.1	1120.2	1119.3	1118.4
5°	1176.3	1183.4	1184.9	1191.6	1196.5	1195.0	1195.7
7.5°	1239.9	1251.3	1262.6	1267.7	1268.6	1271.6	1272.7
10°	1279.0	1288.4	1305.9	1303.3	1316.4	1323.8	1311.5
12.5°	1316.7	1329.3	1341.5	1344.8	1352.2	1354.6	1349.7
15°	1350.7	1357.4	1358.2	1356.3	1358.6	1356.7	1349.6
17.5°	1318.9	1308.0	1285.9	1275.4	1267.1	1254.9	1250.0
20°	1266.3	1234.2	1196.9	1181.9	1164.4	1130.0	1138.2
22.5°	1152.8	1116.2	1078.9	1035.2	1014.4	981.8	979.9
25°	976.2	913.1	843.6	795.0	766.7	734.2	720.0
27.5°	759.0	679.5	622.6	593.8	567.5	541.8	540.7
30°	616.2	556.4	512.4	487.7	471.7	460.8	463.1
32.5°	519.4	478.4	448.7	428.3	416.4	408.2	408.1
35°	424.6	396.6	377.5	369.0	360.4	354.4	354.8
37.5°	363.4	346.5	335.9	326.5	321.1	318.2	316.5
40°	332.0	318.2	310.0	304.4	299.9	295.8	295.0
42.5°	307.2	295.8	287.5	283.1	279.0	276.0	275.3
45°	272.6	263.3	255.8	250.9	249.1	246.5	246.5
47.5°	242.5	233.3	227.5	224.4	221.2	219.5	219.4
50°	222.2	215.1	209.9	208.0	205.4	204.3	203.9
52.5°	204.0	198.7	194.9	193.7	192.5	191.1	191.3
55°	179.2	176.3	174.8	173.6	171.8	169.5	171.0
57.5°	158.4	155.9	151.8	148.3	146.6	145.0	145.6
60°	143.8	138.5	133.3	129.2	128.1	124.7	124.7
62.5°	125.3	117.9	111.5	109.2	108.1	106.5	106.2
65°	96.3	93.4	91.9	90.4	89.6	89.6	88.9
67.5°	79.8	78.6	77.0	76.6	75.9	75.7	75.4
70°	70.6	69.1	68.3	68.0	67.2	67.6	66.5
72.5°	61.6	60.4	60.3	59.3	58.9	58.9	58.1
75°	48.5	48.5	48.2	47.8	47.1	46.7	47.1
77.5°	37.3	37.4	36.7	36.7	36.6	36.7	36.3
80°	29.9	30.2	29.9	29.5	29.1	29.5	29.1
82.5°	23.6	23.1	23.0	22.9	22.9	22.6	22.6
85°	13.4	13.8	13.4	13.1	13.1	13.1	13.4
87.5°	6.6	6.7	6.7	6.7	6.8	6.8	6.5
90°	7.5	7.9	8.2	8.3	8.4	8.6	8.7
92.5°	8.1	8.2	8.4	8.5	8.6	8.6	8.7
95°	13.7	14.0	14.2	14.1	14.0	14.0	13.9
97.5°	17.7	18.0	18.2	18.3	18.4	18.5	18.6
100°	20.2	20.7	21.1	21.2	21.4	21.5	21.7
102.5°	21.2	21.9	22.4	22.6	22.8	23.0	23.2
105°	22.1	22.9	23.4	23.7	24.0	24.3	24.6
107.5°	25.2	24.4	24.1	24.4	24.7	25.0	25.3
110°	35.0	27.8	24.4	24.7	25.0	25.3	25.5



TEST NUMBER: P331645

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.1	37.9	24.9	25.1	25.3	25.6	25.8
115°	99.7	66.4	47.2	42.0	36.9	31.7	26.5
117.5°	196.8	188.8	176.3	159.3	142.3	125.3	108.3
120°	239.6	240.4	236.0	226.3	216.6	206.9	197.2
122.5°	253.8	254.3	253.6	251.8	249.9	248.0	246.1
125°	274.7	275.2	275.6	275.8	276.0	276.2	276.4
127.5°	294.3	295.0	295.4	295.5	295.5	295.5	295.6
130°	306.6	307.4	307.8	307.7	307.6	307.6	307.5
132.5°	318.4	319.1	319.4	319.3	319.3	319.2	319.1
135°	335.5	336.2	336.5	336.4	336.2	336.1	335.9
137.5°	351.3	352.0	352.2	352.0	351.8	351.5	351.3
140°	361.5	362.1	362.3	361.9	361.6	361.2	360.8
142.5°	370.9	371.5	371.6	371.2	370.9	370.5	370.1
145°	384.0	384.5	384.6	384.2	383.9	383.5	383.1
147.5°	395.4	395.8	395.8	395.5	395.2	394.9	394.6
150°	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)