

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331323-940

Luminaire Tested: **SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331323-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5664.9 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15
7	57	45	37	32	51	41	34	30	33	29	25	27	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13990	13990	13990	13990
5°	15686	14083	12478	14083
10°	17974	13967	10799	13967
15°	19883	13710	9541	13710
20°	19581	13435	8698	13435
25°	17655	13069	8165	13069
30°	14590	12486	7774	12486
35°	10634	11874	7496	11874
40°	8494	11152	7341	11152
45°	7421	10319	7133	10319
50°	6978	9510	6993	9510
55°	6432	8690	6804	8690
60°	5893	7818	6516	7818
65°	5368	7033	6235	7033
70°	4877	6274	5816	6274
75°	4323	5421	5153	5421
80°	3710	4491	4147	4491
85°	3335	3335	2464	3335



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	1.5
10°-20°	239.9	4.2
20°-30°	348.2	6.1
30°-40°	367.4	6.5
40°-50°	325.3	5.7
50°-60°	259.6	4.6
60°-70°	176.5	3.1
70°-80°	90.5	1.6
80°-90°	26.7	0.5
90°-100°	215.4	3.8
100°-110°	730.9	12.9
110°-120°	776.4	13.7
120°-130°	639.2	11.3
130°-140°	513.3	9.1
140°-150°	387.9	6.8
150°-160°	272.6	4.8
160°-170°	160.5	2.8
170°-180°	52.2	0.9
0°-30°	670.6	11.8
0°-40°	1038.0	18.3
0°-60°	1623.0	28.6
0°-90°	1916.5	33.8
90°-120°	1722.7	30.4
90°-150°	3263.0	57.6
90°-180°	3748.0	66.2
0°-180°	5664.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	866	866	866	866	866	
5°	968	869	770	869	968	97
15°	1190	820	571	820	1190	328
25°	991	734	458	734	991	448
35°	540	602	380	602	540	351
45°	325	452	312	452	325	256
55°	228	309	242	309	228	205
65°	140	184	163	184	140	140
75°	69	87	83	87	69	74
85°	18	18	13	18	18	21
90°	34	1	34	1	34	19
95°	118	36	118	36	118	154
105°	1167	126	1167	126	1167	1130
115°	1536	223	1536	223	1536	1504
125°	1246	311	1246	311	1246	1126
135°	1033	365	1033	365	1033	802
145°	825	416	825	416	825	524
155°	693	473	693	473	693	323
165°	608	516	608	516	608	174
175°	548	538	548	538	548	53
180°	539	539	539	539	539	



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	906.5	906.8	907.2	903.0	902.5	902.5	898.8	895.5	891.8	886.7	887.3
5°	967.8	971.4	972.8	968.8	962.8	962.1	956.4	947.1	938.4	931.5	926.5
7.5°	1040.9	1042.3	1039.1	1033.8	1029.4	1021.4	1010.8	1000.5	986.1	972.8	963.0
10°	1096.3	1098.3	1092.6	1084.9	1078.6	1069.3	1054.0	1038.3	1019.4	1001.0	986.4
12.5°	1138.4	1143.4	1136.0	1135.1	1124.2	1111.4	1093.1	1085.2	1058.5	1033.0	1017.3
15°	1189.5	1189.2	1189.9	1183.6	1175.5	1173.6	1154.2	1133.3	1095.6	1080.7	1054.6
17.5°	1174.7	1179.8	1182.1	1182.1	1181.9	1180.6	1174.4	1161.2	1142.3	1118.0	1088.1
20°	1139.6	1146.2	1147.3	1154.9	1159.2	1164.9	1167.2	1163.6	1151.9	1131.6	1105.6
22.5°	1085.2	1087.1	1090.2	1102.2	1111.5	1125.7	1133.1	1145.4	1140.9	1131.0	1109.4
25°	991.0	987.7	999.3	1005.4	1027.0	1049.6	1066.0	1084.0	1099.9	1109.6	1103.3
27.5°	878.0	873.0	890.5	906.3	923.9	948.4	973.8	1003.9	1028.9	1060.2	1070.9
30°	782.6	785.6	802.3	819.2	845.9	880.5	909.1	942.1	977.8	1012.7	1037.0
32.5°	679.8	691.3	701.8	727.8	751.3	789.9	831.9	873.1	917.6	957.3	994.9
35°	539.5	552.8	567.5	586.5	619.4	657.7	698.7	754.3	814.9	869.2	913.8
37.5°	454.1	452.0	460.4	474.1	500.8	531.7	578.8	633.8	705.2	768.9	831.9
40°	403.0	401.6	407.6	420.3	440.6	463.2	504.5	552.8	619.1	697.0	772.0
42.5°	367.7	368.5	371.9	380.8	394.8	413.4	444.3	485.4	546.1	619.5	700.0
45°	325.0	327.3	331.0	335.4	343.3	358.6	375.9	405.3	453.3	514.5	593.8
47.5°	294.3	294.4	298.0	301.8	306.6	315.2	329.4	347.8	381.6	431.5	499.6
50°	277.8	275.4	278.0	281.1	286.1	292.0	301.4	318.7	341.3	381.7	438.5
52.5°	257.5	257.5	259.9	261.1	265.6	271.5	280.1	292.0	312.5	344.1	390.9
55°	228.5	230.2	231.5	233.4	237.5	241.7	248.4	256.5	272.4	296.0	330.6
57.5°	201.2	201.7	203.0	206.8	209.4	213.3	219.6	226.9	237.3	254.9	280.9
60°	182.5	182.5	185.1	186.8	190.1	194.1	199.1	206.2	215.4	229.8	250.7
62.5°	165.4	165.1	166.2	169.0	171.5	175.2	180.2	186.2	194.9	207.7	224.9
65°	140.5	139.9	141.9	142.5	145.2	148.8	152.8	159.2	166.2	175.5	190.8
67.5°	116.5	117.3	118.4	119.7	121.2	125.0	127.7	132.2	138.0	145.8	156.2
70°	103.3	103.3	103.3	104.2	106.2	108.3	110.9	114.6	120.2	126.9	136.2
72.5°	88.3	89.3	90.4	89.9	92.4	93.5	96.8	98.8	104.2	108.5	116.7
75°	69.3	69.3	69.3	70.9	72.0	72.9	74.9	77.0	79.6	84.9	89.3
77.5°	51.7	51.5	51.9	52.3	53.3	54.6	55.1	57.0	59.4	61.9	65.5
80°	39.9	40.7	40.9	41.6	41.6	42.3	42.6	44.9	46.6	48.3	50.6
82.5°	30.9	31.0	31.1	31.2	31.5	31.9	32.7	33.5	34.1	35.5	37.3
85°	18.0	17.7	17.7	18.3	18.0	18.0	18.6	19.4	19.4	19.6	20.7
87.5°	13.7	13.7	14.0	13.7	13.7	13.8	13.4	13.6	14.0	14.5	14.5
90°	34.2	34.2	34.2	34.2	34.2	33.2	31.1	33.2	34.2	35.2	34.2
92.5°	57.4	59.0	58.2	61.5	62.3	68.8	77.5	90.3	113.8	134.6	132.8
95°	118.1	117.1	120.2	128.4	141.9	164.7	208.2	271.4	355.3	406.1	359.4
97.5°	232.5	241.1	256.3	281.8	331.3	406.1	518.2	633.3	727.2	693.2	522.1
100°	370.9	389.5	419.5	464.0	550.0	675.4	817.3	945.7	967.5	818.3	563.5
102.5°	652.6	677.9	715.4	791.4	884.8	1017.6	1121.4	1150.5	1057.0	822.5	547.8
105°	1167.4	1182.0	1226.5	1290.7	1355.0	1389.1	1375.6	1258.6	1043.1	767.6	516.9
107.5°	1491.2	1510.5	1519.4	1523.0	1514.8	1464.7	1357.0	1180.7	952.2	708.7	501.6
110°	1589.0	1590.1	1580.7	1561.0	1516.5	1431.6	1299.0	1113.6	895.0	680.6	498.3



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1587.3	1581.8	1564.1	1531.2	1469.3	1371.9	1230.2	1052.2	855.2	662.4	499.1
115°	1536.2	1526.9	1499.9	1452.3	1378.8	1272.0	1136.4	976.9	805.9	642.2	503.5
117.5°	1444.8	1437.0	1408.5	1358.3	1283.3	1183.2	1060.2	920.1	774.8	632.5	510.9
120°	1386.0	1375.6	1345.6	1296.9	1224.4	1130.2	1020.3	891.9	758.2	626.7	515.9
122.5°	1324.6	1316.0	1289.2	1241.4	1176.3	1091.2	987.2	869.5	744.1	623.4	521.7
125°	1246.2	1237.9	1212.0	1172.6	1112.5	1034.8	943.7	837.0	724.1	617.4	530.4
127.5°	1177.4	1170.7	1148.3	1111.5	1059.1	987.4	901.4	804.9	705.4	613.9	539.3
130°	1138.4	1130.2	1109.5	1074.2	1023.4	955.1	873.3	784.2	693.0	612.2	545.9
132.5°	1097.8	1090.4	1071.3	1036.1	986.1	921.9	846.8	764.3	683.1	611.4	552.5
135°	1032.8	1028.6	1010.0	975.8	931.2	873.3	804.9	736.5	669.1	610.1	560.4
137.5°	968.9	962.8	946.4	916.9	876.4	825.8	771.5	714.3	659.4	609.9	567.5
140°	925.1	918.8	903.3	876.4	843.2	797.6	750.0	700.3	653.6	609.1	570.8
142.5°	881.1	879.9	866.0	841.5	810.0	772.0	730.9	688.7	647.8	609.1	573.3
145°	824.6	821.4	811.1	793.4	768.7	738.6	706.5	672.3	640.2	607.0	576.0
147.5°	777.1	775.3	768.2	754.1	733.6	711.7	686.6	659.7	632.3	603.3	576.8
150°	748.9	747.9	741.7	729.2	713.7	695.1	673.3	650.5	625.6	600.8	576.0
152.5°	724.9	724.7	720.1	709.4	697.1	681.0	662.5	641.4	619.8	596.6	574.3
155°	693.0	695.1	690.9	683.7	672.3	660.8	645.3	628.7	609.1	589.4	571.8
157.5°	665.8	665.8	664.0	658.0	649.9	641.0	627.9	614.0	599.0	581.9	567.0
160°	648.5	648.5	647.4	642.2	635.0	627.8	616.4	604.9	591.5	577.0	564.5
162.5°	631.9	632.7	631.7	628.1	620.9	615.3	605.6	595.8	584.9	572.8	562.0
165°	608.1	609.1	609.1	604.9	600.8	596.6	589.4	582.2	573.9	564.5	557.3
167.5°	586.1	587.4	587.5	585.2	583.4	579.7	574.7	569.1	563.1	557.3	552.5
170°	572.8	574.9	576.0	572.8	571.8	569.7	565.6	562.5	557.3	553.1	550.0
172.5°	562.0	563.3	564.4	562.9	561.9	560.6	557.3	555.0	551.5	548.2	546.7
175°	548.0	550.0	551.1	550.0	550.0	549.0	548.0	547.0	543.9	542.8	541.8
177.5°	539.5	541.2	542.0	542.0	542.0	542.0	541.2	541.2	539.5	538.7	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	889.1	887.0	885.6	880.9	876.6	872.4	871.0	871.6	865.7	860.1	857.7
5°	923.8	917.1	910.8	901.8	891.2	879.5	873.5	868.9	857.2	844.5	837.2
7.5°	954.8	945.3	933.1	916.2	900.7	882.3	870.7	860.4	843.3	825.5	814.6
10°	973.7	960.7	945.1	924.4	905.4	883.2	867.5	851.9	831.9	810.6	797.3
12.5°	990.0	972.5	957.1	930.6	908.1	880.2	861.7	839.6	818.6	793.3	780.2
15°	1028.7	996.4	967.1	937.1	909.5	870.5	849.9	820.2	792.6	761.3	746.3
17.5°	1058.5	1022.3	976.2	938.1	905.8	862.6	832.3	796.8	764.1	728.3	708.0
20°	1075.7	1034.0	984.4	939.1	900.4	851.2	818.2	781.9	743.6	703.3	681.4
22.5°	1085.7	1042.1	992.9	935.1	889.8	841.9	800.4	760.6	721.8	678.3	655.2
25°	1089.0	1049.0	997.0	931.7	876.5	822.2	772.2	733.6	686.7	646.0	612.4
27.5°	1073.1	1044.5	994.5	925.5	861.1	797.6	742.0	698.2	648.6	604.6	570.7
30°	1053.6	1037.0	988.4	919.1	848.8	780.6	719.3	669.7	620.5	575.8	541.2
32.5°	1023.6	1019.9	977.2	910.1	835.8	759.0	695.6	645.4	590.8	547.0	514.0
35°	964.4	980.4	953.4	889.8	811.2	728.3	659.7	602.4	545.8	503.8	472.9
37.5°	885.2	924.9	917.8	860.1	778.0	694.9	619.1	559.3	505.3	463.0	432.6
40°	830.5	881.2	888.5	837.5	754.7	669.1	588.8	529.1	476.5	437.9	407.2
42.5°	772.0	831.1	851.2	810.4	729.1	641.9	561.6	499.9	447.8	410.2	383.1
45°	673.7	752.0	788.3	764.9	686.3	597.1	514.5	451.9	404.7	369.3	348.3
47.5°	581.8	667.4	716.2	707.9	638.8	550.5	468.9	408.8	362.7	334.6	315.8
50°	516.8	604.8	663.7	666.4	604.8	517.2	435.2	378.6	336.4	310.0	294.7
52.5°	460.4	544.3	608.6	622.7	566.7	482.5	405.1	348.8	311.6	287.4	273.7
55°	386.6	457.5	528.9	554.8	509.9	429.9	358.3	308.7	273.8	257.1	245.1
57.5°	321.5	380.6	446.4	475.1	447.4	379.0	311.8	268.8	240.4	225.8	216.6
60°	287.0	333.7	392.3	426.6	402.6	341.7	283.0	242.1	218.8	205.8	197.2
62.5°	255.1	296.4	345.9	377.3	364.3	306.7	254.3	218.1	198.0	185.8	179.6
65°	210.4	243.1	281.4	310.4	301.8	258.1	215.2	184.1	168.2	158.5	153.6
67.5°	173.3	196.9	223.5	248.8	241.8	210.9	176.5	152.3	140.4	132.1	129.1
70°	149.9	167.8	191.5	211.8	206.2	180.8	153.6	132.9	122.5	115.6	112.5
72.5°	127.5	142.2	160.3	176.9	173.1	152.0	129.3	113.7	105.8	99.3	96.8
75°	96.2	107.5	118.6	129.6	128.6	112.3	98.9	86.9	80.6	75.6	74.6
77.5°	71.1	77.4	84.9	91.4	89.6	80.3	69.8	63.0	58.3	54.9	54.4
80°	54.3	58.0	63.3	67.9	65.6	61.6	53.3	48.3	44.9	41.6	40.3
82.5°	39.3	43.1	46.2	48.8	47.0	43.2	38.1	34.7	32.7	30.4	29.9
85°	20.7	22.6	24.0	24.6	24.0	21.7	19.4	18.0	16.3	15.3	15.0
87.5°	13.6	12.1	11.1	11.0	9.8	9.4	7.5	6.1	6.4	7.0	6.9
90°	28.0	20.7	15.5	12.4	10.3	8.3	4.1	1.1	4.1	8.3	10.3
92.5°	103.3	70.4	47.0	37.3	30.2	25.7	18.2	12.7	18.2	25.7	30.2
95°	239.2	149.2	101.5	76.7	60.1	50.7	40.4	36.3	40.4	50.7	60.1
97.5°	322.4	196.8	137.0	108.8	89.7	75.6	64.6	59.0	64.6	75.6	89.7
100°	339.7	213.4	158.5	129.5	108.8	92.2	82.8	79.7	82.8	92.2	108.8
102.5°	340.6	228.3	177.5	148.6	127.0	110.4	101.1	98.8	101.1	110.4	127.0
105°	346.0	253.8	205.1	176.1	153.3	137.8	130.5	126.4	130.5	137.8	153.3
107.5°	360.3	279.9	232.6	203.5	180.8	166.6	159.5	156.2	159.5	166.6	180.8
110°	371.8	297.3	251.7	221.7	199.9	186.5	180.2	176.1	180.2	186.5	199.9



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	384.3	313.9	269.9	239.1	218.1	205.5	198.5	194.3	198.5	205.5	218.1
115°	403.0	339.7	295.2	267.2	246.6	234.1	227.9	222.7	227.9	234.1	246.6
117.5°	422.8	363.6	322.4	293.4	273.5	262.5	256.3	252.2	256.3	262.5	273.5
120°	436.1	380.1	339.7	310.8	290.1	280.7	274.5	270.4	274.5	280.7	290.1
122.5°	447.7	395.9	358.0	328.1	307.5	297.3	291.1	287.8	291.1	297.3	307.5
125°	466.2	419.5	382.3	353.2	332.5	320.1	313.9	310.8	313.9	320.1	332.5
127.5°	483.3	441.5	405.2	375.4	355.5	341.9	333.1	329.0	333.1	341.9	355.5
130°	494.1	454.8	418.5	389.5	368.8	354.3	343.9	339.7	343.9	354.3	368.8
132.5°	504.9	466.4	431.8	402.8	381.2	365.9	354.7	349.7	354.7	365.9	381.2
135°	519.0	482.7	449.6	420.5	396.7	381.2	368.8	364.6	368.8	381.2	396.7
137.5°	529.8	496.0	463.2	436.3	412.7	396.1	383.7	378.7	383.7	396.1	412.7
140°	535.6	503.5	472.3	445.4	422.7	406.1	393.6	389.5	393.6	406.1	422.7
142.5°	540.6	509.3	479.0	453.7	431.8	415.2	403.6	400.3	403.6	415.2	431.8
145°	547.0	517.9	490.0	467.2	446.5	431.0	420.5	416.4	420.5	431.0	446.5
147.5°	550.5	525.0	498.6	478.4	461.2	446.8	436.9	433.8	436.9	446.8	461.2
150°	552.1	528.3	504.4	485.8	470.3	456.8	448.5	445.4	448.5	456.8	470.3
152.5°	552.9	531.6	510.2	493.3	478.6	466.7	458.5	457.0	458.5	466.7	478.6
155°	554.2	536.5	519.0	503.5	492.0	480.6	474.4	473.4	474.4	480.6	492.0
157.5°	554.2	540.1	525.2	512.1	503.0	493.1	488.1	487.1	488.1	493.1	503.0
160°	554.2	541.8	529.3	517.9	509.6	501.3	497.2	496.1	497.2	501.3	509.6
162.5°	553.4	542.6	531.8	522.9	515.4	508.8	504.7	505.3	504.7	508.8	515.4
165°	551.1	543.9	534.5	528.3	523.1	516.9	514.9	515.9	514.9	516.9	523.1
167.5°	549.7	543.6	536.8	532.9	529.1	525.2	523.3	524.6	523.3	525.2	529.1
170°	548.0	542.8	537.6	534.5	532.4	529.3	528.3	530.4	528.3	529.3	532.4
172.5°	545.5	542.0	538.4	536.2	534.9	531.8	532.4	533.7	532.4	531.8	534.9
175°	542.8	540.7	538.7	537.6	537.6	535.6	536.5	537.6	536.5	535.6	537.6
177.5°	541.2	539.5	538.7	538.7	538.7	537.0	537.8	539.5	537.8	537.0	538.7
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	855.1	853.5	847.8	844.9	840.2	835.6	832.7	834.0	835.1	834.6	833.7
5°	830.5	824.2	814.6	806.2	800.2	789.3	784.6	782.3	780.2	777.9	775.6
7.5°	801.4	791.4	777.6	765.7	754.5	740.8	733.1	728.3	723.5	718.3	713.6
10°	780.6	766.6	752.0	735.3	722.0	709.6	698.7	691.3	684.7	678.3	673.7
12.5°	758.8	742.6	724.5	701.8	687.1	669.4	667.8	654.9	644.4	640.5	635.1
15°	724.0	701.3	678.3	651.4	639.7	623.8	613.8	603.8	594.8	588.4	586.7
17.5°	684.5	655.1	632.3	613.0	593.9	577.5	568.3	560.3	552.9	544.4	543.3
20°	654.3	629.1	604.1	587.1	567.5	550.8	539.5	531.5	525.1	520.1	515.9
22.5°	625.9	598.2	575.3	556.7	537.3	523.9	515.0	507.3	502.0	496.5	492.4
25°	580.1	558.5	533.5	512.6	496.5	487.9	480.5	473.9	470.6	466.9	462.3
27.5°	540.1	516.0	492.7	476.4	462.4	454.7	449.5	445.0	441.8	439.7	437.0
30°	511.8	487.5	469.2	453.3	441.6	433.9	430.6	427.9	424.3	422.9	421.6
32.5°	484.6	462.8	447.1	433.3	422.1	417.1	414.1	411.7	408.8	407.5	404.8
35°	446.2	427.9	412.6	404.9	395.9	391.6	389.3	385.9	383.3	382.0	381.7
37.5°	410.1	394.1	384.1	374.3	370.4	367.7	364.6	362.3	361.5	361.3	361.0
40°	386.6	373.6	364.6	356.7	355.0	351.0	348.3	346.3	346.3	346.7	346.3
42.5°	365.3	353.7	345.7	338.9	336.9	334.5	331.8	331.7	332.3	333.3	332.3
45°	333.1	324.7	319.1	315.7	312.0	309.7	309.3	310.4	310.7	311.0	312.0
47.5°	303.3	297.7	292.7	289.0	287.4	287.0	286.6	288.3	289.9	290.5	292.0
50°	285.7	279.4	275.1	272.8	271.4	270.7	271.4	273.4	274.7	276.4	277.4
52.5°	266.0	261.5	258.6	256.7	256.2	256.6	256.7	259.0	261.2	261.7	262.3
55°	238.8	235.4	234.8	231.8	233.1	232.7	234.4	235.8	237.7	239.8	240.1
57.5°	211.6	208.9	207.1	207.4	207.8	209.3	210.6	213.0	215.2	217.2	217.5
60°	193.5	192.2	191.2	191.2	191.8	193.9	195.5	197.8	199.1	200.5	201.4
62.5°	177.0	175.7	174.6	175.1	176.9	178.1	180.0	181.3	182.6	184.0	184.4
65°	150.9	150.2	151.2	151.9	152.2	153.8	156.2	157.2	158.5	159.2	161.5
67.5°	126.8	127.0	126.8	127.8	129.7	130.1	132.2	134.6	134.9	136.2	137.7
70°	110.6	111.2	111.9	112.5	114.2	114.9	116.5	117.5	118.9	119.8	120.9
72.5°	95.7	95.8	96.5	96.3	97.7	99.2	100.6	101.6	102.9	104.2	105.1
75°	73.6	73.6	74.3	74.6	76.2	77.9	77.6	78.3	79.6	81.0	81.6
77.5°	53.8	53.1	53.8	54.0	54.6	56.0	56.3	57.2	58.8	58.3	59.0
80°	40.9	39.9	40.9	41.3	41.3	43.0	43.0	43.6	44.6	43.6	44.6
82.5°	29.2	28.8	29.5	29.6	30.1	30.1	30.7	30.9	31.8	31.4	31.8
85°	14.6	14.4	14.6	14.4	14.6	15.0	15.0	14.6	14.6	15.3	14.4
87.5°	7.0	7.4	8.1	9.6	10.5	10.5	10.1	9.8	9.5	9.3	9.5
90°	12.4	15.5	20.7	28.0	34.2	35.2	34.2	33.2	31.1	33.2	34.2
92.5°	37.3	47.0	70.4	103.3	132.8	134.6	113.8	90.3	77.5	68.8	62.3
95°	76.7	101.5	149.2	239.2	359.4	406.1	355.3	271.4	208.2	164.7	141.9
97.5°	108.8	137.0	196.8	322.4	522.1	693.2	727.2	633.3	518.2	406.1	331.3
100°	129.5	158.5	213.4	339.7	563.5	818.3	967.5	945.7	817.3	675.4	550.0
102.5°	148.6	177.5	228.3	340.6	547.8	822.5	1057.0	1150.5	1121.4	1017.6	884.8
105°	176.1	205.1	253.8	346.0	516.9	767.6	1043.1	1258.6	1375.6	1389.1	1355.0
107.5°	203.5	232.6	279.9	360.3	501.6	708.7	952.2	1180.7	1357.0	1464.7	1514.8
110°	221.7	251.7	297.3	371.8	498.3	680.6	895.0	1113.6	1299.0	1431.6	1516.5



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	239.1	269.9	313.9	384.3	499.1	662.4	855.2	1052.2	1230.2	1371.9	1469.3
115°	267.2	295.2	339.7	403.0	503.5	642.2	805.9	976.9	1136.4	1272.0	1378.8
117.5°	293.4	322.4	363.6	422.8	510.9	632.5	774.8	920.1	1060.2	1183.2	1283.3
120°	310.8	339.7	380.1	436.1	515.9	626.7	758.2	891.9	1020.3	1130.2	1224.4
122.5°	328.1	358.0	395.9	447.7	521.7	623.4	744.1	869.5	987.2	1091.2	1176.3
125°	353.2	382.3	419.5	466.2	530.4	617.4	724.1	837.0	943.7	1034.8	1112.5
127.5°	375.4	405.2	441.5	483.3	539.3	613.9	705.4	804.9	901.4	987.4	1059.1
130°	389.5	418.5	454.8	494.1	545.9	612.2	693.0	784.2	873.3	955.1	1023.4
132.5°	402.8	431.8	466.4	504.9	552.5	611.4	683.1	764.3	846.8	921.9	986.1
135°	420.5	449.6	482.7	519.0	560.4	610.1	669.1	736.5	804.9	873.3	931.2
137.5°	436.3	463.2	496.0	529.8	567.5	609.9	659.4	714.3	771.5	825.8	876.4
140°	445.4	472.3	503.5	535.6	570.8	609.1	653.6	700.3	750.0	797.6	843.2
142.5°	453.7	479.0	509.3	540.6	573.3	609.1	647.8	688.7	730.9	772.0	810.0
145°	467.2	490.0	517.9	547.0	576.0	607.0	640.2	672.3	706.5	738.6	768.7
147.5°	478.4	498.6	525.0	550.5	576.8	603.3	632.3	659.7	686.6	711.7	733.6
150°	485.8	504.4	528.3	552.1	576.0	600.8	625.6	650.5	673.3	695.1	713.7
152.5°	493.3	510.2	531.6	552.9	574.3	596.6	619.8	641.4	662.5	681.0	697.1
155°	503.5	519.0	536.5	554.2	571.8	589.4	609.1	628.7	645.3	660.8	672.3
157.5°	512.1	525.2	540.1	554.2	567.0	581.9	599.0	614.0	627.9	641.0	649.9
160°	517.9	529.3	541.8	554.2	564.5	577.0	591.5	604.9	616.4	627.8	635.0
162.5°	522.9	531.8	542.6	553.4	562.0	572.8	584.9	595.8	605.6	615.3	620.9
165°	528.3	534.5	543.9	551.1	557.3	564.5	573.9	582.2	589.4	596.6	600.8
167.5°	532.9	536.8	543.6	549.7	552.5	557.3	563.1	569.1	574.7	579.7	583.4
170°	534.5	537.6	542.8	548.0	550.0	553.1	557.3	562.5	565.6	569.7	571.8
172.5°	536.2	538.4	542.0	545.5	546.7	548.2	551.5	555.0	557.3	560.6	561.9
175°	537.6	538.7	540.7	542.8	541.8	542.8	543.9	547.0	548.0	549.0	550.0
177.5°	538.7	538.7	539.5	541.2	539.5	538.7	539.5	541.2	541.2	542.0	542.0
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	831.1	830.5	830.5	828.1	830.5	830.5	831.1	833.7	834.6	835.1	834.0
5°	771.0	769.9	768.3	769.9	768.3	769.9	771.0	775.6	777.9	780.2	782.3
7.5°	711.5	707.5	706.9	702.9	706.9	707.5	711.5	713.6	718.3	723.5	728.3
10°	668.1	665.4	665.0	658.7	665.0	665.4	668.1	673.7	678.3	684.7	691.3
12.5°	635.0	628.6	629.9	626.2	629.9	628.6	635.0	635.1	640.5	644.4	654.9
15°	577.7	577.7	576.5	570.8	576.5	577.7	577.7	586.7	588.4	594.8	603.8
17.5°	536.7	536.0	532.8	534.4	532.8	536.0	536.7	543.3	544.4	552.9	560.3
20°	512.2	510.1	506.2	506.2	506.2	510.1	512.2	515.9	520.1	525.1	531.5
22.5°	489.0	488.8	484.6	486.0	484.6	488.8	489.0	492.4	496.5	502.0	507.3
25°	461.9	459.2	457.3	458.3	457.3	459.2	461.9	462.3	466.9	470.6	473.9
27.5°	436.2	434.7	434.6	431.9	434.6	434.7	436.2	437.0	439.7	441.8	445.0
30°	421.2	417.9	418.6	417.0	418.6	417.9	421.2	421.6	422.9	424.3	427.9
32.5°	404.2	403.1	402.3	400.9	402.3	403.1	404.2	404.8	407.5	408.8	411.7
35°	380.9	381.3	379.6	380.3	379.6	381.3	380.9	381.7	382.0	383.3	385.9
37.5°	360.7	361.8	361.0	361.1	361.0	361.8	360.7	361.0	361.3	361.5	362.3
40°	347.3	347.3	347.3	348.3	347.3	347.3	347.3	346.3	346.7	346.3	346.3
42.5°	334.6	334.0	333.5	333.4	333.5	334.0	334.6	332.3	333.3	332.3	331.7
45°	312.7	313.7	314.1	312.4	314.1	313.7	312.7	312.0	311.0	310.7	310.4
47.5°	292.9	293.0	292.9	294.4	292.9	293.0	292.9	292.0	290.5	289.9	288.3
50°	279.1	278.4	279.1	278.4	279.1	278.4	279.1	277.4	276.4	274.7	273.4
52.5°	264.4	264.6	264.1	264.0	264.1	264.6	264.4	262.3	261.7	261.2	259.0
55°	241.5	242.1	241.7	241.7	241.7	242.1	241.5	240.1	239.8	237.7	235.8
57.5°	217.7	218.3	218.7	217.2	218.7	218.3	217.7	217.5	217.2	215.2	213.0
60°	201.2	202.8	202.5	201.8	202.5	202.8	201.2	201.4	200.5	199.1	197.8
62.5°	185.9	186.5	186.5	186.4	186.5	186.5	185.9	184.4	184.0	182.6	181.3
65°	162.5	163.2	162.2	163.2	162.2	163.2	162.5	161.5	159.2	158.5	157.2
67.5°	137.2	137.5	138.2	138.7	138.2	137.5	137.2	137.7	136.2	134.9	134.6
70°	121.5	121.2	122.3	123.2	122.3	121.2	121.5	120.9	119.8	118.9	117.5
72.5°	105.0	105.8	105.4	106.2	105.4	105.8	105.0	105.1	104.2	102.9	101.6
75°	81.0	81.9	81.6	82.6	81.6	81.9	81.0	81.6	81.0	79.6	78.3
77.5°	58.5	58.6	58.5	59.0	58.5	58.6	58.5	59.0	58.3	58.8	57.2
80°	44.6	44.0	43.2	44.6	43.2	44.0	44.6	44.6	43.6	44.6	43.6
82.5°	31.0	31.5	30.8	30.8	30.8	31.5	31.0	31.8	31.4	31.8	30.9
85°	14.4	14.0	13.3	13.3	13.3	14.0	14.4	14.4	15.3	14.6	14.6
87.5°	9.5	9.3	9.3	9.0	9.3	9.3	9.5	9.5	9.3	9.5	9.8
90°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	33.2	31.1	33.2
92.5°	61.5	58.2	59.0	57.4	59.0	58.2	61.5	62.3	68.8	77.5	90.3
95°	128.4	120.2	117.1	118.1	117.1	120.2	128.4	141.9	164.7	208.2	271.4
97.5°	281.8	256.3	241.1	232.5	241.1	256.3	281.8	331.3	406.1	518.2	633.3
100°	464.0	419.5	389.5	370.9	389.5	419.5	464.0	550.0	675.4	817.3	945.7
102.5°	791.4	715.4	677.9	652.6	677.9	715.4	791.4	884.8	1017.6	1121.4	1150.5
105°	1290.7	1226.5	1182.0	1167.4	1182.0	1226.5	1290.7	1355.0	1389.1	1375.6	1258.6
107.5°	1523.0	1519.4	1510.5	1491.2	1510.5	1519.4	1523.0	1514.8	1464.7	1357.0	1180.7
110°	1561.0	1580.7	1590.1	1589.0	1590.1	1580.7	1561.0	1516.5	1431.6	1299.0	1113.6



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1531.2	1564.1	1581.8	1587.3	1581.8	1564.1	1531.2	1469.3	1371.9	1230.2	1052.2
115°	1452.3	1499.9	1526.9	1536.2	1526.9	1499.9	1452.3	1378.8	1272.0	1136.4	976.9
117.5°	1358.3	1408.5	1437.0	1444.8	1437.0	1408.5	1358.3	1283.3	1183.2	1060.2	920.1
120°	1296.9	1345.6	1375.6	1386.0	1375.6	1345.6	1296.9	1224.4	1130.2	1020.3	891.9
122.5°	1241.4	1289.2	1316.0	1324.6	1316.0	1289.2	1241.4	1176.3	1091.2	987.2	869.5
125°	1172.6	1212.0	1237.9	1246.2	1237.9	1212.0	1172.6	1112.5	1034.8	943.7	837.0
127.5°	1111.5	1148.3	1170.7	1177.4	1170.7	1148.3	1111.5	1059.1	987.4	901.4	804.9
130°	1074.2	1109.5	1130.2	1138.4	1130.2	1109.5	1074.2	1023.4	955.1	873.3	784.2
132.5°	1036.1	1071.3	1090.4	1097.8	1090.4	1071.3	1036.1	986.1	921.9	846.8	764.3
135°	975.8	1010.0	1028.6	1032.8	1028.6	1010.0	975.8	931.2	873.3	804.9	736.5
137.5°	916.9	946.4	962.8	968.9	962.8	946.4	916.9	876.4	825.8	771.5	714.3
140°	876.4	903.3	918.8	925.1	918.8	903.3	876.4	843.2	797.6	750.0	700.3
142.5°	841.5	866.0	879.9	881.1	879.9	866.0	841.5	810.0	772.0	730.9	688.7
145°	793.4	811.1	821.4	824.6	821.4	811.1	793.4	768.7	738.6	706.5	672.3
147.5°	754.1	768.2	775.3	777.1	775.3	768.2	754.1	733.6	711.7	686.6	659.7
150°	729.2	741.7	747.9	748.9	747.9	741.7	729.2	713.7	695.1	673.3	650.5
152.5°	709.4	720.1	724.7	724.9	724.7	720.1	709.4	697.1	681.0	662.5	641.4
155°	683.7	690.9	695.1	693.0	695.1	690.9	683.7	672.3	660.8	645.3	628.7
157.5°	658.0	664.0	665.8	665.8	665.8	664.0	658.0	649.9	641.0	627.9	614.0
160°	642.2	647.4	648.5	648.5	648.5	647.4	642.2	635.0	627.8	616.4	604.9
162.5°	628.1	631.7	632.7	631.9	632.7	631.7	628.1	620.9	615.3	605.6	595.8
165°	604.9	609.1	609.1	608.1	609.1	609.1	604.9	600.8	596.6	589.4	582.2
167.5°	585.2	587.5	587.4	586.1	587.4	587.5	585.2	583.4	579.7	574.7	569.1
170°	572.8	576.0	574.9	572.8	574.9	576.0	572.8	571.8	569.7	565.6	562.5
172.5°	562.9	564.4	563.3	562.0	563.3	564.4	562.9	561.9	560.6	557.3	555.0
175°	550.0	551.1	550.0	548.0	550.0	551.1	550.0	550.0	549.0	548.0	547.0
177.5°	542.0	542.0	541.2	539.5	541.2	542.0	542.0	542.0	542.0	541.2	541.2
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	832.7	835.6	840.2	844.9	847.8	853.5	855.1	857.7	860.1	865.7	871.6
5°	784.6	789.3	800.2	806.2	814.6	824.2	830.5	837.2	844.5	857.2	868.9
7.5°	733.1	740.8	754.5	765.7	777.6	791.4	801.4	814.6	825.5	843.3	860.4
10°	698.7	709.6	722.0	735.3	752.0	766.6	780.6	797.3	810.6	831.9	851.9
12.5°	667.8	669.4	687.1	701.8	724.5	742.6	758.8	780.2	793.3	818.6	839.6
15°	613.8	623.8	639.7	651.4	678.3	701.3	724.0	746.3	761.3	792.6	820.2
17.5°	568.3	577.5	593.9	613.0	632.3	655.1	684.5	708.0	728.3	764.1	796.8
20°	539.5	550.8	567.5	587.1	604.1	629.1	654.3	681.4	703.3	743.6	781.9
22.5°	515.0	523.9	537.3	556.7	575.3	598.2	625.9	655.2	678.3	721.8	760.6
25°	480.5	487.9	496.5	512.6	533.5	558.5	580.1	612.4	646.0	686.7	733.6
27.5°	449.5	454.7	462.4	476.4	492.7	516.0	540.1	570.7	604.6	648.6	698.2
30°	430.6	433.9	441.6	453.3	469.2	487.5	511.8	541.2	575.8	620.5	669.7
32.5°	414.1	417.1	422.1	433.3	447.1	462.8	484.6	514.0	547.0	590.8	645.4
35°	389.3	391.6	395.9	404.9	412.6	427.9	446.2	472.9	503.8	545.8	602.4
37.5°	364.6	367.7	370.4	374.3	384.1	394.1	410.1	432.6	463.0	505.3	559.3
40°	348.3	351.0	355.0	356.7	364.6	373.6	386.6	407.2	437.9	476.5	529.1
42.5°	331.8	334.5	336.9	338.9	345.7	353.7	365.3	383.1	410.2	447.8	499.9
45°	309.3	309.7	312.0	315.7	319.1	324.7	333.1	348.3	369.3	404.7	451.9
47.5°	286.6	287.0	287.4	289.0	292.7	297.7	303.3	315.8	334.6	362.7	408.8
50°	271.4	270.7	271.4	272.8	275.1	279.4	285.7	294.7	310.0	336.4	378.6
52.5°	256.7	256.6	256.2	256.7	258.6	261.5	266.0	273.7	287.4	311.6	348.8
55°	234.4	232.7	233.1	231.8	234.8	235.4	238.8	245.1	257.1	273.8	308.7
57.5°	210.6	209.3	207.8	207.4	207.1	208.9	211.6	216.6	225.8	240.4	268.8
60°	195.5	193.9	191.8	191.2	191.2	192.2	193.5	197.2	205.8	218.8	242.1
62.5°	180.0	178.1	176.9	175.1	174.6	175.7	177.0	179.6	185.8	198.0	218.1
65°	156.2	153.8	152.2	151.9	151.2	150.2	150.9	153.6	158.5	168.2	184.1
67.5°	132.2	130.1	129.7	127.8	126.8	127.0	126.8	129.1	132.1	140.4	152.3
70°	116.5	114.9	114.2	112.5	111.9	111.2	110.6	112.5	115.6	122.5	132.9
72.5°	100.6	99.2	97.7	96.3	96.5	95.8	95.7	96.8	99.3	105.8	113.7
75°	77.6	77.9	76.2	74.6	74.3	73.6	73.6	74.6	75.6	80.6	86.9
77.5°	56.3	56.0	54.6	54.0	53.8	53.1	53.8	54.4	54.9	58.3	63.0
80°	43.0	43.0	41.3	41.3	40.9	39.9	40.9	40.3	41.6	44.9	48.3
82.5°	30.7	30.1	30.1	29.6	29.5	28.8	29.2	29.9	30.4	32.7	34.7
85°	15.0	15.0	14.6	14.4	14.6	14.4	14.6	15.0	15.3	16.3	18.0
87.5°	10.1	10.5	10.5	9.6	8.1	7.4	7.0	6.9	7.0	6.4	6.1
90°	34.2	35.2	34.2	28.0	20.7	15.5	12.4	10.3	8.3	4.1	1.1
92.5°	113.8	134.6	132.8	103.3	70.4	47.0	37.3	30.2	25.7	18.2	12.7
95°	355.3	406.1	359.4	239.2	149.2	101.5	76.7	60.1	50.7	40.4	36.3
97.5°	727.2	693.2	522.1	322.4	196.8	137.0	108.8	89.7	75.6	64.6	59.0
100°	967.5	818.3	563.5	339.7	213.4	158.5	129.5	108.8	92.2	82.8	79.7
102.5°	1057.0	822.5	547.8	340.6	228.3	177.5	148.6	127.0	110.4	101.1	98.8
105°	1043.1	767.6	516.9	346.0	253.8	205.1	176.1	153.3	137.8	130.5	126.4
107.5°	952.2	708.7	501.6	360.3	279.9	232.6	203.5	180.8	166.6	159.5	156.2
110°	895.0	680.6	498.3	371.8	297.3	251.7	221.7	199.9	186.5	180.2	176.1



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	855.2	662.4	499.1	384.3	313.9	269.9	239.1	218.1	205.5	198.5	194.3
115°	805.9	642.2	503.5	403.0	339.7	295.2	267.2	246.6	234.1	227.9	222.7
117.5°	774.8	632.5	510.9	422.8	363.6	322.4	293.4	273.5	262.5	256.3	252.2
120°	758.2	626.7	515.9	436.1	380.1	339.7	310.8	290.1	280.7	274.5	270.4
122.5°	744.1	623.4	521.7	447.7	395.9	358.0	328.1	307.5	297.3	291.1	287.8
125°	724.1	617.4	530.4	466.2	419.5	382.3	353.2	332.5	320.1	313.9	310.8
127.5°	705.4	613.9	539.3	483.3	441.5	405.2	375.4	355.5	341.9	333.1	329.0
130°	693.0	612.2	545.9	494.1	454.8	418.5	389.5	368.8	354.3	343.9	339.7
132.5°	683.1	611.4	552.5	504.9	466.4	431.8	402.8	381.2	365.9	354.7	349.7
135°	669.1	610.1	560.4	519.0	482.7	449.6	420.5	396.7	381.2	368.8	364.6
137.5°	659.4	609.9	567.5	529.8	496.0	463.2	436.3	412.7	396.1	383.7	378.7
140°	653.6	609.1	570.8	535.6	503.5	472.3	445.4	422.7	406.1	393.6	389.5
142.5°	647.8	609.1	573.3	540.6	509.3	479.0	453.7	431.8	415.2	403.6	400.3
145°	640.2	607.0	576.0	547.0	517.9	490.0	467.2	446.5	431.0	420.5	416.4
147.5°	632.3	603.3	576.8	550.5	525.0	498.6	478.4	461.2	446.8	436.9	433.8
150°	625.6	600.8	576.0	552.1	528.3	504.4	485.8	470.3	456.8	448.5	445.4
152.5°	619.8	596.6	574.3	552.9	531.6	510.2	493.3	478.6	466.7	458.5	457.0
155°	609.1	589.4	571.8	554.2	536.5	519.0	503.5	492.0	480.6	474.4	473.4
157.5°	599.0	581.9	567.0	554.2	540.1	525.2	512.1	503.0	493.1	488.1	487.1
160°	591.5	577.0	564.5	554.2	541.8	529.3	517.9	509.6	501.3	497.2	496.1
162.5°	584.9	572.8	562.0	553.4	542.6	531.8	522.9	515.4	508.8	504.7	505.3
165°	573.9	564.5	557.3	551.1	543.9	534.5	528.3	523.1	516.9	514.9	515.9
167.5°	563.1	557.3	552.5	549.7	543.6	536.8	532.9	529.1	525.2	523.3	524.6
170°	557.3	553.1	550.0	548.0	542.8	537.6	534.5	532.4	529.3	528.3	530.4
172.5°	551.5	548.2	546.7	545.5	542.0	538.4	536.2	534.9	531.8	532.4	533.7
175°	543.9	542.8	541.8	542.8	540.7	538.7	537.6	537.6	535.6	536.5	537.6
177.5°	539.5	538.7	539.5	541.2	539.5	538.7	538.7	538.7	537.0	537.8	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	871.0	872.4	876.6	880.9	885.6	887.0	889.1	887.3	886.7	891.8	895.5
5°	873.5	879.5	891.2	901.8	910.8	917.1	923.8	926.5	931.5	938.4	947.1
7.5°	870.7	882.3	900.7	916.2	933.1	945.3	954.8	963.0	972.8	986.1	1000.5
10°	867.5	883.2	905.4	924.4	945.1	960.7	973.7	986.4	1001.0	1019.4	1038.3
12.5°	861.7	880.2	908.1	930.6	957.1	972.5	990.0	1017.3	1033.0	1058.5	1085.2
15°	849.9	870.5	909.5	937.1	967.1	996.4	1028.7	1054.6	1080.7	1095.6	1133.3
17.5°	832.3	862.6	905.8	938.1	976.2	1022.3	1058.5	1088.1	1118.0	1142.3	1161.2
20°	818.2	851.2	900.4	939.1	984.4	1034.0	1075.7	1105.6	1131.6	1151.9	1163.6
22.5°	800.4	841.9	889.8	935.1	992.9	1042.1	1085.7	1109.4	1131.0	1140.9	1145.4
25°	772.2	822.2	876.5	931.7	997.0	1049.0	1089.0	1103.3	1109.6	1099.9	1084.0
27.5°	742.0	797.6	861.1	925.5	994.5	1044.5	1073.1	1070.9	1060.2	1028.9	1003.9
30°	719.3	780.6	848.8	919.1	988.4	1037.0	1053.6	1037.0	1012.7	977.8	942.1
32.5°	695.6	759.0	835.8	910.1	977.2	1019.9	1023.6	994.9	957.3	917.6	873.1
35°	659.7	728.3	811.2	889.8	953.4	980.4	964.4	913.8	869.2	814.9	754.3
37.5°	619.1	694.9	778.0	860.1	917.8	924.9	885.2	831.9	768.9	705.2	633.8
40°	588.8	669.1	754.7	837.5	888.5	881.2	830.5	772.0	697.0	619.1	552.8
42.5°	561.6	641.9	729.1	810.4	851.2	831.1	772.0	700.0	619.5	546.1	485.4
45°	514.5	597.1	686.3	764.9	788.3	752.0	673.7	593.8	514.5	453.3	405.3
47.5°	468.9	550.5	638.8	707.9	716.2	667.4	581.8	499.6	431.5	381.6	347.8
50°	435.2	517.2	604.8	666.4	663.7	604.8	516.8	438.5	381.7	341.3	318.7
52.5°	405.1	482.5	566.7	622.7	608.6	544.3	460.4	390.9	344.1	312.5	292.0
55°	358.3	429.9	509.9	554.8	528.9	457.5	386.6	330.6	296.0	272.4	256.5
57.5°	311.8	379.0	447.4	475.1	446.4	380.6	321.5	280.9	254.9	237.3	226.9
60°	283.0	341.7	402.6	426.6	392.3	333.7	287.0	250.7	229.8	215.4	206.2
62.5°	254.3	306.7	364.3	377.3	345.9	296.4	255.1	224.9	207.7	194.9	186.2
65°	215.2	258.1	301.8	310.4	281.4	243.1	210.4	190.8	175.5	166.2	159.2
67.5°	176.5	210.9	241.8	248.8	223.5	196.9	173.3	156.2	145.8	138.0	132.2
70°	153.6	180.8	206.2	211.8	191.5	167.8	149.9	136.2	126.9	120.2	114.6
72.5°	129.3	152.0	173.1	176.9	160.3	142.2	127.5	116.7	108.5	104.2	98.8
75°	98.9	112.3	128.6	129.6	118.6	107.5	96.2	89.3	84.9	79.6	77.0
77.5°	69.8	80.3	89.6	91.4	84.9	77.4	71.1	65.5	61.9	59.4	57.0
80°	53.3	61.6	65.6	67.9	63.3	58.0	54.3	50.6	48.3	46.6	44.9
82.5°	38.1	43.2	47.0	48.8	46.2	43.1	39.3	37.3	35.5	34.1	33.5
85°	19.4	21.7	24.0	24.6	24.0	22.6	20.7	20.7	19.6	19.4	19.4
87.5°	7.5	9.4	9.8	11.0	11.1	12.1	13.6	14.5	14.5	14.0	13.6
90°	4.1	8.3	10.3	12.4	15.5	20.7	28.0	34.2	35.2	34.2	33.2
92.5°	18.2	25.7	30.2	37.3	47.0	70.4	103.3	132.8	134.6	113.8	90.3
95°	40.4	50.7	60.1	76.7	101.5	149.2	239.2	359.4	406.1	355.3	271.4
97.5°	64.6	75.6	89.7	108.8	137.0	196.8	322.4	522.1	693.2	727.2	633.3
100°	82.8	92.2	108.8	129.5	158.5	213.4	339.7	563.5	818.3	967.5	945.7
102.5°	101.1	110.4	127.0	148.6	177.5	228.3	340.6	547.8	822.5	1057.0	1150.5
105°	130.5	137.8	153.3	176.1	205.1	253.8	346.0	516.9	767.6	1043.1	1258.6
107.5°	159.5	166.6	180.8	203.5	232.6	279.9	360.3	501.6	708.7	952.2	1180.7
110°	180.2	186.5	199.9	221.7	251.7	297.3	371.8	498.3	680.6	895.0	1113.6



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	198.5	205.5	218.1	239.1	269.9	313.9	384.3	499.1	662.4	855.2	1052.2
115°	227.9	234.1	246.6	267.2	295.2	339.7	403.0	503.5	642.2	805.9	976.9
117.5°	256.3	262.5	273.5	293.4	322.4	363.6	422.8	510.9	632.5	774.8	920.1
120°	274.5	280.7	290.1	310.8	339.7	380.1	436.1	515.9	626.7	758.2	891.9
122.5°	291.1	297.3	307.5	328.1	358.0	395.9	447.7	521.7	623.4	744.1	869.5
125°	313.9	320.1	332.5	353.2	382.3	419.5	466.2	530.4	617.4	724.1	837.0
127.5°	333.1	341.9	355.5	375.4	405.2	441.5	483.3	539.3	613.9	705.4	804.9
130°	343.9	354.3	368.8	389.5	418.5	454.8	494.1	545.9	612.2	693.0	784.2
132.5°	354.7	365.9	381.2	402.8	431.8	466.4	504.9	552.5	611.4	683.1	764.3
135°	368.8	381.2	396.7	420.5	449.6	482.7	519.0	560.4	610.1	669.1	736.5
137.5°	383.7	396.1	412.7	436.3	463.2	496.0	529.8	567.5	609.9	659.4	714.3
140°	393.6	406.1	422.7	445.4	472.3	503.5	535.6	570.8	609.1	653.6	700.3
142.5°	403.6	415.2	431.8	453.7	479.0	509.3	540.6	573.3	609.1	647.8	688.7
145°	420.5	431.0	446.5	467.2	490.0	517.9	547.0	576.0	607.0	640.2	672.3
147.5°	436.9	446.8	461.2	478.4	498.6	525.0	550.5	576.8	603.3	632.3	659.7
150°	448.5	456.8	470.3	485.8	504.4	528.3	552.1	576.0	600.8	625.6	650.5
152.5°	458.5	466.7	478.6	493.3	510.2	531.6	552.9	574.3	596.6	619.8	641.4
155°	474.4	480.6	492.0	503.5	519.0	536.5	554.2	571.8	589.4	609.1	628.7
157.5°	488.1	493.1	503.0	512.1	525.2	540.1	554.2	567.0	581.9	599.0	614.0
160°	497.2	501.3	509.6	517.9	529.3	541.8	554.2	564.5	577.0	591.5	604.9
162.5°	504.7	508.8	515.4	522.9	531.8	542.6	553.4	562.0	572.8	584.9	595.8
165°	514.9	516.9	523.1	528.3	534.5	543.9	551.1	557.3	564.5	573.9	582.2
167.5°	523.3	525.2	529.1	532.9	536.8	543.6	549.7	552.5	557.3	563.1	569.1
170°	528.3	529.3	532.4	534.5	537.6	542.8	548.0	550.0	553.1	557.3	562.5
172.5°	532.4	531.8	534.9	536.2	538.4	542.0	545.5	546.7	548.2	551.5	555.0
175°	536.5	535.6	537.6	537.6	538.7	540.7	542.8	541.8	542.8	543.9	547.0
177.5°	537.8	537.0	538.7	538.7	538.7	539.5	541.2	539.5	538.7	539.5	541.2
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	898.8	902.5	902.5	903.0	907.2	906.8	906.5
5°	956.4	962.1	962.8	968.8	972.8	971.4	967.8
7.5°	1010.8	1021.4	1029.4	1033.8	1039.1	1042.3	1040.9
10°	1054.0	1069.3	1078.6	1084.9	1092.6	1098.3	1096.3
12.5°	1093.1	1111.4	1124.2	1135.1	1136.0	1143.4	1138.4
15°	1154.2	1173.6	1175.5	1183.6	1189.9	1189.2	1189.5
17.5°	1174.4	1180.6	1181.9	1182.1	1182.1	1179.8	1174.7
20°	1167.2	1164.9	1159.2	1154.9	1147.3	1146.2	1139.6
22.5°	1133.1	1125.7	1111.5	1102.2	1090.2	1087.1	1085.2
25°	1066.0	1049.6	1027.0	1005.4	999.3	987.7	991.0
27.5°	973.8	948.4	923.9	906.3	890.5	873.0	878.0
30°	909.1	880.5	845.9	819.2	802.3	785.6	782.6
32.5°	831.9	789.9	751.3	727.8	701.8	691.3	679.8
35°	698.7	657.7	619.4	586.5	567.5	552.8	539.5
37.5°	578.8	531.7	500.8	474.1	460.4	452.0	454.1
40°	504.5	463.2	440.6	420.3	407.6	401.6	403.0
42.5°	444.3	413.4	394.8	380.8	371.9	368.5	367.7
45°	375.9	358.6	343.3	335.4	331.0	327.3	325.0
47.5°	329.4	315.2	306.6	301.8	298.0	294.4	294.3
50°	301.4	292.0	286.1	281.1	278.0	275.4	277.8
52.5°	280.1	271.5	265.6	261.1	259.9	257.5	257.5
55°	248.4	241.7	237.5	233.4	231.5	230.2	228.5
57.5°	219.6	213.3	209.4	206.8	203.0	201.7	201.2
60°	199.1	194.1	190.1	186.8	185.1	182.5	182.5
62.5°	180.2	175.2	171.5	169.0	166.2	165.1	165.4
65°	152.8	148.8	145.2	142.5	141.9	139.9	140.5
67.5°	127.7	125.0	121.2	119.7	118.4	117.3	116.5
70°	110.9	108.3	106.2	104.2	103.3	103.3	103.3
72.5°	96.8	93.5	92.4	89.9	90.4	89.3	88.3
75°	74.9	72.9	72.0	70.9	69.3	69.3	69.3
77.5°	55.1	54.6	53.3	52.3	51.9	51.5	51.7
80°	42.6	42.3	41.6	41.6	40.9	40.7	39.9
82.5°	32.7	31.9	31.5	31.2	31.1	31.0	30.9
85°	18.6	18.0	18.0	18.3	17.7	17.7	18.0
87.5°	13.4	13.8	13.7	13.7	14.0	13.7	13.7
90°	31.1	33.2	34.2	34.2	34.2	34.2	34.2
92.5°	77.5	68.8	62.3	61.5	58.2	59.0	57.4
95°	208.2	164.7	141.9	128.4	120.2	117.1	118.1
97.5°	518.2	406.1	331.3	281.8	256.3	241.1	232.5
100°	817.3	675.4	550.0	464.0	419.5	389.5	370.9
102.5°	1121.4	1017.6	884.8	791.4	715.4	677.9	652.6
105°	1375.6	1389.1	1355.0	1290.7	1226.5	1182.0	1167.4
107.5°	1357.0	1464.7	1514.8	1523.0	1519.4	1510.5	1491.2
110°	1299.0	1431.6	1516.5	1561.0	1580.7	1590.1	1589.0



TEST NUMBER: P331323-940

CATALOG NUMBER: SA2XXDIP-C485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1230.2	1371.9	1469.3	1531.2	1564.1	1581.8	1587.3
115°	1136.4	1272.0	1378.8	1452.3	1499.9	1526.9	1536.2
117.5°	1060.2	1183.2	1283.3	1358.3	1408.5	1437.0	1444.8
120°	1020.3	1130.2	1224.4	1296.9	1345.6	1375.6	1386.0
122.5°	987.2	1091.2	1176.3	1241.4	1289.2	1316.0	1324.6
125°	943.7	1034.8	1112.5	1172.6	1212.0	1237.9	1246.2
127.5°	901.4	987.4	1059.1	1111.5	1148.3	1170.7	1177.4
130°	873.3	955.1	1023.4	1074.2	1109.5	1130.2	1138.4
132.5°	846.8	921.9	986.1	1036.1	1071.3	1090.4	1097.8
135°	804.9	873.3	931.2	975.8	1010.0	1028.6	1032.8
137.5°	771.5	825.8	876.4	916.9	946.4	962.8	968.9
140°	750.0	797.6	843.2	876.4	903.3	918.8	925.1
142.5°	730.9	772.0	810.0	841.5	866.0	879.9	881.1
145°	706.5	738.6	768.7	793.4	811.1	821.4	824.6
147.5°	686.6	711.7	733.6	754.1	768.2	775.3	777.1
150°	673.3	695.1	713.7	729.2	741.7	747.9	748.9
152.5°	662.5	681.0	697.1	709.4	720.1	724.7	724.9
155°	645.3	660.8	672.3	683.7	690.9	695.1	693.0
157.5°	627.9	641.0	649.9	658.0	664.0	665.8	665.8
160°	616.4	627.8	635.0	642.2	647.4	648.5	648.5
162.5°	605.6	615.3	620.9	628.1	631.7	632.7	631.9
165°	589.4	596.6	600.8	604.9	609.1	609.1	608.1
167.5°	574.7	579.7	583.4	585.2	587.5	587.4	586.1
170°	565.6	569.7	571.8	572.8	576.0	574.9	572.8
172.5°	557.3	560.6	561.9	562.9	564.4	563.3	562.0
175°	548.0	549.0	550.0	550.0	551.1	550.0	548.0
177.5°	541.2	542.0	542.0	542.0	542.0	541.2	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7

(END OF REPORT)