

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331292-940

Luminaire Tested: **SA2XXDIP-C485D330U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331292-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D330U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2807.4 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331292-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331292-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63																			63									
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53																			53									
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	44																			44									
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	38																			38									
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32																			32									
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28																			28									
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25																			25									
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	22																			22									
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20																			20									
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18																			18									
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16																			16									

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11183	11183	11183
5°	11225	11063	11128
10°	11158	10952	11006
15°	11020	10810	10798
20°	10825	10596	10584
25°	10630	10334	10334
30°	10381	10094	10006
35°	10147	9806	9662
40°	9853	9518	9333
45°	9565	9229	9001
50°	9251	8932	8616
55°	8923	8586	8267
60°	8557	8173	7869
65°	8164	7759	7404
70°	7671	7260	6916
75°	6981	6687	6525
80°	6192	6007	5700
85°	5057	4798	4316



TEST NUMBER: P331292-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	2.3
10°-20°	183.3	6.5
20°-30°	269.4	9.6
30°-40°	312.9	11.1
40°-50°	312.5	11.1
50°-60°	272.6	9.7
60°-70°	201.5	7.2
70°-80°	114.1	4.1
80°-90°	32.2	1.1
90°-100°	23.7	0.8
100°-110°	73.5	2.6
110°-120°	125.6	4.5
120°-130°	165.1	5.9
130°-140°	185.4	6.6
140°-150°	181.8	6.5
150°-160°	152.4	5.4
160°-170°	101.1	3.6
170°-180°	35.3	1.3
0°-30°	517.7	18.4
0°-40°	830.6	29.6
0°-60°	1415.7	50.4
0°-90°	1763.6	62.8
90°-120°	222.7	7.9
90°-150°	755.0	26.9
90°-180°	1044.0	37.2
0°-180°	2807.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	693	693	693	693	693	
5°	693	690	683	688	687	66
15°	659	655	647	649	646	186
25°	597	591	580	581	580	274
35°	515	508	498	494	490	321
45°	419	414	404	397	394	323
55°	317	313	305	297	294	283
65°	214	210	203	197	194	211
75°	112	110	107	104	105	120
85°	27	27	26	24	23	31
90°	0	4	11	10	11	2
95°	16	19	20	20	20	19
105°	68	69	69	70	70	72
115°	126	128	127	127	126	125
125°	183	186	185	184	184	164
135°	237	241	241	241	240	183
145°	288	290	292	292	291	180
155°	329	330	331	333	332	151
165°	358	358	358	360	359	101
175°	373	372	371	373	371	35
180°	373	373	373	373	373	



TEST NUMBER: P331292-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	695.8	695.2	694.6	694.0	693.4	692.5	691.2	689.9	688.6	687.2	688.5
5°	692.6	692.0	691.4	690.8	690.3	689.1	687.5	685.9	684.2	682.6	683.8
7.5°	686.4	685.5	684.7	683.7	682.8	681.5	679.8	678.2	676.5	674.8	676.1
10°	680.6	679.6	678.5	677.5	676.5	675.0	673.2	671.5	669.8	668.0	669.1
12.5°	672.6	671.7	670.7	669.9	669.0	667.6	665.8	664.1	662.3	660.5	661.3
15°	659.3	658.4	657.5	656.7	655.8	654.3	652.4	650.5	648.5	646.7	647.2
17.5°	642.2	641.4	640.5	639.6	638.7	637.3	635.3	633.4	631.4	629.5	630.2
20°	630.0	629.1	628.2	627.3	626.4	625.0	622.9	620.8	618.8	616.7	617.2
22.5°	617.8	616.5	615.3	614.0	612.8	611.2	609.2	607.3	605.3	603.3	603.4
25°	596.7	595.5	594.3	593.2	592.0	590.1	587.6	585.1	582.6	580.1	580.3
27.5°	572.7	571.7	570.6	569.5	568.5	566.9	565.0	562.9	561.0	559.0	558.6
30°	556.8	555.5	554.4	553.2	552.0	550.3	548.0	545.9	543.7	541.4	541.0
32.5°	539.7	538.8	537.8	536.8	535.9	534.2	531.9	529.6	527.3	525.0	524.1
35°	514.8	513.3	511.8	510.3	508.9	506.9	504.6	502.2	499.8	497.5	496.6
37.5°	486.7	485.4	484.1	482.8	481.4	479.7	477.2	474.9	472.5	470.2	469.0
40°	467.5	466.3	465.1	464.0	462.8	461.0	458.6	456.3	453.9	451.6	450.2
42.5°	448.9	447.6	446.5	445.3	444.2	442.4	440.0	437.7	435.2	432.8	431.4
45°	418.9	417.9	416.8	415.8	414.7	413.1	410.9	408.7	406.4	404.2	402.6
47.5°	389.1	388.1	387.1	386.1	385.1	383.5	381.2	378.9	376.6	374.3	372.6
50°	368.3	367.6	366.8	366.0	365.3	363.9	361.9	359.8	357.7	355.6	353.6
52.5°	348.0	347.1	346.1	345.1	344.1	342.7	340.7	338.8	336.8	334.8	333.1
55°	317.0	316.1	315.2	314.3	313.4	312.1	310.3	308.5	306.7	305.0	303.3
57.5°	285.8	285.1	284.4	283.7	283.0	281.7	279.7	277.8	275.8	273.8	272.1
60°	265.0	264.5	263.9	263.2	262.7	261.4	259.3	257.2	255.1	253.1	251.5
62.5°	244.8	243.9	242.9	241.9	241.0	239.8	238.2	236.6	235.0	233.4	231.8
65°	213.7	212.9	212.0	211.1	210.3	209.0	207.6	206.1	204.6	203.1	201.8
67.5°	182.2	181.5	180.7	180.0	179.3	178.3	177.0	175.7	174.3	173.0	172.0
70°	162.5	161.9	161.3	160.7	160.2	159.2	157.8	156.5	155.2	153.8	152.8
72.5°	142.2	141.7	141.1	140.4	139.9	139.2	138.3	137.4	136.6	135.7	134.6
75°	111.9	111.6	111.3	111.0	110.7	110.2	109.4	108.7	108.0	107.2	106.3
77.5°	84.7	84.2	83.7	83.2	82.7	82.3	82.0	81.7	81.4	81.1	80.7
80°	66.6	66.4	66.3	66.2	66.0	65.8	65.5	65.2	64.9	64.6	64.1
82.5°	49.6	49.5	49.5	49.5	49.4	49.3	49.1	49.0	48.8	48.6	48.1
85°	27.3	27.2	27.0	26.8	26.8	26.6	26.4	26.3	26.1	25.9	25.5
87.5°	9.6	9.5	9.5	9.5	9.4	9.4	9.5	9.5	9.6	9.6	9.3
90°	0.4	1.2	2.0	2.9	3.7	4.9	6.4	7.9	9.5	11.1	10.9
92.5°	5.6	6.2	6.9	7.5	8.1	8.6	8.9	9.3	9.6	10.0	10.1
95°	16.4	17.1	17.7	18.5	19.2	19.6	19.7	19.9	20.1	20.2	20.2
97.5°	30.0	30.6	31.1	31.7	32.4	32.8	33.1	33.3	33.6	33.9	33.9
100°	40.0	40.6	41.1	41.7	42.3	42.6	42.8	43.1	43.2	43.5	43.5
102.5°	50.6	51.0	51.5	51.9	52.3	52.8	53.0	53.2	53.5	53.8	53.9
105°	67.8	67.9	68.1	68.4	68.6	68.8	68.9	69.0	69.2	69.3	69.5
107.5°	85.0	85.3	85.6	86.0	86.2	86.4	86.4	86.4	86.4	86.4	86.4
110°	96.1	96.5	96.9	97.4	97.7	98.0	98.0	98.0	98.0	98.0	98.0



TEST NUMBER: P331292-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.2	108.6	109.1	109.4	109.9	110.0	109.9	109.9	109.9	109.9	109.7
115°	126.0	126.4	126.9	127.2	127.7	127.9	127.7	127.5	127.4	127.2	127.2
117.5°	143.7	144.4	144.9	145.4	146.1	146.2	145.7	145.3	144.9	144.5	144.4
120°	155.6	156.2	156.8	157.3	157.8	157.8	157.3	156.8	156.2	155.6	155.6
122.5°	166.5	167.1	167.8	168.4	169.2	169.3	168.9	168.5	168.1	167.7	167.6
125°	183.3	184.0	184.6	185.2	185.8	186.1	185.8	185.7	185.5	185.2	185.0
127.5°	199.8	200.6	201.4	202.2	203.0	203.2	203.0	202.8	202.5	202.2	202.0
130°	210.2	211.1	212.0	212.9	213.7	214.2	214.0	213.9	213.7	213.6	213.5
132.5°	221.8	222.5	223.2	223.9	224.7	225.1	225.1	225.2	225.2	225.2	224.9
135°	237.2	238.0	238.8	239.5	240.3	240.8	240.9	241.0	241.2	241.3	241.2
137.5°	253.5	254.1	254.8	255.5	256.1	256.5	256.6	256.8	257.0	257.2	257.2
140°	263.4	264.0	264.7	265.3	265.9	266.4	266.7	267.1	267.4	267.8	267.8
142.5°	273.5	274.1	274.7	275.4	276.0	276.4	276.6	276.9	277.1	277.3	277.4
145°	287.9	288.5	288.9	289.4	289.9	290.3	290.8	291.2	291.6	292.0	292.1
147.5°	300.9	301.5	302.0	302.6	303.2	303.6	303.9	304.3	304.5	304.8	305.0
150°	309.7	310.1	310.5	310.9	311.4	311.7	312.0	312.3	312.5	312.8	313.1
152.5°	317.5	317.9	318.3	318.8	319.1	319.6	319.9	320.2	320.6	320.9	321.2
155°	329.2	329.4	329.7	329.8	330.0	330.3	330.5	330.6	330.9	331.1	331.4
157.5°	339.2	339.4	339.5	339.7	339.8	339.9	340.1	340.2	340.3	340.5	340.9
160°	345.3	345.4	345.5	345.7	345.8	346.0	346.0	346.1	346.2	346.3	346.6
162.5°	350.8	350.9	350.9	350.9	351.0	351.0	351.1	351.2	351.2	351.2	351.8
165°	358.2	358.1	358.0	358.0	357.9	357.8	357.8	357.8	357.8	357.8	358.4
167.5°	364.4	364.2	364.0	363.7	363.6	363.5	363.4	363.4	363.4	363.4	363.8
170°	367.7	367.5	367.2	367.0	366.8	366.7	366.6	366.5	366.5	366.4	366.8
172.5°	369.9	369.7	369.5	369.3	369.1	368.9	368.9	368.8	368.7	368.6	369.2
175°	372.7	372.5	372.3	372.0	371.8	371.7	371.6	371.4	371.2	371.1	371.6
177.5°	373.8	373.6	373.4	373.4	373.2	373.0	372.9	372.8	372.6	372.6	372.9
180°	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4



TEST NUMBER: P331292-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	692.6	692.6	692.6	692.6	692.6	692.6	692.6	692.6
2.5°	689.6	690.8	692.0	692.5	692.2	692.0	691.8	691.5
5°	685.0	686.2	687.3	687.8	687.5	687.2	686.9	686.6
7.5°	677.3	678.4	679.7	680.0	679.8	679.4	679.0	678.8
10°	670.3	671.5	672.7	673.1	672.6	672.2	671.7	671.3
12.5°	662.2	663.0	663.8	664.1	663.7	663.4	663.1	662.7
15°	647.8	648.5	649.0	648.9	648.2	647.5	646.8	646.0
17.5°	630.8	631.5	632.2	632.1	631.4	630.8	630.1	629.4
20°	617.6	618.0	618.5	618.4	617.8	617.2	616.6	616.0
22.5°	603.5	603.6	603.7	603.6	603.2	602.9	602.5	602.2
25°	580.7	580.9	581.2	581.2	580.9	580.7	580.3	580.1
27.5°	558.1	557.7	557.2	556.7	556.0	555.3	554.6	553.8
30°	540.6	540.1	539.7	539.1	538.5	538.0	537.3	536.7
32.5°	523.3	522.5	521.7	521.0	520.4	519.9	519.2	518.6
35°	495.7	494.8	493.9	493.1	492.4	491.6	490.9	490.2
37.5°	468.0	466.9	465.8	464.8	464.1	463.4	462.7	462.1
40°	448.9	447.5	446.2	445.2	444.6	444.1	443.4	442.8
42.5°	430.0	428.6	427.0	426.0	425.1	424.3	423.5	422.6
45°	401.0	399.4	397.7	396.6	396.0	395.5	394.8	394.2
47.5°	370.9	369.1	367.4	366.1	365.2	364.4	363.6	362.7
50°	351.5	349.4	347.3	345.9	345.2	344.5	343.7	343.0
52.5°	331.4	329.7	328.0	326.6	325.7	324.7	323.7	322.7
55°	301.5	299.7	297.9	296.7	295.9	295.2	294.4	293.7
57.5°	270.4	268.6	266.9	265.7	265.1	264.6	264.0	263.4
60°	249.8	248.2	246.6	245.5	245.0	244.6	244.2	243.7
62.5°	230.3	228.8	227.3	226.3	225.7	225.2	224.6	224.0
65°	200.5	199.1	197.8	196.7	196.0	195.3	194.6	193.8
67.5°	170.9	169.9	168.9	168.1	167.5	166.8	166.3	165.7
70°	151.8	150.7	149.7	148.9	148.3	147.7	147.1	146.5
72.5°	133.7	132.6	131.6	130.8	130.4	129.8	129.4	128.9
75°	105.4	104.6	103.7	103.3	103.7	104.0	104.2	104.6
77.5°	80.3	79.8	79.4	78.9	78.5	78.1	77.7	77.2
80°	63.7	63.2	62.9	62.4	62.2	61.9	61.5	61.3
82.5°	47.5	46.9	46.4	46.0	46.0	45.9	45.8	45.8
85°	25.1	24.6	24.2	23.9	23.7	23.6	23.5	23.3
87.5°	8.9	8.5	8.1	7.8	7.8	7.7	7.6	7.5
90°	10.8	10.6	10.4	10.4	10.5	10.6	10.6	10.7
92.5°	10.1	10.1	10.2	10.2	10.2	10.2	10.2	10.2
95°	20.2	20.2	20.2	20.1	20.0	19.8	19.7	19.5
97.5°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.8
100°	43.5	43.5	43.5	43.4	43.3	43.3	43.2	43.2
102.5°	53.9	53.9	54.0	54.0	53.9	53.9	53.9	53.8
105°	69.6	69.7	69.9	69.9	69.9	69.9	69.9	69.9
107.5°	86.5	86.6	86.6	86.5	86.1	85.9	85.5	85.2
110°	98.0	98.0	98.0	97.9	97.6	97.5	97.3	97.0



TEST NUMBER: P331292-940

CATALOG NUMBER: SA2XXDIP-C485D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	109.5	109.3	109.1	109.0	108.9	108.7	108.5	108.3
115°	127.2	127.1	127.0	126.9	126.6	126.4	126.3	126.0
117.5°	144.2	144.0	143.8	143.7	143.5	143.3	143.0	142.9
120°	155.6	155.6	155.6	155.5	155.3	155.1	154.9	154.7
122.5°	167.4	167.2	167.0	166.9	166.7	166.6	166.4	166.3
125°	184.9	184.6	184.4	184.2	184.2	184.1	184.0	184.0
127.5°	201.8	201.5	201.3	201.0	200.8	200.5	200.4	200.1
130°	213.3	213.2	213.0	212.9	212.6	212.2	212.0	211.7
132.5°	224.5	224.3	224.0	223.7	223.5	223.3	223.0	222.8
135°	241.2	241.1	241.0	240.9	240.7	240.5	240.3	240.0
137.5°	257.1	257.0	257.0	256.8	256.5	256.3	256.0	255.7
140°	267.8	267.8	267.8	267.6	267.3	267.1	266.8	266.5
142.5°	277.5	277.5	277.6	277.5	277.2	276.9	276.6	276.3
145°	292.2	292.2	292.3	292.2	291.9	291.7	291.4	291.1
147.5°	305.1	305.2	305.4	305.3	305.1	304.8	304.5	304.3
150°	313.3	313.4	313.7	313.7	313.4	313.3	313.1	312.8
152.5°	321.5	321.7	322.0	322.0	321.7	321.5	321.2	320.9
155°	331.8	332.2	332.5	332.6	332.3	332.2	332.0	331.7
157.5°	341.3	341.9	342.3	342.4	342.1	341.7	341.4	341.1
160°	347.1	347.5	347.9	347.9	347.7	347.4	347.1	346.9
162.5°	352.2	352.7	353.2	353.2	352.9	352.6	352.2	351.9
165°	358.8	359.4	359.8	359.9	359.5	359.2	358.8	358.6
167.5°	364.4	364.8	365.3	365.4	365.1	364.6	364.3	363.9
170°	367.4	367.8	368.4	368.4	368.0	367.6	367.1	366.7
172.5°	369.6	370.1	370.6	370.7	370.2	369.8	369.4	369.0
175°	372.1	372.6	373.1	373.1	372.7	372.3	371.8	371.4
177.5°	373.3	373.5	373.9	373.9	373.5	373.3	372.9	372.6
180°	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4

(END OF REPORT)