

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331651

Luminaire Tested: **SA2XXRDIP-C485D530U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331651
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3972.8 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331651
CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	71	67	64	61	58	53	51	49	43	42	40	35
3	82	73	67	61	75	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	69	61	54	49	52	47	43	43	40	37	35	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	32	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	33	39	34	30	33	29	26	27	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	23	25	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	16
10	49	37	30	26	45	35	29	24	30	25	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17354	17354	17354	17354
5°	19379	17462	15483	17462
10°	21502	17339	13421	17339
15°	22559	17085	10574	17085
20°	19557	16708	9149	16708
25°	12827	16192	8170	16192
30°	8634	15567	7394	15567
35°	6993	14781	6668	14781
40°	6218	13923	6171	13923
45°	5628	12919	5507	12919
50°	5122	11921	5102	11921
55°	4814	10818	4752	10818
60°	4027	9804	3978	9804
65°	3396	8902	3851	8902
70°	3139	7950	3630	7950
75°	2938	6918	3356	6918
80°	2706	5690	2985	5690
85°	2482	4502	2631	4502



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	2.6
10°-20°	283.9	7.1
20°-30°	365.8	9.2
30°-40°	347.6	8.8
40°-50°	297.8	7.5
50°-60°	226.8	5.7
60°-70°	143.4	3.6
70°-80°	71.6	1.8
80°-90°	20.4	0.5
90°-100°	24.1	0.6
100°-110°	88.2	2.2
110°-120°	235.8	5.9
120°-130°	389.3	9.8
130°-140°	414.0	10.4
140°-150°	384.8	9.7
150°-160°	309.4	7.8
160°-170°	199.4	5.0
170°-180°	68.6	1.7
0°-30°	751.6	18.9
0°-40°	1099.2	27.7
0°-60°	1623.8	40.9
0°-90°	1859.2	46.8
90°-120°	348.1	8.8
90°-150°	1536.2	38.7
90°-180°	2114.0	53.2
0°-180°	3972.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1196	1077	955	1077	1196	118
15°	1350	1022	633	1022	1350	364
25°	720	909	459	909	720	342
35°	355	750	338	750	355	227
45°	246	566	241	566	246	191
55°	171	384	169	384	171	150
65°	89	233	101	233	89	90
75°	47	111	54	111	47	50
85°	13	24	14	24	13	15
90°	14	0	14	0	14	7
95°	22	34	22	34	22	21
105°	40	159	40	159	40	41
115°	43	300	43	300	43	107
125°	446	424	446	424	446	386
135°	542	525	542	525	542	418
145°	618	609	618	609	618	387
155°	671	671	671	671	671	310
165°	705	707	705	707	705	199
175°	719	723	719	723	719	68
180°	721	721	721	721	721	



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1118.4	1119.3	1120.2	1118.1	1118.1	1116.3	1112.4	1109.4	1101.0	1099.8	1099.8
5°	1195.7	1195.0	1196.5	1191.6	1184.9	1183.4	1176.3	1167.0	1157.3	1146.4	1144.2
7.5°	1272.7	1271.6	1268.6	1267.7	1262.6	1251.3	1239.9	1227.7	1211.6	1195.8	1187.9
10°	1311.5	1323.8	1316.4	1303.3	1305.9	1288.4	1279.0	1263.0	1249.5	1226.0	1220.8
12.5°	1349.7	1354.6	1352.2	1344.8	1341.5	1329.3	1316.7	1302.7	1277.9	1256.8	1238.4
15°	1349.6	1356.7	1358.6	1356.3	1358.2	1357.4	1350.7	1339.1	1317.5	1294.3	1274.2
17.5°	1250.0	1254.9	1267.1	1275.4	1285.9	1308.0	1318.9	1323.2	1319.9	1306.7	1292.5
20°	1138.2	1130.0	1164.4	1181.9	1196.9	1234.2	1266.3	1278.6	1298.4	1298.1	1294.3
22.5°	979.9	981.8	1014.4	1035.2	1078.9	1116.2	1152.8	1199.2	1237.5	1262.8	1277.6
25°	720.0	734.2	766.7	795.0	843.6	913.1	976.2	1049.4	1118.4	1173.0	1224.9
27.5°	540.7	541.8	567.5	593.8	622.6	679.5	759.0	846.4	944.9	1026.1	1119.6
30°	463.1	460.8	471.7	487.7	512.4	556.4	616.2	702.1	800.3	922.8	1031.8
32.5°	408.1	408.2	416.4	428.3	448.7	478.4	519.4	589.1	682.0	802.4	930.2
35°	354.8	354.4	360.4	369.0	377.5	396.6	424.6	461.2	525.1	637.5	768.2
37.5°	316.5	318.2	321.1	326.5	335.9	346.5	363.4	387.9	433.4	499.9	609.7
40°	295.0	295.8	299.9	304.4	310.0	318.2	332.0	351.8	385.0	438.0	518.3
42.5°	275.3	276.0	279.0	283.1	287.5	295.8	307.2	324.3	351.3	392.6	458.9
45°	246.5	246.5	249.1	250.9	255.8	263.3	272.6	286.8	305.5	336.1	380.2
47.5°	219.4	219.5	221.2	224.4	227.5	233.3	242.5	254.1	267.7	291.4	329.0
50°	203.9	204.3	205.4	208.0	209.9	215.1	222.2	232.3	246.5	264.8	296.1
52.5°	191.3	191.1	192.5	193.7	194.9	198.7	204.0	212.9	225.6	241.5	267.5
55°	171.0	169.5	171.8	173.6	174.8	176.3	179.2	184.9	195.7	209.1	228.5
57.5°	145.6	145.0	146.6	148.3	151.8	155.9	158.4	162.0	167.6	177.2	196.5
60°	124.7	124.7	128.1	129.2	133.3	138.5	143.8	146.8	152.4	158.7	172.9
62.5°	106.2	106.5	108.1	109.2	111.5	117.9	125.3	131.8	137.1	143.2	152.6
65°	88.9	89.6	89.6	90.4	91.9	93.4	96.3	101.6	110.9	119.5	126.6
67.5°	75.4	75.7	75.9	76.6	77.0	78.6	79.8	82.2	84.3	92.5	101.3
70°	66.5	67.6	67.2	68.0	68.3	69.1	70.6	71.7	75.1	76.9	82.2
72.5°	58.1	58.9	58.9	59.3	60.3	60.4	61.6	62.7	64.9	66.5	69.3
75°	47.1	46.7	47.1	47.8	48.2	48.5	48.5	50.0	51.2	52.7	54.5
77.5°	36.3	36.7	36.6	36.7	36.7	37.4	37.3	38.0	39.1	39.9	40.8
80°	29.1	29.5	29.1	29.5	29.9	30.2	29.9	30.2	31.4	32.1	32.1
82.5°	22.6	22.6	22.9	22.9	23.0	23.1	23.6	23.7	24.5	24.3	24.6
85°	13.4	13.1	13.1	13.1	13.4	13.8	13.4	13.4	13.8	13.8	13.8
87.5°	7.6	7.9	7.8	7.8	7.7	7.6	7.5	7.7	7.3	7.5	7.0
90°	14.1	13.9	13.6	13.4	13.2	12.8	12.2	11.6	11.0	10.4	9.5
92.5°	14.1	14.0	13.8	13.7	13.5	13.3	13.0	12.7	12.4	12.1	11.6
95°	22.4	22.6	22.7	22.8	22.9	22.7	22.1	21.5	20.9	20.4	19.5
97.5°	30.0	29.8	29.7	29.5	29.4	29.1	28.6	28.2	27.7	27.2	25.4
100°	35.0	34.7	34.5	34.3	34.0	33.5	32.5	31.6	30.7	29.7	27.8
102.5°	37.5	37.1	36.8	36.5	36.2	35.4	34.2	33.0	31.8	30.6	27.1
105°	39.7	39.2	38.7	38.3	37.8	36.9	35.7	34.4	33.1	31.8	26.5
107.5°	40.8	40.3	39.9	39.4	39.0	39.4	40.7	42.0	43.3	44.6	25.5
110°	41.2	40.8	40.3	39.8	39.4	44.9	56.5	68.1	79.7	91.3	124.8



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	41.6	41.3	40.9	40.5	40.2	61.1	103.4	145.7	188.0	230.4	238.6
115°	42.8	51.1	59.5	67.8	76.2	107.2	160.9	214.6	268.3	322.0	319.1
117.5°	174.7	202.2	229.6	257.0	284.5	304.7	317.7	330.7	343.7	356.6	354.7
120°	318.3	334.0	349.7	365.3	381.0	388.1	386.7	385.3	383.9	382.5	380.4
122.5°	397.2	400.3	403.3	406.4	409.4	410.5	409.7	408.8	408.0	407.2	404.9
125°	446.2	445.9	445.5	445.2	444.8	444.2	443.4	442.6	441.8	441.0	438.8
127.5°	477.1	477.0	477.0	476.9	476.8	476.2	475.0	473.8	472.6	471.5	469.8
130°	496.3	496.4	496.5	496.6	496.8	496.2	494.9	493.6	492.4	491.1	489.8
132.5°	515.1	515.2	515.3	515.4	515.5	515.1	514.0	512.9	511.8	510.7	509.4
135°	542.2	542.5	542.7	542.9	543.2	542.7	541.5	540.4	539.2	538.0	537.0
137.5°	567.0	567.4	567.7	568.1	568.5	568.2	567.0	565.9	564.8	563.6	562.4
140°	582.4	583.0	583.6	584.1	584.7	584.5	583.4	582.4	581.4	580.3	579.0
142.5°	597.4	598.0	598.6	599.2	599.8	599.6	598.6	597.7	596.7	595.8	594.3
145°	618.4	619.0	619.6	620.2	620.7	620.6	619.8	619.0	618.2	617.4	615.4
147.5°	636.9	637.4	637.9	638.4	638.8	638.8	638.2	637.6	637.0	636.4	634.4
150°	648.2	648.7	649.3	649.9	650.5	650.4	649.7	649.0	648.3	647.6	645.8
152.5°	657.8	658.5	659.3	660.1	660.8	660.9	660.2	659.5	658.8	658.1	656.3
155°	671.1	672.1	673.0	673.9	674.8	675.0	674.3	673.6	672.9	672.2	670.8
157.5°	683.3	684.2	685.1	686.0	687.0	687.0	686.2	685.4	684.6	683.9	682.9
160°	690.4	691.2	692.1	692.9	693.7	693.7	693.0	692.3	691.7	691.0	690.3
162.5°	696.3	697.3	698.3	699.3	700.3	700.4	699.6	698.8	698.0	697.2	696.6
165°	705.0	705.9	706.7	707.5	708.3	708.3	707.5	706.7	705.9	705.0	704.7
167.5°	710.6	711.6	712.7	713.7	714.8	714.9	714.1	713.2	712.4	711.6	711.3
170°	713.9	715.0	716.0	717.0	718.1	718.2	717.4	716.6	715.8	715.0	714.7
172.5°	716.4	717.5	718.5	719.6	720.6	720.7	719.9	719.1	718.3	717.5	717.2
175°	718.6	719.8	720.9	722.1	723.3	723.4	722.6	721.8	721.0	720.2	719.9
177.5°	720.0	720.8	721.6	722.5	723.3	723.4	722.8	722.1	721.5	720.8	720.7
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1100.4	1098.1	1096.0	1090.6	1087.9	1081.9	1081.0	1080.7	1073.0	1065.5	1063.4
5°	1138.2	1132.3	1123.3	1112.8	1102.0	1090.8	1083.3	1077.4	1062.4	1048.2	1040.0
7.5°	1176.3	1163.5	1148.0	1128.2	1111.7	1093.2	1079.5	1067.1	1045.9	1025.6	1011.9
10°	1204.7	1183.8	1163.3	1136.0	1114.7	1093.8	1074.4	1057.6	1033.7	1006.8	987.7
12.5°	1222.3	1199.3	1171.0	1144.4	1116.8	1090.2	1064.2	1042.6	1014.6	986.8	964.1
15°	1246.2	1221.5	1187.2	1149.1	1113.6	1078.9	1049.0	1022.1	985.5	952.3	924.6
17.5°	1265.7	1231.7	1194.8	1150.8	1109.7	1065.6	1027.1	992.7	952.0	911.9	879.4
20°	1271.9	1238.3	1195.7	1151.7	1103.1	1051.2	1009.8	972.4	928.7	885.0	847.7
22.5°	1268.0	1241.9	1194.5	1141.8	1092.1	1037.8	991.0	947.6	899.2	854.6	811.3
25°	1241.7	1232.7	1187.9	1130.4	1073.6	1010.5	956.4	908.9	853.7	805.9	758.8
27.5°	1180.2	1199.6	1171.8	1110.5	1047.4	979.7	918.9	864.9	807.5	753.7	706.8
30°	1121.1	1165.5	1153.5	1096.8	1026.2	959.7	891.4	835.0	773.8	718.5	672.2
32.5°	1040.1	1113.5	1125.2	1077.7	1004.7	931.6	860.0	803.9	740.0	681.7	636.6
35°	911.2	1021.0	1071.4	1041.1	967.9	889.2	815.2	749.9	685.6	628.1	583.3
37.5°	757.4	906.9	991.0	993.1	925.9	844.0	763.5	698.6	632.8	576.4	527.9
40°	657.6	819.7	929.1	953.4	896.6	808.1	726.7	660.6	596.4	541.1	485.5
42.5°	568.0	729.5	864.0	906.2	861.1	773.2	691.5	622.4	559.9	507.6	450.8
45°	459.3	600.5	748.7	824.2	799.2	717.7	631.5	565.8	507.1	461.9	407.4
47.5°	387.5	487.0	630.4	732.5	732.0	657.7	572.9	509.9	455.5	413.2	369.0
50°	346.5	433.2	554.6	670.3	680.0	617.7	537.0	474.6	423.9	379.4	343.9
52.5°	309.8	381.2	490.3	601.3	628.9	574.9	496.7	439.1	389.8	348.9	318.5
55°	261.8	317.0	400.0	503.8	545.6	507.5	438.0	384.3	344.3	310.0	283.8
57.5°	221.4	262.9	329.4	413.0	461.7	437.7	380.5	336.8	302.6	271.5	250.9
60°	196.1	230.0	286.4	356.3	410.0	393.2	344.3	303.6	274.5	247.6	228.2
62.5°	172.2	201.4	249.7	306.4	355.7	348.7	308.8	274.6	249.1	224.6	208.2
65°	138.5	159.8	197.5	242.0	281.6	284.9	256.2	233.0	210.2	190.8	176.3
67.5°	110.3	124.2	150.8	188.2	217.9	228.5	210.9	193.2	175.1	160.1	147.5
70°	93.0	104.2	123.6	153.9	181.1	192.3	182.2	168.4	152.7	140.4	129.6
72.5°	75.4	86.3	100.6	122.8	146.2	158.3	154.8	144.8	132.1	121.9	111.7
75°	56.8	60.1	69.8	84.8	103.1	113.5	116.1	110.9	100.8	93.0	87.0
77.5°	42.0	44.0	48.6	56.5	68.4	77.7	81.6	81.0	74.0	69.5	63.9
80°	33.6	34.7	37.0	40.3	49.3	58.6	61.2	61.2	56.4	54.5	48.9
82.5°	25.5	26.4	27.7	29.6	33.8	41.9	44.8	45.4	42.3	39.9	35.5
85°	14.6	14.2	14.9	16.1	16.8	19.0	23.5	24.3	23.5	20.5	19.4
87.5°	6.8	6.9	6.7	6.2	6.2	6.3	7.5	8.8	7.8	7.2	6.8
90°	8.6	7.7	6.7	5.6	4.3	3.1	1.8	0.5	1.8	3.1	4.3
92.5°	11.2	10.7	10.3	10.1	10.2	10.3	10.4	10.5	10.4	10.3	10.2
95°	18.7	17.9	17.1	18.6	22.4	26.3	30.1	33.9	30.1	26.3	22.4
97.5°	23.5	21.6	19.7	24.2	35.0	45.8	56.5	67.3	56.5	45.8	35.0
100°	25.8	23.8	21.9	28.8	44.7	60.6	76.5	92.4	76.5	60.6	44.7
102.5°	63.6	80.1	96.5	106.5	109.8	113.2	116.6	119.9	116.6	113.2	109.8
105°	95.2	126.8	158.5	172.6	169.1	165.6	162.1	158.6	162.1	165.6	169.1
107.5°	120.5	158.5	196.4	214.0	211.2	208.4	205.6	202.8	205.6	208.4	211.2
110°	158.4	191.9	225.4	240.9	238.5	236.1	233.6	231.2	233.6	236.1	238.5



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.9	255.2	263.5	266.5	264.4	262.2	260.1	257.9	260.1	262.2	264.4
115°	316.2	313.3	310.4	308.0	306.0	304.0	302.0	300.1	302.0	304.0	306.0
117.5°	352.7	350.7	348.7	346.6	344.4	342.2	340.0	337.8	340.0	342.2	344.4
120°	378.4	376.3	374.2	372.3	370.5	368.8	367.0	365.3	367.0	368.8	370.5
122.5°	402.6	400.3	398.1	396.0	394.2	392.4	390.5	388.7	390.5	392.4	394.2
125°	436.6	434.4	432.2	430.3	428.8	427.3	425.8	424.3	425.8	427.3	428.8
127.5°	468.2	466.5	464.9	463.2	461.5	459.9	458.2	456.5	458.2	459.9	461.5
130°	488.5	487.3	486.0	484.4	482.6	480.7	478.8	477.0	478.8	480.7	482.6
132.5°	508.2	506.9	505.6	504.2	502.6	501.0	499.4	497.9	499.4	501.0	502.6
135°	536.0	534.9	533.9	532.4	530.6	528.7	526.9	525.0	526.9	528.7	530.6
137.5°	561.3	560.1	558.9	557.6	556.3	555.0	553.7	552.5	553.7	555.0	556.3
140°	577.8	576.5	575.2	574.1	573.2	572.3	571.3	570.4	571.3	572.3	573.2
142.5°	592.8	591.4	589.9	588.8	587.9	587.1	586.3	585.4	586.3	587.1	587.9
145°	613.4	611.5	609.5	608.6	608.7	608.8	608.9	609.0	608.9	608.8	608.7
147.5°	632.5	630.5	628.6	627.8	628.3	628.7	629.1	629.6	629.1	628.7	628.3
150°	643.9	642.1	640.2	639.7	640.5	641.3	642.1	642.9	642.1	641.3	640.5
152.5°	654.6	652.8	651.0	650.6	651.5	652.4	653.3	654.2	653.3	652.4	651.5
155°	669.4	668.0	666.6	666.4	667.5	668.5	669.6	670.6	669.6	668.5	667.5
157.5°	681.9	680.9	680.0	679.9	680.8	681.7	682.6	683.4	682.6	681.7	680.8
160°	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	690.3	689.6	688.9
162.5°	696.0	695.4	694.8	694.9	695.5	696.2	696.9	697.6	696.9	696.2	695.5
165°	704.3	704.0	703.7	703.8	704.5	705.2	705.9	706.6	705.9	705.2	704.5
167.5°	711.0	710.6	710.3	710.5	711.2	711.9	712.6	713.3	712.6	711.9	711.2
170°	714.5	714.3	714.0	714.3	715.0	715.7	716.4	717.0	716.4	715.7	715.0
172.5°	717.0	716.8	716.5	716.8	717.5	718.2	718.9	719.6	718.9	718.2	717.5
175°	719.7	719.5	719.3	719.5	720.4	721.2	722.0	722.8	722.0	721.2	720.4
177.5°	720.6	720.5	720.4	720.7	721.4	722.0	722.7	723.3	722.7	722.0	721.4
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1059.5	1057.4	1053.5	1047.6	1044.0	1037.7	1033.5	1035.9	1036.5	1035.9	1035.3
5°	1031.1	1023.2	1012.4	1001.9	992.2	981.8	975.8	973.2	967.9	965.0	963.5
7.5°	996.6	983.1	967.8	949.6	934.1	917.9	909.6	905.5	894.8	889.0	883.9
10°	970.9	949.6	934.3	910.4	895.9	874.6	860.0	860.4	845.8	837.6	831.6
12.5°	942.6	919.2	893.7	872.2	852.0	834.9	817.3	810.2	794.7	786.8	770.7
15°	895.5	868.2	841.4	812.2	791.7	765.2	739.8	708.8	683.8	662.1	656.1
17.5°	844.1	810.4	783.4	749.2	714.0	669.4	640.0	622.0	606.9	595.5	587.0
20°	808.9	774.5	745.8	694.2	646.8	616.5	594.9	581.1	565.4	553.1	546.3
22.5°	771.8	736.0	696.8	639.2	602.3	578.0	558.7	542.8	532.2	522.6	516.5
25°	719.2	680.0	615.4	575.8	546.0	520.6	507.1	497.4	486.2	473.1	467.2
27.5°	663.7	601.3	554.9	525.5	497.0	480.5	468.4	453.9	443.9	438.0	431.8
30°	622.1	559.8	523.6	491.4	471.3	453.0	438.8	430.6	420.9	410.8	406.7
32.5°	575.8	526.0	491.3	464.6	444.1	428.5	417.3	404.0	397.0	390.8	382.2
35°	518.3	480.6	448.9	427.2	407.8	395.1	382.0	374.2	361.5	356.3	352.9
37.5°	469.6	436.9	413.2	390.4	375.0	361.0	353.0	340.5	335.0	327.7	320.6
40°	442.1	410.0	387.3	368.6	351.4	340.9	330.9	320.8	312.6	309.2	300.6
42.5°	414.1	387.9	365.1	344.7	333.2	322.1	309.4	302.0	293.4	288.0	282.7
45°	375.3	352.2	332.7	315.9	303.2	291.7	283.4	271.1	266.3	255.4	250.9
47.5°	341.2	319.7	301.2	285.2	272.8	265.3	253.3	243.6	235.9	229.2	223.5
50°	317.0	299.1	281.2	267.0	255.8	245.0	232.7	227.8	215.8	212.5	209.1
52.5°	294.9	277.9	261.5	247.6	236.4	225.9	215.0	208.7	200.6	197.2	194.8
55°	264.0	247.6	231.9	219.6	208.4	197.5	190.8	183.0	179.2	176.6	173.6
57.5°	232.9	218.2	206.1	193.7	182.4	173.8	166.0	161.3	157.4	154.0	150.4
60°	213.2	199.0	188.2	176.6	165.1	158.0	152.0	146.4	141.9	136.7	135.2
62.5°	192.3	179.9	170.0	158.7	148.6	142.1	136.5	131.2	125.8	118.2	116.1
65°	163.6	153.9	143.4	134.1	125.1	118.8	110.5	104.6	102.3	101.6	101.2
67.5°	137.6	128.4	119.4	109.9	101.7	95.8	91.6	90.7	89.2	88.7	87.7
70°	120.2	111.7	102.7	93.7	85.9	84.8	83.3	81.8	79.9	79.2	78.4
72.5°	104.7	95.8	86.9	79.7	76.3	74.9	73.4	71.9	70.7	69.9	69.5
75°	80.3	72.1	66.1	63.5	61.6	60.5	58.3	57.1	56.4	55.3	54.9
77.5°	57.8	53.2	50.4	48.8	46.8	45.6	44.4	43.2	42.4	42.2	41.6
80°	44.1	41.8	40.0	37.7	37.0	35.5	35.1	34.0	34.4	33.2	33.2
82.5°	34.2	31.4	29.8	28.8	28.0	26.8	26.4	25.9	26.0	25.2	25.2
85°	17.6	16.8	16.1	15.3	15.3	14.2	14.6	14.2	14.2	13.4	13.1
87.5°	6.8	6.7	6.3	6.5	6.7	6.6	6.7	6.5	6.6	6.7	6.5
90°	5.6	6.7	7.7	8.6	9.5	10.4	11.0	11.6	12.2	12.8	13.2
92.5°	10.1	10.3	10.7	11.2	11.6	12.1	12.4	12.7	13.0	13.3	13.5
95°	18.6	17.1	17.9	18.7	19.5	20.4	20.9	21.5	22.1	22.7	22.9
97.5°	24.2	19.7	21.6	23.5	25.4	27.2	27.7	28.2	28.6	29.1	29.4
100°	28.8	21.9	23.8	25.8	27.8	29.7	30.7	31.6	32.5	33.5	34.0
102.5°	106.5	96.5	80.1	63.6	47.1	30.6	31.8	33.0	34.2	35.4	36.2
105°	172.6	158.5	126.8	95.2	63.5	31.8	33.1	34.4	35.7	36.9	37.8
107.5°	214.0	196.4	158.5	120.5	82.5	44.6	43.3	42.0	40.7	39.4	39.0
110°	240.9	225.4	191.9	158.4	124.8	91.3	79.7	68.1	56.5	44.9	39.4



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	266.5	263.5	255.2	246.9	238.6	230.4	188.0	145.7	103.4	61.1	40.2
115°	308.0	310.4	313.3	316.2	319.1	322.0	268.3	214.6	160.9	107.2	76.2
117.5°	346.6	348.7	350.7	352.7	354.7	356.6	343.7	330.7	317.7	304.7	284.5
120°	372.3	374.2	376.3	378.4	380.4	382.5	383.9	385.3	386.7	388.1	381.0
122.5°	396.0	398.1	400.3	402.6	404.9	407.2	408.0	408.8	409.7	410.5	409.4
125°	430.3	432.2	434.4	436.6	438.8	441.0	441.8	442.6	443.4	444.2	444.8
127.5°	463.2	464.9	466.5	468.2	469.8	471.5	472.6	473.8	475.0	476.2	476.8
130°	484.4	486.0	487.3	488.5	489.8	491.1	492.4	493.6	494.9	496.2	496.8
132.5°	504.2	505.6	506.9	508.2	509.4	510.7	511.8	512.9	514.0	515.1	515.5
135°	532.4	533.9	534.9	536.0	537.0	538.0	539.2	540.4	541.5	542.7	543.2
137.5°	557.6	558.9	560.1	561.3	562.4	563.6	564.8	565.9	567.0	568.2	568.5
140°	574.1	575.2	576.5	577.8	579.0	580.3	581.4	582.4	583.4	584.5	584.7
142.5°	588.8	589.9	591.4	592.8	594.3	595.8	596.7	597.7	598.6	599.6	599.8
145°	608.6	609.5	611.5	613.4	615.4	617.4	618.2	619.0	619.8	620.6	620.7
147.5°	627.8	628.6	630.5	632.5	634.4	636.4	637.0	637.6	638.2	638.8	638.8
150°	639.7	640.2	642.1	643.9	645.8	647.6	648.3	649.0	649.7	650.4	650.5
152.5°	650.6	651.0	652.8	654.6	656.3	658.1	658.8	659.5	660.2	660.9	660.8
155°	666.4	666.6	668.0	669.4	670.8	672.2	672.9	673.6	674.3	675.0	674.8
157.5°	679.9	680.0	680.9	681.9	682.9	683.9	684.6	685.4	686.2	687.0	687.0
160°	688.2	688.2	688.9	689.6	690.3	691.0	691.7	692.3	693.0	693.7	693.7
162.5°	694.9	694.8	695.4	696.0	696.6	697.2	698.0	698.8	699.6	700.4	700.3
165°	703.8	703.7	704.0	704.3	704.7	705.0	705.9	706.7	707.5	708.3	708.3
167.5°	710.5	710.3	710.6	711.0	711.3	711.6	712.4	713.2	714.1	714.9	714.8
170°	714.3	714.0	714.3	714.5	714.7	715.0	715.8	716.6	717.4	718.2	718.1
172.5°	716.8	716.5	716.8	717.0	717.2	717.5	718.3	719.1	719.9	720.7	720.6
175°	719.5	719.3	719.5	719.7	719.9	720.2	721.0	721.8	722.6	723.4	723.3
177.5°	720.7	720.4	720.5	720.6	720.7	720.8	721.5	722.1	722.8	723.4	723.3
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1032.0	1032.6	1031.7	1032.3	1031.7	1032.6	1032.0	1035.3	1035.9	1036.5	1035.9
5°	961.6	957.1	956.4	955.3	956.4	957.1	961.6	963.5	965.0	967.9	973.2
7.5°	877.5	876.8	875.0	872.3	875.0	876.8	877.5	883.9	889.0	894.8	905.5
10°	823.4	821.6	821.2	818.6	821.2	821.6	823.4	831.6	837.6	845.8	860.4
12.5°	760.1	748.1	746.8	740.3	746.8	748.1	760.1	770.7	786.8	794.7	810.2
15°	647.2	644.9	637.5	632.6	637.5	644.9	647.2	656.1	662.1	683.8	708.8
17.5°	582.6	575.3	573.0	572.0	573.0	575.3	582.6	587.0	595.5	606.9	622.0
20°	541.1	534.4	533.3	532.5	533.3	534.4	541.1	546.3	553.1	565.4	581.1
22.5°	512.4	505.4	502.5	500.3	502.5	505.4	512.4	516.5	522.6	532.2	542.8
25°	463.4	460.8	459.3	458.6	459.3	460.8	463.4	467.2	473.1	486.2	497.4
27.5°	425.1	419.4	418.2	416.3	418.2	419.4	425.1	431.8	438.0	443.9	453.9
30°	403.3	401.4	398.8	396.6	398.8	401.4	403.3	406.7	410.8	420.9	430.6
32.5°	377.6	376.1	373.7	372.7	373.7	376.1	377.6	382.2	390.8	397.0	404.0
35°	349.2	343.9	341.7	338.3	341.7	343.9	349.2	352.9	356.3	361.5	374.2
37.5°	319.1	316.3	313.2	314.3	313.2	316.3	319.1	320.6	327.7	335.0	340.5
40°	295.8	293.9	293.1	292.8	293.1	293.9	295.8	300.6	309.2	312.6	320.8
42.5°	277.2	272.1	270.1	270.1	270.1	272.1	277.2	282.7	288.0	293.4	302.0
45°	249.1	244.2	240.9	241.2	240.9	244.2	249.1	250.9	255.4	266.3	271.1
47.5°	220.3	220.1	218.0	218.7	218.0	220.1	220.3	223.5	229.2	235.9	243.6
50°	206.5	204.3	202.8	203.1	202.8	204.3	206.5	209.1	212.5	215.8	227.8
52.5°	193.4	191.4	190.2	191.8	190.2	191.4	193.4	194.8	197.2	200.6	208.7
55°	171.8	169.5	169.2	168.8	169.2	169.5	171.8	173.6	176.6	179.2	183.0
57.5°	147.7	146.2	143.9	143.0	143.9	146.2	147.7	150.4	154.0	157.4	161.3
60°	130.3	127.3	123.6	123.2	123.6	127.3	130.3	135.2	136.7	141.9	146.4
62.5°	114.5	113.9	113.2	113.1	113.2	113.9	114.5	116.1	118.2	125.8	131.2
65°	100.5	100.1	100.5	100.8	100.5	100.1	100.5	101.2	101.6	102.3	104.6
67.5°	87.5	86.9	86.2	86.5	86.2	86.9	87.5	87.7	88.7	89.2	90.7
70°	77.7	77.3	76.9	76.9	76.9	77.3	77.7	78.4	79.2	79.9	81.8
72.5°	68.1	68.0	67.7	67.4	67.7	68.0	68.1	69.5	69.9	70.7	71.9
75°	54.5	53.8	53.8	53.8	53.8	53.8	54.5	54.9	55.3	56.4	57.1
77.5°	41.5	41.2	40.8	40.5	40.8	41.2	41.5	41.6	42.2	42.4	43.2
80°	32.9	32.5	32.1	32.1	32.1	32.5	32.9	33.2	33.2	34.4	34.0
82.5°	25.1	24.7	24.6	24.3	24.6	24.7	25.1	25.2	25.2	26.0	25.9
85°	13.4	13.8	13.4	14.2	13.4	13.8	13.4	13.1	13.4	14.2	14.2
87.5°	6.6	6.3	6.7	6.4	6.7	6.3	6.6	6.5	6.7	6.6	6.5
90°	13.4	13.6	13.9	14.1	13.9	13.6	13.4	13.2	12.8	12.2	11.6
92.5°	13.7	13.8	14.0	14.1	14.0	13.8	13.7	13.5	13.3	13.0	12.7
95°	22.8	22.7	22.6	22.4	22.6	22.7	22.8	22.9	22.7	22.1	21.5
97.5°	29.5	29.7	29.8	30.0	29.8	29.7	29.5	29.4	29.1	28.6	28.2
100°	34.3	34.5	34.7	35.0	34.7	34.5	34.3	34.0	33.5	32.5	31.6
102.5°	36.5	36.8	37.1	37.5	37.1	36.8	36.5	36.2	35.4	34.2	33.0
105°	38.3	38.7	39.2	39.7	39.2	38.7	38.3	37.8	36.9	35.7	34.4
107.5°	39.4	39.9	40.3	40.8	40.3	39.9	39.4	39.0	39.4	40.7	42.0
110°	39.8	40.3	40.8	41.2	40.8	40.3	39.8	39.4	44.9	56.5	68.1



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	40.5	40.9	41.3	41.6	41.3	40.9	40.5	40.2	61.1	103.4	145.7
115°	67.8	59.5	51.1	42.8	51.1	59.5	67.8	76.2	107.2	160.9	214.6
117.5°	257.0	229.6	202.2	174.7	202.2	229.6	257.0	284.5	304.7	317.7	330.7
120°	365.3	349.7	334.0	318.3	334.0	349.7	365.3	381.0	388.1	386.7	385.3
122.5°	406.4	403.3	400.3	397.2	400.3	403.3	406.4	409.4	410.5	409.7	408.8
125°	445.2	445.5	445.9	446.2	445.9	445.5	445.2	444.8	444.2	443.4	442.6
127.5°	476.9	477.0	477.0	477.1	477.0	477.0	476.9	476.8	476.2	475.0	473.8
130°	496.6	496.5	496.4	496.3	496.4	496.5	496.6	496.8	496.2	494.9	493.6
132.5°	515.4	515.3	515.2	515.1	515.2	515.3	515.4	515.5	515.1	514.0	512.9
135°	542.9	542.7	542.5	542.2	542.5	542.7	542.9	543.2	542.7	541.5	540.4
137.5°	568.1	567.7	567.4	567.0	567.4	567.7	568.1	568.5	568.2	567.0	565.9
140°	584.1	583.6	583.0	582.4	583.0	583.6	584.1	584.7	584.5	583.4	582.4
142.5°	599.2	598.6	598.0	597.4	598.0	598.6	599.2	599.8	599.6	598.6	597.7
145°	620.2	619.6	619.0	618.4	619.0	619.6	620.2	620.7	620.6	619.8	619.0
147.5°	638.4	637.9	637.4	636.9	637.4	637.9	638.4	638.8	638.8	638.2	637.6
150°	649.9	649.3	648.7	648.2	648.7	649.3	649.9	650.5	650.4	649.7	649.0
152.5°	660.1	659.3	658.5	657.8	658.5	659.3	660.1	660.8	660.9	660.2	659.5
155°	673.9	673.0	672.1	671.1	672.1	673.0	673.9	674.8	675.0	674.3	673.6
157.5°	686.0	685.1	684.2	683.3	684.2	685.1	686.0	687.0	687.0	686.2	685.4
160°	692.9	692.1	691.2	690.4	691.2	692.1	692.9	693.7	693.7	693.0	692.3
162.5°	699.3	698.3	697.3	696.3	697.3	698.3	699.3	700.3	700.4	699.6	698.8
165°	707.5	706.7	705.9	705.0	705.9	706.7	707.5	708.3	708.3	707.5	706.7
167.5°	713.7	712.7	711.6	710.6	711.6	712.7	713.7	714.8	714.9	714.1	713.2
170°	717.0	716.0	715.0	713.9	715.0	716.0	717.0	718.1	718.2	717.4	716.6
172.5°	719.6	718.5	717.5	716.4	717.5	718.5	719.6	720.6	720.7	719.9	719.1
175°	722.1	720.9	719.8	718.6	719.8	720.9	722.1	723.3	723.4	722.6	721.8
177.5°	722.5	721.6	720.8	720.0	720.8	721.6	722.5	723.3	723.4	722.8	722.1
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1033.5	1037.7	1044.0	1047.6	1053.5	1057.4	1059.5	1063.4	1065.5	1073.0	1080.7
5°	975.8	981.8	992.2	1001.9	1012.4	1023.2	1031.1	1040.0	1048.2	1062.4	1077.4
7.5°	909.6	917.9	934.1	949.6	967.8	983.1	996.6	1011.9	1025.6	1045.9	1067.1
10°	860.0	874.6	895.9	910.4	934.3	949.6	970.9	987.7	1006.8	1033.7	1057.6
12.5°	817.3	834.9	852.0	872.2	893.7	919.2	942.6	964.1	986.8	1014.6	1042.6
15°	739.8	765.2	791.7	812.2	841.4	868.2	895.5	924.6	952.3	985.5	1022.1
17.5°	640.0	669.4	714.0	749.2	783.4	810.4	844.1	879.4	911.9	952.0	992.7
20°	594.9	616.5	646.8	694.2	745.8	774.5	808.9	847.7	885.0	928.7	972.4
22.5°	558.7	578.0	602.3	639.2	696.8	736.0	771.8	811.3	854.6	899.2	947.6
25°	507.1	520.6	546.0	575.8	615.4	680.0	719.2	758.8	805.9	853.7	908.9
27.5°	468.4	480.5	497.0	525.5	554.9	601.3	663.7	706.8	753.7	807.5	864.9
30°	438.8	453.0	471.3	491.4	523.6	559.8	622.1	672.2	718.5	773.8	835.0
32.5°	417.3	428.5	444.1	464.6	491.3	526.0	575.8	636.6	681.7	740.0	803.9
35°	382.0	395.1	407.8	427.2	448.9	480.6	518.3	583.3	628.1	685.6	749.9
37.5°	353.0	361.0	375.0	390.4	413.2	436.9	469.6	527.9	576.4	632.8	698.6
40°	330.9	340.9	351.4	368.6	387.3	410.0	442.1	485.5	541.1	596.4	660.6
42.5°	309.4	322.1	333.2	344.7	365.1	387.9	414.1	450.8	507.6	559.9	622.4
45°	283.4	291.7	303.2	315.9	332.7	352.2	375.3	407.4	461.9	507.1	565.8
47.5°	253.3	265.3	272.8	285.2	301.2	319.7	341.2	369.0	413.2	455.5	509.9
50°	232.7	245.0	255.8	267.0	281.2	299.1	317.0	343.9	379.4	423.9	474.6
52.5°	215.0	225.9	236.4	247.6	261.5	277.9	294.9	318.5	348.9	389.8	439.1
55°	190.8	197.5	208.4	219.6	231.9	247.6	264.0	283.8	310.0	344.3	384.3
57.5°	166.0	173.8	182.4	193.7	206.1	218.2	232.9	250.9	271.5	302.6	336.8
60°	152.0	158.0	165.1	176.6	188.2	199.0	213.2	228.2	247.6	274.5	303.6
62.5°	136.5	142.1	148.6	158.7	170.0	179.9	192.3	208.2	224.6	249.1	274.6
65°	110.5	118.8	125.1	134.1	143.4	153.9	163.6	176.3	190.8	210.2	233.0
67.5°	91.6	95.8	101.7	109.9	119.4	128.4	137.6	147.5	160.1	175.1	193.2
70°	83.3	84.8	85.9	93.7	102.7	111.7	120.2	129.6	140.4	152.7	168.4
72.5°	73.4	74.9	76.3	79.7	86.9	95.8	104.7	111.7	121.9	132.1	144.8
75°	58.3	60.5	61.6	63.5	66.1	72.1	80.3	87.0	93.0	100.8	110.9
77.5°	44.4	45.6	46.8	48.8	50.4	53.2	57.8	63.9	69.5	74.0	81.0
80°	35.1	35.5	37.0	37.7	40.0	41.8	44.1	48.9	54.5	56.4	61.2
82.5°	26.4	26.8	28.0	28.8	29.8	31.4	34.2	35.5	39.9	42.3	45.4
85°	14.6	14.2	15.3	15.3	16.1	16.8	17.6	19.4	20.5	23.5	24.3
87.5°	6.7	6.6	6.7	6.5	6.3	6.7	6.8	6.8	7.2	7.8	8.8
90°	11.0	10.4	9.5	8.6	7.7	6.7	5.6	4.3	3.1	1.8	0.5
92.5°	12.4	12.1	11.6	11.2	10.7	10.3	10.1	10.2	10.3	10.4	10.5
95°	20.9	20.4	19.5	18.7	17.9	17.1	18.6	22.4	26.3	30.1	33.9
97.5°	27.7	27.2	25.4	23.5	21.6	19.7	24.2	35.0	45.8	56.5	67.3
100°	30.7	29.7	27.8	25.8	23.8	21.9	28.8	44.7	60.6	76.5	92.4
102.5°	31.8	30.6	47.1	63.6	80.1	96.5	106.5	109.8	113.2	116.6	119.9
105°	33.1	31.8	63.5	95.2	126.8	158.5	172.6	169.1	165.6	162.1	158.6
107.5°	43.3	44.6	82.5	120.5	158.5	196.4	214.0	211.2	208.4	205.6	202.8
110°	79.7	91.3	124.8	158.4	191.9	225.4	240.9	238.5	236.1	233.6	231.2



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	188.0	230.4	238.6	246.9	255.2	263.5	266.5	264.4	262.2	260.1	257.9
115°	268.3	322.0	319.1	316.2	313.3	310.4	308.0	306.0	304.0	302.0	300.1
117.5°	343.7	356.6	354.7	352.7	350.7	348.7	346.6	344.4	342.2	340.0	337.8
120°	383.9	382.5	380.4	378.4	376.3	374.2	372.3	370.5	368.8	367.0	365.3
122.5°	408.0	407.2	404.9	402.6	400.3	398.1	396.0	394.2	392.4	390.5	388.7
125°	441.8	441.0	438.8	436.6	434.4	432.2	430.3	428.8	427.3	425.8	424.3
127.5°	472.6	471.5	469.8	468.2	466.5	464.9	463.2	461.5	459.9	458.2	456.5
130°	492.4	491.1	489.8	488.5	487.3	486.0	484.4	482.6	480.7	478.8	477.0
132.5°	511.8	510.7	509.4	508.2	506.9	505.6	504.2	502.6	501.0	499.4	497.9
135°	539.2	538.0	537.0	536.0	534.9	533.9	532.4	530.6	528.7	526.9	525.0
137.5°	564.8	563.6	562.4	561.3	560.1	558.9	557.6	556.3	555.0	553.7	552.5
140°	581.4	580.3	579.0	577.8	576.5	575.2	574.1	573.2	572.3	571.3	570.4
142.5°	596.7	595.8	594.3	592.8	591.4	589.9	588.8	587.9	587.1	586.3	585.4
145°	618.2	617.4	615.4	613.4	611.5	609.5	608.6	608.7	608.8	608.9	609.0
147.5°	637.0	636.4	634.4	632.5	630.5	628.6	627.8	628.3	628.7	629.1	629.6
150°	648.3	647.6	645.8	643.9	642.1	640.2	639.7	640.5	641.3	642.1	642.9
152.5°	658.8	658.1	656.3	654.6	652.8	651.0	650.6	651.5	652.4	653.3	654.2
155°	672.9	672.2	670.8	669.4	668.0	666.6	666.4	667.5	668.5	669.6	670.6
157.5°	684.6	683.9	682.9	681.9	680.9	680.0	679.9	680.8	681.7	682.6	683.4
160°	691.7	691.0	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0
162.5°	698.0	697.2	696.6	696.0	695.4	694.8	694.9	695.5	696.2	696.9	697.6
165°	705.9	705.0	704.7	704.3	704.0	703.7	703.8	704.5	705.2	705.9	706.6
167.5°	712.4	711.6	711.3	711.0	710.6	710.3	710.5	711.2	711.9	712.6	713.3
170°	715.8	715.0	714.7	714.5	714.3	714.0	714.3	715.0	715.7	716.4	717.0
172.5°	718.3	717.5	717.2	717.0	716.8	716.5	716.8	717.5	718.2	718.9	719.6
175°	721.0	720.2	719.9	719.7	719.5	719.3	719.5	720.4	721.2	722.0	722.8
177.5°	721.5	720.8	720.7	720.6	720.5	720.4	720.7	721.4	722.0	722.7	723.3
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1081.0	1081.9	1087.9	1090.6	1096.0	1098.1	1100.4	1099.8	1099.8	1101.0	1109.4
5°	1083.3	1090.8	1102.0	1112.8	1123.3	1132.3	1138.2	1144.2	1146.4	1157.3	1167.0
7.5°	1079.5	1093.2	1111.7	1128.2	1148.0	1163.5	1176.3	1187.9	1195.8	1211.6	1227.7
10°	1074.4	1093.8	1114.7	1136.0	1163.3	1183.8	1204.7	1220.8	1226.0	1249.5	1263.0
12.5°	1064.2	1090.2	1116.8	1144.4	1171.0	1199.3	1222.3	1238.4	1256.8	1277.9	1302.7
15°	1049.0	1078.9	1113.6	1149.1	1187.2	1221.5	1246.2	1274.2	1294.3	1317.5	1339.1
17.5°	1027.1	1065.6	1109.7	1150.8	1194.8	1231.7	1265.7	1292.5	1306.7	1319.9	1323.2
20°	1009.8	1051.2	1103.1	1151.7	1195.7	1238.3	1271.9	1294.3	1298.1	1298.4	1278.6
22.5°	991.0	1037.8	1092.1	1141.8	1194.5	1241.9	1268.0	1277.6	1262.8	1237.5	1199.2
25°	956.4	1010.5	1073.6	1130.4	1187.9	1232.7	1241.7	1224.9	1173.0	1118.4	1049.4
27.5°	918.9	979.7	1047.4	1110.5	1171.8	1199.6	1180.2	1119.6	1026.1	944.9	846.4
30°	891.4	959.7	1026.2	1096.8	1153.5	1165.5	1121.1	1031.8	922.8	800.3	702.1
32.5°	860.0	931.6	1004.7	1077.7	1125.2	1113.5	1040.1	930.2	802.4	682.0	589.1
35°	815.2	889.2	967.9	1041.1	1071.4	1021.0	911.2	768.2	637.5	525.1	461.2
37.5°	763.5	844.0	925.9	993.1	991.0	906.9	757.4	609.7	499.9	433.4	387.9
40°	726.7	808.1	896.6	953.4	929.1	819.7	657.6	518.3	438.0	385.0	351.8
42.5°	691.5	773.2	861.1	906.2	864.0	729.5	568.0	458.9	392.6	351.3	324.3
45°	631.5	717.7	799.2	824.2	748.7	600.5	459.3	380.2	336.1	305.5	286.8
47.5°	572.9	657.7	732.0	732.5	630.4	487.0	387.5	329.0	291.4	267.7	254.1
50°	537.0	617.7	680.0	670.3	554.6	433.2	346.5	296.1	264.8	246.5	232.3
52.5°	496.7	574.9	628.9	601.3	490.3	381.2	309.8	267.5	241.5	225.6	212.9
55°	438.0	507.5	545.6	503.8	400.0	317.0	261.8	228.5	209.1	195.7	184.9
57.5°	380.5	437.7	461.7	413.0	329.4	262.9	221.4	196.5	177.2	167.6	162.0
60°	344.3	393.2	410.0	356.3	286.4	230.0	196.1	172.9	158.7	152.4	146.8
62.5°	308.8	348.7	355.7	306.4	249.7	201.4	172.2	152.6	143.2	137.1	131.8
65°	256.2	284.9	281.6	242.0	197.5	159.8	138.5	126.6	119.5	110.9	101.6
67.5°	210.9	228.5	217.9	188.2	150.8	124.2	110.3	101.3	92.5	84.3	82.2
70°	182.2	192.3	181.1	153.9	123.6	104.2	93.0	82.2	76.9	75.1	71.7
72.5°	154.8	158.3	146.2	122.8	100.6	86.3	75.4	69.3	66.5	64.9	62.7
75°	116.1	113.5	103.1	84.8	69.8	60.1	56.8	54.5	52.7	51.2	50.0
77.5°	81.6	77.7	68.4	56.5	48.6	44.0	42.0	40.8	39.9	39.1	38.0
80°	61.2	58.6	49.3	40.3	37.0	34.7	33.6	32.1	32.1	31.4	30.2
82.5°	44.8	41.9	33.8	29.6	27.7	26.4	25.5	24.6	24.3	24.5	23.7
85°	23.5	19.0	16.8	16.1	14.9	14.2	14.6	13.8	13.8	13.8	13.4
87.5°	7.5	6.3	6.2	6.2	6.7	6.9	6.8	7.0	7.5	7.3	7.7
90°	1.8	3.1	4.3	5.6	6.7	7.7	8.6	9.5	10.4	11.0	11.6
92.5°	10.4	10.3	10.2	10.1	10.3	10.7	11.2	11.6	12.1	12.4	12.7
95°	30.1	26.3	22.4	18.6	17.1	17.9	18.7	19.5	20.4	20.9	21.5
97.5°	56.5	45.8	35.0	24.2	19.7	21.6	23.5	25.4	27.2	27.7	28.2
100°	76.5	60.6	44.7	28.8	21.9	23.8	25.8	27.8	29.7	30.7	31.6
102.5°	116.6	113.2	109.8	106.5	96.5	80.1	63.6	47.1	30.6	31.8	33.0
105°	162.1	165.6	169.1	172.6	158.5	126.8	95.2	63.5	31.8	33.1	34.4
107.5°	205.6	208.4	211.2	214.0	196.4	158.5	120.5	82.5	44.6	43.3	42.0
110°	233.6	236.1	238.5	240.9	225.4	191.9	158.4	124.8	91.3	79.7	68.1



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	260.1	262.2	264.4	266.5	263.5	255.2	246.9	238.6	230.4	188.0	145.7
115°	302.0	304.0	306.0	308.0	310.4	313.3	316.2	319.1	322.0	268.3	214.6
117.5°	340.0	342.2	344.4	346.6	348.7	350.7	352.7	354.7	356.6	343.7	330.7
120°	367.0	368.8	370.5	372.3	374.2	376.3	378.4	380.4	382.5	383.9	385.3
122.5°	390.5	392.4	394.2	396.0	398.1	400.3	402.6	404.9	407.2	408.0	408.8
125°	425.8	427.3	428.8	430.3	432.2	434.4	436.6	438.8	441.0	441.8	442.6
127.5°	458.2	459.9	461.5	463.2	464.9	466.5	468.2	469.8	471.5	472.6	473.8
130°	478.8	480.7	482.6	484.4	486.0	487.3	488.5	489.8	491.1	492.4	493.6
132.5°	499.4	501.0	502.6	504.2	505.6	506.9	508.2	509.4	510.7	511.8	512.9
135°	526.9	528.7	530.6	532.4	533.9	534.9	536.0	537.0	538.0	539.2	540.4
137.5°	553.7	555.0	556.3	557.6	558.9	560.1	561.3	562.4	563.6	564.8	565.9
140°	571.3	572.3	573.2	574.1	575.2	576.5	577.8	579.0	580.3	581.4	582.4
142.5°	586.3	587.1	587.9	588.8	589.9	591.4	592.8	594.3	595.8	596.7	597.7
145°	608.9	608.8	608.7	608.6	609.5	611.5	613.4	615.4	617.4	618.2	619.0
147.5°	629.1	628.7	628.3	627.8	628.6	630.5	632.5	634.4	636.4	637.0	637.6
150°	642.1	641.3	640.5	639.7	640.2	642.1	643.9	645.8	647.6	648.3	649.0
152.5°	653.3	652.4	651.5	650.6	651.0	652.8	654.6	656.3	658.1	658.8	659.5
155°	669.6	668.5	667.5	666.4	666.6	668.0	669.4	670.8	672.2	672.9	673.6
157.5°	682.6	681.7	680.8	679.9	680.0	680.9	681.9	682.9	683.9	684.6	685.4
160°	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	691.7	692.3
162.5°	696.9	696.2	695.5	694.9	694.8	695.4	696.0	696.6	697.2	698.0	698.8
165°	705.9	705.2	704.5	703.8	703.7	704.0	704.3	704.7	705.0	705.9	706.7
167.5°	712.6	711.9	711.2	710.5	710.3	710.6	711.0	711.3	711.6	712.4	713.2
170°	716.4	715.7	715.0	714.3	714.0	714.3	714.5	714.7	715.0	715.8	716.6
172.5°	718.9	718.2	717.5	716.8	716.5	716.8	717.0	717.2	717.5	718.3	719.1
175°	722.0	721.2	720.4	719.5	719.3	719.5	719.7	719.9	720.2	721.0	721.8
177.5°	722.7	722.0	721.4	720.7	720.4	720.5	720.6	720.7	720.8	721.5	722.1
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1112.4	1116.3	1118.1	1118.1	1120.2	1119.3	1118.4
5°	1176.3	1183.4	1184.9	1191.6	1196.5	1195.0	1195.7
7.5°	1239.9	1251.3	1262.6	1267.7	1268.6	1271.6	1272.7
10°	1279.0	1288.4	1305.9	1303.3	1316.4	1323.8	1311.5
12.5°	1316.7	1329.3	1341.5	1344.8	1352.2	1354.6	1349.7
15°	1350.7	1357.4	1358.2	1356.3	1358.6	1356.7	1349.6
17.5°	1318.9	1308.0	1285.9	1275.4	1267.1	1254.9	1250.0
20°	1266.3	1234.2	1196.9	1181.9	1164.4	1130.0	1138.2
22.5°	1152.8	1116.2	1078.9	1035.2	1014.4	981.8	979.9
25°	976.2	913.1	843.6	795.0	766.7	734.2	720.0
27.5°	759.0	679.5	622.6	593.8	567.5	541.8	540.7
30°	616.2	556.4	512.4	487.7	471.7	460.8	463.1
32.5°	519.4	478.4	448.7	428.3	416.4	408.2	408.1
35°	424.6	396.6	377.5	369.0	360.4	354.4	354.8
37.5°	363.4	346.5	335.9	326.5	321.1	318.2	316.5
40°	332.0	318.2	310.0	304.4	299.9	295.8	295.0
42.5°	307.2	295.8	287.5	283.1	279.0	276.0	275.3
45°	272.6	263.3	255.8	250.9	249.1	246.5	246.5
47.5°	242.5	233.3	227.5	224.4	221.2	219.5	219.4
50°	222.2	215.1	209.9	208.0	205.4	204.3	203.9
52.5°	204.0	198.7	194.9	193.7	192.5	191.1	191.3
55°	179.2	176.3	174.8	173.6	171.8	169.5	171.0
57.5°	158.4	155.9	151.8	148.3	146.6	145.0	145.6
60°	143.8	138.5	133.3	129.2	128.1	124.7	124.7
62.5°	125.3	117.9	111.5	109.2	108.1	106.5	106.2
65°	96.3	93.4	91.9	90.4	89.6	89.6	88.9
67.5°	79.8	78.6	77.0	76.6	75.9	75.7	75.4
70°	70.6	69.1	68.3	68.0	67.2	67.6	66.5
72.5°	61.6	60.4	60.3	59.3	58.9	58.9	58.1
75°	48.5	48.5	48.2	47.8	47.1	46.7	47.1
77.5°	37.3	37.4	36.7	36.7	36.6	36.7	36.3
80°	29.9	30.2	29.9	29.5	29.1	29.5	29.1
82.5°	23.6	23.1	23.0	22.9	22.9	22.6	22.6
85°	13.4	13.8	13.4	13.1	13.1	13.1	13.4
87.5°	7.5	7.6	7.7	7.8	7.8	7.9	7.6
90°	12.2	12.8	13.2	13.4	13.6	13.9	14.1
92.5°	13.0	13.3	13.5	13.7	13.8	14.0	14.1
95°	22.1	22.7	22.9	22.8	22.7	22.6	22.4
97.5°	28.6	29.1	29.4	29.5	29.7	29.8	30.0
100°	32.5	33.5	34.0	34.3	34.5	34.7	35.0
102.5°	34.2	35.4	36.2	36.5	36.8	37.1	37.5
105°	35.7	36.9	37.8	38.3	38.7	39.2	39.7
107.5°	40.7	39.4	39.0	39.4	39.9	40.3	40.8
110°	56.5	44.9	39.4	39.8	40.3	40.8	41.2



TEST NUMBER: P331651

CATALOG NUMBER: SA2XXRDIP-C485D530U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	103.4	61.1	40.2	40.5	40.9	41.3	41.6
115°	160.9	107.2	76.2	67.8	59.5	51.1	42.8
117.5°	317.7	304.7	284.5	257.0	229.6	202.2	174.7
120°	386.7	388.1	381.0	365.3	349.7	334.0	318.3
122.5°	409.7	410.5	409.4	406.4	403.3	400.3	397.2
125°	443.4	444.2	444.8	445.2	445.5	445.9	446.2
127.5°	475.0	476.2	476.8	476.9	477.0	477.0	477.1
130°	494.9	496.2	496.8	496.6	496.5	496.4	496.3
132.5°	514.0	515.1	515.5	515.4	515.3	515.2	515.1
135°	541.5	542.7	543.2	542.9	542.7	542.5	542.2
137.5°	567.0	568.2	568.5	568.1	567.7	567.4	567.0
140°	583.4	584.5	584.7	584.1	583.6	583.0	582.4
142.5°	598.6	599.6	599.8	599.2	598.6	598.0	597.4
145°	619.8	620.6	620.7	620.2	619.6	619.0	618.4
147.5°	638.2	638.8	638.8	638.4	637.9	637.4	636.9
150°	649.7	650.4	650.5	649.9	649.3	648.7	648.2
152.5°	660.2	660.9	660.8	660.1	659.3	658.5	657.8
155°	674.3	675.0	674.8	673.9	673.0	672.1	671.1
157.5°	686.2	687.0	687.0	686.0	685.1	684.2	683.3
160°	693.0	693.7	693.7	692.9	692.1	691.2	690.4
162.5°	699.6	700.4	700.3	699.3	698.3	697.3	696.3
165°	707.5	708.3	708.3	707.5	706.7	705.9	705.0
167.5°	714.1	714.9	714.8	713.7	712.7	711.6	710.6
170°	717.4	718.2	718.1	717.0	716.0	715.0	713.9
172.5°	719.9	720.7	720.6	719.6	718.5	717.5	716.4
175°	722.6	723.4	723.3	722.1	720.9	719.8	718.6
177.5°	722.8	723.4	723.3	722.5	721.6	720.8	720.0
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2

(END OF REPORT)