

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331366-940

Luminaire Tested: **SA2XXDIP-C675D1080U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331366-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6455.4 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331366-940
CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41				41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41	35				35
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30				30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26				26
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	22				22
5	68	57	49	43	61	52	45	40	43	38	34	35	32	29	28	25	23	20				20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18				18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	22	23	20	18	16				16
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14				14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				13
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	1.7
10°-20°	327.9	5.1
20°-30°	475.9	7.4
30°-40°	502.2	7.8
40°-50°	444.7	6.9
50°-60°	354.9	5.5
60°-70°	241.2	3.7
70°-80°	123.7	1.9
80°-90°	33.0	0.5
90°-100°	43.7	0.7
100°-110°	160.2	2.5
110°-120°	428.4	6.6
120°-130°	707.1	11.0
130°-140°	752.0	11.6
140°-150°	699.0	10.8
150°-160°	562.0	8.7
160°-170°	362.1	5.6
170°-180°	124.6	1.9
0°-30°	916.7	14.2
0°-40°	1418.9	22.0
0°-60°	2218.4	34.4
0°-90°	2616.3	40.5
90°-120°	632.3	9.8
90°-150°	2790.4	43.2
90°-180°	3839.0	59.5
0°-180°	6455.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	28
90°	26	1	26	1	26	13
95°	41	62	41	62	41	38
105°	72	288	72	288	72	75
115°	78	545	78	545	78	195
125°	810	771	810	771	810	701
135°	985	954	985	954	985	759
145°	1123	1106	1123	1106	1123	702
155°	1219	1218	1219	1218	1219	563
165°	1281	1284	1281	1284	1281	362
175°	1305	1313	1305	1313	1305	124
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	14.6	14.5	14.8	14.4	14.3	14.4	14.3	13.6	13.8	14.0	14.0
90°	25.6	25.1	24.8	24.3	23.9	23.2	22.1	21.0	20.0	19.0	17.3
92.5°	25.6	25.3	25.1	24.9	24.6	24.2	23.6	23.1	22.6	22.0	21.1
95°	40.8	40.9	41.2	41.4	41.6	41.2	40.1	39.1	38.0	37.0	35.5
97.5°	54.4	54.1	53.9	53.7	53.4	52.9	52.0	51.2	50.3	49.5	46.1
100°	63.5	63.1	62.7	62.2	61.8	60.8	59.1	57.4	55.7	54.0	50.5
102.5°	68.0	67.5	66.9	66.3	65.7	64.3	62.2	59.9	57.8	55.6	85.5
105°	72.1	71.2	70.4	69.6	68.7	67.1	64.7	62.4	60.1	57.8	115.3
107.5°	74.1	73.3	72.4	71.6	70.8	71.5	73.8	76.2	78.6	81.0	149.9
110°	74.9	74.0	73.2	72.3	71.5	81.6	102.7	123.8	144.8	165.9	226.8



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	75.6	75.0	74.3	73.7	72.9	111.0	187.9	264.7	341.6	418.4	433.5
115°	77.8	92.9	108.1	123.2	138.4	194.7	292.3	389.8	487.3	584.9	579.6
117.5°	317.4	367.2	417.1	466.9	516.7	553.5	577.0	600.7	624.2	647.8	644.2
120°	578.3	606.6	635.1	663.5	692.0	705.0	702.4	699.9	697.3	694.8	691.1
122.5°	721.6	727.1	732.6	738.2	743.6	745.6	744.1	742.6	741.1	739.6	735.5
125°	810.5	809.9	809.2	808.6	808.0	806.9	805.4	804.0	802.5	801.0	797.0
127.5°	866.6	866.5	866.4	866.2	866.1	865.0	862.8	860.7	858.5	856.4	853.4
130°	901.5	901.7	901.9	902.1	902.3	901.3	898.9	896.6	894.3	892.0	889.7
132.5°	935.6	935.9	936.0	936.2	936.5	935.6	933.6	931.6	929.6	927.6	925.3
135°	984.9	985.3	985.7	986.1	986.6	985.7	983.6	981.5	979.5	977.3	975.4
137.5°	1029.8	1030.6	1031.3	1032.0	1032.7	1032.0	1029.9	1027.9	1025.8	1023.8	1021.6
140°	1057.9	1058.9	1060.0	1061.0	1062.1	1061.7	1059.8	1057.9	1056.0	1054.1	1051.8
142.5°	1085.2	1086.3	1087.3	1088.3	1089.4	1089.0	1087.4	1085.6	1083.9	1082.2	1079.5
145°	1123.3	1124.4	1125.4	1126.5	1127.5	1127.3	1125.8	1124.4	1122.8	1121.4	1117.8
147.5°	1156.8	1157.7	1158.6	1159.5	1160.4	1160.3	1159.2	1158.1	1157.0	1155.9	1152.4
150°	1177.3	1178.4	1179.5	1180.4	1181.5	1181.4	1180.2	1178.9	1177.7	1176.3	1173.0
152.5°	1194.8	1196.1	1197.6	1198.9	1200.3	1200.4	1199.2	1197.8	1196.6	1195.3	1192.1
155°	1219.1	1220.8	1222.4	1224.1	1225.7	1226.0	1224.8	1223.4	1222.2	1220.9	1218.4
157.5°	1241.2	1242.9	1244.5	1246.2	1247.8	1247.9	1246.4	1245.0	1243.6	1242.2	1240.4
160°	1254.1	1255.6	1257.0	1258.6	1260.0	1260.1	1258.8	1257.6	1256.3	1255.1	1253.8
162.5°	1264.7	1266.5	1268.4	1270.2	1271.9	1272.2	1270.7	1269.3	1267.8	1266.4	1265.3
165°	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7	1280.1
167.5°	1290.7	1292.6	1294.5	1296.4	1298.2	1298.5	1297.0	1295.6	1294.1	1292.6	1292.0
170°	1296.7	1298.7	1300.6	1302.4	1304.3	1304.6	1303.1	1301.6	1300.1	1298.7	1298.2
172.5°	1301.3	1303.2	1305.1	1307.0	1308.9	1309.1	1307.6	1306.2	1304.7	1303.2	1302.8
175°	1305.3	1307.4	1309.5	1311.6	1313.8	1314.0	1312.6	1311.1	1309.7	1308.1	1307.7
177.5°	1307.8	1309.3	1310.8	1312.3	1313.8	1314.0	1312.8	1311.6	1310.5	1309.3	1309.1
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	14.0	13.7	13.4	13.7	12.1	11.7	9.7	8.2	8.3	8.4	8.1
90°	15.6	13.9	12.2	10.3	7.9	5.6	3.3	1.0	3.3	5.6	7.9
92.5°	20.3	19.4	18.6	18.3	18.5	18.7	18.9	19.2	18.9	18.7	18.5
95°	34.1	32.5	31.0	33.8	40.8	47.7	54.7	61.6	54.7	47.7	40.8
97.5°	42.6	39.2	35.8	44.0	63.5	83.1	102.7	122.3	102.7	83.1	63.5
100°	46.9	43.2	39.7	52.3	81.2	110.0	138.9	167.8	138.9	110.0	81.2
102.5°	115.5	145.4	175.4	193.4	199.5	205.6	211.7	217.8	211.7	205.6	199.5
105°	172.8	230.3	287.8	313.4	307.1	300.8	294.5	288.2	294.5	300.8	307.1
107.5°	218.9	287.8	356.9	388.8	383.6	378.5	373.4	368.4	373.4	378.5	383.6
110°	287.7	348.5	409.4	437.7	433.2	428.8	424.4	419.9	424.4	428.8	433.2



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	448.5	463.5	478.6	484.1	480.2	476.3	472.4	468.5	472.4	476.3	480.2
115°	574.4	569.1	563.8	559.4	555.8	552.2	548.7	545.1	548.7	552.2	555.8
117.5°	640.6	636.9	633.3	629.5	625.5	621.5	617.5	613.5	617.5	621.5	625.5
120°	687.2	683.5	679.7	676.2	673.1	669.9	666.7	663.5	666.7	669.9	673.1
122.5°	731.3	727.2	723.1	719.3	716.0	712.7	709.4	706.1	709.4	712.7	716.0
125°	793.0	789.0	785.0	781.6	778.9	776.1	773.4	770.7	773.4	776.1	778.9
127.5°	850.3	847.4	844.4	841.4	838.4	835.4	832.3	829.3	832.3	835.4	838.4
130°	887.3	885.0	882.7	879.9	876.6	873.2	869.8	866.4	869.8	873.2	876.6
132.5°	923.0	920.7	918.4	915.8	912.9	910.1	907.2	904.3	907.2	910.1	912.9
135°	973.5	971.6	969.7	967.1	963.8	960.4	957.0	953.6	957.0	960.4	963.8
137.5°	1019.5	1017.4	1015.1	1012.9	1010.6	1008.2	1005.8	1003.4	1005.8	1008.2	1010.6
140°	1049.5	1047.1	1044.8	1042.9	1041.2	1039.5	1037.8	1036.1	1037.8	1039.5	1041.2
142.5°	1076.8	1074.2	1071.6	1069.4	1067.9	1066.4	1064.9	1063.4	1064.9	1066.4	1067.9
145°	1114.2	1110.6	1107.1	1105.4	1105.6	1105.8	1106.0	1106.3	1106.0	1105.8	1105.6
147.5°	1148.8	1145.3	1141.7	1140.4	1141.2	1142.0	1142.8	1143.6	1142.8	1142.0	1141.2
150°	1169.7	1166.3	1162.9	1162.0	1163.4	1164.9	1166.4	1167.9	1166.4	1164.9	1163.4
152.5°	1188.9	1185.7	1182.5	1181.8	1183.4	1185.0	1186.7	1188.3	1186.7	1185.0	1183.4
155°	1215.8	1213.4	1210.9	1210.5	1212.4	1214.3	1216.2	1218.1	1216.2	1214.3	1212.4
157.5°	1238.6	1236.9	1235.1	1235.0	1236.6	1238.2	1239.8	1241.4	1239.8	1238.2	1236.6
160°	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1253.8	1252.5	1251.2
162.5°	1264.3	1263.1	1262.0	1262.1	1263.4	1264.6	1266.0	1267.2	1266.0	1264.6	1263.4
165°	1279.4	1278.7	1278.1	1278.4	1279.7	1280.9	1282.2	1283.5	1282.2	1280.9	1279.7
167.5°	1291.4	1290.8	1290.2	1290.6	1291.8	1293.1	1294.4	1295.7	1294.4	1293.1	1291.8
170°	1297.8	1297.4	1297.0	1297.4	1298.7	1299.9	1301.2	1302.4	1301.2	1299.9	1298.7
172.5°	1302.3	1302.0	1301.5	1302.0	1303.2	1304.5	1305.7	1307.0	1305.7	1304.5	1303.2
175°	1307.3	1306.9	1306.4	1307.0	1308.5	1309.9	1311.4	1312.9	1311.4	1309.9	1308.5
177.5°	1308.9	1308.8	1308.6	1309.1	1310.3	1311.4	1312.7	1313.8	1312.7	1311.4	1310.3
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	8.2	8.3	8.2	8.6	8.6	8.6	8.4	8.6	8.8	8.3	8.4
90°	10.3	12.2	13.9	15.6	17.3	19.0	20.0	21.0	22.1	23.2	23.9
92.5°	18.3	18.6	19.4	20.3	21.1	22.0	22.6	23.1	23.6	24.2	24.6
95°	33.8	31.0	32.5	34.1	35.5	37.0	38.0	39.1	40.1	41.2	41.6
97.5°	44.0	35.8	39.2	42.6	46.1	49.5	50.3	51.2	52.0	52.9	53.4
100°	52.3	39.7	43.2	46.9	50.5	54.0	55.7	57.4	59.1	60.8	61.8
102.5°	193.4	175.4	145.4	115.5	85.5	55.6	57.8	59.9	62.2	64.3	65.7
105°	313.4	287.8	230.3	172.8	115.3	57.8	60.1	62.4	64.7	67.1	68.7
107.5°	388.8	356.9	287.8	218.9	149.9	81.0	78.6	76.2	73.8	71.5	70.8
110°	437.7	409.4	348.5	287.7	226.8	165.9	144.8	123.8	102.7	81.6	71.5



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	484.1	478.6	463.5	448.5	433.5	418.4	341.6	264.7	187.9	111.0	72.9
115°	559.4	563.8	569.1	574.4	579.6	584.9	487.3	389.8	292.3	194.7	138.4
117.5°	629.5	633.3	636.9	640.6	644.2	647.8	624.2	600.7	577.0	553.5	516.7
120°	676.2	679.7	683.5	687.2	691.1	694.8	697.3	699.9	702.4	705.0	692.0
122.5°	719.3	723.1	727.2	731.3	735.5	739.6	741.1	742.6	744.1	745.6	743.6
125°	781.6	785.0	789.0	793.0	797.0	801.0	802.5	804.0	805.4	806.9	808.0
127.5°	841.4	844.4	847.4	850.3	853.4	856.4	858.5	860.7	862.8	865.0	866.1
130°	879.9	882.7	885.0	887.3	889.7	892.0	894.3	896.6	898.9	901.3	902.3
132.5°	915.8	918.4	920.7	923.0	925.3	927.6	929.6	931.6	933.6	935.6	936.5
135°	967.1	969.7	971.6	973.5	975.4	977.3	979.5	981.5	983.6	985.7	986.6
137.5°	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8	1027.9	1029.9	1032.0	1032.7
140°	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0	1057.9	1059.8	1061.7	1062.1
142.5°	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9	1085.6	1087.4	1089.0	1089.4
145°	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8	1124.4	1125.8	1127.3	1127.5
147.5°	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0	1158.1	1159.2	1160.3	1160.4
150°	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7	1178.9	1180.2	1181.4	1181.5
152.5°	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6	1197.8	1199.2	1200.4	1200.3
155°	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2	1223.4	1224.8	1226.0	1225.7
157.5°	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6	1245.0	1246.4	1247.9	1247.8
160°	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3	1257.6	1258.8	1260.1	1260.0
162.5°	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8	1269.3	1270.7	1272.2	1271.9
165°	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6
167.5°	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1	1295.6	1297.0	1298.5	1298.2
170°	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1	1301.6	1303.1	1304.6	1304.3
172.5°	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7	1306.2	1307.6	1309.1	1308.9
175°	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7	1311.1	1312.6	1314.0	1313.8
177.5°	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5	1311.6	1312.8	1314.0	1313.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	8.5	8.2	8.3	8.0	8.3	8.2	8.5	8.4	8.3	8.8	8.6
90°	24.3	24.8	25.1	25.6	25.1	24.8	24.3	23.9	23.2	22.1	21.0
92.5°	24.9	25.1	25.3	25.6	25.3	25.1	24.9	24.6	24.2	23.6	23.1
95°	41.4	41.2	40.9	40.8	40.9	41.2	41.4	41.6	41.2	40.1	39.1
97.5°	53.7	53.9	54.1	54.4	54.1	53.9	53.7	53.4	52.9	52.0	51.2
100°	62.2	62.7	63.1	63.5	63.1	62.7	62.2	61.8	60.8	59.1	57.4
102.5°	66.3	66.9	67.5	68.0	67.5	66.9	66.3	65.7	64.3	62.2	59.9
105°	69.6	70.4	71.2	72.1	71.2	70.4	69.6	68.7	67.1	64.7	62.4
107.5°	71.6	72.4	73.3	74.1	73.3	72.4	71.6	70.8	71.5	73.8	76.2
110°	72.3	73.2	74.0	74.9	74.0	73.2	72.3	71.5	81.6	102.7	123.8



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	73.7	74.3	75.0	75.6	75.0	74.3	73.7	72.9	111.0	187.9	264.7
115°	123.2	108.1	92.9	77.8	92.9	108.1	123.2	138.4	194.7	292.3	389.8
117.5°	466.9	417.1	367.2	317.4	367.2	417.1	466.9	516.7	553.5	577.0	600.7
120°	663.5	635.1	606.6	578.3	606.6	635.1	663.5	692.0	705.0	702.4	699.9
122.5°	738.2	732.6	727.1	721.6	727.1	732.6	738.2	743.6	745.6	744.1	742.6
125°	808.6	809.2	809.9	810.5	809.9	809.2	808.6	808.0	806.9	805.4	804.0
127.5°	866.2	866.4	866.5	866.6	866.5	866.4	866.2	866.1	865.0	862.8	860.7
130°	902.1	901.9	901.7	901.5	901.7	901.9	902.1	902.3	901.3	898.9	896.6
132.5°	936.2	936.0	935.9	935.6	935.9	936.0	936.2	936.5	935.6	933.6	931.6
135°	986.1	985.7	985.3	984.9	985.3	985.7	986.1	986.6	985.7	983.6	981.5
137.5°	1032.0	1031.3	1030.6	1029.8	1030.6	1031.3	1032.0	1032.7	1032.0	1029.9	1027.9
140°	1061.0	1060.0	1058.9	1057.9	1058.9	1060.0	1061.0	1062.1	1061.7	1059.8	1057.9
142.5°	1088.3	1087.3	1086.3	1085.2	1086.3	1087.3	1088.3	1089.4	1089.0	1087.4	1085.6
145°	1126.5	1125.4	1124.4	1123.3	1124.4	1125.4	1126.5	1127.5	1127.3	1125.8	1124.4
147.5°	1159.5	1158.6	1157.7	1156.8	1157.7	1158.6	1159.5	1160.4	1160.3	1159.2	1158.1
150°	1180.4	1179.5	1178.4	1177.3	1178.4	1179.5	1180.4	1181.5	1181.4	1180.2	1178.9
152.5°	1198.9	1197.6	1196.1	1194.8	1196.1	1197.6	1198.9	1200.3	1200.4	1199.2	1197.8
155°	1224.1	1222.4	1220.8	1219.1	1220.8	1222.4	1224.1	1225.7	1226.0	1224.8	1223.4
157.5°	1246.2	1244.5	1242.9	1241.2	1242.9	1244.5	1246.2	1247.8	1247.9	1246.4	1245.0
160°	1258.6	1257.0	1255.6	1254.1	1255.6	1257.0	1258.6	1260.0	1260.1	1258.8	1257.6
162.5°	1270.2	1268.4	1266.5	1264.7	1266.5	1268.4	1270.2	1271.9	1272.2	1270.7	1269.3
165°	1285.0	1283.6	1282.1	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6
167.5°	1296.4	1294.5	1292.6	1290.7	1292.6	1294.5	1296.4	1298.2	1298.5	1297.0	1295.6
170°	1302.4	1300.6	1298.7	1296.7	1298.7	1300.6	1302.4	1304.3	1304.6	1303.1	1301.6
172.5°	1307.0	1305.1	1303.2	1301.3	1303.2	1305.1	1307.0	1308.9	1309.1	1307.6	1306.2
175°	1311.6	1309.5	1307.4	1305.3	1307.4	1309.5	1311.6	1313.8	1314.0	1312.6	1311.1
177.5°	1312.3	1310.8	1309.3	1307.8	1309.3	1310.8	1312.3	1313.8	1314.0	1312.8	1311.6
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331366-940
 CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	8.4	8.6	8.6	8.6	8.2	8.3	8.2	8.1	8.4	8.3	8.2
90°	20.0	19.0	17.3	15.6	13.9	12.2	10.3	7.9	5.6	3.3	1.0
92.5°	22.6	22.0	21.1	20.3	19.4	18.6	18.3	18.5	18.7	18.9	19.2
95°	38.0	37.0	35.5	34.1	32.5	31.0	33.8	40.8	47.7	54.7	61.6
97.5°	50.3	49.5	46.1	42.6	39.2	35.8	44.0	63.5	83.1	102.7	122.3
100°	55.7	54.0	50.5	46.9	43.2	39.7	52.3	81.2	110.0	138.9	167.8
102.5°	57.8	55.6	85.5	115.5	145.4	175.4	193.4	199.5	205.6	211.7	217.8
105°	60.1	57.8	115.3	172.8	230.3	287.8	313.4	307.1	300.8	294.5	288.2
107.5°	78.6	81.0	149.9	218.9	287.8	356.9	388.8	383.6	378.5	373.4	368.4
110°	144.8	165.9	226.8	287.7	348.5	409.4	437.7	433.2	428.8	424.4	419.9



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	341.6	418.4	433.5	448.5	463.5	478.6	484.1	480.2	476.3	472.4	468.5
115°	487.3	584.9	579.6	574.4	569.1	563.8	559.4	555.8	552.2	548.7	545.1
117.5°	624.2	647.8	644.2	640.6	636.9	633.3	629.5	625.5	621.5	617.5	613.5
120°	697.3	694.8	691.1	687.2	683.5	679.7	676.2	673.1	669.9	666.7	663.5
122.5°	741.1	739.6	735.5	731.3	727.2	723.1	719.3	716.0	712.7	709.4	706.1
125°	802.5	801.0	797.0	793.0	789.0	785.0	781.6	778.9	776.1	773.4	770.7
127.5°	858.5	856.4	853.4	850.3	847.4	844.4	841.4	838.4	835.4	832.3	829.3
130°	894.3	892.0	889.7	887.3	885.0	882.7	879.9	876.6	873.2	869.8	866.4
132.5°	929.6	927.6	925.3	923.0	920.7	918.4	915.8	912.9	910.1	907.2	904.3
135°	979.5	977.3	975.4	973.5	971.6	969.7	967.1	963.8	960.4	957.0	953.6
137.5°	1025.8	1023.8	1021.6	1019.5	1017.4	1015.1	1012.9	1010.6	1008.2	1005.8	1003.4
140°	1056.0	1054.1	1051.8	1049.5	1047.1	1044.8	1042.9	1041.2	1039.5	1037.8	1036.1
142.5°	1083.9	1082.2	1079.5	1076.8	1074.2	1071.6	1069.4	1067.9	1066.4	1064.9	1063.4
145°	1122.8	1121.4	1117.8	1114.2	1110.6	1107.1	1105.4	1105.6	1105.8	1106.0	1106.3
147.5°	1157.0	1155.9	1152.4	1148.8	1145.3	1141.7	1140.4	1141.2	1142.0	1142.8	1143.6
150°	1177.7	1176.3	1173.0	1169.7	1166.3	1162.9	1162.0	1163.4	1164.9	1166.4	1167.9
152.5°	1196.6	1195.3	1192.1	1188.9	1185.7	1182.5	1181.8	1183.4	1185.0	1186.7	1188.3
155°	1222.2	1220.9	1218.4	1215.8	1213.4	1210.9	1210.5	1212.4	1214.3	1216.2	1218.1
157.5°	1243.6	1242.2	1240.4	1238.6	1236.9	1235.1	1235.0	1236.6	1238.2	1239.8	1241.4
160°	1256.3	1255.1	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1
162.5°	1267.8	1266.4	1265.3	1264.3	1263.1	1262.0	1262.1	1263.4	1264.6	1266.0	1267.2
165°	1282.1	1280.7	1280.1	1279.4	1278.7	1278.1	1278.4	1279.7	1280.9	1282.2	1283.5
167.5°	1294.1	1292.6	1292.0	1291.4	1290.8	1290.2	1290.6	1291.8	1293.1	1294.4	1295.7
170°	1300.1	1298.7	1298.2	1297.8	1297.4	1297.0	1297.4	1298.7	1299.9	1301.2	1302.4
172.5°	1304.7	1303.2	1302.8	1302.3	1302.0	1301.5	1302.0	1303.2	1304.5	1305.7	1307.0
175°	1309.7	1308.1	1307.7	1307.3	1306.9	1306.4	1307.0	1308.5	1309.9	1311.4	1312.9
177.5°	1310.5	1309.3	1309.1	1308.9	1308.8	1308.6	1309.1	1310.3	1311.4	1312.7	1313.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	9.7	11.7	12.1	13.7	13.4	13.7	14.0	14.0	14.0	13.8	13.6
90°	3.3	5.6	7.9	10.3	12.2	13.9	15.6	17.3	19.0	20.0	21.0
92.5°	18.9	18.7	18.5	18.3	18.6	19.4	20.3	21.1	22.0	22.6	23.1
95°	54.7	47.7	40.8	33.8	31.0	32.5	34.1	35.5	37.0	38.0	39.1
97.5°	102.7	83.1	63.5	44.0	35.8	39.2	42.6	46.1	49.5	50.3	51.2
100°	138.9	110.0	81.2	52.3	39.7	43.2	46.9	50.5	54.0	55.7	57.4
102.5°	211.7	205.6	199.5	193.4	175.4	145.4	115.5	85.5	55.6	57.8	59.9
105°	294.5	300.8	307.1	313.4	287.8	230.3	172.8	115.3	57.8	60.1	62.4
107.5°	373.4	378.5	383.6	388.8	356.9	287.8	218.9	149.9	81.0	78.6	76.2
110°	424.4	428.8	433.2	437.7	409.4	348.5	287.7	226.8	165.9	144.8	123.8



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	472.4	476.3	480.2	484.1	478.6	463.5	448.5	433.5	418.4	341.6	264.7
115°	548.7	552.2	555.8	559.4	563.8	569.1	574.4	579.6	584.9	487.3	389.8
117.5°	617.5	621.5	625.5	629.5	633.3	636.9	640.6	644.2	647.8	624.2	600.7
120°	666.7	669.9	673.1	676.2	679.7	683.5	687.2	691.1	694.8	697.3	699.9
122.5°	709.4	712.7	716.0	719.3	723.1	727.2	731.3	735.5	739.6	741.1	742.6
125°	773.4	776.1	778.9	781.6	785.0	789.0	793.0	797.0	801.0	802.5	804.0
127.5°	832.3	835.4	838.4	841.4	844.4	847.4	850.3	853.4	856.4	858.5	860.7
130°	869.8	873.2	876.6	879.9	882.7	885.0	887.3	889.7	892.0	894.3	896.6
132.5°	907.2	910.1	912.9	915.8	918.4	920.7	923.0	925.3	927.6	929.6	931.6
135°	957.0	960.4	963.8	967.1	969.7	971.6	973.5	975.4	977.3	979.5	981.5
137.5°	1005.8	1008.2	1010.6	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8	1027.9
140°	1037.8	1039.5	1041.2	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0	1057.9
142.5°	1064.9	1066.4	1067.9	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9	1085.6
145°	1106.0	1105.8	1105.6	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8	1124.4
147.5°	1142.8	1142.0	1141.2	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0	1158.1
150°	1166.4	1164.9	1163.4	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7	1178.9
152.5°	1186.7	1185.0	1183.4	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6	1197.8
155°	1216.2	1214.3	1212.4	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2	1223.4
157.5°	1239.8	1238.2	1236.6	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6	1245.0
160°	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3	1257.6
162.5°	1266.0	1264.6	1263.4	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8	1269.3
165°	1282.2	1280.9	1279.7	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1	1283.6
167.5°	1294.4	1293.1	1291.8	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1	1295.6
170°	1301.2	1299.9	1298.7	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1	1301.6
172.5°	1305.7	1304.5	1303.2	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7	1306.2
175°	1311.4	1309.9	1308.5	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7	1311.1
177.5°	1312.7	1311.4	1310.3	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5	1311.6
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	14.3	14.4	14.3	14.4	14.8	14.5	14.6
90°	22.1	23.2	23.9	24.3	24.8	25.1	25.6
92.5°	23.6	24.2	24.6	24.9	25.1	25.3	25.6
95°	40.1	41.2	41.6	41.4	41.2	40.9	40.8
97.5°	52.0	52.9	53.4	53.7	53.9	54.1	54.4
100°	59.1	60.8	61.8	62.2	62.7	63.1	63.5
102.5°	62.2	64.3	65.7	66.3	66.9	67.5	68.0
105°	64.7	67.1	68.7	69.6	70.4	71.2	72.1
107.5°	73.8	71.5	70.8	71.6	72.4	73.3	74.1
110°	102.7	81.6	71.5	72.3	73.2	74.0	74.9



TEST NUMBER: P331366-940

CATALOG NUMBER: SA2XXDIP-C675D1080U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	187.9	111.0	72.9	73.7	74.3	75.0	75.6
115°	292.3	194.7	138.4	123.2	108.1	92.9	77.8
117.5°	577.0	553.5	516.7	466.9	417.1	367.2	317.4
120°	702.4	705.0	692.0	663.5	635.1	606.6	578.3
122.5°	744.1	745.6	743.6	738.2	732.6	727.1	721.6
125°	805.4	806.9	808.0	808.6	809.2	809.9	810.5
127.5°	862.8	865.0	866.1	866.2	866.4	866.5	866.6
130°	898.9	901.3	902.3	902.1	901.9	901.7	901.5
132.5°	933.6	935.6	936.5	936.2	936.0	935.9	935.6
135°	983.6	985.7	986.6	986.1	985.7	985.3	984.9
137.5°	1029.9	1032.0	1032.7	1032.0	1031.3	1030.6	1029.8
140°	1059.8	1061.7	1062.1	1061.0	1060.0	1058.9	1057.9
142.5°	1087.4	1089.0	1089.4	1088.3	1087.3	1086.3	1085.2
145°	1125.8	1127.3	1127.5	1126.5	1125.4	1124.4	1123.3
147.5°	1159.2	1160.3	1160.4	1159.5	1158.6	1157.7	1156.8
150°	1180.2	1181.4	1181.5	1180.4	1179.5	1178.4	1177.3
152.5°	1199.2	1200.4	1200.3	1198.9	1197.6	1196.1	1194.8
155°	1224.8	1226.0	1225.7	1224.1	1222.4	1220.8	1219.1
157.5°	1246.4	1247.9	1247.8	1246.2	1244.5	1242.9	1241.2
160°	1258.8	1260.1	1260.0	1258.6	1257.0	1255.6	1254.1
162.5°	1270.7	1272.2	1271.9	1270.2	1268.4	1266.5	1264.7
165°	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7
167.5°	1297.0	1298.5	1298.2	1296.4	1294.5	1292.6	1290.7
170°	1303.1	1304.6	1304.3	1302.4	1300.6	1298.7	1296.7
172.5°	1307.6	1309.1	1308.9	1307.0	1305.1	1303.2	1301.3
175°	1312.6	1314.0	1313.8	1311.6	1309.5	1307.4	1305.3
177.5°	1312.8	1314.0	1313.8	1312.3	1310.8	1309.3	1307.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0

(END OF REPORT)