

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331346-940

Luminaire Tested: **SA2XXDIP-C675D530U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331346-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D530U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4095.9 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331346-940
CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331346-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																			
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	55	54	50																			
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42																			
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35																			
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30																			
5	70	58	50	44	65	54	47	41	48	42	37	41	37	33	36	32	29	26																			
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23																			
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20																			
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18																			
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17																			
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15285	15285	15285
5°	15344	15123	15211
10°	15252	14969	15044
15°	15064	14775	14760
20°	14795	14483	14467
25°	14530	14125	14125
30°	14188	13798	13679
35°	13868	13403	13204
40°	13468	13009	12760
45°	13075	12618	12305
50°	12645	12210	11776
55°	12197	11738	11299
60°	11699	11170	10756
65°	11163	10609	10120
70°	10485	9928	9456
75°	9538	9145	8914
80°	8461	8210	7782
85°	6928	6576	5891



TEST NUMBER: P331346-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	2.2
10°-20°	250.5	6.1
20°-30°	368.2	9.0
30°-40°	427.7	10.4
40°-50°	427.2	10.4
50°-60°	372.6	9.1
60°-70°	275.5	6.7
70°-80°	156.0	3.8
80°-90°	44.4	1.1
90°-100°	38.2	0.9
100°-110°	118.6	2.9
110°-120°	202.7	4.9
120°-130°	266.6	6.5
130°-140°	299.2	7.3
140°-150°	293.4	7.2
150°-160°	246.1	6.0
160°-170°	163.2	4.0
170°-180°	57.0	1.4
0°-30°	707.7	17.3
0°-40°	1135.4	27.7
0°-60°	1935.1	47.2
0°-90°	2411.0	58.9
90°-120°	359.5	8.8
90°-150°	1218.6	29.8
90°-180°	1685.0	41.1
0°-180°	4095.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	947	943	933	940	938	90
15°	901	895	884	887	883	254
25°	816	808	793	794	793	375
35°	704	694	680	675	670	439
45°	573	566	553	543	539	442
55°	433	428	417	406	401	387
65°	292	286	278	270	265	289
75°	153	151	147	142	143	163
85°	37	36	36	33	32	43
90°	0	7	18	17	17	3
95°	26	31	32	32	32	30
105°	109	111	112	113	113	115
115°	203	206	206	205	203	201
125°	296	300	299	298	297	264
135°	383	388	390	389	387	296
145°	465	468	471	472	470	290
155°	531	533	534	537	536	244
165°	578	578	578	581	579	163
175°	602	600	599	602	600	57
180°	602	602	602	602	602	



TEST NUMBER: P331346-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	951.1	950.3	949.5	948.7	947.9	946.6	944.8	943.0	941.2	939.4	941.0
5°	946.7	945.9	945.1	944.3	943.5	942.0	939.8	937.5	935.3	933.1	934.7
7.5°	938.3	937.1	935.9	934.6	933.4	931.6	929.3	927.0	924.8	922.5	924.1
10°	930.3	928.9	927.5	926.0	924.7	922.7	920.3	917.9	915.4	913.0	914.6
12.5°	919.4	918.2	916.9	915.6	914.4	912.6	910.1	907.7	905.3	902.9	904.0
15°	901.2	900.0	898.8	897.6	896.3	894.4	891.8	889.1	886.5	883.9	884.8
17.5°	877.9	876.6	875.5	874.2	873.1	871.1	868.4	865.8	863.1	860.4	861.4
20°	861.1	860.0	858.7	857.5	856.3	854.3	851.4	848.6	845.8	842.9	843.6
22.5°	844.4	842.7	841.0	839.3	837.6	835.4	832.8	830.1	827.4	824.7	824.8
25°	815.6	814.0	812.4	810.7	809.1	806.6	803.2	799.8	796.3	792.9	793.3
27.5°	782.8	781.4	780.0	778.5	777.0	775.0	772.2	769.5	766.8	764.1	763.5
30°	761.0	759.4	757.8	756.2	754.6	752.2	749.2	746.2	743.2	740.1	739.5
32.5°	737.7	736.4	735.1	733.8	732.5	730.3	727.1	723.9	720.7	717.5	716.4
35°	703.6	701.7	699.6	697.6	695.5	692.9	689.7	686.4	683.2	680.0	678.8
37.5°	665.2	663.4	661.6	659.9	658.2	655.6	652.4	649.2	646.0	642.7	641.1
40°	639.0	637.4	635.8	634.2	632.6	630.2	626.9	623.7	620.5	617.2	615.4
42.5°	613.6	611.9	610.3	608.7	607.1	604.7	601.4	598.2	594.9	591.7	589.7
45°	572.6	571.1	569.7	568.4	566.9	564.7	561.7	558.7	555.6	552.6	550.4
47.5°	531.8	530.5	529.1	527.8	526.5	524.2	521.0	517.9	514.8	511.6	509.3
50°	503.4	502.4	501.4	500.3	499.4	497.4	494.6	491.8	488.9	486.1	483.3
52.5°	475.7	474.4	473.1	471.7	470.4	468.4	465.7	463.1	460.4	457.7	455.4
55°	433.3	432.1	430.9	429.6	428.5	426.6	424.2	421.8	419.4	417.0	414.5
57.5°	390.7	389.8	388.8	387.8	386.8	385.0	382.4	379.7	377.0	374.3	371.9
60°	362.3	361.5	360.7	359.9	359.1	357.2	354.5	351.6	348.7	345.9	343.7
62.5°	334.7	333.3	332.1	330.7	329.5	327.7	325.6	323.3	321.2	319.0	316.9
65°	292.2	291.0	289.8	288.6	287.3	285.7	283.7	281.7	279.6	277.7	275.8
67.5°	249.1	248.1	247.1	246.1	245.1	243.8	241.9	240.1	238.4	236.5	235.1
70°	222.1	221.3	220.5	219.7	218.9	217.6	215.7	213.9	212.1	210.3	208.8
72.5°	194.5	193.6	192.8	192.0	191.2	190.2	189.0	187.9	186.7	185.5	184.1
75°	152.9	152.5	152.1	151.7	151.3	150.6	149.6	148.6	147.6	146.6	145.3
77.5°	115.8	115.1	114.4	113.7	113.1	112.5	112.1	111.6	111.3	110.8	110.3
80°	91.0	90.9	90.6	90.4	90.2	89.9	89.5	89.1	88.7	88.3	87.7
82.5°	67.8	67.7	67.7	67.6	67.6	67.4	67.1	67.0	66.7	66.4	65.7
85°	37.4	37.1	36.9	36.7	36.5	36.3	36.1	35.9	35.7	35.5	34.9
87.5°	13.2	13.2	13.1	13.0	13.0	13.0	13.2	13.4	13.6	13.7	13.2
90°	0.5	1.9	3.2	4.5	6.0	7.8	10.3	12.8	15.3	17.8	17.6
92.5°	9.1	10.1	11.1	12.0	13.0	13.8	14.4	15.0	15.6	16.1	16.2
95°	26.5	27.6	28.7	29.9	30.9	31.7	31.8	32.1	32.3	32.5	32.5
97.5°	48.3	49.3	50.3	51.3	52.3	53.0	53.4	53.9	54.3	54.8	54.8
100°	64.6	65.5	66.3	67.3	68.2	68.8	69.2	69.5	69.8	70.2	70.2
102.5°	81.7	82.4	83.1	83.8	84.5	85.2	85.6	86.0	86.4	86.9	86.9
105°	109.3	109.7	110.0	110.3	110.7	110.9	111.2	111.4	111.6	111.9	112.1
107.5°	137.2	137.7	138.2	138.7	139.2	139.5	139.5	139.5	139.5	139.5	139.6
110°	155.1	155.8	156.4	157.1	157.8	158.1	158.1	158.1	158.1	158.1	158.1



TEST NUMBER: P331346-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	174.6	175.3	175.9	176.6	177.4	177.6	177.5	177.5	177.4	177.3	177.0
115°	203.4	204.1	204.7	205.5	206.1	206.3	206.1	205.9	205.6	205.5	205.4
117.5°	232.1	233.0	233.9	234.8	235.7	235.9	235.2	234.5	233.9	233.3	233.0
120°	251.2	252.1	253.0	253.9	254.9	254.9	253.9	253.0	252.1	251.2	251.2
122.5°	268.7	269.7	270.9	272.0	273.0	273.2	272.6	272.0	271.3	270.7	270.5
125°	296.0	296.9	298.0	299.0	300.0	300.3	300.0	299.7	299.3	299.0	298.6
127.5°	322.4	323.8	325.0	326.4	327.6	328.1	327.7	327.3	326.9	326.5	326.0
130°	339.2	340.6	342.1	343.6	345.0	345.6	345.4	345.2	345.0	344.7	344.6
132.5°	357.8	359.1	360.3	361.5	362.7	363.3	363.4	363.4	363.5	363.5	363.0
135°	382.9	384.1	385.4	386.6	387.9	388.6	388.8	389.1	389.3	389.5	389.4
137.5°	409.2	410.3	411.3	412.3	413.3	413.9	414.3	414.6	414.8	415.1	415.0
140°	425.1	426.1	427.1	428.1	429.2	430.0	430.5	431.1	431.7	432.2	432.2
142.5°	441.4	442.4	443.4	444.4	445.4	446.1	446.6	446.9	447.3	447.6	447.7
145°	464.8	465.6	466.4	467.2	468.0	468.7	469.3	470.0	470.7	471.4	471.4
147.5°	485.6	486.5	487.5	488.5	489.4	490.1	490.5	491.0	491.4	492.0	492.1
150°	499.9	500.5	501.2	501.9	502.6	503.1	503.5	504.0	504.4	505.0	505.2
152.5°	512.5	513.2	513.8	514.5	515.1	515.8	516.3	516.8	517.4	518.0	518.4
155°	531.4	531.7	532.1	532.4	532.7	533.1	533.4	533.8	534.0	534.4	535.0
157.5°	547.5	547.8	548.0	548.2	548.5	548.7	548.8	549.1	549.3	549.5	550.3
160°	557.3	557.5	557.8	557.9	558.2	558.4	558.5	558.6	558.7	558.8	559.5
162.5°	566.2	566.3	566.3	566.4	566.4	566.5	566.6	566.8	566.9	566.9	567.8
165°	578.2	578.0	577.9	577.8	577.7	577.7	577.7	577.7	577.7	577.7	578.5
167.5°	588.1	587.8	587.5	587.1	586.7	586.6	586.6	586.6	586.5	586.5	587.3
170°	593.4	593.1	592.7	592.4	592.1	591.8	591.7	591.6	591.5	591.4	592.2
172.5°	597.1	596.7	596.4	596.0	595.8	595.5	595.4	595.3	595.1	595.0	595.8
175°	601.5	601.2	600.8	600.6	600.2	599.9	599.7	599.5	599.2	599.0	599.8
177.5°	603.4	603.1	602.8	602.5	602.3	602.1	601.9	601.7	601.5	601.4	601.9
180°	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5



TEST NUMBER: P331346-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	942.6	944.3	945.9	946.6	946.2	945.9	945.6	945.3
5°	936.3	937.9	939.5	940.1	939.8	939.3	939.0	938.5
7.5°	925.8	927.4	929.0	929.5	929.1	928.7	928.3	927.8
10°	916.2	917.9	919.5	920.0	919.4	918.8	918.2	917.6
12.5°	905.1	906.2	907.4	907.7	907.2	906.9	906.4	906.0
15°	885.6	886.4	887.2	887.1	886.0	885.0	884.0	883.0
17.5°	862.3	863.2	864.2	864.2	863.2	862.2	861.2	860.2
20°	844.2	844.8	845.3	845.3	844.5	843.6	842.8	842.0
22.5°	825.0	825.1	825.2	825.0	824.6	824.0	823.6	823.1
25°	793.7	794.1	794.5	794.5	794.1	793.7	793.3	792.9
27.5°	762.9	762.3	761.7	760.9	759.9	758.9	758.0	757.0
30°	738.9	738.2	737.6	736.9	736.1	735.3	734.5	733.7
32.5°	715.3	714.3	713.1	712.2	711.4	710.6	709.7	708.9
35°	677.6	676.4	675.1	674.0	673.1	672.0	671.0	669.9
37.5°	639.7	638.2	636.7	635.4	634.5	633.5	632.6	631.6
40°	613.6	611.7	609.9	608.6	607.8	607.0	606.2	605.4
42.5°	587.7	585.8	583.8	582.2	581.0	580.0	578.8	577.7
45°	548.1	545.9	543.7	542.2	541.4	540.6	539.8	538.9
47.5°	506.9	504.5	502.2	500.4	499.3	498.1	497.0	495.8
50°	480.5	477.6	474.7	472.9	471.8	470.8	469.8	468.8
52.5°	453.0	450.7	448.4	446.5	445.1	443.8	442.5	441.1
55°	412.1	409.7	407.2	405.5	404.5	403.5	402.4	401.4
57.5°	369.5	367.1	364.8	363.2	362.4	361.7	360.9	360.1
60°	341.4	339.2	337.0	335.6	335.0	334.4	333.8	333.1
62.5°	314.9	312.8	310.8	309.3	308.5	307.7	307.0	306.2
65°	274.0	272.2	270.4	268.9	268.0	266.9	265.9	264.9
67.5°	233.6	232.3	230.9	229.7	228.9	228.1	227.3	226.5
70°	207.4	206.1	204.6	203.5	202.7	201.9	201.1	200.3
72.5°	182.7	181.3	179.9	178.8	178.2	177.5	176.9	176.2
75°	144.1	142.9	141.7	141.3	141.7	142.1	142.5	142.9
77.5°	109.7	109.1	108.4	107.9	107.3	106.7	106.2	105.6
80°	87.1	86.5	85.9	85.3	85.0	84.5	84.2	83.7
82.5°	64.9	64.1	63.4	63.0	62.9	62.8	62.7	62.6
85°	34.3	33.7	33.1	32.6	32.5	32.3	32.1	31.8
87.5°	12.7	12.1	11.6	11.3	11.1	11.1	10.9	10.7
90°	17.4	17.1	16.9	16.9	16.9	17.0	17.2	17.3
92.5°	16.2	16.3	16.3	16.4	16.4	16.4	16.5	16.5
95°	32.5	32.5	32.5	32.5	32.2	32.0	31.7	31.6
97.5°	54.8	54.8	54.8	54.7	54.7	54.7	54.7	54.6
100°	70.2	70.2	70.2	70.1	70.0	69.9	69.8	69.6
102.5°	87.0	87.1	87.2	87.2	87.1	86.9	86.9	86.8
105°	112.4	112.5	112.8	112.9	112.9	112.9	112.9	112.9
107.5°	139.6	139.7	139.8	139.6	139.0	138.6	138.0	137.5
110°	158.1	158.1	158.1	158.0	157.7	157.3	156.9	156.6



TEST NUMBER: P331346-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	176.7	176.5	176.2	175.9	175.7	175.4	175.1	175.0
115°	205.2	205.1	205.0	204.7	204.4	204.1	203.8	203.4
117.5°	232.7	232.5	232.2	231.9	231.6	231.2	230.9	230.5
120°	251.2	251.2	251.2	251.0	250.7	250.4	250.0	249.7
122.5°	270.2	269.9	269.7	269.4	269.1	268.9	268.7	268.4
125°	298.3	298.0	297.7	297.4	297.3	297.2	297.0	296.9
127.5°	325.7	325.2	324.9	324.4	324.0	323.7	323.3	323.0
130°	344.3	344.1	343.8	343.5	343.0	342.6	342.1	341.7
132.5°	362.5	361.9	361.5	361.1	360.7	360.3	360.0	359.6
135°	389.3	389.1	389.1	388.8	388.5	388.2	387.8	387.4
137.5°	414.9	414.8	414.7	414.5	414.0	413.6	413.1	412.7
140°	432.2	432.2	432.2	432.0	431.5	431.1	430.6	430.2
142.5°	447.8	447.9	448.0	447.8	447.4	446.9	446.5	446.0
145°	471.6	471.7	471.8	471.6	471.2	470.7	470.3	469.8
147.5°	492.4	492.7	492.9	492.8	492.4	492.0	491.5	491.1
150°	505.6	506.0	506.3	506.3	506.0	505.6	505.2	505.0
152.5°	518.8	519.2	519.7	519.7	519.2	518.8	518.4	518.0
155°	535.6	536.1	536.7	536.8	536.5	536.1	535.7	535.5
157.5°	551.0	551.8	552.6	552.7	552.1	551.6	551.1	550.5
160°	560.2	560.9	561.5	561.7	561.2	560.8	560.3	559.8
162.5°	568.5	569.3	570.1	570.2	569.6	569.1	568.6	568.0
165°	579.3	580.1	580.8	580.9	580.3	579.8	579.3	578.6
167.5°	588.1	588.9	589.7	589.8	589.2	588.6	588.0	587.4
170°	593.0	593.8	594.5	594.6	593.9	593.3	592.5	591.9
172.5°	596.6	597.4	598.2	598.2	597.6	596.9	596.2	595.6
175°	600.6	601.4	602.2	602.3	601.5	600.8	600.2	599.5
177.5°	602.4	603.0	603.5	603.5	603.0	602.4	601.9	601.4
180°	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5

(END OF REPORT)