

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331347-940

Luminaire Tested: **SA2XXDIP-C675D530U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331347-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D530U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4251.1 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331347-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331347-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	99	95	91	87	92	88	85	82	76	74	72	65	63	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	48	46	44	40
3	82	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	75	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	32	35	31	28	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	37	31	38	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15285	15285	15285
5°	15344	15123	15211
10°	15252	14969	15044
15°	15064	14775	14760
20°	14795	14483	14467
25°	14530	14125	14125
30°	14188	13798	13679
35°	13868	13403	13204
40°	13468	13009	12760
45°	13075	12618	12305
50°	12645	12210	11776
55°	12197	11738	11299
60°	11699	11170	10756
65°	11163	10609	10120
70°	10485	9928	9456
75°	9538	9145	8914
80°	8461	8210	7782
85°	6928	6576	5891



TEST NUMBER: P331347-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	2.1
10°-20°	250.5	5.9
20°-30°	368.2	8.7
30°-40°	427.7	10.1
40°-50°	427.2	10.0
50°-60°	372.6	8.8
60°-70°	275.5	6.5
70°-80°	156.0	3.7
80°-90°	44.3	1.0
90°-100°	105.7	2.5
100°-110°	358.8	8.4
110°-120°	381.2	9.0
120°-130°	313.8	7.4
130°-140°	252.0	5.9
140°-150°	190.4	4.5
150°-160°	133.8	3.1
160°-170°	78.8	1.9
170°-180°	25.6	0.6
0°-30°	707.7	16.6
0°-40°	1135.4	26.7
0°-60°	1935.1	45.5
0°-90°	2411.0	56.7
90°-120°	845.7	19.9
90°-150°	1601.9	37.7
90°-180°	1840.0	43.3
0°-180°	4251.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	947	943	933	940	938	90
15°	901	895	884	887	883	254
25°	816	808	793	794	793	375
35°	704	694	680	675	670	439
45°	573	566	553	543	539	442
55°	433	428	417	406	401	387
65°	292	286	278	270	265	289
75°	153	151	147	142	143	163
85°	37	36	36	33	32	43
90°	0	7	17	16	17	3
95°	18	44	199	75	58	19
105°	62	94	377	674	573	66
115°	109	138	315	651	754	108
125°	153	180	303	527	612	135
135°	179	214	300	443	507	138
145°	204	235	298	370	405	128
155°	232	251	289	327	340	107
165°	253	261	277	294	298	71
175°	264	264	266	270	269	25
180°	264	264	264	264	264	



TEST NUMBER: P331347-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	951.1	950.3	949.5	948.7	947.9	946.6	944.8	943.0	941.2	939.4	941.0
5°	946.7	945.9	945.1	944.3	943.5	942.0	939.8	937.5	935.3	933.1	934.7
7.5°	938.3	937.1	935.9	934.6	933.4	931.6	929.3	927.0	924.8	922.5	924.1
10°	930.3	928.9	927.5	926.0	924.7	922.7	920.3	917.9	915.4	913.0	914.6
12.5°	919.4	918.2	916.9	915.6	914.4	912.6	910.1	907.7	905.3	902.9	904.0
15°	901.2	900.0	898.8	897.6	896.3	894.4	891.8	889.1	886.5	883.9	884.8
17.5°	877.9	876.6	875.5	874.2	873.1	871.1	868.4	865.8	863.1	860.4	861.4
20°	861.1	860.0	858.7	857.5	856.3	854.3	851.4	848.6	845.8	842.9	843.6
22.5°	844.4	842.7	841.0	839.3	837.6	835.4	832.8	830.1	827.4	824.7	824.8
25°	815.6	814.0	812.4	810.7	809.1	806.6	803.2	799.8	796.3	792.9	793.3
27.5°	782.8	781.4	780.0	778.5	777.0	775.0	772.2	769.5	766.8	764.1	763.5
30°	761.0	759.4	757.8	756.2	754.6	752.2	749.2	746.2	743.2	740.1	739.5
32.5°	737.7	736.4	735.1	733.8	732.5	730.3	727.1	723.9	720.7	717.5	716.4
35°	703.6	701.7	699.6	697.6	695.5	692.9	689.7	686.4	683.2	680.0	678.8
37.5°	665.2	663.4	661.6	659.9	658.2	655.6	652.4	649.2	646.0	642.7	641.1
40°	639.0	637.4	635.8	634.2	632.6	630.2	626.9	623.7	620.5	617.2	615.4
42.5°	613.6	611.9	610.3	608.7	607.1	604.7	601.4	598.2	594.9	591.7	589.7
45°	572.6	571.1	569.7	568.4	566.9	564.7	561.7	558.7	555.6	552.6	550.4
47.5°	531.8	530.5	529.1	527.8	526.5	524.2	521.0	517.9	514.8	511.6	509.3
50°	503.4	502.4	501.4	500.3	499.4	497.4	494.6	491.8	488.9	486.1	483.3
52.5°	475.7	474.4	473.1	471.7	470.4	468.4	465.7	463.1	460.4	457.7	455.4
55°	433.3	432.1	430.9	429.6	428.5	426.6	424.2	421.8	419.4	417.0	414.5
57.5°	390.7	389.8	388.8	387.8	386.8	385.0	382.4	379.7	377.0	374.3	371.9
60°	362.3	361.5	360.7	359.9	359.1	357.2	354.5	351.6	348.7	345.9	343.7
62.5°	334.7	333.3	332.1	330.7	329.5	327.7	325.6	323.3	321.2	319.0	316.9
65°	292.2	291.0	289.8	288.6	287.3	285.7	283.7	281.7	279.6	277.7	275.8
67.5°	249.1	248.1	247.1	246.1	245.1	243.8	241.9	240.1	238.4	236.5	235.1
70°	222.1	221.3	220.5	219.7	218.9	217.6	215.7	213.9	212.1	210.3	208.8
72.5°	194.5	193.6	192.8	192.0	191.2	190.2	189.0	187.9	186.7	185.5	184.1
75°	152.9	152.5	152.1	151.7	151.3	150.6	149.6	148.6	147.6	146.6	145.3
77.5°	115.8	115.1	114.4	113.7	113.1	112.5	112.1	111.6	111.3	110.8	110.3
80°	91.0	90.9	90.6	90.4	90.2	89.9	89.5	89.1	88.7	88.3	87.7
82.5°	67.8	67.7	67.7	67.6	67.6	67.4	67.1	67.0	66.7	66.4	65.7
85°	37.4	37.1	36.9	36.7	36.5	36.3	36.1	35.9	35.7	35.5	34.9
87.5°	13.2	13.2	13.3	13.2	13.0	13.0	13.2	13.6	13.9	13.6	13.1
90°	0.5	2.1	4.1	5.1	6.1	7.7	10.2	13.7	16.8	17.3	16.8
92.5°	6.2	8.9	12.6	14.9	18.3	23.1	34.6	50.7	65.2	66.1	55.8
95°	17.8	19.8	24.9	29.5	37.6	49.8	73.2	117.4	176.5	199.4	174.4
97.5°	29.0	31.7	37.1	44.1	53.4	67.2	96.7	158.3	256.3	340.3	357.0
100°	39.1	40.7	45.3	53.4	63.6	77.8	104.8	166.8	276.6	401.7	474.9
102.5°	48.5	49.7	54.2	62.3	72.9	87.1	112.1	167.2	268.9	403.8	518.9
105°	62.1	64.1	67.6	75.3	86.4	100.7	124.6	169.9	253.8	376.8	512.1
107.5°	76.7	78.3	81.8	88.8	99.9	114.2	137.4	176.8	246.2	347.9	467.4
110°	86.4	88.5	91.6	98.2	108.8	123.6	146.0	182.5	244.6	334.1	439.3



TEST NUMBER: P331347-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	95.4	97.5	100.9	107.1	117.3	132.5	154.1	188.7	245.0	325.1	419.8
115°	109.3	111.9	114.9	121.0	131.2	144.9	166.8	197.8	247.2	315.3	395.7
117.5°	123.8	125.8	128.9	134.3	144.0	158.3	178.5	207.6	250.8	310.5	380.4
120°	132.7	134.7	137.8	142.4	152.6	166.8	186.6	214.1	253.2	307.6	372.3
122.5°	141.2	142.9	146.0	151.0	161.1	175.8	194.4	219.8	256.1	306.0	365.3
125°	152.6	154.1	157.1	163.3	173.4	187.6	206.0	228.8	260.4	303.1	355.4
127.5°	161.5	163.5	167.8	174.5	184.3	198.9	216.8	237.3	264.7	301.4	346.3
130°	166.8	168.8	173.9	181.0	191.2	205.5	223.3	242.5	268.0	300.5	340.2
132.5°	171.7	174.2	179.6	187.2	197.7	212.0	228.9	247.9	271.3	300.1	335.3
135°	179.0	181.0	187.2	194.7	206.4	220.7	237.0	254.8	275.1	299.5	328.5
137.5°	185.9	188.3	194.5	202.6	214.2	227.4	243.5	260.0	278.6	299.4	323.7
140°	191.2	193.2	199.4	207.5	218.6	231.9	247.2	262.9	280.2	299.0	320.9
142.5°	196.5	198.1	203.8	212.0	222.7	235.1	250.0	265.4	281.4	299.0	318.1
145°	204.5	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	314.2
147.5°	212.9	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.4
150°	218.6	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2
152.5°	224.4	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3
155°	232.4	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0
157.5°	239.1	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0
160°	243.6	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3
162.5°	248.1	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1
165°	253.2	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7
167.5°	257.5	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4
170°	260.4	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6
172.5°	262.0	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7
175°	263.9	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0
177.5°	264.8	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331347-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	946.7	946.7	946.7	946.7	946.7	946.7	946.7	946.7
2.5°	942.6	944.3	945.9	946.6	946.2	945.9	945.6	945.3
5°	936.3	937.9	939.5	940.1	939.8	939.3	939.0	938.5
7.5°	925.8	927.4	929.0	929.5	929.1	928.7	928.3	927.8
10°	916.2	917.9	919.5	920.0	919.4	918.8	918.2	917.6
12.5°	905.1	906.2	907.4	907.7	907.2	906.9	906.4	906.0
15°	885.6	886.4	887.2	887.1	886.0	885.0	884.0	883.0
17.5°	862.3	863.2	864.2	864.2	863.2	862.2	861.2	860.2
20°	844.2	844.8	845.3	845.3	844.5	843.6	842.8	842.0
22.5°	825.0	825.1	825.2	825.0	824.6	824.0	823.6	823.1
25°	793.7	794.1	794.5	794.5	794.1	793.7	793.3	792.9
27.5°	762.9	762.3	761.7	760.9	759.9	758.9	758.0	757.0
30°	738.9	738.2	737.6	736.9	736.1	735.3	734.5	733.7
32.5°	715.3	714.3	713.1	712.2	711.4	710.6	709.7	708.9
35°	677.6	676.4	675.1	674.0	673.1	672.0	671.0	669.9
37.5°	639.7	638.2	636.7	635.4	634.5	633.5	632.6	631.6
40°	613.6	611.7	609.9	608.6	607.8	607.0	606.2	605.4
42.5°	587.7	585.8	583.8	582.2	581.0	580.0	578.8	577.7
45°	548.1	545.9	543.7	542.2	541.4	540.6	539.8	538.9
47.5°	506.9	504.5	502.2	500.4	499.3	498.1	497.0	495.8
50°	480.5	477.6	474.7	472.9	471.8	470.8	469.8	468.8
52.5°	453.0	450.7	448.4	446.5	445.1	443.8	442.5	441.1
55°	412.1	409.7	407.2	405.5	404.5	403.5	402.4	401.4
57.5°	369.5	367.1	364.8	363.2	362.4	361.7	360.9	360.1
60°	341.4	339.2	337.0	335.6	335.0	334.4	333.8	333.1
62.5°	314.9	312.8	310.8	309.3	308.5	307.7	307.0	306.2
65°	274.0	272.2	270.4	268.9	268.0	266.9	265.9	264.9
67.5°	233.6	232.3	230.9	229.7	228.9	228.1	227.3	226.5
70°	207.4	206.1	204.6	203.5	202.7	201.9	201.1	200.3
72.5°	182.7	181.3	179.9	178.8	178.2	177.5	176.9	176.2
75°	144.1	142.9	141.7	141.3	141.7	142.1	142.5	142.9
77.5°	109.7	109.1	108.4	107.9	107.3	106.7	106.2	105.6
80°	87.1	86.5	85.9	85.3	85.0	84.5	84.2	83.7
82.5°	64.9	64.1	63.4	63.0	62.9	62.8	62.7	62.6
85°	34.3	33.7	33.1	32.6	32.5	32.3	32.1	31.8
87.5°	12.5	11.8	11.5	11.3	11.1	11.0	10.8	10.6
90°	16.2	15.2	16.2	16.8	16.8	16.8	16.8	16.8
92.5°	44.3	38.1	33.8	30.6	30.2	28.6	29.0	28.2
95°	133.2	102.2	80.9	69.6	63.0	59.0	57.4	58.0
97.5°	310.9	254.4	199.4	162.6	138.3	125.8	118.4	114.1
100°	464.3	401.3	331.5	270.0	227.8	206.0	191.2	182.1
102.5°	564.8	550.5	499.6	434.4	388.5	351.2	332.8	320.4
105°	617.9	675.3	682.0	665.1	633.6	602.1	580.2	573.1
107.5°	579.6	666.2	719.1	743.7	747.6	745.9	741.5	732.1
110°	546.7	637.7	702.8	744.5	766.3	776.1	780.6	780.1



TEST NUMBER: P331347-940

CATALOG NUMBER: SA2XXDIP-C675D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	516.6	604.0	673.5	721.3	751.7	767.9	776.5	779.3
115°	479.6	557.9	624.5	676.9	712.9	736.4	749.6	754.1
117.5°	451.7	520.4	580.9	630.0	666.8	691.5	705.4	709.3
120°	437.8	500.9	554.8	601.1	636.7	660.6	675.3	680.4
122.5°	426.9	484.6	535.7	577.5	609.4	632.9	646.0	650.3
125°	410.9	463.2	508.0	546.2	575.7	594.9	607.7	611.8
127.5°	395.1	442.6	484.7	520.0	545.6	563.7	574.7	578.0
130°	385.0	428.7	468.9	502.4	527.4	544.7	554.8	558.8
132.5°	375.2	415.7	452.6	484.1	508.6	525.9	535.3	539.0
135°	361.6	395.1	428.7	457.2	479.0	495.8	505.0	507.0
137.5°	350.7	378.8	405.4	430.3	450.1	464.6	472.6	475.6
140°	343.8	368.2	391.6	413.9	430.3	443.4	451.0	454.1
142.5°	338.0	358.8	379.0	397.7	413.1	425.2	431.9	432.6
145°	330.0	346.8	362.6	377.4	389.5	398.1	403.2	404.7
147.5°	323.9	337.1	349.4	360.2	370.2	377.1	380.6	381.5
150°	319.3	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	314.9	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	308.7	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	301.5	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	296.9	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	292.5	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	285.8	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	279.4	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	276.2	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	272.5	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	268.5	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)