

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331683

Luminaire Tested: **SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331683
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4605.2 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331683
CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	100	96	92	89	93	89	86	83	77	75	73	66	64	62	55	54	53	48				
2	92	85	79	74	85	79	74	70	68	65	62	59	56	54	50	48	46	42				
3	84	75	68	63	78	70	64	59	61	57	53	53	49	46	45	42	40	37				
4	78	67	60	54	72	63	56	51	55	50	46	48	44	41	41	38	36	32				
5	72	61	53	47	67	57	50	45	50	44	40	43	39	36	37	34	32	29				
6	66	55	47	42	62	52	45	40	45	40	36	40	35	32	34	31	28	26				
7	62	50	42	37	57	47	40	35	42	36	32	36	32	29	32	28	26	23				
8	57	46	38	33	54	43	36	32	38	33	29	34	29	26	29	26	23	21				
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	21	19				
10	50	39	32	27	47	37	30	26	33	28	24	29	25	22	25	22	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	3.0
10°-20°	388.0	8.4
20°-30°	500.0	10.9
30°-40°	475.2	10.3
40°-50°	407.1	8.8
50°-60°	310.0	6.7
60°-70°	196.0	4.3
70°-80°	97.9	2.1
80°-90°	28.1	0.6
90°-100°	118.6	2.6
100°-110°	402.4	8.7
110°-120°	427.5	9.3
120°-130°	351.9	7.6
130°-140°	282.6	6.1
140°-150°	213.5	4.6
150°-160°	150.1	3.3
160°-170°	88.3	1.9
170°-180°	28.8	0.6
0°-30°	1027.3	22.3
0°-40°	1502.5	32.6
0°-60°	2219.6	48.2
0°-90°	2541.6	55.2
90°-120°	948.4	20.6
90°-150°	1796.4	39.0
90°-180°	2064.0	44.8
0°-180°	4605.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	20
90°	19	1	19	1	19	11
95°	65	20	65	20	65	85
105°	643	70	643	70	643	622
115°	846	123	846	123	846	828
125°	686	171	686	171	686	620
135°	569	201	569	201	569	442
145°	454	229	454	229	454	288
155°	382	261	382	261	382	178
165°	335	284	335	284	335	96
175°	302	296	302	296	302	29
180°	296	296	296	296	296	



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	10.3	10.7	10.7	10.7	10.7	10.6	10.4	11.0	10.7	11.2	10.7
90°	18.8	18.8	18.8	18.8	18.8	18.2	17.1	18.2	18.8	19.4	18.8
92.5°	31.6	32.5	32.1	33.9	34.3	37.9	42.7	49.7	62.6	74.1	73.1
95°	65.0	64.4	66.2	70.7	78.1	90.7	114.6	149.4	195.6	223.6	197.9
97.5°	128.0	132.8	141.1	155.1	182.4	223.6	285.3	348.7	400.3	381.6	287.4
100°	204.2	214.4	231.0	255.5	302.8	371.8	450.0	520.7	532.6	450.5	310.2
102.5°	359.3	373.2	393.8	435.7	487.1	560.3	617.4	633.4	581.9	452.8	301.6
105°	642.7	650.7	675.2	710.6	745.9	764.8	757.3	692.9	574.3	422.6	284.6
107.5°	821.0	831.6	836.5	838.4	834.0	806.4	747.1	650.0	524.2	390.2	276.1
110°	874.8	875.4	870.3	859.4	834.9	788.1	715.1	613.1	492.7	374.7	274.3



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	873.9	870.8	861.1	843.0	808.9	755.3	677.3	579.3	470.8	364.6	274.8
115°	845.7	840.6	825.8	799.5	759.1	700.3	625.6	537.8	443.7	353.6	277.2
117.5°	795.4	791.1	775.5	747.8	706.5	651.4	583.6	506.5	426.6	348.2	281.3
120°	763.0	757.3	740.8	714.0	674.1	622.2	561.7	491.0	417.5	345.0	284.0
122.5°	729.3	724.5	709.8	683.4	647.6	600.7	543.5	478.7	409.7	343.2	287.2
125°	686.1	681.5	667.2	645.6	612.5	569.7	519.5	460.8	398.6	339.9	292.0
127.5°	648.2	644.5	632.2	611.9	583.1	543.6	496.3	443.1	388.4	338.0	296.9
130°	626.7	622.2	610.8	591.4	563.4	525.8	480.8	431.7	381.5	337.0	300.5
132.5°	604.4	600.3	589.8	570.4	542.9	507.6	466.2	420.8	376.0	336.6	304.2
135°	568.6	566.3	556.0	537.2	512.7	480.8	443.1	405.5	368.4	335.9	308.5
137.5°	533.4	530.0	521.0	504.8	482.5	454.6	424.8	393.3	363.0	335.8	312.4
140°	509.3	505.8	497.3	482.5	464.2	439.1	412.9	385.5	359.9	335.3	314.2
142.5°	485.1	484.4	476.8	463.3	446.0	425.0	402.4	379.1	356.7	335.3	315.6
145°	453.9	452.2	446.5	436.8	423.2	406.6	388.9	370.1	352.4	334.2	317.1
147.5°	427.8	426.8	422.9	415.2	403.9	391.8	378.0	363.2	348.1	332.1	317.5
150°	412.3	411.7	408.3	401.5	392.9	382.7	370.7	358.1	344.5	330.8	317.1
152.5°	399.1	399.0	396.5	390.5	383.8	374.9	364.8	353.1	341.3	328.5	316.2
155°	381.5	382.7	380.4	376.4	370.1	363.8	355.3	346.2	335.3	324.5	314.8
157.5°	366.6	366.6	365.6	362.2	357.8	352.9	345.7	338.1	329.7	320.4	312.2
160°	357.0	357.0	356.4	353.6	349.6	345.6	339.3	333.0	325.6	317.7	310.8
162.5°	347.9	348.3	347.8	345.8	341.8	338.8	333.4	328.0	322.0	315.4	309.4
165°	334.8	335.3	335.3	333.0	330.8	328.5	324.5	320.5	315.9	310.8	306.8
167.5°	322.7	323.4	323.5	322.2	321.2	319.1	316.4	313.3	310.0	306.8	304.2
170°	315.4	316.5	317.1	315.4	314.8	313.7	311.4	309.7	306.8	304.5	302.8
172.5°	309.4	310.1	310.7	309.9	309.3	308.6	306.8	305.6	303.6	301.8	301.0
175°	301.7	302.8	303.4	302.8	302.8	302.3	301.7	301.1	299.4	298.8	298.3
177.5°	297.0	297.9	298.4	298.4	298.4	298.4	297.9	297.9	297.0	296.5	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	10.0	9.6	9.1	8.3	8.5	8.7	10.3	12.0	10.7	9.9	9.3
90°	15.4	11.4	8.6	6.8	5.7	4.6	2.3	0.6	2.3	4.6	5.7
92.5°	56.9	38.8	25.9	20.5	16.7	14.1	10.0	7.0	10.0	14.1	16.7
95°	131.7	82.1	55.9	42.2	33.1	27.9	22.2	20.0	22.2	27.9	33.1
97.5°	177.5	108.4	75.4	59.9	49.4	41.6	35.6	32.5	35.6	41.6	49.4
100°	187.1	117.5	87.3	71.3	59.9	50.8	45.6	43.9	45.6	50.8	59.9
102.5°	187.5	125.7	97.7	81.8	69.9	60.8	55.7	54.4	55.7	60.8	69.9
105°	190.5	139.7	112.9	96.9	84.4	75.8	71.9	69.6	71.9	75.8	84.4
107.5°	198.3	154.1	128.1	112.0	99.6	91.7	87.8	86.0	87.8	91.7	99.6
110°	204.7	163.7	138.6	122.0	110.1	102.7	99.2	96.9	99.2	102.7	110.1



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	211.6	172.8	148.6	131.6	120.1	113.1	109.3	107.0	109.3	113.1	120.1
115°	221.8	187.1	162.5	147.1	135.7	128.9	125.5	122.6	125.5	128.9	135.7
117.5°	232.8	200.2	177.5	161.5	150.6	144.5	141.1	138.8	141.1	144.5	150.6
120°	240.1	209.3	187.1	171.1	159.7	154.5	151.1	148.8	151.1	154.5	159.7
122.5°	246.5	218.0	197.1	180.7	169.3	163.7	160.3	158.4	160.3	163.7	169.3
125°	256.6	231.0	210.4	194.5	183.1	176.2	172.8	171.1	172.8	176.2	183.1
127.5°	266.1	243.1	223.1	206.7	195.7	188.2	183.4	181.1	183.4	188.2	195.7
130°	272.0	250.4	230.4	214.4	203.0	195.0	189.3	187.1	189.3	195.0	203.0
132.5°	278.0	256.7	237.7	221.7	209.9	201.4	195.3	192.5	195.3	201.4	209.9
135°	285.7	265.8	247.5	231.5	218.4	209.9	203.0	200.7	203.0	209.9	218.4
137.5°	291.6	273.1	255.0	240.2	227.2	218.1	211.2	208.5	211.2	218.1	227.2
140°	294.8	277.2	260.1	245.2	232.7	223.6	216.7	214.4	216.7	223.6	232.7
142.5°	297.6	280.4	263.7	249.8	237.7	228.6	222.2	220.4	222.2	228.6	237.7
145°	301.1	285.1	269.7	257.2	245.8	237.2	231.5	229.3	231.5	237.2	245.8
147.5°	303.1	289.0	274.5	263.4	253.9	246.0	240.5	238.8	240.5	246.0	253.9
150°	304.0	290.8	277.7	267.5	258.9	251.5	246.9	245.2	246.9	251.5	258.9
152.5°	304.4	292.7	280.9	271.6	263.5	257.0	252.4	251.6	252.4	257.0	263.5
155°	305.1	295.4	285.7	277.2	270.9	264.6	261.2	260.6	261.2	264.6	270.9
157.5°	305.1	297.3	289.1	282.0	276.9	271.5	268.7	268.1	268.7	271.5	276.9
160°	305.1	298.3	291.4	285.1	280.6	276.0	273.7	273.2	273.7	276.0	280.6
162.5°	304.6	298.7	292.8	287.9	283.8	280.1	277.8	278.2	277.8	280.1	283.8
165°	303.4	299.4	294.3	290.8	288.0	284.6	283.4	284.0	283.4	284.6	288.0
167.5°	302.6	299.3	295.5	293.4	291.3	289.1	288.1	288.8	288.1	289.1	291.3
170°	301.7	298.8	296.0	294.3	293.1	291.4	290.8	292.0	290.8	291.4	293.1
172.5°	300.3	298.4	296.4	295.2	294.5	292.8	293.1	293.8	293.1	292.8	294.5
175°	298.8	297.7	296.5	296.0	296.0	294.8	295.4	296.0	295.4	294.8	296.0
177.5°	297.9	297.0	296.5	296.5	296.5	295.6	296.1	297.0	296.1	295.6	296.5
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	9.1	9.1	8.8	9.6	10.3	10.0	9.9	9.4	9.1	9.4	9.1
90°	6.8	8.6	11.4	15.4	18.8	19.4	18.8	18.2	17.1	18.2	18.8
92.5°	20.5	25.9	38.8	56.9	73.1	74.1	62.6	49.7	42.7	37.9	34.3
95°	42.2	55.9	82.1	131.7	197.9	223.6	195.6	149.4	114.6	90.7	78.1
97.5°	59.9	75.4	108.4	177.5	287.4	381.6	400.3	348.7	285.3	223.6	182.4
100°	71.3	87.3	117.5	187.1	310.2	450.5	532.6	520.7	450.0	371.8	302.8
102.5°	81.8	97.7	125.7	187.5	301.6	452.8	581.9	633.4	617.4	560.3	487.1
105°	96.9	112.9	139.7	190.5	284.6	422.6	574.3	692.9	757.3	764.8	745.9
107.5°	112.0	128.1	154.1	198.3	276.1	390.2	524.2	650.0	747.1	806.4	834.0
110°	122.0	138.6	163.7	204.7	274.3	374.7	492.7	613.1	715.1	788.1	834.9



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	131.6	148.6	172.8	211.6	274.8	364.6	470.8	579.3	677.3	755.3	808.9
115°	147.1	162.5	187.1	221.8	277.2	353.6	443.7	537.8	625.6	700.3	759.1
117.5°	161.5	177.5	200.2	232.8	281.3	348.2	426.6	506.5	583.6	651.4	706.5
120°	171.1	187.1	209.3	240.1	284.0	345.0	417.5	491.0	561.7	622.2	674.1
122.5°	180.7	197.1	218.0	246.5	287.2	343.2	409.7	478.7	543.5	600.7	647.6
125°	194.5	210.4	231.0	256.6	292.0	339.9	398.6	460.8	519.5	569.7	612.5
127.5°	206.7	223.1	243.1	266.1	296.9	338.0	388.4	443.1	496.3	543.6	583.1
130°	214.4	230.4	250.4	272.0	300.5	337.0	381.5	431.7	480.8	525.8	563.4
132.5°	221.7	237.7	256.7	278.0	304.2	336.6	376.0	420.8	466.2	507.6	542.9
135°	231.5	247.5	265.8	285.7	308.5	335.9	368.4	405.5	443.1	480.8	512.7
137.5°	240.2	255.0	273.1	291.6	312.4	335.8	363.0	393.3	424.8	454.6	482.5
140°	245.2	260.1	277.2	294.8	314.2	335.3	359.9	385.5	412.9	439.1	464.2
142.5°	249.8	263.7	280.4	297.6	315.6	335.3	356.7	379.1	402.4	425.0	446.0
145°	257.2	269.7	285.1	301.1	317.1	334.2	352.4	370.1	388.9	406.6	423.2
147.5°	263.4	274.5	289.0	303.1	317.5	332.1	348.1	363.2	378.0	391.8	403.9
150°	267.5	277.7	290.8	304.0	317.1	330.8	344.5	358.1	370.7	382.7	392.9
152.5°	271.6	280.9	292.7	304.4	316.2	328.5	341.3	353.1	364.8	374.9	383.8
155°	277.2	285.7	295.4	305.1	314.8	324.5	335.3	346.2	355.3	363.8	370.1
157.5°	282.0	289.1	297.3	305.1	312.2	320.4	329.7	338.1	345.7	352.9	357.8
160°	285.1	291.4	298.3	305.1	310.8	317.7	325.6	333.0	339.3	345.6	349.6
162.5°	287.9	292.8	298.7	304.6	309.4	315.4	322.0	328.0	333.4	338.8	341.8
165°	290.8	294.3	299.4	303.4	306.8	310.8	315.9	320.5	324.5	328.5	330.8
167.5°	293.4	295.5	299.3	302.6	304.2	306.8	310.0	313.3	316.4	319.1	321.2
170°	294.3	296.0	298.8	301.7	302.8	304.5	306.8	309.7	311.4	313.7	314.8
172.5°	295.2	296.4	298.4	300.3	301.0	301.8	303.6	305.6	306.8	308.6	309.3
175°	296.0	296.5	297.7	298.8	298.3	298.8	299.4	301.1	301.7	302.3	302.8
177.5°	296.5	296.5	297.0	297.9	297.0	296.5	297.0	297.9	297.9	298.4	298.4
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	9.1	8.7	9.1	8.7	9.1	8.7	9.1	9.1	9.4	9.1	9.4
90°	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.2	17.1	18.2
92.5°	33.9	32.1	32.5	31.6	32.5	32.1	33.9	34.3	37.9	42.7	49.7
95°	70.7	66.2	64.4	65.0	64.4	66.2	70.7	78.1	90.7	114.6	149.4
97.5°	155.1	141.1	132.8	128.0	132.8	141.1	155.1	182.4	223.6	285.3	348.7
100°	255.5	231.0	214.4	204.2	214.4	231.0	255.5	302.8	371.8	450.0	520.7
102.5°	435.7	393.8	373.2	359.3	373.2	393.8	435.7	487.1	560.3	617.4	633.4
105°	710.6	675.2	650.7	642.7	650.7	675.2	710.6	745.9	764.8	757.3	692.9
107.5°	838.4	836.5	831.6	821.0	831.6	836.5	838.4	834.0	806.4	747.1	650.0
110°	859.4	870.3	875.4	874.8	875.4	870.3	859.4	834.9	788.1	715.1	613.1



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	843.0	861.1	870.8	873.9	870.8	861.1	843.0	808.9	755.3	677.3	579.3
115°	799.5	825.8	840.6	845.7	840.6	825.8	799.5	759.1	700.3	625.6	537.8
117.5°	747.8	775.5	791.1	795.4	791.1	775.5	747.8	706.5	651.4	583.6	506.5
120°	714.0	740.8	757.3	763.0	757.3	740.8	714.0	674.1	622.2	561.7	491.0
122.5°	683.4	709.8	724.5	729.3	724.5	709.8	683.4	647.6	600.7	543.5	478.7
125°	645.6	667.2	681.5	686.1	681.5	667.2	645.6	612.5	569.7	519.5	460.8
127.5°	611.9	632.2	644.5	648.2	644.5	632.2	611.9	583.1	543.6	496.3	443.1
130°	591.4	610.8	622.2	626.7	622.2	610.8	591.4	563.4	525.8	480.8	431.7
132.5°	570.4	589.8	600.3	604.4	600.3	589.8	570.4	542.9	507.6	466.2	420.8
135°	537.2	556.0	566.3	568.6	566.3	556.0	537.2	512.7	480.8	443.1	405.5
137.5°	504.8	521.0	530.0	533.4	530.0	521.0	504.8	482.5	454.6	424.8	393.3
140°	482.5	497.3	505.8	509.3	505.8	497.3	482.5	464.2	439.1	412.9	385.5
142.5°	463.3	476.8	484.4	485.1	484.4	476.8	463.3	446.0	425.0	402.4	379.1
145°	436.8	446.5	452.2	453.9	452.2	446.5	436.8	423.2	406.6	388.9	370.1
147.5°	415.2	422.9	426.8	427.8	426.8	422.9	415.2	403.9	391.8	378.0	363.2
150°	401.5	408.3	411.7	412.3	411.7	408.3	401.5	392.9	382.7	370.7	358.1
152.5°	390.5	396.5	399.0	399.1	399.0	396.5	390.5	383.8	374.9	364.8	353.1
155°	376.4	380.4	382.7	381.5	382.7	380.4	376.4	370.1	363.8	355.3	346.2
157.5°	362.2	365.6	366.6	366.6	366.6	365.6	362.2	357.8	352.9	345.7	338.1
160°	353.6	356.4	357.0	357.0	357.0	356.4	353.6	349.6	345.6	339.3	333.0
162.5°	345.8	347.8	348.3	347.9	348.3	347.8	345.8	341.8	338.8	333.4	328.0
165°	333.0	335.3	335.3	334.8	335.3	335.3	333.0	330.8	328.5	324.5	320.5
167.5°	322.2	323.5	323.4	322.7	323.4	323.5	322.2	321.2	319.1	316.4	313.3
170°	315.4	317.1	316.5	315.4	316.5	317.1	315.4	314.8	313.7	311.4	309.7
172.5°	309.9	310.7	310.1	309.4	310.1	310.7	309.9	309.3	308.6	306.8	305.6
175°	302.8	303.4	302.8	301.7	302.8	303.4	302.8	302.8	302.3	301.7	301.1
177.5°	298.4	298.4	297.9	297.0	297.9	298.4	298.4	298.4	298.4	297.9	297.9
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	9.9	10.0	10.3	9.6	8.8	9.1	9.1	9.3	9.9	10.7	12.0
90°	18.8	19.4	18.8	15.4	11.4	8.6	6.8	5.7	4.6	2.3	0.6
92.5°	62.6	74.1	73.1	56.9	38.8	25.9	20.5	16.7	14.1	10.0	7.0
95°	195.6	223.6	197.9	131.7	82.1	55.9	42.2	33.1	27.9	22.2	20.0
97.5°	400.3	381.6	287.4	177.5	108.4	75.4	59.9	49.4	41.6	35.6	32.5
100°	532.6	450.5	310.2	187.1	117.5	87.3	71.3	59.9	50.8	45.6	43.9
102.5°	581.9	452.8	301.6	187.5	125.7	97.7	81.8	69.9	60.8	55.7	54.4
105°	574.3	422.6	284.6	190.5	139.7	112.9	96.9	84.4	75.8	71.9	69.6
107.5°	524.2	390.2	276.1	198.3	154.1	128.1	112.0	99.6	91.7	87.8	86.0
110°	492.7	374.7	274.3	204.7	163.7	138.6	122.0	110.1	102.7	99.2	96.9



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	470.8	364.6	274.8	211.6	172.8	148.6	131.6	120.1	113.1	109.3	107.0
115°	443.7	353.6	277.2	221.8	187.1	162.5	147.1	135.7	128.9	125.5	122.6
117.5°	426.6	348.2	281.3	232.8	200.2	177.5	161.5	150.6	144.5	141.1	138.8
120°	417.5	345.0	284.0	240.1	209.3	187.1	171.1	159.7	154.5	151.1	148.8
122.5°	409.7	343.2	287.2	246.5	218.0	197.1	180.7	169.3	163.7	160.3	158.4
125°	398.6	339.9	292.0	256.6	231.0	210.4	194.5	183.1	176.2	172.8	171.1
127.5°	388.4	338.0	296.9	266.1	243.1	223.1	206.7	195.7	188.2	183.4	181.1
130°	381.5	337.0	300.5	272.0	250.4	230.4	214.4	203.0	195.0	189.3	187.1
132.5°	376.0	336.6	304.2	278.0	256.7	237.7	221.7	209.9	201.4	195.3	192.5
135°	368.4	335.9	308.5	285.7	265.8	247.5	231.5	218.4	209.9	203.0	200.7
137.5°	363.0	335.8	312.4	291.6	273.1	255.0	240.2	227.2	218.1	211.2	208.5
140°	359.9	335.3	314.2	294.8	277.2	260.1	245.2	232.7	223.6	216.7	214.4
142.5°	356.7	335.3	315.6	297.6	280.4	263.7	249.8	237.7	228.6	222.2	220.4
145°	352.4	334.2	317.1	301.1	285.1	269.7	257.2	245.8	237.2	231.5	229.3
147.5°	348.1	332.1	317.5	303.1	289.0	274.5	263.4	253.9	246.0	240.5	238.8
150°	344.5	330.8	317.1	304.0	290.8	277.7	267.5	258.9	251.5	246.9	245.2
152.5°	341.3	328.5	316.2	304.4	292.7	280.9	271.6	263.5	257.0	252.4	251.6
155°	335.3	324.5	314.8	305.1	295.4	285.7	277.2	270.9	264.6	261.2	260.6
157.5°	329.7	320.4	312.2	305.1	297.3	289.1	282.0	276.9	271.5	268.7	268.1
160°	325.6	317.7	310.8	305.1	298.3	291.4	285.1	280.6	276.0	273.7	273.2
162.5°	322.0	315.4	309.4	304.6	298.7	292.8	287.9	283.8	280.1	277.8	278.2
165°	315.9	310.8	306.8	303.4	299.4	294.3	290.8	288.0	284.6	283.4	284.0
167.5°	310.0	306.8	304.2	302.6	299.3	295.5	293.4	291.3	289.1	288.1	288.8
170°	306.8	304.5	302.8	301.7	298.8	296.0	294.3	293.1	291.4	290.8	292.0
172.5°	303.6	301.8	301.0	300.3	298.4	296.4	295.2	294.5	292.8	293.1	293.8
175°	299.4	298.8	298.3	298.8	297.7	296.5	296.0	296.0	294.8	295.4	296.0
177.5°	297.0	296.5	297.0	297.9	297.0	296.5	296.5	296.5	295.6	296.1	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.3	8.7	8.5	8.3	9.1	9.6	10.0	10.7	11.2	10.7	11.0
90°	2.3	4.6	5.7	6.8	8.6	11.4	15.4	18.8	19.4	18.8	18.2
92.5°	10.0	14.1	16.7	20.5	25.9	38.8	56.9	73.1	74.1	62.6	49.7
95°	22.2	27.9	33.1	42.2	55.9	82.1	131.7	197.9	223.6	195.6	149.4
97.5°	35.6	41.6	49.4	59.9	75.4	108.4	177.5	287.4	381.6	400.3	348.7
100°	45.6	50.8	59.9	71.3	87.3	117.5	187.1	310.2	450.5	532.6	520.7
102.5°	55.7	60.8	69.9	81.8	97.7	125.7	187.5	301.6	452.8	581.9	633.4
105°	71.9	75.8	84.4	96.9	112.9	139.7	190.5	284.6	422.6	574.3	692.9
107.5°	87.8	91.7	99.6	112.0	128.1	154.1	198.3	276.1	390.2	524.2	650.0
110°	99.2	102.7	110.1	122.0	138.6	163.7	204.7	274.3	374.7	492.7	613.1



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	109.3	113.1	120.1	131.6	148.6	172.8	211.6	274.8	364.6	470.8	579.3
115°	125.5	128.9	135.7	147.1	162.5	187.1	221.8	277.2	353.6	443.7	537.8
117.5°	141.1	144.5	150.6	161.5	177.5	200.2	232.8	281.3	348.2	426.6	506.5
120°	151.1	154.5	159.7	171.1	187.1	209.3	240.1	284.0	345.0	417.5	491.0
122.5°	160.3	163.7	169.3	180.7	197.1	218.0	246.5	287.2	343.2	409.7	478.7
125°	172.8	176.2	183.1	194.5	210.4	231.0	256.6	292.0	339.9	398.6	460.8
127.5°	183.4	188.2	195.7	206.7	223.1	243.1	266.1	296.9	338.0	388.4	443.1
130°	189.3	195.0	203.0	214.4	230.4	250.4	272.0	300.5	337.0	381.5	431.7
132.5°	195.3	201.4	209.9	221.7	237.7	256.7	278.0	304.2	336.6	376.0	420.8
135°	203.0	209.9	218.4	231.5	247.5	265.8	285.7	308.5	335.9	368.4	405.5
137.5°	211.2	218.1	227.2	240.2	255.0	273.1	291.6	312.4	335.8	363.0	393.3
140°	216.7	223.6	232.7	245.2	260.1	277.2	294.8	314.2	335.3	359.9	385.5
142.5°	222.2	228.6	237.7	249.8	263.7	280.4	297.6	315.6	335.3	356.7	379.1
145°	231.5	237.2	245.8	257.2	269.7	285.1	301.1	317.1	334.2	352.4	370.1
147.5°	240.5	246.0	253.9	263.4	274.5	289.0	303.1	317.5	332.1	348.1	363.2
150°	246.9	251.5	258.9	267.5	277.7	290.8	304.0	317.1	330.8	344.5	358.1
152.5°	252.4	257.0	263.5	271.6	280.9	292.7	304.4	316.2	328.5	341.3	353.1
155°	261.2	264.6	270.9	277.2	285.7	295.4	305.1	314.8	324.5	335.3	346.2
157.5°	268.7	271.5	276.9	282.0	289.1	297.3	305.1	312.2	320.4	329.7	338.1
160°	273.7	276.0	280.6	285.1	291.4	298.3	305.1	310.8	317.7	325.6	333.0
162.5°	277.8	280.1	283.8	287.9	292.8	298.7	304.6	309.4	315.4	322.0	328.0
165°	283.4	284.6	288.0	290.8	294.3	299.4	303.4	306.8	310.8	315.9	320.5
167.5°	288.1	289.1	291.3	293.4	295.5	299.3	302.6	304.2	306.8	310.0	313.3
170°	290.8	291.4	293.1	294.3	296.0	298.8	301.7	302.8	304.5	306.8	309.7
172.5°	293.1	292.8	294.5	295.2	296.4	298.4	300.3	301.0	301.8	303.6	305.6
175°	295.4	294.8	296.0	296.0	296.5	297.7	298.8	298.3	298.8	299.4	301.1
177.5°	296.1	295.6	296.5	296.5	296.5	297.0	297.9	297.0	296.5	297.0	297.9
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	10.4	10.6	10.7	10.7	10.7	10.7	10.3
90°	17.1	18.2	18.8	18.8	18.8	18.8	18.8
92.5°	42.7	37.9	34.3	33.9	32.1	32.5	31.6
95°	114.6	90.7	78.1	70.7	66.2	64.4	65.0
97.5°	285.3	223.6	182.4	155.1	141.1	132.8	128.0
100°	450.0	371.8	302.8	255.5	231.0	214.4	204.2
102.5°	617.4	560.3	487.1	435.7	393.8	373.2	359.3
105°	757.3	764.8	745.9	710.6	675.2	650.7	642.7
107.5°	747.1	806.4	834.0	838.4	836.5	831.6	821.0
110°	715.1	788.1	834.9	859.4	870.3	875.4	874.8



TEST NUMBER: P331683

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	677.3	755.3	808.9	843.0	861.1	870.8	873.9
115°	625.6	700.3	759.1	799.5	825.8	840.6	845.7
117.5°	583.6	651.4	706.5	747.8	775.5	791.1	795.4
120°	561.7	622.2	674.1	714.0	740.8	757.3	763.0
122.5°	543.5	600.7	647.6	683.4	709.8	724.5	729.3
125°	519.5	569.7	612.5	645.6	667.2	681.5	686.1
127.5°	496.3	543.6	583.1	611.9	632.2	644.5	648.2
130°	480.8	525.8	563.4	591.4	610.8	622.2	626.7
132.5°	466.2	507.6	542.9	570.4	589.8	600.3	604.4
135°	443.1	480.8	512.7	537.2	556.0	566.3	568.6
137.5°	424.8	454.6	482.5	504.8	521.0	530.0	533.4
140°	412.9	439.1	464.2	482.5	497.3	505.8	509.3
142.5°	402.4	425.0	446.0	463.3	476.8	484.4	485.1
145°	388.9	406.6	423.2	436.8	446.5	452.2	453.9
147.5°	378.0	391.8	403.9	415.2	422.9	426.8	427.8
150°	370.7	382.7	392.9	401.5	408.3	411.7	412.3
152.5°	364.8	374.9	383.8	390.5	396.5	399.0	399.1
155°	355.3	363.8	370.1	376.4	380.4	382.7	381.5
157.5°	345.7	352.9	357.8	362.2	365.6	366.6	366.6
160°	339.3	345.6	349.6	353.6	356.4	357.0	357.0
162.5°	333.4	338.8	341.8	345.8	347.8	348.3	347.9
165°	324.5	328.5	330.8	333.0	335.3	335.3	334.8
167.5°	316.4	319.1	321.2	322.2	323.5	323.4	322.7
170°	311.4	313.7	314.8	315.4	317.1	316.5	315.4
172.5°	306.8	308.6	309.3	309.9	310.7	310.1	309.4
175°	301.7	302.3	302.8	302.8	303.4	302.8	301.7
177.5°	297.9	298.4	298.4	298.4	298.4	297.9	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5

(END OF REPORT)