

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331412-940

Luminaire Tested: **SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331412-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6833.6 lumens  
Efficiency: N/A  
Efficacy: 104.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331412-940  
CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32
4	75	65	57	52	69	60	54	48	52	47	43	44	40	37	36	33	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	39	59	49	42	37	42	37	33	36	32	28	30	27	24	22
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	24857	24857	24857	24857
5°	27869	25020	22172	25020
10°	31936	24815	19189	24815
15°	35328	24359	16951	24359
20°	34790	23871	15454	23871
25°	31370	23222	14503	23222
30°	25922	22184	13811	22184
35°	18892	21098	13318	21098
40°	15091	19816	13044	19816
45°	13186	18333	12673	18333
50°	12396	16900	12424	16900
55°	11426	15440	12090	15440
60°	10469	13892	11580	13892
65°	9540	12500	11075	12500
70°	8658	11146	10334	11146
75°	7679	9632	9158	9632
80°	6602	7978	7373	7978
85°	5910	5910	4372	5910



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.6	2.1
10°-20°	426.3	6.2
20°-30°	618.6	9.1
30°-40°	652.8	9.6
40°-50°	578.0	8.5
50°-60°	461.3	6.8
60°-70°	313.5	4.6
70°-80°	160.7	2.4
80°-90°	43.6	0.6
90°-100°	77.8	1.1
100°-110°	241.6	3.5
110°-120°	412.9	6.0
120°-130°	543.0	7.9
130°-140°	609.4	8.9
140°-150°	597.6	8.7
150°-160°	501.2	7.3
160°-170°	332.4	4.9
170°-180°	116.2	1.7
0°-30°	1191.5	17.4
0°-40°	1844.3	27.0
0°-60°	2883.6	42.2
0°-90°	3401.5	49.8
90°-120°	732.3	10.7
90°-150°	2482.3	36.3
90°-180°	3432.0	50.2
0°-180°	6833.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1540	1540	1540	1540	1540	
5°	1720	1544	1368	1544	1720	172
15°	2114	1457	1014	1457	2114	583
25°	1761	1304	814	1304	1761	796
35°	958	1070	676	1070	958	623
45°	578	803	555	803	578	454
55°	406	548	430	548	406	364
65°	250	327	290	327	250	248
75°	123	154	147	154	123	132
85°	32	32	24	32	32	36
90°	35	1	35	1	35	17
95°	64	54	64	54	64	72
105°	230	223	230	223	230	242
115°	414	414	414	414	414	409
125°	605	603	605	603	605	539
135°	789	780	789	780	789	608
145°	957	947	957	947	957	598
155°	1091	1082	1091	1082	1091	502
165°	1179	1178	1179	1178	1179	332
175°	1221	1225	1221	1225	1221	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1610.6	1611.1	1612.0	1604.5	1603.5	1603.5	1596.9	1591.2	1584.6	1575.6	1576.5
5°	1719.5	1726.0	1728.3	1721.3	1710.6	1709.4	1699.3	1682.7	1667.4	1654.9	1646.1
7.5°	1849.4	1852.0	1846.2	1836.8	1828.9	1814.7	1796.0	1777.7	1752.0	1728.5	1710.9
10°	1947.9	1951.4	1941.3	1927.7	1916.5	1899.9	1872.7	1844.9	1811.2	1778.6	1752.6
12.5°	2022.7	2031.4	2018.5	2016.7	1997.4	1974.7	1942.3	1928.2	1880.8	1835.4	1807.5
15°	2113.5	2112.9	2114.2	2102.8	2088.7	2085.1	2050.8	2013.6	1946.7	1920.0	1873.9
17.5°	2087.2	2096.2	2100.4	2100.2	2099.9	2097.7	2086.7	2063.2	2029.6	1986.5	1933.1
20°	2024.8	2036.6	2038.4	2052.0	2059.7	2069.7	2073.9	2067.3	2046.7	2010.5	1964.4
22.5°	1928.2	1931.5	1937.1	1958.3	1975.0	2000.2	2013.3	2035.2	2027.2	2009.6	1971.0
25°	1760.9	1755.0	1775.7	1786.3	1824.8	1865.0	1894.0	1925.9	1954.4	1971.5	1960.2
27.5°	1560.0	1551.0	1582.1	1610.3	1641.6	1685.2	1730.4	1783.7	1828.1	1883.6	1902.6
30°	1390.4	1395.8	1425.4	1455.5	1502.9	1564.4	1615.3	1673.9	1737.2	1799.3	1842.5
32.5°	1207.7	1228.2	1247.0	1293.2	1334.9	1403.5	1478.0	1551.3	1630.2	1700.8	1767.7
35°	958.5	982.2	1008.3	1042.0	1100.5	1168.6	1241.4	1340.2	1447.9	1544.4	1623.6
37.5°	806.8	803.1	818.0	842.3	889.7	944.7	1028.5	1126.1	1252.9	1366.2	1478.0
40°	716.0	713.5	724.2	746.7	782.8	823.0	896.4	982.2	1099.9	1238.4	1371.5
42.5°	653.4	654.9	660.8	676.6	701.4	734.5	789.4	862.5	970.3	1100.6	1243.8
45°	577.5	581.7	588.2	595.8	610.0	637.2	668.0	720.1	805.3	914.2	1055.0
47.5°	522.8	522.9	529.6	536.3	544.7	560.1	585.1	617.9	678.0	766.6	887.7
50°	493.5	489.4	494.1	499.4	508.3	518.9	535.5	566.2	606.5	678.1	779.3
52.5°	457.5	457.6	461.9	463.9	471.8	482.5	497.6	518.9	555.4	611.4	694.6
55°	405.9	408.8	411.3	414.7	421.9	429.5	441.4	455.6	484.0	526.0	587.5
57.5°	357.4	358.3	360.7	367.5	371.9	379.1	390.3	403.1	421.6	452.7	499.0
60°	324.2	324.2	329.0	331.9	337.9	344.9	353.8	366.2	382.8	408.2	445.6
62.5°	294.0	293.5	295.3	300.2	304.7	311.4	320.2	330.7	346.3	369.0	399.7
65°	249.7	248.5	252.1	253.2	258.0	264.5	271.6	282.9	295.2	311.8	339.0
67.5°	207.1	208.5	210.4	212.7	215.3	222.1	226.9	234.8	245.3	259.0	277.5
70°	183.4	183.4	183.4	185.2	188.8	192.3	197.1	203.6	213.6	225.4	242.0
72.5°	156.9	158.8	160.7	159.6	164.2	166.3	171.9	175.6	185.2	192.8	207.4
75°	123.1	123.1	123.1	126.0	127.8	129.6	133.1	136.7	141.4	150.9	158.5
77.5°	91.8	91.6	92.2	92.9	94.8	96.9	98.0	101.2	105.6	109.9	116.5
80°	71.0	72.2	72.8	73.9	73.9	75.2	75.7	79.9	82.8	85.8	90.0
82.5°	54.9	55.1	55.3	55.5	56.0	56.7	58.2	59.6	60.5	63.0	66.3
85°	31.9	31.4	31.4	32.5	31.9	31.9	33.2	34.3	34.3	34.9	36.6
87.5°	19.4	19.3	19.7	19.2	19.2	19.7	19.8	19.4	20.0	20.5	20.0
90°	35.2	35.0	34.8	34.5	34.3	34.4	34.9	35.3	35.8	36.3	31.2
92.5°	33.5	33.5	33.4	33.4	33.3	33.3	33.2	33.1	33.0	32.9	31.7
95°	64.2	64.6	65.2	65.6	66.1	66.3	66.3	66.3	66.3	66.3	65.8
97.5°	111.3	111.3	111.4	111.4	111.5	111.5	111.5	111.5	111.5	111.5	110.6
100°	141.9	142.1	142.4	142.6	142.9	142.9	142.9	142.9	142.9	142.9	142.2
102.5°	176.7	176.9	177.2	177.4	177.6	177.6	177.5	177.3	177.1	176.9	176.0
105°	230.0	230.0	230.0	230.0	230.0	229.7	229.3	228.8	228.4	227.8	227.4
107.5°	280.1	281.2	282.2	283.3	284.3	284.7	284.5	284.4	284.2	284.0	284.0
110°	319.1	319.7	320.4	321.1	321.8	322.2	322.2	322.2	322.2	322.2	322.2



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.3	356.9	357.3	357.8	358.4	358.9	359.4	360.0	360.5	361.1	361.2
115°	414.3	415.0	415.7	416.4	417.1	417.5	417.8	418.0	418.2	418.5	418.9
117.5°	469.7	470.3	471.0	471.7	472.4	473.1	473.6	474.1	474.7	475.2	476.5
120°	508.5	509.3	510.0	510.7	511.3	511.7	511.7	511.7	511.7	511.7	513.5
122.5°	546.7	547.2	547.7	548.2	548.8	549.2	549.8	550.4	550.9	551.4	552.8
125°	604.9	605.1	605.4	605.6	605.8	606.3	607.0	607.7	608.3	609.0	609.8
127.5°	657.9	658.7	659.4	660.1	660.8	661.6	662.5	663.3	664.1	664.9	665.8
130°	696.1	697.0	697.9	698.8	699.7	700.4	700.9	701.3	701.8	702.3	702.8
132.5°	732.5	733.3	734.0	734.8	735.5	736.4	737.4	738.3	739.4	740.4	740.3
135°	789.3	790.0	790.7	791.3	792.0	792.5	792.7	793.0	793.2	793.4	793.0
137.5°	840.6	841.6	842.5	843.4	844.4	844.9	845.1	845.3	845.4	845.6	845.0
140°	876.3	877.2	878.2	879.0	879.9	880.4	880.4	880.4	880.4	880.4	879.3
142.5°	908.6	909.5	910.4	911.3	912.3	912.7	912.5	912.3	912.1	912.0	911.2
145°	957.1	958.0	958.9	959.8	960.7	961.1	960.9	960.6	960.4	960.2	958.8
147.5°	1000.4	1001.2	1002.1	1003.0	1003.9	1004.1	1003.5	1003.1	1002.6	1002.0	1001.1
150°	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6	1027.6
152.5°	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1	1054.0
155°	1090.7	1091.4	1092.1	1092.8	1093.4	1093.2	1092.1	1090.9	1089.8	1088.6	1088.0
157.5°	1121.3	1122.5	1123.6	1124.6	1125.8	1125.5	1124.0	1122.4	1120.9	1119.3	1118.8
160°	1140.4	1141.3	1142.3	1143.2	1144.1	1143.9	1142.5	1141.1	1139.7	1138.4	1138.1
162.5°	1157.0	1158.1	1159.2	1160.3	1161.4	1161.2	1159.6	1158.1	1156.5	1154.9	1154.7
165°	1178.8	1179.9	1181.1	1182.2	1183.3	1183.1	1181.5	1179.9	1178.3	1176.7	1176.7
167.5°	1196.6	1197.7	1198.9	1200.2	1201.3	1201.1	1199.5	1197.9	1196.3	1194.7	1194.7
170°	1205.7	1207.0	1208.4	1209.8	1211.2	1211.0	1209.4	1207.8	1206.2	1204.6	1204.9
172.5°	1213.1	1214.5	1215.8	1217.3	1218.6	1218.5	1216.9	1215.3	1213.7	1212.1	1212.3
175°	1221.2	1222.6	1224.0	1225.4	1226.7	1226.6	1225.0	1223.4	1221.8	1220.1	1220.7
177.5°	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9	1225.3
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1579.8	1576.0	1573.7	1565.1	1557.6	1550.0	1547.7	1548.5	1538.2	1528.2	1523.9
5°	1641.4	1629.5	1618.3	1602.3	1583.4	1562.6	1552.0	1543.7	1523.0	1500.6	1487.6
7.5°	1696.5	1679.5	1658.0	1627.9	1600.3	1567.7	1547.0	1528.7	1498.4	1466.7	1447.2
10°	1730.1	1707.0	1679.2	1642.5	1608.8	1569.1	1541.3	1513.6	1478.0	1440.2	1416.5
12.5°	1759.0	1727.9	1700.5	1653.4	1613.6	1564.0	1531.0	1491.7	1454.4	1409.4	1386.3
15°	1827.7	1770.3	1718.2	1665.0	1615.9	1546.7	1510.0	1457.3	1408.2	1352.6	1326.0
17.5°	1880.9	1816.4	1734.4	1666.7	1609.4	1532.8	1478.9	1415.8	1357.7	1294.1	1257.9
20°	1911.2	1837.2	1749.0	1668.6	1599.9	1512.3	1453.8	1389.3	1321.2	1249.6	1210.6
22.5°	1929.1	1851.4	1764.2	1661.4	1581.0	1495.8	1422.1	1351.4	1282.5	1205.1	1164.2
25°	1934.8	1863.9	1771.6	1655.6	1557.4	1460.9	1372.2	1303.5	1220.0	1147.9	1088.2
27.5°	1906.7	1855.7	1767.0	1644.4	1530.0	1417.2	1318.3	1240.5	1152.5	1074.2	1014.1
30°	1872.1	1842.5	1756.1	1633.1	1508.2	1387.0	1278.1	1189.9	1102.3	1023.1	961.5
32.5°	1818.6	1812.2	1736.3	1616.9	1485.1	1348.6	1235.9	1146.8	1049.8	971.9	913.2
35°	1713.5	1742.0	1694.0	1581.0	1441.4	1294.1	1172.2	1070.4	969.8	895.2	840.2
37.5°	1572.7	1643.2	1630.7	1528.3	1382.4	1234.7	1100.1	993.7	897.9	822.6	768.6
40°	1475.7	1565.6	1578.6	1488.1	1340.8	1188.7	1046.2	940.2	846.7	778.1	723.6
42.5°	1371.5	1476.6	1512.3	1439.8	1295.3	1140.4	997.8	888.1	795.6	728.9	680.6
45°	1197.0	1336.1	1400.5	1359.1	1219.5	1060.9	914.2	802.9	718.9	656.2	618.9
47.5°	1033.8	1185.7	1272.5	1257.8	1135.1	978.0	832.9	726.2	644.4	594.4	561.1
50°	918.3	1074.5	1179.2	1184.0	1074.5	918.9	773.4	672.8	597.6	550.9	523.6
52.5°	818.0	967.1	1081.3	1106.3	1006.8	857.4	719.9	619.7	553.6	510.6	486.2
55°	687.0	813.0	939.6	985.8	905.9	763.8	636.7	548.5	486.3	456.8	435.5
57.5°	571.1	676.2	793.1	844.1	794.9	673.3	554.0	477.5	427.0	401.2	384.9
60°	510.1	592.9	697.1	758.0	715.3	607.1	502.9	430.2	388.8	365.7	350.3
62.5°	453.3	526.6	614.7	670.4	647.2	545.1	451.8	387.5	351.8	330.2	319.1
65°	374.0	431.9	500.0	551.4	536.1	458.5	382.3	327.2	298.8	281.6	272.8
67.5°	307.9	349.8	397.0	442.1	429.7	374.8	313.4	270.6	249.5	234.7	229.3
70°	266.3	298.2	340.2	376.3	366.2	321.3	272.8	236.1	217.8	205.4	200.0
72.5°	226.5	252.8	284.8	314.3	307.6	270.2	229.7	202.0	187.9	176.5	172.1
75°	171.0	191.1	210.6	230.2	228.4	199.4	175.8	154.4	143.2	134.3	132.5
77.5°	126.3	137.5	150.8	162.4	159.2	142.6	124.0	111.8	103.5	97.6	96.7
80°	96.5	103.0	112.4	120.7	116.5	109.5	94.7	85.8	79.9	73.9	71.6
82.5°	69.9	76.4	82.1	86.6	83.5	76.8	67.7	61.6	58.1	54.0	53.1
85°	36.6	40.2	42.6	43.8	42.6	38.4	34.3	31.9	29.0	27.2	26.7
87.5°	19.4	18.4	17.4	17.6	15.6	15.1	12.6	10.6	10.7	10.8	10.3
90°	26.1	21.0	16.0	12.1	9.4	6.6	3.8	1.1	3.8	6.6	9.4
92.5°	30.6	29.3	28.2	26.6	24.5	22.5	20.4	18.5	20.4	22.5	24.5
95°	65.4	64.9	64.5	63.0	60.7	58.5	56.2	53.9	56.2	58.5	60.7
97.5°	109.7	108.8	108.0	106.5	104.5	102.5	100.4	98.4	100.4	102.5	104.5
100°	141.5	140.9	140.2	138.9	137.1	135.3	133.4	131.5	133.4	135.3	137.1
102.5°	175.1	174.3	173.4	172.3	170.8	169.3	167.8	166.4	167.8	169.3	170.8
105°	226.9	226.5	226.0	225.4	224.8	224.1	223.4	222.7	223.4	224.1	224.8
107.5°	284.0	284.0	284.0	283.5	282.5	281.5	280.4	279.5	280.4	281.5	282.5
110°	322.2	322.2	322.2	321.5	320.0	318.7	317.3	315.9	317.3	318.7	320.0





TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	361.4	361.6	361.9	361.2	359.8	358.5	357.0	355.7	357.0	358.5	359.8
115°	419.4	419.8	420.3	419.8	418.5	417.1	415.7	414.3	415.7	417.1	418.5
117.5°	477.8	479.1	480.4	480.1	478.2	476.4	474.6	472.7	474.6	476.4	478.2
120°	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	513.5	515.4	517.2
122.5°	554.0	555.4	556.6	556.2	553.9	551.7	549.6	547.3	549.6	551.7	553.9
125°	610.5	611.1	611.8	611.1	609.0	607.0	604.9	602.8	604.9	607.0	609.0
127.5°	666.6	667.4	668.3	667.4	664.8	662.2	659.5	656.9	659.5	662.2	664.8
130°	703.2	703.6	704.1	702.8	699.8	696.9	693.8	690.9	693.8	696.9	699.8
132.5°	740.2	740.1	740.0	738.8	736.3	733.9	731.5	729.0	731.5	733.9	736.3
135°	792.5	792.0	791.6	790.1	787.6	785.1	782.5	780.0	782.5	785.1	787.6
137.5°	844.5	843.8	843.2	841.9	839.8	837.8	835.7	833.6	835.7	837.8	839.8
140°	878.2	877.0	875.8	874.2	872.2	870.0	868.0	865.9	868.0	870.0	872.2
142.5°	910.3	909.5	908.7	907.3	905.3	903.2	901.2	899.1	901.2	903.2	905.3
145°	957.4	956.0	954.7	953.1	951.5	949.9	948.3	946.7	948.3	949.9	951.5
147.5°	1000.2	999.3	998.4	996.9	995.0	993.0	991.1	989.2	991.1	993.0	995.0
150°	1026.7	1025.8	1024.8	1023.7	1022.3	1020.9	1019.6	1018.2	1019.6	1020.9	1022.3
152.5°	1052.8	1051.8	1050.6	1049.4	1048.0	1046.6	1045.3	1043.8	1045.3	1046.6	1048.0
155°	1087.3	1086.5	1085.8	1085.2	1084.5	1083.8	1083.1	1082.4	1083.1	1083.8	1084.5
157.5°	1118.5	1118.0	1117.6	1117.2	1116.7	1116.2	1115.8	1115.4	1115.8	1116.2	1116.7
160°	1137.9	1137.6	1137.4	1137.1	1136.6	1136.1	1135.7	1135.2	1135.7	1136.1	1136.6
162.5°	1154.4	1154.2	1154.0	1153.9	1153.7	1153.6	1153.5	1153.4	1153.5	1153.6	1153.7
165°	1176.7	1176.7	1176.7	1176.8	1177.0	1177.2	1177.5	1177.7	1177.5	1177.2	1177.0
167.5°	1194.8	1194.8	1194.9	1195.2	1196.0	1196.6	1197.3	1198.0	1197.3	1196.6	1196.0
170°	1205.1	1205.3	1205.6	1206.0	1206.7	1207.4	1208.1	1208.8	1208.1	1207.4	1206.7
172.5°	1212.5	1212.8	1213.0	1213.4	1214.2	1214.9	1215.6	1216.2	1215.6	1214.9	1214.2
175°	1221.1	1221.6	1222.0	1222.6	1223.2	1224.0	1224.7	1225.4	1224.7	1224.0	1223.2
177.5°	1225.7	1226.0	1226.4	1226.9	1227.4	1228.0	1228.5	1229.0	1228.5	1228.0	1227.4
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1519.2	1516.4	1506.5	1501.3	1492.7	1484.7	1479.4	1481.8	1483.7	1482.7	1481.4
5°	1475.7	1464.5	1447.2	1432.4	1421.8	1402.3	1394.0	1389.9	1386.3	1382.2	1378.0
7.5°	1423.9	1406.1	1381.4	1360.4	1340.5	1316.3	1302.4	1294.1	1285.7	1276.3	1268.0
10°	1387.0	1362.1	1336.1	1306.4	1282.8	1260.9	1241.4	1228.3	1216.6	1205.2	1197.0
12.5°	1348.1	1319.5	1287.3	1246.8	1220.8	1189.5	1186.4	1163.5	1145.0	1138.1	1128.4
15°	1286.4	1246.1	1205.2	1157.4	1136.7	1108.2	1090.5	1072.7	1056.8	1045.5	1042.6
17.5°	1216.2	1164.1	1123.5	1089.0	1055.1	1026.0	1009.7	995.5	982.3	967.3	965.3
20°	1162.7	1117.7	1073.4	1043.1	1008.3	978.7	958.5	944.3	933.1	924.3	916.5
22.5°	1112.1	1062.8	1022.2	989.2	954.8	930.9	915.0	901.3	891.9	882.1	874.9
25°	1030.7	992.3	947.9	910.6	882.2	866.8	853.8	842.0	836.1	829.6	821.3
27.5°	959.6	916.9	875.4	846.5	821.5	807.9	798.7	790.6	785.1	781.2	776.5
30°	909.5	866.2	833.7	805.3	784.6	771.0	765.1	760.4	753.9	751.4	749.1
32.5°	861.1	822.2	794.4	769.8	750.0	741.2	735.8	731.5	726.4	724.0	719.3
35°	792.9	760.4	733.1	719.5	703.6	695.8	691.7	685.8	681.0	678.7	678.1
37.5°	728.6	700.3	682.4	664.9	658.2	653.4	647.8	643.7	642.3	641.9	641.4
40°	687.0	663.9	647.9	633.7	630.7	623.7	618.9	615.4	615.4	616.0	615.4
42.5°	649.1	628.4	614.3	602.0	598.5	594.3	589.6	589.3	590.3	592.3	590.3
45°	591.7	576.9	566.9	560.9	554.4	550.3	549.7	551.4	552.1	552.7	554.4
47.5°	539.0	529.1	520.0	513.4	510.6	509.9	509.2	512.3	515.1	516.2	518.9
50°	507.7	496.4	488.7	484.6	482.2	481.1	482.2	485.8	488.1	491.1	492.8
52.5°	472.6	464.7	459.4	456.2	455.2	455.9	456.2	460.2	464.0	465.0	465.9
55°	424.3	418.3	417.1	411.8	414.2	413.6	416.5	418.9	422.5	426.1	426.6
57.5°	375.9	371.2	368.0	368.5	369.3	371.8	374.3	378.4	382.3	386.0	386.4
60°	343.8	341.4	339.7	339.7	340.8	344.4	347.3	351.4	353.8	356.2	357.9
62.5°	314.4	312.1	310.3	311.2	314.3	316.5	319.9	322.1	324.5	326.8	327.7
65°	268.0	266.9	268.7	269.8	270.4	273.4	277.5	279.3	281.6	282.9	287.0
67.5°	225.3	225.5	225.3	226.9	230.4	231.1	235.1	239.2	239.6	241.9	244.6
70°	196.4	197.6	198.9	200.0	203.0	204.1	207.1	208.8	211.2	213.0	214.8
72.5°	170.0	170.1	171.4	171.1	173.6	176.2	178.7	180.5	182.8	185.1	186.8
75°	130.7	130.7	132.0	132.5	135.5	138.5	137.9	139.0	141.4	143.7	145.0
77.5°	95.5	94.2	95.5	96.1	97.0	99.5	100.0	101.7	104.3	103.5	104.9
80°	72.8	71.0	72.8	73.4	73.4	76.3	76.3	77.5	79.3	77.5	79.3
82.5°	52.0	51.1	52.4	52.5	53.5	53.6	54.6	54.8	56.5	55.7	56.5
85°	26.0	25.4	26.0	25.4	26.0	26.7	26.7	26.0	26.0	27.2	25.4
87.5°	10.4	10.8	11.3	12.3	12.8	13.4	12.8	12.8	12.7	11.6	11.6
90°	12.1	16.0	21.0	26.1	31.2	36.3	35.8	35.3	34.9	34.4	34.3
92.5°	26.6	28.2	29.3	30.6	31.7	32.9	33.0	33.1	33.2	33.3	33.3
95°	63.0	64.5	64.9	65.4	65.8	66.3	66.3	66.3	66.3	66.3	66.1
97.5°	106.5	108.0	108.8	109.7	110.6	111.5	111.5	111.5	111.5	111.5	111.5
100°	138.9	140.2	140.9	141.5	142.2	142.9	142.9	142.9	142.9	142.9	142.9
102.5°	172.3	173.4	174.3	175.1	176.0	176.9	177.1	177.3	177.5	177.6	177.6
105°	225.4	226.0	226.5	226.9	227.4	227.8	228.4	228.8	229.3	229.7	230.0
107.5°	283.5	284.0	284.0	284.0	284.0	284.0	284.2	284.4	284.5	284.7	284.3
110°	321.5	322.2	322.2	322.2	322.2	322.2	322.2	322.2	322.2	322.2	321.8



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	361.2	361.9	361.6	361.4	361.2	361.1	360.5	360.0	359.4	358.9	358.4
115°	419.8	420.3	419.8	419.4	418.9	418.5	418.2	418.0	417.8	417.5	417.1
117.5°	480.1	480.4	479.1	477.8	476.5	475.2	474.7	474.1	473.6	473.1	472.4
120°	519.1	519.1	517.2	515.4	513.5	511.7	511.7	511.7	511.7	511.7	511.3
122.5°	556.2	556.6	555.4	554.0	552.8	551.4	550.9	550.4	549.8	549.2	548.8
125°	611.1	611.8	611.1	610.5	609.8	609.0	608.3	607.7	607.0	606.3	605.8
127.5°	667.4	668.3	667.4	666.6	665.8	664.9	664.1	663.3	662.5	661.6	660.8
130°	702.8	704.1	703.6	703.2	702.8	702.3	701.8	701.3	700.9	700.4	699.7
132.5°	738.8	740.0	740.1	740.2	740.3	740.4	739.4	738.3	737.4	736.4	735.5
135°	790.1	791.6	792.0	792.5	793.0	793.4	793.2	793.0	792.7	792.5	792.0
137.5°	841.9	843.2	843.8	844.5	845.0	845.6	845.4	845.3	845.1	844.9	844.4
140°	874.2	875.8	877.0	878.2	879.3	880.4	880.4	880.4	880.4	880.4	879.9
142.5°	907.3	908.7	909.5	910.3	911.2	912.0	912.1	912.3	912.5	912.7	912.3
145°	953.1	954.7	956.0	957.4	958.8	960.2	960.4	960.6	960.9	961.1	960.7
147.5°	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6	1003.1	1003.5	1004.1	1003.9
150°	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4
152.5°	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5
155°	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8	1090.9	1092.1	1093.2	1093.4
157.5°	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9	1122.4	1124.0	1125.5	1125.8
160°	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7	1141.1	1142.5	1143.9	1144.1
162.5°	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5	1158.1	1159.6	1161.2	1161.4
165°	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3	1179.9	1181.5	1183.1	1183.3
167.5°	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3	1197.9	1199.5	1201.1	1201.3
170°	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2	1207.8	1209.4	1211.0	1211.2
172.5°	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7	1215.3	1216.9	1218.5	1218.6
175°	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8	1223.4	1225.0	1226.6	1226.7
177.5°	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331412-940  
 CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1476.6	1475.7	1475.7	1471.4	1475.7	1475.7	1476.6	1481.4	1482.7	1483.7	1481.8
5°	1369.8	1368.0	1365.0	1368.0	1365.0	1368.0	1369.8	1378.0	1382.2	1386.3	1389.9
7.5°	1264.1	1257.0	1255.9	1248.9	1255.9	1257.0	1264.1	1268.0	1276.3	1285.7	1294.1
10°	1187.0	1182.2	1181.6	1170.4	1181.6	1182.2	1187.0	1197.0	1205.2	1216.6	1228.3
12.5°	1128.3	1116.9	1119.1	1112.6	1119.1	1116.9	1128.3	1128.4	1138.1	1145.0	1163.5
15°	1026.6	1026.6	1024.2	1014.1	1024.2	1026.6	1026.6	1042.6	1045.5	1056.8	1072.7
17.5°	953.6	952.3	946.7	949.6	946.7	952.3	953.6	965.3	967.3	982.3	995.5
20°	910.0	906.5	899.4	899.4	899.4	906.5	910.0	916.5	924.3	933.1	944.3
22.5°	868.9	868.6	861.0	863.4	861.0	868.6	868.9	874.9	882.1	891.9	901.3
25°	820.6	815.9	812.4	814.1	812.4	815.9	820.6	821.3	829.6	836.1	842.0
27.5°	775.0	772.4	772.1	767.3	772.1	772.4	775.0	776.5	781.2	785.1	790.6
30°	748.5	742.6	743.8	740.8	743.8	742.6	748.5	749.1	751.4	753.9	760.4
32.5°	718.2	716.0	714.9	712.4	714.9	716.0	718.2	719.3	724.0	726.4	731.5
35°	676.9	677.5	674.5	675.7	674.5	677.5	676.9	678.1	678.7	681.0	685.8
37.5°	640.8	642.7	641.3	641.7	641.3	642.7	640.8	641.4	641.9	642.3	643.7
40°	617.2	617.2	617.2	618.9	617.2	617.2	617.2	615.4	616.0	615.4	615.4
42.5°	594.4	593.4	592.5	592.4	592.5	593.4	594.4	590.3	592.3	590.3	589.3
45°	555.6	557.4	557.9	555.0	557.9	557.4	555.6	554.4	552.7	552.1	551.4
47.5°	520.5	520.7	520.5	523.1	520.5	520.7	520.5	518.9	516.2	515.1	512.3
50°	495.9	494.6	495.9	494.6	495.9	494.6	495.9	492.8	491.1	488.1	485.8
52.5°	469.8	470.0	469.3	469.1	469.3	470.0	469.8	465.9	465.0	464.0	460.2
55°	429.0	430.2	429.5	429.5	429.5	430.2	429.0	426.6	426.1	422.5	418.9
57.5°	386.7	387.8	388.6	386.0	388.6	387.8	386.7	386.4	386.0	382.3	378.4
60°	357.4	360.3	359.7	358.6	359.7	360.3	357.4	357.9	356.2	353.8	351.4
62.5°	330.4	331.4	331.4	331.1	331.4	331.4	330.4	327.7	326.8	324.5	322.1
65°	288.7	289.9	288.1	289.9	288.1	289.9	288.7	287.0	282.9	281.6	279.3
67.5°	243.9	244.2	245.6	246.4	245.6	244.2	243.9	244.6	241.9	239.6	239.2
70°	216.0	215.3	217.1	218.9	217.1	215.3	216.0	214.8	213.0	211.2	208.8
72.5°	186.6	187.9	187.3	188.6	187.3	187.9	186.6	186.8	185.1	182.8	180.5
75°	143.7	145.5	145.0	146.8	145.0	145.5	143.7	145.0	143.7	141.4	139.0
77.5°	103.9	104.2	103.9	104.9	103.9	104.2	103.9	104.9	103.5	104.3	101.7
80°	79.3	78.1	77.0	79.3	77.0	78.1	79.3	79.3	77.5	79.3	77.5
82.5°	55.1	55.8	54.7	54.7	54.7	55.8	55.1	56.5	55.7	56.5	54.8
85°	25.4	24.9	23.6	23.6	23.6	24.9	25.4	25.4	27.2	26.0	26.0
87.5°	11.7	11.2	11.2	10.8	11.2	11.2	11.7	11.6	11.6	12.7	12.8
90°	34.5	34.8	35.0	35.2	35.0	34.8	34.5	34.3	34.4	34.9	35.3
92.5°	33.4	33.4	33.5	33.5	33.5	33.4	33.4	33.3	33.3	33.2	33.1
95°	65.6	65.2	64.6	64.2	64.6	65.2	65.6	66.1	66.3	66.3	66.3
97.5°	111.4	111.4	111.3	111.3	111.3	111.4	111.4	111.5	111.5	111.5	111.5
100°	142.6	142.4	142.1	141.9	142.1	142.4	142.6	142.9	142.9	142.9	142.9
102.5°	177.4	177.2	176.9	176.7	176.9	177.2	177.4	177.6	177.6	177.5	177.3
105°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	229.7	229.3	228.8
107.5°	283.3	282.2	281.2	280.1	281.2	282.2	283.3	284.3	284.7	284.5	284.4
110°	321.1	320.4	319.7	319.1	319.7	320.4	321.1	321.8	322.2	322.2	322.2



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	357.8	357.3	356.9	356.3	356.9	357.3	357.8	358.4	358.9	359.4	360.0
115°	416.4	415.7	415.0	414.3	415.0	415.7	416.4	417.1	417.5	417.8	418.0
117.5°	471.7	471.0	470.3	469.7	470.3	471.0	471.7	472.4	473.1	473.6	474.1
120°	510.7	510.0	509.3	508.5	509.3	510.0	510.7	511.3	511.7	511.7	511.7
122.5°	548.2	547.7	547.2	546.7	547.2	547.7	548.2	548.8	549.2	549.8	550.4
125°	605.6	605.4	605.1	604.9	605.1	605.4	605.6	605.8	606.3	607.0	607.7
127.5°	660.1	659.4	658.7	657.9	658.7	659.4	660.1	660.8	661.6	662.5	663.3
130°	698.8	697.9	697.0	696.1	697.0	697.9	698.8	699.7	700.4	700.9	701.3
132.5°	734.8	734.0	733.3	732.5	733.3	734.0	734.8	735.5	736.4	737.4	738.3
135°	791.3	790.7	790.0	789.3	790.0	790.7	791.3	792.0	792.5	792.7	793.0
137.5°	843.4	842.5	841.6	840.6	841.6	842.5	843.4	844.4	844.9	845.1	845.3
140°	879.0	878.2	877.2	876.3	877.2	878.2	879.0	879.9	880.4	880.4	880.4
142.5°	911.3	910.4	909.5	908.6	909.5	910.4	911.3	912.3	912.7	912.5	912.3
145°	959.8	958.9	958.0	957.1	958.0	958.9	959.8	960.7	961.1	960.9	960.6
147.5°	1003.0	1002.1	1001.2	1000.4	1001.2	1002.1	1003.0	1003.9	1004.1	1003.5	1003.1
150°	1030.6	1029.9	1029.2	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9
152.5°	1057.7	1056.9	1056.0	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9
155°	1092.8	1092.1	1091.4	1090.7	1091.4	1092.1	1092.8	1093.4	1093.2	1092.1	1090.9
157.5°	1124.6	1123.6	1122.5	1121.3	1122.5	1123.6	1124.6	1125.8	1125.5	1124.0	1122.4
160°	1143.2	1142.3	1141.3	1140.4	1141.3	1142.3	1143.2	1144.1	1143.9	1142.5	1141.1
162.5°	1160.3	1159.2	1158.1	1157.0	1158.1	1159.2	1160.3	1161.4	1161.2	1159.6	1158.1
165°	1182.2	1181.1	1179.9	1178.8	1179.9	1181.1	1182.2	1183.3	1183.1	1181.5	1179.9
167.5°	1200.2	1198.9	1197.7	1196.6	1197.7	1198.9	1200.2	1201.3	1201.1	1199.5	1197.9
170°	1209.8	1208.4	1207.0	1205.7	1207.0	1208.4	1209.8	1211.2	1211.0	1209.4	1207.8
172.5°	1217.3	1215.8	1214.5	1213.1	1214.5	1215.8	1217.3	1218.6	1218.5	1216.9	1215.3
175°	1225.4	1224.0	1222.6	1221.2	1222.6	1224.0	1225.4	1226.7	1226.6	1225.0	1223.4
177.5°	1228.2	1227.2	1226.0	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331412-940  
 CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1479.4	1484.7	1492.7	1501.3	1506.5	1516.4	1519.2	1523.9	1528.2	1538.2	1548.5
5°	1394.0	1402.3	1421.8	1432.4	1447.2	1464.5	1475.7	1487.6	1500.6	1523.0	1543.7
7.5°	1302.4	1316.3	1340.5	1360.4	1381.4	1406.1	1423.9	1447.2	1466.7	1498.4	1528.7
10°	1241.4	1260.9	1282.8	1306.4	1336.1	1362.1	1387.0	1416.5	1440.2	1478.0	1513.6
12.5°	1186.4	1189.5	1220.8	1246.8	1287.3	1319.5	1348.1	1386.3	1409.4	1454.4	1491.7
15°	1090.5	1108.2	1136.7	1157.4	1205.2	1246.1	1286.4	1326.0	1352.6	1408.2	1457.3
17.5°	1009.7	1026.0	1055.1	1089.0	1123.5	1164.1	1216.2	1257.9	1294.1	1357.7	1415.8
20°	958.5	978.7	1008.3	1043.1	1073.4	1117.7	1162.7	1210.6	1249.6	1321.2	1389.3
22.5°	915.0	930.9	954.8	989.2	1022.2	1062.8	1112.1	1164.2	1205.1	1282.5	1351.4
25°	853.8	866.8	882.2	910.6	947.9	992.3	1030.7	1088.2	1147.9	1220.0	1303.5
27.5°	798.7	807.9	821.5	846.5	875.4	916.9	959.6	1014.1	1074.2	1152.5	1240.5
30°	765.1	771.0	784.6	805.3	833.7	866.2	909.5	961.5	1023.1	1102.3	1189.9
32.5°	735.8	741.2	750.0	769.8	794.4	822.2	861.1	913.2	971.9	1049.8	1146.8
35°	691.7	695.8	703.6	719.5	733.1	760.4	792.9	840.2	895.2	969.8	1070.4
37.5°	647.8	653.4	658.2	664.9	682.4	700.3	728.6	768.6	822.6	897.9	993.7
40°	618.9	623.7	630.7	633.7	647.9	663.9	687.0	723.6	778.1	846.7	940.2
42.5°	589.6	594.3	598.5	602.0	614.3	628.4	649.1	680.6	728.9	795.6	888.1
45°	549.7	550.3	554.4	560.9	566.9	576.9	591.7	618.9	656.2	718.9	802.9
47.5°	509.2	509.9	510.6	513.4	520.0	529.1	539.0	561.1	594.4	644.4	726.2
50°	482.2	481.1	482.2	484.6	488.7	496.4	507.7	523.6	550.9	597.6	672.8
52.5°	456.2	455.9	455.2	456.2	459.4	464.7	472.6	486.2	510.6	553.6	619.7
55°	416.5	413.6	414.2	411.8	417.1	418.3	424.3	435.5	456.8	486.3	548.5
57.5°	374.3	371.8	369.3	368.5	368.0	371.2	375.9	384.9	401.2	427.0	477.5
60°	347.3	344.4	340.8	339.7	339.7	341.4	343.8	350.3	365.7	388.8	430.2
62.5°	319.9	316.5	314.3	311.2	310.3	312.1	314.4	319.1	330.2	351.8	387.5
65°	277.5	273.4	270.4	269.8	268.7	266.9	268.0	272.8	281.6	298.8	327.2
67.5°	235.1	231.1	230.4	226.9	225.3	225.5	225.3	229.3	234.7	249.5	270.6
70°	207.1	204.1	203.0	200.0	198.9	197.6	196.4	200.0	205.4	217.8	236.1
72.5°	178.7	176.2	173.6	171.1	171.4	170.1	170.0	172.1	176.5	187.9	202.0
75°	137.9	138.5	135.5	132.5	132.0	130.7	130.7	132.5	134.3	143.2	154.4
77.5°	100.0	99.5	97.0	96.1	95.5	94.2	95.5	96.7	97.6	103.5	111.8
80°	76.3	76.3	73.4	73.4	72.8	71.0	72.8	71.6	73.9	79.9	85.8
82.5°	54.6	53.6	53.5	52.5	52.4	51.1	52.0	53.1	54.0	58.1	61.6
85°	26.7	26.7	26.0	25.4	26.0	25.4	26.0	26.7	27.2	29.0	31.9
87.5°	12.8	13.4	12.8	12.3	11.3	10.8	10.4	10.3	10.8	10.7	10.6
90°	35.8	36.3	31.2	26.1	21.0	16.0	12.1	9.4	6.6	3.8	1.1
92.5°	33.0	32.9	31.7	30.6	29.3	28.2	26.6	24.5	22.5	20.4	18.5
95°	66.3	66.3	65.8	65.4	64.9	64.5	63.0	60.7	58.5	56.2	53.9
97.5°	111.5	111.5	110.6	109.7	108.8	108.0	106.5	104.5	102.5	100.4	98.4
100°	142.9	142.9	142.2	141.5	140.9	140.2	138.9	137.1	135.3	133.4	131.5
102.5°	177.1	176.9	176.0	175.1	174.3	173.4	172.3	170.8	169.3	167.8	166.4
105°	228.4	227.8	227.4	226.9	226.5	226.0	225.4	224.8	224.1	223.4	222.7
107.5°	284.2	284.0	284.0	284.0	284.0	284.0	283.5	282.5	281.5	280.4	279.5
110°	322.2	322.2	322.2	322.2	322.2	322.2	321.5	320.0	318.7	317.3	315.9



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	360.5	361.1	361.2	361.4	361.6	361.9	361.2	359.8	358.5	357.0	355.7
115°	418.2	418.5	418.9	419.4	419.8	420.3	419.8	418.5	417.1	415.7	414.3
117.5°	474.7	475.2	476.5	477.8	479.1	480.4	480.1	478.2	476.4	474.6	472.7
120°	511.7	511.7	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7
122.5°	550.9	551.4	552.8	554.0	555.4	556.6	556.2	553.9	551.7	549.6	547.3
125°	608.3	609.0	609.8	610.5	611.1	611.8	611.1	609.0	607.0	604.9	602.8
127.5°	664.1	664.9	665.8	666.6	667.4	668.3	667.4	664.8	662.2	659.5	656.9
130°	701.8	702.3	702.8	703.2	703.6	704.1	702.8	699.8	696.9	693.8	690.9
132.5°	739.4	740.4	740.3	740.2	740.1	740.0	738.8	736.3	733.9	731.5	729.0
135°	793.2	793.4	793.0	792.5	792.0	791.6	790.1	787.6	785.1	782.5	780.0
137.5°	845.4	845.6	845.0	844.5	843.8	843.2	841.9	839.8	837.8	835.7	833.6
140°	880.4	880.4	879.3	878.2	877.0	875.8	874.2	872.2	870.0	868.0	865.9
142.5°	912.1	912.0	911.2	910.3	909.5	908.7	907.3	905.3	903.2	901.2	899.1
145°	960.4	960.2	958.8	957.4	956.0	954.7	953.1	951.5	949.9	948.3	946.7
147.5°	1002.6	1002.0	1001.1	1000.2	999.3	998.4	996.9	995.0	993.0	991.1	989.2
150°	1029.2	1028.6	1027.6	1026.7	1025.8	1024.8	1023.7	1022.3	1020.9	1019.6	1018.2
152.5°	1056.0	1055.1	1054.0	1052.8	1051.8	1050.6	1049.4	1048.0	1046.6	1045.3	1043.8
155°	1089.8	1088.6	1088.0	1087.3	1086.5	1085.8	1085.2	1084.5	1083.8	1083.1	1082.4
157.5°	1120.9	1119.3	1118.8	1118.5	1118.0	1117.6	1117.2	1116.7	1116.2	1115.8	1115.4
160°	1139.7	1138.4	1138.1	1137.9	1137.6	1137.4	1137.1	1136.6	1136.1	1135.7	1135.2
162.5°	1156.5	1154.9	1154.7	1154.4	1154.2	1154.0	1153.9	1153.7	1153.6	1153.5	1153.4
165°	1178.3	1176.7	1176.7	1176.7	1176.7	1176.7	1176.8	1177.0	1177.2	1177.5	1177.7
167.5°	1196.3	1194.7	1194.7	1194.8	1194.8	1194.9	1195.2	1196.0	1196.6	1197.3	1198.0
170°	1206.2	1204.6	1204.9	1205.1	1205.3	1205.6	1206.0	1206.7	1207.4	1208.1	1208.8
172.5°	1213.7	1212.1	1212.3	1212.5	1212.8	1213.0	1213.4	1214.2	1214.9	1215.6	1216.2
175°	1221.8	1220.1	1220.7	1221.1	1221.6	1222.0	1222.6	1223.2	1224.0	1224.7	1225.4
177.5°	1226.0	1224.9	1225.3	1225.7	1226.0	1226.4	1226.9	1227.4	1228.0	1228.5	1229.0
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1547.7	1550.0	1557.6	1565.1	1573.7	1576.0	1579.8	1576.5	1575.6	1584.6	1591.2
5°	1552.0	1562.6	1583.4	1602.3	1618.3	1629.5	1641.4	1646.1	1654.9	1667.4	1682.7
7.5°	1547.0	1567.7	1600.3	1627.9	1658.0	1679.5	1696.5	1710.9	1728.5	1752.0	1777.7
10°	1541.3	1569.1	1608.8	1642.5	1679.2	1707.0	1730.1	1752.6	1778.6	1811.2	1844.9
12.5°	1531.0	1564.0	1613.6	1653.4	1700.5	1727.9	1759.0	1807.5	1835.4	1880.8	1928.2
15°	1510.0	1546.7	1615.9	1665.0	1718.2	1770.3	1827.7	1873.9	1920.0	1946.7	2013.6
17.5°	1478.9	1532.8	1609.4	1666.7	1734.4	1816.4	1880.9	1933.1	1986.5	2029.6	2063.2
20°	1453.8	1512.3	1599.9	1668.6	1749.0	1837.2	1911.2	1964.4	2010.5	2046.7	2067.3
22.5°	1422.1	1495.8	1581.0	1661.4	1764.2	1851.4	1929.1	1971.0	2009.6	2027.2	2035.2
25°	1372.2	1460.9	1557.4	1655.6	1771.6	1863.9	1934.8	1960.2	1971.5	1954.4	1925.9
27.5°	1318.3	1417.2	1530.0	1644.4	1767.0	1855.7	1906.7	1902.6	1883.6	1828.1	1783.7
30°	1278.1	1387.0	1508.2	1633.1	1756.1	1842.5	1872.1	1842.5	1799.3	1737.2	1673.9
32.5°	1235.9	1348.6	1485.1	1616.9	1736.3	1812.2	1818.6	1767.7	1700.8	1630.2	1551.3
35°	1172.2	1294.1	1441.4	1581.0	1694.0	1742.0	1713.5	1623.6	1544.4	1447.9	1340.2
37.5°	1100.1	1234.7	1382.4	1528.3	1630.7	1643.2	1572.7	1478.0	1366.2	1252.9	1126.1
40°	1046.2	1188.7	1340.8	1488.1	1578.6	1565.6	1475.7	1371.5	1238.4	1099.9	982.2
42.5°	997.8	1140.4	1295.3	1439.8	1512.3	1476.6	1371.5	1243.8	1100.6	970.3	862.5
45°	914.2	1060.9	1219.5	1359.1	1400.5	1336.1	1197.0	1055.0	914.2	805.3	720.1
47.5°	832.9	978.0	1135.1	1257.8	1272.5	1185.7	1033.8	887.7	766.6	678.0	617.9
50°	773.4	918.9	1074.5	1184.0	1179.2	1074.5	918.3	779.3	678.1	606.5	566.2
52.5°	719.9	857.4	1006.8	1106.3	1081.3	967.1	818.0	694.6	611.4	555.4	518.9
55°	636.7	763.8	905.9	985.8	939.6	813.0	687.0	587.5	526.0	484.0	455.6
57.5°	554.0	673.3	794.9	844.1	793.1	676.2	571.1	499.0	452.7	421.6	403.1
60°	502.9	607.1	715.3	758.0	697.1	592.9	510.1	445.6	408.2	382.8	366.2
62.5°	451.8	545.1	647.2	670.4	614.7	526.6	453.3	399.7	369.0	346.3	330.7
65°	382.3	458.5	536.1	551.4	500.0	431.9	374.0	339.0	311.8	295.2	282.9
67.5°	313.4	374.8	429.7	442.1	397.0	349.8	307.9	277.5	259.0	245.3	234.8
70°	272.8	321.3	366.2	376.3	340.2	298.2	266.3	242.0	225.4	213.6	203.6
72.5°	229.7	270.2	307.6	314.3	284.8	252.8	226.5	207.4	192.8	185.2	175.6
75°	175.8	199.4	228.4	230.2	210.6	191.1	171.0	158.5	150.9	141.4	136.7
77.5°	124.0	142.6	159.2	162.4	150.8	137.5	126.3	116.5	109.9	105.6	101.2
80°	94.7	109.5	116.5	120.7	112.4	103.0	96.5	90.0	85.8	82.8	79.9
82.5°	67.7	76.8	83.5	86.6	82.1	76.4	69.9	66.3	63.0	60.5	59.6
85°	34.3	38.4	42.6	43.8	42.6	40.2	36.6	36.6	34.9	34.3	34.3
87.5°	12.6	15.1	15.6	17.6	17.4	18.4	19.4	20.0	20.5	20.0	19.4
90°	3.8	6.6	9.4	12.1	16.0	21.0	26.1	31.2	36.3	35.8	35.3
92.5°	20.4	22.5	24.5	26.6	28.2	29.3	30.6	31.7	32.9	33.0	33.1
95°	56.2	58.5	60.7	63.0	64.5	64.9	65.4	65.8	66.3	66.3	66.3
97.5°	100.4	102.5	104.5	106.5	108.0	108.8	109.7	110.6	111.5	111.5	111.5
100°	133.4	135.3	137.1	138.9	140.2	140.9	141.5	142.2	142.9	142.9	142.9
102.5°	167.8	169.3	170.8	172.3	173.4	174.3	175.1	176.0	176.9	177.1	177.3
105°	223.4	224.1	224.8	225.4	226.0	226.5	226.9	227.4	227.8	228.4	228.8
107.5°	280.4	281.5	282.5	283.5	284.0	284.0	284.0	284.0	284.0	284.2	284.4
110°	317.3	318.7	320.0	321.5	322.2	322.2	322.2	322.2	322.2	322.2	322.2





TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	357.0	358.5	359.8	361.2	361.9	361.6	361.4	361.2	361.1	360.5	360.0
115°	415.7	417.1	418.5	419.8	420.3	419.8	419.4	418.9	418.5	418.2	418.0
117.5°	474.6	476.4	478.2	480.1	480.4	479.1	477.8	476.5	475.2	474.7	474.1
120°	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	511.7	511.7
122.5°	549.6	551.7	553.9	556.2	556.6	555.4	554.0	552.8	551.4	550.9	550.4
125°	604.9	607.0	609.0	611.1	611.8	611.1	610.5	609.8	609.0	608.3	607.7
127.5°	659.5	662.2	664.8	667.4	668.3	667.4	666.6	665.8	664.9	664.1	663.3
130°	693.8	696.9	699.8	702.8	704.1	703.6	703.2	702.8	702.3	701.8	701.3
132.5°	731.5	733.9	736.3	738.8	740.0	740.1	740.2	740.3	740.4	739.4	738.3
135°	782.5	785.1	787.6	790.1	791.6	792.0	792.5	793.0	793.4	793.2	793.0
137.5°	835.7	837.8	839.8	841.9	843.2	843.8	844.5	845.0	845.6	845.4	845.3
140°	868.0	870.0	872.2	874.2	875.8	877.0	878.2	879.3	880.4	880.4	880.4
142.5°	901.2	903.2	905.3	907.3	908.7	909.5	910.3	911.2	912.0	912.1	912.3
145°	948.3	949.9	951.5	953.1	954.7	956.0	957.4	958.8	960.2	960.4	960.6
147.5°	991.1	993.0	995.0	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6	1003.1
150°	1019.6	1020.9	1022.3	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2	1029.9
152.5°	1045.3	1046.6	1048.0	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0	1056.9
155°	1083.1	1083.8	1084.5	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8	1090.9
157.5°	1115.8	1116.2	1116.7	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9	1122.4
160°	1135.7	1136.1	1136.6	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7	1141.1
162.5°	1153.5	1153.6	1153.7	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5	1158.1
165°	1177.5	1177.2	1177.0	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3	1179.9
167.5°	1197.3	1196.6	1196.0	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3	1197.9
170°	1208.1	1207.4	1206.7	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2	1207.8
172.5°	1215.6	1214.9	1214.2	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7	1215.3
175°	1224.7	1224.0	1223.2	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8	1223.4
177.5°	1228.5	1228.0	1227.4	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0	1227.2
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1596.9	1603.5	1603.5	1604.5	1612.0	1611.1	1610.6
5°	1699.3	1709.4	1710.6	1721.3	1728.3	1726.0	1719.5
7.5°	1796.0	1814.7	1828.9	1836.8	1846.2	1852.0	1849.4
10°	1872.7	1899.9	1916.5	1927.7	1941.3	1951.4	1947.9
12.5°	1942.3	1974.7	1997.4	2016.7	2018.5	2031.4	2022.7
15°	2050.8	2085.1	2088.7	2102.8	2114.2	2112.9	2113.5
17.5°	2086.7	2097.7	2099.9	2100.2	2100.4	2096.2	2087.2
20°	2073.9	2069.7	2059.7	2052.0	2038.4	2036.6	2024.8
22.5°	2013.3	2000.2	1975.0	1958.3	1937.1	1931.5	1928.2
25°	1894.0	1865.0	1824.8	1786.3	1775.7	1755.0	1760.9
27.5°	1730.4	1685.2	1641.6	1610.3	1582.1	1551.0	1560.0
30°	1615.3	1564.4	1502.9	1455.5	1425.4	1395.8	1390.4
32.5°	1478.0	1403.5	1334.9	1293.2	1247.0	1228.2	1207.7
35°	1241.4	1168.6	1100.5	1042.0	1008.3	982.2	958.5
37.5°	1028.5	944.7	889.7	842.3	818.0	803.1	806.8
40°	896.4	823.0	782.8	746.7	724.2	713.5	716.0
42.5°	789.4	734.5	701.4	676.6	660.8	654.9	653.4
45°	668.0	637.2	610.0	595.8	588.2	581.7	577.5
47.5°	585.1	560.1	544.7	536.3	529.6	522.9	522.8
50°	535.5	518.9	508.3	499.4	494.1	489.4	493.5
52.5°	497.6	482.5	471.8	463.9	461.9	457.6	457.5
55°	441.4	429.5	421.9	414.7	411.3	408.8	405.9
57.5°	390.3	379.1	371.9	367.5	360.7	358.3	357.4
60°	353.8	344.9	337.9	331.9	329.0	324.2	324.2
62.5°	320.2	311.4	304.7	300.2	295.3	293.5	294.0
65°	271.6	264.5	258.0	253.2	252.1	248.5	249.7
67.5°	226.9	222.1	215.3	212.7	210.4	208.5	207.1
70°	197.1	192.3	188.8	185.2	183.4	183.4	183.4
72.5°	171.9	166.3	164.2	159.6	160.7	158.8	156.9
75°	133.1	129.6	127.8	126.0	123.1	123.1	123.1
77.5°	98.0	96.9	94.8	92.9	92.2	91.6	91.8
80°	75.7	75.2	73.9	73.9	72.8	72.2	71.0
82.5°	58.2	56.7	56.0	55.5	55.3	55.1	54.9
85°	33.2	31.9	31.9	32.5	31.4	31.4	31.9
87.5°	19.8	19.7	19.2	19.2	19.7	19.3	19.4
90°	34.9	34.4	34.3	34.5	34.8	35.0	35.2
92.5°	33.2	33.3	33.3	33.4	33.4	33.5	33.5
95°	66.3	66.3	66.1	65.6	65.2	64.6	64.2
97.5°	111.5	111.5	111.5	111.4	111.4	111.3	111.3
100°	142.9	142.9	142.9	142.6	142.4	142.1	141.9
102.5°	177.5	177.6	177.6	177.4	177.2	176.9	176.7
105°	229.3	229.7	230.0	230.0	230.0	230.0	230.0
107.5°	284.5	284.7	284.3	283.3	282.2	281.2	280.1
110°	322.2	322.2	321.8	321.1	320.4	319.7	319.1



TEST NUMBER: P331412-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	359.4	358.9	358.4	357.8	357.3	356.9	356.3
115°	417.8	417.5	417.1	416.4	415.7	415.0	414.3
117.5°	473.6	473.1	472.4	471.7	471.0	470.3	469.7
120°	511.7	511.7	511.3	510.7	510.0	509.3	508.5
122.5°	549.8	549.2	548.8	548.2	547.7	547.2	546.7
125°	607.0	606.3	605.8	605.6	605.4	605.1	604.9
127.5°	662.5	661.6	660.8	660.1	659.4	658.7	657.9
130°	700.9	700.4	699.7	698.8	697.9	697.0	696.1
132.5°	737.4	736.4	735.5	734.8	734.0	733.3	732.5
135°	792.7	792.5	792.0	791.3	790.7	790.0	789.3
137.5°	845.1	844.9	844.4	843.4	842.5	841.6	840.6
140°	880.4	880.4	879.9	879.0	878.2	877.2	876.3
142.5°	912.5	912.7	912.3	911.3	910.4	909.5	908.6
145°	960.9	961.1	960.7	959.8	958.9	958.0	957.1
147.5°	1003.5	1004.1	1003.9	1003.0	1002.1	1001.2	1000.4
150°	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6
152.5°	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1
155°	1092.1	1093.2	1093.4	1092.8	1092.1	1091.4	1090.7
157.5°	1124.0	1125.5	1125.8	1124.6	1123.6	1122.5	1121.3
160°	1142.5	1143.9	1144.1	1143.2	1142.3	1141.3	1140.4
162.5°	1159.6	1161.2	1161.4	1160.3	1159.2	1158.1	1157.0
165°	1181.5	1183.1	1183.3	1182.2	1181.1	1179.9	1178.8
167.5°	1199.5	1201.1	1201.3	1200.2	1198.9	1197.7	1196.6
170°	1209.4	1211.0	1211.2	1209.8	1208.4	1207.0	1205.7
172.5°	1216.9	1218.5	1218.6	1217.3	1215.8	1214.5	1213.1
175°	1225.0	1226.6	1226.7	1225.4	1224.0	1222.6	1221.2
177.5°	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4

(END OF REPORT)