

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331419-940

Luminaire Tested: **SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331419-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6883.9 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331419-940  
CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331419-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	69	81	74	69	65	62	58	55	51	48	46	40	39	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21	18
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331419-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.7	1.7
10°-20°	325.6	4.7
20°-30°	478.6	7.0
30°-40°	555.9	8.1
40°-50°	555.3	8.1
50°-60°	484.3	7.0
60°-70°	358.1	5.2
70°-80°	202.8	2.9
80°-90°	59.4	0.9
90°-100°	215.4	3.1
100°-110°	730.9	10.6
110°-120°	776.4	11.3
120°-130°	639.2	9.3
130°-140°	513.3	7.5
140°-150°	387.9	5.6
150°-160°	272.6	4.0
160°-170°	160.5	2.3
170°-180°	52.2	0.8
0°-30°	919.9	13.4
0°-40°	1475.8	21.4
0°-60°	2515.4	36.5
0°-90°	3135.6	45.5
90°-120°	1722.7	25.0
90°-150°	3263.0	47.4
90°-180°	3748.0	54.4
0°-180°	6883.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	1	14	35	34	34	4
95°	36	89	406	153	118	38
105°	126	191	768	1372	1167	134
115°	223	281	642	1325	1536	221
125°	311	368	617	1074	1246	276
135°	365	435	610	902	1033	282
145°	416	479	607	754	825	261
155°	473	511	589	667	693	218
165°	516	531	564	599	608	145
175°	538	538	543	550	548	51
180°	539	539	539	539	539	



TEST NUMBER: P331419-940  
 CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.2	17.5	17.8	17.8	17.8	18.0	18.6	19.7	20.5	20.3	19.4
90°	1.1	4.1	8.3	10.3	12.4	15.5	20.7	28.0	34.2	35.2	34.2
92.5°	12.7	18.2	25.7	30.2	37.3	47.0	70.4	103.3	132.8	134.6	113.8
95°	36.3	40.4	50.7	60.1	76.7	101.5	149.2	239.2	359.4	406.1	355.3
97.5°	59.0	64.6	75.6	89.7	108.8	137.0	196.8	322.4	522.1	693.2	727.2
100°	79.7	82.8	92.2	108.8	129.5	158.5	213.4	339.7	563.5	818.3	967.5
102.5°	98.8	101.1	110.4	127.0	148.6	177.5	228.3	340.6	547.8	822.5	1057.0
105°	126.4	130.5	137.8	153.3	176.1	205.1	253.8	346.0	516.9	767.6	1043.1
107.5°	156.2	159.5	166.6	180.8	203.5	232.6	279.9	360.3	501.6	708.7	952.2
110°	176.1	180.2	186.5	199.9	221.7	251.7	297.3	371.8	498.3	680.6	895.0



TEST NUMBER: P331419-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	194.3	198.5	205.5	218.1	239.1	269.9	313.9	384.3	499.1	662.4	855.2
115°	222.7	227.9	234.1	246.6	267.2	295.2	339.7	403.0	503.5	642.2	805.9
117.5°	252.2	256.3	262.5	273.5	293.4	322.4	363.6	422.8	510.9	632.5	774.8
120°	270.4	274.5	280.7	290.1	310.8	339.7	380.1	436.1	515.9	626.7	758.2
122.5°	287.8	291.1	297.3	307.5	328.1	358.0	395.9	447.7	521.7	623.4	744.1
125°	310.8	313.9	320.1	332.5	353.2	382.3	419.5	466.2	530.4	617.4	724.1
127.5°	329.0	333.1	341.9	355.5	375.4	405.2	441.5	483.3	539.3	613.9	705.4
130°	339.7	343.9	354.3	368.8	389.5	418.5	454.8	494.1	545.9	612.2	693.0
132.5°	349.7	354.7	365.9	381.2	402.8	431.8	466.4	504.9	552.5	611.4	683.1
135°	364.6	368.8	381.2	396.7	420.5	449.6	482.7	519.0	560.4	610.1	669.1
137.5°	378.7	383.7	396.1	412.7	436.3	463.2	496.0	529.8	567.5	609.9	659.4
140°	389.5	393.6	406.1	422.7	445.4	472.3	503.5	535.6	570.8	609.1	653.6
142.5°	400.3	403.6	415.2	431.8	453.7	479.0	509.3	540.6	573.3	609.1	647.8
145°	416.4	420.5	431.0	446.5	467.2	490.0	517.9	547.0	576.0	607.0	640.2
147.5°	433.8	436.9	446.8	461.2	478.4	498.6	525.0	550.5	576.8	603.3	632.3
150°	445.4	448.5	456.8	470.3	485.8	504.4	528.3	552.1	576.0	600.8	625.6
152.5°	457.0	458.5	466.7	478.6	493.3	510.2	531.6	552.9	574.3	596.6	619.8
155°	473.4	474.4	480.6	492.0	503.5	519.0	536.5	554.2	571.8	589.4	609.1
157.5°	487.1	488.1	493.1	503.0	512.1	525.2	540.1	554.2	567.0	581.9	599.0
160°	496.1	497.2	501.3	509.6	517.9	529.3	541.8	554.2	564.5	577.0	591.5
162.5°	505.3	504.7	508.8	515.4	522.9	531.8	542.6	553.4	562.0	572.8	584.9
165°	515.9	514.9	516.9	523.1	528.3	534.5	543.9	551.1	557.3	564.5	573.9
167.5°	524.6	523.3	525.2	529.1	532.9	536.8	543.6	549.7	552.5	557.3	563.1
170°	530.4	528.3	529.3	532.4	534.5	537.6	542.8	548.0	550.0	553.1	557.3
172.5°	533.7	532.4	531.8	534.9	536.2	538.4	542.0	545.5	546.7	548.2	551.5
175°	537.6	536.5	535.6	537.6	537.6	538.7	540.7	542.8	541.8	542.8	543.9
177.5°	539.5	537.8	537.0	538.7	538.7	538.7	539.5	541.2	539.5	538.7	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331419-940  
 CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	18.6	17.6	17.4	17.1	16.9	16.8	16.5	16.3
90°	33.2	31.1	33.2	34.2	34.2	34.2	34.2	34.2
92.5°	90.3	77.5	68.8	62.3	61.5	58.2	59.0	57.4
95°	271.4	208.2	164.7	141.9	128.4	120.2	117.1	118.1
97.5°	633.3	518.2	406.1	331.3	281.8	256.3	241.1	232.5
100°	945.7	817.3	675.4	550.0	464.0	419.5	389.5	370.9
102.5°	1150.5	1121.4	1017.6	884.8	791.4	715.4	677.9	652.6
105°	1258.6	1375.6	1389.1	1355.0	1290.7	1226.5	1182.0	1167.4
107.5°	1180.7	1357.0	1464.7	1514.8	1523.0	1519.4	1510.5	1491.2
110°	1113.6	1299.0	1431.6	1516.5	1561.0	1580.7	1590.1	1589.0





TEST NUMBER: P331419-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1052.2	1230.2	1371.9	1469.3	1531.2	1564.1	1581.8	1587.3
115°	976.9	1136.4	1272.0	1378.8	1452.3	1499.9	1526.9	1536.2
117.5°	920.1	1060.2	1183.2	1283.3	1358.3	1408.5	1437.0	1444.8
120°	891.9	1020.3	1130.2	1224.4	1296.9	1345.6	1375.6	1386.0
122.5°	869.5	987.2	1091.2	1176.3	1241.4	1289.2	1316.0	1324.6
125°	837.0	943.7	1034.8	1112.5	1172.6	1212.0	1237.9	1246.2
127.5°	804.9	901.4	987.4	1059.1	1111.5	1148.3	1170.7	1177.4
130°	784.2	873.3	955.1	1023.4	1074.2	1109.5	1130.2	1138.4
132.5°	764.3	846.8	921.9	986.1	1036.1	1071.3	1090.4	1097.8
135°	736.5	804.9	873.3	931.2	975.8	1010.0	1028.6	1032.8
137.5°	714.3	771.5	825.8	876.4	916.9	946.4	962.8	968.9
140°	700.3	750.0	797.6	843.2	876.4	903.3	918.8	925.1
142.5°	688.7	730.9	772.0	810.0	841.5	866.0	879.9	881.1
145°	672.3	706.5	738.6	768.7	793.4	811.1	821.4	824.6
147.5°	659.7	686.6	711.7	733.6	754.1	768.2	775.3	777.1
150°	650.5	673.3	695.1	713.7	729.2	741.7	747.9	748.9
152.5°	641.4	662.5	681.0	697.1	709.4	720.1	724.7	724.9
155°	628.7	645.3	660.8	672.3	683.7	690.9	695.1	693.0
157.5°	614.0	627.9	641.0	649.9	658.0	664.0	665.8	665.8
160°	604.9	616.4	627.8	635.0	642.2	647.4	648.5	648.5
162.5°	595.8	605.6	615.3	620.9	628.1	631.7	632.7	631.9
165°	582.2	589.4	596.6	600.8	604.9	609.1	609.1	608.1
167.5°	569.1	574.7	579.7	583.4	585.2	587.5	587.4	586.1
170°	562.5	565.6	569.7	571.8	572.8	576.0	574.9	572.8
172.5°	555.0	557.3	560.6	561.9	562.9	564.4	563.3	562.0
175°	547.0	548.0	549.0	550.0	550.0	551.1	550.0	548.0
177.5°	541.2	541.2	542.0	542.0	542.0	542.0	541.2	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7

(END OF REPORT)