

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331685

Luminaire Tested: **SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331685
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4212.3 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331685
CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331685

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	92	88	92	89	85	83	76	74	72	65	63	62	55	53	52	47
2	91	84	78	73	84	78	73	69	68	64	60	58	55	52	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	77	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	31
5	70	59	51	45	65	55	48	43	48	43	39	42	38	34	36	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	35	30	37	31	27	32	27	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331685

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	2.5
10°-20°	289.9	6.9
20°-30°	407.1	9.7
30°-40°	443.9	10.5
40°-50°	408.2	9.7
50°-60°	320.6	7.6
60°-70°	209.0	5.0
70°-80°	107.8	2.6
80°-90°	30.7	0.7
90°-100°	42.8	1.0
100°-110°	133.0	3.2
110°-120°	227.3	5.4
120°-130°	298.9	7.1
130°-140°	335.5	8.0
140°-150°	329.0	7.8
150°-160°	275.9	6.6
160°-170°	183.0	4.3
170°-180°	64.0	1.5
0°-30°	802.6	19.1
0°-40°	1246.6	29.6
0°-60°	1975.3	46.9
0°-90°	2322.8	55.1
90°-120°	403.1	9.6
90°-150°	1366.6	32.4
90°-180°	1889.0	44.8
0°-180°	4212.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	1	8	20	19	19	3
95°	30	35	36	36	35	34
105°	123	124	126	127	127	129
115°	228	231	230	230	228	226
125°	332	337	335	334	333	296
135°	429	435	437	436	434	332
145°	521	525	529	529	527	325
155°	596	598	599	602	600	274
165°	648	648	648	651	649	183
175°	675	673	672	675	672	64
180°	676	676	676	676	676	



TEST NUMBER: P331685

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.2	12.0	10.9	9.7	8.6	8.3	8.9	9.4	10.0	10.5	10.3
90°	0.6	2.1	3.6	5.1	6.7	8.8	11.6	14.4	17.2	20.0	19.7
92.5°	10.2	11.3	12.4	13.5	14.6	15.5	16.2	16.8	17.5	18.1	18.2
95°	29.7	30.9	32.2	33.5	34.7	35.5	35.7	36.0	36.2	36.5	36.5
97.5°	54.2	55.3	56.4	57.5	58.6	59.4	59.9	60.4	60.9	61.4	61.4
100°	72.4	73.4	74.4	75.5	76.5	77.2	77.6	77.9	78.3	78.7	78.7
102.5°	91.6	92.4	93.2	94.0	94.8	95.5	96.0	96.4	96.9	97.4	97.5
105°	122.6	123.0	123.4	123.7	124.1	124.4	124.7	124.9	125.2	125.5	125.7
107.5°	153.9	154.4	155.0	155.5	156.1	156.4	156.4	156.4	156.4	156.4	156.5
110°	173.9	174.7	175.4	176.2	177.0	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331685

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	195.8	196.6	197.3	198.1	198.9	199.2	199.1	199.0	198.9	198.8	198.5
115°	228.1	228.9	229.6	230.4	231.1	231.4	231.1	230.9	230.6	230.4	230.3
117.5°	260.3	261.3	262.3	263.3	264.3	264.5	263.8	263.0	262.3	261.6	261.3
120°	281.7	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	281.7
122.5°	301.3	302.5	303.8	305.0	306.2	306.4	305.7	305.0	304.3	303.6	303.3
125°	331.9	333.0	334.2	335.3	336.4	336.8	336.4	336.1	335.7	335.3	334.9
127.5°	361.6	363.1	364.5	366.0	367.4	367.9	367.5	367.0	366.6	366.1	365.6
130°	380.4	382.0	383.6	385.3	386.9	387.6	387.4	387.1	386.9	386.6	386.4
132.5°	401.3	402.7	404.0	405.4	406.7	407.4	407.5	407.5	407.6	407.6	407.1
135°	429.4	430.8	432.2	433.6	435.0	435.8	436.0	436.3	436.6	436.8	436.7
137.5°	458.9	460.1	461.2	462.4	463.5	464.2	464.6	464.9	465.2	465.5	465.4
140°	476.7	477.9	479.0	480.1	481.3	482.2	482.8	483.4	484.1	484.7	484.7
142.5°	495.0	496.1	497.3	498.4	499.5	500.3	500.8	501.2	501.6	502.0	502.1
145°	521.2	522.1	523.0	523.9	524.8	525.6	526.3	527.1	527.9	528.6	528.7
147.5°	544.6	545.6	546.7	547.8	548.8	549.6	550.1	550.6	551.1	551.7	551.9
150°	560.6	561.3	562.1	562.8	563.6	564.2	564.7	565.2	565.7	566.3	566.6
152.5°	574.7	575.5	576.2	577.0	577.7	578.4	579.0	579.6	580.2	580.9	581.3
155°	595.9	596.3	596.7	597.0	597.4	597.8	598.2	598.6	598.9	599.3	600.0
157.5°	614.0	614.3	614.5	614.8	615.1	615.3	615.5	615.8	616.0	616.2	617.1
160°	625.0	625.2	625.5	625.7	626.0	626.2	626.3	626.4	626.6	626.7	627.5
162.5°	635.0	635.1	635.1	635.2	635.2	635.3	635.4	635.6	635.7	635.8	636.7
165°	648.4	648.2	648.1	648.0	647.9	647.8	647.8	647.8	647.8	647.8	648.7
167.5°	659.5	659.2	658.8	658.4	658.0	657.8	657.8	657.8	657.7	657.7	658.6
170°	665.5	665.1	664.7	664.3	664.0	663.7	663.6	663.4	663.3	663.2	664.1
172.5°	669.6	669.2	668.8	668.4	668.1	667.8	667.7	667.6	667.4	667.3	668.2
175°	674.6	674.2	673.8	673.5	673.1	672.8	672.5	672.3	672.0	671.7	672.6
177.5°	676.7	676.3	676.0	675.7	675.4	675.2	675.0	674.8	674.6	674.4	675.0
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331685

CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	10.1	9.8	9.6	9.5	9.5	9.5	9.6	9.6
90°	19.5	19.2	18.9	18.9	19.0	19.1	19.3	19.4
92.5°	18.2	18.3	18.3	18.4	18.4	18.4	18.5	18.5
95°	36.5	36.5	36.5	36.4	36.1	35.9	35.6	35.4
97.5°	61.4	61.4	61.4	61.3	61.3	61.3	61.3	61.2
100°	78.7	78.7	78.7	78.6	78.5	78.4	78.3	78.1
102.5°	97.6	97.7	97.8	97.8	97.7	97.5	97.4	97.3
105°	126.0	126.2	126.5	126.6	126.6	126.6	126.6	126.6
107.5°	156.6	156.7	156.8	156.5	155.9	155.4	154.8	154.2
110°	177.3	177.3	177.3	177.2	176.8	176.4	176.0	175.6



TEST NUMBER: P331685
CATALOG NUMBER: SA2XXRDIP-C675D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	197.9	197.6	197.3	197.0	196.7	196.4	196.2
115°	230.1	230.0	229.9	229.6	229.2	228.9	228.5	228.1
117.5°	261.0	260.7	260.4	260.1	259.7	259.3	258.9	258.5
120°	281.7	281.7	281.7	281.5	281.1	280.8	280.4	280.0
122.5°	303.0	302.7	302.4	302.1	301.8	301.5	301.3	301.0
125°	334.5	334.2	333.8	333.5	333.4	333.3	333.1	333.0
127.5°	365.2	364.7	364.3	363.8	363.4	363.0	362.6	362.2
130°	386.1	385.9	385.6	385.2	384.7	384.2	383.7	383.2
132.5°	406.5	405.9	405.4	404.9	404.5	404.1	403.7	403.3
135°	436.6	436.4	436.3	436.0	435.7	435.3	434.9	434.5
137.5°	465.3	465.2	465.1	464.8	464.3	463.8	463.3	462.8
140°	484.7	484.7	484.7	484.5	483.9	483.4	482.9	482.4
142.5°	502.2	502.3	502.4	502.2	501.7	501.2	500.7	500.2
145°	528.9	529.0	529.1	528.9	528.4	527.9	527.4	526.9
147.5°	552.2	552.5	552.8	552.7	552.2	551.7	551.2	550.7
150°	567.0	567.4	567.8	567.8	567.4	567.0	566.6	566.3
152.5°	581.8	582.3	582.8	582.8	582.3	581.8	581.3	580.9
155°	600.6	601.2	601.9	602.0	601.6	601.2	600.8	600.5
157.5°	617.9	618.8	619.7	619.8	619.2	618.6	618.0	617.3
160°	628.2	629.0	629.7	629.9	629.4	628.9	628.3	627.8
162.5°	637.5	638.4	639.3	639.4	638.8	638.2	637.6	637.0
165°	649.6	650.5	651.3	651.5	650.8	650.2	649.6	648.9
167.5°	659.5	660.4	661.3	661.4	660.7	660.1	659.4	658.7
170°	665.0	665.9	666.7	666.8	666.0	665.3	664.5	663.8
172.5°	669.1	670.0	670.8	670.9	670.2	669.4	668.6	667.9
175°	673.5	674.4	675.3	675.4	674.6	673.8	673.1	672.3
177.5°	675.6	676.2	676.8	676.8	676.2	675.6	675.0	674.4
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7

(END OF REPORT)