

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331688

Luminaire Tested: **SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331688  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5132.5 lumens  
Efficiency: N/A  
Efficacy: 111.8 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	91	88	91	87	84	81	74	72	70	62	60	59	50	49	48	43
2	90	83	78	73	83	77	72	68	66	62	59	55	53	50	45	44	42	37
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37	33
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	32	29
5	70	59	52	46	65	55	49	43	48	43	39	41	37	34	34	31	29	26
6	65	54	46	40	60	50	43	38	43	38	34	37	33	30	31	28	26	23
7	60	49	41	36	56	46	39	34	40	34	30	34	30	27	29	26	23	21
8	56	45	37	32	52	42	35	31	36	31	27	31	27	24	27	24	21	19
9	53	41	34	29	49	38	32	28	34	28	25	29	25	22	25	22	20	17
10	49	38	31	26	46	35	29	25	31	26	23	27	23	20	23	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.3	2.7
10°-20°	388.0	7.6
20°-30°	500.0	9.7
30°-40°	475.2	9.3
40°-50°	407.1	7.9
50°-60°	310.0	6.0
60°-70°	196.0	3.8
70°-80°	97.9	1.9
80°-90°	29.2	0.6
90°-100°	58.7	1.1
100°-110°	182.3	3.6
110°-120°	311.6	6.1
120°-130°	409.8	8.0
130°-140°	459.9	9.0
140°-150°	450.9	8.8
150°-160°	378.2	7.4
160°-170°	250.9	4.9
170°-180°	87.7	1.7
0°-30°	1027.3	20.0
0°-40°	1502.5	29.3
0°-60°	2219.6	43.2
0°-90°	2542.6	49.5
90°-120°	552.6	10.8
90°-150°	1873.2	36.5
90°-180°	2590.0	50.5
0°-180°	5132.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	20
90°	27	1	27	1	27	12
95°	48	41	48	41	48	54
105°	174	168	174	168	174	182
115°	313	313	313	313	313	309
125°	456	455	456	455	456	407
135°	596	589	596	589	596	458
145°	722	714	722	714	722	451
155°	823	817	823	817	823	379
165°	890	889	890	889	890	251
175°	922	925	922	925	922	88
180°	926	926	926	926	926	



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	11.8	12.2	12.2	12.2	12.1	12.1	12.2	12.7	12.3	12.8	11.6
90°	26.6	26.4	26.2	26.1	25.9	26.0	26.3	26.7	27.0	27.4	23.5
92.5°	25.3	25.3	25.3	25.2	25.2	25.1	25.1	25.0	24.9	24.9	24.0
95°	48.5	48.8	49.2	49.5	49.9	50.0	50.0	50.0	50.0	50.0	49.7
97.5°	83.9	84.0	84.0	84.1	84.1	84.1	84.1	84.1	84.1	84.1	83.4
100°	107.1	107.3	107.4	107.6	107.8	107.9	107.9	107.9	107.9	107.9	107.3
102.5°	133.3	133.5	133.7	133.9	134.0	134.1	133.9	133.8	133.6	133.5	132.8
105°	173.5	173.5	173.5	173.5	173.5	173.4	173.0	172.7	172.3	172.0	171.6
107.5°	211.4	212.2	213.0	213.8	214.6	214.9	214.7	214.6	214.5	214.3	214.3
110°	240.7	241.3	241.8	242.3	242.8	243.1	243.1	243.1	243.1	243.1	243.1



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	268.9	269.3	269.6	270.0	270.4	270.8	271.2	271.6	272.1	272.5	272.6
115°	312.7	313.2	313.7	314.2	314.7	315.1	315.3	315.4	315.6	315.8	316.1
117.5°	354.4	354.9	355.4	356.0	356.5	356.9	357.4	357.8	358.2	358.6	359.6
120°	383.8	384.3	384.8	385.3	385.9	386.1	386.1	386.1	386.1	386.1	387.5
122.5°	412.6	412.9	413.3	413.7	414.1	414.5	414.9	415.3	415.7	416.1	417.1
125°	456.5	456.7	456.8	457.0	457.2	457.5	458.0	458.6	459.1	459.6	460.1
127.5°	496.5	497.1	497.6	498.2	498.7	499.3	499.9	500.6	501.2	501.8	502.4
130°	525.3	526.0	526.7	527.3	528.0	528.6	528.9	529.3	529.6	530.0	530.3
132.5°	552.8	553.3	553.9	554.4	555.0	555.7	556.4	557.2	558.0	558.7	558.6
135°	595.6	596.1	596.7	597.2	597.7	598.0	598.2	598.4	598.6	598.7	598.4
137.5°	634.4	635.1	635.8	636.5	637.2	637.6	637.7	637.9	638.0	638.1	637.7
140°	661.3	662.0	662.7	663.4	664.0	664.4	664.4	664.4	664.4	664.4	663.5
142.5°	685.7	686.4	687.0	687.7	688.4	688.7	688.6	688.4	688.3	688.2	687.6
145°	722.2	722.9	723.6	724.3	725.0	725.3	725.1	724.9	724.8	724.6	723.5
147.5°	754.9	755.6	756.2	756.9	757.6	757.7	757.3	756.9	756.5	756.2	755.5
150°	776.2	776.7	777.2	777.7	778.3	778.3	777.7	777.2	776.7	776.2	775.5
152.5°	796.2	796.8	797.5	798.2	798.8	798.8	798.2	797.5	796.8	796.2	795.3
155°	823.1	823.6	824.1	824.6	825.2	825.0	824.1	823.2	822.4	821.5	821.0
157.5°	846.2	847.0	847.9	848.7	849.5	849.4	848.2	847.0	845.8	844.6	844.3
160°	860.6	861.3	862.0	862.7	863.4	863.2	862.2	861.1	860.1	859.0	858.9
162.5°	873.1	873.9	874.8	875.6	876.4	876.3	875.1	873.9	872.7	871.5	871.4
165°	889.5	890.4	891.2	892.1	893.0	892.8	891.6	890.4	889.2	887.9	887.9
167.5°	903.0	903.9	904.8	905.7	906.6	906.4	905.2	904.0	902.8	901.5	901.6
170°	909.8	910.9	911.9	913.0	914.0	913.9	912.7	911.5	910.3	909.0	909.2
172.5°	915.5	916.5	917.5	918.6	919.6	919.5	918.3	917.1	915.9	914.7	914.9
175°	921.6	922.6	923.6	924.7	925.7	925.6	924.4	923.2	922.0	920.8	921.1
177.5°	924.4	925.2	926.0	926.9	927.7	927.7	926.9	926.0	925.2	924.4	924.6
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	10.9	10.5	9.8	8.8	8.8	8.7	10.4	12.0	10.8	10.0	9.6
90°	19.7	15.9	12.1	9.1	7.0	5.0	2.9	0.8	2.9	5.0	7.0
92.5°	23.0	22.1	21.2	20.0	18.5	17.0	15.4	13.9	15.4	17.0	18.5
95°	49.3	49.0	48.6	47.6	45.9	44.1	42.4	40.6	42.4	44.1	45.9
97.5°	82.8	82.1	81.5	80.4	78.8	77.3	75.8	74.3	75.8	77.3	78.8
100°	106.8	106.3	105.8	104.8	103.4	102.0	100.7	99.3	100.7	102.0	103.4
102.5°	132.2	131.5	130.9	130.0	128.9	127.8	126.6	125.5	126.6	127.8	128.9
105°	171.3	170.9	170.6	170.1	169.6	169.1	168.6	168.1	168.6	169.1	169.6
107.5°	214.3	214.3	214.3	213.9	213.2	212.4	211.7	210.9	211.7	212.4	213.2
110°	243.1	243.1	243.1	242.6	241.5	240.5	239.4	238.4	239.4	240.5	241.5





TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.8	272.9	273.0	272.6	271.5	270.5	269.5	268.4	269.5	270.5	271.5
115°	316.5	316.8	317.2	316.8	315.8	314.7	313.7	312.7	313.7	314.7	315.8
117.5°	360.6	361.5	362.5	362.3	360.9	359.5	358.1	356.7	358.1	359.5	360.9
120°	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	387.5	388.9	390.3
122.5°	418.1	419.1	420.0	419.7	418.0	416.4	414.7	413.0	414.7	416.4	418.0
125°	460.6	461.2	461.7	461.2	459.6	458.0	456.5	454.9	456.5	458.0	459.6
127.5°	503.1	503.7	504.3	503.6	501.7	499.7	497.7	495.7	497.7	499.7	501.7
130°	530.6	531.0	531.3	530.4	528.1	525.9	523.6	521.4	523.6	525.9	528.1
132.5°	558.6	558.5	558.4	557.5	555.6	553.8	552.0	550.1	552.0	553.8	555.6
135°	598.0	597.7	597.3	596.2	594.3	592.4	590.5	588.6	590.5	592.4	594.3
137.5°	637.2	636.8	636.3	635.3	633.8	632.2	630.6	629.1	630.6	632.2	633.8
140°	662.7	661.8	660.9	659.7	658.1	656.6	655.0	653.5	655.0	656.6	658.1
142.5°	687.0	686.4	685.8	684.7	683.2	681.6	680.0	678.5	680.0	681.6	683.2
145°	722.5	721.5	720.4	719.3	718.1	716.9	715.6	714.4	715.6	716.9	718.1
147.5°	754.8	754.1	753.4	752.3	750.8	749.4	747.9	746.5	747.9	749.4	750.8
150°	774.8	774.1	773.4	772.5	771.5	770.4	769.4	768.4	769.4	770.4	771.5
152.5°	794.5	793.7	792.8	791.9	790.9	789.8	788.8	787.7	788.8	789.8	790.9
155°	820.5	819.9	819.4	818.9	818.4	817.9	817.3	816.8	817.3	817.9	818.4
157.5°	844.0	843.7	843.4	843.1	842.7	842.4	842.0	841.7	842.0	842.4	842.7
160°	858.7	858.5	858.3	858.1	857.7	857.4	857.0	856.7	857.0	857.4	857.7
162.5°	871.2	871.0	870.8	870.7	870.6	870.6	870.5	870.4	870.5	870.6	870.6
165°	887.9	887.9	887.9	888.0	888.2	888.4	888.6	888.7	888.6	888.4	888.2
167.5°	901.6	901.7	901.7	902.0	902.5	903.0	903.5	904.0	903.5	903.0	902.5
170°	909.4	909.6	909.7	910.1	910.6	911.1	911.7	912.2	911.7	911.1	910.6
172.5°	915.0	915.2	915.4	915.7	916.2	916.8	917.3	917.8	917.3	916.8	916.2
175°	921.5	921.8	922.2	922.6	923.1	923.6	924.2	924.7	924.2	923.6	923.1
177.5°	924.9	925.2	925.5	925.8	926.2	926.7	927.1	927.5	927.1	926.7	926.2
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	9.6	9.8	9.7	10.5	11.2	11.6	11.5	11.0	11.0	10.9	10.5
90°	9.1	12.1	15.9	19.7	23.5	27.4	27.0	26.7	26.3	26.0	25.9
92.5°	20.0	21.2	22.1	23.0	24.0	24.9	24.9	25.0	25.1	25.1	25.2
95°	47.6	48.6	49.0	49.3	49.7	50.0	50.0	50.0	50.0	50.0	49.9
97.5°	80.4	81.5	82.1	82.8	83.4	84.1	84.1	84.1	84.1	84.1	84.1
100°	104.8	105.8	106.3	106.8	107.3	107.9	107.9	107.9	107.9	107.9	107.8
102.5°	130.0	130.9	131.5	132.2	132.8	133.5	133.6	133.8	133.9	134.1	134.0
105°	170.1	170.6	170.9	171.3	171.6	172.0	172.3	172.7	173.0	173.4	173.5
107.5°	213.9	214.3	214.3	214.3	214.3	214.3	214.5	214.6	214.7	214.9	214.6
110°	242.6	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	242.8



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	272.6	273.0	272.9	272.8	272.6	272.5	272.1	271.6	271.2	270.8	270.4
115°	316.8	317.2	316.8	316.5	316.1	315.8	315.6	315.4	315.3	315.1	314.7
117.5°	362.3	362.5	361.5	360.6	359.6	358.6	358.2	357.8	357.4	356.9	356.5
120°	391.7	391.7	390.3	388.9	387.5	386.1	386.1	386.1	386.1	386.1	385.9
122.5°	419.7	420.0	419.1	418.1	417.1	416.1	415.7	415.3	414.9	414.5	414.1
125°	461.2	461.7	461.2	460.6	460.1	459.6	459.1	458.6	458.0	457.5	457.2
127.5°	503.6	504.3	503.7	503.1	502.4	501.8	501.2	500.6	499.9	499.3	498.7
130°	530.4	531.3	531.0	530.6	530.3	530.0	529.6	529.3	528.9	528.6	528.0
132.5°	557.5	558.4	558.5	558.6	558.6	558.7	558.0	557.2	556.4	555.7	555.0
135°	596.2	597.3	597.7	598.0	598.4	598.7	598.6	598.4	598.2	598.0	597.7
137.5°	635.3	636.3	636.8	637.2	637.7	638.1	638.0	637.9	637.7	637.6	637.2
140°	659.7	660.9	661.8	662.7	663.5	664.4	664.4	664.4	664.4	664.4	664.0
142.5°	684.7	685.8	686.4	687.0	687.6	688.2	688.3	688.4	688.6	688.7	688.4
145°	719.3	720.4	721.5	722.5	723.5	724.6	724.8	724.9	725.1	725.3	725.0
147.5°	752.3	753.4	754.1	754.8	755.5	756.2	756.5	756.9	757.3	757.7	757.6
150°	772.5	773.4	774.1	774.8	775.5	776.2	776.7	777.2	777.7	778.3	778.3
152.5°	791.9	792.8	793.7	794.5	795.3	796.2	796.8	797.5	798.2	798.8	798.8
155°	818.9	819.4	819.9	820.5	821.0	821.5	822.4	823.2	824.1	825.0	825.2
157.5°	843.1	843.4	843.7	844.0	844.3	844.6	845.8	847.0	848.2	849.4	849.5
160°	858.1	858.3	858.5	858.7	858.9	859.0	860.1	861.1	862.2	863.2	863.4
162.5°	870.7	870.8	871.0	871.2	871.4	871.5	872.7	873.9	875.1	876.3	876.4
165°	888.0	887.9	887.9	887.9	887.9	887.9	889.2	890.4	891.6	892.8	893.0
167.5°	902.0	901.7	901.7	901.6	901.6	901.5	902.8	904.0	905.2	906.4	906.6
170°	910.1	909.7	909.6	909.4	909.2	909.0	910.3	911.5	912.7	913.9	914.0
172.5°	915.7	915.4	915.2	915.0	914.9	914.7	915.9	917.1	918.3	919.5	919.6
175°	922.6	922.2	921.8	921.5	921.1	920.8	922.0	923.2	924.4	925.6	925.7
177.5°	925.8	925.5	925.2	924.9	924.6	924.4	925.2	926.0	926.9	927.7	927.7
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	10.5	10.1	10.6	10.2	10.6	10.1	10.5	10.5	10.9	11.0	11.0
90°	26.1	26.2	26.4	26.6	26.4	26.2	26.1	25.9	26.0	26.3	26.7
92.5°	25.2	25.3	25.3	25.3	25.3	25.3	25.2	25.2	25.1	25.1	25.0
95°	49.5	49.2	48.8	48.5	48.8	49.2	49.5	49.9	50.0	50.0	50.0
97.5°	84.1	84.0	84.0	83.9	84.0	84.0	84.1	84.1	84.1	84.1	84.1
100°	107.6	107.4	107.3	107.1	107.3	107.4	107.6	107.8	107.9	107.9	107.9
102.5°	133.9	133.7	133.5	133.3	133.5	133.7	133.9	134.0	134.1	133.9	133.8
105°	173.5	173.5	173.5	173.5	173.5	173.5	173.5	173.5	173.4	173.0	172.7
107.5°	213.8	213.0	212.2	211.4	212.2	213.0	213.8	214.6	214.9	214.7	214.6
110°	242.3	241.8	241.3	240.7	241.3	241.8	242.3	242.8	243.1	243.1	243.1



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	270.0	269.6	269.3	268.9	269.3	269.6	270.0	270.4	270.8	271.2	271.6
115°	314.2	313.7	313.2	312.7	313.2	313.7	314.2	314.7	315.1	315.3	315.4
117.5°	356.0	355.4	354.9	354.4	354.9	355.4	356.0	356.5	356.9	357.4	357.8
120°	385.3	384.8	384.3	383.8	384.3	384.8	385.3	385.9	386.1	386.1	386.1
122.5°	413.7	413.3	412.9	412.6	412.9	413.3	413.7	414.1	414.5	414.9	415.3
125°	457.0	456.8	456.7	456.5	456.7	456.8	457.0	457.2	457.5	458.0	458.6
127.5°	498.2	497.6	497.1	496.5	497.1	497.6	498.2	498.7	499.3	499.9	500.6
130°	527.3	526.7	526.0	525.3	526.0	526.7	527.3	528.0	528.6	528.9	529.3
132.5°	554.4	553.9	553.3	552.8	553.3	553.9	554.4	555.0	555.7	556.4	557.2
135°	597.2	596.7	596.1	595.6	596.1	596.7	597.2	597.7	598.0	598.2	598.4
137.5°	636.5	635.8	635.1	634.4	635.1	635.8	636.5	637.2	637.6	637.7	637.9
140°	663.4	662.7	662.0	661.3	662.0	662.7	663.4	664.0	664.4	664.4	664.4
142.5°	687.7	687.0	686.4	685.7	686.4	687.0	687.7	688.4	688.7	688.6	688.4
145°	724.3	723.6	722.9	722.2	722.9	723.6	724.3	725.0	725.3	725.1	724.9
147.5°	756.9	756.2	755.6	754.9	755.6	756.2	756.9	757.6	757.7	757.3	756.9
150°	777.7	777.2	776.7	776.2	776.7	777.2	777.7	778.3	778.3	777.7	777.2
152.5°	798.2	797.5	796.8	796.2	796.8	797.5	798.2	798.8	798.8	798.2	797.5
155°	824.6	824.1	823.6	823.1	823.6	824.1	824.6	825.2	825.0	824.1	823.2
157.5°	848.7	847.9	847.0	846.2	847.0	847.9	848.7	849.5	849.4	848.2	847.0
160°	862.7	862.0	861.3	860.6	861.3	862.0	862.7	863.4	863.2	862.2	861.1
162.5°	875.6	874.8	873.9	873.1	873.9	874.8	875.6	876.4	876.3	875.1	873.9
165°	892.1	891.2	890.4	889.5	890.4	891.2	892.1	893.0	892.8	891.6	890.4
167.5°	905.7	904.8	903.9	903.0	903.9	904.8	905.7	906.6	906.4	905.2	904.0
170°	913.0	911.9	910.9	909.8	910.9	911.9	913.0	914.0	913.9	912.7	911.5
172.5°	918.6	917.5	916.5	915.5	916.5	917.5	918.6	919.6	919.5	918.3	917.1
175°	924.7	923.6	922.6	921.6	922.6	923.6	924.7	925.7	925.6	924.4	923.2
177.5°	926.9	926.0	925.2	924.4	925.2	926.0	926.9	927.7	927.7	926.9	926.0
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	11.5	11.6	11.2	10.5	9.7	9.8	9.6	9.6	10.0	10.8	12.0
90°	27.0	27.4	23.5	19.7	15.9	12.1	9.1	7.0	5.0	2.9	0.8
92.5°	24.9	24.9	24.0	23.0	22.1	21.2	20.0	18.5	17.0	15.4	13.9
95°	50.0	50.0	49.7	49.3	49.0	48.6	47.6	45.9	44.1	42.4	40.6
97.5°	84.1	84.1	83.4	82.8	82.1	81.5	80.4	78.8	77.3	75.8	74.3
100°	107.9	107.9	107.3	106.8	106.3	105.8	104.8	103.4	102.0	100.7	99.3
102.5°	133.6	133.5	132.8	132.2	131.5	130.9	130.0	128.9	127.8	126.6	125.5
105°	172.3	172.0	171.6	171.3	170.9	170.6	170.1	169.6	169.1	168.6	168.1
107.5°	214.5	214.3	214.3	214.3	214.3	214.3	213.9	213.2	212.4	211.7	210.9
110°	243.1	243.1	243.1	243.1	243.1	243.1	242.6	241.5	240.5	239.4	238.4



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.1	272.5	272.6	272.8	272.9	273.0	272.6	271.5	270.5	269.5	268.4
115°	315.6	315.8	316.1	316.5	316.8	317.2	316.8	315.8	314.7	313.7	312.7
117.5°	358.2	358.6	359.6	360.6	361.5	362.5	362.3	360.9	359.5	358.1	356.7
120°	386.1	386.1	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1
122.5°	415.7	416.1	417.1	418.1	419.1	420.0	419.7	418.0	416.4	414.7	413.0
125°	459.1	459.6	460.1	460.6	461.2	461.7	461.2	459.6	458.0	456.5	454.9
127.5°	501.2	501.8	502.4	503.1	503.7	504.3	503.6	501.7	499.7	497.7	495.7
130°	529.6	530.0	530.3	530.6	531.0	531.3	530.4	528.1	525.9	523.6	521.4
132.5°	558.0	558.7	558.6	558.6	558.5	558.4	557.5	555.6	553.8	552.0	550.1
135°	598.6	598.7	598.4	598.0	597.7	597.3	596.2	594.3	592.4	590.5	588.6
137.5°	638.0	638.1	637.7	637.2	636.8	636.3	635.3	633.8	632.2	630.6	629.1
140°	664.4	664.4	663.5	662.7	661.8	660.9	659.7	658.1	656.6	655.0	653.5
142.5°	688.3	688.2	687.6	687.0	686.4	685.8	684.7	683.2	681.6	680.0	678.5
145°	724.8	724.6	723.5	722.5	721.5	720.4	719.3	718.1	716.9	715.6	714.4
147.5°	756.5	756.2	755.5	754.8	754.1	753.4	752.3	750.8	749.4	747.9	746.5
150°	776.7	776.2	775.5	774.8	774.1	773.4	772.5	771.5	770.4	769.4	768.4
152.5°	796.8	796.2	795.3	794.5	793.7	792.8	791.9	790.9	789.8	788.8	787.7
155°	822.4	821.5	821.0	820.5	819.9	819.4	818.9	818.4	817.9	817.3	816.8
157.5°	845.8	844.6	844.3	844.0	843.7	843.4	843.1	842.7	842.4	842.0	841.7
160°	860.1	859.0	858.9	858.7	858.5	858.3	858.1	857.7	857.4	857.0	856.7
162.5°	872.7	871.5	871.4	871.2	871.0	870.8	870.7	870.6	870.6	870.5	870.4
165°	889.2	887.9	887.9	887.9	887.9	887.9	888.0	888.2	888.4	888.6	888.7
167.5°	902.8	901.5	901.6	901.6	901.7	901.7	902.0	902.5	903.0	903.5	904.0
170°	910.3	909.0	909.2	909.4	909.6	909.7	910.1	910.6	911.1	911.7	912.2
172.5°	915.9	914.7	914.9	915.0	915.2	915.4	915.7	916.2	916.8	917.3	917.8
175°	922.0	920.8	921.1	921.5	921.8	922.2	922.6	923.1	923.6	924.2	924.7
177.5°	925.2	924.4	924.6	924.9	925.2	925.5	925.8	926.2	926.7	927.1	927.5
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.4	8.7	8.8	8.8	9.8	10.5	10.9	11.6	12.8	12.3	12.7
90°	2.9	5.0	7.0	9.1	12.1	15.9	19.7	23.5	27.4	27.0	26.7
92.5°	15.4	17.0	18.5	20.0	21.2	22.1	23.0	24.0	24.9	24.9	25.0
95°	42.4	44.1	45.9	47.6	48.6	49.0	49.3	49.7	50.0	50.0	50.0
97.5°	75.8	77.3	78.8	80.4	81.5	82.1	82.8	83.4	84.1	84.1	84.1
100°	100.7	102.0	103.4	104.8	105.8	106.3	106.8	107.3	107.9	107.9	107.9
102.5°	126.6	127.8	128.9	130.0	130.9	131.5	132.2	132.8	133.5	133.6	133.8
105°	168.6	169.1	169.6	170.1	170.6	170.9	171.3	171.6	172.0	172.3	172.7
107.5°	211.7	212.4	213.2	213.9	214.3	214.3	214.3	214.3	214.3	214.5	214.6
110°	239.4	240.5	241.5	242.6	243.1	243.1	243.1	243.1	243.1	243.1	243.1





TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	269.5	270.5	271.5	272.6	273.0	272.9	272.8	272.6	272.5	272.1	271.6
115°	313.7	314.7	315.8	316.8	317.2	316.8	316.5	316.1	315.8	315.6	315.4
117.5°	358.1	359.5	360.9	362.3	362.5	361.5	360.6	359.6	358.6	358.2	357.8
120°	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	386.1	386.1
122.5°	414.7	416.4	418.0	419.7	420.0	419.1	418.1	417.1	416.1	415.7	415.3
125°	456.5	458.0	459.6	461.2	461.7	461.2	460.6	460.1	459.6	459.1	458.6
127.5°	497.7	499.7	501.7	503.6	504.3	503.7	503.1	502.4	501.8	501.2	500.6
130°	523.6	525.9	528.1	530.4	531.3	531.0	530.6	530.3	530.0	529.6	529.3
132.5°	552.0	553.8	555.6	557.5	558.4	558.5	558.6	558.6	558.7	558.0	557.2
135°	590.5	592.4	594.3	596.2	597.3	597.7	598.0	598.4	598.7	598.6	598.4
137.5°	630.6	632.2	633.8	635.3	636.3	636.8	637.2	637.7	638.1	638.0	637.9
140°	655.0	656.6	658.1	659.7	660.9	661.8	662.7	663.5	664.4	664.4	664.4
142.5°	680.0	681.6	683.2	684.7	685.8	686.4	687.0	687.6	688.2	688.3	688.4
145°	715.6	716.9	718.1	719.3	720.4	721.5	722.5	723.5	724.6	724.8	724.9
147.5°	747.9	749.4	750.8	752.3	753.4	754.1	754.8	755.5	756.2	756.5	756.9
150°	769.4	770.4	771.5	772.5	773.4	774.1	774.8	775.5	776.2	776.7	777.2
152.5°	788.8	789.8	790.9	791.9	792.8	793.7	794.5	795.3	796.2	796.8	797.5
155°	817.3	817.9	818.4	818.9	819.4	819.9	820.5	821.0	821.5	822.4	823.2
157.5°	842.0	842.4	842.7	843.1	843.4	843.7	844.0	844.3	844.6	845.8	847.0
160°	857.0	857.4	857.7	858.1	858.3	858.5	858.7	858.9	859.0	860.1	861.1
162.5°	870.5	870.6	870.6	870.7	870.8	871.0	871.2	871.4	871.5	872.7	873.9
165°	888.6	888.4	888.2	888.0	887.9	887.9	887.9	887.9	887.9	889.2	890.4
167.5°	903.5	903.0	902.5	902.0	901.7	901.7	901.6	901.6	901.5	902.8	904.0
170°	911.7	911.1	910.6	910.1	909.7	909.6	909.4	909.2	909.0	910.3	911.5
172.5°	917.3	916.8	916.2	915.7	915.4	915.2	915.0	914.9	914.7	915.9	917.1
175°	924.2	923.6	923.1	922.6	922.2	921.8	921.5	921.1	920.8	922.0	923.2
177.5°	927.1	926.7	926.2	925.8	925.5	925.2	924.9	924.6	924.4	925.2	926.0
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	12.2	12.1	12.1	12.2	12.2	12.2	11.8
90°	26.3	26.0	25.9	26.1	26.2	26.4	26.6
92.5°	25.1	25.1	25.2	25.2	25.3	25.3	25.3
95°	50.0	50.0	49.9	49.5	49.2	48.8	48.5
97.5°	84.1	84.1	84.1	84.1	84.0	84.0	83.9
100°	107.9	107.9	107.8	107.6	107.4	107.3	107.1
102.5°	133.9	134.1	134.0	133.9	133.7	133.5	133.3
105°	173.0	173.4	173.5	173.5	173.5	173.5	173.5
107.5°	214.7	214.9	214.6	213.8	213.0	212.2	211.4
110°	243.1	243.1	242.8	242.3	241.8	241.3	240.7



TEST NUMBER: P331688

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	271.2	270.8	270.4	270.0	269.6	269.3	268.9
115°	315.3	315.1	314.7	314.2	313.7	313.2	312.7
117.5°	357.4	356.9	356.5	356.0	355.4	354.9	354.4
120°	386.1	386.1	385.9	385.3	384.8	384.3	383.8
122.5°	414.9	414.5	414.1	413.7	413.3	412.9	412.6
125°	458.0	457.5	457.2	457.0	456.8	456.7	456.5
127.5°	499.9	499.3	498.7	498.2	497.6	497.1	496.5
130°	528.9	528.6	528.0	527.3	526.7	526.0	525.3
132.5°	556.4	555.7	555.0	554.4	553.9	553.3	552.8
135°	598.2	598.0	597.7	597.2	596.7	596.1	595.6
137.5°	637.7	637.6	637.2	636.5	635.8	635.1	634.4
140°	664.4	664.4	664.0	663.4	662.7	662.0	661.3
142.5°	688.6	688.7	688.4	687.7	687.0	686.4	685.7
145°	725.1	725.3	725.0	724.3	723.6	722.9	722.2
147.5°	757.3	757.7	757.6	756.9	756.2	755.6	754.9
150°	777.7	778.3	778.3	777.7	777.2	776.7	776.2
152.5°	798.2	798.8	798.8	798.2	797.5	796.8	796.2
155°	824.1	825.0	825.2	824.6	824.1	823.6	823.1
157.5°	848.2	849.4	849.5	848.7	847.9	847.0	846.2
160°	862.2	863.2	863.4	862.7	862.0	861.3	860.6
162.5°	875.1	876.3	876.4	875.6	874.8	873.9	873.1
165°	891.6	892.8	893.0	892.1	891.2	890.4	889.5
167.5°	905.2	906.4	906.6	905.7	904.8	903.9	903.0
170°	912.7	913.9	914.0	913.0	911.9	910.9	909.8
172.5°	918.3	919.5	919.6	918.6	917.5	916.5	915.5
175°	924.4	925.6	925.7	924.7	923.6	922.6	921.6
177.5°	926.9	927.7	927.7	926.9	926.0	925.2	924.4
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2

(END OF REPORT)