

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331690

Luminaire Tested: **SA2XXRDIP-C675D725U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331690
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5219.6 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331690
CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331690

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44				38	
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38				33	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33				28	
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28				25	
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25				22	
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22				19	
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20				17	
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18				16	
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16				14	
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331690

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	2.0
10°-20°	289.9	5.6
20°-30°	407.1	7.8
30°-40°	443.9	8.5
40°-50°	408.2	7.8
50°-60°	320.6	6.1
60°-70°	209.0	4.0
70°-80°	107.8	2.1
80°-90°	30.4	0.6
90°-100°	33.0	0.6
100°-110°	120.9	2.3
110°-120°	323.3	6.2
120°-130°	533.6	10.2
130°-140°	567.5	10.9
140°-150°	527.5	10.1
150°-160°	424.1	8.1
160°-170°	273.3	5.2
170°-180°	94.1	1.8
0°-30°	802.6	15.4
0°-40°	1246.6	23.9
0°-60°	1975.3	37.8
0°-90°	2322.5	44.5
90°-120°	477.2	9.1
90°-150°	2105.7	40.3
90°-180°	2897.0	55.5
0°-180°	5219.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	1	8	14	18	19	4
95°	46	24	28	31	31	57
105°	218	227	44	51	54	232
115°	411	424	441	126	59	405
125°	582	591	604	609	612	518
135°	720	731	738	744	743	556
145°	835	835	846	851	848	522
155°	919	914	921	925	920	423
165°	969	965	966	971	966	274
175°	991	986	987	992	985	94
180°	989	989	989	989	989	



TEST NUMBER: P331690

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.2	12.1	11.0	9.9	8.8	8.4	8.6	8.9	9.1	9.4	9.4
90°	0.7	2.5	4.2	6.0	7.7	9.2	10.5	11.8	13.0	14.3	15.1
92.5°	14.4	14.3	14.1	14.0	13.8	14.1	14.7	15.3	16.0	16.6	17.0
95°	46.5	41.3	36.0	30.8	25.5	23.4	24.6	25.7	26.8	27.9	28.7
97.5°	92.3	77.5	62.7	47.9	33.1	27.0	29.6	32.2	34.8	37.3	38.0
100°	126.6	104.8	83.1	61.3	39.5	30.0	32.7	35.4	38.1	40.8	42.0
102.5°	164.4	159.8	155.2	150.6	145.9	132.3	109.7	87.1	64.5	41.9	43.6
105°	217.5	222.2	227.0	231.8	236.5	217.2	173.8	130.4	87.0	43.6	45.4
107.5°	278.0	281.8	285.7	289.5	293.4	269.3	217.2	165.2	113.1	61.1	59.3
110°	316.9	320.2	323.6	326.9	330.2	308.9	263.0	217.1	171.1	125.2	109.3



TEST NUMBER: P331690

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.5	356.5	359.4	362.4	365.3	361.1	349.8	338.4	327.1	315.7	257.8
115°	411.3	414.0	416.7	419.4	422.1	425.5	429.4	433.4	437.4	441.4	367.8
117.5°	463.0	466.0	469.0	472.0	475.0	477.9	480.7	483.4	486.1	488.9	471.1
120°	500.7	503.1	505.5	507.9	510.3	512.9	515.8	518.6	521.5	524.3	526.2
122.5°	532.8	535.3	537.8	540.3	542.8	545.6	548.8	551.9	555.0	558.1	559.2
125°	581.6	583.6	585.7	587.8	589.8	592.4	595.4	598.4	601.4	604.5	605.6
127.5°	625.8	628.1	630.4	632.6	634.9	637.2	639.5	641.7	644.0	646.2	647.9
130°	653.8	656.4	658.9	661.4	664.0	666.1	667.9	669.6	671.4	673.1	674.9
132.5°	682.4	684.6	686.8	688.9	691.1	693.0	694.8	696.5	698.3	700.0	701.5
135°	719.6	722.2	724.7	727.3	729.8	731.8	733.2	734.6	736.1	737.5	739.1
137.5°	757.3	759.0	760.8	762.6	764.4	766.1	767.7	769.3	770.9	772.6	774.1
140°	781.9	783.1	784.4	785.7	786.9	788.5	790.2	792.0	793.7	795.5	796.9
142.5°	802.5	803.6	804.8	805.9	807.0	808.6	810.6	812.6	814.6	816.6	817.9
145°	834.8	834.6	834.5	834.3	834.2	835.4	838.1	840.8	843.5	846.2	847.4
147.5°	863.0	862.4	861.8	861.2	860.6	861.6	864.3	866.9	869.6	872.3	873.1
150°	881.3	880.2	879.1	878.0	876.8	877.6	880.1	882.6	885.2	887.7	888.7
152.5°	896.7	895.5	894.3	893.0	891.8	892.4	894.8	897.2	899.6	902.0	903.0
155°	919.2	917.8	916.3	914.9	913.5	913.7	915.6	917.5	919.4	921.3	922.3
157.5°	936.8	935.6	934.4	933.2	932.0	932.0	933.4	934.7	936.0	937.4	938.5
160°	947.1	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	948.1
162.5°	956.3	955.3	954.4	953.4	952.4	952.4	953.2	954.0	954.9	955.7	956.8
165°	968.6	967.6	966.7	965.7	964.7	964.5	965.0	965.5	965.9	966.4	967.5
167.5°	977.7	976.8	975.8	974.9	973.9	973.6	974.1	974.5	975.0	975.4	976.5
170°	982.9	981.9	981.0	980.0	979.1	978.7	979.1	979.4	979.7	980.0	981.1
172.5°	986.3	985.3	984.4	983.4	982.5	982.2	982.5	982.8	983.1	983.4	984.6
175°	990.7	989.6	988.5	987.4	986.3	985.9	986.2	986.5	986.8	987.2	988.3
177.5°	991.5	990.6	989.7	988.8	987.9	987.5	987.6	987.8	987.9	988.0	988.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331690

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	9.3	9.3	9.3	9.3	9.4	9.5	9.5	9.6
90°	15.9	16.7	17.5	18.0	18.4	18.7	19.0	19.3
92.5°	17.4	17.8	18.2	18.6	18.7	18.9	19.1	19.3
95°	29.5	30.3	31.1	31.4	31.2	31.1	30.9	30.8
97.5°	38.6	39.2	39.9	40.3	40.5	40.7	40.9	41.1
100°	43.3	44.6	45.9	46.7	47.0	47.3	47.6	47.9
102.5°	45.2	46.9	48.5	49.6	50.0	50.5	50.9	51.4
105°	47.1	48.9	50.6	51.8	52.5	53.1	53.7	54.4
107.5°	57.5	55.7	54.0	53.4	54.0	54.7	55.3	55.9
110°	93.4	77.5	61.6	54.0	54.6	55.2	55.9	56.5



TEST NUMBER: P331690

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	199.8	141.8	83.8	55.0	55.6	56.1	56.6	57.1
115°	294.2	220.6	147.0	104.4	93.0	81.5	70.1	58.7
117.5°	453.3	435.4	417.6	389.9	352.3	314.7	277.1	239.5
120°	528.2	530.1	532.0	522.2	500.7	479.3	457.8	436.4
122.5°	560.4	561.5	562.7	561.2	557.0	552.8	548.7	544.5
125°	606.7	607.8	608.9	609.7	610.2	610.7	611.1	611.6
127.5°	649.5	651.1	652.7	653.6	653.7	653.8	653.9	654.0
130°	676.6	678.4	680.1	680.9	680.8	680.6	680.4	680.3
132.5°	703.0	704.5	706.0	706.7	706.5	706.4	706.2	706.0
135°	740.7	742.3	743.9	744.5	744.2	743.9	743.5	743.2
137.5°	775.7	777.2	778.8	779.3	778.8	778.2	777.7	777.1
140°	798.3	799.7	801.2	801.5	800.7	799.9	799.1	798.3
142.5°	819.2	820.5	821.8	822.1	821.3	820.5	819.7	818.9
145°	848.5	849.6	850.7	850.8	850.1	849.3	848.5	847.7
147.5°	873.9	874.8	875.6	875.7	875.0	874.3	873.7	873.0
150°	889.6	890.6	891.5	891.6	890.8	890.0	889.2	888.4
152.5°	903.9	904.9	905.9	905.8	904.8	903.7	902.7	901.6
155°	923.3	924.2	925.2	925.0	923.7	922.5	921.2	919.9
157.5°	939.5	940.6	941.7	941.6	940.4	939.1	937.9	936.7
160°	949.0	950.0	950.9	950.8	949.7	948.6	947.5	946.4
162.5°	957.8	958.9	960.0	959.9	958.5	957.1	955.8	954.4
165°	968.6	969.8	970.9	970.9	969.8	968.6	967.5	966.4
167.5°	977.7	978.8	979.9	979.7	978.3	976.9	975.4	974.0
170°	982.2	983.3	984.5	984.3	982.9	981.4	980.0	978.6
172.5°	985.7	986.8	987.9	987.7	986.3	984.9	983.4	982.0
175°	989.4	990.5	991.6	991.4	989.8	988.2	986.6	985.0
177.5°	989.8	990.7	991.6	991.5	990.3	989.2	988.0	986.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6

(END OF REPORT)