

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331381-940

Luminaire Tested: **SA2XXDIP-C865D330U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331381-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D330U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4299.4 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331381-940
CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331381-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73				73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	61				61
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51				51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44				44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	37				37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	32				32
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29				29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25				25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23				23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20				20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19				19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331381-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	2.7
10°-20°	325.6	7.6
20°-30°	478.6	11.1
30°-40°	555.9	12.9
40°-50°	555.3	12.9
50°-60°	484.3	11.3
60°-70°	358.1	8.3
70°-80°	202.8	4.7
80°-90°	55.5	1.3
90°-100°	13.3	0.3
100°-110°	48.7	1.1
110°-120°	130.3	3.0
120°-130°	215.1	5.0
130°-140°	228.7	5.3
140°-150°	212.6	4.9
150°-160°	170.9	4.0
160°-170°	110.1	2.6
170°-180°	37.9	0.9
0°-30°	919.9	21.4
0°-40°	1475.8	34.3
0°-60°	2515.4	58.5
0°-90°	3131.8	72.8
90°-120°	192.3	4.5
90°-150°	848.7	19.7
90°-180°	1168.0	27.2
0°-180°	4299.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	0	3	6	7	8	3
95°	19	10	11	13	12	23
105°	88	91	18	21	22	94
115°	166	171	178	51	24	163
125°	234	238	244	246	246	209
135°	290	295	297	300	300	224
145°	336	336	341	343	342	210
155°	370	368	371	373	371	171
165°	390	389	390	391	390	110
175°	399	397	398	400	397	38
180°	398	398	398	398	398	



TEST NUMBER: P331381-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.1	16.9	16.5	16.2	16.0	15.7	15.3	15.1	14.7	14.4	13.8
90°	0.3	1.0	1.7	2.4	3.1	3.7	4.2	4.7	5.3	5.8	6.1
92.5°	5.8	5.8	5.7	5.6	5.5	5.7	5.9	6.2	6.4	6.7	6.9
95°	18.7	16.6	14.5	12.4	10.3	9.5	9.9	10.3	10.8	11.2	11.6
97.5°	37.2	31.2	25.2	19.4	13.4	10.9	11.9	12.9	14.0	15.1	15.3
100°	51.0	42.3	33.4	24.7	16.0	12.0	13.2	14.3	15.3	16.4	16.9
102.5°	66.3	64.4	62.5	60.7	58.9	53.3	44.2	35.1	26.0	16.9	17.6
105°	87.7	89.5	91.5	93.5	95.3	87.6	70.1	52.6	35.0	17.6	18.3
107.5°	112.0	113.6	115.1	116.7	118.2	108.5	87.6	66.6	45.6	24.6	23.9
110°	127.7	129.0	130.5	131.8	133.1	124.5	106.0	87.5	68.9	50.5	44.1



TEST NUMBER: P331381-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.5	143.7	144.9	146.1	147.2	145.5	141.0	136.4	131.8	127.2	103.9
115°	165.8	166.8	168.0	169.1	170.1	171.5	173.1	174.7	176.3	177.9	148.2
117.5°	186.6	187.8	189.0	190.3	191.5	192.6	193.8	194.8	195.9	197.1	189.8
120°	201.8	202.8	203.8	204.7	205.6	206.7	207.9	209.0	210.2	211.3	212.1
122.5°	214.7	215.8	216.8	217.8	218.8	219.9	221.1	222.4	223.7	225.0	225.4
125°	234.4	235.2	236.0	236.9	237.7	238.8	240.0	241.2	242.4	243.6	244.1
127.5°	252.2	253.2	254.0	255.0	255.9	256.8	257.7	258.7	259.6	260.5	261.1
130°	263.5	264.6	265.6	266.6	267.6	268.5	269.2	269.9	270.6	271.3	272.0
132.5°	275.1	275.9	276.8	277.7	278.6	279.3	280.0	280.7	281.4	282.1	282.8
135°	290.1	291.1	292.1	293.1	294.2	295.0	295.5	296.1	296.7	297.3	297.9
137.5°	305.2	305.9	306.7	307.4	308.1	308.8	309.4	310.0	310.8	311.4	312.0
140°	315.1	315.7	316.1	316.6	317.2	317.8	318.5	319.2	319.9	320.6	321.2
142.5°	323.4	323.9	324.3	324.9	325.3	325.9	326.7	327.5	328.3	329.1	329.7
145°	336.4	336.4	336.4	336.3	336.2	336.7	337.8	338.9	340.0	341.1	341.5
147.5°	347.9	347.6	347.3	347.1	346.9	347.2	348.3	349.5	350.5	351.6	351.9
150°	355.2	354.7	354.3	353.8	353.4	353.7	354.7	355.8	356.8	357.8	358.2
152.5°	361.4	361.0	360.4	359.9	359.4	359.6	360.6	361.6	362.6	363.6	363.9
155°	370.5	369.9	369.3	368.7	368.2	368.3	369.1	369.8	370.6	371.3	371.8
157.5°	377.6	377.1	376.6	376.1	375.6	375.7	376.2	376.7	377.3	377.8	378.3
160°	381.7	381.4	380.9	380.6	380.2	380.2	380.6	380.9	381.4	381.7	382.1
162.5°	385.4	385.0	384.7	384.2	383.9	383.9	384.1	384.5	384.9	385.2	385.7
165°	390.4	390.0	389.6	389.2	388.9	388.8	389.0	389.1	389.3	389.5	389.9
167.5°	394.0	393.7	393.3	392.9	392.5	392.4	392.6	392.8	393.0	393.2	393.6
170°	396.2	395.7	395.4	395.0	394.6	394.5	394.6	394.8	394.8	395.0	395.5
172.5°	397.5	397.2	396.7	396.4	396.0	395.8	396.0	396.1	396.3	396.4	396.8
175°	399.3	398.9	398.4	398.0	397.5	397.3	397.5	397.6	397.8	397.9	398.3
177.5°	399.6	399.2	398.9	398.5	398.1	398.1	398.1	398.1	398.1	398.2	398.6
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4



TEST NUMBER: P331381-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	13.3	12.7	12.1	11.8	11.6	11.4	11.2	11.1
90°	6.4	6.7	7.0	7.3	7.4	7.5	7.7	7.8
92.5°	7.0	7.2	7.3	7.5	7.6	7.7	7.7	7.8
95°	11.9	12.2	12.5	12.7	12.6	12.5	12.5	12.4
97.5°	15.6	15.8	16.1	16.2	16.3	16.4	16.5	16.6
100°	17.5	18.0	18.5	18.8	18.9	19.1	19.2	19.4
102.5°	18.2	18.9	19.5	20.0	20.2	20.3	20.5	20.7
105°	19.0	19.7	20.4	20.9	21.1	21.4	21.7	21.9
107.5°	23.2	22.5	21.8	21.5	21.8	22.0	22.3	22.6
110°	37.6	31.2	24.8	21.8	22.0	22.3	22.6	22.7



TEST NUMBER: P331381-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	80.5	57.2	33.8	22.2	22.4	22.6	22.8	23.0
115°	118.6	88.9	59.2	42.1	37.5	32.9	28.3	23.6
117.5°	182.7	175.5	168.4	157.2	142.0	126.9	111.7	96.6
120°	212.9	213.7	214.4	210.4	201.8	193.1	184.5	175.8
122.5°	225.9	226.3	226.8	226.1	224.5	222.8	221.1	219.5
125°	244.5	245.0	245.4	245.8	245.9	246.1	246.3	246.5
127.5°	261.8	262.4	263.1	263.4	263.5	263.5	263.5	263.6
130°	272.7	273.4	274.1	274.5	274.4	274.3	274.3	274.2
132.5°	283.4	283.9	284.5	284.8	284.7	284.7	284.6	284.5
135°	298.5	299.2	299.8	300.1	300.0	299.8	299.7	299.5
137.5°	312.6	313.3	313.9	314.1	313.9	313.7	313.4	313.3
140°	321.7	322.4	322.9	323.1	322.7	322.4	322.1	321.7
142.5°	330.2	330.7	331.3	331.4	331.0	330.7	330.4	330.0
145°	342.0	342.4	342.9	343.0	342.6	342.3	342.0	341.6
147.5°	352.2	352.6	352.9	352.9	352.7	352.4	352.1	351.9
150°	358.6	358.9	359.4	359.4	359.1	358.7	358.4	358.1
152.5°	364.4	364.7	365.1	365.1	364.6	364.3	363.8	363.4
155°	372.1	372.5	372.9	372.8	372.3	371.8	371.3	370.8
157.5°	378.7	379.2	379.5	379.5	379.0	378.5	378.0	377.6
160°	382.5	382.9	383.3	383.3	382.8	382.4	381.9	381.5
162.5°	386.0	386.5	386.9	386.9	386.3	385.8	385.2	384.7
165°	390.4	390.8	391.3	391.3	390.8	390.4	389.9	389.5
167.5°	394.0	394.5	394.9	394.8	394.3	393.7	393.2	392.5
170°	395.9	396.4	396.8	396.7	396.2	395.6	395.0	394.4
172.5°	397.3	397.7	398.1	398.1	397.5	397.0	396.4	395.8
175°	398.8	399.2	399.7	399.6	399.0	398.3	397.6	397.0
177.5°	399.0	399.3	399.7	399.6	399.1	398.7	398.2	397.8
180°	398.4	398.4	398.4	398.4	398.4	398.4	398.4	398.4

(END OF REPORT)