

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331693

Luminaire Tested: **SA2XXRDIP-C675D925U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331693  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6240.8 lumens  
Efficiency: N/A  
Efficacy: 120.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331693  
CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	89	85	88	84	81	79	69	67	65	56	54	53	43	42	41	36
2	88	81	76	71	80	74	70	65	62	58	55	50	47	45	39	37	36	31
3	81	72	65	60	74	66	60	56	55	51	47	45	42	39	35	33	31	27
4	74	64	57	51	68	59	53	48	49	45	41	40	37	34	32	29	28	24
5	69	58	50	44	62	53	46	41	44	39	36	36	33	30	29	26	25	21
6	63	52	44	39	58	48	41	36	40	35	31	33	29	27	27	24	22	19
7	59	47	40	34	54	44	37	32	37	32	28	30	27	24	24	22	20	17
8	55	43	36	31	50	40	33	29	34	29	25	28	24	22	23	20	18	16
9	51	39	32	27	47	36	30	26	31	26	23	26	22	20	21	18	17	14
10	48	36	29	25	44	34	27	23	29	24	21	24	20	18	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.3	2.2
10°-20°	388.0	6.2
20°-30°	500.0	8.0
30°-40°	475.2	7.6
40°-50°	407.1	6.5
50°-60°	310.0	5.0
60°-70°	196.0	3.1
70°-80°	97.9	1.6
80°-90°	28.6	0.5
90°-100°	42.1	0.7
100°-110°	154.4	2.5
110°-120°	412.7	6.6
120°-130°	681.3	10.9
130°-140°	724.5	11.6
140°-150°	673.4	10.8
150°-160°	541.4	8.7
160°-170°	348.9	5.6
170°-180°	120.1	1.9
0°-30°	1027.3	16.5
0°-40°	1502.5	24.1
0°-60°	2219.6	35.6
0°-90°	2542.0	40.7
90°-120°	609.2	9.8
90°-150°	2688.4	43.1
90°-180°	3699.0	59.3
0°-180°	6240.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	20
90°	25	1	25	1	25	12
95°	39	59	39	59	39	37
105°	69	278	69	278	69	72
115°	75	525	75	525	75	188
125°	781	742	781	742	781	676
135°	949	919	949	919	949	731
145°	1082	1066	1082	1066	1082	677
155°	1174	1174	1174	1174	1174	542
165°	1234	1237	1234	1237	1234	348
175°	1258	1265	1258	1265	1258	120
180°	1262	1262	1262	1262	1262	



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	11.5	11.8	11.7	11.6	11.5	11.4	11.2	11.4	10.8	11.0	10.3
90°	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3	19.3	18.3	16.6
92.5°	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2	21.7	21.2	20.4
95°	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6	36.6	35.6	34.2
97.5°	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3	48.5	47.7	44.4
100°	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3	53.7	52.1	48.6
102.5°	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7	55.6	53.5	82.4
105°	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2	57.9	55.7	111.1
107.5°	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4	75.7	78.0	144.4
110°	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2	139.5	159.8	218.5



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1	329.1	403.1	417.6
115°	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6	469.5	563.5	558.4
117.5°	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7	601.4	624.1	620.7
120°	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3	671.9	669.4	665.8
122.5°	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5	714.0	712.6	708.6
125°	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6	773.2	771.7	767.9
127.5°	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2	827.1	825.1	822.2
130°	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9	861.6	859.4	857.2
132.5°	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6	895.7	893.7	891.5
135°	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7	943.6	941.6	939.8
137.5°	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3	988.3	986.4	984.3
140°	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2	1017.4	1015.6	1013.4
142.5°	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9	1044.3	1042.6	1040.1
145°	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3	1081.8	1080.4	1077.0
147.5°	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8	1114.7	1113.7	1110.3
150°	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8	1134.6	1133.4	1130.2
152.5°	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1	1152.9	1151.7	1148.6
155°	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8	1177.5	1176.3	1173.9
157.5°	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5	1198.2	1196.8	1195.1
160°	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6	1210.4	1209.2	1208.0
162.5°	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9	1221.5	1220.2	1219.1
165°	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9	1233.3
167.5°	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2	1246.8	1245.4	1244.8
170°	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1	1252.6	1251.2	1250.8
172.5°	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4	1257.0	1255.6	1255.2
175°	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2	1261.8	1260.3	1259.9
177.5°	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7	1262.6	1261.4	1261.3
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	9.9	10.0	9.7	8.9	8.9	8.8	10.4	12.0	10.8	10.1	9.7
90°	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9	3.1	5.4	7.6
92.5°	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4	18.2	18.0	17.8
95°	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4	52.7	46.0	39.3
97.5°	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8	98.9	80.1	61.2
100°	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7	133.8	106.0	78.2
102.5°	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9	204.0	198.1	192.2
105°	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6	283.7	289.8	295.9
107.5°	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9	359.8	364.7	369.6
110°	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6	408.9	413.1	417.4





TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3	455.1	458.9	462.7
115°	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1	528.6	532.0	535.5
117.5°	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1	594.9	598.8	602.7
120°	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3	642.3	645.4	648.4
122.5°	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2	683.4	686.6	689.8
125°	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5	745.1	747.8	750.4
127.5°	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9	801.9	804.8	807.7
130°	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8	838.0	841.2	844.5
132.5°	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3	874.0	876.8	879.6
135°	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8	922.0	925.3	928.5
137.5°	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8	969.1	971.4	973.6
140°	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2	999.9	1001.5	1003.1
142.5°	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5	1026.0	1027.5	1028.9
145°	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8	1065.6	1065.4	1065.2
147.5°	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8	1101.0	1100.3	1099.5
150°	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2	1123.8	1122.3	1120.9
152.5°	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9	1143.3	1141.7	1140.2
155°	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6	1171.8	1169.9	1168.1
157.5°	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0	1194.5	1193.0	1191.4
160°	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1208.0	1206.8	1205.5
162.5°	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9	1219.7	1218.5	1217.2
165°	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6	1235.4	1234.2	1232.9
167.5°	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3	1247.1	1245.9	1244.6
170°	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9	1253.6	1252.4	1251.2
172.5°	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2	1258.0	1256.8	1255.6
175°	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9	1263.5	1262.1	1260.6
177.5°	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8	1264.7	1263.6	1262.4
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	9.7	9.7	9.2	9.5	9.9	9.8	10.0	9.8	10.0	10.2	9.9
90°	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3	21.3	22.3	23.0
92.5°	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2	22.8	23.3	23.7
95°	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6	38.7	39.7	40.1
97.5°	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3	50.1	50.9	51.4
100°	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3	56.9	58.6	59.6
102.5°	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7	59.9	62.0	63.3
105°	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2	62.4	64.6	66.2
107.5°	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4	71.2	68.9	68.2
110°	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2	98.9	78.6	68.9



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1	181.0	107.0	70.3
115°	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6	281.6	187.6	133.3
117.5°	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7	556.0	533.2	497.8
120°	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3	676.8	679.2	666.7
122.5°	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5	716.9	718.4	716.5
125°	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6	776.0	777.4	778.4
127.5°	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2	831.3	833.4	834.4
130°	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9	866.1	868.3	869.4
132.5°	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6	899.5	901.4	902.2
135°	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7	947.7	949.7	950.5
137.5°	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3	992.3	994.3	995.0
140°	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2	1021.1	1022.9	1023.3
142.5°	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9	1047.6	1049.3	1049.6
145°	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3	1084.7	1086.1	1086.3
147.5°	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8	1116.8	1117.9	1118.0
150°	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8	1137.1	1138.3	1138.4
152.5°	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1	1155.3	1156.5	1156.5
155°	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8	1180.0	1181.2	1181.0
157.5°	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5	1200.9	1202.3	1202.2
160°	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6	1212.9	1214.1	1214.0
162.5°	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9	1224.3	1225.7	1225.5
165°	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5
167.5°	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2	1249.6	1251.1	1250.8
170°	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1	1255.5	1256.9	1256.7
172.5°	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4	1259.9	1261.3	1261.1
175°	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2	1264.6	1266.0	1265.7
177.5°	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7	1264.9	1266.0	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	10.0	9.7	10.2	9.8	10.2	9.7	10.0	9.9	10.2	10.0	9.8
90°	23.4	23.8	24.3	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3
92.5°	23.9	24.2	24.4	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2
95°	39.9	39.7	39.5	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6
97.5°	51.7	51.9	52.2	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3
100°	60.0	60.4	60.8	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3
102.5°	63.9	64.4	65.0	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7
105°	67.0	67.8	68.6	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2
107.5°	69.0	69.8	70.6	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4
110°	69.7	70.5	71.3	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	70.9	71.6	72.2	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1
115°	118.7	104.1	89.5	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6
117.5°	449.8	401.8	353.8	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7
120°	639.3	611.9	584.5	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3
122.5°	711.2	705.8	700.5	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5
125°	779.0	779.6	780.3	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6
127.5°	834.6	834.7	834.8	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2
130°	869.2	868.9	868.7	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9
132.5°	902.0	901.8	901.6	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6
135°	950.1	949.7	949.3	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7
137.5°	994.3	993.6	992.9	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3
140°	1022.3	1021.3	1020.3	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2
142.5°	1048.6	1047.6	1046.6	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9
145°	1085.3	1084.3	1083.3	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3
147.5°	1117.1	1116.3	1115.4	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8
150°	1137.4	1136.3	1135.3	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8
152.5°	1155.1	1153.8	1152.5	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1
155°	1179.4	1177.7	1176.1	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8
157.5°	1200.6	1199.0	1197.4	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5
160°	1212.5	1211.1	1209.7	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6
162.5°	1223.8	1222.0	1220.3	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9
165°	1238.1	1236.7	1235.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7
167.5°	1249.0	1247.2	1245.4	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2
170°	1254.9	1253.0	1251.2	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1
172.5°	1259.2	1257.4	1255.6	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4
175°	1263.7	1261.7	1259.6	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2
177.5°	1264.4	1262.9	1261.4	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	10.0	9.8	9.9	9.5	9.2	9.7	9.7	9.7	10.1	10.8	12.0
90°	19.3	18.3	16.6	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9
92.5°	21.7	21.2	20.4	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4
95°	36.6	35.6	34.2	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4
97.5°	48.5	47.7	44.4	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8
100°	53.7	52.1	48.6	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7
102.5°	55.6	53.5	82.4	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9
105°	57.9	55.7	111.1	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6
107.5°	75.7	78.0	144.4	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9
110°	139.5	159.8	218.5	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.1	403.1	417.6	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3
115°	469.5	563.5	558.4	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1
117.5°	601.4	624.1	620.7	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1
120°	671.9	669.4	665.8	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3
122.5°	714.0	712.6	708.6	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2
125°	773.2	771.7	767.9	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5
127.5°	827.1	825.1	822.2	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9
130°	861.6	859.4	857.2	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8
132.5°	895.7	893.7	891.5	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3
135°	943.6	941.6	939.8	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8
137.5°	988.3	986.4	984.3	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8
140°	1017.4	1015.6	1013.4	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2
142.5°	1044.3	1042.6	1040.1	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5
145°	1081.8	1080.4	1077.0	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8
147.5°	1114.7	1113.7	1110.3	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8
150°	1134.6	1133.4	1130.2	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2
152.5°	1152.9	1151.7	1148.6	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9
155°	1177.5	1176.3	1173.9	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6
157.5°	1198.2	1196.8	1195.1	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0
160°	1210.4	1209.2	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2
162.5°	1221.5	1220.2	1219.1	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9
165°	1235.3	1233.9	1233.3	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6
167.5°	1246.8	1245.4	1244.8	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3
170°	1252.6	1251.2	1250.8	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9
172.5°	1257.0	1255.6	1255.2	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2
175°	1261.8	1260.3	1259.9	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9
177.5°	1262.6	1261.4	1261.3	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.4	8.8	8.9	8.9	9.7	10.0	9.9	10.3	11.0	10.8	11.4
90°	3.1	5.4	7.6	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3
92.5°	18.2	18.0	17.8	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2
95°	52.7	46.0	39.3	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6
97.5°	98.9	80.1	61.2	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3
100°	133.8	106.0	78.2	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3
102.5°	204.0	198.1	192.2	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7
105°	283.7	289.8	295.9	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2
107.5°	359.8	364.7	369.6	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4
110°	408.9	413.1	417.4	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2





TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.1	458.9	462.7	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1
115°	528.6	532.0	535.5	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6
117.5°	594.9	598.8	602.7	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7
120°	642.3	645.4	648.4	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3
122.5°	683.4	686.6	689.8	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5
125°	745.1	747.8	750.4	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6
127.5°	801.9	804.8	807.7	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2
130°	838.0	841.2	844.5	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9
132.5°	874.0	876.8	879.6	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6
135°	922.0	925.3	928.5	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7
137.5°	969.1	971.4	973.6	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3
140°	999.9	1001.5	1003.1	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2
142.5°	1026.0	1027.5	1028.9	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9
145°	1065.6	1065.4	1065.2	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3
147.5°	1101.0	1100.3	1099.5	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8
150°	1123.8	1122.3	1120.9	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8
152.5°	1143.3	1141.7	1140.2	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1
155°	1171.8	1169.9	1168.1	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8
157.5°	1194.5	1193.0	1191.4	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5
160°	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6
162.5°	1219.7	1218.5	1217.2	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9
165°	1235.4	1234.2	1232.9	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7
167.5°	1247.1	1245.9	1244.6	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2
170°	1253.6	1252.4	1251.2	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1
172.5°	1258.0	1256.8	1255.6	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4
175°	1263.5	1262.1	1260.6	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2
177.5°	1264.7	1263.6	1262.4	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	11.2	11.4	11.5	11.6	11.7	11.8	11.5
90°	21.3	22.3	23.0	23.4	23.8	24.3	24.7
92.5°	22.8	23.3	23.7	23.9	24.2	24.4	24.7
95°	38.7	39.7	40.1	39.9	39.7	39.5	39.3
97.5°	50.1	50.9	51.4	51.7	51.9	52.2	52.4
100°	56.9	58.6	59.6	60.0	60.4	60.8	61.2
102.5°	59.9	62.0	63.3	63.9	64.4	65.0	65.6
105°	62.4	64.6	66.2	67.0	67.8	68.6	69.4
107.5°	71.2	68.9	68.2	69.0	69.8	70.6	71.4
110°	98.9	78.6	68.9	69.7	70.5	71.3	72.2



TEST NUMBER: P331693

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	181.0	107.0	70.3	70.9	71.6	72.2	72.9
115°	281.6	187.6	133.3	118.7	104.1	89.5	74.9
117.5°	556.0	533.2	497.8	449.8	401.8	353.8	305.8
120°	676.8	679.2	666.7	639.3	611.9	584.5	557.1
122.5°	716.9	718.4	716.5	711.2	705.8	700.5	695.2
125°	776.0	777.4	778.4	779.0	779.6	780.3	780.9
127.5°	831.3	833.4	834.4	834.6	834.7	834.8	834.9
130°	866.1	868.3	869.4	869.2	868.9	868.7	868.5
132.5°	899.5	901.4	902.2	902.0	901.8	901.6	901.4
135°	947.7	949.7	950.5	950.1	949.7	949.3	948.9
137.5°	992.3	994.3	995.0	994.3	993.6	992.9	992.2
140°	1021.1	1022.9	1023.3	1022.3	1021.3	1020.3	1019.2
142.5°	1047.6	1049.3	1049.6	1048.6	1047.6	1046.6	1045.5
145°	1084.7	1086.1	1086.3	1085.3	1084.3	1083.3	1082.3
147.5°	1116.8	1117.9	1118.0	1117.1	1116.3	1115.4	1114.6
150°	1137.1	1138.3	1138.4	1137.4	1136.3	1135.3	1134.3
152.5°	1155.3	1156.5	1156.5	1155.1	1153.8	1152.5	1151.1
155°	1180.0	1181.2	1181.0	1179.4	1177.7	1176.1	1174.5
157.5°	1200.9	1202.3	1202.2	1200.6	1199.0	1197.4	1195.9
160°	1212.9	1214.1	1214.0	1212.5	1211.1	1209.7	1208.3
162.5°	1224.3	1225.7	1225.5	1223.8	1222.0	1220.3	1218.5
165°	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9
167.5°	1249.6	1251.1	1250.8	1249.0	1247.2	1245.4	1243.5
170°	1255.5	1256.9	1256.7	1254.9	1253.0	1251.2	1249.4
172.5°	1259.9	1261.3	1261.1	1259.2	1257.4	1255.6	1253.8
175°	1264.6	1266.0	1265.7	1263.7	1261.7	1259.6	1257.6
177.5°	1264.9	1266.0	1265.8	1264.4	1262.9	1261.4	1260.0
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2

(END OF REPORT)