

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331695

Luminaire Tested: **SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331695  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6154.9 lumens  
Efficiency: N/A  
Efficacy: 118.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331695  
CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	89	86	88	85	81	79	70	68	66	56	55	53	43	43	42	36
2	88	81	76	71	80	75	70	66	62	58	55	50	48	46	39	38	36	31
3	81	72	65	60	74	66	60	56	55	51	47	45	42	39	35	33	32	27
4	74	64	57	51	68	59	53	48	49	45	41	40	37	34	32	30	28	24
5	69	58	50	44	63	53	47	42	45	40	36	37	33	30	29	27	25	21
6	63	52	44	39	58	48	41	36	40	35	32	33	30	27	27	24	22	19
7	59	47	40	34	54	44	37	32	37	32	28	31	27	24	25	22	20	17
8	55	43	36	31	50	40	33	29	34	29	25	28	24	22	23	20	18	16
9	51	39	32	27	47	37	30	26	31	26	23	26	22	20	21	19	17	15
10	48	36	29	25	44	34	28	23	29	24	21	24	21	18	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.3	2.3
10°-20°	388.0	6.3
20°-30°	500.0	8.1
30°-40°	475.2	7.7
40°-50°	407.1	6.6
50°-60°	310.0	5.0
60°-70°	196.0	3.2
70°-80°	97.9	1.6
80°-90°	30.1	0.5
90°-100°	207.5	3.4
100°-110°	704.2	11.4
110°-120°	748.1	12.2
120°-130°	615.8	10.0
130°-140°	494.5	8.0
140°-150°	373.7	6.1
150°-160°	262.6	4.3
160°-170°	154.6	2.5
170°-180°	50.3	0.8
0°-30°	1027.3	16.7
0°-40°	1502.5	24.4
0°-60°	2219.6	36.1
0°-90°	2543.6	41.3
90°-120°	1659.8	27.0
90°-150°	3143.8	51.1
90°-180°	3611.0	58.7
0°-180°	6154.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	21
90°	33	1	33	1	33	18
95°	114	35	114	35	114	148
105°	1125	122	1125	122	1125	1088
115°	1480	215	1480	215	1480	1449
125°	1201	299	1201	299	1201	1085
135°	995	351	995	351	995	773
145°	794	401	794	401	794	505
155°	668	456	668	456	668	312
165°	586	497	586	497	586	168
175°	528	518	528	518	528	51
180°	519	519	519	519	519	



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	13.1	13.5	13.5	13.5	13.5	13.3	12.9	13.7	13.5	14.1	13.5
90°	32.9	32.9	32.9	32.9	32.9	31.9	29.9	31.9	32.9	33.9	32.9
92.5°	55.3	56.9	56.1	59.3	60.1	66.3	74.7	87.0	109.6	129.7	127.9
95°	113.8	112.8	115.8	123.8	136.7	158.7	200.6	261.5	342.3	391.2	346.3
97.5°	224.0	232.3	246.9	271.5	319.2	391.2	499.2	610.2	700.6	667.9	503.0
100°	357.3	375.3	404.2	447.1	530.0	650.7	787.4	911.2	932.2	788.4	542.9
102.5°	628.8	653.1	689.2	762.5	852.5	980.5	1080.5	1108.4	1018.4	792.4	527.8
105°	1124.8	1138.7	1181.7	1243.5	1305.4	1338.4	1325.4	1212.6	1005.0	739.5	498.0
107.5°	1436.8	1455.3	1463.9	1467.3	1459.5	1411.2	1307.4	1137.6	917.4	682.9	483.2
110°	1531.0	1532.0	1523.0	1504.0	1461.1	1379.3	1251.5	1072.9	862.3	655.7	480.1



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1529.4	1524.0	1507.0	1475.3	1415.6	1321.8	1185.3	1013.8	824.0	638.1	480.8
115°	1480.1	1471.1	1445.1	1399.2	1328.4	1225.6	1094.8	941.1	776.5	618.8	485.0
117.5°	1392.0	1384.5	1357.1	1308.6	1236.4	1139.9	1021.4	886.4	746.5	609.4	492.2
120°	1335.4	1325.4	1296.4	1249.5	1179.7	1088.8	983.1	859.3	730.6	603.8	497.0
122.5°	1276.3	1267.9	1242.1	1196.0	1133.4	1051.3	951.1	837.7	717.0	600.6	502.6
125°	1200.6	1192.6	1167.7	1129.8	1071.9	997.0	909.2	806.4	697.6	594.8	511.0
127.5°	1134.4	1128.0	1106.4	1070.9	1020.4	951.3	868.5	775.5	679.7	591.4	519.6
130°	1096.8	1088.8	1068.9	1035.0	986.1	920.2	841.3	755.5	667.7	589.8	526.0
132.5°	1057.7	1050.5	1032.2	998.2	950.1	888.2	815.8	736.3	658.1	589.0	532.3
135°	995.0	991.0	973.1	940.1	897.2	841.3	775.5	709.6	644.7	587.8	539.9
137.5°	933.6	927.6	911.8	883.5	844.3	795.6	743.3	688.2	635.3	587.6	546.7
140°	891.2	885.3	870.3	844.3	812.4	768.5	722.6	674.7	629.8	586.8	549.9
142.5°	848.9	847.7	834.4	810.8	780.5	743.7	704.2	663.5	624.2	586.8	552.3
145°	794.4	791.4	781.5	764.5	740.5	711.6	680.7	647.7	616.8	584.8	554.9
147.5°	748.7	746.9	740.1	726.6	706.8	685.6	661.5	635.5	609.2	581.3	555.7
150°	721.6	720.6	714.6	702.6	687.6	669.7	648.7	626.8	602.8	578.9	554.9
152.5°	698.4	698.2	693.8	683.4	671.7	656.1	638.3	618.0	597.2	574.9	553.3
155°	667.7	669.7	665.7	658.7	647.7	636.7	621.8	605.8	586.8	567.9	550.9
157.5°	641.5	641.5	639.7	633.9	626.2	617.6	605.0	591.6	577.1	560.7	546.3
160°	624.8	624.8	623.8	618.8	611.8	604.8	593.8	582.8	569.9	555.9	543.9
162.5°	608.8	609.6	608.6	605.2	598.2	592.8	583.4	574.1	563.5	551.9	541.5
165°	585.8	586.8	586.8	582.8	578.9	574.9	567.9	560.9	552.9	543.9	536.9
167.5°	564.7	565.9	566.1	563.9	562.1	558.5	553.7	548.3	542.5	536.9	532.3
170°	551.9	553.9	554.9	551.9	550.9	548.9	544.9	541.9	536.9	532.9	530.0
172.5°	541.5	542.7	543.7	542.3	541.3	540.1	536.9	534.7	531.4	528.2	526.8
175°	528.0	530.0	531.0	530.0	530.0	529.0	528.0	527.0	524.0	523.0	522.0
177.5°	519.8	521.4	522.2	522.2	522.2	522.2	521.4	521.4	519.8	519.0	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	12.3	11.3	10.3	9.3	9.3	9.4	10.6	12.0	11.0	10.6	10.2
90°	26.9	20.0	15.0	12.0	10.0	8.0	4.0	1.0	4.0	8.0	10.0
92.5°	99.6	67.9	45.3	35.9	29.1	24.8	17.6	12.2	17.6	24.8	29.1
95°	230.5	143.7	97.8	73.9	57.9	48.9	38.9	34.9	38.9	48.9	57.9
97.5°	310.6	189.6	131.9	104.8	86.4	72.9	62.3	56.9	62.3	72.9	86.4
100°	327.4	205.6	152.7	124.8	104.8	88.8	79.8	76.8	79.8	88.8	104.8
102.5°	328.2	220.0	171.1	143.1	122.4	106.4	97.4	95.2	97.4	106.4	122.4
105°	333.3	244.5	197.6	169.7	147.7	132.7	125.8	121.8	125.8	132.7	147.7
107.5°	347.1	269.7	224.2	196.0	174.3	160.5	153.7	150.5	153.7	160.5	174.3
110°	358.3	286.4	242.5	213.6	192.6	179.6	173.7	169.7	173.7	179.6	192.6





TEST NUMBER: P331695  
 CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	370.3	302.4	260.1	230.3	210.2	198.0	191.2	187.2	191.2	198.0	210.2
115°	388.2	327.4	284.4	257.5	237.5	225.6	219.6	214.6	219.6	225.6	237.5
117.5°	407.4	350.3	310.6	282.6	263.5	252.9	246.9	242.9	246.9	252.9	263.5
120°	420.2	366.3	327.4	299.4	279.4	270.5	264.5	260.5	264.5	270.5	279.4
122.5°	431.3	381.4	344.9	316.2	296.2	286.4	280.4	277.3	280.4	286.4	296.2
125°	449.1	404.2	368.3	340.3	320.4	308.4	302.4	299.4	302.4	308.4	320.4
127.5°	465.7	425.4	390.4	361.7	342.5	329.3	321.0	317.0	321.0	329.3	342.5
130°	476.1	438.1	403.2	375.3	355.3	341.3	331.3	327.4	331.3	341.3	355.3
132.5°	486.4	449.3	416.0	388.0	367.3	352.5	341.7	336.9	341.7	352.5	367.3
135°	500.0	465.1	433.1	405.2	382.2	367.3	355.3	351.3	355.3	367.3	382.2
137.5°	510.4	477.9	446.3	420.4	397.6	381.6	369.7	364.9	369.7	381.6	397.6
140°	516.0	485.0	455.1	429.2	407.2	391.2	379.3	375.3	379.3	391.2	407.2
142.5°	520.8	490.6	461.5	437.1	416.0	400.0	388.8	385.6	388.8	400.0	416.0
145°	527.0	499.0	472.1	450.1	430.2	415.2	405.2	401.2	405.2	415.2	430.2
147.5°	530.4	505.8	480.5	460.9	444.3	430.5	421.0	418.0	421.0	430.5	444.3
150°	531.9	509.0	486.0	468.1	453.1	440.1	432.1	429.2	432.1	440.1	453.1
152.5°	532.7	512.2	491.6	475.3	461.1	449.7	441.7	440.3	441.7	449.7	461.1
155°	533.9	517.0	500.0	485.0	474.1	463.1	457.1	456.1	457.1	463.1	474.1
157.5°	533.9	520.4	506.0	493.4	484.6	475.1	470.3	469.3	470.3	475.1	484.6
160°	533.9	522.0	510.0	499.0	491.0	483.0	479.1	478.1	479.1	483.0	491.0
162.5°	533.1	522.8	512.4	503.8	496.6	490.2	486.2	486.8	486.2	490.2	496.6
165°	531.0	524.0	515.0	509.0	504.0	498.0	496.0	497.0	496.0	498.0	504.0
167.5°	529.6	523.8	517.2	513.4	509.8	506.0	504.2	505.4	504.2	506.0	509.8
170°	528.0	523.0	518.0	515.0	513.0	510.0	509.0	511.0	509.0	510.0	513.0
172.5°	525.6	522.2	518.8	516.6	515.4	512.4	513.0	514.2	513.0	512.4	515.4
175°	523.0	521.0	519.0	518.0	518.0	516.0	517.0	518.0	517.0	516.0	518.0
177.5°	521.4	519.8	519.0	519.0	519.0	517.4	518.2	519.8	518.2	517.4	519.0
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	10.2	10.3	10.5	11.9	13.1	12.9	12.7	12.1	11.7	12.1	11.9
90°	12.0	15.0	20.0	26.9	32.9	33.9	32.9	31.9	29.9	31.9	32.9
92.5°	35.9	45.3	67.9	99.6	127.9	129.7	109.6	87.0	74.7	66.3	60.1
95°	73.9	97.8	143.7	230.5	346.3	391.2	342.3	261.5	200.6	158.7	136.7
97.5°	104.8	131.9	189.6	310.6	503.0	667.9	700.6	610.2	499.2	391.2	319.2
100°	124.8	152.7	205.6	327.4	542.9	788.4	932.2	911.2	787.4	650.7	530.0
102.5°	143.1	171.1	220.0	328.2	527.8	792.4	1018.4	1108.4	1080.5	980.5	852.5
105°	169.7	197.6	244.5	333.3	498.0	739.5	1005.0	1212.6	1325.4	1338.4	1305.4
107.5°	196.0	224.2	269.7	347.1	483.2	682.9	917.4	1137.6	1307.4	1411.2	1459.5
110°	213.6	242.5	286.4	358.3	480.1	655.7	862.3	1072.9	1251.5	1379.3	1461.1



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.3	260.1	302.4	370.3	480.8	638.1	824.0	1013.8	1185.3	1321.8	1415.6
115°	257.5	284.4	327.4	388.2	485.0	618.8	776.5	941.1	1094.8	1225.6	1328.4
117.5°	282.6	310.6	350.3	407.4	492.2	609.4	746.5	886.4	1021.4	1139.9	1236.4
120°	299.4	327.4	366.3	420.2	497.0	603.8	730.6	859.3	983.1	1088.8	1179.7
122.5°	316.2	344.9	381.4	431.3	502.6	600.6	717.0	837.7	951.1	1051.3	1133.4
125°	340.3	368.3	404.2	449.1	511.0	594.8	697.6	806.4	909.2	997.0	1071.9
127.5°	361.7	390.4	425.4	465.7	519.6	591.4	679.7	775.5	868.5	951.3	1020.4
130°	375.3	403.2	438.1	476.1	526.0	589.8	667.7	755.5	841.3	920.2	986.1
132.5°	388.0	416.0	449.3	486.4	532.3	589.0	658.1	736.3	815.8	888.2	950.1
135°	405.2	433.1	465.1	500.0	539.9	587.8	644.7	709.6	775.5	841.3	897.2
137.5°	420.4	446.3	477.9	510.4	546.7	587.6	635.3	688.2	743.3	795.6	844.3
140°	429.2	455.1	485.0	516.0	549.9	586.8	629.8	674.7	722.6	768.5	812.4
142.5°	437.1	461.5	490.6	520.8	552.3	586.8	624.2	663.5	704.2	743.7	780.5
145°	450.1	472.1	499.0	527.0	554.9	584.8	616.8	647.7	680.7	711.6	740.5
147.5°	460.9	480.5	505.8	530.4	555.7	581.3	609.2	635.5	661.5	685.6	706.8
150°	468.1	486.0	509.0	531.9	554.9	578.9	602.8	626.8	648.7	669.7	687.6
152.5°	475.3	491.6	512.2	532.7	553.3	574.9	597.2	618.0	638.3	656.1	671.7
155°	485.0	500.0	517.0	533.9	550.9	567.9	586.8	605.8	621.8	636.7	647.7
157.5°	493.4	506.0	520.4	533.9	546.3	560.7	577.1	591.6	605.0	617.6	626.2
160°	499.0	510.0	522.0	533.9	543.9	555.9	569.9	582.8	593.8	604.8	611.8
162.5°	503.8	512.4	522.8	533.1	541.5	551.9	563.5	574.1	583.4	592.8	598.2
165°	509.0	515.0	524.0	531.0	536.9	543.9	552.9	560.9	567.9	574.9	578.9
167.5°	513.4	517.2	523.8	529.6	532.3	536.9	542.5	548.3	553.7	558.5	562.1
170°	515.0	518.0	523.0	528.0	530.0	532.9	536.9	541.9	544.9	548.9	550.9
172.5°	516.6	518.8	522.2	525.6	526.8	528.2	531.4	534.7	536.9	540.1	541.3
175°	518.0	519.0	521.0	523.0	522.0	523.0	524.0	527.0	528.0	529.0	530.0
177.5°	519.0	519.0	519.8	521.4	519.8	519.0	519.8	521.4	521.4	522.2	522.2
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	11.9	11.5	11.9	11.5	11.9	11.5	11.9	11.9	12.1	11.7	12.1
90°	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.9	31.9	29.9	31.9
92.5°	59.3	56.1	56.9	55.3	56.9	56.1	59.3	60.1	66.3	74.7	87.0
95°	123.8	115.8	112.8	113.8	112.8	115.8	123.8	136.7	158.7	200.6	261.5
97.5°	271.5	246.9	232.3	224.0	232.3	246.9	271.5	319.2	391.2	499.2	610.2
100°	447.1	404.2	375.3	357.3	375.3	404.2	447.1	530.0	650.7	787.4	911.2
102.5°	762.5	689.2	653.1	628.8	653.1	689.2	762.5	852.5	980.5	1080.5	1108.4
105°	1243.5	1181.7	1138.7	1124.8	1138.7	1181.7	1243.5	1305.4	1338.4	1325.4	1212.6
107.5°	1467.3	1463.9	1455.3	1436.8	1455.3	1463.9	1467.3	1459.5	1411.2	1307.4	1137.6
110°	1504.0	1523.0	1532.0	1531.0	1532.0	1523.0	1504.0	1461.1	1379.3	1251.5	1072.9



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1475.3	1507.0	1524.0	1529.4	1524.0	1507.0	1475.3	1415.6	1321.8	1185.3	1013.8
115°	1399.2	1445.1	1471.1	1480.1	1471.1	1445.1	1399.2	1328.4	1225.6	1094.8	941.1
117.5°	1308.6	1357.1	1384.5	1392.0	1384.5	1357.1	1308.6	1236.4	1139.9	1021.4	886.4
120°	1249.5	1296.4	1325.4	1335.4	1325.4	1296.4	1249.5	1179.7	1088.8	983.1	859.3
122.5°	1196.0	1242.1	1267.9	1276.3	1267.9	1242.1	1196.0	1133.4	1051.3	951.1	837.7
125°	1129.8	1167.7	1192.6	1200.6	1192.6	1167.7	1129.8	1071.9	997.0	909.2	806.4
127.5°	1070.9	1106.4	1128.0	1134.4	1128.0	1106.4	1070.9	1020.4	951.3	868.5	775.5
130°	1035.0	1068.9	1088.8	1096.8	1088.8	1068.9	1035.0	986.1	920.2	841.3	755.5
132.5°	998.2	1032.2	1050.5	1057.7	1050.5	1032.2	998.2	950.1	888.2	815.8	736.3
135°	940.1	973.1	991.0	995.0	991.0	973.1	940.1	897.2	841.3	775.5	709.6
137.5°	883.5	911.8	927.6	933.6	927.6	911.8	883.5	844.3	795.6	743.3	688.2
140°	844.3	870.3	885.3	891.2	885.3	870.3	844.3	812.4	768.5	722.6	674.7
142.5°	810.8	834.4	847.7	848.9	847.7	834.4	810.8	780.5	743.7	704.2	663.5
145°	764.5	781.5	791.4	794.4	791.4	781.5	764.5	740.5	711.6	680.7	647.7
147.5°	726.6	740.1	746.9	748.7	746.9	740.1	726.6	706.8	685.6	661.5	635.5
150°	702.6	714.6	720.6	721.6	720.6	714.6	702.6	687.6	669.7	648.7	626.8
152.5°	683.4	693.8	698.2	698.4	698.2	693.8	683.4	671.7	656.1	638.3	618.0
155°	658.7	665.7	669.7	667.7	669.7	665.7	658.7	647.7	636.7	621.8	605.8
157.5°	633.9	639.7	641.5	641.5	641.5	639.7	633.9	626.2	617.6	605.0	591.6
160°	618.8	623.8	624.8	624.8	624.8	623.8	618.8	611.8	604.8	593.8	582.8
162.5°	605.2	608.6	609.6	608.8	609.6	608.6	605.2	598.2	592.8	583.4	574.1
165°	582.8	586.8	586.8	585.8	586.8	586.8	582.8	578.9	574.9	567.9	560.9
167.5°	563.9	566.1	565.9	564.7	565.9	566.1	563.9	562.1	558.5	553.7	548.3
170°	551.9	554.9	553.9	551.9	553.9	554.9	551.9	550.9	548.9	544.9	541.9
172.5°	542.3	543.7	542.7	541.5	542.7	543.7	542.3	541.3	540.1	536.9	534.7
175°	530.0	531.0	530.0	528.0	530.0	531.0	530.0	530.0	529.0	528.0	527.0
177.5°	522.2	522.2	521.4	519.8	521.4	522.2	522.2	522.2	522.2	521.4	521.4
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	12.7	12.9	13.1	11.9	10.5	10.3	10.2	10.2	10.6	11.0	12.0
90°	32.9	33.9	32.9	26.9	20.0	15.0	12.0	10.0	8.0	4.0	1.0
92.5°	109.6	129.7	127.9	99.6	67.9	45.3	35.9	29.1	24.8	17.6	12.2
95°	342.3	391.2	346.3	230.5	143.7	97.8	73.9	57.9	48.9	38.9	34.9
97.5°	700.6	667.9	503.0	310.6	189.6	131.9	104.8	86.4	72.9	62.3	56.9
100°	932.2	788.4	542.9	327.4	205.6	152.7	124.8	104.8	88.8	79.8	76.8
102.5°	1018.4	792.4	527.8	328.2	220.0	171.1	143.1	122.4	106.4	97.4	95.2
105°	1005.0	739.5	498.0	333.3	244.5	197.6	169.7	147.7	132.7	125.8	121.8
107.5°	917.4	682.9	483.2	347.1	269.7	224.2	196.0	174.3	160.5	153.7	150.5
110°	862.3	655.7	480.1	358.3	286.4	242.5	213.6	192.6	179.6	173.7	169.7



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	824.0	638.1	480.8	370.3	302.4	260.1	230.3	210.2	198.0	191.2	187.2
115°	776.5	618.8	485.0	388.2	327.4	284.4	257.5	237.5	225.6	219.6	214.6
117.5°	746.5	609.4	492.2	407.4	350.3	310.6	282.6	263.5	252.9	246.9	242.9
120°	730.6	603.8	497.0	420.2	366.3	327.4	299.4	279.4	270.5	264.5	260.5
122.5°	717.0	600.6	502.6	431.3	381.4	344.9	316.2	296.2	286.4	280.4	277.3
125°	697.6	594.8	511.0	449.1	404.2	368.3	340.3	320.4	308.4	302.4	299.4
127.5°	679.7	591.4	519.6	465.7	425.4	390.4	361.7	342.5	329.3	321.0	317.0
130°	667.7	589.8	526.0	476.1	438.1	403.2	375.3	355.3	341.3	331.3	327.4
132.5°	658.1	589.0	532.3	486.4	449.3	416.0	388.0	367.3	352.5	341.7	336.9
135°	644.7	587.8	539.9	500.0	465.1	433.1	405.2	382.2	367.3	355.3	351.3
137.5°	635.3	587.6	546.7	510.4	477.9	446.3	420.4	397.6	381.6	369.7	364.9
140°	629.8	586.8	549.9	516.0	485.0	455.1	429.2	407.2	391.2	379.3	375.3
142.5°	624.2	586.8	552.3	520.8	490.6	461.5	437.1	416.0	400.0	388.8	385.6
145°	616.8	584.8	554.9	527.0	499.0	472.1	450.1	430.2	415.2	405.2	401.2
147.5°	609.2	581.3	555.7	530.4	505.8	480.5	460.9	444.3	430.5	421.0	418.0
150°	602.8	578.9	554.9	531.9	509.0	486.0	468.1	453.1	440.1	432.1	429.2
152.5°	597.2	574.9	553.3	532.7	512.2	491.6	475.3	461.1	449.7	441.7	440.3
155°	586.8	567.9	550.9	533.9	517.0	500.0	485.0	474.1	463.1	457.1	456.1
157.5°	577.1	560.7	546.3	533.9	520.4	506.0	493.4	484.6	475.1	470.3	469.3
160°	569.9	555.9	543.9	533.9	522.0	510.0	499.0	491.0	483.0	479.1	478.1
162.5°	563.5	551.9	541.5	533.1	522.8	512.4	503.8	496.6	490.2	486.2	486.8
165°	552.9	543.9	536.9	531.0	524.0	515.0	509.0	504.0	498.0	496.0	497.0
167.5°	542.5	536.9	532.3	529.6	523.8	517.2	513.4	509.8	506.0	504.2	505.4
170°	536.9	532.9	530.0	528.0	523.0	518.0	515.0	513.0	510.0	509.0	511.0
172.5°	531.4	528.2	526.8	525.6	522.2	518.8	516.6	515.4	512.4	513.0	514.2
175°	524.0	523.0	522.0	523.0	521.0	519.0	518.0	518.0	516.0	517.0	518.0
177.5°	519.8	519.0	519.8	521.4	519.8	519.0	519.0	519.0	517.4	518.2	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.6	9.4	9.3	9.3	10.3	11.3	12.3	13.5	14.1	13.5	13.7
90°	4.0	8.0	10.0	12.0	15.0	20.0	26.9	32.9	33.9	32.9	31.9
92.5°	17.6	24.8	29.1	35.9	45.3	67.9	99.6	127.9	129.7	109.6	87.0
95°	38.9	48.9	57.9	73.9	97.8	143.7	230.5	346.3	391.2	342.3	261.5
97.5°	62.3	72.9	86.4	104.8	131.9	189.6	310.6	503.0	667.9	700.6	610.2
100°	79.8	88.8	104.8	124.8	152.7	205.6	327.4	542.9	788.4	932.2	911.2
102.5°	97.4	106.4	122.4	143.1	171.1	220.0	328.2	527.8	792.4	1018.4	1108.4
105°	125.8	132.7	147.7	169.7	197.6	244.5	333.3	498.0	739.5	1005.0	1212.6
107.5°	153.7	160.5	174.3	196.0	224.2	269.7	347.1	483.2	682.9	917.4	1137.6
110°	173.7	179.6	192.6	213.6	242.5	286.4	358.3	480.1	655.7	862.3	1072.9





TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	191.2	198.0	210.2	230.3	260.1	302.4	370.3	480.8	638.1	824.0	1013.8
115°	219.6	225.6	237.5	257.5	284.4	327.4	388.2	485.0	618.8	776.5	941.1
117.5°	246.9	252.9	263.5	282.6	310.6	350.3	407.4	492.2	609.4	746.5	886.4
120°	264.5	270.5	279.4	299.4	327.4	366.3	420.2	497.0	603.8	730.6	859.3
122.5°	280.4	286.4	296.2	316.2	344.9	381.4	431.3	502.6	600.6	717.0	837.7
125°	302.4	308.4	320.4	340.3	368.3	404.2	449.1	511.0	594.8	697.6	806.4
127.5°	321.0	329.3	342.5	361.7	390.4	425.4	465.7	519.6	591.4	679.7	775.5
130°	331.3	341.3	355.3	375.3	403.2	438.1	476.1	526.0	589.8	667.7	755.5
132.5°	341.7	352.5	367.3	388.0	416.0	449.3	486.4	532.3	589.0	658.1	736.3
135°	355.3	367.3	382.2	405.2	433.1	465.1	500.0	539.9	587.8	644.7	709.6
137.5°	369.7	381.6	397.6	420.4	446.3	477.9	510.4	546.7	587.6	635.3	688.2
140°	379.3	391.2	407.2	429.2	455.1	485.0	516.0	549.9	586.8	629.8	674.7
142.5°	388.8	400.0	416.0	437.1	461.5	490.6	520.8	552.3	586.8	624.2	663.5
145°	405.2	415.2	430.2	450.1	472.1	499.0	527.0	554.9	584.8	616.8	647.7
147.5°	421.0	430.5	444.3	460.9	480.5	505.8	530.4	555.7	581.3	609.2	635.5
150°	432.1	440.1	453.1	468.1	486.0	509.0	531.9	554.9	578.9	602.8	626.8
152.5°	441.7	449.7	461.1	475.3	491.6	512.2	532.7	553.3	574.9	597.2	618.0
155°	457.1	463.1	474.1	485.0	500.0	517.0	533.9	550.9	567.9	586.8	605.8
157.5°	470.3	475.1	484.6	493.4	506.0	520.4	533.9	546.3	560.7	577.1	591.6
160°	479.1	483.0	491.0	499.0	510.0	522.0	533.9	543.9	555.9	569.9	582.8
162.5°	486.2	490.2	496.6	503.8	512.4	522.8	533.1	541.5	551.9	563.5	574.1
165°	496.0	498.0	504.0	509.0	515.0	524.0	531.0	536.9	543.9	552.9	560.9
167.5°	504.2	506.0	509.8	513.4	517.2	523.8	529.6	532.3	536.9	542.5	548.3
170°	509.0	510.0	513.0	515.0	518.0	523.0	528.0	530.0	532.9	536.9	541.9
172.5°	513.0	512.4	515.4	516.6	518.8	522.2	525.6	526.8	528.2	531.4	534.7
175°	517.0	516.0	518.0	518.0	519.0	521.0	523.0	522.0	523.0	524.0	527.0
177.5°	518.2	517.4	519.0	519.0	519.0	519.8	521.4	519.8	519.0	519.8	521.4
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	12.9	13.3	13.5	13.5	13.5	13.5	13.1
90°	29.9	31.9	32.9	32.9	32.9	32.9	32.9
92.5°	74.7	66.3	60.1	59.3	56.1	56.9	55.3
95°	200.6	158.7	136.7	123.8	115.8	112.8	113.8
97.5°	499.2	391.2	319.2	271.5	246.9	232.3	224.0
100°	787.4	650.7	530.0	447.1	404.2	375.3	357.3
102.5°	1080.5	980.5	852.5	762.5	689.2	653.1	628.8
105°	1325.4	1338.4	1305.4	1243.5	1181.7	1138.7	1124.8
107.5°	1307.4	1411.2	1459.5	1467.3	1463.9	1455.3	1436.8
110°	1251.5	1379.3	1461.1	1504.0	1523.0	1532.0	1531.0



TEST NUMBER: P331695

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1185.3	1321.8	1415.6	1475.3	1507.0	1524.0	1529.4
115°	1094.8	1225.6	1328.4	1399.2	1445.1	1471.1	1480.1
117.5°	1021.4	1139.9	1236.4	1308.6	1357.1	1384.5	1392.0
120°	983.1	1088.8	1179.7	1249.5	1296.4	1325.4	1335.4
122.5°	951.1	1051.3	1133.4	1196.0	1242.1	1267.9	1276.3
125°	909.2	997.0	1071.9	1129.8	1167.7	1192.6	1200.6
127.5°	868.5	951.3	1020.4	1070.9	1106.4	1128.0	1134.4
130°	841.3	920.2	986.1	1035.0	1068.9	1088.8	1096.8
132.5°	815.8	888.2	950.1	998.2	1032.2	1050.5	1057.7
135°	775.5	841.3	897.2	940.1	973.1	991.0	995.0
137.5°	743.3	795.6	844.3	883.5	911.8	927.6	933.6
140°	722.6	768.5	812.4	844.3	870.3	885.3	891.2
142.5°	704.2	743.7	780.5	810.8	834.4	847.7	848.9
145°	680.7	711.6	740.5	764.5	781.5	791.4	794.4
147.5°	661.5	685.6	706.8	726.6	740.1	746.9	748.7
150°	648.7	669.7	687.6	702.6	714.6	720.6	721.6
152.5°	638.3	656.1	671.7	683.4	693.8	698.2	698.4
155°	621.8	636.7	647.7	658.7	665.7	669.7	667.7
157.5°	605.0	617.6	626.2	633.9	639.7	641.5	641.5
160°	593.8	604.8	611.8	618.8	623.8	624.8	624.8
162.5°	583.4	592.8	598.2	605.2	608.6	609.6	608.8
165°	567.9	574.9	578.9	582.8	586.8	586.8	585.8
167.5°	553.7	558.5	562.1	563.9	566.1	565.9	564.7
170°	544.9	548.9	550.9	551.9	554.9	553.9	551.9
172.5°	536.9	540.1	541.3	542.3	543.7	542.7	541.5
175°	528.0	529.0	530.0	530.0	531.0	530.0	528.0
177.5°	521.4	522.2	522.2	522.2	522.2	521.4	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0

(END OF REPORT)