

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331729

Luminaire Tested: **SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331729
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7609.1 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				
1	97	93	89	86	89	85	82	79	71	69	67	57	56	55	45	44	44	38				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				
3	82	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29				
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25				
5	69	58	50	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23				
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20				
7	59	48	40	35	54	44	37	33	38	32	29	32	28	25	26	23	21	18				
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17				
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15				
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30832	30832	30832	30832
5°	34434	31024	27509	31024
10°	38203	30808	23845	30808
15°	40082	30355	18788	30355
20°	34749	29687	16258	29687
25°	22789	28771	14516	28771
30°	15340	27660	13136	27660
35°	12423	26260	11848	26260
40°	11049	24738	10964	24738
45°	9999	22952	9787	22952
50°	9100	21182	9065	21182
55°	8555	19220	8442	19220
60°	7156	17418	7072	17418
65°	6032	15817	6842	15817
70°	5575	14124	6453	14124
75°	5215	12296	5958	12296
80°	4816	10116	5309	10116
85°	4428	7984	4668	7984



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.4
10°-20°	504.4	6.6
20°-30°	650.0	8.5
30°-40°	617.7	8.1
40°-50°	529.1	7.0
50°-60°	402.9	5.3
60°-70°	254.7	3.3
70°-80°	127.2	1.7
80°-90°	36.7	0.5
90°-100°	49.0	0.6
100°-110°	179.7	2.4
110°-120°	480.4	6.3
120°-130°	793.0	10.4
130°-140°	843.3	11.1
140°-150°	783.8	10.3
150°-160°	630.2	8.3
160°-170°	406.1	5.3
170°-180°	139.8	1.8
0°-30°	1335.4	17.5
0°-40°	1953.1	25.7
0°-60°	2885.1	37.9
0°-90°	3303.8	43.4
90°-120°	709.1	9.3
90°-150°	3129.2	41.1
90°-180°	4305.0	56.6
0°-180°	7609.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	2125	1914	1697	1914	2125	210
15°	2398	1816	1124	1816	2398	647
25°	1279	1615	815	1615	1279	607
35°	630	1332	601	1332	630	403
45°	438	1005	429	1005	438	339
55°	304	683	300	683	304	267
65°	158	414	179	414	158	161
75°	84	197	96	197	84	89
85°	24	43	25	43	24	26
90°	29	1	29	1	29	14
95°	46	69	46	69	46	43
105°	81	323	81	323	81	84
115°	87	611	87	611	87	218
125°	909	864	909	864	909	786
135°	1104	1069	1104	1069	1104	851
145°	1260	1241	1260	1241	1260	788
155°	1367	1366	1367	1366	1367	631
165°	1436	1439	1436	1439	1436	405
175°	1464	1472	1464	1472	1464	139
180°	1469	1469	1469	1469	1469	



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1987.1	1988.7	1990.3	1986.5	1986.5	1983.4	1976.5	1971.2	1956.3	1954.2	1954.2
5°	2124.6	2123.2	2125.9	2117.3	2105.3	2102.7	2090.1	2073.5	2056.2	2037.0	2033.0
7.5°	2261.2	2259.2	2253.9	2252.5	2243.3	2223.3	2203.0	2181.4	2152.7	2124.7	2110.6
10°	2330.2	2352.1	2338.9	2315.6	2320.3	2289.1	2272.5	2244.0	2220.1	2178.3	2169.0
12.5°	2398.2	2406.8	2402.6	2389.4	2383.5	2361.8	2339.4	2314.6	2270.5	2233.0	2200.3
15°	2397.9	2410.5	2413.8	2409.9	2413.2	2411.9	2399.9	2379.3	2340.9	2299.7	2263.9
17.5°	2220.9	2229.7	2251.4	2266.1	2284.7	2324.0	2343.4	2350.9	2345.2	2321.7	2296.5
20°	2022.4	2007.8	2068.8	2100.0	2126.5	2192.9	2250.0	2271.9	2307.0	2306.4	2299.7
22.5°	1741.0	1744.5	1802.4	1839.4	1916.9	1983.2	2048.3	2130.7	2198.7	2243.7	2270.0
25°	1279.2	1304.5	1362.2	1412.6	1498.9	1622.3	1734.4	1864.5	1987.2	2084.1	2176.3
27.5°	960.8	962.6	1008.4	1055.0	1106.2	1207.3	1348.5	1503.8	1678.8	1823.2	1989.3
30°	822.8	818.8	838.0	866.5	910.3	988.6	1094.8	1247.4	1421.9	1639.5	1833.3
32.5°	725.1	725.3	739.8	760.9	797.3	850.1	922.8	1046.8	1211.7	1425.6	1652.8
35°	630.3	629.7	640.3	655.5	670.8	704.6	754.4	819.4	932.9	1132.6	1364.8
37.5°	562.4	565.3	570.5	580.0	596.9	615.7	645.6	689.3	770.1	888.2	1083.4
40°	524.2	525.5	532.8	540.8	550.7	565.3	589.9	625.0	684.1	778.3	920.9
42.5°	489.1	490.5	495.6	503.1	510.9	525.5	545.8	576.2	624.1	697.6	815.3
45°	437.9	437.9	442.6	445.9	454.5	467.8	484.4	509.6	542.7	597.2	675.5
47.5°	389.9	390.0	393.1	398.8	404.2	414.6	430.9	451.5	475.6	517.7	584.6
50°	362.3	362.9	364.9	369.6	372.9	382.2	394.8	412.7	437.9	470.4	526.2
52.5°	340.0	339.6	342.1	344.1	346.4	353.0	362.4	378.2	400.8	429.0	475.2
55°	303.9	301.2	305.2	308.5	310.5	313.2	318.5	328.4	347.7	371.6	406.1
57.5°	258.8	257.7	260.5	263.5	269.8	276.9	281.5	287.8	297.8	314.9	349.1
60°	221.6	221.6	227.6	229.6	236.9	246.2	255.5	260.8	270.7	282.0	307.2
62.5°	188.7	189.2	192.0	194.0	198.1	209.5	222.5	234.2	243.6	254.4	271.1
65°	157.9	159.2	159.2	160.6	163.2	165.9	171.2	180.5	197.1	212.3	224.9
67.5°	134.0	134.4	134.8	136.2	136.8	139.7	141.9	146.0	149.8	164.3	179.9
70°	118.1	120.1	119.4	120.8	121.4	122.7	125.4	127.4	133.4	136.7	146.0
72.5°	103.2	104.7	104.6	105.4	107.1	107.4	109.5	111.5	115.3	118.1	123.1
75°	83.6	82.9	83.6	84.9	85.6	86.3	86.3	88.9	90.9	93.6	96.9
77.5°	64.5	65.2	65.0	65.2	65.3	66.5	66.4	67.5	69.5	70.9	72.5
80°	51.8	52.4	51.8	52.4	53.1	53.7	53.1	53.7	55.7	57.1	57.1
82.5°	40.1	40.2	40.6	40.7	40.9	41.0	41.9	42.1	43.5	43.3	43.8
85°	23.9	23.2	23.2	23.2	23.9	24.5	23.9	23.9	24.5	24.5	24.5
87.5°	14.2	14.7	14.6	14.5	14.4	14.2	14.0	14.3	13.5	13.8	12.9
90°	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6	22.4	21.3	19.4
92.5°	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9	25.3	24.7	23.7
95°	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8	42.6	41.5	39.8
97.5°	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4	56.4	55.5	51.7
100°	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4	62.5	60.6	56.6
102.5°	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2	64.8	62.3	59.9
105°	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0	67.4	64.8	62.3
107.5°	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5	88.1	90.8	168.1
110°	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8	162.4	186.0	254.3



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9	383.1	469.2	486.1
115°	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1	546.5	655.9	650.0
117.5°	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6	700.0	726.5	722.4
120°	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9	782.0	779.2	775.0
122.5°	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8	831.1	829.4	824.8
125°	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6	899.9	898.3	893.8
127.5°	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2	962.8	960.4	957.0
130°	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5	1002.9	1000.3	997.7
132.5°	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7	1042.5	1040.3	1037.7
135°	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7	1098.4	1096.0	1093.9
137.5°	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7	1150.4	1148.1	1145.7
140°	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4	1184.2	1182.1	1179.5
142.5°	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4	1215.5	1213.6	1210.6
145°	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9	1259.2	1257.6	1253.6
147.5°	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7	1297.5	1296.3	1292.3
150°	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1	1320.7	1319.2	1315.5
152.5°	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3	1341.9	1340.5	1336.9
155°	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0	1370.6	1369.2	1366.4
157.5°	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2	1394.6	1393.0	1391.0
160°	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3	1408.9	1407.5	1406.1
162.5°	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4	1421.8	1420.2	1419.0
165°	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2	1435.5
167.5°	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9	1451.2	1449.6	1448.9
170°	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7	1458.0	1456.4	1455.9
172.5°	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8	1463.1	1461.5	1461.0
175°	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3	1468.7	1467.0	1466.5
177.5°	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9	1469.6	1468.3	1468.1
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1955.2	1951.0	1947.3	1937.7	1932.9	1922.3	1920.7	1920.2	1906.4	1893.1	1889.4
5°	2022.4	2011.8	1995.8	1977.3	1958.0	1938.1	1924.8	1914.2	1887.7	1862.5	1847.9
7.5°	2090.1	2067.2	2039.8	2004.6	1975.3	1942.4	1917.9	1896.0	1858.4	1822.3	1798.0
10°	2140.5	2103.3	2066.8	2018.4	1980.6	1943.4	1908.9	1879.1	1836.6	1788.8	1755.0
12.5°	2171.8	2130.9	2080.6	2033.3	1984.3	1937.0	1890.9	1852.5	1802.6	1753.3	1713.0
15°	2214.1	2170.3	2109.3	2041.6	1978.6	1916.9	1863.8	1816.0	1751.0	1691.9	1642.8
17.5°	2248.8	2188.5	2123.0	2044.7	1971.7	1893.3	1824.9	1763.9	1691.5	1620.3	1562.4
20°	2259.9	2200.2	2124.6	2046.3	1960.0	1867.8	1794.1	1727.8	1650.1	1572.5	1506.2
22.5°	2253.0	2206.6	2122.4	2028.7	1940.4	1843.9	1760.7	1683.7	1597.6	1518.4	1441.4
25°	2206.2	2190.2	2110.6	2008.4	1907.6	1795.5	1699.2	1615.0	1516.8	1431.9	1348.2
27.5°	2097.0	2131.3	2082.0	1973.1	1861.0	1740.8	1632.6	1536.7	1434.8	1339.2	1255.9
30°	1991.9	2070.8	2049.6	1948.7	1823.3	1705.2	1583.8	1483.6	1374.8	1276.6	1194.3
32.5°	1848.0	1978.4	1999.2	1914.8	1785.1	1655.3	1528.1	1428.4	1314.8	1211.3	1131.1
35°	1619.0	1814.0	1903.6	1849.9	1719.8	1579.8	1448.4	1332.3	1218.2	1116.0	1036.4
37.5°	1345.7	1611.4	1760.7	1764.5	1645.1	1499.5	1356.5	1241.2	1124.4	1024.1	937.9
40°	1168.4	1456.4	1650.8	1693.9	1593.1	1435.8	1291.2	1173.7	1059.6	961.4	862.6
42.5°	1009.2	1296.1	1535.1	1610.1	1529.9	1373.7	1228.6	1105.8	994.9	902.0	801.0
45°	816.1	1066.9	1330.3	1464.4	1419.9	1275.3	1122.0	1005.2	901.0	820.8	723.9
47.5°	688.5	865.2	1120.1	1301.4	1300.6	1168.6	1017.8	906.0	809.3	734.1	655.7
50°	615.7	769.7	985.3	1191.0	1208.2	1097.4	954.1	843.3	753.1	674.1	611.1
52.5°	550.4	677.3	871.2	1068.4	1117.5	1021.5	882.5	780.2	692.6	620.0	566.0
55°	465.1	563.3	710.6	895.1	969.4	901.7	778.3	682.8	611.8	550.7	504.3
57.5°	393.5	467.1	585.3	733.8	820.4	777.8	676.0	598.4	537.6	482.4	445.7
60°	348.3	408.7	508.9	633.0	728.5	698.7	611.8	539.4	487.7	439.9	405.4
62.5°	305.9	357.8	443.6	544.3	631.9	619.6	548.6	487.9	442.6	399.0	369.8
65°	246.2	284.0	351.0	430.0	500.3	506.3	455.2	414.0	373.6	339.1	313.2
67.5°	196.0	220.7	267.9	334.4	387.1	405.9	374.7	343.3	311.2	284.5	262.1
70°	165.2	185.1	219.6	273.4	321.8	341.7	323.8	299.2	271.4	249.5	230.2
72.5°	133.9	153.3	178.7	218.2	259.7	281.2	275.0	257.3	234.7	216.6	198.4
75°	100.9	106.8	124.1	150.6	183.1	201.7	206.4	197.1	179.1	165.2	154.6
77.5°	74.6	78.2	86.4	100.3	121.6	138.1	144.9	143.8	131.5	123.4	113.5
80°	59.7	61.7	65.7	71.7	87.6	104.2	108.8	108.8	100.2	96.9	86.9
82.5°	45.4	46.8	49.2	52.5	60.0	74.4	79.6	80.7	75.2	70.9	63.0
85°	25.9	25.2	26.5	28.5	29.9	33.8	41.8	43.1	41.8	36.5	34.5
87.5°	12.5	12.7	12.3	11.3	11.3	11.3	13.5	15.6	14.0	12.9	12.4
90°	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5	21.2	21.0	20.8
95°	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1	61.3	53.5	45.7
97.5°	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1	115.2	93.2	71.2
100°	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2	155.8	123.4	91.1
102.5°	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3	237.4	230.6	223.7
105°	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2	330.3	337.3	344.4
107.5°	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1	418.8	424.5	430.2
110°	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9	475.9	480.9	485.8



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4	529.8	534.1	538.5
115°	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3	615.3	619.3	623.3
117.5°	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0	692.5	697.0	701.5
120°	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1	747.7	751.2	754.8
122.5°	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8	795.5	799.2	803.0
125°	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3	867.3	870.4	873.5
127.5°	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0	933.4	936.8	940.2
130°	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6	975.4	979.2	983.0
132.5°	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1	1017.4	1020.6	1023.8
135°	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4	1073.2	1077.0	1080.8
137.5°	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3	1128.0	1130.6	1133.3
140°	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9	1163.8	1165.7	1167.6
142.5°	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5	1194.2	1195.9	1197.6
145°	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6	1240.3	1240.1	1239.9
147.5°	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5	1281.6	1280.7	1279.8
150°	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7	1308.0	1306.4	1304.7
152.5°	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6	1330.8	1328.9	1327.1
155°	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0	1363.9	1361.8	1359.6
157.5°	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2	1390.4	1388.6	1386.8
160°	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1406.1	1404.6	1403.2
162.5°	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1	1419.7	1418.2	1416.8
165°	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4	1437.9	1436.5	1435.1
167.5°	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0	1451.6	1450.1	1448.7
170°	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6	1459.2	1457.8	1456.4
172.5°	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7	1464.3	1462.9	1461.5
175°	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3	1470.7	1469.0	1467.4
177.5°	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4	1472.1	1470.7	1469.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1882.5	1878.8	1871.9	1861.3	1854.9	1843.8	1836.3	1840.6	1841.6	1840.6	1839.5
5°	1831.9	1818.0	1798.8	1780.2	1762.9	1744.4	1733.7	1729.1	1719.8	1714.5	1711.9
7.5°	1770.8	1746.8	1719.5	1687.2	1659.7	1630.9	1616.2	1608.9	1589.9	1579.5	1570.5
10°	1725.1	1687.3	1660.1	1617.6	1591.8	1553.9	1528.1	1528.7	1502.8	1488.2	1477.6
12.5°	1674.7	1633.2	1587.9	1549.7	1513.7	1483.3	1452.2	1439.5	1412.1	1398.0	1369.3
15°	1591.1	1542.7	1494.9	1443.1	1406.6	1359.5	1314.4	1259.3	1214.9	1176.4	1165.8
17.5°	1499.8	1439.8	1391.9	1331.1	1268.6	1189.4	1137.1	1105.1	1078.3	1058.0	1042.9
20°	1437.2	1376.1	1325.0	1233.5	1149.2	1095.5	1057.0	1032.4	1004.6	982.7	970.7
22.5°	1371.3	1307.6	1238.0	1135.8	1070.1	1027.0	992.7	964.5	945.6	928.5	917.6
25°	1277.9	1208.2	1093.5	1023.1	970.0	924.9	901.0	883.8	863.9	840.7	830.0
27.5°	1179.2	1068.4	986.0	933.7	883.0	853.7	832.2	806.4	788.6	778.2	767.1
30°	1105.4	994.6	930.2	873.2	837.3	804.8	779.6	765.0	747.8	729.9	722.6
32.5°	1023.1	934.6	872.9	825.4	789.0	761.3	741.4	717.8	705.3	694.3	679.0
35°	920.9	853.9	797.5	759.1	724.6	702.0	678.8	664.8	642.3	633.0	627.0
37.5°	834.4	776.3	734.2	693.6	666.3	641.3	627.1	605.0	595.2	582.3	569.7
40°	785.6	728.5	688.1	654.9	624.4	605.8	587.9	570.0	555.4	549.4	534.1
42.5°	735.7	689.3	648.8	612.4	592.0	572.3	549.7	536.5	521.4	511.7	502.3
45°	666.8	625.7	591.2	561.3	538.8	518.2	503.6	481.7	473.1	453.8	445.9
47.5°	606.3	568.1	535.2	506.8	484.8	471.4	450.0	432.9	419.1	407.3	397.0
50°	563.3	531.5	499.6	474.4	454.5	435.3	413.4	404.7	383.5	377.5	371.6
52.5°	524.0	493.8	464.6	439.9	420.0	401.3	382.0	370.8	356.4	350.5	346.1
55°	469.1	439.9	412.0	390.1	370.2	351.0	339.1	325.1	318.5	313.8	308.5
57.5°	413.9	387.6	366.3	344.1	324.1	308.8	295.0	286.6	279.7	273.6	267.3
60°	378.9	353.6	334.4	313.8	293.3	280.7	270.0	260.1	252.1	242.8	240.2
62.5°	341.7	319.7	302.0	282.0	264.1	252.5	242.4	233.0	223.5	209.9	206.2
65°	290.6	273.4	254.8	238.2	222.3	211.0	196.4	185.8	181.8	180.5	179.8
67.5°	244.4	228.1	212.2	195.2	180.7	170.3	162.8	161.2	158.4	157.6	155.8
70°	213.6	198.4	182.5	166.5	152.6	150.6	148.0	145.3	142.0	140.7	139.3
72.5°	186.0	170.3	154.3	141.6	135.6	133.1	130.4	127.8	125.5	124.2	123.4
75°	142.7	128.1	117.4	112.8	109.5	107.5	103.5	101.5	100.2	98.2	97.5
77.5°	102.7	94.5	89.6	86.7	83.2	81.1	78.8	76.8	75.4	75.0	73.9
80°	78.3	74.3	71.0	67.0	65.7	63.0	62.4	60.4	61.0	59.1	59.1
82.5°	60.8	55.7	52.9	51.1	49.8	47.6	47.0	46.0	46.2	44.7	44.7
85°	31.2	29.9	28.5	27.2	27.2	25.2	25.9	25.2	25.2	23.9	23.2
87.5°	12.4	12.3	11.6	12.0	12.4	12.2	12.5	12.2	12.4	12.6	12.3
90°	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6	24.8	26.0	26.8
92.5°	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9	26.5	27.1	27.6
95°	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8	45.0	46.2	46.7
97.5°	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4	58.3	59.3	59.9
100°	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4	66.3	68.2	69.3
102.5°	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2	69.7	72.1	73.7
105°	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0	72.6	75.2	77.0
107.5°	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5	82.8	80.2	79.4
110°	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8	115.2	91.5	80.2



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9	210.7	124.5	81.8
115°	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1	327.8	218.4	155.2
117.5°	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6	647.1	620.7	579.5
120°	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9	787.7	790.6	776.0
122.5°	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8	834.5	836.2	833.9
125°	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6	903.2	904.9	906.1
127.5°	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2	967.6	970.0	971.3
130°	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5	1008.1	1010.7	1011.9
132.5°	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7	1047.0	1049.2	1050.2
135°	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7	1103.1	1105.4	1106.4
137.5°	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7	1155.0	1157.3	1158.1
140°	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4	1188.5	1190.6	1191.1
142.5°	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4	1219.4	1221.3	1221.7
145°	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9	1262.5	1264.2	1264.4
147.5°	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7	1300.0	1301.2	1301.3
150°	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1	1323.5	1324.9	1325.0
152.5°	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3	1344.8	1346.2	1346.1
155°	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0	1373.5	1374.9	1374.6
157.5°	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2	1397.8	1399.4	1399.3
160°	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3	1411.7	1413.1	1413.0
162.5°	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4	1425.0	1426.7	1426.4
165°	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8
167.5°	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9	1454.5	1456.2	1455.9
170°	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7	1461.3	1463.0	1462.7
172.5°	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8	1466.4	1468.1	1467.9
175°	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3	1472.0	1473.6	1473.3
177.5°	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9	1472.2	1473.6	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1833.7	1834.7	1833.1	1834.2	1833.1	1834.7	1833.7	1839.5	1840.6	1841.6	1840.6
5°	1708.5	1700.6	1699.2	1697.3	1699.2	1700.6	1708.5	1711.9	1714.5	1719.8	1729.1
7.5°	1559.1	1557.9	1554.6	1550.0	1554.6	1557.9	1559.1	1570.5	1579.5	1589.9	1608.9
10°	1463.0	1459.7	1459.1	1454.4	1459.1	1459.7	1463.0	1477.6	1488.2	1502.8	1528.7
12.5°	1350.5	1329.1	1326.9	1315.3	1326.9	1329.1	1350.5	1369.3	1398.0	1412.1	1439.5
15°	1149.9	1145.9	1132.6	1124.0	1132.6	1145.9	1149.9	1165.8	1176.4	1214.9	1259.3
17.5°	1035.2	1022.2	1018.1	1016.2	1018.1	1022.2	1035.2	1042.9	1058.0	1078.3	1105.1
20°	961.4	949.5	947.5	946.2	947.5	949.5	961.4	970.7	982.7	1004.6	1032.4
22.5°	910.5	898.0	892.8	888.8	892.8	898.0	910.5	917.6	928.5	945.6	964.5
25°	823.4	818.8	816.1	814.8	816.1	818.8	823.4	830.0	840.7	863.9	883.8
27.5°	755.3	745.1	743.1	739.7	743.1	745.1	755.3	767.1	778.2	788.6	806.4
30°	716.6	713.3	708.6	704.6	708.6	713.3	716.6	722.6	729.9	747.8	765.0
32.5°	670.9	668.2	664.0	662.2	664.0	668.2	670.9	679.0	694.3	705.3	717.8
35°	620.4	611.1	607.1	601.1	607.1	611.1	620.4	627.0	633.0	642.3	664.8
37.5°	566.9	562.0	556.4	558.4	556.4	562.0	566.9	569.7	582.3	595.2	605.0
40°	525.5	522.2	520.9	520.2	520.9	522.2	525.5	534.1	549.4	555.4	570.0
42.5°	492.6	483.4	480.0	479.8	480.0	483.4	492.6	502.3	511.7	521.4	536.5
45°	442.6	433.9	428.0	428.6	428.0	433.9	442.6	445.9	453.8	473.1	481.7
47.5°	391.3	391.1	387.4	388.6	387.4	391.1	391.3	397.0	407.3	419.1	432.9
50°	366.9	362.9	360.3	360.9	360.3	362.9	366.9	371.6	377.5	383.5	404.7
52.5°	343.6	340.1	338.0	340.8	338.0	340.1	343.6	346.1	350.5	356.4	370.8
55°	305.2	301.2	300.6	299.9	300.6	301.2	305.2	308.5	313.8	318.5	325.1
57.5°	262.4	259.7	255.7	254.0	255.7	259.7	262.4	267.3	273.6	279.7	286.6
60°	231.6	226.3	219.6	219.0	219.6	226.3	231.6	240.2	242.8	252.1	260.1
62.5°	203.4	202.4	201.0	200.9	201.0	202.4	203.4	206.2	209.9	223.5	233.0
65°	178.5	177.8	178.5	179.1	178.5	177.8	178.5	179.8	180.5	181.8	185.8
67.5°	155.5	154.3	153.1	153.7	153.1	154.3	155.5	155.8	157.6	158.4	161.2
70°	138.0	137.3	136.7	136.7	136.7	137.3	138.0	139.3	140.7	142.0	145.3
72.5°	121.0	120.9	120.2	119.7	120.2	120.9	121.0	123.4	124.2	125.5	127.8
75°	96.9	95.5	95.5	95.5	95.5	95.5	96.9	97.5	98.2	100.2	101.5
77.5°	73.8	73.1	72.5	71.9	72.5	73.1	73.8	73.9	75.0	75.4	76.8
80°	58.4	57.7	57.1	57.1	57.1	57.7	58.4	59.1	59.1	61.0	60.4
82.5°	44.6	43.9	43.8	43.3	43.8	43.9	44.6	44.7	44.7	46.2	46.0
85°	23.9	24.5	23.9	25.2	23.9	24.5	23.9	23.2	23.9	25.2	25.2
87.5°	12.4	11.9	12.5	12.1	12.5	11.9	12.4	12.3	12.6	12.4	12.2
90°	27.3	27.8	28.2	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6
92.5°	27.9	28.1	28.4	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9
95°	46.4	46.2	45.9	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8
97.5°	60.2	60.5	60.7	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4
100°	69.8	70.3	70.8	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4
102.5°	74.3	75.0	75.7	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2
105°	78.0	78.9	79.8	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0
107.5°	80.3	81.2	82.2	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5
110°	81.1	82.1	83.0	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	82.6	83.3	84.1	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9
115°	138.2	121.2	104.2	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1
117.5°	523.6	467.7	411.8	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6
120°	744.1	712.2	680.3	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9
122.5°	827.8	821.6	815.4	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8
125°	906.8	907.5	908.2	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6
127.5°	971.4	971.6	971.7	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2
130°	1011.7	1011.4	1011.2	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5
132.5°	1049.9	1049.7	1049.5	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7
135°	1105.9	1105.4	1105.0	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7
137.5°	1157.3	1156.5	1155.7	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7
140°	1189.9	1188.7	1187.5	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4
142.5°	1220.5	1219.3	1218.2	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4
145°	1263.3	1262.1	1260.9	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9
147.5°	1300.3	1299.3	1298.3	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7
150°	1323.8	1322.7	1321.5	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1
152.5°	1344.5	1343.0	1341.4	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3
155°	1372.7	1370.9	1369.0	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0
157.5°	1397.5	1395.6	1393.8	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2
160°	1411.4	1409.7	1408.1	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3
162.5°	1424.4	1422.4	1420.3	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4
165°	1441.1	1439.5	1437.8	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5
167.5°	1453.8	1451.7	1449.6	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9
170°	1460.6	1458.5	1456.4	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7
172.5°	1465.7	1463.6	1461.5	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8
175°	1470.9	1468.5	1466.2	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3
177.5°	1471.7	1470.0	1468.3	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1836.3	1843.8	1854.9	1861.3	1871.9	1878.8	1882.5	1889.4	1893.1	1906.4	1920.2
5°	1733.7	1744.4	1762.9	1780.2	1798.8	1818.0	1831.9	1847.9	1862.5	1887.7	1914.2
7.5°	1616.2	1630.9	1659.7	1687.2	1719.5	1746.8	1770.8	1798.0	1822.3	1858.4	1896.0
10°	1528.1	1553.9	1591.8	1617.6	1660.1	1687.3	1725.1	1755.0	1788.8	1836.6	1879.1
12.5°	1452.2	1483.3	1513.7	1549.7	1587.9	1633.2	1674.7	1713.0	1753.3	1802.6	1852.5
15°	1314.4	1359.5	1406.6	1443.1	1494.9	1542.7	1591.1	1642.8	1691.9	1751.0	1816.0
17.5°	1137.1	1189.4	1268.6	1331.1	1391.9	1439.8	1499.8	1562.4	1620.3	1691.5	1763.9
20°	1057.0	1095.5	1149.2	1233.5	1325.0	1376.1	1437.2	1506.2	1572.5	1650.1	1727.8
22.5°	992.7	1027.0	1070.1	1135.8	1238.0	1307.6	1371.3	1441.4	1518.4	1597.6	1683.7
25°	901.0	924.9	970.0	1023.1	1093.5	1208.2	1277.9	1348.2	1431.9	1516.8	1615.0
27.5°	832.2	853.7	883.0	933.7	986.0	1068.4	1179.2	1255.9	1339.2	1434.8	1536.7
30°	779.6	804.8	837.3	873.2	930.2	994.6	1105.4	1194.3	1276.6	1374.8	1483.6
32.5°	741.4	761.3	789.0	825.4	872.9	934.6	1023.1	1131.1	1211.3	1314.8	1428.4
35°	678.8	702.0	724.6	759.1	797.5	853.9	920.9	1036.4	1116.0	1218.2	1332.3
37.5°	627.1	641.3	666.3	693.6	734.2	776.3	834.4	937.9	1024.1	1124.4	1241.2
40°	587.9	605.8	624.4	654.9	688.1	728.5	785.6	862.6	961.4	1059.6	1173.7
42.5°	549.7	572.3	592.0	612.4	648.8	689.3	735.7	801.0	902.0	994.9	1105.8
45°	503.6	518.2	538.8	561.3	591.2	625.7	666.8	723.9	820.8	901.0	1005.2
47.5°	450.0	471.4	484.8	506.8	535.2	568.1	606.3	655.7	734.1	809.3	906.0
50°	413.4	435.3	454.5	474.4	499.6	531.5	563.3	611.1	674.1	753.1	843.3
52.5°	382.0	401.3	420.0	439.9	464.6	493.8	524.0	566.0	620.0	692.6	780.2
55°	339.1	351.0	370.2	390.1	412.0	439.9	469.1	504.3	550.7	611.8	682.8
57.5°	295.0	308.8	324.1	344.1	366.3	387.6	413.9	445.7	482.4	537.6	598.4
60°	270.0	280.7	293.3	313.8	334.4	353.6	378.9	405.4	439.9	487.7	539.4
62.5°	242.4	252.5	264.1	282.0	302.0	319.7	341.7	369.8	399.0	442.6	487.9
65°	196.4	211.0	222.3	238.2	254.8	273.4	290.6	313.2	339.1	373.6	414.0
67.5°	162.8	170.3	180.7	195.2	212.2	228.1	244.4	262.1	284.5	311.2	343.3
70°	148.0	150.6	152.6	166.5	182.5	198.4	213.6	230.2	249.5	271.4	299.2
72.5°	130.4	133.1	135.6	141.6	154.3	170.3	186.0	198.4	216.6	234.7	257.3
75°	103.5	107.5	109.5	112.8	117.4	128.1	142.7	154.6	165.2	179.1	197.1
77.5°	78.8	81.1	83.2	86.7	89.6	94.5	102.7	113.5	123.4	131.5	143.8
80°	62.4	63.0	65.7	67.0	71.0	74.3	78.3	86.9	96.9	100.2	108.8
82.5°	47.0	47.6	49.8	51.1	52.9	55.7	60.8	63.0	70.9	75.2	80.7
85°	25.9	25.2	27.2	27.2	28.5	29.9	31.2	34.5	36.5	41.8	43.1
87.5°	12.5	12.2	12.4	12.0	11.6	12.3	12.4	12.4	12.9	14.0	15.6
90°	22.4	21.3	19.4	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1
92.5°	25.3	24.7	23.7	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5
95°	42.6	41.5	39.8	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1
97.5°	56.4	55.5	51.7	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1
100°	62.5	60.6	56.6	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2
102.5°	64.8	62.3	95.9	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3
105°	67.4	64.8	129.3	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2
107.5°	88.1	90.8	168.1	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1
110°	162.4	186.0	254.3	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	383.1	469.2	486.1	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4
115°	546.5	655.9	650.0	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3
117.5°	700.0	726.5	722.4	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0
120°	782.0	779.2	775.0	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1
122.5°	831.1	829.4	824.8	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8
125°	899.9	898.3	893.8	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3
127.5°	962.8	960.4	957.0	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0
130°	1002.9	1000.3	997.7	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6
132.5°	1042.5	1040.3	1037.7	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1
135°	1098.4	1096.0	1093.9	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4
137.5°	1150.4	1148.1	1145.7	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3
140°	1184.2	1182.1	1179.5	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9
142.5°	1215.5	1213.6	1210.6	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5
145°	1259.2	1257.6	1253.6	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6
147.5°	1297.5	1296.3	1292.3	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5
150°	1320.7	1319.2	1315.5	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7
152.5°	1341.9	1340.5	1336.9	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6
155°	1370.6	1369.2	1366.4	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0
157.5°	1394.6	1393.0	1391.0	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2
160°	1408.9	1407.5	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5
162.5°	1421.8	1420.2	1419.0	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1
165°	1437.8	1436.2	1435.5	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4
167.5°	1451.2	1449.6	1448.9	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0
170°	1458.0	1456.4	1455.9	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6
172.5°	1463.1	1461.5	1461.0	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7
175°	1468.7	1467.0	1466.5	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3
177.5°	1469.6	1468.3	1468.1	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1920.7	1922.3	1932.9	1937.7	1947.3	1951.0	1955.2	1954.2	1954.2	1956.3	1971.2
5°	1924.8	1938.1	1958.0	1977.3	1995.8	2011.8	2022.4	2033.0	2037.0	2056.2	2073.5
7.5°	1917.9	1942.4	1975.3	2004.6	2039.8	2067.2	2090.1	2110.6	2124.7	2152.7	2181.4
10°	1908.9	1943.4	1980.6	2018.4	2066.8	2103.3	2140.5	2169.0	2178.3	2220.1	2244.0
12.5°	1890.9	1937.0	1984.3	2033.3	2080.6	2130.9	2171.8	2200.3	2233.0	2270.5	2314.6
15°	1863.8	1916.9	1978.6	2041.6	2109.3	2170.3	2214.1	2263.9	2299.7	2340.9	2379.3
17.5°	1824.9	1893.3	1971.7	2044.7	2123.0	2188.5	2248.8	2296.5	2321.7	2345.2	2350.9
20°	1794.1	1867.8	1960.0	2046.3	2124.6	2200.2	2259.9	2299.7	2306.4	2307.0	2271.9
22.5°	1760.7	1843.9	1940.4	2028.7	2122.4	2206.6	2253.0	2270.0	2243.7	2198.7	2130.7
25°	1699.2	1795.5	1907.6	2008.4	2110.6	2190.2	2206.2	2176.3	2084.1	1987.2	1864.5
27.5°	1632.6	1740.8	1861.0	1973.1	2082.0	2131.3	2097.0	1989.3	1823.2	1678.8	1503.8
30°	1583.8	1705.2	1823.3	1948.7	2049.6	2070.8	1991.9	1833.3	1639.5	1421.9	1247.4
32.5°	1528.1	1655.3	1785.1	1914.8	1999.2	1978.4	1848.0	1652.8	1425.6	1211.7	1046.8
35°	1448.4	1579.8	1719.8	1849.9	1903.6	1814.0	1619.0	1364.8	1132.6	932.9	819.4
37.5°	1356.5	1499.5	1645.1	1764.5	1760.7	1611.4	1345.7	1083.4	888.2	770.1	689.3
40°	1291.2	1435.8	1593.1	1693.9	1650.8	1456.4	1168.4	920.9	778.3	684.1	625.0
42.5°	1228.6	1373.7	1529.9	1610.1	1535.1	1296.1	1009.2	815.3	697.6	624.1	576.2
45°	1122.0	1275.3	1419.9	1464.4	1330.3	1066.9	816.1	675.5	597.2	542.7	509.6
47.5°	1017.8	1168.6	1300.6	1301.4	1120.1	865.2	688.5	584.6	517.7	475.6	451.5
50°	954.1	1097.4	1208.2	1191.0	985.3	769.7	615.7	526.2	470.4	437.9	412.7
52.5°	882.5	1021.5	1117.5	1068.4	871.2	677.3	550.4	475.2	429.0	400.8	378.2
55°	778.3	901.7	969.4	895.1	710.6	563.3	465.1	406.1	371.6	347.7	328.4
57.5°	676.0	777.8	820.4	733.8	585.3	467.1	393.5	349.1	314.9	297.8	287.8
60°	611.8	698.7	728.5	633.0	508.9	408.7	348.3	307.2	282.0	270.7	260.8
62.5°	548.6	619.6	631.9	544.3	443.6	357.8	305.9	271.1	254.4	243.6	234.2
65°	455.2	506.3	500.3	430.0	351.0	284.0	246.2	224.9	212.3	197.1	180.5
67.5°	374.7	405.9	387.1	334.4	267.9	220.7	196.0	179.9	164.3	149.8	146.0
70°	323.8	341.7	321.8	273.4	219.6	185.1	165.2	146.0	136.7	133.4	127.4
72.5°	275.0	281.2	259.7	218.2	178.7	153.3	133.9	123.1	118.1	115.3	111.5
75°	206.4	201.7	183.1	150.6	124.1	106.8	100.9	96.9	93.6	90.9	88.9
77.5°	144.9	138.1	121.6	100.3	86.4	78.2	74.6	72.5	70.9	69.5	67.5
80°	108.8	104.2	87.6	71.7	65.7	61.7	59.7	57.1	57.1	55.7	53.7
82.5°	79.6	74.4	60.0	52.5	49.2	46.8	45.4	43.8	43.3	43.5	42.1
85°	41.8	33.8	29.9	28.5	26.5	25.2	25.9	24.5	24.5	24.5	23.9
87.5°	13.5	11.3	11.3	11.3	12.3	12.7	12.5	12.9	13.8	13.5	14.3
90°	3.7	6.3	8.9	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6
92.5°	21.2	21.0	20.8	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9
95°	61.3	53.5	45.7	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8
97.5°	115.2	93.2	71.2	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4
100°	155.8	123.4	91.1	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4
102.5°	237.4	230.6	223.7	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2
105°	330.3	337.3	344.4	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0
107.5°	418.8	424.5	430.2	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5
110°	475.9	480.9	485.8	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	529.8	534.1	538.5	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9
115°	615.3	619.3	623.3	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1
117.5°	692.5	697.0	701.5	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6
120°	747.7	751.2	754.8	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9
122.5°	795.5	799.2	803.0	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8
125°	867.3	870.4	873.5	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6
127.5°	933.4	936.8	940.2	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2
130°	975.4	979.2	983.0	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5
132.5°	1017.4	1020.6	1023.8	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7
135°	1073.2	1077.0	1080.8	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7
137.5°	1128.0	1130.6	1133.3	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7
140°	1163.8	1165.7	1167.6	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4
142.5°	1194.2	1195.9	1197.6	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4
145°	1240.3	1240.1	1239.9	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9
147.5°	1281.6	1280.7	1279.8	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7
150°	1308.0	1306.4	1304.7	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1
152.5°	1330.8	1328.9	1327.1	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3
155°	1363.9	1361.8	1359.6	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0
157.5°	1390.4	1388.6	1386.8	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2
160°	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3
162.5°	1419.7	1418.2	1416.8	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4
165°	1437.9	1436.5	1435.1	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5
167.5°	1451.6	1450.1	1448.7	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9
170°	1459.2	1457.8	1456.4	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7
172.5°	1464.3	1462.9	1461.5	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8
175°	1470.7	1469.0	1467.4	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3
177.5°	1472.1	1470.7	1469.4	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1976.5	1983.4	1986.5	1986.5	1990.3	1988.7	1987.1
5°	2090.1	2102.7	2105.3	2117.3	2125.9	2123.2	2124.6
7.5°	2203.0	2223.3	2243.3	2252.5	2253.9	2259.2	2261.2
10°	2272.5	2289.1	2320.3	2315.6	2338.9	2352.1	2330.2
12.5°	2339.4	2361.8	2383.5	2389.4	2402.6	2406.8	2398.2
15°	2399.9	2411.9	2413.2	2409.9	2413.8	2410.5	2397.9
17.5°	2343.4	2324.0	2284.7	2266.1	2251.4	2229.7	2220.9
20°	2250.0	2192.9	2126.5	2100.0	2068.8	2007.8	2022.4
22.5°	2048.3	1983.2	1916.9	1839.4	1802.4	1744.5	1741.0
25°	1734.4	1622.3	1498.9	1412.6	1362.2	1304.5	1279.2
27.5°	1348.5	1207.3	1106.2	1055.0	1008.4	962.6	960.8
30°	1094.8	988.6	910.3	866.5	838.0	818.8	822.8
32.5°	922.8	850.1	797.3	760.9	739.8	725.3	725.1
35°	754.4	704.6	670.8	655.5	640.3	629.7	630.3
37.5°	645.6	615.7	596.9	580.0	570.5	565.3	562.4
40°	589.9	565.3	550.7	540.8	532.8	525.5	524.2
42.5°	545.8	525.5	510.9	503.1	495.6	490.5	489.1
45°	484.4	467.8	454.5	445.9	442.6	437.9	437.9
47.5°	430.9	414.6	404.2	398.8	393.1	390.0	389.9
50°	394.8	382.2	372.9	369.6	364.9	362.9	362.3
52.5°	362.4	353.0	346.4	344.1	342.1	339.6	340.0
55°	318.5	313.2	310.5	308.5	305.2	301.2	303.9
57.5°	281.5	276.9	269.8	263.5	260.5	257.7	258.8
60°	255.5	246.2	236.9	229.6	227.6	221.6	221.6
62.5°	222.5	209.5	198.1	194.0	192.0	189.2	188.7
65°	171.2	165.9	163.2	160.6	159.2	159.2	157.9
67.5°	141.9	139.7	136.8	136.2	134.8	134.4	134.0
70°	125.4	122.7	121.4	120.8	119.4	120.1	118.1
72.5°	109.5	107.4	107.1	105.4	104.6	104.7	103.2
75°	86.3	86.3	85.6	84.9	83.6	82.9	83.6
77.5°	66.4	66.5	65.3	65.2	65.0	65.2	64.5
80°	53.1	53.7	53.1	52.4	51.8	52.4	51.8
82.5°	41.9	41.0	40.9	40.7	40.6	40.2	40.1
85°	23.9	24.5	23.9	23.2	23.2	23.2	23.9
87.5°	14.0	14.2	14.4	14.5	14.6	14.7	14.2
90°	24.8	26.0	26.8	27.3	27.8	28.2	28.7
92.5°	26.5	27.1	27.6	27.9	28.1	28.4	28.7
95°	45.0	46.2	46.7	46.4	46.2	45.9	45.7
97.5°	58.3	59.3	59.9	60.2	60.5	60.7	61.0
100°	66.3	68.2	69.3	69.8	70.3	70.8	71.2
102.5°	69.7	72.1	73.7	74.3	75.0	75.7	76.3
105°	72.6	75.2	77.0	78.0	78.9	79.8	80.8
107.5°	82.8	80.2	79.4	80.3	81.2	82.2	83.1
110°	115.2	91.5	80.2	81.1	82.1	83.0	84.0



TEST NUMBER: P331729

CATALOG NUMBER: SA2XXRDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	210.7	124.5	81.8	82.6	83.3	84.1	84.8
115°	327.8	218.4	155.2	138.2	121.2	104.2	87.2
117.5°	647.1	620.7	579.5	523.6	467.7	411.8	355.9
120°	787.7	790.6	776.0	744.1	712.2	680.3	648.5
122.5°	834.5	836.2	833.9	827.8	821.6	815.4	809.2
125°	903.2	904.9	906.1	906.8	907.5	908.2	908.9
127.5°	967.6	970.0	971.3	971.4	971.6	971.7	971.8
130°	1008.1	1010.7	1011.9	1011.7	1011.4	1011.2	1011.0
132.5°	1047.0	1049.2	1050.2	1049.9	1049.7	1049.5	1049.2
135°	1103.1	1105.4	1106.4	1105.9	1105.4	1105.0	1104.5
137.5°	1155.0	1157.3	1158.1	1157.3	1156.5	1155.7	1154.9
140°	1188.5	1190.6	1191.1	1189.9	1188.7	1187.5	1186.4
142.5°	1219.4	1221.3	1221.7	1220.5	1219.3	1218.2	1217.0
145°	1262.5	1264.2	1264.4	1263.3	1262.1	1260.9	1259.7
147.5°	1300.0	1301.2	1301.3	1300.3	1299.3	1298.3	1297.3
150°	1323.5	1324.9	1325.0	1323.8	1322.7	1321.5	1320.3
152.5°	1344.8	1346.2	1346.1	1344.5	1343.0	1341.4	1339.9
155°	1373.5	1374.9	1374.6	1372.7	1370.9	1369.0	1367.1
157.5°	1397.8	1399.4	1399.3	1397.5	1395.6	1393.8	1391.9
160°	1411.7	1413.1	1413.0	1411.4	1409.7	1408.1	1406.4
162.5°	1425.0	1426.7	1426.4	1424.4	1422.4	1420.3	1418.3
165°	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2
167.5°	1454.5	1456.2	1455.9	1453.8	1451.7	1449.6	1447.4
170°	1461.3	1463.0	1462.7	1460.6	1458.5	1456.4	1454.2
172.5°	1466.4	1468.1	1467.9	1465.7	1463.6	1461.5	1459.3
175°	1472.0	1473.6	1473.3	1470.9	1468.5	1466.2	1463.8
177.5°	1472.2	1473.6	1473.4	1471.7	1470.0	1468.3	1466.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1

(END OF REPORT)