

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331728

Luminaire Tested: **SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331728
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6631.8 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331728
CATALOG NUMBER: SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331728

CATALOG NUMBER: SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				46
1	97	93	89	86	89	86	82	80	71	69	67	59	57	56	47	46	45				39	
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	42	40	38				34	
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33				29	
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29				25	
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	25				22	
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23				20	
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	25	23	20				18	
8	54	42	35	30	50	40	33	28	34	29	25	28	24	22	23	21	18				16	
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17				14	
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23675	23675	23675
5°	23765	23378	23506
10°	23582	22996	22799
15°	23311	22313	21670
20°	22936	21340	20270
25°	22552	20236	18912
30°	22018	19099	17169
35°	21498	17864	15640
40°	20976	16585	13873
45°	20361	15150	12271
50°	19733	13700	10698
55°	19088	12141	9188
60°	18338	10498	7627
65°	17490	8821	6946
70°	16475	7265	6387
75°	15234	6625	5958
80°	13445	5923	5430
85°	10578	4668	4668



TEST NUMBER: P331728

CATALOG NUMBER: SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	2.1
10°-20°	376.8	5.7
20°-30°	529.2	8.0
30°-40°	577.1	8.7
40°-50°	530.6	8.0
50°-60°	416.7	6.3
60°-70°	271.7	4.1
70°-80°	140.1	2.1
80°-90°	41.0	0.6
90°-100°	207.5	3.1
100°-110°	704.2	10.6
110°-120°	748.1	11.3
120°-130°	615.8	9.3
130°-140°	494.5	7.5
140°-150°	373.7	5.6
150°-160°	262.6	4.0
160°-170°	154.6	2.3
170°-180°	50.3	0.8
0°-30°	1043.3	15.7
0°-40°	1620.3	24.4
0°-60°	2567.6	38.7
0°-90°	3020.4	45.5
90°-120°	1659.8	25.0
90°-150°	3143.8	47.4
90°-180°	3611.0	54.4
0°-180°	6631.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1459	1442	1453	1450	139
15°	1395	1378	1335	1310	1296	393
25°	1266	1221	1136	1083	1062	582
35°	1091	1020	906	826	794	682
45°	892	800	664	573	537	688
55°	678	572	431	355	326	606
65°	458	350	231	188	182	454
75°	244	154	106	97	96	258
85°	57	31	25	25	25	67
90°	1	14	34	32	33	4
95°	35	86	391	148	114	37
105°	122	184	740	1322	1125	129
115°	215	271	619	1277	1480	213
125°	299	354	595	1034	1201	266
135°	351	419	588	869	995	271
145°	401	461	585	726	794	252
155°	456	492	568	642	668	210
165°	497	512	544	577	586	140
175°	518	518	523	530	528	49
180°	519	519	519	519	519	



TEST NUMBER: P331728

CATALOG NUMBER: SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1471.6	1470.4	1469.2	1468.0	1466.9	1465.0	1462.4	1459.8	1457.2	1454.6	1457.0
5°	1466.3	1464.8	1463.3	1461.8	1460.4	1457.7	1453.9	1450.1	1446.2	1442.4	1445.0
7.5°	1451.1	1449.3	1447.5	1445.7	1443.8	1440.7	1436.2	1431.7	1427.2	1422.7	1423.5
10°	1438.4	1436.3	1434.3	1432.2	1430.1	1426.2	1420.3	1414.4	1408.5	1402.6	1401.7
12.5°	1422.5	1419.9	1417.4	1414.9	1412.3	1407.3	1399.7	1392.2	1384.6	1377.1	1375.5
15°	1394.6	1391.4	1388.1	1384.9	1381.6	1375.0	1365.0	1355.0	1344.9	1334.9	1329.3
17.5°	1360.4	1355.4	1350.5	1345.5	1340.6	1331.7	1318.8	1305.9	1293.1	1280.2	1273.6
20°	1334.9	1329.0	1323.1	1317.2	1311.3	1301.0	1286.2	1271.5	1256.8	1242.0	1234.6
22.5°	1307.3	1300.7	1294.1	1287.5	1280.9	1269.3	1252.6	1236.0	1219.4	1202.7	1193.2
25°	1265.9	1256.5	1247.0	1237.6	1228.2	1213.7	1194.2	1174.8	1155.3	1135.9	1123.8
27.5°	1216.0	1205.7	1195.5	1185.2	1175.0	1158.9	1136.9	1115.0	1093.0	1071.1	1057.0
30°	1181.0	1169.8	1158.6	1147.4	1136.2	1118.8	1095.2	1071.6	1048.0	1024.4	1009.4
32.5°	1147.0	1133.9	1120.8	1107.7	1094.6	1076.1	1052.0	1027.9	1003.9	979.8	962.7
35°	1090.7	1075.7	1060.7	1045.6	1030.6	1010.1	984.1	958.2	932.3	906.3	887.7
37.5°	1034.5	1018.0	1001.5	984.9	968.4	946.3	918.7	891.0	863.4	835.7	815.2
40°	995.2	977.5	959.8	942.1	924.4	901.3	872.7	844.1	815.5	786.9	765.9
42.5°	954.9	936.2	917.6	899.0	880.3	856.2	826.7	797.1	767.6	738.0	716.4
45°	891.7	871.9	852.2	832.4	812.7	787.3	756.4	725.4	694.4	663.5	642.5
47.5°	830.1	809.2	788.3	767.3	746.4	719.9	688.0	656.0	624.0	592.1	571.3
50°	785.6	764.6	743.7	722.7	701.8	675.1	642.7	610.2	577.8	545.4	525.0
52.5°	742.0	720.1	698.3	676.4	654.5	627.7	596.0	564.2	532.5	500.8	481.1
55°	678.1	655.1	632.1	609.1	586.1	558.6	526.8	494.9	463.1	431.3	413.6
57.5°	612.5	588.9	565.3	541.7	518.2	491.1	460.4	429.8	399.2	368.6	352.4
60°	567.9	544.3	520.8	497.2	473.6	446.6	416.2	385.8	355.5	325.1	310.1
62.5°	524.4	500.8	477.2	453.6	430.0	403.8	374.8	345.9	316.9	287.9	273.6
65°	457.8	433.9	410.0	386.1	362.3	337.0	310.5	284.0	257.4	230.9	220.9
67.5°	393.6	369.9	346.2	322.4	298.7	274.9	251.1	227.2	203.3	179.4	174.8
70°	349.0	326.0	303.0	280.0	257.0	235.3	215.0	194.6	174.3	153.9	151.0
72.5°	306.5	284.5	262.4	240.4	218.3	199.1	182.8	166.4	150.1	133.8	131.3
75°	244.2	223.5	202.9	182.2	161.6	146.3	136.2	126.2	116.2	106.2	104.1
77.5°	182.9	164.7	146.6	128.5	110.4	99.0	94.1	89.3	84.5	79.6	78.4
80°	144.6	129.6	114.6	99.5	84.5	75.5	72.5	69.6	66.6	63.7	62.5
82.5°	109.6	97.9	86.1	74.4	62.7	55.8	53.8	51.8	49.8	47.8	47.1
85°	57.1	50.9	44.7	38.5	32.3	28.8	27.9	27.0	26.1	25.2	25.2
87.5°	17.2	15.9	14.8	13.3	11.8	11.5	12.5	13.9	15.1	15.3	14.8
90°	1.0	4.0	8.0	10.0	12.0	15.0	20.0	26.9	32.9	33.9	32.9
92.5°	12.2	17.6	24.8	29.1	35.9	45.3	67.9	99.6	127.9	129.7	109.6
95°	34.9	38.9	48.9	57.9	73.9	97.8	143.7	230.5	346.3	391.2	342.3
97.5°	56.9	62.3	72.9	86.4	104.8	131.9	189.6	310.6	503.0	667.9	700.6
100°	76.8	79.8	88.8	104.8	124.8	152.7	205.6	327.4	542.9	788.4	932.2
102.5°	95.2	97.4	106.4	122.4	143.1	171.1	220.0	328.2	527.8	792.4	1018.4
105°	121.8	125.8	132.7	147.7	169.7	197.6	244.5	333.3	498.0	739.5	1005.0
107.5°	150.5	153.7	160.5	174.3	196.0	224.2	269.7	347.1	483.2	682.9	917.4
110°	169.7	173.7	179.6	192.6	213.6	242.5	286.4	358.3	480.1	655.7	862.3



TEST NUMBER: P331728

CATALOG NUMBER: SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.2	191.2	198.0	210.2	230.3	260.1	302.4	370.3	480.8	638.1	824.0
115°	214.6	219.6	225.6	237.5	257.5	284.4	327.4	388.2	485.0	618.8	776.5
117.5°	242.9	246.9	252.9	263.5	282.6	310.6	350.3	407.4	492.2	609.4	746.5
120°	260.5	264.5	270.5	279.4	299.4	327.4	366.3	420.2	497.0	603.8	730.6
122.5°	277.3	280.4	286.4	296.2	316.2	344.9	381.4	431.3	502.6	600.6	717.0
125°	299.4	302.4	308.4	320.4	340.3	368.3	404.2	449.1	511.0	594.8	697.6
127.5°	317.0	321.0	329.3	342.5	361.7	390.4	425.4	465.7	519.6	591.4	679.7
130°	327.4	331.3	341.3	355.3	375.3	403.2	438.1	476.1	526.0	589.8	667.7
132.5°	336.9	341.7	352.5	367.3	388.0	416.0	449.3	486.4	532.3	589.0	658.1
135°	351.3	355.3	367.3	382.2	405.2	433.1	465.1	500.0	539.9	587.8	644.7
137.5°	364.9	369.7	381.6	397.6	420.4	446.3	477.9	510.4	546.7	587.6	635.3
140°	375.3	379.3	391.2	407.2	429.2	455.1	485.0	516.0	549.9	586.8	629.8
142.5°	385.6	388.8	400.0	416.0	437.1	461.5	490.6	520.8	552.3	586.8	624.2
145°	401.2	405.2	415.2	430.2	450.1	472.1	499.0	527.0	554.9	584.8	616.8
147.5°	418.0	421.0	430.5	444.3	460.9	480.5	505.8	530.4	555.7	581.3	609.2
150°	429.2	432.1	440.1	453.1	468.1	486.0	509.0	531.9	554.9	578.9	602.8
152.5°	440.3	441.7	449.7	461.1	475.3	491.6	512.2	532.7	553.3	574.9	597.2
155°	456.1	457.1	463.1	474.1	485.0	500.0	517.0	533.9	550.9	567.9	586.8
157.5°	469.3	470.3	475.1	484.6	493.4	506.0	520.4	533.9	546.3	560.7	577.1
160°	478.1	479.1	483.0	491.0	499.0	510.0	522.0	533.9	543.9	555.9	569.9
162.5°	486.8	486.2	490.2	496.6	503.8	512.4	522.8	533.1	541.5	551.9	563.5
165°	497.0	496.0	498.0	504.0	509.0	515.0	524.0	531.0	536.9	543.9	552.9
167.5°	505.4	504.2	506.0	509.8	513.4	517.2	523.8	529.6	532.3	536.9	542.5
170°	511.0	509.0	510.0	513.0	515.0	518.0	523.0	528.0	530.0	532.9	536.9
172.5°	514.2	513.0	512.4	515.4	516.6	518.8	522.2	525.6	526.8	528.2	531.4
175°	518.0	517.0	516.0	518.0	518.0	519.0	521.0	523.0	522.0	523.0	524.0
177.5°	519.8	518.2	517.4	519.0	519.0	519.0	519.8	521.4	519.8	519.0	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331728

CATALOG NUMBER: SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1459.3	1461.7	1464.0	1465.0	1464.5	1464.0	1463.6	1463.1
5°	1447.7	1450.3	1453.0	1453.9	1453.0	1452.1	1451.2	1450.3
7.5°	1424.3	1425.0	1425.8	1425.4	1423.9	1422.4	1420.8	1419.3
10°	1400.8	1399.9	1399.0	1397.7	1395.9	1394.2	1392.4	1390.6
12.5°	1373.9	1372.3	1370.7	1368.5	1365.5	1362.6	1359.6	1356.7
15°	1323.7	1318.1	1312.5	1308.2	1305.3	1302.3	1299.4	1296.4
17.5°	1266.9	1260.2	1253.6	1247.7	1242.6	1237.6	1232.5	1227.4
20°	1227.3	1219.9	1212.5	1205.6	1199.1	1192.6	1186.1	1179.7
22.5°	1183.8	1174.3	1164.8	1157.6	1152.8	1147.9	1143.1	1138.3
25°	1111.7	1099.6	1087.5	1079.2	1074.8	1070.4	1066.0	1061.6
27.5°	1042.9	1028.8	1014.7	1004.2	997.2	990.1	983.1	976.1
30°	994.3	979.3	964.2	952.7	944.8	936.8	928.9	920.9
32.5°	945.5	928.3	911.2	898.8	891.4	883.9	876.4	868.9
35°	869.1	850.6	832.0	819.5	813.0	806.5	800.0	793.5
37.5°	794.8	774.3	753.9	739.9	732.5	725.0	717.6	710.2
40°	745.0	724.1	703.1	688.8	681.2	673.5	665.8	658.2
42.5°	694.8	673.1	651.5	636.9	629.5	622.1	614.6	607.2
45°	621.6	600.7	579.7	565.7	558.6	551.6	544.5	537.4
47.5°	550.4	529.6	508.8	495.2	488.8	482.3	475.9	469.5
50°	504.7	484.3	464.0	450.7	444.5	438.3	432.1	425.9
52.5°	461.5	441.9	422.2	409.6	403.8	398.1	392.4	386.7
55°	395.9	378.2	360.5	348.8	343.2	337.6	332.0	326.4
57.5°	336.2	320.0	303.8	293.3	288.6	283.8	279.1	274.4
60°	295.0	280.0	264.9	255.1	250.3	245.6	240.9	236.2
62.5°	259.3	245.0	230.6	222.0	219.2	216.4	213.5	210.7
65°	210.8	200.8	190.8	185.3	184.4	183.6	182.7	181.8
67.5°	170.2	165.6	161.0	158.2	157.3	156.3	155.4	154.5
70°	148.0	145.1	142.1	140.1	138.9	137.7	136.5	135.3
72.5°	128.8	126.3	123.8	122.3	121.5	120.8	120.1	119.4
75°	102.0	100.0	97.9	96.7	96.4	96.1	95.8	95.5
77.5°	77.3	76.1	74.9	74.1	73.6	73.1	72.7	72.2
80°	61.3	60.2	59.0	58.4	58.4	58.4	58.4	58.4
82.5°	46.4	45.6	44.9	44.6	44.6	44.6	44.6	44.6
85°	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2
87.5°	14.4	13.8	13.9	14.0	14.0	14.0	14.0	14.0
90°	31.9	29.9	31.9	32.9	32.9	32.9	32.9	32.9
92.5°	87.0	74.7	66.3	60.1	59.3	56.1	56.9	55.3
95°	261.5	200.6	158.7	136.7	123.8	115.8	112.8	113.8
97.5°	610.2	499.2	391.2	319.2	271.5	246.9	232.3	224.0
100°	911.2	787.4	650.7	530.0	447.1	404.2	375.3	357.3
102.5°	1108.4	1080.5	980.5	852.5	762.5	689.2	653.1	628.8
105°	1212.6	1325.4	1338.4	1305.4	1243.5	1181.7	1138.7	1124.8
107.5°	1137.6	1307.4	1411.2	1459.5	1467.3	1463.9	1455.3	1436.8
110°	1072.9	1251.5	1379.3	1461.1	1504.0	1523.0	1532.0	1531.0



TEST NUMBER: P331728

CATALOG NUMBER: SA2XXRDIP-C865D925U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1013.8	1185.3	1321.8	1415.6	1475.3	1507.0	1524.0	1529.4
115°	941.1	1094.8	1225.6	1328.4	1399.2	1445.1	1471.1	1480.1
117.5°	886.4	1021.4	1139.9	1236.4	1308.6	1357.1	1384.5	1392.0
120°	859.3	983.1	1088.8	1179.7	1249.5	1296.4	1325.4	1335.4
122.5°	837.7	951.1	1051.3	1133.4	1196.0	1242.1	1267.9	1276.3
125°	806.4	909.2	997.0	1071.9	1129.8	1167.7	1192.6	1200.6
127.5°	775.5	868.5	951.3	1020.4	1070.9	1106.4	1128.0	1134.4
130°	755.5	841.3	920.2	986.1	1035.0	1068.9	1088.8	1096.8
132.5°	736.3	815.8	888.2	950.1	998.2	1032.2	1050.5	1057.7
135°	709.6	775.5	841.3	897.2	940.1	973.1	991.0	995.0
137.5°	688.2	743.3	795.6	844.3	883.5	911.8	927.6	933.6
140°	674.7	722.6	768.5	812.4	844.3	870.3	885.3	891.2
142.5°	663.5	704.2	743.7	780.5	810.8	834.4	847.7	848.9
145°	647.7	680.7	711.6	740.5	764.5	781.5	791.4	794.4
147.5°	635.5	661.5	685.6	706.8	726.6	740.1	746.9	748.7
150°	626.8	648.7	669.7	687.6	702.6	714.6	720.6	721.6
152.5°	618.0	638.3	656.1	671.7	683.4	693.8	698.2	698.4
155°	605.8	621.8	636.7	647.7	658.7	665.7	669.7	667.7
157.5°	591.6	605.0	617.6	626.2	633.9	639.7	641.5	641.5
160°	582.8	593.8	604.8	611.8	618.8	623.8	624.8	624.8
162.5°	574.1	583.4	592.8	598.2	605.2	608.6	609.6	608.8
165°	560.9	567.9	574.9	578.9	582.8	586.8	586.8	585.8
167.5°	548.3	553.7	558.5	562.1	563.9	566.1	565.9	564.7
170°	541.9	544.9	548.9	550.9	551.9	554.9	553.9	551.9
172.5°	534.7	536.9	540.1	541.3	542.3	543.7	542.7	541.5
175°	527.0	528.0	529.0	530.0	530.0	531.0	530.0	528.0
177.5°	521.4	521.4	522.2	522.2	522.2	522.2	521.4	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0

(END OF REPORT)