

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331619-940

Luminaire Tested: **SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331619-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1966.0 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331619-940
CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331619-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47	47	47	47	47	47	47	47	47	47	47	47																
	1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40	40	40	40	40	40	40	40	40	40	40	40																
	2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35	35	35	35	35	35	35	35	35	35	35	35																
	3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30	30	30	30	30	30																
	4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26	26	26	26	26	26	26	26	26	26	26	26																
	5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23	23	23	23	23	23	23	23	23	23	23	23																
	6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	25	23	20	20	20	20	20	20	20	20	20	20	20	20																
	7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18	18	18	18	18	18	18	18	18	18	18	18	18															
	8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16	16	16	16	16	16	16	16	16	16	16	16	16															
	9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15	15	15	15	15	15	15	15	15	15	15	15	15															
	10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14	14	14	14	14	14	14	14	14	14	14	14	14															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331619-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	2.1
10°-20°	115.0	5.9
20°-30°	161.6	8.2
30°-40°	176.2	9.0
40°-50°	162.0	8.2
50°-60°	127.2	6.5
60°-70°	82.9	4.2
70°-80°	42.8	2.2
80°-90°	12.6	0.6
90°-100°	23.7	1.2
100°-110°	73.5	3.7
110°-120°	125.6	6.4
120°-130°	165.1	8.4
130°-140°	185.4	9.4
140°-150°	181.8	9.2
150°-160°	152.4	7.8
160°-170°	101.1	5.1
170°-180°	35.3	1.8
0°-30°	318.5	16.2
0°-40°	494.7	25.2
0°-60°	783.8	39.9
0°-90°	922.1	46.9
90°-120°	222.7	11.3
90°-150°	755.0	38.4
90°-180°	1044.0	53.1
0°-180°	1966.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	0	4	11	10	11	2
95°	16	19	20	20	20	19
105°	68	69	69	70	70	72
115°	126	128	127	127	126	125
125°	183	186	185	184	184	164
135°	237	241	241	241	240	183
145°	288	290	292	292	291	180
155°	329	330	331	333	332	151
165°	358	358	358	360	359	101
175°	373	372	371	373	371	35
180°	373	373	373	373	373	



TEST NUMBER: P331619-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.3	4.8	4.5	4.0	3.7	3.6	3.8	4.2	4.5	4.8	4.7
90°	0.4	1.2	2.0	2.9	3.7	4.9	6.4	7.9	9.5	11.1	10.9
92.5°	5.6	6.2	6.9	7.5	8.1	8.6	8.9	9.3	9.6	10.0	10.1
95°	16.4	17.1	17.7	18.5	19.2	19.6	19.7	19.9	20.1	20.2	20.2
97.5°	30.0	30.6	31.1	31.7	32.4	32.8	33.1	33.3	33.6	33.9	33.9
100°	40.0	40.6	41.1	41.7	42.3	42.6	42.8	43.1	43.2	43.5	43.5
102.5°	50.6	51.0	51.5	51.9	52.3	52.8	53.0	53.2	53.5	53.8	53.9
105°	67.8	67.9	68.1	68.4	68.6	68.8	68.9	69.0	69.2	69.3	69.5
107.5°	85.0	85.3	85.6	86.0	86.2	86.4	86.4	86.4	86.4	86.4	86.4
110°	96.1	96.5	96.9	97.4	97.7	98.0	98.0	98.0	98.0	98.0	98.0



TEST NUMBER: P331619-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.2	108.6	109.1	109.4	109.9	110.0	109.9	109.9	109.9	109.9	109.7
115°	126.0	126.4	126.9	127.2	127.7	127.9	127.7	127.5	127.4	127.2	127.2
117.5°	143.7	144.4	144.9	145.4	146.1	146.2	145.7	145.3	144.9	144.5	144.4
120°	155.6	156.2	156.8	157.3	157.8	157.8	157.3	156.8	156.2	155.6	155.6
122.5°	166.5	167.1	167.8	168.4	169.2	169.3	168.9	168.5	168.1	167.7	167.6
125°	183.3	184.0	184.6	185.2	185.8	186.1	185.8	185.7	185.5	185.2	185.0
127.5°	199.8	200.6	201.4	202.2	203.0	203.2	203.0	202.8	202.5	202.2	202.0
130°	210.2	211.1	212.0	212.9	213.7	214.2	214.0	213.9	213.7	213.6	213.5
132.5°	221.8	222.5	223.2	223.9	224.7	225.1	225.1	225.2	225.2	225.2	224.9
135°	237.2	238.0	238.8	239.5	240.3	240.8	240.9	241.0	241.2	241.3	241.2
137.5°	253.5	254.1	254.8	255.5	256.1	256.5	256.6	256.8	257.0	257.2	257.2
140°	263.4	264.0	264.7	265.3	265.9	266.4	266.7	267.1	267.4	267.8	267.8
142.5°	273.5	274.1	274.7	275.4	276.0	276.4	276.6	276.9	277.1	277.3	277.4
145°	287.9	288.5	288.9	289.4	289.9	290.3	290.8	291.2	291.6	292.0	292.1
147.5°	300.9	301.5	302.0	302.6	303.2	303.6	303.9	304.3	304.5	304.8	305.0
150°	309.7	310.1	310.5	310.9	311.4	311.7	312.0	312.3	312.5	312.8	313.1
152.5°	317.5	317.9	318.3	318.8	319.1	319.6	319.9	320.2	320.6	320.9	321.2
155°	329.2	329.4	329.7	329.8	330.0	330.3	330.5	330.6	330.9	331.1	331.4
157.5°	339.2	339.4	339.5	339.7	339.8	339.9	340.1	340.2	340.3	340.5	340.9
160°	345.3	345.4	345.5	345.7	345.8	346.0	346.0	346.1	346.2	346.3	346.6
162.5°	350.8	350.9	350.9	350.9	351.0	351.0	351.1	351.2	351.2	351.2	351.8
165°	358.2	358.1	358.0	358.0	357.9	357.8	357.8	357.8	357.8	357.8	358.4
167.5°	364.4	364.2	364.0	363.7	363.6	363.5	363.4	363.4	363.4	363.4	363.8
170°	367.7	367.5	367.2	367.0	366.8	366.7	366.6	366.5	366.5	366.4	366.8
172.5°	369.9	369.7	369.5	369.3	369.1	368.9	368.9	368.8	368.7	368.6	369.2
175°	372.7	372.5	372.3	372.0	371.8	371.7	371.6	371.4	371.2	371.1	371.6
177.5°	373.8	373.6	373.4	373.4	373.2	373.0	372.9	372.8	372.6	372.6	372.9
180°	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4



TEST NUMBER: P331619-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	4.6	4.5	4.4	4.4	4.4	4.4	4.4	4.4
90°	10.8	10.6	10.4	10.4	10.5	10.6	10.6	10.7
92.5°	10.1	10.1	10.2	10.2	10.2	10.2	10.2	10.2
95°	20.2	20.2	20.2	20.1	20.0	19.8	19.7	19.5
97.5°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.8
100°	43.5	43.5	43.5	43.4	43.3	43.3	43.2	43.2
102.5°	53.9	53.9	54.0	54.0	53.9	53.9	53.9	53.8
105°	69.6	69.7	69.9	69.9	69.9	69.9	69.9	69.9
107.5°	86.5	86.6	86.6	86.5	86.1	85.9	85.5	85.2
110°	98.0	98.0	98.0	97.9	97.6	97.5	97.3	97.0



TEST NUMBER: P331619-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	109.5	109.3	109.1	109.0	108.9	108.7	108.5	108.3
115°	127.2	127.1	127.0	126.9	126.6	126.4	126.3	126.0
117.5°	144.2	144.0	143.8	143.7	143.5	143.3	143.0	142.9
120°	155.6	155.6	155.6	155.5	155.3	155.1	154.9	154.7
122.5°	167.4	167.2	167.0	166.9	166.7	166.6	166.4	166.3
125°	184.9	184.6	184.4	184.2	184.2	184.1	184.0	184.0
127.5°	201.8	201.5	201.3	201.0	200.8	200.5	200.4	200.1
130°	213.3	213.2	213.0	212.9	212.6	212.2	212.0	211.7
132.5°	224.5	224.3	224.0	223.7	223.5	223.3	223.0	222.8
135°	241.2	241.1	241.0	240.9	240.7	240.5	240.3	240.0
137.5°	257.1	257.0	257.0	256.8	256.5	256.3	256.0	255.7
140°	267.8	267.8	267.8	267.6	267.3	267.1	266.8	266.5
142.5°	277.5	277.5	277.6	277.5	277.2	276.9	276.6	276.3
145°	292.2	292.2	292.3	292.2	291.9	291.7	291.4	291.1
147.5°	305.1	305.2	305.4	305.3	305.1	304.8	304.5	304.3
150°	313.3	313.4	313.7	313.7	313.4	313.3	313.1	312.8
152.5°	321.5	321.7	322.0	322.0	321.7	321.5	321.2	320.9
155°	331.8	332.2	332.5	332.6	332.3	332.2	332.0	331.7
157.5°	341.3	341.9	342.3	342.4	342.1	341.7	341.4	341.1
160°	347.1	347.5	347.9	347.9	347.7	347.4	347.1	346.9
162.5°	352.2	352.7	353.2	353.2	352.9	352.6	352.2	351.9
165°	358.8	359.4	359.8	359.9	359.5	359.2	358.8	358.6
167.5°	364.4	364.8	365.3	365.4	365.1	364.6	364.3	363.9
170°	367.4	367.8	368.4	368.4	368.0	367.6	367.1	366.7
172.5°	369.6	370.1	370.6	370.7	370.2	369.8	369.4	369.0
175°	372.1	372.6	373.1	373.1	372.7	372.3	371.8	371.4
177.5°	373.3	373.5	373.9	373.9	373.5	373.3	372.9	372.6
180°	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4

(END OF REPORT)