

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331458-935

Luminaire Tested: **SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331458-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7411.7 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	36	33
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.5	2.2
10°-20°	475.3	6.4
20°-30°	689.9	9.3
30°-40°	728.0	9.8
40°-50°	644.6	8.7
50°-60°	514.4	6.9
60°-70°	349.6	4.7
70°-80°	179.3	2.4
80°-90°	47.9	0.6
90°-100°	208.0	2.8
100°-110°	705.7	9.5
110°-120°	749.7	10.1
120°-130°	617.2	8.3
130°-140°	495.6	6.7
140°-150°	374.5	5.1
150°-160°	263.2	3.6
160°-170°	154.9	2.1
170°-180°	50.4	0.7
0°-30°	1328.7	17.9
0°-40°	2056.7	27.7
0°-60°	3215.7	43.4
0°-90°	3792.4	51.2
90°-120°	1663.4	22.4
90°-150°	3150.7	42.5
90°-180°	3619.0	48.8
0°-180°	7411.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	40
90°	33	1	33	1	33	19
95°	114	35	114	35	114	148
105°	1127	122	1127	122	1127	1091
115°	1483	215	1483	215	1483	1453
125°	1203	300	1203	300	1203	1087
135°	997	352	997	352	997	775
145°	796	402	796	402	796	506
155°	669	457	669	457	669	312
165°	587	498	587	498	587	168
175°	529	519	529	519	529	51
180°	520	520	520	520	520	



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	20.3	20.3	20.8	20.3	20.3	20.7	20.2	20.1	20.8	21.6	21.9
90°	33.0	33.0	33.0	33.0	33.0	32.0	30.0	32.0	33.0	34.0	33.0
92.5°	55.4	57.0	56.2	59.4	60.2	66.4	74.8	87.2	109.9	130.0	128.2
95°	114.0	113.0	116.1	124.0	137.0	159.0	201.0	262.1	343.1	392.1	347.1
97.5°	224.5	232.8	247.5	272.1	319.9	392.1	500.3	611.5	702.1	669.3	504.1
100°	358.1	376.1	405.1	448.1	531.1	652.1	789.2	913.2	934.2	790.1	544.1
102.5°	630.2	654.5	690.8	764.1	854.4	982.6	1082.8	1110.9	1020.6	794.2	528.9
105°	1127.2	1141.3	1184.2	1246.2	1308.3	1341.3	1328.3	1215.2	1007.2	741.1	499.1
107.5°	1439.9	1458.4	1467.1	1470.5	1462.7	1414.3	1310.3	1140.1	919.4	684.3	484.3
110°	1534.3	1535.3	1526.3	1507.3	1464.3	1382.2	1254.2	1075.2	864.2	657.1	481.1



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1532.7	1527.3	1510.3	1478.5	1418.7	1324.6	1187.8	1016.0	825.8	639.6	481.9
115°	1483.3	1474.3	1448.3	1402.3	1331.3	1228.2	1097.3	943.2	778.2	620.1	486.1
117.5°	1395.1	1387.5	1360.0	1311.5	1239.1	1142.5	1023.6	888.4	748.1	610.7	493.3
120°	1338.3	1328.3	1299.2	1252.2	1182.2	1091.2	985.2	861.2	732.1	605.1	498.1
122.5°	1279.0	1270.7	1244.8	1198.6	1135.8	1053.6	953.2	839.6	718.5	601.9	503.7
125°	1203.2	1195.2	1170.3	1132.2	1074.2	999.2	911.2	808.1	699.1	596.2	512.1
127.5°	1136.9	1130.4	1108.8	1073.2	1022.6	953.4	870.4	777.1	681.1	592.7	520.7
130°	1099.2	1091.2	1071.3	1037.2	988.2	922.2	843.2	757.2	669.2	591.1	527.1
132.5°	1060.0	1052.8	1034.4	1000.4	952.2	890.2	817.6	738.0	659.5	590.3	533.5
135°	997.2	993.2	975.2	942.2	899.1	843.2	777.1	711.1	646.1	589.1	541.1
137.5°	935.6	929.6	913.8	885.4	846.2	797.4	744.9	689.7	636.7	588.9	547.9
140°	893.2	887.2	872.2	846.2	814.2	770.2	724.2	676.1	631.1	588.1	551.1
142.5°	850.8	849.5	836.2	812.5	782.1	745.4	705.8	665.0	625.5	588.1	553.5
145°	796.2	793.2	783.2	766.1	742.2	713.2	682.2	649.1	618.1	586.1	556.1
147.5°	750.4	748.6	741.8	728.1	708.3	687.2	663.0	637.0	610.5	582.6	556.9
150°	723.2	722.1	716.2	704.1	689.1	671.1	650.1	628.1	604.1	580.1	556.1
152.5°	699.9	699.7	695.3	684.9	673.1	657.5	639.7	619.3	598.5	576.1	554.5
155°	669.2	671.1	667.1	660.1	649.1	638.1	623.1	607.1	588.1	569.1	552.1
157.5°	642.9	642.9	641.1	635.3	627.5	618.9	606.3	592.9	578.3	561.9	547.5
160°	626.1	626.1	625.1	620.1	613.1	606.1	595.1	584.1	571.1	557.2	545.1
162.5°	610.1	610.9	609.9	606.5	599.5	594.1	584.7	575.3	564.7	553.1	542.7
165°	587.1	588.1	588.1	584.1	580.1	576.1	569.1	562.1	554.1	545.1	538.1
167.5°	565.9	567.1	567.3	565.1	563.4	559.7	554.9	549.5	543.7	538.1	533.5
170°	553.1	555.1	556.1	553.1	552.1	550.1	546.1	543.1	538.1	534.1	531.1
172.5°	542.7	543.9	544.9	543.5	542.5	541.3	538.1	535.9	532.5	529.3	527.9
175°	529.1	531.1	532.1	531.1	531.1	530.1	529.1	528.1	525.1	524.1	523.1
177.5°	520.9	522.5	523.3	523.3	523.3	523.3	522.5	522.5	520.9	520.1	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	21.3	19.8	18.9	19.3	17.3	16.9	14.0	11.8	11.9	12.1	11.5
90°	27.0	20.0	15.0	12.0	10.0	8.0	4.0	1.0	4.0	8.0	10.0
92.5°	99.8	68.0	45.4	36.0	29.2	24.8	17.6	12.2	17.6	24.8	29.2
95°	231.0	144.0	98.0	74.0	58.0	49.0	39.0	35.0	39.0	49.0	58.0
97.5°	311.3	190.0	132.2	105.0	86.6	73.0	62.4	57.0	62.4	73.0	86.6
100°	328.0	206.0	153.0	125.0	105.0	89.0	80.0	77.0	80.0	89.0	105.0
102.5°	328.9	220.4	171.4	143.4	122.6	106.6	97.6	95.4	97.6	106.6	122.6
105°	334.1	245.0	198.0	170.0	148.0	133.0	126.1	122.0	126.1	133.0	148.0
107.5°	347.8	270.3	224.6	196.5	174.6	160.8	154.0	150.8	154.0	160.8	174.6
110°	359.0	287.1	243.1	214.0	193.0	180.0	174.0	170.0	174.0	180.0	193.0



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	371.1	303.1	260.6	230.8	210.6	198.5	191.7	187.6	191.7	198.5	210.6
115°	389.1	328.0	285.1	258.0	238.1	226.0	220.1	215.1	220.1	226.0	238.1
117.5°	408.3	351.0	311.3	283.3	264.1	253.5	247.5	243.5	247.5	253.5	264.1
120°	421.1	367.0	328.0	300.1	280.1	271.0	265.0	261.1	265.0	271.0	280.1
122.5°	432.3	382.3	345.7	316.8	296.9	287.1	281.0	277.8	281.0	287.1	296.9
125°	450.1	405.1	369.1	341.0	321.1	309.1	303.1	300.1	303.1	309.1	321.1
127.5°	466.7	426.3	391.2	362.5	343.3	330.1	321.7	317.6	321.7	330.1	343.3
130°	477.1	439.1	404.1	376.1	356.1	342.1	332.1	328.0	332.1	342.1	356.1
132.5°	487.5	450.3	416.9	388.9	368.1	353.3	342.5	337.7	342.5	353.3	368.1
135°	501.1	466.1	434.1	406.0	383.1	368.1	356.1	352.1	356.1	368.1	383.1
137.5°	511.5	478.9	447.3	421.3	398.5	382.5	370.5	365.7	370.5	382.5	398.5
140°	517.1	486.1	456.1	430.1	408.1	392.1	380.0	376.1	380.0	392.1	408.1
142.5°	521.9	491.7	462.5	438.1	416.9	400.9	389.7	386.5	389.7	400.9	416.9
145°	528.1	500.1	473.1	451.1	431.1	416.1	406.0	402.1	406.0	416.1	431.1
147.5°	531.5	506.9	481.5	461.9	445.3	431.4	421.9	418.9	421.9	431.4	445.3
150°	533.1	510.1	487.1	469.1	454.1	441.1	433.1	430.1	433.1	441.1	454.1
152.5°	533.9	513.3	492.7	476.3	462.1	450.6	442.7	441.3	442.7	450.6	462.1
155°	535.1	518.1	501.1	486.1	475.1	464.1	458.1	457.1	458.1	464.1	475.1
157.5°	535.1	521.5	507.1	494.5	485.7	476.1	471.3	470.3	471.3	476.1	485.7
160°	535.1	523.1	511.1	500.1	492.1	484.1	480.1	479.1	480.1	484.1	492.1
162.5°	534.3	523.9	513.5	504.9	497.7	491.3	487.3	487.9	487.3	491.3	497.7
165°	532.1	525.1	516.1	510.1	505.1	499.1	497.1	498.1	497.1	499.1	505.1
167.5°	530.7	524.9	518.3	514.5	510.9	507.1	505.3	506.5	505.3	507.1	510.9
170°	529.1	524.1	519.1	516.1	514.1	511.1	510.1	512.1	510.1	511.1	514.1
172.5°	526.7	523.3	519.9	517.7	516.5	513.5	514.1	515.3	514.1	513.5	516.5
175°	524.1	522.1	520.1	519.1	519.1	517.1	518.1	519.1	518.1	517.1	519.1
177.5°	522.5	520.9	520.1	520.1	520.1	518.5	519.3	520.9	519.3	518.5	520.1
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	11.4	11.5	11.9	13.3	14.0	13.7	12.9	12.7	12.3	11.7	11.9
90°	12.0	15.0	20.0	27.0	33.0	34.0	33.0	32.0	30.0	32.0	33.0
92.5°	36.0	45.4	68.0	99.8	128.2	130.0	109.9	87.2	74.8	66.4	60.2
95°	74.0	98.0	144.0	231.0	347.1	392.1	343.1	262.1	201.0	159.0	137.0
97.5°	105.0	132.2	190.0	311.3	504.1	669.3	702.1	611.5	500.3	392.1	319.9
100°	125.0	153.0	206.0	328.0	544.1	790.1	934.2	913.2	789.2	652.1	531.1
102.5°	143.4	171.4	220.4	328.9	528.9	794.2	1020.6	1110.9	1082.8	982.6	854.4
105°	170.0	198.0	245.0	334.1	499.1	741.1	1007.2	1215.2	1328.3	1341.3	1308.3
107.5°	196.5	224.6	270.3	347.8	484.3	684.3	919.4	1140.1	1310.3	1414.3	1462.7
110°	214.0	243.1	287.1	359.0	481.1	657.1	864.2	1075.2	1254.2	1382.2	1464.3



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.8	260.6	303.1	371.1	481.9	639.6	825.8	1016.0	1187.8	1324.6	1418.7
115°	258.0	285.1	328.0	389.1	486.1	620.1	778.2	943.2	1097.3	1228.2	1331.3
117.5°	283.3	311.3	351.0	408.3	493.3	610.7	748.1	888.4	1023.6	1142.5	1239.1
120°	300.1	328.0	367.0	421.1	498.1	605.1	732.1	861.2	985.2	1091.2	1182.2
122.5°	316.8	345.7	382.3	432.3	503.7	601.9	718.5	839.6	953.2	1053.6	1135.8
125°	341.0	369.1	405.1	450.1	512.1	596.2	699.1	808.1	911.2	999.2	1074.2
127.5°	362.5	391.2	426.3	466.7	520.7	592.7	681.1	777.1	870.4	953.4	1022.6
130°	376.1	404.1	439.1	477.1	527.1	591.1	669.2	757.2	843.2	922.2	988.2
132.5°	388.9	416.9	450.3	487.5	533.5	590.3	659.5	738.0	817.6	890.2	952.2
135°	406.0	434.1	466.1	501.1	541.1	589.1	646.1	711.1	777.1	843.2	899.1
137.5°	421.3	447.3	478.9	511.5	547.9	588.9	636.7	689.7	744.9	797.4	846.2
140°	430.1	456.1	486.1	517.1	551.1	588.1	631.1	676.1	724.2	770.2	814.2
142.5°	438.1	462.5	491.7	521.9	553.5	588.1	625.5	665.0	705.8	745.4	782.1
145°	451.1	473.1	500.1	528.1	556.1	586.1	618.1	649.1	682.2	713.2	742.2
147.5°	461.9	481.5	506.9	531.5	556.9	582.6	610.5	637.0	663.0	687.2	708.3
150°	469.1	487.1	510.1	533.1	556.1	580.1	604.1	628.1	650.1	671.1	689.1
152.5°	476.3	492.7	513.3	533.9	554.5	576.1	598.5	619.3	639.7	657.5	673.1
155°	486.1	501.1	518.1	535.1	552.1	569.1	588.1	607.1	623.1	638.1	649.1
157.5°	494.5	507.1	521.5	535.1	547.5	561.9	578.3	592.9	606.3	618.9	627.5
160°	500.1	511.1	523.1	535.1	545.1	557.2	571.1	584.1	595.1	606.1	613.1
162.5°	504.9	513.5	523.9	534.3	542.7	553.1	564.7	575.3	584.7	594.1	599.5
165°	510.1	516.1	525.1	532.1	538.1	545.1	554.1	562.1	569.1	576.1	580.1
167.5°	514.5	518.3	524.9	530.7	533.5	538.1	543.7	549.5	554.9	559.7	563.4
170°	516.1	519.1	524.1	529.1	531.1	534.1	538.1	543.1	546.1	550.1	552.1
172.5°	517.7	519.9	523.3	526.7	527.9	529.3	532.5	535.9	538.1	541.3	542.5
175°	519.1	520.1	522.1	524.1	523.1	524.1	525.1	528.1	529.1	530.1	531.1
177.5°	520.1	520.1	520.9	522.5	520.9	520.1	520.9	522.5	522.5	523.3	523.3
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	11.9	11.4	11.4	10.8	11.4	11.4	11.9	11.9	11.7	12.3	12.7
90°	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0	32.0	30.0	32.0
92.5°	59.4	56.2	57.0	55.4	57.0	56.2	59.4	60.2	66.4	74.8	87.2
95°	124.0	116.1	113.0	114.0	113.0	116.1	124.0	137.0	159.0	201.0	262.1
97.5°	272.1	247.5	232.8	224.5	232.8	247.5	272.1	319.9	392.1	500.3	611.5
100°	448.1	405.1	376.1	358.1	376.1	405.1	448.1	531.1	652.1	789.2	913.2
102.5°	764.1	690.8	654.5	630.2	654.5	690.8	764.1	854.4	982.6	1082.8	1110.9
105°	1246.2	1184.2	1141.3	1127.2	1141.3	1184.2	1246.2	1308.3	1341.3	1328.3	1215.2
107.5°	1470.5	1467.1	1458.4	1439.9	1458.4	1467.1	1470.5	1462.7	1414.3	1310.3	1140.1
110°	1507.3	1526.3	1535.3	1534.3	1535.3	1526.3	1507.3	1464.3	1382.2	1254.2	1075.2



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1478.5	1510.3	1527.3	1532.7	1527.3	1510.3	1478.5	1418.7	1324.6	1187.8	1016.0
115°	1402.3	1448.3	1474.3	1483.3	1474.3	1448.3	1402.3	1331.3	1228.2	1097.3	943.2
117.5°	1311.5	1360.0	1387.5	1395.1	1387.5	1360.0	1311.5	1239.1	1142.5	1023.6	888.4
120°	1252.2	1299.2	1328.3	1338.3	1328.3	1299.2	1252.2	1182.2	1091.2	985.2	861.2
122.5°	1198.6	1244.8	1270.7	1279.0	1270.7	1244.8	1198.6	1135.8	1053.6	953.2	839.6
125°	1132.2	1170.3	1195.2	1203.2	1195.2	1170.3	1132.2	1074.2	999.2	911.2	808.1
127.5°	1073.2	1108.8	1130.4	1136.9	1130.4	1108.8	1073.2	1022.6	953.4	870.4	777.1
130°	1037.2	1071.3	1091.2	1099.2	1091.2	1071.3	1037.2	988.2	922.2	843.2	757.2
132.5°	1000.4	1034.4	1052.8	1060.0	1052.8	1034.4	1000.4	952.2	890.2	817.6	738.0
135°	942.2	975.2	993.2	997.2	993.2	975.2	942.2	899.1	843.2	777.1	711.1
137.5°	885.4	913.8	929.6	935.6	929.6	913.8	885.4	846.2	797.4	744.9	689.7
140°	846.2	872.2	887.2	893.2	887.2	872.2	846.2	814.2	770.2	724.2	676.1
142.5°	812.5	836.2	849.5	850.8	849.5	836.2	812.5	782.1	745.4	705.8	665.0
145°	766.1	783.2	793.2	796.2	793.2	783.2	766.1	742.2	713.2	682.2	649.1
147.5°	728.1	741.8	748.6	750.4	748.6	741.8	728.1	708.3	687.2	663.0	637.0
150°	704.1	716.2	722.1	723.2	722.1	716.2	704.1	689.1	671.1	650.1	628.1
152.5°	684.9	695.3	699.7	699.9	699.7	695.3	684.9	673.1	657.5	639.7	619.3
155°	660.1	667.1	671.1	669.2	671.1	667.1	660.1	649.1	638.1	623.1	607.1
157.5°	635.3	641.1	642.9	642.9	642.9	641.1	635.3	627.5	618.9	606.3	592.9
160°	620.1	625.1	626.1	626.1	626.1	625.1	620.1	613.1	606.1	595.1	584.1
162.5°	606.5	609.9	610.9	610.1	610.9	609.9	606.5	599.5	594.1	584.7	575.3
165°	584.1	588.1	588.1	587.1	588.1	588.1	584.1	580.1	576.1	569.1	562.1
167.5°	565.1	567.3	567.1	565.9	567.1	567.3	565.1	563.4	559.7	554.9	549.5
170°	553.1	556.1	555.1	553.1	555.1	556.1	553.1	552.1	550.1	546.1	543.1
172.5°	543.5	544.9	543.9	542.7	543.9	544.9	543.5	542.5	541.3	538.1	535.9
175°	531.1	532.1	531.1	529.1	531.1	532.1	531.1	531.1	530.1	529.1	528.1
177.5°	523.3	523.3	522.5	520.9	522.5	523.3	523.3	523.3	523.3	522.5	522.5
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	12.9	13.7	14.0	13.3	11.9	11.5	11.4	11.5	12.1	11.9	11.8
90°	33.0	34.0	33.0	27.0	20.0	15.0	12.0	10.0	8.0	4.0	1.0
92.5°	109.9	130.0	128.2	99.8	68.0	45.4	36.0	29.2	24.8	17.6	12.2
95°	343.1	392.1	347.1	231.0	144.0	98.0	74.0	58.0	49.0	39.0	35.0
97.5°	702.1	669.3	504.1	311.3	190.0	132.2	105.0	86.6	73.0	62.4	57.0
100°	934.2	790.1	544.1	328.0	206.0	153.0	125.0	105.0	89.0	80.0	77.0
102.5°	1020.6	794.2	528.9	328.9	220.4	171.4	143.4	122.6	106.6	97.6	95.4
105°	1007.2	741.1	499.1	334.1	245.0	198.0	170.0	148.0	133.0	126.1	122.0
107.5°	919.4	684.3	484.3	347.8	270.3	224.6	196.5	174.6	160.8	154.0	150.8
110°	864.2	657.1	481.1	359.0	287.1	243.1	214.0	193.0	180.0	174.0	170.0



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	825.8	639.6	481.9	371.1	303.1	260.6	230.8	210.6	198.5	191.7	187.6
115°	778.2	620.1	486.1	389.1	328.0	285.1	258.0	238.1	226.0	220.1	215.1
117.5°	748.1	610.7	493.3	408.3	351.0	311.3	283.3	264.1	253.5	247.5	243.5
120°	732.1	605.1	498.1	421.1	367.0	328.0	300.1	280.1	271.0	265.0	261.1
122.5°	718.5	601.9	503.7	432.3	382.3	345.7	316.8	296.9	287.1	281.0	277.8
125°	699.1	596.2	512.1	450.1	405.1	369.1	341.0	321.1	309.1	303.1	300.1
127.5°	681.1	592.7	520.7	466.7	426.3	391.2	362.5	343.3	330.1	321.7	317.6
130°	669.2	591.1	527.1	477.1	439.1	404.1	376.1	356.1	342.1	332.1	328.0
132.5°	659.5	590.3	533.5	487.5	450.3	416.9	388.9	368.1	353.3	342.5	337.7
135°	646.1	589.1	541.1	501.1	466.1	434.1	406.0	383.1	368.1	356.1	352.1
137.5°	636.7	588.9	547.9	511.5	478.9	447.3	421.3	398.5	382.5	370.5	365.7
140°	631.1	588.1	551.1	517.1	486.1	456.1	430.1	408.1	392.1	380.0	376.1
142.5°	625.5	588.1	553.5	521.9	491.7	462.5	438.1	416.9	400.9	389.7	386.5
145°	618.1	586.1	556.1	528.1	500.1	473.1	451.1	431.1	416.1	406.0	402.1
147.5°	610.5	582.6	556.9	531.5	506.9	481.5	461.9	445.3	431.4	421.9	418.9
150°	604.1	580.1	556.1	533.1	510.1	487.1	469.1	454.1	441.1	433.1	430.1
152.5°	598.5	576.1	554.5	533.9	513.3	492.7	476.3	462.1	450.6	442.7	441.3
155°	588.1	569.1	552.1	535.1	518.1	501.1	486.1	475.1	464.1	458.1	457.1
157.5°	578.3	561.9	547.5	535.1	521.5	507.1	494.5	485.7	476.1	471.3	470.3
160°	571.1	557.2	545.1	535.1	523.1	511.1	500.1	492.1	484.1	480.1	479.1
162.5°	564.7	553.1	542.7	534.3	523.9	513.5	504.9	497.7	491.3	487.3	487.9
165°	554.1	545.1	538.1	532.1	525.1	516.1	510.1	505.1	499.1	497.1	498.1
167.5°	543.7	538.1	533.5	530.7	524.9	518.3	514.5	510.9	507.1	505.3	506.5
170°	538.1	534.1	531.1	529.1	524.1	519.1	516.1	514.1	511.1	510.1	512.1
172.5°	532.5	529.3	527.9	526.7	523.3	519.9	517.7	516.5	513.5	514.1	515.3
175°	525.1	524.1	523.1	524.1	522.1	520.1	519.1	519.1	517.1	518.1	519.1
177.5°	520.9	520.1	520.9	522.5	520.9	520.1	520.1	520.1	518.5	519.3	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	14.0	16.9	17.3	19.3	18.9	19.8	21.3	21.9	21.6	20.8	20.1
90°	4.0	8.0	10.0	12.0	15.0	20.0	27.0	33.0	34.0	33.0	32.0
92.5°	17.6	24.8	29.2	36.0	45.4	68.0	99.8	128.2	130.0	109.9	87.2
95°	39.0	49.0	58.0	74.0	98.0	144.0	231.0	347.1	392.1	343.1	262.1
97.5°	62.4	73.0	86.6	105.0	132.2	190.0	311.3	504.1	669.3	702.1	611.5
100°	80.0	89.0	105.0	125.0	153.0	206.0	328.0	544.1	790.1	934.2	913.2
102.5°	97.6	106.6	122.6	143.4	171.4	220.4	328.9	528.9	794.2	1020.6	1110.9
105°	126.1	133.0	148.0	170.0	198.0	245.0	334.1	499.1	741.1	1007.2	1215.2
107.5°	154.0	160.8	174.6	196.5	224.6	270.3	347.8	484.3	684.3	919.4	1140.1
110°	174.0	180.0	193.0	214.0	243.1	287.1	359.0	481.1	657.1	864.2	1075.2



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	191.7	198.5	210.6	230.8	260.6	303.1	371.1	481.9	639.6	825.8	1016.0
115°	220.1	226.0	238.1	258.0	285.1	328.0	389.1	486.1	620.1	778.2	943.2
117.5°	247.5	253.5	264.1	283.3	311.3	351.0	408.3	493.3	610.7	748.1	888.4
120°	265.0	271.0	280.1	300.1	328.0	367.0	421.1	498.1	605.1	732.1	861.2
122.5°	281.0	287.1	296.9	316.8	345.7	382.3	432.3	503.7	601.9	718.5	839.6
125°	303.1	309.1	321.1	341.0	369.1	405.1	450.1	512.1	596.2	699.1	808.1
127.5°	321.7	330.1	343.3	362.5	391.2	426.3	466.7	520.7	592.7	681.1	777.1
130°	332.1	342.1	356.1	376.1	404.1	439.1	477.1	527.1	591.1	669.2	757.2
132.5°	342.5	353.3	368.1	388.9	416.9	450.3	487.5	533.5	590.3	659.5	738.0
135°	356.1	368.1	383.1	406.0	434.1	466.1	501.1	541.1	589.1	646.1	711.1
137.5°	370.5	382.5	398.5	421.3	447.3	478.9	511.5	547.9	588.9	636.7	689.7
140°	380.0	392.1	408.1	430.1	456.1	486.1	517.1	551.1	588.1	631.1	676.1
142.5°	389.7	400.9	416.9	438.1	462.5	491.7	521.9	553.5	588.1	625.5	665.0
145°	406.0	416.1	431.1	451.1	473.1	500.1	528.1	556.1	586.1	618.1	649.1
147.5°	421.9	431.4	445.3	461.9	481.5	506.9	531.5	556.9	582.6	610.5	637.0
150°	433.1	441.1	454.1	469.1	487.1	510.1	533.1	556.1	580.1	604.1	628.1
152.5°	442.7	450.6	462.1	476.3	492.7	513.3	533.9	554.5	576.1	598.5	619.3
155°	458.1	464.1	475.1	486.1	501.1	518.1	535.1	552.1	569.1	588.1	607.1
157.5°	471.3	476.1	485.7	494.5	507.1	521.5	535.1	547.5	561.9	578.3	592.9
160°	480.1	484.1	492.1	500.1	511.1	523.1	535.1	545.1	557.2	571.1	584.1
162.5°	487.3	491.3	497.7	504.9	513.5	523.9	534.3	542.7	553.1	564.7	575.3
165°	497.1	499.1	505.1	510.1	516.1	525.1	532.1	538.1	545.1	554.1	562.1
167.5°	505.3	507.1	510.9	514.5	518.3	524.9	530.7	533.5	538.1	543.7	549.5
170°	510.1	511.1	514.1	516.1	519.1	524.1	529.1	531.1	534.1	538.1	543.1
172.5°	514.1	513.5	516.5	517.7	519.9	523.3	526.7	527.9	529.3	532.5	535.9
175°	518.1	517.1	519.1	519.1	520.1	522.1	524.1	523.1	524.1	525.1	528.1
177.5°	519.3	518.5	520.1	520.1	520.1	520.9	522.5	520.9	520.1	520.9	522.5
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	20.2	20.7	20.3	20.3	20.8	20.3	20.3
90°	30.0	32.0	33.0	33.0	33.0	33.0	33.0
92.5°	74.8	66.4	60.2	59.4	56.2	57.0	55.4
95°	201.0	159.0	137.0	124.0	116.1	113.0	114.0
97.5°	500.3	392.1	319.9	272.1	247.5	232.8	224.5
100°	789.2	652.1	531.1	448.1	405.1	376.1	358.1
102.5°	1082.8	982.6	854.4	764.1	690.8	654.5	630.2
105°	1328.3	1341.3	1308.3	1246.2	1184.2	1141.3	1127.2
107.5°	1310.3	1414.3	1462.7	1470.5	1467.1	1458.4	1439.9
110°	1254.2	1382.2	1464.3	1507.3	1526.3	1535.3	1534.3



TEST NUMBER: P331458-935

CATALOG NUMBER: SA2XXDIP-C1005D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1187.8	1324.6	1418.7	1478.5	1510.3	1527.3	1532.7
115°	1097.3	1228.2	1331.3	1402.3	1448.3	1474.3	1483.3
117.5°	1023.6	1142.5	1239.1	1311.5	1360.0	1387.5	1395.1
120°	985.2	1091.2	1182.2	1252.2	1299.2	1328.3	1338.3
122.5°	953.2	1053.6	1135.8	1198.6	1244.8	1270.7	1279.0
125°	911.2	999.2	1074.2	1132.2	1170.3	1195.2	1203.2
127.5°	870.4	953.4	1022.6	1073.2	1108.8	1130.4	1136.9
130°	843.2	922.2	988.2	1037.2	1071.3	1091.2	1099.2
132.5°	817.6	890.2	952.2	1000.4	1034.4	1052.8	1060.0
135°	777.1	843.2	899.1	942.2	975.2	993.2	997.2
137.5°	744.9	797.4	846.2	885.4	913.8	929.6	935.6
140°	724.2	770.2	814.2	846.2	872.2	887.2	893.2
142.5°	705.8	745.4	782.1	812.5	836.2	849.5	850.8
145°	682.2	713.2	742.2	766.1	783.2	793.2	796.2
147.5°	663.0	687.2	708.3	728.1	741.8	748.6	750.4
150°	650.1	671.1	689.1	704.1	716.2	722.1	723.2
152.5°	639.7	657.5	673.1	684.9	695.3	699.7	699.9
155°	623.1	638.1	649.1	660.1	667.1	671.1	669.2
157.5°	606.3	618.9	627.5	635.3	641.1	642.9	642.9
160°	595.1	606.1	613.1	620.1	625.1	626.1	626.1
162.5°	584.7	594.1	599.5	606.5	609.9	610.9	610.1
165°	569.1	576.1	580.1	584.1	588.1	588.1	587.1
167.5°	554.9	559.7	563.4	565.1	567.3	567.1	565.9
170°	546.1	550.1	552.1	553.1	556.1	555.1	553.1
172.5°	538.1	541.3	542.5	543.5	544.9	543.9	542.7
175°	529.1	530.1	531.1	531.1	532.1	531.1	529.1
177.5°	522.5	523.3	523.3	523.3	523.3	522.5	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1

(END OF REPORT)