

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331627-940

Luminaire Tested: **SA2XXRDIP-C290D725U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331627-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3593.0 lumens  
Efficiency: N/A  
Efficacy: 115.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331627-940  
CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	32	32	31	24				
2	85	78	73	68	76	70	66	62	56	52	50	42	40	38	29	28	27	21				
3	78	69	63	57	70	62	57	52	49	45	42	37	35	33	26	25	23	19				
4	72	62	54	49	64	56	49	44	44	40	36	34	31	28	24	22	21	16				
5	66	55	47	42	59	50	43	38	40	35	32	30	27	25	22	20	18	15				
6	61	49	42	36	54	45	38	33	36	31	28	28	24	22	20	18	16	13				
7	56	45	37	32	50	40	34	29	33	28	24	25	22	20	18	16	15	12				
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13	11				
9	48	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10				
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9411	9411	9411	9411
5°	10511	9470	8399	9470
10°	11663	9404	7279	9404
15°	12236	9267	5735	9267
20°	10608	9062	4962	9062
25°	6957	8783	4431	8783
30°	4683	8444	4010	8444
35°	3792	8016	3617	8016
40°	3372	7552	3347	7552
45°	3053	7005	2987	7005
50°	2778	6465	2768	6465
55°	2609	5866	2578	5866
60°	2186	5318	2160	5318
65°	1841	4829	2090	4829
70°	1699	4310	1969	4310
75°	1591	3755	1822	3755
80°	1469	3096	1618	3096
85°	1352	2445	1426	2445



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.3	1.5
10°-20°	154.0	4.3
20°-30°	198.4	5.5
30°-40°	188.6	5.2
40°-50°	161.5	4.5
50°-60°	123.0	3.4
60°-70°	77.8	2.2
70°-80°	38.8	1.1
80°-90°	12.3	0.3
90°-100°	29.4	0.8
100°-110°	107.8	3.0
110°-120°	288.3	8.0
120°-130°	475.8	13.2
130°-140°	506.0	14.1
140°-150°	470.3	13.1
150°-160°	378.1	10.5
160°-170°	243.7	6.8
170°-180°	83.9	2.3
0°-30°	407.7	11.3
0°-40°	596.2	16.6
0°-60°	880.8	24.5
0°-90°	1009.6	28.1
90°-120°	425.5	11.8
90°-150°	1877.7	52.3
90°-180°	2583.0	71.9
0°-180°	3593.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	583	583	583	583	583	
5°	648	584	518	584	648	64
15°	732	554	343	554	732	197
25°	390	493	249	493	390	185
35°	192	407	184	407	192	123
45°	134	307	131	307	134	103
55°	93	208	92	208	93	81
65°	48	126	55	126	48	49
75°	26	60	29	60	26	27
85°	7	13	8	13	7	8
90°	17	1	17	1	17	8
95°	28	42	28	42	28	26
105°	48	194	48	194	48	50
115°	52	367	52	367	52	131
125°	545	519	545	519	545	472
135°	663	642	663	642	663	511
145°	756	744	756	744	756	473
155°	820	820	820	820	820	379
165°	862	864	862	864	862	243
175°	878	883	878	883	878	84
180°	882	882	882	882	882	



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	606.6	607.1	607.6	606.5	606.5	605.5	603.3	601.7	597.2	596.6	596.6
5°	648.5	648.2	649.0	646.3	642.7	641.9	638.0	632.9	627.7	621.9	620.6
7.5°	690.3	689.6	688.0	687.6	684.8	678.7	672.5	665.9	657.2	648.6	644.4
10°	711.4	718.1	714.0	706.9	708.3	698.8	693.8	685.0	677.7	664.9	662.2
12.5°	732.1	734.8	733.4	729.4	727.6	721.0	714.2	706.6	693.1	681.7	671.7
15°	732.0	735.8	736.9	735.7	736.6	736.3	732.6	726.4	714.6	702.0	691.1
17.5°	678.0	680.6	687.3	691.8	697.5	709.4	715.4	717.6	716.0	708.7	701.1
20°	617.4	613.0	631.6	641.1	649.2	669.4	686.9	693.6	704.3	704.1	702.0
22.5°	531.5	532.5	550.2	561.5	585.1	605.5	625.3	650.4	671.2	684.9	692.9
25°	390.5	398.2	415.8	431.2	457.5	495.3	529.5	569.2	606.6	636.2	664.4
27.5°	293.3	293.9	307.8	322.1	337.7	368.5	411.7	459.1	512.5	556.6	607.3
30°	251.2	249.9	255.8	264.6	277.9	301.8	334.2	380.8	434.1	500.5	559.6
32.5°	221.3	221.4	225.9	232.3	243.3	259.5	281.7	319.6	369.9	435.2	504.5
35°	192.4	192.3	195.5	200.1	204.7	215.1	230.3	250.1	284.8	345.7	416.6
37.5°	171.7	172.5	174.2	177.1	182.2	188.0	197.1	210.4	235.1	271.2	330.7
40°	160.0	160.4	162.6	165.1	168.1	172.5	180.0	190.8	208.8	237.6	281.2
42.5°	149.4	149.7	151.3	153.6	156.0	160.4	166.7	175.9	190.6	212.9	248.9
45°	133.7	133.7	135.1	136.1	138.8	142.8	147.8	155.6	165.7	182.3	206.2
47.5°	119.0	119.0	120.0	121.7	123.4	126.5	131.5	137.9	145.2	158.0	178.4
50°	110.6	110.8	111.4	112.8	113.9	116.6	120.6	126.0	133.7	143.7	160.6
52.5°	103.8	103.7	104.4	105.0	105.8	107.7	110.7	115.5	122.3	131.0	145.1
55°	92.7	91.9	93.2	94.2	94.8	95.6	97.2	100.2	106.1	113.4	123.9
57.5°	79.0	78.6	79.5	80.4	82.4	84.5	86.0	87.8	90.9	96.1	106.6
60°	67.7	67.7	69.5	70.1	72.3	75.2	78.0	79.6	82.7	86.1	93.8
62.5°	57.6	57.8	58.6	59.2	60.5	63.9	67.9	71.5	74.4	77.7	82.8
65°	48.2	48.6	48.6	49.0	49.8	50.6	52.3	55.1	60.2	64.8	68.7
67.5°	40.9	41.0	41.2	41.6	41.7	42.6	43.3	44.6	45.7	50.1	54.9
70°	36.0	36.6	36.5	36.8	37.1	37.5	38.3	38.9	40.8	41.7	44.6
72.5°	31.5	31.9	31.9	32.2	32.7	32.8	33.4	34.1	35.2	36.0	37.6
75°	25.5	25.3	25.5	25.9	26.1	26.3	26.3	27.1	27.7	28.5	29.6
77.5°	19.7	19.9	19.9	19.9	20.0	20.3	20.2	20.6	21.2	21.7	22.1
80°	15.8	16.0	15.8	16.0	16.2	16.4	16.2	16.4	17.0	17.4	17.4
82.5°	12.2	12.3	12.4	12.4	12.5	12.5	12.8	12.8	13.3	13.2	13.4
85°	7.3	7.1	7.1	7.1	7.3	7.5	7.3	7.3	7.5	7.5	7.5
87.5°	6.1	6.2	6.1	6.1	6.0	5.9	5.7	5.8	5.4	5.4	5.1
90°	17.2	16.9	16.7	16.4	16.1	15.6	14.9	14.2	13.5	12.8	11.6
92.5°	17.2	17.0	16.9	16.7	16.6	16.2	15.9	15.5	15.2	14.8	14.3
95°	27.5	27.6	27.7	27.8	28.0	27.7	27.0	26.3	25.6	24.9	23.9
97.5°	36.6	36.5	36.3	36.1	35.9	35.6	35.0	34.4	33.9	33.3	31.0
100°	42.7	42.4	42.2	41.9	41.6	40.9	39.8	38.6	37.5	36.4	34.0
102.5°	45.8	45.4	45.0	44.6	44.2	43.2	41.8	40.3	38.9	37.4	35.5
105°	48.5	47.9	47.3	46.8	46.2	45.1	43.6	42.0	40.5	38.9	37.6
107.5°	49.8	49.3	48.8	48.2	47.6	48.2	49.7	51.3	52.9	54.5	100.9
110°	50.4	49.8	49.2	48.7	48.2	54.9	69.1	83.3	97.5	111.6	152.6



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.9	50.5	50.0	49.6	49.0	74.7	126.4	178.2	229.9	281.5	291.7
115°	52.3	62.5	72.7	82.9	93.1	131.1	196.7	262.3	328.0	393.6	390.0
117.5°	213.6	247.1	280.6	314.1	347.7	372.4	388.3	404.2	420.1	436.0	433.5
120°	389.1	408.2	427.4	446.5	465.7	474.4	472.7	471.0	469.2	467.5	465.0
122.5°	485.5	489.3	492.9	496.7	500.4	501.8	500.7	499.7	498.6	497.7	494.9
125°	545.4	544.9	544.6	544.1	543.7	543.0	542.0	541.0	540.0	539.0	536.3
127.5°	583.2	583.1	583.0	582.9	582.8	582.0	580.6	579.2	577.7	576.2	574.3
130°	606.6	606.7	606.9	607.1	607.2	606.5	604.9	603.3	601.8	600.2	598.7
132.5°	629.5	629.7	629.9	630.0	630.2	629.5	628.2	626.9	625.5	624.2	622.7
135°	662.7	663.0	663.3	663.6	663.9	663.3	661.9	660.5	659.1	657.6	656.4
137.5°	692.9	693.5	693.9	694.5	694.9	694.5	693.0	691.7	690.3	688.9	687.4
140°	711.9	712.6	713.3	714.0	714.7	714.4	713.1	711.9	710.6	709.4	707.8
142.5°	730.2	730.9	731.6	732.4	733.1	732.8	731.6	730.5	729.3	728.2	726.4
145°	755.9	756.6	757.3	758.0	758.7	758.6	757.6	756.6	755.6	754.6	752.2
147.5°	778.5	779.1	779.6	780.2	780.9	780.8	780.1	779.3	778.6	777.8	775.4
150°	792.2	792.9	793.6	794.3	795.0	795.0	794.2	793.3	792.5	791.6	789.3
152.5°	804.0	804.9	805.8	806.8	807.7	807.8	806.9	806.0	805.2	804.3	802.2
155°	820.3	821.4	822.6	823.7	824.8	825.0	824.1	823.3	822.4	821.5	819.8
157.5°	835.3	836.3	837.4	838.6	839.6	839.7	838.7	837.8	836.9	835.9	834.6
160°	843.9	844.9	845.9	846.9	847.8	847.9	847.1	846.2	845.4	844.5	843.6
162.5°	851.0	852.3	853.5	854.7	856.0	856.0	855.1	854.1	853.2	852.2	851.5
165°	861.7	862.7	863.7	864.8	865.8	865.8	864.8	863.7	862.7	861.7	861.3
167.5°	868.5	869.8	871.1	872.4	873.6	873.8	872.8	871.8	870.8	869.8	869.4
170°	872.6	873.9	875.1	876.5	877.7	877.9	876.8	875.8	874.9	873.9	873.6
172.5°	875.7	876.9	878.2	879.5	880.7	880.9	879.9	879.0	878.0	876.9	876.6
175°	878.3	879.8	881.2	882.6	884.0	884.2	883.2	882.3	881.3	880.3	879.9
177.5°	880.0	881.0	882.1	883.1	884.1	884.2	883.4	882.6	881.8	881.0	880.9
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	596.9	595.6	594.4	591.6	590.0	586.8	586.4	586.2	582.0	577.9	576.8
5°	617.4	614.1	609.3	603.6	597.7	591.7	587.6	584.3	576.2	568.6	564.1
7.5°	638.0	631.1	622.7	612.0	603.0	593.0	585.5	578.8	567.3	556.2	548.8
10°	653.4	642.1	631.0	616.2	604.6	593.3	582.7	573.6	560.7	546.1	535.7
12.5°	663.0	650.5	635.2	620.7	605.7	591.3	577.2	565.5	550.3	535.2	523.0
15°	675.9	662.5	643.9	623.2	604.0	585.1	569.0	554.4	534.6	516.5	501.5
17.5°	686.5	668.1	648.1	624.2	601.9	578.0	557.1	538.5	516.4	494.6	477.0
20°	689.9	671.6	648.5	624.6	598.3	570.2	547.7	527.4	503.7	480.0	459.8
22.5°	687.8	673.6	647.9	619.3	592.4	562.9	537.5	514.0	487.7	463.5	440.1
25°	673.5	668.6	644.4	613.1	582.4	548.1	518.7	493.0	463.1	437.1	411.6
27.5°	640.2	650.7	635.6	602.4	568.1	531.5	498.4	469.1	438.0	408.8	383.4
30°	608.1	632.1	625.7	594.9	556.6	520.6	483.5	452.9	419.7	389.7	364.6
32.5°	564.2	604.0	610.3	584.5	544.9	505.3	466.5	436.0	401.4	369.8	345.3
35°	494.2	553.8	581.1	564.7	525.0	482.2	442.2	406.7	371.8	340.7	316.4
37.5°	410.8	492.0	537.5	538.7	502.2	457.8	414.1	378.9	343.2	312.6	286.3
40°	356.7	444.6	504.0	517.1	486.3	438.4	394.1	358.3	323.5	293.5	263.3
42.5°	308.1	395.7	468.6	491.5	467.1	419.4	375.1	337.6	303.7	275.4	244.5
45°	249.1	325.7	406.1	447.0	433.5	389.3	342.5	306.8	275.1	250.6	221.0
47.5°	210.2	264.1	342.0	397.3	397.1	356.8	310.7	276.6	247.1	224.1	200.2
50°	188.0	235.0	300.8	363.6	368.8	335.0	291.2	257.4	229.9	205.8	186.5
52.5°	168.0	206.8	265.9	326.2	341.2	311.8	269.4	238.2	211.4	189.2	172.8
55°	142.0	172.0	217.0	273.2	296.0	275.3	237.6	208.4	186.7	168.1	153.9
57.5°	120.1	142.6	178.7	224.0	250.4	237.5	206.3	182.6	164.1	147.2	136.1
60°	106.4	124.8	155.3	193.2	222.4	213.3	186.7	164.7	148.9	134.3	123.8
62.5°	93.4	109.2	135.5	166.2	192.9	189.1	167.5	148.9	135.1	121.8	112.9
65°	75.2	86.7	107.2	131.3	152.8	154.5	138.9	126.4	114.0	103.5	95.6
67.5°	59.8	67.4	81.8	102.1	118.2	123.9	114.4	104.8	95.0	86.9	80.0
70°	50.5	56.5	67.1	83.5	98.3	104.3	98.8	91.3	82.8	76.2	70.3
72.5°	40.8	46.8	54.6	66.6	79.3	85.9	83.9	78.6	71.7	66.1	60.5
75°	30.8	32.6	37.9	46.0	55.9	61.6	63.0	60.2	54.7	50.5	47.2
77.5°	22.7	23.9	26.4	30.6	37.1	42.2	44.2	43.9	40.1	37.7	34.6
80°	18.2	18.8	20.1	21.8	26.8	31.8	33.3	33.3	30.6	29.6	26.6
82.5°	13.8	14.3	15.1	16.1	18.3	22.7	24.3	24.6	23.0	21.7	19.3
85°	7.9	7.7	8.1	8.7	9.1	10.3	12.8	13.2	12.8	11.1	10.5
87.5°	4.8	4.8	4.5	4.1	4.0	3.8	4.4	4.8	4.5	4.3	4.3
90°	10.5	9.4	8.2	6.9	5.4	3.7	2.2	0.6	2.2	3.7	5.4
92.5°	13.6	13.1	12.6	12.3	12.5	12.6	12.8	12.8	12.8	12.6	12.5
95°	22.9	21.9	20.9	22.7	27.5	32.1	36.8	41.5	36.8	32.1	27.5
97.5°	28.7	26.4	24.1	29.5	42.7	55.9	69.1	82.3	69.1	55.9	42.7
100°	31.6	29.2	26.8	35.2	54.7	74.1	93.5	112.9	93.5	74.1	54.7
102.5°	77.7	97.8	118.0	130.1	134.3	138.4	142.5	146.6	142.5	138.4	134.3
105°	116.3	155.0	193.7	210.9	206.7	202.4	198.1	193.9	198.1	202.4	206.7
107.5°	147.3	193.7	240.1	261.6	258.2	254.8	251.3	247.9	251.3	254.8	258.2
110°	193.6	234.5	275.4	294.4	291.5	288.6	285.5	282.6	285.5	288.6	291.5





TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	301.8	311.9	322.0	325.7	323.2	320.5	317.9	315.2	317.9	320.5	323.2
115°	386.5	382.9	379.4	376.4	374.0	371.6	369.2	366.8	369.2	371.6	374.0
117.5°	431.1	428.6	426.1	423.6	420.9	418.2	415.5	412.9	415.5	418.2	420.9
120°	462.4	459.9	457.4	455.0	452.9	450.8	448.6	446.5	448.6	450.8	452.9
122.5°	492.1	489.4	486.5	484.0	481.8	479.6	477.3	475.1	477.3	479.6	481.8
125°	533.6	530.9	528.2	525.9	524.1	522.3	520.4	518.6	520.4	522.3	524.1
127.5°	572.2	570.2	568.2	566.1	564.1	562.1	560.1	558.0	560.1	562.1	564.1
130°	597.1	595.6	594.0	592.1	589.8	587.5	585.3	583.0	585.3	587.5	589.8
132.5°	621.1	619.6	618.0	616.3	614.3	612.4	610.5	608.5	610.5	612.4	614.3
135°	655.1	653.8	652.6	650.8	648.5	646.2	644.0	641.7	644.0	646.2	648.5
137.5°	686.0	684.6	683.1	681.6	680.0	678.4	676.8	675.3	676.8	678.4	680.0
140°	706.2	704.6	703.1	701.7	700.6	699.5	698.3	697.2	698.3	699.5	700.6
142.5°	724.6	722.8	721.0	719.6	718.6	717.6	716.6	715.6	716.6	717.6	718.6
145°	749.8	747.3	744.9	743.9	744.0	744.1	744.2	744.4	744.2	744.1	744.0
147.5°	773.0	770.7	768.3	767.4	767.9	768.5	769.0	769.5	769.0	768.5	767.9
150°	787.0	784.8	782.6	781.9	782.9	783.9	784.9	785.9	784.9	783.9	782.9
152.5°	800.0	797.9	795.8	795.2	796.3	797.5	798.5	799.6	798.5	797.5	796.3
155°	818.1	816.5	814.8	814.6	815.8	817.1	818.4	819.7	818.4	817.1	815.8
157.5°	833.5	832.3	831.1	831.1	832.1	833.2	834.3	835.4	834.3	833.2	832.1
160°	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	843.6	842.8	842.0
162.5°	850.7	850.0	849.3	849.3	850.2	851.0	851.9	852.7	851.9	851.0	850.2
165°	860.9	860.5	860.1	860.2	861.1	862.0	862.8	863.7	862.8	862.0	861.1
167.5°	869.0	868.6	868.2	868.4	869.3	870.1	871.0	871.8	871.0	870.1	869.3
170°	873.3	873.1	872.7	873.1	873.9	874.8	875.6	876.5	875.6	874.8	873.9
172.5°	876.4	876.1	875.8	876.1	876.9	877.8	878.6	879.5	878.6	877.8	876.9
175°	879.7	879.4	879.1	879.5	880.5	881.5	882.4	883.4	882.4	881.5	880.5
177.5°	880.8	880.7	880.6	880.9	881.7	882.5	883.3	884.1	883.3	882.5	881.7
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	574.7	573.5	571.4	568.2	566.2	562.8	560.6	561.9	562.2	561.9	561.6
5°	559.3	555.0	549.1	543.4	538.1	532.5	529.2	527.9	525.0	523.4	522.5
7.5°	540.6	533.2	525.0	515.1	506.7	497.8	493.4	491.2	485.4	482.2	479.5
10°	526.6	515.1	506.8	493.8	485.9	474.4	466.5	466.7	458.8	454.3	451.1
12.5°	511.2	498.6	484.7	473.1	462.1	452.8	443.3	439.4	431.1	426.8	418.0
15°	485.7	470.9	456.4	440.6	429.4	415.0	401.3	384.4	370.9	359.1	355.9
17.5°	457.9	439.5	424.9	406.4	387.3	363.1	347.1	337.3	329.2	323.0	318.3
20°	438.7	420.1	404.5	376.6	350.8	334.4	322.7	315.1	306.7	300.0	296.3
22.5°	418.7	399.2	377.9	346.7	326.6	313.5	303.1	294.4	288.6	283.5	280.1
25°	390.1	368.8	333.8	312.4	296.1	282.3	275.1	269.8	263.8	256.6	253.4
27.5°	360.0	326.2	301.0	285.0	269.6	260.6	254.0	246.2	240.8	237.6	234.2
30°	337.4	303.6	284.0	266.5	255.7	245.7	238.0	233.5	228.3	222.8	220.6
32.5°	312.4	285.3	266.4	252.0	240.9	232.4	226.3	219.1	215.3	212.0	207.3
35°	281.2	260.6	243.4	231.8	221.1	214.3	207.2	203.0	196.1	193.2	191.5
37.5°	254.8	237.0	224.2	211.8	203.4	195.8	191.5	184.7	181.7	177.7	173.9
40°	239.8	222.4	210.1	199.9	190.6	184.9	179.5	174.0	169.5	167.7	163.1
42.5°	224.6	210.4	198.0	187.0	180.7	174.7	167.8	163.8	159.2	156.2	153.4
45°	203.6	191.0	180.5	171.4	164.4	158.2	153.7	147.0	144.5	138.6	136.1
47.5°	185.1	173.4	163.4	154.7	148.0	143.9	137.4	132.2	128.0	124.3	121.2
50°	172.0	162.2	152.5	144.8	138.8	132.9	126.2	123.6	117.1	115.2	113.4
52.5°	160.0	150.7	141.9	134.3	128.2	122.5	116.6	113.2	108.8	107.0	105.7
55°	143.2	134.3	125.8	119.1	113.1	107.2	103.5	99.2	97.2	95.8	94.2
57.5°	126.4	118.3	111.8	105.0	98.9	94.3	90.1	87.5	85.4	83.6	81.6
60°	115.7	108.0	102.1	95.8	89.5	85.7	82.5	79.4	77.0	74.1	73.3
62.5°	104.3	97.6	92.2	86.1	80.6	77.1	74.0	71.2	68.2	64.1	63.0
65°	88.7	83.5	77.8	72.7	67.9	64.4	59.9	56.7	55.5	55.1	54.9
67.5°	74.6	69.6	64.7	59.6	55.2	52.0	49.7	49.2	48.3	48.2	47.5
70°	65.2	60.5	55.7	50.8	46.5	46.0	45.2	44.3	43.3	43.0	42.5
72.5°	56.8	52.0	47.1	43.2	41.4	40.7	39.9	39.0	38.3	37.9	37.7
75°	43.5	39.1	35.8	34.4	33.4	32.8	31.6	31.0	30.6	30.0	29.8
77.5°	31.4	28.8	27.4	26.5	25.4	24.8	24.1	23.5	23.0	22.9	22.6
80°	23.9	22.6	21.7	20.4	20.1	19.3	19.1	18.5	18.6	18.0	18.0
82.5°	18.5	17.0	16.1	15.6	15.2	14.5	14.4	14.1	14.1	13.6	13.6
85°	9.5	9.1	8.7	8.3	8.3	7.7	7.9	7.7	7.7	7.3	7.1
87.5°	4.5	4.5	4.5	4.7	4.9	5.0	5.1	5.1	5.3	5.4	5.4
90°	6.9	8.2	9.4	10.5	11.6	12.8	13.5	14.2	14.9	15.6	16.1
92.5°	12.3	12.6	13.1	13.6	14.3	14.8	15.2	15.5	15.9	16.2	16.6
95°	22.7	20.9	21.9	22.9	23.9	24.9	25.6	26.3	27.0	27.7	28.0
97.5°	29.5	24.1	26.4	28.7	31.0	33.3	33.9	34.4	35.0	35.6	35.9
100°	35.2	26.8	29.2	31.6	34.0	36.4	37.5	38.6	39.8	40.9	41.6
102.5°	130.1	118.0	97.8	77.7	57.5	37.4	38.9	40.3	41.8	43.2	44.2
105°	210.9	193.7	155.0	116.3	77.6	38.9	40.5	42.0	43.6	45.1	46.2
107.5°	261.6	240.1	193.7	147.3	100.9	54.5	52.9	51.3	49.7	48.2	47.6
110°	294.4	275.4	234.5	193.6	152.6	111.6	97.5	83.3	69.1	54.9	48.2



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	325.7	322.0	311.9	301.8	291.7	281.5	229.9	178.2	126.4	74.7	49.0
115°	376.4	379.4	382.9	386.5	390.0	393.6	328.0	262.3	196.7	131.1	93.1
117.5°	423.6	426.1	428.6	431.1	433.5	436.0	420.1	404.2	388.3	372.4	347.7
120°	455.0	457.4	459.9	462.4	465.0	467.5	469.2	471.0	472.7	474.4	465.7
122.5°	484.0	486.5	489.4	492.1	494.9	497.7	498.6	499.7	500.7	501.8	500.4
125°	525.9	528.2	530.9	533.6	536.3	539.0	540.0	541.0	542.0	543.0	543.7
127.5°	566.1	568.2	570.2	572.2	574.3	576.2	577.7	579.2	580.6	582.0	582.8
130°	592.1	594.0	595.6	597.1	598.7	600.2	601.8	603.3	604.9	606.5	607.2
132.5°	616.3	618.0	619.6	621.1	622.7	624.2	625.5	626.9	628.2	629.5	630.2
135°	650.8	652.6	653.8	655.1	656.4	657.6	659.1	660.5	661.9	663.3	663.9
137.5°	681.6	683.1	684.6	686.0	687.4	688.9	690.3	691.7	693.0	694.5	694.9
140°	701.7	703.1	704.6	706.2	707.8	709.4	710.6	711.9	713.1	714.4	714.7
142.5°	719.6	721.0	722.8	724.6	726.4	728.2	729.3	730.5	731.6	732.8	733.1
145°	743.9	744.9	747.3	749.8	752.2	754.6	755.6	756.6	757.6	758.6	758.7
147.5°	767.4	768.3	770.7	773.0	775.4	777.8	778.6	779.3	780.1	780.8	780.9
150°	781.9	782.6	784.8	787.0	789.3	791.6	792.5	793.3	794.2	795.0	795.0
152.5°	795.2	795.8	797.9	800.0	802.2	804.3	805.2	806.0	806.9	807.8	807.7
155°	814.6	814.8	816.5	818.1	819.8	821.5	822.4	823.3	824.1	825.0	824.8
157.5°	831.1	831.1	832.3	833.5	834.6	835.9	836.9	837.8	838.7	839.7	839.6
160°	841.2	841.2	842.0	842.8	843.6	844.5	845.4	846.2	847.1	847.9	847.8
162.5°	849.3	849.3	850.0	850.7	851.5	852.2	853.2	854.1	855.1	856.0	856.0
165°	860.2	860.1	860.5	860.9	861.3	861.7	862.7	863.7	864.8	865.8	865.8
167.5°	868.4	868.2	868.6	869.0	869.4	869.8	870.8	871.8	872.8	873.8	873.6
170°	873.1	872.7	873.1	873.3	873.6	873.9	874.9	875.8	876.8	877.9	877.7
172.5°	876.1	875.8	876.1	876.4	876.6	876.9	878.0	879.0	879.9	880.9	880.7
175°	879.5	879.1	879.4	879.7	879.9	880.3	881.3	882.3	883.2	884.2	884.0
177.5°	880.9	880.6	880.7	880.8	880.9	881.0	881.8	882.6	883.4	884.2	884.1
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	559.8	560.1	559.6	559.9	559.6	560.1	559.8	561.6	561.9	562.2	561.9
5°	521.6	519.2	518.7	518.2	518.7	519.2	521.6	522.5	523.4	525.0	527.9
7.5°	476.0	475.6	474.6	473.1	474.6	475.6	476.0	479.5	482.2	485.4	491.2
10°	446.7	445.6	445.4	444.0	445.4	445.6	446.7	451.1	454.3	458.8	466.7
12.5°	412.2	405.7	405.1	401.5	405.1	405.7	412.2	418.0	426.8	431.1	439.4
15°	351.1	349.8	345.7	343.1	345.7	349.8	351.1	355.9	359.1	370.9	384.4
17.5°	316.0	312.0	310.8	310.2	310.8	312.0	316.0	318.3	323.0	329.2	337.3
20°	293.5	289.9	289.3	288.8	289.3	289.9	293.5	296.3	300.0	306.7	315.1
22.5°	277.9	274.1	272.6	271.3	272.6	274.1	277.9	280.1	283.5	288.6	294.4
25°	251.4	249.9	249.1	248.7	249.1	249.9	251.4	253.4	256.6	263.8	269.8
27.5°	230.6	227.5	226.9	225.8	226.9	227.5	230.6	234.2	237.6	240.8	246.2
30°	218.7	217.8	216.3	215.1	216.3	217.8	218.7	220.6	222.8	228.3	233.5
32.5°	204.8	203.9	202.7	202.2	202.7	203.9	204.8	207.3	212.0	215.3	219.1
35°	189.4	186.5	185.3	183.5	185.3	186.5	189.4	191.5	193.2	196.1	203.0
37.5°	173.1	171.6	169.9	170.5	169.9	171.6	173.1	173.9	177.7	181.7	184.7
40°	160.4	159.4	159.0	158.8	159.0	159.4	160.4	163.1	167.7	169.5	174.0
42.5°	150.3	147.6	146.5	146.5	146.5	147.6	150.3	153.4	156.2	159.2	163.8
45°	135.1	132.5	130.6	130.8	130.6	132.5	135.1	136.1	138.6	144.5	147.0
47.5°	119.5	119.4	118.2	118.6	118.2	119.4	119.5	121.2	124.3	128.0	132.2
50°	112.0	110.8	109.9	110.2	109.9	110.8	112.0	113.4	115.2	117.1	123.6
52.5°	104.9	103.8	103.2	104.1	103.2	103.8	104.9	105.7	107.0	108.8	113.2
55°	93.2	91.9	91.8	91.6	91.8	91.9	93.2	94.2	95.8	97.2	99.2
57.5°	80.1	79.3	78.0	77.6	78.0	79.3	80.1	81.6	83.6	85.4	87.5
60°	70.7	69.1	67.1	66.9	67.1	69.1	70.7	73.3	74.1	77.0	79.4
62.5°	62.1	61.8	61.3	61.3	61.3	61.8	62.1	63.0	64.1	68.2	71.2
65°	54.5	54.3	54.5	54.7	54.5	54.3	54.5	54.9	55.1	55.5	56.7
67.5°	47.4	47.1	46.7	46.9	46.7	47.1	47.4	47.5	48.2	48.3	49.2
70°	42.1	41.9	41.7	41.7	41.7	41.9	42.1	42.5	43.0	43.3	44.3
72.5°	36.9	36.9	36.7	36.6	36.7	36.9	36.9	37.7	37.9	38.3	39.0
75°	29.6	29.2	29.2	29.2	29.2	29.2	29.6	29.8	30.0	30.6	31.0
77.5°	22.6	22.3	22.1	21.9	22.1	22.3	22.6	22.6	22.9	23.0	23.5
80°	17.8	17.7	17.4	17.4	17.4	17.7	17.8	18.0	18.0	18.6	18.5
82.5°	13.6	13.4	13.4	13.2	13.4	13.4	13.6	13.6	13.6	14.1	14.1
85°	7.3	7.5	7.3	7.7	7.3	7.5	7.3	7.1	7.3	7.7	7.7
87.5°	5.4	5.3	5.5	5.4	5.5	5.3	5.4	5.4	5.4	5.3	5.1
90°	16.4	16.7	16.9	17.2	16.9	16.7	16.4	16.1	15.6	14.9	14.2
92.5°	16.7	16.9	17.0	17.2	17.0	16.9	16.7	16.6	16.2	15.9	15.5
95°	27.8	27.7	27.6	27.5	27.6	27.7	27.8	28.0	27.7	27.0	26.3
97.5°	36.1	36.3	36.5	36.6	36.5	36.3	36.1	35.9	35.6	35.0	34.4
100°	41.9	42.2	42.4	42.7	42.4	42.2	41.9	41.6	40.9	39.8	38.6
102.5°	44.6	45.0	45.4	45.8	45.4	45.0	44.6	44.2	43.2	41.8	40.3
105°	46.8	47.3	47.9	48.5	47.9	47.3	46.8	46.2	45.1	43.6	42.0
107.5°	48.2	48.8	49.3	49.8	49.3	48.8	48.2	47.6	48.2	49.7	51.3
110°	48.7	49.2	49.8	50.4	49.8	49.2	48.7	48.2	54.9	69.1	83.3



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	49.6	50.0	50.5	50.9	50.5	50.0	49.6	49.0	74.7	126.4	178.2
115°	82.9	72.7	62.5	52.3	62.5	72.7	82.9	93.1	131.1	196.7	262.3
117.5°	314.1	280.6	247.1	213.6	247.1	280.6	314.1	347.7	372.4	388.3	404.2
120°	446.5	427.4	408.2	389.1	408.2	427.4	446.5	465.7	474.4	472.7	471.0
122.5°	496.7	492.9	489.3	485.5	489.3	492.9	496.7	500.4	501.8	500.7	499.7
125°	544.1	544.6	544.9	545.4	544.9	544.6	544.1	543.7	543.0	542.0	541.0
127.5°	582.9	583.0	583.1	583.2	583.1	583.0	582.9	582.8	582.0	580.6	579.2
130°	607.1	606.9	606.7	606.6	606.7	606.9	607.1	607.2	606.5	604.9	603.3
132.5°	630.0	629.9	629.7	629.5	629.7	629.9	630.0	630.2	629.5	628.2	626.9
135°	663.6	663.3	663.0	662.7	663.0	663.3	663.6	663.9	663.3	661.9	660.5
137.5°	694.5	693.9	693.5	692.9	693.5	693.9	694.5	694.9	694.5	693.0	691.7
140°	714.0	713.3	712.6	711.9	712.6	713.3	714.0	714.7	714.4	713.1	711.9
142.5°	732.4	731.6	730.9	730.2	730.9	731.6	732.4	733.1	732.8	731.6	730.5
145°	758.0	757.3	756.6	755.9	756.6	757.3	758.0	758.7	758.6	757.6	756.6
147.5°	780.2	779.6	779.1	778.5	779.1	779.6	780.2	780.9	780.8	780.1	779.3
150°	794.3	793.6	792.9	792.2	792.9	793.6	794.3	795.0	795.0	794.2	793.3
152.5°	806.8	805.8	804.9	804.0	804.9	805.8	806.8	807.7	807.8	806.9	806.0
155°	823.7	822.6	821.4	820.3	821.4	822.6	823.7	824.8	825.0	824.1	823.3
157.5°	838.6	837.4	836.3	835.3	836.3	837.4	838.6	839.6	839.7	838.7	837.8
160°	846.9	845.9	844.9	843.9	844.9	845.9	846.9	847.8	847.9	847.1	846.2
162.5°	854.7	853.5	852.3	851.0	852.3	853.5	854.7	856.0	856.0	855.1	854.1
165°	864.8	863.7	862.7	861.7	862.7	863.7	864.8	865.8	865.8	864.8	863.7
167.5°	872.4	871.1	869.8	868.5	869.8	871.1	872.4	873.6	873.8	872.8	871.8
170°	876.5	875.1	873.9	872.6	873.9	875.1	876.5	877.7	877.9	876.8	875.8
172.5°	879.5	878.2	876.9	875.7	876.9	878.2	879.5	880.7	880.9	879.9	879.0
175°	882.6	881.2	879.8	878.3	879.8	881.2	882.6	884.0	884.2	883.2	882.3
177.5°	883.1	882.1	881.0	880.0	881.0	882.1	883.1	884.1	884.2	883.4	882.6
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	560.6	562.8	566.2	568.2	571.4	573.5	574.7	576.8	577.9	582.0	586.2
5°	529.2	532.5	538.1	543.4	549.1	555.0	559.3	564.1	568.6	576.2	584.3
7.5°	493.4	497.8	506.7	515.1	525.0	533.2	540.6	548.8	556.2	567.3	578.8
10°	466.5	474.4	485.9	493.8	506.8	515.1	526.6	535.7	546.1	560.7	573.6
12.5°	443.3	452.8	462.1	473.1	484.7	498.6	511.2	523.0	535.2	550.3	565.5
15°	401.3	415.0	429.4	440.6	456.4	470.9	485.7	501.5	516.5	534.6	554.4
17.5°	347.1	363.1	387.3	406.4	424.9	439.5	457.9	477.0	494.6	516.4	538.5
20°	322.7	334.4	350.8	376.6	404.5	420.1	438.7	459.8	480.0	503.7	527.4
22.5°	303.1	313.5	326.6	346.7	377.9	399.2	418.7	440.1	463.5	487.7	514.0
25°	275.1	282.3	296.1	312.4	333.8	368.8	390.1	411.6	437.1	463.1	493.0
27.5°	254.0	260.6	269.6	285.0	301.0	326.2	360.0	383.4	408.8	438.0	469.1
30°	238.0	245.7	255.7	266.5	284.0	303.6	337.4	364.6	389.7	419.7	452.9
32.5°	226.3	232.4	240.9	252.0	266.4	285.3	312.4	345.3	369.8	401.4	436.0
35°	207.2	214.3	221.1	231.8	243.4	260.6	281.2	316.4	340.7	371.8	406.7
37.5°	191.5	195.8	203.4	211.8	224.2	237.0	254.8	286.3	312.6	343.2	378.9
40°	179.5	184.9	190.6	199.9	210.1	222.4	239.8	263.3	293.5	323.5	358.3
42.5°	167.8	174.7	180.7	187.0	198.0	210.4	224.6	244.5	275.4	303.7	337.6
45°	153.7	158.2	164.4	171.4	180.5	191.0	203.6	221.0	250.6	275.1	306.8
47.5°	137.4	143.9	148.0	154.7	163.4	173.4	185.1	200.2	224.1	247.1	276.6
50°	126.2	132.9	138.8	144.8	152.5	162.2	172.0	186.5	205.8	229.9	257.4
52.5°	116.6	122.5	128.2	134.3	141.9	150.7	160.0	172.8	189.2	211.4	238.2
55°	103.5	107.2	113.1	119.1	125.8	134.3	143.2	153.9	168.1	186.7	208.4
57.5°	90.1	94.3	98.9	105.0	111.8	118.3	126.4	136.1	147.2	164.1	182.6
60°	82.5	85.7	89.5	95.8	102.1	108.0	115.7	123.8	134.3	148.9	164.7
62.5°	74.0	77.1	80.6	86.1	92.2	97.6	104.3	112.9	121.8	135.1	148.9
65°	59.9	64.4	67.9	72.7	77.8	83.5	88.7	95.6	103.5	114.0	126.4
67.5°	49.7	52.0	55.2	59.6	64.7	69.6	74.6	80.0	86.9	95.0	104.8
70°	45.2	46.0	46.5	50.8	55.7	60.5	65.2	70.3	76.2	82.8	91.3
72.5°	39.9	40.7	41.4	43.2	47.1	52.0	56.8	60.5	66.1	71.7	78.6
75°	31.6	32.8	33.4	34.4	35.8	39.1	43.5	47.2	50.5	54.7	60.2
77.5°	24.1	24.8	25.4	26.5	27.4	28.8	31.4	34.6	37.7	40.1	43.9
80°	19.1	19.3	20.1	20.4	21.7	22.6	23.9	26.6	29.6	30.6	33.3
82.5°	14.4	14.5	15.2	15.6	16.1	17.0	18.5	19.3	21.7	23.0	24.6
85°	7.9	7.7	8.3	8.3	8.7	9.1	9.5	10.5	11.1	12.8	13.2
87.5°	5.1	5.0	4.9	4.7	4.5	4.5	4.5	4.3	4.3	4.5	4.8
90°	13.5	12.8	11.6	10.5	9.4	8.2	6.9	5.4	3.7	2.2	0.6
92.5°	15.2	14.8	14.3	13.6	13.1	12.6	12.3	12.5	12.6	12.8	12.8
95°	25.6	24.9	23.9	22.9	21.9	20.9	22.7	27.5	32.1	36.8	41.5
97.5°	33.9	33.3	31.0	28.7	26.4	24.1	29.5	42.7	55.9	69.1	82.3
100°	37.5	36.4	34.0	31.6	29.2	26.8	35.2	54.7	74.1	93.5	112.9
102.5°	38.9	37.4	57.5	77.7	97.8	118.0	130.1	134.3	138.4	142.5	146.6
105°	40.5	38.9	77.6	116.3	155.0	193.7	210.9	206.7	202.4	198.1	193.9
107.5°	52.9	54.5	100.9	147.3	193.7	240.1	261.6	258.2	254.8	251.3	247.9
110°	97.5	111.6	152.6	193.6	234.5	275.4	294.4	291.5	288.6	285.5	282.6



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	229.9	281.5	291.7	301.8	311.9	322.0	325.7	323.2	320.5	317.9	315.2
115°	328.0	393.6	390.0	386.5	382.9	379.4	376.4	374.0	371.6	369.2	366.8
117.5°	420.1	436.0	433.5	431.1	428.6	426.1	423.6	420.9	418.2	415.5	412.9
120°	469.2	467.5	465.0	462.4	459.9	457.4	455.0	452.9	450.8	448.6	446.5
122.5°	498.6	497.7	494.9	492.1	489.4	486.5	484.0	481.8	479.6	477.3	475.1
125°	540.0	539.0	536.3	533.6	530.9	528.2	525.9	524.1	522.3	520.4	518.6
127.5°	577.7	576.2	574.3	572.2	570.2	568.2	566.1	564.1	562.1	560.1	558.0
130°	601.8	600.2	598.7	597.1	595.6	594.0	592.1	589.8	587.5	585.3	583.0
132.5°	625.5	624.2	622.7	621.1	619.6	618.0	616.3	614.3	612.4	610.5	608.5
135°	659.1	657.6	656.4	655.1	653.8	652.6	650.8	648.5	646.2	644.0	641.7
137.5°	690.3	688.9	687.4	686.0	684.6	683.1	681.6	680.0	678.4	676.8	675.3
140°	710.6	709.4	707.8	706.2	704.6	703.1	701.7	700.6	699.5	698.3	697.2
142.5°	729.3	728.2	726.4	724.6	722.8	721.0	719.6	718.6	717.6	716.6	715.6
145°	755.6	754.6	752.2	749.8	747.3	744.9	743.9	744.0	744.1	744.2	744.4
147.5°	778.6	777.8	775.4	773.0	770.7	768.3	767.4	767.9	768.5	769.0	769.5
150°	792.5	791.6	789.3	787.0	784.8	782.6	781.9	782.9	783.9	784.9	785.9
152.5°	805.2	804.3	802.2	800.0	797.9	795.8	795.2	796.3	797.5	798.5	799.6
155°	822.4	821.5	819.8	818.1	816.5	814.8	814.6	815.8	817.1	818.4	819.7
157.5°	836.9	835.9	834.6	833.5	832.3	831.1	831.1	832.1	833.2	834.3	835.4
160°	845.4	844.5	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5
162.5°	853.2	852.2	851.5	850.7	850.0	849.3	849.3	850.2	851.0	851.9	852.7
165°	862.7	861.7	861.3	860.9	860.5	860.1	860.2	861.1	862.0	862.8	863.7
167.5°	870.8	869.8	869.4	869.0	868.6	868.2	868.4	869.3	870.1	871.0	871.8
170°	874.9	873.9	873.6	873.3	873.1	872.7	873.1	873.9	874.8	875.6	876.5
172.5°	878.0	876.9	876.6	876.4	876.1	875.8	876.1	876.9	877.8	878.6	879.5
175°	881.3	880.3	879.9	879.7	879.4	879.1	879.5	880.5	881.5	882.4	883.4
177.5°	881.8	881.0	880.9	880.8	880.7	880.6	880.9	881.7	882.5	883.3	884.1
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	586.4	586.8	590.0	591.6	594.4	595.6	596.9	596.6	596.6	597.2	601.7
5°	587.6	591.7	597.7	603.6	609.3	614.1	617.4	620.6	621.9	627.7	632.9
7.5°	585.5	593.0	603.0	612.0	622.7	631.1	638.0	644.4	648.6	657.2	665.9
10°	582.7	593.3	604.6	616.2	631.0	642.1	653.4	662.2	664.9	677.7	685.0
12.5°	577.2	591.3	605.7	620.7	635.2	650.5	663.0	671.7	681.7	693.1	706.6
15°	569.0	585.1	604.0	623.2	643.9	662.5	675.9	691.1	702.0	714.6	726.4
17.5°	557.1	578.0	601.9	624.2	648.1	668.1	686.5	701.1	708.7	716.0	717.6
20°	547.7	570.2	598.3	624.6	648.5	671.6	689.9	702.0	704.1	704.3	693.6
22.5°	537.5	562.9	592.4	619.3	647.9	673.6	687.8	692.9	684.9	671.2	650.4
25°	518.7	548.1	582.4	613.1	644.4	668.6	673.5	664.4	636.2	606.6	569.2
27.5°	498.4	531.5	568.1	602.4	635.6	650.7	640.2	607.3	556.6	512.5	459.1
30°	483.5	520.6	556.6	594.9	625.7	632.1	608.1	559.6	500.5	434.1	380.8
32.5°	466.5	505.3	544.9	584.5	610.3	604.0	564.2	504.5	435.2	369.9	319.6
35°	442.2	482.2	525.0	564.7	581.1	553.8	494.2	416.6	345.7	284.8	250.1
37.5°	414.1	457.8	502.2	538.7	537.5	492.0	410.8	330.7	271.2	235.1	210.4
40°	394.1	438.4	486.3	517.1	504.0	444.6	356.7	281.2	237.6	208.8	190.8
42.5°	375.1	419.4	467.1	491.5	468.6	395.7	308.1	248.9	212.9	190.6	175.9
45°	342.5	389.3	433.5	447.0	406.1	325.7	249.1	206.2	182.3	165.7	155.6
47.5°	310.7	356.8	397.1	397.3	342.0	264.1	210.2	178.4	158.0	145.2	137.9
50°	291.2	335.0	368.8	363.6	300.8	235.0	188.0	160.6	143.7	133.7	126.0
52.5°	269.4	311.8	341.2	326.2	265.9	206.8	168.0	145.1	131.0	122.3	115.5
55°	237.6	275.3	296.0	273.2	217.0	172.0	142.0	123.9	113.4	106.1	100.2
57.5°	206.3	237.5	250.4	224.0	178.7	142.6	120.1	106.6	96.1	90.9	87.8
60°	186.7	213.3	222.4	193.2	155.3	124.8	106.4	93.8	86.1	82.7	79.6
62.5°	167.5	189.1	192.9	166.2	135.5	109.2	93.4	82.8	77.7	74.4	71.5
65°	138.9	154.5	152.8	131.3	107.2	86.7	75.2	68.7	64.8	60.2	55.1
67.5°	114.4	123.9	118.2	102.1	81.8	67.4	59.8	54.9	50.1	45.7	44.6
70°	98.8	104.3	98.3	83.5	67.1	56.5	50.5	44.6	41.7	40.8	38.9
72.5°	83.9	85.9	79.3	66.6	54.6	46.8	40.8	37.6	36.0	35.2	34.1
75°	63.0	61.6	55.9	46.0	37.9	32.6	30.8	29.6	28.5	27.7	27.1
77.5°	44.2	42.2	37.1	30.6	26.4	23.9	22.7	22.1	21.7	21.2	20.6
80°	33.3	31.8	26.8	21.8	20.1	18.8	18.2	17.4	17.4	17.0	16.4
82.5°	24.3	22.7	18.3	16.1	15.1	14.3	13.8	13.4	13.2	13.3	12.8
85°	12.8	10.3	9.1	8.7	8.1	7.7	7.9	7.5	7.5	7.5	7.3
87.5°	4.4	3.8	4.0	4.1	4.5	4.8	4.8	5.1	5.4	5.4	5.8
90°	2.2	3.7	5.4	6.9	8.2	9.4	10.5	11.6	12.8	13.5	14.2
92.5°	12.8	12.6	12.5	12.3	12.6	13.1	13.6	14.3	14.8	15.2	15.5
95°	36.8	32.1	27.5	22.7	20.9	21.9	22.9	23.9	24.9	25.6	26.3
97.5°	69.1	55.9	42.7	29.5	24.1	26.4	28.7	31.0	33.3	33.9	34.4
100°	93.5	74.1	54.7	35.2	26.8	29.2	31.6	34.0	36.4	37.5	38.6
102.5°	142.5	138.4	134.3	130.1	118.0	97.8	77.7	57.5	37.4	38.9	40.3
105°	198.1	202.4	206.7	210.9	193.7	155.0	116.3	77.6	38.9	40.5	42.0
107.5°	251.3	254.8	258.2	261.6	240.1	193.7	147.3	100.9	54.5	52.9	51.3
110°	285.5	288.6	291.5	294.4	275.4	234.5	193.6	152.6	111.6	97.5	83.3





TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	317.9	320.5	323.2	325.7	322.0	311.9	301.8	291.7	281.5	229.9	178.2
115°	369.2	371.6	374.0	376.4	379.4	382.9	386.5	390.0	393.6	328.0	262.3
117.5°	415.5	418.2	420.9	423.6	426.1	428.6	431.1	433.5	436.0	420.1	404.2
120°	448.6	450.8	452.9	455.0	457.4	459.9	462.4	465.0	467.5	469.2	471.0
122.5°	477.3	479.6	481.8	484.0	486.5	489.4	492.1	494.9	497.7	498.6	499.7
125°	520.4	522.3	524.1	525.9	528.2	530.9	533.6	536.3	539.0	540.0	541.0
127.5°	560.1	562.1	564.1	566.1	568.2	570.2	572.2	574.3	576.2	577.7	579.2
130°	585.3	587.5	589.8	592.1	594.0	595.6	597.1	598.7	600.2	601.8	603.3
132.5°	610.5	612.4	614.3	616.3	618.0	619.6	621.1	622.7	624.2	625.5	626.9
135°	644.0	646.2	648.5	650.8	652.6	653.8	655.1	656.4	657.6	659.1	660.5
137.5°	676.8	678.4	680.0	681.6	683.1	684.6	686.0	687.4	688.9	690.3	691.7
140°	698.3	699.5	700.6	701.7	703.1	704.6	706.2	707.8	709.4	710.6	711.9
142.5°	716.6	717.6	718.6	719.6	721.0	722.8	724.6	726.4	728.2	729.3	730.5
145°	744.2	744.1	744.0	743.9	744.9	747.3	749.8	752.2	754.6	755.6	756.6
147.5°	769.0	768.5	767.9	767.4	768.3	770.7	773.0	775.4	777.8	778.6	779.3
150°	784.9	783.9	782.9	781.9	782.6	784.8	787.0	789.3	791.6	792.5	793.3
152.5°	798.5	797.5	796.3	795.2	795.8	797.9	800.0	802.2	804.3	805.2	806.0
155°	818.4	817.1	815.8	814.6	814.8	816.5	818.1	819.8	821.5	822.4	823.3
157.5°	834.3	833.2	832.1	831.1	831.1	832.3	833.5	834.6	835.9	836.9	837.8
160°	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	845.4	846.2
162.5°	851.9	851.0	850.2	849.3	849.3	850.0	850.7	851.5	852.2	853.2	854.1
165°	862.8	862.0	861.1	860.2	860.1	860.5	860.9	861.3	861.7	862.7	863.7
167.5°	871.0	870.1	869.3	868.4	868.2	868.6	869.0	869.4	869.8	870.8	871.8
170°	875.6	874.8	873.9	873.1	872.7	873.1	873.3	873.6	873.9	874.9	875.8
172.5°	878.6	877.8	876.9	876.1	875.8	876.1	876.4	876.6	876.9	878.0	879.0
175°	882.4	881.5	880.5	879.5	879.1	879.4	879.7	879.9	880.3	881.3	882.3
177.5°	883.3	882.5	881.7	880.9	880.6	880.7	880.8	880.9	881.0	881.8	882.6
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	603.3	605.5	606.5	606.5	607.6	607.1	606.6
5°	638.0	641.9	642.7	646.3	649.0	648.2	648.5
7.5°	672.5	678.7	684.8	687.6	688.0	689.6	690.3
10°	693.8	698.8	708.3	706.9	714.0	718.1	711.4
12.5°	714.2	721.0	727.6	729.4	733.4	734.8	732.1
15°	732.6	736.3	736.6	735.7	736.9	735.8	732.0
17.5°	715.4	709.4	697.5	691.8	687.3	680.6	678.0
20°	686.9	669.4	649.2	641.1	631.6	613.0	617.4
22.5°	625.3	605.5	585.1	561.5	550.2	532.5	531.5
25°	529.5	495.3	457.5	431.2	415.8	398.2	390.5
27.5°	411.7	368.5	337.7	322.1	307.8	293.9	293.3
30°	334.2	301.8	277.9	264.6	255.8	249.9	251.2
32.5°	281.7	259.5	243.3	232.3	225.9	221.4	221.3
35°	230.3	215.1	204.7	200.1	195.5	192.3	192.4
37.5°	197.1	188.0	182.2	177.1	174.2	172.5	171.7
40°	180.0	172.5	168.1	165.1	162.6	160.4	160.0
42.5°	166.7	160.4	156.0	153.6	151.3	149.7	149.4
45°	147.8	142.8	138.8	136.1	135.1	133.7	133.7
47.5°	131.5	126.5	123.4	121.7	120.0	119.0	119.0
50°	120.6	116.6	113.9	112.8	111.4	110.8	110.6
52.5°	110.7	107.7	105.8	105.0	104.4	103.7	103.8
55°	97.2	95.6	94.8	94.2	93.2	91.9	92.7
57.5°	86.0	84.5	82.4	80.4	79.5	78.6	79.0
60°	78.0	75.2	72.3	70.1	69.5	67.7	67.7
62.5°	67.9	63.9	60.5	59.2	58.6	57.8	57.6
65°	52.3	50.6	49.8	49.0	48.6	48.6	48.2
67.5°	43.3	42.6	41.7	41.6	41.2	41.0	40.9
70°	38.3	37.5	37.1	36.8	36.5	36.6	36.0
72.5°	33.4	32.8	32.7	32.2	31.9	31.9	31.5
75°	26.3	26.3	26.1	25.9	25.5	25.3	25.5
77.5°	20.2	20.3	20.0	19.9	19.9	19.9	19.7
80°	16.2	16.4	16.2	16.0	15.8	16.0	15.8
82.5°	12.8	12.5	12.5	12.4	12.4	12.3	12.2
85°	7.3	7.5	7.3	7.1	7.1	7.1	7.3
87.5°	5.7	5.9	6.0	6.1	6.1	6.2	6.1
90°	14.9	15.6	16.1	16.4	16.7	16.9	17.2
92.5°	15.9	16.2	16.6	16.7	16.9	17.0	17.2
95°	27.0	27.7	28.0	27.8	27.7	27.6	27.5
97.5°	35.0	35.6	35.9	36.1	36.3	36.5	36.6
100°	39.8	40.9	41.6	41.9	42.2	42.4	42.7
102.5°	41.8	43.2	44.2	44.6	45.0	45.4	45.8
105°	43.6	45.1	46.2	46.8	47.3	47.9	48.5
107.5°	49.7	48.2	47.6	48.2	48.8	49.3	49.8
110°	69.1	54.9	48.2	48.7	49.2	49.8	50.4



TEST NUMBER: P331627-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	126.4	74.7	49.0	49.6	50.0	50.5	50.9
115°	196.7	131.1	93.1	82.9	72.7	62.5	52.3
117.5°	388.3	372.4	347.7	314.1	280.6	247.1	213.6
120°	472.7	474.4	465.7	446.5	427.4	408.2	389.1
122.5°	500.7	501.8	500.4	496.7	492.9	489.3	485.5
125°	542.0	543.0	543.7	544.1	544.6	544.9	545.4
127.5°	580.6	582.0	582.8	582.9	583.0	583.1	583.2
130°	604.9	606.5	607.2	607.1	606.9	606.7	606.6
132.5°	628.2	629.5	630.2	630.0	629.9	629.7	629.5
135°	661.9	663.3	663.9	663.6	663.3	663.0	662.7
137.5°	693.0	694.5	694.9	694.5	693.9	693.5	692.9
140°	713.1	714.4	714.7	714.0	713.3	712.6	711.9
142.5°	731.6	732.8	733.1	732.4	731.6	730.9	730.2
145°	757.6	758.6	758.7	758.0	757.3	756.6	755.9
147.5°	780.1	780.8	780.9	780.2	779.6	779.1	778.5
150°	794.2	795.0	795.0	794.3	793.6	792.9	792.2
152.5°	806.9	807.8	807.7	806.8	805.8	804.9	804.0
155°	824.1	825.0	824.8	823.7	822.6	821.4	820.3
157.5°	838.7	839.7	839.6	838.6	837.4	836.3	835.3
160°	847.1	847.9	847.8	846.9	845.9	844.9	843.9
162.5°	855.1	856.0	856.0	854.7	853.5	852.3	851.0
165°	864.8	865.8	865.8	864.8	863.7	862.7	861.7
167.5°	872.8	873.8	873.6	872.4	871.1	869.8	868.5
170°	876.8	877.9	877.7	876.5	875.1	873.9	872.6
172.5°	879.9	880.9	880.7	879.5	878.2	876.9	875.7
175°	883.2	884.2	884.0	882.6	881.2	879.8	878.3
177.5°	883.4	884.2	884.1	883.1	882.1	881.0	880.0
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5

(END OF REPORT)