

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331632-940

Luminaire Tested: **SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331632-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3446.2 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331632-940
CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331632-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23				23
2	85	78	72	67	75	70	65	61	55	51	48	41	38	37	28	26	25	20				20
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17				17
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	21	19	15				15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13				13
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12				12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10				10
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12	9				9
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	8				8
10	44	33	26	21	40	30	24	20	24	20	16	18	15	13	13	11	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331632-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	1.2
10°-20°	115.0	3.3
20°-30°	161.6	4.7
30°-40°	176.2	5.1
40°-50°	162.0	4.7
50°-60°	127.2	3.7
60°-70°	82.9	2.4
70°-80°	42.8	1.2
80°-90°	14.4	0.4
90°-100°	144.9	4.2
100°-110°	491.8	14.3
110°-120°	522.5	15.2
120°-130°	430.1	12.5
130°-140°	345.4	10.0
140°-150°	261.0	7.6
150°-160°	183.4	5.3
160°-170°	108.0	3.1
170°-180°	35.1	1.0
0°-30°	318.5	9.2
0°-40°	494.7	14.4
0°-60°	783.8	22.7
0°-90°	923.9	26.8
90°-120°	1159.2	33.6
90°-150°	2195.7	63.7
90°-180°	2522.0	73.2
0°-180°	3446.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	1	9	24	23	23	2
95°	24	60	273	103	80	26
105°	85	128	516	923	786	90
115°	150	189	432	892	1034	149
125°	209	247	415	722	839	186
135°	245	293	410	607	695	190
145°	280	322	408	507	555	176
155°	318	344	397	449	466	147
165°	347	358	380	403	409	98
175°	362	362	365	370	369	34
180°	362	362	362	362	362	



TEST NUMBER: P331632-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.4	5.2	5.2	4.8	4.5	4.7	5.4	6.3	7.2	7.3	7.1
90°	0.7	2.8	5.6	7.0	8.4	10.4	13.9	18.8	23.0	23.7	23.0
92.5°	8.5	12.3	17.3	20.3	25.1	31.7	47.4	69.6	89.3	90.6	76.5
95°	24.4	27.2	34.2	40.4	51.5	68.3	100.4	161.0	241.9	273.2	239.1
97.5°	39.8	43.5	50.9	60.4	73.2	92.1	132.4	217.0	351.3	466.5	489.4
100°	53.7	55.7	62.1	73.2	87.1	106.6	143.6	228.6	379.2	550.6	651.0
102.5°	66.5	68.0	74.3	85.4	100.0	119.5	153.6	229.2	368.6	553.5	711.2
105°	85.1	87.8	92.7	103.2	118.5	138.0	170.8	232.8	347.9	516.5	702.0
107.5°	105.1	107.4	112.1	121.7	136.9	156.6	188.3	242.5	337.5	476.9	640.7
110°	118.5	121.3	125.5	134.6	149.2	169.4	200.0	250.2	335.3	458.0	602.3



TEST NUMBER: P331632-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.7	133.6	138.3	146.8	160.9	181.6	211.2	258.6	335.8	445.7	575.5
115°	149.9	153.4	157.6	165.9	179.9	198.7	228.6	271.2	338.8	432.2	542.3
117.5°	169.7	172.5	176.6	184.0	197.4	217.0	244.7	284.5	343.8	425.6	521.4
120°	181.9	184.8	188.9	195.2	209.1	228.6	255.8	293.5	347.1	421.7	510.2
122.5°	193.7	195.9	200.0	206.9	220.8	240.9	266.4	301.3	351.1	419.5	500.8
125°	209.1	211.2	215.3	223.7	237.7	257.2	282.3	313.7	356.9	415.4	487.2
127.5°	221.4	224.2	230.1	239.2	252.6	272.7	297.1	325.2	362.9	413.0	474.7
130°	228.6	231.4	238.4	248.2	262.1	281.6	306.0	332.5	367.4	412.0	466.4
132.5°	235.3	238.7	246.2	256.5	271.0	290.5	313.8	339.7	371.8	411.4	459.7
135°	245.4	248.2	256.5	267.0	283.0	302.6	324.9	349.2	377.1	410.5	450.3
137.5°	254.9	258.2	266.5	277.7	293.6	311.7	333.8	356.5	381.8	410.5	443.7
140°	262.1	264.8	273.2	284.4	299.7	317.9	338.8	360.3	384.1	409.8	439.9
142.5°	269.3	271.6	279.4	290.5	305.3	322.4	342.7	363.7	385.8	409.8	436.0
145°	280.2	283.0	290.0	300.4	314.3	329.7	348.6	368.0	387.5	408.5	430.8
147.5°	291.9	294.0	300.7	310.3	321.9	335.6	353.3	370.4	388.2	406.0	425.5
150°	299.7	301.8	307.4	316.5	326.9	339.5	355.5	371.5	387.5	404.3	421.0
152.5°	307.6	308.5	314.1	322.0	331.9	343.4	357.8	372.1	386.5	401.5	417.1
155°	318.5	319.2	323.4	331.1	338.8	349.2	361.1	372.9	384.8	396.6	409.8
157.5°	327.8	328.4	331.8	338.5	344.6	353.4	363.5	372.9	381.6	391.6	403.1
160°	333.9	334.6	337.3	343.0	348.6	356.1	364.5	372.9	379.9	388.3	398.1
162.5°	340.0	339.6	342.4	346.9	351.9	357.8	365.2	372.4	378.3	385.5	393.5
165°	347.1	346.4	347.9	352.0	355.5	359.7	366.0	370.9	375.1	379.9	386.2
167.5°	353.0	352.1	353.4	356.1	358.6	361.2	365.8	369.9	371.8	375.1	378.9
170°	356.9	355.5	356.1	358.3	359.7	361.8	365.2	368.7	370.1	372.2	375.1
172.5°	359.1	358.3	357.8	360.0	360.8	362.3	364.7	367.0	367.9	368.9	371.1
175°	361.8	361.1	360.3	361.8	361.8	362.5	363.8	365.2	364.5	365.2	366.0
177.5°	363.0	361.9	361.3	362.5	362.5	362.5	363.0	364.2	363.0	362.5	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331632-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	6.9	6.6	6.8	6.9	6.9	6.9	6.9	6.9
90°	22.3	21.0	22.3	23.0	23.0	23.0	23.0	23.0
92.5°	60.8	52.2	46.3	42.0	41.4	39.1	39.8	38.6
95°	182.6	140.1	110.8	95.5	86.4	80.9	78.7	79.5
97.5°	426.1	348.7	273.2	222.9	189.6	172.5	162.3	156.4
100°	636.4	550.0	454.5	370.1	312.3	282.3	262.1	249.5
102.5°	774.2	754.7	684.7	595.4	532.5	481.3	456.1	439.2
105°	846.9	925.7	934.8	911.8	868.5	825.3	795.3	785.6
107.5°	794.5	913.1	985.6	1019.4	1024.8	1022.4	1016.5	1003.4
110°	749.3	874.1	963.3	1020.5	1050.4	1063.7	1070.0	1069.3



TEST NUMBER: P331632-940

CATALOG NUMBER: SA2XXRDIP-C290D725U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	708.1	827.8	923.2	988.7	1030.4	1052.6	1064.4	1068.2
115°	657.3	764.6	856.0	927.7	977.2	1009.3	1027.4	1033.8
117.5°	619.1	713.4	796.2	863.5	914.0	947.9	967.0	972.2
120°	600.1	686.6	760.5	823.9	872.7	905.4	925.7	932.6
122.5°	585.1	664.3	734.2	791.6	835.4	867.5	885.6	891.4
125°	563.2	635.0	696.3	748.6	789.1	815.6	832.9	838.6
127.5°	541.6	606.5	664.4	712.7	748.0	772.8	787.8	792.3
130°	527.6	587.6	642.7	688.7	722.8	746.5	760.5	766.1
132.5°	514.2	569.8	620.4	663.6	697.2	720.9	733.7	738.7
135°	495.6	541.6	587.6	626.6	656.7	679.7	692.1	695.0
137.5°	480.7	519.2	555.7	589.7	617.1	636.9	647.8	652.0
140°	471.2	504.7	536.7	567.4	589.7	607.8	618.3	622.5
142.5°	463.4	491.9	519.4	545.1	566.3	582.7	592.1	592.9
145°	452.4	475.4	497.0	517.2	534.0	545.8	552.8	554.8
147.5°	443.9	462.0	478.8	493.7	507.5	516.9	521.7	522.9
150°	437.7	453.1	467.7	480.3	490.7	499.1	503.3	504.0
152.5°	431.6	445.9	458.3	469.1	477.3	484.6	487.7	487.8
155°	423.1	434.3	444.7	452.4	460.0	464.9	467.7	466.4
157.5°	413.2	422.6	431.3	437.3	442.7	446.8	448.1	448.1
160°	407.1	414.7	422.4	427.3	432.2	435.7	436.3	436.3
162.5°	400.9	407.5	414.0	417.9	422.7	425.1	425.8	425.2
165°	391.7	396.6	401.5	404.3	407.1	409.8	409.8	409.2
167.5°	383.0	386.7	390.0	392.6	393.9	395.4	395.2	394.4
170°	378.5	380.6	383.3	384.8	385.5	387.5	386.8	385.5
172.5°	373.4	375.1	377.3	378.1	378.8	379.8	379.1	378.3
175°	368.0	368.7	369.4	370.1	370.1	370.9	370.1	368.7
177.5°	364.2	364.2	364.7	364.7	364.7	364.7	364.2	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

(END OF REPORT)