

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331428-935

Luminaire Tested: **SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331428-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4593.6 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331428-935
CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331428-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76
1	104	99	95	91	98	95	91	88	86	83	81	78	76	74	71	69	68	64
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	62	60	57	54
3	86	76	69	62	82	73	66	60	67	61	56	61	56	52	55	52	49	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	60	52	46	69	58	50	44	53	47	42	49	43	39	45	40	37	34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	31	27	23	21
10	50	38	30	25	48	37	29	25	34	28	24	32	26	22	29	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331428-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	2.8
10°-20°	363.1	7.9
20°-30°	533.7	11.6
30°-40°	619.9	13.5
40°-50°	619.3	13.5
50°-60°	540.0	11.8
60°-70°	399.3	8.7
70°-80°	226.2	4.9
80°-90°	62.2	1.4
90°-100°	63.3	1.4
100°-110°	214.7	4.7
110°-120°	228.0	5.0
120°-130°	187.7	4.1
130°-140°	150.7	3.3
140°-150°	113.9	2.5
150°-160°	80.1	1.7
160°-170°	47.1	1.0
170°-180°	15.3	0.3
0°-30°	1025.8	22.3
0°-40°	1645.7	35.8
0°-60°	2805.0	61.1
0°-90°	3492.7	76.0
90°-120°	505.9	11.0
90°-150°	958.3	20.9
90°-180°	1101.0	24.0
0°-180°	4593.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	0	4	10	10	10	3
95°	11	26	119	45	35	11
105°	37	56	225	403	343	39
115°	65	83	189	389	451	65
125°	91	108	181	315	366	81
135°	107	128	179	265	303	83
145°	122	141	178	221	242	77
155°	139	150	173	196	204	64
165°	152	156	166	176	179	43
175°	158	158	159	161	161	15
180°	158	158	158	158	158	



TEST NUMBER: P331428-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.0	18.8	18.5	18.2	17.8	17.6	17.4	17.4	17.2	16.9	16.1
90°	0.3	1.2	2.4	3.0	3.6	4.6	6.1	8.2	10.1	10.3	10.1
92.5°	3.7	5.3	7.6	8.9	10.9	13.8	20.7	30.4	39.0	39.5	33.4
95°	10.7	11.9	14.9	17.7	22.5	29.8	43.8	70.3	105.6	119.2	104.4
97.5°	17.3	18.9	22.2	26.3	31.9	40.2	57.8	94.7	153.3	203.5	213.5
100°	23.4	24.4	27.0	31.9	38.1	46.6	62.7	99.8	165.5	240.3	284.1
102.5°	29.0	29.7	32.5	37.3	43.7	52.2	67.1	100.0	160.8	241.5	310.4
105°	37.1	38.3	40.5	45.0	51.7	60.3	74.6	101.6	151.8	225.4	306.3
107.5°	45.9	46.8	48.9	53.1	59.8	68.4	82.2	105.8	147.3	208.1	279.7
110°	51.7	53.0	54.8	58.7	65.1	74.0	87.3	109.2	146.4	199.8	262.9



TEST NUMBER: P331428-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	58.3	60.4	64.1	70.2	79.3	92.2	112.9	146.5	194.5	251.2
115°	65.4	66.9	68.8	72.4	78.5	86.7	99.8	118.3	147.8	188.6	236.7
117.5°	74.0	75.3	77.1	80.3	86.2	94.7	106.8	124.2	150.1	185.7	227.6
120°	79.4	80.6	82.5	85.2	91.3	99.8	111.7	128.1	151.5	184.1	222.7
122.5°	84.6	85.5	87.3	90.3	96.3	105.1	116.2	131.5	153.2	183.0	218.5
125°	91.3	92.2	94.0	97.6	103.8	112.3	123.2	136.9	155.8	181.3	212.7
127.5°	96.6	97.8	100.4	104.4	110.2	119.0	129.7	142.0	158.3	180.3	207.2
130°	99.8	101.0	104.0	108.3	114.4	122.9	133.5	145.1	160.3	179.8	203.5
132.5°	102.7	104.2	107.5	111.9	118.3	126.8	137.0	148.3	162.3	179.5	200.6
135°	107.1	108.3	111.9	116.5	123.6	132.0	141.8	152.4	164.6	179.2	196.5
137.5°	111.2	112.7	116.3	121.2	128.1	136.0	145.7	155.6	166.7	179.1	193.6
140°	114.4	115.6	119.2	124.2	130.8	138.7	147.8	157.3	167.6	178.9	191.9
142.5°	117.5	118.6	121.9	126.8	133.3	140.7	149.6	158.8	168.3	178.9	190.3
145°	122.3	123.6	126.6	131.1	137.2	143.9	152.1	160.7	169.1	178.2	188.0
147.5°	127.4	128.3	131.2	135.4	140.5	146.5	154.2	161.7	169.4	177.2	185.7
150°	130.8	131.7	134.1	138.1	142.7	148.2	155.2	162.1	169.1	176.4	183.7
152.5°	134.2	134.7	137.1	140.5	144.9	149.8	156.1	162.4	168.7	175.2	182.0
155°	139.1	139.3	141.1	144.5	147.8	152.4	157.6	162.7	167.9	173.1	178.9
157.5°	143.0	143.4	144.8	147.7	150.4	154.2	158.6	162.7	166.5	170.9	175.9
160°	145.7	146.0	147.2	149.6	152.1	155.5	159.1	162.7	165.8	169.4	173.7
162.5°	148.4	148.2	149.5	151.4	153.6	156.2	159.4	162.5	165.1	168.2	171.8
165°	151.5	151.2	151.8	153.6	155.2	157.0	159.7	161.9	163.7	165.8	168.5
167.5°	154.0	153.7	154.2	155.4	156.5	157.6	159.6	161.4	162.3	163.7	165.4
170°	155.8	155.2	155.5	156.4	157.0	157.9	159.4	160.9	161.5	162.5	163.7
172.5°	156.7	156.4	156.2	157.1	157.5	158.2	159.2	160.2	160.6	161.0	162.0
175°	157.9	157.6	157.3	157.9	157.9	158.2	158.8	159.4	159.1	159.4	159.7
177.5°	158.4	157.9	157.7	158.2	158.2	158.2	158.4	158.9	158.4	158.2	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331428-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	15.3	14.5	13.9	13.5	13.3	13.0	12.8	12.6
90°	9.7	9.1	9.7	10.1	10.1	10.1	10.1	10.1
92.5°	26.5	22.7	20.2	18.3	18.1	17.1	17.3	16.9
95°	79.7	61.1	48.4	41.7	37.7	35.3	34.4	34.7
97.5°	186.0	152.1	119.2	97.3	82.7	75.3	70.9	68.3
100°	277.8	240.0	198.4	161.5	136.3	123.2	114.4	108.9
102.5°	337.9	329.3	298.9	259.8	232.4	210.1	199.1	191.7
105°	369.6	404.0	407.9	398.0	379.0	360.2	347.1	342.9
107.5°	346.7	398.6	430.2	444.9	447.3	446.3	443.6	438.0
110°	327.0	381.5	420.4	445.4	458.5	464.3	467.0	466.7



TEST NUMBER: P331428-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	309.0	361.3	402.9	431.5	449.7	459.3	464.5	466.1
115°	286.9	333.7	373.6	404.9	426.5	440.5	448.4	451.2
117.5°	270.2	311.3	347.5	376.9	398.9	413.7	422.0	424.3
120°	261.9	299.6	331.9	359.6	380.9	395.2	404.0	407.1
122.5°	255.4	289.9	320.5	345.4	364.5	378.7	386.5	389.0
125°	245.8	277.2	303.9	326.7	344.4	355.9	363.5	366.0
127.5°	236.3	264.8	290.0	311.0	326.4	337.3	343.8	345.8
130°	230.3	256.5	280.5	300.6	315.5	325.8	331.9	334.3
132.5°	224.5	248.7	270.8	289.6	304.3	314.6	320.2	322.4
135°	216.3	236.3	256.5	273.5	286.5	296.6	302.1	303.3
137.5°	209.8	226.6	242.5	257.4	269.3	277.9	282.8	284.6
140°	205.6	220.2	234.3	247.6	257.4	265.3	269.8	271.6
142.5°	202.2	214.6	226.7	237.9	247.1	254.3	258.4	258.7
145°	197.4	207.5	216.9	225.8	233.0	238.2	241.3	242.1
147.5°	193.7	201.6	209.0	215.4	221.4	225.6	227.6	228.3
150°	191.1	197.8	204.1	209.6	214.1	217.8	219.6	220.0
152.5°	188.4	194.6	200.0	204.7	208.4	211.5	212.8	212.9
155°	184.7	189.5	194.1	197.4	200.8	202.9	204.1	203.5
157.5°	180.4	184.4	188.2	190.9	193.2	195.0	195.5	195.5
160°	177.6	181.0	184.3	186.5	188.6	190.1	190.5	190.5
162.5°	175.0	177.9	180.7	182.4	184.5	185.5	185.8	185.5
165°	171.0	173.1	175.2	176.4	177.6	178.9	178.9	178.6
167.5°	167.1	168.8	170.2	171.3	171.9	172.5	172.5	172.1
170°	165.2	166.1	167.3	167.9	168.2	169.1	168.8	168.2
172.5°	163.0	163.7	164.6	165.0	165.3	165.7	165.4	165.1
175°	160.7	160.9	161.3	161.5	161.5	161.9	161.5	160.9
177.5°	158.9	158.9	159.2	159.2	159.2	159.2	158.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2

(END OF REPORT)