

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331429-935

Luminaire Tested: **SA2XXDIP-C1005D530U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331429-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5609.1 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331429-935  
CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68				
1	102	98	94	91	96	93	90	87	83	80	78	73	72	70	65	64	62	58				
2	94	87	81	75	88	82	77	72	73	69	66	65	62	59	58	56	53	50				
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46	43				
4	79	68	61	55	74	65	58	53	58	53	48	52	48	44	47	43	40	37				
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	43	39	36	33				
6	67	55	47	42	64	53	46	40	48	42	37	43	38	35	39	35	32	29				
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	36	32	29	26				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	24				
9	55	42	35	30	52	40	34	29	37	31	27	34	29	25	31	26	24	22				
10	51	39	32	27	48	37	31	26	34	29	25	31	26	23	28	24	22	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.5	2.9
10°-20°	475.3	8.5
20°-30°	689.9	12.3
30°-40°	728.0	13.0
40°-50°	644.6	11.5
50°-60°	514.4	9.2
60°-70°	349.6	6.2
70°-80°	179.3	3.2
80°-90°	44.7	0.8
90°-100°	20.7	0.4
100°-110°	76.0	1.4
110°-120°	203.0	3.6
120°-130°	335.2	6.0
130°-140°	356.5	6.4
140°-150°	331.3	5.9
150°-160°	266.4	4.7
160°-170°	171.7	3.1
170°-180°	59.1	1.1
0°-30°	1328.7	23.7
0°-40°	2056.7	36.7
0°-60°	3215.7	57.3
0°-90°	3789.3	67.6
90°-120°	299.7	5.3
90°-150°	1322.7	23.6
90°-180°	1820.0	32.4
0°-180°	5609.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	39
90°	12	0	12	0	12	7
95°	19	29	19	29	19	18
105°	34	137	34	137	34	36
115°	37	258	37	258	37	92
125°	384	365	384	365	384	332
135°	467	452	467	452	467	360
145°	532	524	532	524	532	333
155°	578	577	578	577	578	267
165°	607	608	607	608	607	171
175°	619	622	619	622	619	59
180°	621	621	621	621	621	



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	16.2	16.1	16.6	16.0	16.0	16.4	16.4	15.8	16.2	16.6	17.0
90°	12.1	12.0	11.7	11.5	11.4	11.0	10.5	10.0	9.5	9.0	8.2
92.5°	12.1	12.1	11.9	11.8	11.6	11.5	11.2	10.9	10.7	10.4	10.0
95°	19.3	19.5	19.5	19.6	19.7	19.5	19.0	18.5	18.0	17.6	16.8
97.5°	25.8	25.7	25.6	25.4	25.3	25.1	24.6	24.3	23.8	23.4	21.9
100°	30.1	29.9	29.7	29.5	29.3	28.8	28.0	27.2	26.4	25.6	23.9
102.5°	32.3	31.9	31.7	31.4	31.2	30.5	29.4	28.4	27.4	26.3	40.6
105°	34.2	33.8	33.3	33.0	32.5	31.8	30.7	29.6	28.5	27.4	54.7
107.5°	35.1	34.7	34.4	33.9	33.6	33.9	35.0	36.2	37.3	38.4	71.0
110°	35.5	35.1	34.7	34.3	33.9	38.7	48.6	58.6	68.6	78.6	107.5



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	35.8	35.6	35.2	34.9	34.6	52.6	89.0	125.4	161.9	198.4	205.4
115°	36.9	44.0	51.2	58.4	65.6	92.3	138.5	184.8	231.0	277.2	274.7
117.5°	150.4	174.1	197.7	221.3	245.0	262.3	273.5	284.7	295.9	307.0	305.4
120°	274.1	287.6	301.1	314.5	328.0	334.2	332.9	331.7	330.5	329.3	327.5
122.5°	342.0	344.7	347.2	349.9	352.5	353.4	352.8	352.0	351.3	350.6	348.6
125°	384.2	383.9	383.6	383.3	383.0	382.5	381.8	381.1	380.4	379.7	377.8
127.5°	410.8	410.7	410.7	410.6	410.5	410.0	409.0	407.9	406.9	406.0	404.5
130°	427.3	427.4	427.5	427.6	427.7	427.2	426.1	425.0	424.0	422.8	421.7
132.5°	443.5	443.6	443.7	443.8	443.8	443.5	442.6	441.6	440.7	439.7	438.6
135°	466.8	467.1	467.3	467.4	467.7	467.3	466.2	465.3	464.3	463.2	462.4
137.5°	488.2	488.5	488.8	489.1	489.5	489.2	488.2	487.2	486.3	485.3	484.2
140°	501.4	502.0	502.5	502.9	503.4	503.3	502.3	501.4	500.6	499.6	498.5
142.5°	514.4	514.9	515.4	515.9	516.4	516.3	515.4	514.6	513.8	513.0	511.7
145°	532.4	533.0	533.5	534.0	534.4	534.3	533.6	533.0	532.3	531.6	529.9
147.5°	548.4	548.8	549.2	549.7	550.0	550.0	549.5	549.0	548.5	547.9	546.2
150°	558.1	558.5	559.0	559.6	560.1	560.0	559.4	558.8	558.2	557.6	556.0
152.5°	566.4	567.0	567.7	568.3	568.9	569.0	568.4	567.8	567.2	566.6	565.1
155°	577.8	578.7	579.5	580.2	581.0	581.2	580.6	580.0	579.4	578.8	577.6
157.5°	588.3	589.1	589.9	590.6	591.5	591.5	590.8	590.1	589.4	588.8	588.0
160°	594.4	595.1	595.9	596.6	597.3	597.3	596.7	596.1	595.6	595.0	594.3
162.5°	599.5	600.4	601.2	602.1	603.0	603.0	602.4	601.7	601.0	600.3	599.8
165°	607.0	607.8	608.5	609.2	609.8	609.8	609.2	608.5	607.8	607.0	606.7
167.5°	611.8	612.7	613.6	614.5	615.4	615.5	614.8	614.1	613.4	612.7	612.4
170°	614.7	615.6	616.5	617.3	618.3	618.4	617.7	617.0	616.3	615.6	615.4
172.5°	616.8	617.8	618.6	619.6	620.4	620.5	619.8	619.1	618.5	617.8	617.5
175°	618.7	619.7	620.7	621.7	622.8	622.8	622.2	621.5	620.8	620.1	619.8
177.5°	619.9	620.6	621.3	622.1	622.8	622.8	622.3	621.7	621.2	620.6	620.5
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	17.3	17.1	17.0	17.8	16.0	15.8	13.5	11.7	11.4	11.1	10.2
90°	7.4	6.6	5.8	4.8	3.7	2.7	1.5	0.4	1.5	2.7	3.7
92.5°	9.6	9.2	8.9	8.7	8.8	8.9	9.0	9.0	9.0	8.9	8.8
95°	16.1	15.4	14.7	16.0	19.3	22.6	25.9	29.2	25.9	22.6	19.3
97.5°	20.2	18.6	17.0	20.8	30.1	39.4	48.6	57.9	48.6	39.4	30.1
100°	22.2	20.5	18.9	24.8	38.5	52.2	65.9	79.6	65.9	52.2	38.5
102.5°	54.8	69.0	83.1	91.7	94.5	97.5	100.4	103.2	100.4	97.5	94.5
105°	82.0	109.2	136.5	148.6	145.6	142.6	139.6	136.6	139.6	142.6	145.6
107.5°	103.8	136.5	169.1	184.3	181.8	179.4	177.0	174.6	177.0	179.4	181.8
110°	136.4	165.2	194.1	207.4	205.3	203.3	201.1	199.1	201.1	203.3	205.3





TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	212.6	219.7	226.9	229.5	227.6	225.8	223.9	222.1	223.9	225.8	227.6
115°	272.2	269.8	267.3	265.2	263.5	261.7	260.0	258.4	260.0	261.7	263.5
117.5°	303.7	302.0	300.2	298.4	296.5	294.6	292.7	290.8	292.7	294.6	296.5
120°	325.8	324.0	322.2	320.6	319.0	317.5	316.0	314.5	316.0	317.5	319.0
122.5°	346.6	344.7	342.8	341.0	339.4	337.9	336.2	334.7	336.2	337.9	339.4
125°	375.9	374.0	372.1	370.5	369.2	367.9	366.6	365.3	366.6	367.9	369.2
127.5°	403.1	401.7	400.3	398.8	397.4	396.0	394.5	393.0	394.5	396.0	397.4
130°	420.6	419.6	418.4	417.1	415.5	413.9	412.2	410.7	412.2	413.9	415.5
132.5°	437.6	436.4	435.3	434.1	432.7	431.4	430.0	428.7	430.0	431.4	432.7
135°	461.5	460.5	459.7	458.4	456.8	455.2	453.7	452.0	453.7	455.2	456.8
137.5°	483.3	482.2	481.2	480.1	479.0	477.9	476.7	475.7	476.7	477.9	479.0
140°	497.5	496.4	495.2	494.3	493.5	492.8	491.9	491.1	491.9	492.8	493.5
142.5°	510.4	509.2	507.9	507.0	506.2	505.5	504.8	504.0	504.8	505.5	506.2
145°	528.1	526.5	524.8	524.0	524.1	524.2	524.3	524.3	524.3	524.2	524.1
147.5°	544.6	542.9	541.2	540.5	541.0	541.3	541.7	542.1	541.7	541.3	541.0
150°	554.4	552.8	551.2	550.8	551.5	552.2	552.8	553.5	552.8	552.2	551.5
152.5°	563.6	562.1	560.5	560.2	560.9	561.7	562.5	563.3	562.5	561.7	560.9
155°	576.4	575.1	573.9	573.8	574.7	575.6	576.5	577.4	576.5	575.6	574.7
157.5°	587.1	586.3	585.5	585.4	586.2	586.9	587.7	588.4	587.7	586.9	586.2
160°	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	594.3	593.7	593.1
162.5°	599.3	598.7	598.2	598.3	598.8	599.4	600.0	600.6	600.0	599.4	598.8
165°	606.4	606.1	605.9	606.0	606.6	607.2	607.8	608.4	607.8	607.2	606.6
167.5°	612.2	611.8	611.6	611.7	612.3	612.9	613.5	614.2	613.5	612.9	612.3
170°	615.2	615.0	614.8	615.0	615.6	616.2	616.8	617.3	616.8	616.2	615.6
172.5°	617.3	617.2	616.9	617.2	617.8	618.4	619.0	619.6	619.0	618.4	617.8
175°	619.7	619.5	619.3	619.5	620.3	621.0	621.6	622.3	621.6	621.0	620.3
177.5°	620.4	620.4	620.3	620.5	621.1	621.6	622.2	622.8	622.2	621.6	621.1
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	9.9	9.6	9.2	9.4	9.0	8.7	8.3	8.4	8.4	7.5	7.6
90°	4.8	5.8	6.6	7.4	8.2	9.0	9.5	10.0	10.5	11.0	11.4
92.5°	8.7	8.9	9.2	9.6	10.0	10.4	10.7	10.9	11.2	11.5	11.6
95°	16.0	14.7	15.4	16.1	16.8	17.6	18.0	18.5	19.0	19.5	19.7
97.5°	20.8	17.0	18.6	20.2	21.9	23.4	23.8	24.3	24.6	25.1	25.3
100°	24.8	18.9	20.5	22.2	23.9	25.6	26.4	27.2	28.0	28.8	29.3
102.5°	91.7	83.1	69.0	54.8	40.6	26.3	27.4	28.4	29.4	30.5	31.2
105°	148.6	136.5	109.2	82.0	54.7	27.4	28.5	29.6	30.7	31.8	32.5
107.5°	184.3	169.1	136.5	103.8	71.0	38.4	37.3	36.2	35.0	33.9	33.6
110°	207.4	194.1	165.2	136.4	107.5	78.6	68.6	58.6	48.6	38.7	33.9



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	229.5	226.9	219.7	212.6	205.4	198.4	161.9	125.4	89.0	52.6	34.6
115°	265.2	267.3	269.8	272.2	274.7	277.2	231.0	184.8	138.5	92.3	65.6
117.5°	298.4	300.2	302.0	303.7	305.4	307.0	295.9	284.7	273.5	262.3	245.0
120°	320.6	322.2	324.0	325.8	327.5	329.3	330.5	331.7	332.9	334.2	328.0
122.5°	341.0	342.8	344.7	346.6	348.6	350.6	351.3	352.0	352.8	353.4	352.5
125°	370.5	372.1	374.0	375.9	377.8	379.7	380.4	381.1	381.8	382.5	383.0
127.5°	398.8	400.3	401.7	403.1	404.5	406.0	406.9	407.9	409.0	410.0	410.5
130°	417.1	418.4	419.6	420.6	421.7	422.8	424.0	425.0	426.1	427.2	427.7
132.5°	434.1	435.3	436.4	437.6	438.6	439.7	440.7	441.6	442.6	443.5	443.8
135°	458.4	459.7	460.5	461.5	462.4	463.2	464.3	465.3	466.2	467.3	467.7
137.5°	480.1	481.2	482.2	483.3	484.2	485.3	486.3	487.2	488.2	489.2	489.5
140°	494.3	495.2	496.4	497.5	498.5	499.6	500.6	501.4	502.3	503.3	503.4
142.5°	507.0	507.9	509.2	510.4	511.7	513.0	513.8	514.6	515.4	516.3	516.4
145°	524.0	524.8	526.5	528.1	529.9	531.6	532.3	533.0	533.6	534.3	534.4
147.5°	540.5	541.2	542.9	544.6	546.2	547.9	548.5	549.0	549.5	550.0	550.0
150°	550.8	551.2	552.8	554.4	556.0	557.6	558.2	558.8	559.4	560.0	560.1
152.5°	560.2	560.5	562.1	563.6	565.1	566.6	567.2	567.8	568.4	569.0	568.9
155°	573.8	573.9	575.1	576.4	577.6	578.8	579.4	580.0	580.6	581.2	581.0
157.5°	585.4	585.5	586.3	587.1	588.0	588.8	589.4	590.1	590.8	591.5	591.5
160°	592.5	592.5	593.1	593.7	594.3	595.0	595.6	596.1	596.7	597.3	597.3
162.5°	598.3	598.2	598.7	599.3	599.8	600.3	601.0	601.7	602.4	603.0	603.0
165°	606.0	605.9	606.1	606.4	606.7	607.0	607.8	608.5	609.2	609.8	609.8
167.5°	611.7	611.6	611.8	612.2	612.4	612.7	613.4	614.1	614.8	615.5	615.4
170°	615.0	614.8	615.0	615.2	615.4	615.6	616.3	617.0	617.7	618.4	618.3
172.5°	617.2	616.9	617.2	617.3	617.5	617.8	618.5	619.1	619.8	620.5	620.4
175°	619.5	619.3	619.5	619.7	619.8	620.1	620.8	621.5	622.2	622.8	622.8
177.5°	620.5	620.3	620.4	620.4	620.5	620.6	621.2	621.7	622.3	622.8	622.8
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331429-935  
 CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	7.6	7.1	7.1	6.6	7.1	7.1	7.6	7.6	7.5	8.4	8.4
90°	11.5	11.7	12.0	12.1	12.0	11.7	11.5	11.4	11.0	10.5	10.0
92.5°	11.8	11.9	12.1	12.1	12.1	11.9	11.8	11.6	11.5	11.2	10.9
95°	19.6	19.5	19.5	19.3	19.5	19.5	19.6	19.7	19.5	19.0	18.5
97.5°	25.4	25.6	25.7	25.8	25.7	25.6	25.4	25.3	25.1	24.6	24.3
100°	29.5	29.7	29.9	30.1	29.9	29.7	29.5	29.3	28.8	28.0	27.2
102.5°	31.4	31.7	31.9	32.3	31.9	31.7	31.4	31.2	30.5	29.4	28.4
105°	33.0	33.3	33.8	34.2	33.8	33.3	33.0	32.5	31.8	30.7	29.6
107.5°	33.9	34.4	34.7	35.1	34.7	34.4	33.9	33.6	33.9	35.0	36.2
110°	34.3	34.7	35.1	35.5	35.1	34.7	34.3	33.9	38.7	48.6	58.6



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	34.9	35.2	35.6	35.8	35.6	35.2	34.9	34.6	52.6	89.0	125.4
115°	58.4	51.2	44.0	36.9	44.0	51.2	58.4	65.6	92.3	138.5	184.8
117.5°	221.3	197.7	174.1	150.4	174.1	197.7	221.3	245.0	262.3	273.5	284.7
120°	314.5	301.1	287.6	274.1	287.6	301.1	314.5	328.0	334.2	332.9	331.7
122.5°	349.9	347.2	344.7	342.0	344.7	347.2	349.9	352.5	353.4	352.8	352.0
125°	383.3	383.6	383.9	384.2	383.9	383.6	383.3	383.0	382.5	381.8	381.1
127.5°	410.6	410.7	410.7	410.8	410.7	410.7	410.6	410.5	410.0	409.0	407.9
130°	427.6	427.5	427.4	427.3	427.4	427.5	427.6	427.7	427.2	426.1	425.0
132.5°	443.8	443.7	443.6	443.5	443.6	443.7	443.8	443.8	443.5	442.6	441.6
135°	467.4	467.3	467.1	466.8	467.1	467.3	467.4	467.7	467.3	466.2	465.3
137.5°	489.1	488.8	488.5	488.2	488.5	488.8	489.1	489.5	489.2	488.2	487.2
140°	502.9	502.5	502.0	501.4	502.0	502.5	502.9	503.4	503.3	502.3	501.4
142.5°	515.9	515.4	514.9	514.4	514.9	515.4	515.9	516.4	516.3	515.4	514.6
145°	534.0	533.5	533.0	532.4	533.0	533.5	534.0	534.4	534.3	533.6	533.0
147.5°	549.7	549.2	548.8	548.4	548.8	549.2	549.7	550.0	550.0	549.5	549.0
150°	559.6	559.0	558.5	558.1	558.5	559.0	559.6	560.1	560.0	559.4	558.8
152.5°	568.3	567.7	567.0	566.4	567.0	567.7	568.3	568.9	569.0	568.4	567.8
155°	580.2	579.5	578.7	577.8	578.7	579.5	580.2	581.0	581.2	580.6	580.0
157.5°	590.6	589.9	589.1	588.3	589.1	589.9	590.6	591.5	591.5	590.8	590.1
160°	596.6	595.9	595.1	594.4	595.1	595.9	596.6	597.3	597.3	596.7	596.1
162.5°	602.1	601.2	600.4	599.5	600.4	601.2	602.1	603.0	603.0	602.4	601.7
165°	609.2	608.5	607.8	607.0	607.8	608.5	609.2	609.8	609.8	609.2	608.5
167.5°	614.5	613.6	612.7	611.8	612.7	613.6	614.5	615.4	615.5	614.8	614.1
170°	617.3	616.5	615.6	614.7	615.6	616.5	617.3	618.3	618.4	617.7	617.0
172.5°	619.6	618.6	617.8	616.8	617.8	618.6	619.6	620.4	620.5	619.8	619.1
175°	621.7	620.7	619.7	618.7	619.7	620.7	621.7	622.8	622.8	622.2	621.5
177.5°	622.1	621.3	620.6	619.9	620.6	621.3	622.1	622.8	622.8	622.3	621.7
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	8.3	8.7	9.0	9.4	9.2	9.6	9.9	10.2	11.1	11.4	11.7
90°	9.5	9.0	8.2	7.4	6.6	5.8	4.8	3.7	2.7	1.5	0.4
92.5°	10.7	10.4	10.0	9.6	9.2	8.9	8.7	8.8	8.9	9.0	9.0
95°	18.0	17.6	16.8	16.1	15.4	14.7	16.0	19.3	22.6	25.9	29.2
97.5°	23.8	23.4	21.9	20.2	18.6	17.0	20.8	30.1	39.4	48.6	57.9
100°	26.4	25.6	23.9	22.2	20.5	18.9	24.8	38.5	52.2	65.9	79.6
102.5°	27.4	26.3	40.6	54.8	69.0	83.1	91.7	94.5	97.5	100.4	103.2
105°	28.5	27.4	54.7	82.0	109.2	136.5	148.6	145.6	142.6	139.6	136.6
107.5°	37.3	38.4	71.0	103.8	136.5	169.1	184.3	181.8	179.4	177.0	174.6
110°	68.6	78.6	107.5	136.4	165.2	194.1	207.4	205.3	203.3	201.1	199.1



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	161.9	198.4	205.4	212.6	219.7	226.9	229.5	227.6	225.8	223.9	222.1
115°	231.0	277.2	274.7	272.2	269.8	267.3	265.2	263.5	261.7	260.0	258.4
117.5°	295.9	307.0	305.4	303.7	302.0	300.2	298.4	296.5	294.6	292.7	290.8
120°	330.5	329.3	327.5	325.8	324.0	322.2	320.6	319.0	317.5	316.0	314.5
122.5°	351.3	350.6	348.6	346.6	344.7	342.8	341.0	339.4	337.9	336.2	334.7
125°	380.4	379.7	377.8	375.9	374.0	372.1	370.5	369.2	367.9	366.6	365.3
127.5°	406.9	406.0	404.5	403.1	401.7	400.3	398.8	397.4	396.0	394.5	393.0
130°	424.0	422.8	421.7	420.6	419.6	418.4	417.1	415.5	413.9	412.2	410.7
132.5°	440.7	439.7	438.6	437.6	436.4	435.3	434.1	432.7	431.4	430.0	428.7
135°	464.3	463.2	462.4	461.5	460.5	459.7	458.4	456.8	455.2	453.7	452.0
137.5°	486.3	485.3	484.2	483.3	482.2	481.2	480.1	479.0	477.9	476.7	475.7
140°	500.6	499.6	498.5	497.5	496.4	495.2	494.3	493.5	492.8	491.9	491.1
142.5°	513.8	513.0	511.7	510.4	509.2	507.9	507.0	506.2	505.5	504.8	504.0
145°	532.3	531.6	529.9	528.1	526.5	524.8	524.0	524.1	524.2	524.3	524.3
147.5°	548.5	547.9	546.2	544.6	542.9	541.2	540.5	541.0	541.3	541.7	542.1
150°	558.2	557.6	556.0	554.4	552.8	551.2	550.8	551.5	552.2	552.8	553.5
152.5°	567.2	566.6	565.1	563.6	562.1	560.5	560.2	560.9	561.7	562.5	563.3
155°	579.4	578.8	577.6	576.4	575.1	573.9	573.8	574.7	575.6	576.5	577.4
157.5°	589.4	588.8	588.0	587.1	586.3	585.5	585.4	586.2	586.9	587.7	588.4
160°	595.6	595.0	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0
162.5°	601.0	600.3	599.8	599.3	598.7	598.2	598.3	598.8	599.4	600.0	600.6
165°	607.8	607.0	606.7	606.4	606.1	605.9	606.0	606.6	607.2	607.8	608.4
167.5°	613.4	612.7	612.4	612.2	611.8	611.6	611.7	612.3	612.9	613.5	614.2
170°	616.3	615.6	615.4	615.2	615.0	614.8	615.0	615.6	616.2	616.8	617.3
172.5°	618.5	617.8	617.5	617.3	617.2	616.9	617.2	617.8	618.4	619.0	619.6
175°	620.8	620.1	619.8	619.7	619.5	619.3	619.5	620.3	621.0	621.6	622.3
177.5°	621.2	620.6	620.5	620.4	620.4	620.3	620.5	621.1	621.6	622.2	622.8
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	13.5	15.8	16.0	17.8	17.0	17.1	17.3	17.0	16.6	16.2	15.8
90°	1.5	2.7	3.7	4.8	5.8	6.6	7.4	8.2	9.0	9.5	10.0
92.5°	9.0	8.9	8.8	8.7	8.9	9.2	9.6	10.0	10.4	10.7	10.9
95°	25.9	22.6	19.3	16.0	14.7	15.4	16.1	16.8	17.6	18.0	18.5
97.5°	48.6	39.4	30.1	20.8	17.0	18.6	20.2	21.9	23.4	23.8	24.3
100°	65.9	52.2	38.5	24.8	18.9	20.5	22.2	23.9	25.6	26.4	27.2
102.5°	100.4	97.5	94.5	91.7	83.1	69.0	54.8	40.6	26.3	27.4	28.4
105°	139.6	142.6	145.6	148.6	136.5	109.2	82.0	54.7	27.4	28.5	29.6
107.5°	177.0	179.4	181.8	184.3	169.1	136.5	103.8	71.0	38.4	37.3	36.2
110°	201.1	203.3	205.3	207.4	194.1	165.2	136.4	107.5	78.6	68.6	58.6





TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	223.9	225.8	227.6	229.5	226.9	219.7	212.6	205.4	198.4	161.9	125.4
115°	260.0	261.7	263.5	265.2	267.3	269.8	272.2	274.7	277.2	231.0	184.8
117.5°	292.7	294.6	296.5	298.4	300.2	302.0	303.7	305.4	307.0	295.9	284.7
120°	316.0	317.5	319.0	320.6	322.2	324.0	325.8	327.5	329.3	330.5	331.7
122.5°	336.2	337.9	339.4	341.0	342.8	344.7	346.6	348.6	350.6	351.3	352.0
125°	366.6	367.9	369.2	370.5	372.1	374.0	375.9	377.8	379.7	380.4	381.1
127.5°	394.5	396.0	397.4	398.8	400.3	401.7	403.1	404.5	406.0	406.9	407.9
130°	412.2	413.9	415.5	417.1	418.4	419.6	420.6	421.7	422.8	424.0	425.0
132.5°	430.0	431.4	432.7	434.1	435.3	436.4	437.6	438.6	439.7	440.7	441.6
135°	453.7	455.2	456.8	458.4	459.7	460.5	461.5	462.4	463.2	464.3	465.3
137.5°	476.7	477.9	479.0	480.1	481.2	482.2	483.3	484.2	485.3	486.3	487.2
140°	491.9	492.8	493.5	494.3	495.2	496.4	497.5	498.5	499.6	500.6	501.4
142.5°	504.8	505.5	506.2	507.0	507.9	509.2	510.4	511.7	513.0	513.8	514.6
145°	524.3	524.2	524.1	524.0	524.8	526.5	528.1	529.9	531.6	532.3	533.0
147.5°	541.7	541.3	541.0	540.5	541.2	542.9	544.6	546.2	547.9	548.5	549.0
150°	552.8	552.2	551.5	550.8	551.2	552.8	554.4	556.0	557.6	558.2	558.8
152.5°	562.5	561.7	560.9	560.2	560.5	562.1	563.6	565.1	566.6	567.2	567.8
155°	576.5	575.6	574.7	573.8	573.9	575.1	576.4	577.6	578.8	579.4	580.0
157.5°	587.7	586.9	586.2	585.4	585.5	586.3	587.1	588.0	588.8	589.4	590.1
160°	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	595.6	596.1
162.5°	600.0	599.4	598.8	598.3	598.2	598.7	599.3	599.8	600.3	601.0	601.7
165°	607.8	607.2	606.6	606.0	605.9	606.1	606.4	606.7	607.0	607.8	608.5
167.5°	613.5	612.9	612.3	611.7	611.6	611.8	612.2	612.4	612.7	613.4	614.1
170°	616.8	616.2	615.6	615.0	614.8	615.0	615.2	615.4	615.6	616.3	617.0
172.5°	619.0	618.4	617.8	617.2	616.9	617.2	617.3	617.5	617.8	618.5	619.1
175°	621.6	621.0	620.3	619.5	619.3	619.5	619.7	619.8	620.1	620.8	621.5
177.5°	622.2	621.6	621.1	620.5	620.3	620.4	620.4	620.5	620.6	621.2	621.7
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	16.4	16.4	16.0	16.0	16.6	16.1	16.2
90°	10.5	11.0	11.4	11.5	11.7	12.0	12.1
92.5°	11.2	11.5	11.6	11.8	11.9	12.1	12.1
95°	19.0	19.5	19.7	19.6	19.5	19.5	19.3
97.5°	24.6	25.1	25.3	25.4	25.6	25.7	25.8
100°	28.0	28.8	29.3	29.5	29.7	29.9	30.1
102.5°	29.4	30.5	31.2	31.4	31.7	31.9	32.3
105°	30.7	31.8	32.5	33.0	33.3	33.8	34.2
107.5°	35.0	33.9	33.6	33.9	34.4	34.7	35.1
110°	48.6	38.7	33.9	34.3	34.7	35.1	35.5



TEST NUMBER: P331429-935

CATALOG NUMBER: SA2XXDIP-C1005D530U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	89.0	52.6	34.6	34.9	35.2	35.6	35.8
115°	138.5	92.3	65.6	58.4	51.2	44.0	36.9
117.5°	273.5	262.3	245.0	221.3	197.7	174.1	150.4
120°	332.9	334.2	328.0	314.5	301.1	287.6	274.1
122.5°	352.8	353.4	352.5	349.9	347.2	344.7	342.0
125°	381.8	382.5	383.0	383.3	383.6	383.9	384.2
127.5°	409.0	410.0	410.5	410.6	410.7	410.7	410.8
130°	426.1	427.2	427.7	427.6	427.5	427.4	427.3
132.5°	442.6	443.5	443.8	443.8	443.7	443.6	443.5
135°	466.2	467.3	467.7	467.4	467.3	467.1	466.8
137.5°	488.2	489.2	489.5	489.1	488.8	488.5	488.2
140°	502.3	503.3	503.4	502.9	502.5	502.0	501.4
142.5°	515.4	516.3	516.4	515.9	515.4	514.9	514.4
145°	533.6	534.3	534.4	534.0	533.5	533.0	532.4
147.5°	549.5	550.0	550.0	549.7	549.2	548.8	548.4
150°	559.4	560.0	560.1	559.6	559.0	558.5	558.1
152.5°	568.4	569.0	568.9	568.3	567.7	567.0	566.4
155°	580.6	581.2	581.0	580.2	579.5	578.7	577.8
157.5°	590.8	591.5	591.5	590.6	589.9	589.1	588.3
160°	596.7	597.3	597.3	596.6	595.9	595.1	594.4
162.5°	602.4	603.0	603.0	602.1	601.2	600.4	599.5
165°	609.2	609.8	609.8	609.2	608.5	607.8	607.0
167.5°	614.8	615.5	615.4	614.5	613.6	612.7	611.8
170°	617.7	618.4	618.3	617.3	616.5	615.6	614.7
172.5°	619.8	620.5	620.4	619.6	618.6	617.8	616.8
175°	622.2	622.8	622.8	621.7	620.7	619.7	618.7
177.5°	622.3	622.8	622.8	622.1	621.3	620.6	619.9
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0

(END OF REPORT)