

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331455-935

Luminaire Tested: **SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331455-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6604.7 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331455-935
CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331455-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331455-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	2.0
10°-20°	363.1	5.5
20°-30°	533.7	8.1
30°-40°	619.9	9.4
40°-50°	619.3	9.4
50°-60°	540.0	8.2
60°-70°	399.3	6.0
70°-80°	226.2	3.4
80°-90°	64.8	1.0
90°-100°	178.7	2.7
100°-110°	606.3	9.2
110°-120°	644.1	9.8
120°-130°	530.2	8.0
130°-140°	425.8	6.4
140°-150°	321.8	4.9
150°-160°	226.1	3.4
160°-170°	133.1	2.0
170°-180°	43.3	0.7
0°-30°	1025.8	15.5
0°-40°	1645.7	24.9
0°-60°	2805.0	42.5
0°-90°	3495.3	52.9
90°-120°	1429.1	21.6
90°-150°	2706.8	41.0
90°-180°	3109.0	47.1
0°-180°	6604.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	1	12	29	28	28	4
95°	30	74	337	127	98	32
105°	105	158	637	1138	968	111
115°	185	233	533	1100	1274	183
125°	258	305	512	891	1034	229
135°	302	361	506	748	857	234
145°	345	397	504	625	684	217
155°	393	424	489	553	575	181
165°	428	441	468	497	504	121
175°	446	446	450	456	455	42
180°	447	447	447	447	447	



TEST NUMBER: P331455-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.2	19.2	19.5	19.3	19.2	19.2	19.6	20.3	20.9	20.7	19.7
90°	0.9	3.4	6.9	8.6	10.3	12.9	17.2	23.2	28.3	29.2	28.3
92.5°	10.5	15.2	21.4	25.1	30.9	39.0	58.5	85.8	110.1	111.7	94.4
95°	30.0	33.5	42.1	49.9	63.6	84.2	123.7	198.5	298.2	336.8	294.7
97.5°	49.0	53.6	62.8	74.4	90.2	113.6	163.2	267.4	433.1	575.1	603.2
100°	66.1	68.7	76.5	90.2	107.5	131.5	177.0	281.9	467.4	678.8	802.6
102.5°	82.0	83.9	91.6	105.4	123.2	147.3	189.4	282.6	454.4	682.3	876.8
105°	104.9	108.3	114.3	127.2	146.1	170.1	210.5	287.0	428.8	636.7	865.3
107.5°	129.6	132.3	138.2	150.1	168.8	193.0	232.2	298.9	416.0	588.0	789.9
110°	146.1	149.6	154.6	165.8	183.9	208.8	246.6	308.5	413.4	564.6	742.4



TEST NUMBER: P331455-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.2	164.6	170.5	181.0	198.3	223.9	260.4	318.8	414.0	549.4	709.5
115°	184.8	189.1	194.2	204.5	221.7	244.9	281.9	334.2	417.6	532.8	668.6
117.5°	209.1	212.6	217.7	226.9	243.3	267.4	301.6	350.8	423.8	524.7	642.7
120°	224.3	227.7	232.9	240.6	257.8	281.9	315.4	361.8	427.9	519.9	629.0
122.5°	238.8	241.4	246.6	255.0	272.2	297.0	328.4	371.3	432.7	517.1	617.3
125°	257.8	260.4	265.5	275.9	293.0	317.1	348.0	386.7	440.0	512.1	600.6
127.5°	272.9	276.4	283.5	294.9	311.4	336.1	366.3	401.0	447.4	509.2	585.2
130°	281.9	285.2	293.9	305.9	323.1	347.2	377.2	409.9	452.9	507.8	574.9
132.5°	290.1	294.2	303.5	316.2	334.1	358.2	386.8	418.8	458.3	507.1	566.6
135°	302.5	305.9	316.2	329.1	348.9	372.9	400.5	430.5	464.9	506.1	555.1
137.5°	314.2	318.3	328.6	342.3	362.0	384.3	411.5	439.5	470.7	505.9	547.0
140°	323.1	326.6	336.8	350.6	369.5	391.8	417.6	444.3	473.5	505.2	542.3
142.5°	332.0	334.8	344.4	358.2	376.3	397.4	422.4	448.4	475.5	505.2	537.4
145°	345.4	348.9	357.5	370.4	387.5	406.5	429.6	453.7	477.8	503.5	531.1
147.5°	359.9	362.5	370.7	382.5	396.8	413.7	435.5	456.7	478.5	500.5	524.5
150°	369.5	372.0	378.9	390.1	403.0	418.4	438.2	458.0	477.8	498.4	519.0
152.5°	379.1	380.3	387.2	397.0	409.2	423.3	441.0	458.7	476.4	495.0	514.2
155°	392.7	393.6	398.7	408.2	417.6	430.5	445.1	459.7	474.3	489.0	505.2
157.5°	404.1	404.9	409.1	417.2	424.8	435.7	448.1	459.7	470.4	482.8	496.9
160°	411.6	412.5	415.9	422.8	429.6	439.1	449.4	459.7	468.3	478.6	490.7
162.5°	419.1	418.6	422.1	427.6	433.8	441.2	450.1	459.0	466.2	475.2	485.2
165°	427.9	427.1	428.8	433.9	438.2	443.4	451.2	457.2	462.3	468.3	476.0
167.5°	435.1	434.1	435.7	438.9	442.0	445.3	451.0	456.0	458.3	462.3	467.1
170°	440.0	438.2	439.1	441.7	443.4	446.0	450.3	454.6	456.3	458.8	462.3
172.5°	442.7	441.7	441.2	443.8	444.8	446.7	449.6	452.5	453.6	454.8	457.5
175°	446.0	445.1	444.3	446.0	446.0	446.9	448.6	450.3	449.4	450.3	451.2
177.5°	447.5	446.2	445.5	446.9	446.9	446.9	447.5	448.9	447.5	446.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331455-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	18.9	17.8	17.5	17.1	17.0	16.7	16.4	16.2
90°	27.5	25.7	27.5	28.3	28.3	28.3	28.3	28.3
92.5°	74.9	64.3	57.1	51.7	51.1	48.3	49.0	47.6
95°	225.2	172.7	136.6	117.7	106.6	99.7	97.1	98.0
97.5°	525.4	429.8	336.8	274.8	233.8	212.6	200.0	192.9
100°	784.5	678.0	560.3	456.3	385.0	348.0	323.1	307.6
102.5°	954.3	930.3	844.2	734.0	656.5	593.4	562.3	541.4
105°	1044.0	1141.2	1152.4	1123.9	1070.7	1017.4	980.4	968.5
107.5°	979.5	1125.7	1215.0	1256.6	1263.3	1260.4	1253.0	1237.1
110°	923.8	1077.5	1187.6	1258.0	1294.9	1311.3	1319.1	1318.2



TEST NUMBER: P331455-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	872.9	1020.5	1138.1	1218.8	1270.2	1297.5	1312.2	1316.8
115°	810.3	942.6	1055.2	1143.8	1204.7	1244.2	1266.6	1274.4
117.5°	763.2	879.4	981.5	1064.5	1126.7	1168.5	1192.1	1198.5
120°	739.9	846.4	937.5	1015.7	1075.8	1116.2	1141.2	1149.8
122.5°	721.3	818.9	905.2	975.9	1029.8	1069.4	1091.7	1098.9
125°	694.3	782.8	858.4	922.9	972.8	1005.4	1026.8	1033.7
127.5°	667.7	747.8	819.1	878.6	922.0	952.6	971.2	976.7
130°	650.5	724.4	792.3	849.0	891.1	920.3	937.5	944.3
132.5°	634.0	702.4	764.7	818.0	859.5	888.7	904.5	910.7
135°	611.0	667.7	724.4	772.5	809.4	837.8	853.3	856.7
137.5°	592.5	640.0	685.0	726.9	760.7	785.1	798.7	803.8
140°	580.9	622.2	661.7	699.5	726.9	749.3	762.2	767.3
142.5°	571.3	606.3	640.3	672.0	698.1	718.4	729.9	730.9
145°	557.7	586.1	612.7	637.6	658.2	672.9	681.4	684.0
147.5°	547.2	569.6	590.3	608.6	625.6	637.2	643.1	644.6
150°	539.7	558.5	576.6	592.0	604.9	615.3	620.4	621.3
152.5°	532.1	549.6	564.9	578.3	588.4	597.4	601.2	601.3
155°	521.6	535.4	548.2	557.7	567.1	573.2	576.6	574.9
157.5°	509.4	520.9	531.8	539.2	545.8	550.8	552.3	552.3
160°	501.8	511.3	520.7	526.8	532.8	537.1	538.0	538.0
162.5°	494.3	502.3	510.4	515.1	521.1	524.0	524.9	524.2
165°	482.9	489.0	495.0	498.4	501.8	505.2	505.2	504.4
167.5°	472.1	476.7	480.9	484.0	485.5	487.4	487.2	486.2
170°	466.6	469.2	472.6	474.3	475.2	477.8	476.9	475.2
172.5°	460.4	462.3	465.0	466.1	466.9	468.1	467.3	466.2
175°	453.7	454.6	455.5	456.3	456.3	457.2	456.3	454.6
177.5°	448.9	448.9	449.6	449.6	449.6	449.6	448.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)