

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331277-935

Luminaire Tested: **SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331277-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4441.4 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331277-935
CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25				
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22				
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	25	24	19				
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16				
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14				
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12				
6	60	48	41	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11				
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	1.1
10°-20°	140.9	3.2
20°-30°	204.5	4.6
30°-40°	215.8	4.9
40°-50°	191.1	4.3
50°-60°	152.5	3.4
60°-70°	103.6	2.3
70°-80°	53.1	1.2
80°-90°	17.5	0.4
90°-100°	75.1	1.7
100°-110°	233.2	5.3
110°-120°	398.7	9.0
120°-130°	524.3	11.8
130°-140°	588.5	13.2
140°-150°	577.0	13.0
150°-160°	484.0	10.9
160°-170°	321.0	7.2
170°-180°	112.2	2.5
0°-30°	393.9	8.9
0°-40°	609.7	13.7
0°-60°	953.2	21.5
0°-90°	1127.5	25.4
90°-120°	707.0	15.9
90°-150°	2396.8	54.0
90°-180°	3314.0	74.6
0°-180°	4441.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	13
90°	34	1	34	1	34	15
95°	62	52	62	52	62	69
105°	222	215	222	215	222	234
115°	400	400	400	400	400	395
125°	584	582	584	582	584	521
135°	762	753	762	753	762	587
145°	924	914	924	914	924	577
155°	1053	1045	1053	1045	1053	485
165°	1138	1137	1138	1137	1138	321
175°	1179	1183	1179	1183	1179	112
180°	1185	1185	1185	1185	1185	



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	10.8	10.8	10.9	10.8	10.7	10.8	10.9	10.8	11.1	11.4	10.6
90°	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1	34.5	35.0	30.1
92.5°	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9	31.9	31.8	30.7
95°	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0	64.0	64.0	63.5
97.5°	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6	107.6	107.6	106.8
100°	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0	138.0	138.0	137.3
102.5°	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2	171.0	170.8	170.0
105°	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9	220.5	220.0	219.6
107.5°	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6	274.4	274.2	274.2
110°	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6	348.1	348.6	348.8
115°	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6	403.8	404.1	404.5
117.5°	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8	458.3	458.8	460.1
120°	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0	494.0	494.0	495.8
122.5°	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4	531.9	532.4	533.7
125°	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8	587.4	588.1	588.8
127.5°	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5	641.3	642.0	642.9
130°	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2	677.6	678.1	678.6
132.5°	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9	713.9	714.9	714.8
135°	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7	765.9	766.1	765.7
137.5°	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1	816.3	816.5	815.9
140°	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1	850.1	850.1	849.0
142.5°	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9	880.7	880.5	879.8
145°	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6	927.3	927.1	925.7
147.5°	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5	968.0	967.5	966.6
150°	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5	993.8	993.2	992.2
152.5°	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7	1017.7
155°	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3	1052.2	1051.1	1050.5
157.5°	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7	1082.3	1080.7	1080.3
160°	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8	1100.4	1099.2	1098.9
162.5°	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2	1116.6	1115.2	1114.9
165°	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3	1137.7	1136.2	1136.2
167.5°	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7	1155.1	1153.6	1153.6
170°	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2	1164.7	1163.1	1163.4
172.5°	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5	1171.9	1170.4	1170.5
175°	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3	1179.7	1178.1	1178.6
177.5°	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8	1183.1
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	9.7	8.8	7.7	7.3	6.4	5.8	4.6	3.6	4.0	4.4	4.6
90°	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0	3.7	6.4	9.0
92.5°	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8	19.7	21.7	23.7
95°	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0	54.2	56.5	58.6
97.5°	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1	96.9	98.9	100.9
100°	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0	128.8	130.6	132.3
102.5°	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7	162.0	163.5	164.9
105°	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0	215.7	216.4	217.1
107.5°	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8	270.8	271.8	272.8
110°	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1	306.3	307.7	309.0



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5	344.7	346.1	347.4
115°	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0	401.4	402.7	404.1
117.5°	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4	458.2	460.0	461.8
120°	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	495.8	497.7	499.4
122.5°	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5	530.6	532.7	534.9
125°	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0	584.1	586.1	588.1
127.5°	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3	636.8	639.4	641.9
130°	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1	669.9	672.9	675.7
132.5°	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9	706.3	708.6	710.9
135°	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1	755.5	758.0	760.4
137.5°	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9	806.9	808.9	810.9
140°	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1	838.1	840.1	842.1
142.5°	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1	870.1	872.1	874.1
145°	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1	915.7	917.2	918.8
147.5°	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1	957.0	958.8	960.7
150°	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1	984.5	985.8	987.1
152.5°	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9	1009.3	1010.6	1011.9
155°	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2	1045.8	1046.5	1047.1
157.5°	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9	1077.4	1077.8	1078.2
160°	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1	1096.6	1097.0	1097.4
162.5°	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7	1113.8	1113.9	1114.0
165°	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1	1137.0	1136.7	1136.4
167.5°	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8	1156.1	1155.4	1154.8
170°	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2	1166.5	1165.8	1165.1
172.5°	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3	1173.7	1173.0	1172.3
175°	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2	1182.5	1181.8	1181.1
177.5°	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7	1186.2	1185.7	1185.2
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	5.0	5.6	6.4	7.4	8.2	9.0	8.8	8.7	8.6	8.2	8.2
90°	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1	33.7	33.2	33.1
92.5°	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9	32.0	32.2	32.2
95°	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0	64.0	64.0	63.8
97.5°	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6	107.6	107.6	107.6
100°	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0	138.0	138.0	137.9
102.5°	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2	171.3	171.5	171.5
105°	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9	221.4	221.8	222.1
107.5°	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6	274.7	274.9	274.5
110°	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	310.7



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6	347.1	346.6	346.0
115°	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6	403.4	403.1	402.7
117.5°	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8	457.3	456.8	456.2
120°	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0	494.0	494.0	493.7
122.5°	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4	530.9	530.3	529.9
125°	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8	586.1	585.4	585.0
127.5°	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5	639.6	638.9	638.1
130°	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2	676.7	676.3	675.6
132.5°	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9	712.0	711.0	710.2
135°	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7	765.4	765.2	764.7
137.5°	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1	816.0	815.8	815.3
140°	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1	850.1	850.1	849.6
142.5°	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9	881.1	881.2	880.9
145°	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6	927.8	928.0	927.6
147.5°	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5	969.0	969.5	969.3
150°	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5	995.1	995.8	995.8
152.5°	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1
155°	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3	1054.5	1055.6	1055.8
157.5°	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7	1085.3	1086.8	1087.0
160°	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8	1103.1	1104.5	1104.7
162.5°	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2	1119.6	1121.2	1121.4
165°	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3	1140.8	1142.4	1142.5
167.5°	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7	1158.2	1159.8	1159.9
170°	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2	1167.8	1169.3	1169.5
172.5°	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5	1175.0	1176.6	1176.6
175°	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3	1182.8	1184.4	1184.5
177.5°	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	8.3	8.1	8.2	8.1	8.2	8.1	8.3	8.2	8.2	8.6	8.7
90°	33.3	33.6	33.8	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1
92.5°	32.3	32.3	32.4	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9
95°	63.4	62.9	62.4	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0
97.5°	107.5	107.5	107.5	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6
100°	137.7	137.5	137.2	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0
102.5°	171.3	171.1	170.8	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2
105°	222.1	222.1	222.1	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9
107.5°	273.5	272.5	271.5	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6
110°	310.0	309.4	308.7	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	345.5	345.0	344.6	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6
115°	402.1	401.4	400.7	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6
117.5°	455.5	454.8	454.1	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8
120°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0
122.5°	529.3	528.8	528.4	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4
125°	584.7	584.5	584.3	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8
127.5°	637.4	636.7	636.0	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5
130°	674.8	673.8	673.0	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2
132.5°	709.5	708.7	708.0	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9
135°	764.1	763.4	762.8	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7
137.5°	814.3	813.5	812.6	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1
140°	848.8	847.9	847.0	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1
142.5°	879.9	879.1	878.2	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9
145°	926.8	925.9	925.0	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6
147.5°	968.5	967.6	966.7	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5
150°	995.1	994.5	993.8	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5
152.5°	1021.2	1020.5	1019.6	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5
155°	1055.2	1054.5	1053.8	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3
157.5°	1085.9	1084.9	1083.8	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7
160°	1103.8	1102.9	1102.0	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8
162.5°	1120.3	1119.3	1118.2	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2
165°	1141.5	1140.4	1139.3	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3
167.5°	1158.8	1157.6	1156.5	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7
170°	1168.1	1166.8	1165.4	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2
172.5°	1175.4	1174.0	1172.7	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5
175°	1183.2	1181.8	1180.5	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3
177.5°	1185.9	1184.9	1183.8	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	8.8	9.0	8.2	7.4	6.4	5.6	5.0	4.6	4.4	4.0	3.6
90°	34.5	35.0	30.1	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0
92.5°	31.9	31.8	30.7	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8
95°	64.0	64.0	63.5	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0
97.5°	107.6	107.6	106.8	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1
100°	138.0	138.0	137.3	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0
102.5°	171.0	170.8	170.0	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7
105°	220.5	220.0	219.6	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0
107.5°	274.4	274.2	274.2	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8
110°	311.1	311.1	311.1	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.1	348.6	348.8	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5
115°	403.8	404.1	404.5	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0
117.5°	458.3	458.8	460.1	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4
120°	494.0	494.0	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0
122.5°	531.9	532.4	533.7	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5
125°	587.4	588.1	588.8	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0
127.5°	641.3	642.0	642.9	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3
130°	677.6	678.1	678.6	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1
132.5°	713.9	714.9	714.8	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9
135°	765.9	766.1	765.7	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1
137.5°	816.3	816.5	815.9	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9
140°	850.1	850.1	849.0	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1
142.5°	880.7	880.5	879.8	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1
145°	927.3	927.1	925.7	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1
147.5°	968.0	967.5	966.6	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1
150°	993.8	993.2	992.2	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1
152.5°	1019.6	1018.7	1017.7	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9
155°	1052.2	1051.1	1050.5	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2
157.5°	1082.3	1080.7	1080.3	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9
160°	1100.4	1099.2	1098.9	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1
162.5°	1116.6	1115.2	1114.9	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7
165°	1137.7	1136.2	1136.2	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1
167.5°	1155.1	1153.6	1153.6	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8
170°	1164.7	1163.1	1163.4	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2
172.5°	1171.9	1170.4	1170.5	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3
175°	1179.7	1178.1	1178.6	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2
177.5°	1183.8	1182.8	1183.1	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.6	5.8	6.4	7.3	7.7	8.8	9.7	10.6	11.4	11.1	10.8
90°	3.7	6.4	9.0	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1
92.5°	19.7	21.7	23.7	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9
95°	54.2	56.5	58.6	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0
97.5°	96.9	98.9	100.9	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6
100°	128.8	130.6	132.3	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0
102.5°	162.0	163.5	164.9	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2
105°	215.7	216.4	217.1	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9
107.5°	270.8	271.8	272.8	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6
110°	306.3	307.7	309.0	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.7	346.1	347.4	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6
115°	401.4	402.7	404.1	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6
117.5°	458.2	460.0	461.8	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8
120°	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0
122.5°	530.6	532.7	534.9	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4
125°	584.1	586.1	588.1	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8
127.5°	636.8	639.4	641.9	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5
130°	669.9	672.9	675.7	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2
132.5°	706.3	708.6	710.9	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9
135°	755.5	758.0	760.4	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7
137.5°	806.9	808.9	810.9	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1
140°	838.1	840.1	842.1	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1
142.5°	870.1	872.1	874.1	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9
145°	915.7	917.2	918.8	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6
147.5°	957.0	958.8	960.7	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5
150°	984.5	985.8	987.1	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5
152.5°	1009.3	1010.6	1011.9	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5
155°	1045.8	1046.5	1047.1	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3
157.5°	1077.4	1077.8	1078.2	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7
160°	1096.6	1097.0	1097.4	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8
162.5°	1113.8	1113.9	1114.0	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2
165°	1137.0	1136.7	1136.4	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3
167.5°	1156.1	1155.4	1154.8	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7
170°	1166.5	1165.8	1165.1	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2
172.5°	1173.7	1173.0	1172.3	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5
175°	1182.5	1181.8	1181.1	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3
177.5°	1186.2	1185.7	1185.2	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	10.9	10.8	10.7	10.8	10.9	10.8	10.8
90°	33.7	33.2	33.1	33.3	33.6	33.8	34.0
92.5°	32.0	32.2	32.2	32.3	32.3	32.4	32.4
95°	64.0	64.0	63.8	63.4	62.9	62.4	62.0
97.5°	107.6	107.6	107.6	107.5	107.5	107.5	107.5
100°	138.0	138.0	137.9	137.7	137.5	137.2	137.0
102.5°	171.3	171.5	171.5	171.3	171.1	170.8	170.7
105°	221.4	221.8	222.1	222.1	222.1	222.1	222.1
107.5°	274.7	274.9	274.5	273.5	272.5	271.5	270.4
110°	311.1	311.1	310.7	310.0	309.4	308.7	308.1



TEST NUMBER: P331277-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.1	346.6	346.0	345.5	345.0	344.6	344.1
115°	403.4	403.1	402.7	402.1	401.4	400.7	400.0
117.5°	457.3	456.8	456.2	455.5	454.8	454.1	453.5
120°	494.0	494.0	493.7	493.1	492.4	491.7	491.0
122.5°	530.9	530.3	529.9	529.3	528.8	528.4	527.9
125°	586.1	585.4	585.0	584.7	584.5	584.3	584.1
127.5°	639.6	638.9	638.1	637.4	636.7	636.0	635.2
130°	676.7	676.3	675.6	674.8	673.8	673.0	672.1
132.5°	712.0	711.0	710.2	709.5	708.7	708.0	707.3
135°	765.4	765.2	764.7	764.1	763.4	762.8	762.1
137.5°	816.0	815.8	815.3	814.3	813.5	812.6	811.7
140°	850.1	850.1	849.6	848.8	847.9	847.0	846.1
142.5°	881.1	881.2	880.9	879.9	879.1	878.2	877.3
145°	927.8	928.0	927.6	926.8	925.9	925.0	924.1
147.5°	969.0	969.5	969.3	968.5	967.6	966.7	966.0
150°	995.1	995.8	995.8	995.1	994.5	993.8	993.2
152.5°	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7
155°	1054.5	1055.6	1055.8	1055.2	1054.5	1053.8	1053.1
157.5°	1085.3	1086.8	1087.0	1085.9	1084.9	1083.8	1082.7
160°	1103.1	1104.5	1104.7	1103.8	1102.9	1102.0	1101.1
162.5°	1119.6	1121.2	1121.4	1120.3	1119.3	1118.2	1117.1
165°	1140.8	1142.4	1142.5	1141.5	1140.4	1139.3	1138.2
167.5°	1158.2	1159.8	1159.9	1158.8	1157.6	1156.5	1155.4
170°	1167.8	1169.3	1169.5	1168.1	1166.8	1165.4	1164.2
172.5°	1175.0	1176.6	1176.6	1175.4	1174.0	1172.7	1171.3
175°	1182.8	1184.4	1184.5	1183.2	1181.8	1180.5	1179.1
177.5°	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2

(END OF REPORT)