

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331684-940

Luminaire Tested: **SA2XXRDIP-C675D530U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331684-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D530U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3955.2 lumens  
Efficiency: N/A  
Efficacy: 98.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331684-940

CATALOG NUMBER: SA2XXRDIP-C675D530U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331684-940

CATALOG NUMBER: SA2XXRDIP-C675D530U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52				
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45				
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43	39				
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	33				
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29				
5	70	59	51	45	65	55	48	42	47	42	38	41	36	33	34	31	29	26				
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23				
7	60	48	40	35	55	45	38	33	39	34	29	34	29	26	29	25	23	20				
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21	18				
9	52	40	33	28	48	37	31	26	33	28	24	29	24	21	24	21	19	17				
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	19	17	15				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331684-940

CATALOG NUMBER: SA2XXRDIP-C675D530U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.2	2.4
10°-20°	258.5	6.5
20°-30°	363.0	9.2
30°-40°	395.9	10.0
40°-50°	364.0	9.2
50°-60°	285.9	7.2
60°-70°	186.4	4.7
70°-80°	96.1	2.4
80°-90°	26.5	0.7
90°-100°	21.5	0.5
100°-110°	78.7	2.0
110°-120°	210.3	5.3
120°-130°	347.1	8.8
130°-140°	369.2	9.3
140°-150°	343.1	8.7
150°-160°	275.9	7.0
160°-170°	177.8	4.5
170°-180°	61.2	1.5
0°-30°	715.7	18.1
0°-40°	1111.6	28.1
0°-60°	1761.4	44.5
0°-90°	2070.4	52.3
90°-120°	310.4	7.8
90°-150°	1369.9	34.6
90°-180°	1885.0	47.7
0°-180°	3955.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	0	6	9	12	13	3
95°	30	16	18	20	20	37
105°	141	148	28	33	35	151
115°	268	276	287	82	38	263
125°	378	385	393	396	398	337
135°	468	475	480	484	484	361
145°	543	543	550	553	551	340
155°	598	594	599	602	598	275
165°	630	628	629	632	629	178
175°	644	642	642	645	641	61
180°	643	643	643	643	643	



TEST NUMBER: P331684-940

CATALOG NUMBER: SA2XXRDIP-C675D530U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.8	10.7	9.6	8.6	7.5	7.0	7.2	7.3	7.5	7.7	7.7
90°	0.4	1.6	2.8	3.8	5.0	6.0	6.9	7.7	8.5	9.3	9.8
92.5°	9.4	9.3	9.2	9.1	9.0	9.2	9.5	10.0	10.3	10.8	11.1
95°	30.2	26.8	23.5	20.0	16.6	15.2	16.0	16.7	17.4	18.2	18.6
97.5°	60.0	50.4	40.8	31.2	21.6	17.6	19.3	21.0	22.6	24.3	24.7
100°	82.4	68.2	54.0	39.9	25.7	19.5	21.2	23.0	24.8	26.5	27.4
102.5°	106.9	104.0	100.9	97.9	95.0	86.1	71.4	56.7	42.0	27.3	28.4
105°	141.4	144.5	147.7	150.8	153.9	141.3	113.1	84.9	56.6	28.4	29.5
107.5°	180.8	183.3	185.8	188.3	190.8	175.1	141.3	107.5	73.6	39.8	38.6
110°	206.2	208.3	210.5	212.7	214.8	201.0	171.1	141.2	111.3	81.4	71.1



TEST NUMBER: P331684-940

CATALOG NUMBER: SA2XXRDIP-C675D530U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	230.0	231.9	233.8	235.8	237.6	235.0	227.6	220.2	212.8	205.5	167.6
115°	267.6	269.3	271.1	272.9	274.6	276.8	279.4	282.0	284.5	287.1	239.2
117.5°	301.2	303.2	305.1	307.1	309.1	310.9	312.7	314.5	316.3	318.0	306.5
120°	325.7	327.3	328.9	330.4	332.0	333.7	335.6	337.4	339.2	341.1	342.3
122.5°	346.6	348.2	349.9	351.5	353.1	355.0	357.0	359.0	361.1	363.1	363.8
125°	378.4	379.7	381.0	382.4	383.7	385.4	387.4	389.3	391.3	393.2	394.0
127.5°	407.1	408.6	410.1	411.5	413.0	414.6	416.0	417.5	418.9	420.4	421.4
130°	425.3	427.0	428.6	430.3	431.9	433.4	434.5	435.6	436.8	437.9	439.1
132.5°	444.0	445.3	446.7	448.2	449.6	450.8	452.0	453.2	454.2	455.4	456.4
135°	468.1	469.8	471.4	473.1	474.7	476.1	477.0	478.0	478.8	479.7	480.8
137.5°	492.7	493.7	494.9	496.1	497.2	498.4	499.4	500.5	501.5	502.6	503.6
140°	508.6	509.4	510.3	511.1	511.9	512.9	514.1	515.2	516.3	517.5	518.4
142.5°	522.0	522.8	523.5	524.2	525.0	526.0	527.4	528.6	529.9	531.3	532.1
145°	543.1	543.0	542.9	542.8	542.7	543.5	545.3	547.0	548.8	550.5	551.3
147.5°	561.4	561.0	560.6	560.3	559.8	560.5	562.2	564.0	565.7	567.5	568.0
150°	573.3	572.6	571.9	571.1	570.4	570.9	572.6	574.2	575.9	577.5	578.1
152.5°	583.4	582.6	581.8	580.9	580.1	580.5	582.1	583.7	585.2	586.8	587.5
155°	598.0	597.1	596.1	595.2	594.2	594.4	595.7	596.9	598.2	599.4	600.0
157.5°	609.4	608.7	607.9	607.1	606.3	606.4	607.2	608.1	608.9	609.8	610.5
160°	616.2	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	616.8
162.5°	622.1	621.4	620.8	620.2	619.6	619.6	620.1	620.6	621.2	621.7	622.4
165°	630.1	629.5	628.8	628.2	627.6	627.5	627.8	628.0	628.4	628.7	629.5
167.5°	636.1	635.4	634.8	634.2	633.6	633.4	633.6	634.0	634.3	634.5	635.3
170°	639.4	638.8	638.2	637.6	636.9	636.7	636.9	637.1	637.3	637.6	638.3
172.5°	641.7	641.1	640.4	639.8	639.2	638.9	639.2	639.4	639.5	639.8	640.5
175°	644.5	643.8	643.1	642.4	641.6	641.4	641.6	641.8	641.9	642.2	642.9
177.5°	645.0	644.4	643.8	643.3	642.7	642.4	642.5	642.6	642.7	642.7	643.4
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331684-940

CATALOG NUMBER: SA2XXRDIP-C675D530U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	7.6	7.5	7.5	7.4	7.5	7.5	7.6	7.6
90°	10.3	10.9	11.4	11.8	11.9	12.1	12.4	12.6
92.5°	11.3	11.6	11.9	12.0	12.2	12.3	12.5	12.6
95°	19.2	19.7	20.2	20.4	20.3	20.2	20.2	20.0
97.5°	25.1	25.5	25.9	26.2	26.3	26.5	26.6	26.8
100°	28.2	29.0	29.9	30.3	30.6	30.8	30.9	31.2
102.5°	29.4	30.5	31.6	32.3	32.5	32.8	33.1	33.4
105°	30.7	31.8	32.9	33.7	34.2	34.5	35.0	35.4
107.5°	37.5	36.3	35.1	34.8	35.1	35.6	35.9	36.4
110°	60.7	50.4	40.0	35.1	35.5	35.9	36.4	36.7





TEST NUMBER: P331684-940

CATALOG NUMBER: SA2XXRDIP-C675D530U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	129.9	92.2	54.5	35.8	36.1	36.5	36.8	37.1
115°	191.4	143.5	95.6	67.9	60.5	53.1	45.6	38.2
117.5°	294.9	283.3	271.7	253.7	229.2	204.7	180.3	155.8
120°	343.6	344.8	346.1	339.7	325.7	311.8	297.8	283.8
122.5°	364.5	365.3	366.0	365.1	362.4	359.6	357.0	354.2
125°	394.7	395.4	396.1	396.6	397.0	397.3	397.6	397.9
127.5°	422.5	423.6	424.6	425.2	425.3	425.3	425.3	425.4
130°	440.1	441.3	442.5	443.0	442.8	442.7	442.6	442.6
132.5°	457.4	458.3	459.3	459.7	459.6	459.5	459.4	459.3
135°	481.9	482.9	483.9	484.4	484.1	483.9	483.8	483.5
137.5°	504.6	505.6	506.7	506.9	506.6	506.2	506.0	505.6
140°	519.3	520.2	521.2	521.4	520.8	520.4	519.9	519.3
142.5°	533.0	533.8	534.7	534.8	534.3	533.8	533.2	532.7
145°	552.0	552.7	553.4	553.5	553.0	552.5	552.0	551.4
147.5°	568.6	569.1	569.6	569.6	569.3	568.8	568.4	567.9
150°	578.7	579.3	580.0	580.1	579.5	579.0	578.5	578.0
152.5°	588.1	588.7	589.3	589.2	588.6	587.9	587.2	586.6
155°	600.7	601.3	601.9	601.7	600.9	600.1	599.3	598.4
157.5°	611.2	611.9	612.6	612.6	611.7	610.9	610.1	609.3
160°	617.3	618.0	618.6	618.6	617.9	617.2	616.4	615.6
162.5°	623.1	623.8	624.6	624.5	623.6	622.7	621.8	620.9
165°	630.2	630.9	631.6	631.6	630.9	630.2	629.5	628.7
167.5°	636.0	636.8	637.5	637.4	636.4	635.5	634.5	633.6
170°	639.0	639.7	640.4	640.3	639.4	638.5	637.6	636.6
172.5°	641.2	641.9	642.7	642.6	641.7	640.7	639.8	638.8
175°	643.6	644.4	645.1	645.0	643.9	642.8	641.9	640.8
177.5°	643.9	644.5	645.1	645.0	644.3	643.5	642.7	642.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1

(END OF REPORT)