

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331694-940

Luminaire Tested: **SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331694-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5216.8 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	33	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21151	21151	21151	21151
5°	23622	21284	18870	21284
10°	26209	21135	16357	21135
15°	27497	20824	12889	20824
20°	23838	20366	11153	20366
25°	15634	19737	9957	19737
30°	10524	18975	9012	18975
35°	8523	18015	8129	18015
40°	7579	16971	7522	16971
45°	6859	15746	6715	15746
50°	6242	14531	6219	14531
55°	5869	13185	5790	13185
60°	4908	11951	4850	11951
65°	4138	10850	4695	10850
70°	3829	9692	4428	9692
75°	3575	8434	4086	8434
80°	3301	6936	3636	6936
85°	3038	5483	3205	5483



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	2.4
10°-20°	346.0	6.6
20°-30°	445.9	8.5
30°-40°	423.7	8.1
40°-50°	363.0	7.0
50°-60°	276.4	5.3
60°-70°	174.7	3.3
70°-80°	87.3	1.7
80°-90°	26.9	0.5
90°-100°	66.8	1.3
100°-110°	207.5	4.0
110°-120°	354.7	6.8
120°-130°	466.5	8.9
130°-140°	523.6	10.0
140°-150°	513.4	9.8
150°-160°	430.6	8.3
160°-170°	285.6	5.5
170°-180°	99.8	1.9
0°-30°	916.1	17.6
0°-40°	1339.8	25.7
0°-60°	1979.2	37.9
0°-90°	2268.2	43.5
90°-120°	629.1	12.1
90°-150°	2132.6	40.9
90°-180°	2949.0	56.5
0°-180°	5216.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1310	1310	1310	1310	1310	
5°	1458	1313	1164	1313	1458	144
15°	1645	1246	771	1246	1645	444
25°	878	1108	559	1108	878	416
35°	432	914	412	914	432	277
45°	300	690	294	690	300	232
55°	208	468	206	468	208	183
65°	108	284	123	284	108	110
75°	57	135	66	135	57	61
85°	16	30	17	30	16	18
90°	30	1	30	1	30	14
95°	55	46	55	46	55	62
105°	198	191	198	191	198	208
115°	356	356	356	356	356	352
125°	520	518	520	518	520	463
135°	678	670	678	670	678	522
145°	822	813	822	813	822	513
155°	937	930	937	930	937	431
165°	1013	1012	1013	1012	1013	286
175°	1049	1053	1049	1053	1049	100
180°	1054	1054	1054	1054	1054	



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1363.2	1364.2	1365.4	1362.8	1362.8	1360.6	1355.8	1352.3	1342.0	1340.6	1340.6
5°	1457.5	1456.5	1458.4	1452.5	1444.3	1442.4	1433.8	1422.5	1410.6	1397.4	1394.6
7.5°	1551.2	1549.9	1546.2	1545.2	1538.9	1525.2	1511.3	1496.5	1476.8	1457.6	1448.0
10°	1598.6	1613.6	1604.5	1588.6	1591.8	1570.4	1559.0	1539.4	1523.0	1494.3	1488.0
12.5°	1645.2	1651.1	1648.2	1639.1	1635.0	1620.2	1604.9	1587.9	1557.6	1531.9	1509.5
15°	1645.0	1653.7	1655.9	1653.2	1655.5	1654.6	1646.4	1632.3	1605.9	1577.6	1553.1
17.5°	1523.6	1529.6	1544.5	1554.6	1567.4	1594.3	1607.6	1612.7	1608.8	1592.8	1575.5
20°	1387.4	1377.3	1419.2	1440.6	1458.8	1504.3	1543.5	1558.5	1582.6	1582.2	1577.6
22.5°	1194.4	1196.8	1236.4	1261.9	1315.0	1360.5	1405.2	1461.7	1508.3	1539.2	1557.3
25°	877.6	894.9	934.5	969.1	1028.2	1112.9	1189.8	1279.1	1363.2	1429.7	1493.0
27.5°	659.1	660.4	691.8	723.7	758.8	828.2	925.1	1031.6	1151.6	1250.7	1364.7
30°	564.5	561.7	574.9	594.5	624.5	678.2	751.0	855.8	975.4	1124.7	1257.7
32.5°	497.4	497.6	507.6	522.0	547.0	583.2	633.0	718.1	831.3	978.0	1133.8
35°	432.4	431.9	439.3	449.7	460.2	483.4	517.5	562.1	640.0	776.9	936.3
37.5°	385.8	387.8	391.4	397.9	409.5	422.4	442.9	472.9	528.2	609.3	743.2
40°	359.6	360.5	365.5	371.0	377.8	387.8	404.7	428.7	469.3	534.0	631.8
42.5°	335.6	336.4	340.0	345.1	350.4	360.5	374.4	395.3	428.1	478.6	559.3
45°	300.4	300.4	303.6	305.9	311.8	320.9	332.3	349.6	372.4	409.7	463.3
47.5°	267.4	267.5	269.7	273.6	277.3	284.4	295.6	309.7	326.3	355.2	401.0
50°	248.5	249.0	250.3	253.5	255.8	262.2	270.8	283.1	300.4	322.7	361.0
52.5°	233.3	232.9	234.7	236.0	237.6	242.2	248.6	259.5	274.9	294.4	326.0
55°	208.5	206.6	209.4	211.7	213.0	214.8	218.5	225.3	238.5	254.9	278.6
57.5°	177.5	176.8	178.7	180.8	185.1	190.0	193.1	197.4	204.3	216.1	239.5
60°	152.0	152.0	156.1	157.5	162.5	168.9	175.2	178.9	185.7	193.4	210.7
62.5°	129.5	129.8	131.7	133.1	135.9	143.7	152.7	160.7	167.1	174.5	186.0
65°	108.3	109.2	109.2	110.1	112.0	113.8	117.4	123.8	135.2	145.6	154.3
67.5°	91.9	92.2	92.5	93.4	93.9	95.9	97.3	100.1	102.8	112.7	123.4
70°	81.1	82.4	81.9	82.8	83.3	84.2	86.1	87.4	91.5	93.8	100.1
72.5°	70.8	71.8	71.7	72.3	73.5	73.7	75.1	76.5	79.1	81.1	84.4
75°	57.3	56.9	57.3	58.2	58.7	59.2	59.2	61.0	62.3	64.2	66.4
77.5°	44.2	44.7	44.6	44.7	44.8	45.6	45.5	46.4	47.7	48.6	49.7
80°	35.5	35.9	35.5	35.9	36.4	36.8	36.4	36.8	38.3	39.1	39.1
82.5°	27.5	27.6	27.8	27.9	28.0	28.1	28.8	28.9	29.9	29.7	30.1
85°	16.4	16.0	16.0	16.0	16.4	16.9	16.4	16.4	16.9	16.9	16.9
87.5°	11.9	12.2	12.1	12.1	12.1	12.1	12.2	12.7	12.3	12.8	11.6
90°	30.2	30.1	29.9	29.7	29.4	29.6	30.0	30.3	30.8	31.1	26.8
92.5°	28.8	28.8	28.7	28.7	28.7	28.6	28.5	28.4	28.4	28.3	27.3
95°	55.2	55.6	56.0	56.4	56.7	57.0	57.0	57.0	57.0	57.0	56.5
97.5°	95.6	95.6	95.7	95.7	95.8	95.8	95.8	95.8	95.8	95.8	95.0
100°	121.9	122.1	122.3	122.5	122.7	122.8	122.8	122.8	122.8	122.8	122.3
102.5°	151.9	152.0	152.2	152.4	152.6	152.7	152.5	152.3	152.1	152.0	151.2
105°	197.5	197.5	197.5	197.5	197.5	197.3	197.0	196.5	196.2	195.7	195.4
107.5°	240.6	241.6	242.5	243.3	244.2	244.6	244.5	244.3	244.2	244.0	244.0
110°	274.1	274.6	275.3	275.9	276.4	276.8	276.8	276.8	276.8	276.8	276.8



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.1	306.6	307.0	307.5	307.8	308.4	308.8	309.2	309.8	310.2	310.4
115°	356.0	356.5	357.1	357.8	358.3	358.7	358.9	359.1	359.4	359.5	359.9
117.5°	403.5	404.0	404.7	405.3	405.8	406.4	406.9	407.3	407.8	408.3	409.4
120°	436.9	437.6	438.1	438.7	439.3	439.6	439.6	439.6	439.6	439.6	441.2
122.5°	469.7	470.1	470.6	471.0	471.4	471.9	472.3	472.8	473.3	473.8	474.9
125°	519.7	519.9	520.0	520.3	520.5	520.8	521.5	522.1	522.6	523.3	523.9
127.5°	565.3	565.9	566.5	567.1	567.8	568.5	569.2	569.9	570.6	571.3	572.0
130°	598.0	598.8	599.6	600.4	601.2	601.7	602.2	602.5	603.0	603.3	603.8
132.5°	629.4	630.0	630.6	631.2	631.9	632.6	633.5	634.4	635.3	636.1	636.0
135°	678.1	678.7	679.3	679.8	680.5	680.8	681.1	681.3	681.4	681.6	681.3
137.5°	722.2	723.0	723.8	724.6	725.4	725.9	726.0	726.2	726.4	726.5	726.0
140°	752.9	753.7	754.4	755.2	756.0	756.4	756.4	756.4	756.4	756.4	755.5
142.5°	780.6	781.4	782.2	783.0	783.8	784.1	783.9	783.8	783.6	783.5	782.7
145°	822.2	823.0	823.9	824.7	825.5	825.7	825.5	825.3	825.1	824.9	823.8
147.5°	859.4	860.2	860.9	861.7	862.5	862.6	862.2	861.7	861.3	860.9	860.1
150°	883.7	884.2	884.8	885.5	886.0	886.0	885.5	884.8	884.2	883.7	882.9
152.5°	906.4	907.2	907.9	908.7	909.5	909.5	908.7	907.9	907.2	906.4	905.4
155°	937.0	937.6	938.3	938.8	939.4	939.2	938.3	937.3	936.3	935.2	934.7
157.5°	963.4	964.3	965.3	966.3	967.1	967.0	965.6	964.3	963.0	961.6	961.3
160°	979.7	980.5	981.3	982.1	982.9	982.8	981.5	980.3	979.2	977.9	977.8
162.5°	994.0	995.0	995.9	996.8	997.8	997.6	996.2	994.9	993.5	992.2	992.0
165°	1012.7	1013.7	1014.7	1015.7	1016.6	1016.5	1015.0	1013.7	1012.3	1010.9	1010.9
167.5°	1028.0	1029.0	1030.0	1031.1	1032.1	1031.9	1030.6	1029.1	1027.8	1026.4	1026.4
170°	1035.8	1037.0	1038.2	1039.4	1040.5	1040.4	1039.1	1037.7	1036.3	1034.9	1035.1
172.5°	1042.2	1043.4	1044.6	1045.8	1047.0	1046.9	1045.5	1044.1	1042.8	1041.3	1041.5
175°	1049.2	1050.3	1051.5	1052.8	1053.9	1053.8	1052.4	1051.1	1049.6	1048.3	1048.7
177.5°	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4	1052.7
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1341.3	1338.4	1335.9	1329.3	1326.1	1318.8	1317.7	1317.3	1307.8	1298.7	1296.2
5°	1387.4	1380.1	1369.1	1356.4	1343.2	1329.5	1320.4	1313.2	1294.9	1277.6	1267.7
7.5°	1433.8	1418.2	1399.3	1375.2	1355.0	1332.5	1315.7	1300.7	1274.9	1250.1	1233.4
10°	1468.4	1442.9	1417.9	1384.6	1358.7	1333.2	1309.6	1289.1	1259.9	1227.2	1203.9
12.5°	1489.9	1461.9	1427.4	1394.8	1361.3	1328.8	1297.2	1270.9	1236.6	1202.7	1175.2
15°	1518.9	1488.9	1447.0	1400.6	1357.4	1315.0	1278.6	1245.8	1201.2	1160.7	1127.0
17.5°	1542.7	1501.4	1456.3	1402.7	1352.6	1298.8	1251.9	1210.1	1160.4	1111.5	1071.8
20°	1550.3	1509.4	1457.5	1403.7	1344.6	1281.3	1230.8	1185.3	1132.0	1078.8	1033.2
22.5°	1545.6	1513.8	1456.0	1391.8	1331.1	1264.9	1207.8	1155.0	1096.0	1041.6	988.8
25°	1513.5	1502.5	1448.0	1377.8	1308.7	1231.7	1165.7	1107.9	1040.5	982.3	924.9
27.5°	1438.5	1462.1	1428.3	1353.6	1276.7	1194.2	1120.0	1054.2	984.3	918.7	861.6
30°	1366.5	1420.6	1406.0	1336.9	1250.8	1169.8	1086.5	1017.8	943.2	875.7	819.3
32.5°	1267.7	1357.3	1371.5	1313.6	1224.6	1135.6	1048.3	979.9	902.0	831.0	776.0
35°	1110.6	1244.5	1305.9	1269.0	1179.8	1083.8	993.6	914.0	835.7	765.6	711.0
37.5°	923.2	1105.5	1207.8	1210.5	1128.5	1028.7	930.6	851.5	771.3	702.5	643.5
40°	801.6	999.1	1132.5	1162.1	1092.9	985.0	885.7	805.2	726.9	659.5	591.7
42.5°	692.3	889.1	1053.1	1104.6	1049.5	942.4	842.8	758.6	682.5	618.8	549.5
45°	559.9	731.9	912.7	1004.6	974.1	874.9	769.7	689.6	618.1	563.0	496.6
47.5°	472.3	593.5	768.4	892.8	892.2	801.6	698.2	621.5	555.3	503.6	449.8
50°	422.4	528.0	675.9	817.1	828.8	752.9	654.5	578.5	516.7	462.4	419.2
52.5°	377.6	464.7	597.6	732.9	766.6	700.8	605.4	535.2	475.1	425.3	388.3
55°	319.1	386.5	487.5	614.0	665.0	618.6	534.0	468.4	419.6	377.8	345.9
57.5°	269.9	320.5	401.5	503.5	562.8	533.6	463.7	410.5	368.8	330.9	305.8
60°	239.0	280.4	349.1	434.3	499.8	479.3	419.6	370.1	334.6	301.8	278.1
62.5°	209.8	245.4	304.3	373.4	433.5	425.1	376.3	334.7	303.6	273.8	253.7
65°	168.9	194.8	240.8	295.0	343.2	347.3	312.3	284.0	256.3	232.6	214.8
67.5°	134.5	151.4	183.8	229.4	265.6	278.5	257.1	235.5	213.5	195.2	179.8
70°	113.3	127.0	150.7	187.5	220.8	234.4	222.1	205.3	186.2	171.1	157.9
72.5°	91.8	105.1	122.6	149.6	178.2	192.9	188.6	176.6	161.0	148.6	136.1
75°	69.2	73.3	85.2	103.3	125.6	138.4	141.6	135.2	122.9	113.3	106.0
77.5°	51.2	53.6	59.3	68.8	83.4	94.8	99.4	98.7	90.2	84.6	77.8
80°	40.9	42.4	45.0	49.1	60.1	71.4	74.6	74.6	68.8	66.4	59.7
82.5°	31.1	32.1	33.8	36.0	41.1	51.1	54.7	55.4	51.6	48.6	43.2
85°	17.7	17.3	18.2	19.5	20.5	23.2	28.7	29.6	28.7	25.1	23.6
87.5°	10.7	10.2	9.3	8.3	8.1	8.0	9.4	10.7	9.7	9.1	8.9
90°	22.5	18.1	13.7	10.3	8.0	5.6	3.3	0.9	3.3	5.6	8.0
92.5°	26.2	25.2	24.2	22.8	21.0	19.4	17.6	15.9	17.6	19.4	21.0
95°	56.2	55.7	55.4	54.2	52.2	50.2	48.2	46.3	48.2	50.2	52.2
97.5°	94.3	93.5	92.7	91.5	89.8	88.0	86.3	84.5	86.3	88.0	89.8
100°	121.6	121.0	120.5	119.3	117.8	116.2	114.6	113.0	114.6	116.2	117.8
102.5°	150.5	149.7	149.0	147.9	146.7	145.4	144.2	142.9	144.2	145.4	146.7
105°	195.0	194.6	194.2	193.7	193.1	192.5	191.9	191.4	191.9	192.5	193.1
107.5°	244.0	244.0	244.0	243.6	242.7	241.8	240.9	240.0	240.9	241.8	242.7
110°	276.8	276.8	276.8	276.2	275.0	273.8	272.6	271.4	272.6	273.8	275.0



TEST NUMBER: P331694-940
 CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	310.5	310.7	310.9	310.3	309.2	308.0	306.7	305.6	306.7	308.0	309.2
115°	360.3	360.7	361.1	360.7	359.5	358.3	357.1	356.0	357.1	358.3	359.5
117.5°	410.5	411.6	412.7	412.5	410.9	409.3	407.7	406.2	407.7	409.3	410.9
120°	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	441.2	442.7	444.3
122.5°	476.0	477.1	478.2	477.8	475.9	474.0	472.1	470.2	472.1	474.0	475.9
125°	524.4	525.0	525.7	525.0	523.3	521.5	519.7	517.9	519.7	521.5	523.3
127.5°	572.7	573.5	574.2	573.4	571.1	568.9	566.6	564.4	566.6	568.9	571.1
130°	604.1	604.5	604.9	603.9	601.3	598.7	596.1	593.5	596.1	598.7	601.3
132.5°	636.0	635.9	635.8	634.7	632.6	630.5	628.4	626.3	628.4	630.5	632.6
135°	680.8	680.5	680.1	678.8	676.6	674.4	672.3	670.1	672.3	674.4	676.6
137.5°	725.5	725.0	724.4	723.3	721.5	719.7	717.9	716.2	717.9	719.7	721.5
140°	754.4	753.4	752.4	751.1	749.3	747.5	745.7	744.0	745.7	747.5	749.3
142.5°	782.1	781.4	780.8	779.5	777.8	776.0	774.2	772.4	774.2	776.0	777.8
145°	822.5	821.4	820.2	818.9	817.5	816.1	814.8	813.3	814.8	816.1	817.5
147.5°	859.3	858.5	857.7	856.5	854.8	853.2	851.5	849.8	851.5	853.2	854.8
150°	882.1	881.3	880.5	879.5	878.3	877.1	875.9	874.8	875.9	877.1	878.3
152.5°	904.6	903.6	902.7	901.6	900.4	899.2	898.0	896.8	898.0	899.2	900.4
155°	934.1	933.5	932.9	932.3	931.7	931.1	930.5	930.0	930.5	931.1	931.7
157.5°	960.9	960.6	960.2	959.8	959.4	959.0	958.6	958.2	958.6	959.0	959.4
160°	977.6	977.4	977.2	976.9	976.5	976.1	975.7	975.4	975.7	976.1	976.5
162.5°	991.8	991.7	991.4	991.3	991.2	991.1	991.0	991.0	991.0	991.1	991.2
165°	1010.9	1010.9	1010.9	1011.0	1011.2	1011.4	1011.6	1011.8	1011.6	1011.4	1011.2
167.5°	1026.4	1026.5	1026.5	1026.9	1027.4	1028.1	1028.7	1029.2	1028.7	1028.1	1027.4
170°	1035.4	1035.5	1035.7	1036.1	1036.7	1037.3	1037.9	1038.5	1037.9	1037.3	1036.7
172.5°	1041.7	1042.0	1042.1	1042.5	1043.1	1043.7	1044.3	1044.9	1044.3	1043.7	1043.1
175°	1049.1	1049.5	1049.9	1050.3	1051.0	1051.5	1052.1	1052.8	1052.1	1051.5	1051.0
177.5°	1053.0	1053.3	1053.6	1054.0	1054.5	1055.0	1055.4	1056.0	1055.4	1055.0	1054.5
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331694-940
 CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1291.5	1288.9	1284.2	1276.8	1272.5	1264.8	1259.7	1262.7	1263.4	1262.7	1261.9
5°	1256.8	1247.1	1233.9	1221.2	1209.4	1196.7	1189.4	1186.2	1179.8	1176.2	1174.4
7.5°	1214.8	1198.3	1179.6	1157.4	1138.5	1118.8	1108.8	1103.7	1090.7	1083.6	1077.4
10°	1183.5	1157.5	1138.9	1109.7	1092.0	1066.0	1048.3	1048.7	1031.0	1020.9	1013.7
12.5°	1148.9	1120.3	1089.3	1063.1	1038.4	1017.6	996.2	987.6	968.7	959.0	939.4
15°	1091.5	1058.3	1025.6	990.0	965.0	932.6	901.7	863.9	833.4	807.0	799.8
17.5°	1028.9	987.7	954.8	913.2	870.3	815.9	780.1	758.1	739.8	725.9	715.4
20°	985.9	944.1	909.0	846.1	788.4	751.5	725.1	708.3	689.1	674.1	665.9
22.5°	940.8	897.1	849.3	779.2	734.1	704.5	681.0	661.6	648.7	636.9	629.5
25°	876.6	828.8	750.1	701.9	665.5	634.5	618.1	606.3	592.6	576.7	569.4
27.5°	809.0	732.9	676.4	640.5	605.7	585.6	570.9	553.2	541.0	533.9	526.3
30°	758.3	682.3	638.2	599.1	574.4	552.1	534.8	524.9	513.0	500.7	495.7
32.5°	701.9	641.1	598.9	566.2	541.3	522.3	508.6	492.4	483.8	476.3	465.8
35°	631.8	585.9	547.2	520.8	497.0	481.6	465.7	456.1	440.6	434.3	430.2
37.5°	572.4	532.5	503.7	475.8	457.1	440.0	430.3	415.0	408.3	399.5	390.8
40°	539.0	499.8	472.0	449.2	428.3	415.5	403.3	391.0	380.9	376.9	366.4
42.5°	504.7	472.9	445.1	420.1	406.1	392.6	377.1	368.1	357.7	351.1	344.6
45°	457.4	429.3	405.6	385.0	369.6	355.5	345.4	330.5	324.6	311.3	305.9
47.5°	416.0	389.7	367.1	347.7	332.5	323.3	308.7	296.9	287.5	279.4	272.4
50°	386.5	364.6	342.8	325.5	311.8	298.6	283.6	277.7	263.1	259.0	254.9
52.5°	359.5	338.8	318.7	301.8	288.1	275.3	262.1	254.3	244.5	240.4	237.5
55°	321.8	301.8	282.7	267.6	254.0	240.8	232.6	223.0	218.5	215.3	211.7
57.5°	283.9	265.9	251.3	236.0	222.3	211.9	202.3	196.6	191.9	187.7	183.3
60°	259.9	242.6	229.4	215.3	201.2	192.5	185.3	178.4	173.0	166.6	164.8
62.5°	234.4	219.3	207.2	193.4	181.2	173.3	166.3	159.9	153.3	144.0	141.4
65°	199.4	187.5	174.8	163.5	152.5	144.7	134.7	127.4	124.8	123.8	123.3
67.5°	167.7	156.5	145.5	133.9	123.9	116.8	111.7	110.6	108.7	108.2	106.9
70°	146.6	136.1	125.2	114.2	104.7	103.3	101.5	99.7	97.4	96.5	95.6
72.5°	127.6	116.8	105.8	97.1	93.0	91.3	89.5	87.7	86.1	85.2	84.6
75°	97.8	87.8	80.6	77.4	75.1	73.7	71.0	69.6	68.8	67.3	66.9
77.5°	70.4	64.8	61.4	59.5	57.1	55.6	54.0	52.7	51.7	51.5	50.7
80°	53.7	51.0	48.7	46.0	45.0	43.2	42.8	41.5	41.9	40.5	40.5
82.5°	41.7	38.3	36.3	35.0	34.2	32.7	32.2	31.6	31.7	30.7	30.7
85°	21.4	20.5	19.5	18.6	18.6	17.3	17.7	17.3	17.3	16.4	16.0
87.5°	9.0	9.3	9.5	10.3	11.1	11.7	11.6	11.1	11.1	11.0	10.6
90°	10.3	13.7	18.1	22.5	26.8	31.1	30.8	30.3	30.0	29.6	29.4
92.5°	22.8	24.2	25.2	26.2	27.3	28.3	28.4	28.4	28.5	28.6	28.7
95°	54.2	55.4	55.7	56.2	56.5	57.0	57.0	57.0	57.0	57.0	56.7
97.5°	91.5	92.7	93.5	94.3	95.0	95.8	95.8	95.8	95.8	95.8	95.8
100°	119.3	120.5	121.0	121.6	122.3	122.8	122.8	122.8	122.8	122.8	122.7
102.5°	147.9	149.0	149.7	150.5	151.2	152.0	152.1	152.3	152.5	152.7	152.6
105°	193.7	194.2	194.6	195.0	195.4	195.7	196.2	196.5	197.0	197.3	197.5
107.5°	243.6	244.0	244.0	244.0	244.0	244.0	244.2	244.3	244.5	244.6	244.2
110°	276.2	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.4



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	310.3	310.9	310.7	310.5	310.4	310.2	309.8	309.2	308.8	308.4	307.8
115°	360.7	361.1	360.7	360.3	359.9	359.5	359.4	359.1	358.9	358.7	358.3
117.5°	412.5	412.7	411.6	410.5	409.4	408.3	407.8	407.3	406.9	406.4	405.8
120°	445.9	445.9	444.3	442.7	441.2	439.6	439.6	439.6	439.6	439.6	439.3
122.5°	477.8	478.2	477.1	476.0	474.9	473.8	473.3	472.8	472.3	471.9	471.4
125°	525.0	525.7	525.0	524.4	523.9	523.3	522.6	522.1	521.5	520.8	520.5
127.5°	573.4	574.2	573.5	572.7	572.0	571.3	570.6	569.9	569.2	568.5	567.8
130°	603.9	604.9	604.5	604.1	603.8	603.3	603.0	602.5	602.2	601.7	601.2
132.5°	634.7	635.8	635.9	636.0	636.0	636.1	635.3	634.4	633.5	632.6	631.9
135°	678.8	680.1	680.5	680.8	681.3	681.6	681.4	681.3	681.1	680.8	680.5
137.5°	723.3	724.4	725.0	725.5	726.0	726.5	726.4	726.2	726.0	725.9	725.4
140°	751.1	752.4	753.4	754.4	755.5	756.4	756.4	756.4	756.4	756.4	756.0
142.5°	779.5	780.8	781.4	782.1	782.7	783.5	783.6	783.8	783.9	784.1	783.8
145°	818.9	820.2	821.4	822.5	823.8	824.9	825.1	825.3	825.5	825.7	825.5
147.5°	856.5	857.7	858.5	859.3	860.1	860.9	861.3	861.7	862.2	862.6	862.5
150°	879.5	880.5	881.3	882.1	882.9	883.7	884.2	884.8	885.5	886.0	886.0
152.5°	901.6	902.7	903.6	904.6	905.4	906.4	907.2	907.9	908.7	909.5	909.5
155°	932.3	932.9	933.5	934.1	934.7	935.2	936.3	937.3	938.3	939.2	939.4
157.5°	959.8	960.2	960.6	960.9	961.3	961.6	963.0	964.3	965.6	967.0	967.1
160°	976.9	977.2	977.4	977.6	977.8	977.9	979.2	980.3	981.5	982.8	982.9
162.5°	991.3	991.4	991.7	991.8	992.0	992.2	993.5	994.9	996.2	997.6	997.8
165°	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3	1013.7	1015.0	1016.5	1016.6
167.5°	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8	1029.1	1030.6	1031.9	1032.1
170°	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3	1037.7	1039.1	1040.4	1040.5
172.5°	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8	1044.1	1045.5	1046.9	1047.0
175°	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6	1051.1	1052.4	1053.8	1053.9
177.5°	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1257.9	1258.6	1257.6	1258.3	1257.6	1258.6	1257.9	1261.9	1262.7	1263.4	1262.7
5°	1172.1	1166.6	1165.7	1164.3	1165.7	1166.6	1172.1	1174.4	1176.2	1179.8	1186.2
7.5°	1069.6	1068.7	1066.5	1063.3	1066.5	1068.7	1069.6	1077.4	1083.6	1090.7	1103.7
10°	1003.6	1001.4	1000.9	997.7	1000.9	1001.4	1003.6	1013.7	1020.9	1031.0	1048.7
12.5°	926.5	911.8	910.3	902.3	910.3	911.8	926.5	939.4	959.0	968.7	987.6
15°	788.8	786.1	776.9	771.1	776.9	786.1	788.8	799.8	807.0	833.4	863.9
17.5°	710.2	701.2	698.4	697.1	698.4	701.2	710.2	715.4	725.9	739.8	758.1
20°	659.5	651.4	650.0	649.1	650.0	651.4	659.5	665.9	674.1	689.1	708.3
22.5°	624.6	616.0	612.5	609.8	612.5	616.0	624.6	629.5	636.9	648.7	661.6
25°	564.9	561.7	559.9	558.9	559.9	561.7	564.9	569.4	576.7	592.6	606.3
27.5°	518.2	511.1	509.8	507.5	509.8	511.1	518.2	526.3	533.9	541.0	553.2
30°	491.6	489.3	486.2	483.4	486.2	489.3	491.6	495.7	500.7	513.0	524.9
32.5°	460.3	458.3	455.6	454.2	455.6	458.3	460.3	465.8	476.3	483.8	492.4
35°	425.6	419.2	416.5	412.4	416.5	419.2	425.6	430.2	434.3	440.6	456.1
37.5°	388.9	385.6	381.7	383.1	381.7	385.6	388.9	390.8	399.5	408.3	415.0
40°	360.5	358.2	357.3	356.9	357.3	358.2	360.5	366.4	376.9	380.9	391.0
42.5°	338.0	331.6	329.3	329.2	329.3	331.6	338.0	344.6	351.1	357.7	368.1
45°	303.6	297.7	293.6	294.1	293.6	297.7	303.6	305.9	311.3	324.6	330.5
47.5°	268.5	268.3	265.7	266.5	265.7	268.3	268.5	272.4	279.4	287.5	296.9
50°	251.7	249.0	247.2	247.6	247.2	249.0	251.7	254.9	259.0	263.1	277.7
52.5°	235.7	233.4	231.8	233.8	231.8	233.4	235.7	237.5	240.4	244.5	254.3
55°	209.4	206.6	206.2	205.7	206.2	206.6	209.4	211.7	215.3	218.5	223.0
57.5°	179.9	178.2	175.4	174.2	175.4	178.2	179.9	183.3	187.7	191.9	196.6
60°	158.8	155.2	150.7	150.2	150.7	155.2	158.8	164.8	166.6	173.0	178.4
62.5°	139.6	138.8	137.9	137.9	137.9	138.8	139.6	141.4	144.0	153.3	159.9
65°	122.4	122.0	122.4	122.9	122.4	122.0	122.4	123.3	123.8	124.8	127.4
67.5°	106.7	105.8	105.0	105.4	105.0	105.8	106.7	106.9	108.2	108.7	110.6
70°	94.7	94.3	93.8	93.8	93.8	94.3	94.7	95.6	96.5	97.4	99.7
72.5°	83.0	82.9	82.5	82.1	82.5	82.9	83.0	84.6	85.2	86.1	87.7
75°	66.4	65.5	65.5	65.5	65.5	65.5	66.4	66.9	67.3	68.8	69.6
77.5°	50.6	50.2	49.7	49.3	49.7	50.2	50.6	50.7	51.5	51.7	52.7
80°	40.0	39.6	39.1	39.1	39.1	39.6	40.0	40.5	40.5	41.9	41.5
82.5°	30.6	30.1	30.1	29.7	30.1	30.1	30.6	30.7	30.7	31.7	31.6
85°	16.4	16.9	16.4	17.3	16.4	16.9	16.4	16.0	16.4	17.3	17.3
87.5°	10.7	10.3	10.8	10.4	10.8	10.3	10.7	10.6	11.0	11.1	11.1
90°	29.7	29.9	30.1	30.2	30.1	29.9	29.7	29.4	29.6	30.0	30.3
92.5°	28.7	28.7	28.8	28.8	28.8	28.7	28.7	28.7	28.6	28.5	28.4
95°	56.4	56.0	55.6	55.2	55.6	56.0	56.4	56.7	57.0	57.0	57.0
97.5°	95.7	95.7	95.6	95.6	95.6	95.7	95.7	95.8	95.8	95.8	95.8
100°	122.5	122.3	122.1	121.9	122.1	122.3	122.5	122.7	122.8	122.8	122.8
102.5°	152.4	152.2	152.0	151.9	152.0	152.2	152.4	152.6	152.7	152.5	152.3
105°	197.5	197.5	197.5	197.5	197.5	197.5	197.5	197.5	197.3	197.0	196.5
107.5°	243.3	242.5	241.6	240.6	241.6	242.5	243.3	244.2	244.6	244.5	244.3
110°	275.9	275.3	274.6	274.1	274.6	275.3	275.9	276.4	276.8	276.8	276.8



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	307.5	307.0	306.6	306.1	306.6	307.0	307.5	307.8	308.4	308.8	309.2
115°	357.8	357.1	356.5	356.0	356.5	357.1	357.8	358.3	358.7	358.9	359.1
117.5°	405.3	404.7	404.0	403.5	404.0	404.7	405.3	405.8	406.4	406.9	407.3
120°	438.7	438.1	437.6	436.9	437.6	438.1	438.7	439.3	439.6	439.6	439.6
122.5°	471.0	470.6	470.1	469.7	470.1	470.6	471.0	471.4	471.9	472.3	472.8
125°	520.3	520.0	519.9	519.7	519.9	520.0	520.3	520.5	520.8	521.5	522.1
127.5°	567.1	566.5	565.9	565.3	565.9	566.5	567.1	567.8	568.5	569.2	569.9
130°	600.4	599.6	598.8	598.0	598.8	599.6	600.4	601.2	601.7	602.2	602.5
132.5°	631.2	630.6	630.0	629.4	630.0	630.6	631.2	631.9	632.6	633.5	634.4
135°	679.8	679.3	678.7	678.1	678.7	679.3	679.8	680.5	680.8	681.1	681.3
137.5°	724.6	723.8	723.0	722.2	723.0	723.8	724.6	725.4	725.9	726.0	726.2
140°	755.2	754.4	753.7	752.9	753.7	754.4	755.2	756.0	756.4	756.4	756.4
142.5°	783.0	782.2	781.4	780.6	781.4	782.2	783.0	783.8	784.1	783.9	783.8
145°	824.7	823.9	823.0	822.2	823.0	823.9	824.7	825.5	825.7	825.5	825.3
147.5°	861.7	860.9	860.2	859.4	860.2	860.9	861.7	862.5	862.6	862.2	861.7
150°	885.5	884.8	884.2	883.7	884.2	884.8	885.5	886.0	886.0	885.5	884.8
152.5°	908.7	907.9	907.2	906.4	907.2	907.9	908.7	909.5	909.5	908.7	907.9
155°	938.8	938.3	937.6	937.0	937.6	938.3	938.8	939.4	939.2	938.3	937.3
157.5°	966.3	965.3	964.3	963.4	964.3	965.3	966.3	967.1	967.0	965.6	964.3
160°	982.1	981.3	980.5	979.7	980.5	981.3	982.1	982.9	982.8	981.5	980.3
162.5°	996.8	995.9	995.0	994.0	995.0	995.9	996.8	997.8	997.6	996.2	994.9
165°	1015.7	1014.7	1013.7	1012.7	1013.7	1014.7	1015.7	1016.6	1016.5	1015.0	1013.7
167.5°	1031.1	1030.0	1029.0	1028.0	1029.0	1030.0	1031.1	1032.1	1031.9	1030.6	1029.1
170°	1039.4	1038.2	1037.0	1035.8	1037.0	1038.2	1039.4	1040.5	1040.4	1039.1	1037.7
172.5°	1045.8	1044.6	1043.4	1042.2	1043.4	1044.6	1045.8	1047.0	1046.9	1045.5	1044.1
175°	1052.8	1051.5	1050.3	1049.2	1050.3	1051.5	1052.8	1053.9	1053.8	1052.4	1051.1
177.5°	1055.3	1054.3	1053.3	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1259.7	1264.8	1272.5	1276.8	1284.2	1288.9	1291.5	1296.2	1298.7	1307.8	1317.3
5°	1189.4	1196.7	1209.4	1221.2	1233.9	1247.1	1256.8	1267.7	1277.6	1294.9	1313.2
7.5°	1108.8	1118.8	1138.5	1157.4	1179.6	1198.3	1214.8	1233.4	1250.1	1274.9	1300.7
10°	1048.3	1066.0	1092.0	1109.7	1138.9	1157.5	1183.5	1203.9	1227.2	1259.9	1289.1
12.5°	996.2	1017.6	1038.4	1063.1	1089.3	1120.3	1148.9	1175.2	1202.7	1236.6	1270.9
15°	901.7	932.6	965.0	990.0	1025.6	1058.3	1091.5	1127.0	1160.7	1201.2	1245.8
17.5°	780.1	815.9	870.3	913.2	954.8	987.7	1028.9	1071.8	1111.5	1160.4	1210.1
20°	725.1	751.5	788.4	846.1	909.0	944.1	985.9	1033.2	1078.8	1132.0	1185.3
22.5°	681.0	704.5	734.1	779.2	849.3	897.1	940.8	988.8	1041.6	1096.0	1155.0
25°	618.1	634.5	665.5	701.9	750.1	828.8	876.6	924.9	982.3	1040.5	1107.9
27.5°	570.9	585.6	605.7	640.5	676.4	732.9	809.0	861.6	918.7	984.3	1054.2
30°	534.8	552.1	574.4	599.1	638.2	682.3	758.3	819.3	875.7	943.2	1017.8
32.5°	508.6	522.3	541.3	566.2	598.9	641.1	701.9	776.0	831.0	902.0	979.9
35°	465.7	481.6	497.0	520.8	547.2	585.9	631.8	711.0	765.6	835.7	914.0
37.5°	430.3	440.0	457.1	475.8	503.7	532.5	572.4	643.5	702.5	771.3	851.5
40°	403.3	415.5	428.3	449.2	472.0	499.8	539.0	591.7	659.5	726.9	805.2
42.5°	377.1	392.6	406.1	420.1	445.1	472.9	504.7	549.5	618.8	682.5	758.6
45°	345.4	355.5	369.6	385.0	405.6	429.3	457.4	496.6	563.0	618.1	689.6
47.5°	308.7	323.3	332.5	347.7	367.1	389.7	416.0	449.8	503.6	555.3	621.5
50°	283.6	298.6	311.8	325.5	342.8	364.6	386.5	419.2	462.4	516.7	578.5
52.5°	262.1	275.3	288.1	301.8	318.7	338.8	359.5	388.3	425.3	475.1	535.2
55°	232.6	240.8	254.0	267.6	282.7	301.8	321.8	345.9	377.8	419.6	468.4
57.5°	202.3	211.9	222.3	236.0	251.3	265.9	283.9	305.8	330.9	368.8	410.5
60°	185.3	192.5	201.2	215.3	229.4	242.6	259.9	278.1	301.8	334.6	370.1
62.5°	166.3	173.3	181.2	193.4	207.2	219.3	234.4	253.7	273.8	303.6	334.7
65°	134.7	144.7	152.5	163.5	174.8	187.5	199.4	214.8	232.6	256.3	284.0
67.5°	111.7	116.8	123.9	133.9	145.5	156.5	167.7	179.8	195.2	213.5	235.5
70°	101.5	103.3	104.7	114.2	125.2	136.1	146.6	157.9	171.1	186.2	205.3
72.5°	89.5	91.3	93.0	97.1	105.8	116.8	127.6	136.1	148.6	161.0	176.6
75°	71.0	73.7	75.1	77.4	80.6	87.8	97.8	106.0	113.3	122.9	135.2
77.5°	54.0	55.6	57.1	59.5	61.4	64.8	70.4	77.8	84.6	90.2	98.7
80°	42.8	43.2	45.0	46.0	48.7	51.0	53.7	59.7	66.4	68.8	74.6
82.5°	32.2	32.7	34.2	35.0	36.3	38.3	41.7	43.2	48.6	51.6	55.4
85°	17.7	17.3	18.6	18.6	19.5	20.5	21.4	23.6	25.1	28.7	29.6
87.5°	11.6	11.7	11.1	10.3	9.5	9.3	9.0	8.9	9.1	9.7	10.7
90°	30.8	31.1	26.8	22.5	18.1	13.7	10.3	8.0	5.6	3.3	0.9
92.5°	28.4	28.3	27.3	26.2	25.2	24.2	22.8	21.0	19.4	17.6	15.9
95°	57.0	57.0	56.5	56.2	55.7	55.4	54.2	52.2	50.2	48.2	46.3
97.5°	95.8	95.8	95.0	94.3	93.5	92.7	91.5	89.8	88.0	86.3	84.5
100°	122.8	122.8	122.3	121.6	121.0	120.5	119.3	117.8	116.2	114.6	113.0
102.5°	152.1	152.0	151.2	150.5	149.7	149.0	147.9	146.7	145.4	144.2	142.9
105°	196.2	195.7	195.4	195.0	194.6	194.2	193.7	193.1	192.5	191.9	191.4
107.5°	244.2	244.0	244.0	244.0	244.0	244.0	243.6	242.7	241.8	240.9	240.0
110°	276.8	276.8	276.8	276.8	276.8	276.8	276.2	275.0	273.8	272.6	271.4



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	309.8	310.2	310.4	310.5	310.7	310.9	310.3	309.2	308.0	306.7	305.6
115°	359.4	359.5	359.9	360.3	360.7	361.1	360.7	359.5	358.3	357.1	356.0
117.5°	407.8	408.3	409.4	410.5	411.6	412.7	412.5	410.9	409.3	407.7	406.2
120°	439.6	439.6	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6
122.5°	473.3	473.8	474.9	476.0	477.1	478.2	477.8	475.9	474.0	472.1	470.2
125°	522.6	523.3	523.9	524.4	525.0	525.7	525.0	523.3	521.5	519.7	517.9
127.5°	570.6	571.3	572.0	572.7	573.5	574.2	573.4	571.1	568.9	566.6	564.4
130°	603.0	603.3	603.8	604.1	604.5	604.9	603.9	601.3	598.7	596.1	593.5
132.5°	635.3	636.1	636.0	636.0	635.9	635.8	634.7	632.6	630.5	628.4	626.3
135°	681.4	681.6	681.3	680.8	680.5	680.1	678.8	676.6	674.4	672.3	670.1
137.5°	726.4	726.5	726.0	725.5	725.0	724.4	723.3	721.5	719.7	717.9	716.2
140°	756.4	756.4	755.5	754.4	753.4	752.4	751.1	749.3	747.5	745.7	744.0
142.5°	783.6	783.5	782.7	782.1	781.4	780.8	779.5	777.8	776.0	774.2	772.4
145°	825.1	824.9	823.8	822.5	821.4	820.2	818.9	817.5	816.1	814.8	813.3
147.5°	861.3	860.9	860.1	859.3	858.5	857.7	856.5	854.8	853.2	851.5	849.8
150°	884.2	883.7	882.9	882.1	881.3	880.5	879.5	878.3	877.1	875.9	874.8
152.5°	907.2	906.4	905.4	904.6	903.6	902.7	901.6	900.4	899.2	898.0	896.8
155°	936.3	935.2	934.7	934.1	933.5	932.9	932.3	931.7	931.1	930.5	930.0
157.5°	963.0	961.6	961.3	960.9	960.6	960.2	959.8	959.4	959.0	958.6	958.2
160°	979.2	977.9	977.8	977.6	977.4	977.2	976.9	976.5	976.1	975.7	975.4
162.5°	993.5	992.2	992.0	991.8	991.7	991.4	991.3	991.2	991.1	991.0	991.0
165°	1012.3	1010.9	1010.9	1010.9	1010.9	1010.9	1011.0	1011.2	1011.4	1011.6	1011.8
167.5°	1027.8	1026.4	1026.4	1026.4	1026.5	1026.5	1026.9	1027.4	1028.1	1028.7	1029.2
170°	1036.3	1034.9	1035.1	1035.4	1035.5	1035.7	1036.1	1036.7	1037.3	1037.9	1038.5
172.5°	1042.8	1041.3	1041.5	1041.7	1042.0	1042.1	1042.5	1043.1	1043.7	1044.3	1044.9
175°	1049.6	1048.3	1048.7	1049.1	1049.5	1049.9	1050.3	1051.0	1051.5	1052.1	1052.8
177.5°	1053.3	1052.4	1052.7	1053.0	1053.3	1053.6	1054.0	1054.5	1055.0	1055.4	1056.0
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1317.7	1318.8	1326.1	1329.3	1335.9	1338.4	1341.3	1340.6	1340.6	1342.0	1352.3
5°	1320.4	1329.5	1343.2	1356.4	1369.1	1380.1	1387.4	1394.6	1397.4	1410.6	1422.5
7.5°	1315.7	1332.5	1355.0	1375.2	1399.3	1418.2	1433.8	1448.0	1457.6	1476.8	1496.5
10°	1309.6	1333.2	1358.7	1384.6	1417.9	1442.9	1468.4	1488.0	1494.3	1523.0	1539.4
12.5°	1297.2	1328.8	1361.3	1394.8	1427.4	1461.9	1489.9	1509.5	1531.9	1557.6	1587.9
15°	1278.6	1315.0	1357.4	1400.6	1447.0	1488.9	1518.9	1553.1	1577.6	1605.9	1632.3
17.5°	1251.9	1298.8	1352.6	1402.7	1456.3	1501.4	1542.7	1575.5	1592.8	1608.8	1612.7
20°	1230.8	1281.3	1344.6	1403.7	1457.5	1509.4	1550.3	1577.6	1582.2	1582.6	1558.5
22.5°	1207.8	1264.9	1331.1	1391.8	1456.0	1513.8	1545.6	1557.3	1539.2	1508.3	1461.7
25°	1165.7	1231.7	1308.7	1377.8	1448.0	1502.5	1513.5	1493.0	1429.7	1363.2	1279.1
27.5°	1120.0	1194.2	1276.7	1353.6	1428.3	1462.1	1438.5	1364.7	1250.7	1151.6	1031.6
30°	1086.5	1169.8	1250.8	1336.9	1406.0	1420.6	1366.5	1257.7	1124.7	975.4	855.8
32.5°	1048.3	1135.6	1224.6	1313.6	1371.5	1357.3	1267.7	1133.8	978.0	831.3	718.1
35°	993.6	1083.8	1179.8	1269.0	1305.9	1244.5	1110.6	936.3	776.9	640.0	562.1
37.5°	930.6	1028.7	1128.5	1210.5	1207.8	1105.5	923.2	743.2	609.3	528.2	472.9
40°	885.7	985.0	1092.9	1162.1	1132.5	999.1	801.6	631.8	534.0	469.3	428.7
42.5°	842.8	942.4	1049.5	1104.6	1053.1	889.1	692.3	559.3	478.6	428.1	395.3
45°	769.7	874.9	974.1	1004.6	912.7	731.9	559.9	463.3	409.7	372.4	349.6
47.5°	698.2	801.6	892.2	892.8	768.4	593.5	472.3	401.0	355.2	326.3	309.7
50°	654.5	752.9	828.8	817.1	675.9	528.0	422.4	361.0	322.7	300.4	283.1
52.5°	605.4	700.8	766.6	732.9	597.6	464.7	377.6	326.0	294.4	274.9	259.5
55°	534.0	618.6	665.0	614.0	487.5	386.5	319.1	278.6	254.9	238.5	225.3
57.5°	463.7	533.6	562.8	503.5	401.5	320.5	269.9	239.5	216.1	204.3	197.4
60°	419.6	479.3	499.8	434.3	349.1	280.4	239.0	210.7	193.4	185.7	178.9
62.5°	376.3	425.1	433.5	373.4	304.3	245.4	209.8	186.0	174.5	167.1	160.7
65°	312.3	347.3	343.2	295.0	240.8	194.8	168.9	154.3	145.6	135.2	123.8
67.5°	257.1	278.5	265.6	229.4	183.8	151.4	134.5	123.4	112.7	102.8	100.1
70°	222.1	234.4	220.8	187.5	150.7	127.0	113.3	100.1	93.8	91.5	87.4
72.5°	188.6	192.9	178.2	149.6	122.6	105.1	91.8	84.4	81.1	79.1	76.5
75°	141.6	138.4	125.6	103.3	85.2	73.3	69.2	66.4	64.2	62.3	61.0
77.5°	99.4	94.8	83.4	68.8	59.3	53.6	51.2	49.7	48.6	47.7	46.4
80°	74.6	71.4	60.1	49.1	45.0	42.4	40.9	39.1	39.1	38.3	36.8
82.5°	54.7	51.1	41.1	36.0	33.8	32.1	31.1	30.1	29.7	29.9	28.9
85°	28.7	23.2	20.5	19.5	18.2	17.3	17.7	16.9	16.9	16.9	16.4
87.5°	9.4	8.0	8.1	8.3	9.3	10.2	10.7	11.6	12.8	12.3	12.7
90°	3.3	5.6	8.0	10.3	13.7	18.1	22.5	26.8	31.1	30.8	30.3
92.5°	17.6	19.4	21.0	22.8	24.2	25.2	26.2	27.3	28.3	28.4	28.4
95°	48.2	50.2	52.2	54.2	55.4	55.7	56.2	56.5	57.0	57.0	57.0
97.5°	86.3	88.0	89.8	91.5	92.7	93.5	94.3	95.0	95.8	95.8	95.8
100°	114.6	116.2	117.8	119.3	120.5	121.0	121.6	122.3	122.8	122.8	122.8
102.5°	144.2	145.4	146.7	147.9	149.0	149.7	150.5	151.2	152.0	152.1	152.3
105°	191.9	192.5	193.1	193.7	194.2	194.6	195.0	195.4	195.7	196.2	196.5
107.5°	240.9	241.8	242.7	243.6	244.0	244.0	244.0	244.0	244.0	244.2	244.3
110°	272.6	273.8	275.0	276.2	276.8	276.8	276.8	276.8	276.8	276.8	276.8



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	306.7	308.0	309.2	310.3	310.9	310.7	310.5	310.4	310.2	309.8	309.2
115°	357.1	358.3	359.5	360.7	361.1	360.7	360.3	359.9	359.5	359.4	359.1
117.5°	407.7	409.3	410.9	412.5	412.7	411.6	410.5	409.4	408.3	407.8	407.3
120°	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	439.6	439.6
122.5°	472.1	474.0	475.9	477.8	478.2	477.1	476.0	474.9	473.8	473.3	472.8
125°	519.7	521.5	523.3	525.0	525.7	525.0	524.4	523.9	523.3	522.6	522.1
127.5°	566.6	568.9	571.1	573.4	574.2	573.5	572.7	572.0	571.3	570.6	569.9
130°	596.1	598.7	601.3	603.9	604.9	604.5	604.1	603.8	603.3	603.0	602.5
132.5°	628.4	630.5	632.6	634.7	635.8	635.9	636.0	636.0	636.1	635.3	634.4
135°	672.3	674.4	676.6	678.8	680.1	680.5	680.8	681.3	681.6	681.4	681.3
137.5°	717.9	719.7	721.5	723.3	724.4	725.0	725.5	726.0	726.5	726.4	726.2
140°	745.7	747.5	749.3	751.1	752.4	753.4	754.4	755.5	756.4	756.4	756.4
142.5°	774.2	776.0	777.8	779.5	780.8	781.4	782.1	782.7	783.5	783.6	783.8
145°	814.8	816.1	817.5	818.9	820.2	821.4	822.5	823.8	824.9	825.1	825.3
147.5°	851.5	853.2	854.8	856.5	857.7	858.5	859.3	860.1	860.9	861.3	861.7
150°	875.9	877.1	878.3	879.5	880.5	881.3	882.1	882.9	883.7	884.2	884.8
152.5°	898.0	899.2	900.4	901.6	902.7	903.6	904.6	905.4	906.4	907.2	907.9
155°	930.5	931.1	931.7	932.3	932.9	933.5	934.1	934.7	935.2	936.3	937.3
157.5°	958.6	959.0	959.4	959.8	960.2	960.6	960.9	961.3	961.6	963.0	964.3
160°	975.7	976.1	976.5	976.9	977.2	977.4	977.6	977.8	977.9	979.2	980.3
162.5°	991.0	991.1	991.2	991.3	991.4	991.7	991.8	992.0	992.2	993.5	994.9
165°	1011.6	1011.4	1011.2	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3	1013.7
167.5°	1028.7	1028.1	1027.4	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8	1029.1
170°	1037.9	1037.3	1036.7	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3	1037.7
172.5°	1044.3	1043.7	1043.1	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8	1044.1
175°	1052.1	1051.5	1051.0	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6	1051.1
177.5°	1055.4	1055.0	1054.5	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3	1054.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1355.8	1360.6	1362.8	1362.8	1365.4	1364.2	1363.2
5°	1433.8	1442.4	1444.3	1452.5	1458.4	1456.5	1457.5
7.5°	1511.3	1525.2	1538.9	1545.2	1546.2	1549.9	1551.2
10°	1559.0	1570.4	1591.8	1588.6	1604.5	1613.6	1598.6
12.5°	1604.9	1620.2	1635.0	1639.1	1648.2	1651.1	1645.2
15°	1646.4	1654.6	1655.5	1653.2	1655.9	1653.7	1645.0
17.5°	1607.6	1594.3	1567.4	1554.6	1544.5	1529.6	1523.6
20°	1543.5	1504.3	1458.8	1440.6	1419.2	1377.3	1387.4
22.5°	1405.2	1360.5	1315.0	1261.9	1236.4	1196.8	1194.4
25°	1189.8	1112.9	1028.2	969.1	934.5	894.9	877.6
27.5°	925.1	828.2	758.8	723.7	691.8	660.4	659.1
30°	751.0	678.2	624.5	594.5	574.9	561.7	564.5
32.5°	633.0	583.2	547.0	522.0	507.6	497.6	497.4
35°	517.5	483.4	460.2	449.7	439.3	431.9	432.4
37.5°	442.9	422.4	409.5	397.9	391.4	387.8	385.8
40°	404.7	387.8	377.8	371.0	365.5	360.5	359.6
42.5°	374.4	360.5	350.4	345.1	340.0	336.4	335.6
45°	332.3	320.9	311.8	305.9	303.6	300.4	300.4
47.5°	295.6	284.4	277.3	273.6	269.7	267.5	267.4
50°	270.8	262.2	255.8	253.5	250.3	249.0	248.5
52.5°	248.6	242.2	237.6	236.0	234.7	232.9	233.3
55°	218.5	214.8	213.0	211.7	209.4	206.6	208.5
57.5°	193.1	190.0	185.1	180.8	178.7	176.8	177.5
60°	175.2	168.9	162.5	157.5	156.1	152.0	152.0
62.5°	152.7	143.7	135.9	133.1	131.7	129.8	129.5
65°	117.4	113.8	112.0	110.1	109.2	109.2	108.3
67.5°	97.3	95.9	93.9	93.4	92.5	92.2	91.9
70°	86.1	84.2	83.3	82.8	81.9	82.4	81.1
72.5°	75.1	73.7	73.5	72.3	71.7	71.8	70.8
75°	59.2	59.2	58.7	58.2	57.3	56.9	57.3
77.5°	45.5	45.6	44.8	44.7	44.6	44.7	44.2
80°	36.4	36.8	36.4	35.9	35.5	35.9	35.5
82.5°	28.8	28.1	28.0	27.9	27.8	27.6	27.5
85°	16.4	16.9	16.4	16.0	16.0	16.0	16.4
87.5°	12.2	12.1	12.1	12.1	12.1	12.2	11.9
90°	30.0	29.6	29.4	29.7	29.9	30.1	30.2
92.5°	28.5	28.6	28.7	28.7	28.7	28.8	28.8
95°	57.0	57.0	56.7	56.4	56.0	55.6	55.2
97.5°	95.8	95.8	95.8	95.7	95.7	95.6	95.6
100°	122.8	122.8	122.7	122.5	122.3	122.1	121.9
102.5°	152.5	152.7	152.6	152.4	152.2	152.0	151.9
105°	197.0	197.3	197.5	197.5	197.5	197.5	197.5
107.5°	244.5	244.6	244.2	243.3	242.5	241.6	240.6
110°	276.8	276.8	276.4	275.9	275.3	274.6	274.1



TEST NUMBER: P331694-940

CATALOG NUMBER: SA2XXRDIP-C675D925U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	308.8	308.4	307.8	307.5	307.0	306.6	306.1
115°	358.9	358.7	358.3	357.8	357.1	356.5	356.0
117.5°	406.9	406.4	405.8	405.3	404.7	404.0	403.5
120°	439.6	439.6	439.3	438.7	438.1	437.6	436.9
122.5°	472.3	471.9	471.4	471.0	470.6	470.1	469.7
125°	521.5	520.8	520.5	520.3	520.0	519.9	519.7
127.5°	569.2	568.5	567.8	567.1	566.5	565.9	565.3
130°	602.2	601.7	601.2	600.4	599.6	598.8	598.0
132.5°	633.5	632.6	631.9	631.2	630.6	630.0	629.4
135°	681.1	680.8	680.5	679.8	679.3	678.7	678.1
137.5°	726.0	725.9	725.4	724.6	723.8	723.0	722.2
140°	756.4	756.4	756.0	755.2	754.4	753.7	752.9
142.5°	783.9	784.1	783.8	783.0	782.2	781.4	780.6
145°	825.5	825.7	825.5	824.7	823.9	823.0	822.2
147.5°	862.2	862.6	862.5	861.7	860.9	860.2	859.4
150°	885.5	886.0	886.0	885.5	884.8	884.2	883.7
152.5°	908.7	909.5	909.5	908.7	907.9	907.2	906.4
155°	938.3	939.2	939.4	938.8	938.3	937.6	937.0
157.5°	965.6	967.0	967.1	966.3	965.3	964.3	963.4
160°	981.5	982.8	982.9	982.1	981.3	980.5	979.7
162.5°	996.2	997.6	997.8	996.8	995.9	995.0	994.0
165°	1015.0	1016.5	1016.6	1015.7	1014.7	1013.7	1012.7
167.5°	1030.6	1031.9	1032.1	1031.1	1030.0	1029.0	1028.0
170°	1039.1	1040.4	1040.5	1039.4	1038.2	1037.0	1035.8
172.5°	1045.5	1046.9	1047.0	1045.8	1044.6	1043.4	1042.2
175°	1052.4	1053.8	1053.9	1052.8	1051.5	1050.3	1049.2
177.5°	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5

(END OF REPORT)