

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331265-935

Luminaire Tested: **SA2XXDIP-C290D725U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331265-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3268.0 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331265-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331265-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	50	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	16	14	12	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331265-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.2
10°-20°	107.6	3.3
20°-30°	158.2	4.8
30°-40°	183.8	5.6
40°-50°	183.6	5.6
50°-60°	160.1	4.9
60°-70°	118.4	3.6
70°-80°	67.0	2.1
80°-90°	21.2	0.6
90°-100°	50.5	1.5
100°-110°	157.0	4.8
110°-120°	268.3	8.2
120°-130°	352.8	10.8
130°-140°	396.0	12.1
140°-150°	388.3	11.9
150°-160°	325.7	10.0
160°-170°	216.0	6.6
170°-180°	75.5	2.3
0°-30°	304.1	9.3
0°-40°	487.8	14.9
0°-60°	831.5	25.4
0°-90°	1038.1	31.8
90°-120°	475.8	14.6
90°-150°	1612.8	49.4
90°-180°	2230.0	68.2
0°-180°	3268.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	1	9	24	22	23	3
95°	35	41	43	43	42	40
105°	145	147	148	149	149	153
115°	269	273	272	271	269	266
125°	392	397	396	394	393	350
135°	507	514	516	515	513	391
145°	615	620	624	624	622	384
155°	703	705	707	710	709	324
165°	765	765	764	769	766	216
175°	796	794	793	797	794	76
180°	798	798	798	798	798	



TEST NUMBER: P331265-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.8	6.0	6.2	6.5	6.6	7.0	7.6	8.1	8.6	9.1	8.8
90°	0.7	2.5	4.3	6.0	7.8	10.4	13.7	17.0	20.2	23.6	23.2
92.5°	12.0	13.3	14.6	15.9	17.2	18.3	19.0	19.8	20.7	21.4	21.4
95°	35.0	36.5	38.0	39.5	41.0	41.8	42.2	42.4	42.8	43.0	43.0
97.5°	64.0	65.3	66.6	67.8	69.2	70.2	70.7	71.3	71.8	72.4	72.4
100°	85.5	86.7	87.8	89.0	90.2	91.1	91.5	92.0	92.4	92.9	92.9
102.5°	108.1	109.0	110.0	111.0	111.9	112.7	113.2	113.8	114.3	114.9	115.0
105°	144.7	145.2	145.6	146.0	146.5	146.9	147.1	147.5	147.7	148.1	148.4
107.5°	181.6	182.3	182.9	183.6	184.2	184.5	184.5	184.5	184.5	184.5	184.7
110°	205.3	206.1	207.1	207.9	208.9	209.3	209.3	209.3	209.3	209.3	209.3



TEST NUMBER: P331265-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.1	232.0	232.9	233.8	234.7	235.1	235.0	234.9	234.7	234.6	234.3
115°	269.2	270.1	271.0	271.9	272.8	273.1	272.8	272.5	272.2	271.9	271.7
117.5°	307.1	308.3	309.5	310.7	311.9	312.1	311.3	310.5	309.6	308.8	308.4
120°	332.4	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	332.4
122.5°	355.6	357.1	358.5	359.9	361.4	361.6	360.8	360.0	359.1	358.3	357.9
125°	391.7	393.0	394.3	395.7	397.1	397.5	397.1	396.6	396.1	395.7	395.3
127.5°	426.8	428.5	430.2	432.0	433.6	434.2	433.7	433.2	432.6	432.0	431.5
130°	448.9	450.8	452.8	454.7	456.7	457.4	457.2	456.8	456.6	456.3	456.0
132.5°	473.6	475.3	476.8	478.4	480.0	480.8	480.9	481.0	481.0	481.0	480.4
135°	506.8	508.4	510.1	511.7	513.3	514.3	514.6	514.9	515.2	515.5	515.4
137.5°	541.7	542.9	544.3	545.7	547.0	547.9	548.3	548.6	549.1	549.4	549.3
140°	562.7	564.0	565.3	566.6	568.0	569.0	569.8	570.6	571.3	572.0	572.0
142.5°	584.2	585.5	586.9	588.2	589.5	590.5	591.0	591.5	592.0	592.5	592.6
145°	615.1	616.1	617.3	618.3	619.3	620.3	621.2	622.1	622.9	623.9	624.1
147.5°	642.7	643.9	645.2	646.4	647.7	648.7	649.3	649.9	650.5	651.1	651.3
150°	661.6	662.5	663.3	664.3	665.1	665.9	666.5	667.1	667.7	668.3	668.7
152.5°	678.2	679.2	680.0	681.0	681.8	682.6	683.4	684.1	684.8	685.5	686.0
155°	703.3	703.7	704.2	704.6	705.1	705.5	705.9	706.5	706.9	707.3	708.1
157.5°	724.7	725.0	725.3	725.6	725.9	726.2	726.4	726.7	726.9	727.2	728.2
160°	737.6	737.9	738.2	738.5	738.8	739.0	739.2	739.3	739.5	739.6	740.5
162.5°	749.4	749.5	749.6	749.6	749.7	749.8	749.9	750.1	750.3	750.4	751.4
165°	765.2	765.1	764.9	764.7	764.6	764.5	764.5	764.5	764.5	764.5	765.6
167.5°	778.3	777.9	777.5	777.1	776.6	776.4	776.4	776.3	776.3	776.2	777.3
170°	785.4	785.0	784.5	784.0	783.6	783.3	783.2	783.0	782.8	782.6	783.8
172.5°	790.2	789.8	789.4	788.8	788.4	788.2	788.0	787.8	787.7	787.6	788.6
175°	796.2	795.7	795.2	794.8	794.4	794.0	793.7	793.4	793.1	792.8	793.8
177.5°	798.6	798.2	797.9	797.5	797.1	796.9	796.6	796.3	796.1	795.9	796.6
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331265-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	8.5	8.3	8.0	7.8	7.8	7.7	7.7	7.7
90°	23.0	22.6	22.4	22.3	22.5	22.6	22.7	22.9
92.5°	21.5	21.6	21.6	21.7	21.7	21.8	21.8	21.8
95°	43.0	43.0	43.0	43.0	42.6	42.4	42.0	41.8
97.5°	72.4	72.4	72.4	72.4	72.4	72.3	72.3	72.2
100°	92.9	92.9	92.9	92.8	92.6	92.5	92.4	92.2
102.5°	115.2	115.3	115.5	115.4	115.3	115.1	114.9	114.8
105°	148.7	149.0	149.3	149.4	149.4	149.4	149.4	149.4
107.5°	184.8	184.9	185.0	184.8	184.1	183.4	182.7	182.0
110°	209.3	209.3	209.3	209.1	208.6	208.2	207.8	207.2



TEST NUMBER: P331265-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	233.8	233.5	233.2	232.8	232.5	232.1	231.9	231.5
115°	271.6	271.5	271.3	271.0	270.5	270.1	269.7	269.2
117.5°	308.1	307.7	307.3	306.9	306.5	306.0	305.6	305.1
120°	332.4	332.4	332.4	332.3	331.7	331.3	330.9	330.5
122.5°	357.6	357.2	356.9	356.5	356.2	355.9	355.5	355.2
125°	394.9	394.3	393.9	393.6	393.5	393.3	393.2	393.0
127.5°	431.0	430.4	429.9	429.4	429.0	428.4	428.0	427.5
130°	455.7	455.4	455.1	454.6	454.0	453.5	452.9	452.3
132.5°	479.7	479.1	478.5	477.9	477.3	476.9	476.4	476.0
135°	515.2	515.1	514.9	514.6	514.2	513.8	513.2	512.8
137.5°	549.2	549.1	549.0	548.6	548.0	547.4	546.8	546.2
140°	572.0	572.0	572.0	571.7	571.2	570.6	570.0	569.4
142.5°	592.7	592.9	593.0	592.7	592.1	591.5	591.0	590.4
145°	624.1	624.3	624.5	624.2	623.6	623.0	622.4	621.8
147.5°	651.7	652.0	652.4	652.3	651.7	651.1	650.6	650.0
150°	669.2	669.6	670.1	670.1	669.6	669.2	668.7	668.3
152.5°	686.6	687.3	687.8	687.8	687.3	686.6	686.0	685.5
155°	708.8	709.6	710.3	710.5	710.0	709.6	709.1	708.7
157.5°	729.3	730.3	731.3	731.4	730.7	730.0	729.3	728.6
160°	741.4	742.4	743.2	743.4	742.8	742.2	741.6	741.0
162.5°	752.4	753.5	754.5	754.6	753.9	753.2	752.4	751.7
165°	766.6	767.7	768.7	768.9	768.1	767.3	766.6	765.9
167.5°	778.3	779.4	780.4	780.6	779.8	779.0	778.3	777.5
170°	784.8	785.8	786.9	787.0	786.1	785.1	784.3	783.3
172.5°	789.6	790.7	791.7	791.8	790.9	790.0	789.1	788.2
175°	794.9	795.9	796.9	797.0	796.2	795.2	794.4	793.5
177.5°	797.3	798.1	798.7	798.7	798.1	797.3	796.6	795.9
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5

(END OF REPORT)