

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331710-940

Luminaire Tested: **SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331710-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3830.7 lumens  
Efficiency: N/A  
Efficacy: 88.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331710-940

CATALOG NUMBER: SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331710-940

CATALOG NUMBER: SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	99	95	92	97	94	90	87	84	82	79	75	73	72	67	66	64	60
2	94	87	81	76	89	83	77	73	74	70	67	67	64	61	60	57	55	52
3	87	77	70	64	82	73	67	62	66	61	57	60	56	52	54	51	48	45
4	80	69	61	55	75	66	59	53	59	54	49	54	49	45	48	45	42	39
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37	34
6	68	56	48	42	64	53	46	41	49	43	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	41	35	32	37	33	30	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	29	34	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	27	24	22
10	52	39	32	27	49	38	31	27	35	29	25	32	27	24	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331710-940

CATALOG NUMBER: SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.4	3.2
10°-20°	336.0	8.8
20°-30°	471.9	12.3
30°-40°	514.6	13.4
40°-50°	473.1	12.4
50°-60°	371.6	9.7
60°-70°	242.3	6.3
70°-80°	124.9	3.3
80°-90°	33.9	0.9
90°-100°	65.5	1.7
100°-110°	222.3	5.8
110°-120°	236.2	6.2
120°-130°	194.4	5.1
130°-140°	156.1	4.1
140°-150°	118.0	3.1
150°-160°	82.9	2.2
160°-170°	48.8	1.3
170°-180°	15.9	0.4
0°-30°	930.3	24.3
0°-40°	1444.9	37.7
0°-60°	2289.6	59.8
0°-90°	2690.7	70.2
90°-120°	524.0	13.7
90°-150°	992.5	25.9
90°-180°	1140.0	29.8
0°-180°	3830.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	0	4	11	10	10	3
95°	11	27	124	47	36	12
105°	38	58	233	417	355	41
115°	68	86	195	403	467	67
125°	94	112	188	327	379	84
135°	111	132	186	274	314	86
145°	127	146	185	229	251	79
155°	144	155	179	203	211	66
165°	157	162	172	182	185	44
175°	164	164	165	167	167	16
180°	164	164	164	164	164	



TEST NUMBER: P331710-940

CATALOG NUMBER: SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.2	13.7	12.3	10.7	9.2	8.6	8.8	9.3	9.6	9.7	9.5
90°	0.4	1.2	2.5	3.1	3.7	4.7	6.3	8.5	10.4	10.7	10.4
92.5°	3.8	5.5	7.8	9.2	11.3	14.3	21.4	31.5	40.4	40.9	34.6
95°	11.1	12.3	15.4	18.3	23.3	30.9	45.4	72.8	109.3	123.5	108.1
97.5°	17.9	19.6	23.0	27.3	33.1	41.6	59.8	98.1	158.8	210.8	221.1
100°	24.3	25.2	28.0	33.1	39.4	48.2	64.9	103.3	171.4	248.9	294.3
102.5°	30.1	30.8	33.6	38.6	45.2	54.0	69.5	103.6	166.6	250.1	321.5
105°	38.4	39.7	41.9	46.6	53.6	62.4	77.2	105.2	157.2	233.4	317.3
107.5°	47.5	48.5	50.6	55.0	61.9	70.8	85.2	109.6	152.6	215.5	289.6
110°	53.6	54.8	56.7	60.8	67.4	76.6	90.4	113.1	151.6	207.0	272.2



TEST NUMBER: P331710-940

CATALOG NUMBER: SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.1	60.4	62.5	66.3	72.7	82.1	95.5	116.9	151.8	201.4	260.1
115°	67.8	69.3	71.2	75.0	81.3	89.8	103.3	122.5	153.1	195.4	245.1
117.5°	76.7	77.9	79.8	83.2	89.3	98.1	110.6	128.6	155.4	192.3	235.7
120°	82.2	83.5	85.4	88.2	94.5	103.3	115.7	132.7	156.9	190.6	230.6
122.5°	87.6	88.5	90.4	93.5	99.8	108.9	120.4	136.2	158.6	189.6	226.3
125°	94.5	95.5	97.4	101.1	107.5	116.3	127.6	141.8	161.3	187.8	220.3
127.5°	100.0	101.3	104.0	108.2	114.1	123.2	134.3	147.0	164.0	186.7	214.5
130°	103.3	104.6	107.7	112.2	118.5	127.2	138.3	150.3	166.0	186.2	210.8
132.5°	106.4	107.9	111.3	115.9	122.5	131.3	141.9	153.6	168.1	185.9	207.8
135°	110.9	112.2	115.9	120.6	128.0	136.7	146.9	157.8	170.5	185.6	203.5
137.5°	115.2	116.7	120.5	125.6	132.7	140.9	150.9	161.1	172.6	185.5	200.5
140°	118.5	119.8	123.5	128.6	135.5	143.7	153.1	162.9	173.6	185.3	198.8
142.5°	121.7	122.8	126.3	131.3	138.0	145.7	154.9	164.4	174.3	185.3	197.1
145°	126.6	128.0	131.1	135.8	142.1	149.0	157.6	166.4	175.1	184.6	194.7
147.5°	132.0	132.9	135.9	140.3	145.5	151.7	159.7	167.5	175.4	183.5	192.3
150°	135.5	136.4	138.9	143.0	147.8	153.5	160.7	167.9	175.1	182.7	190.3
152.5°	139.0	139.5	142.0	145.5	150.1	155.2	161.7	168.2	174.7	181.5	188.5
155°	144.0	144.3	146.2	149.6	153.1	157.8	163.2	168.5	173.9	179.2	185.3
157.5°	148.1	148.5	150.0	153.0	155.8	159.7	164.3	168.5	172.5	177.0	182.2
160°	150.9	151.2	152.5	155.0	157.6	161.0	164.8	168.5	171.7	175.5	179.9
162.5°	153.7	153.5	154.8	156.8	159.1	161.8	165.1	168.3	170.9	174.2	177.9
165°	156.9	156.6	157.2	159.1	160.7	162.6	165.4	167.6	169.5	171.7	174.5
167.5°	159.5	159.2	159.7	161.0	162.1	163.3	165.3	167.2	168.1	169.5	171.3
170°	161.3	160.7	161.0	161.9	162.6	163.5	165.1	166.7	167.3	168.3	169.5
172.5°	162.3	161.9	161.8	162.7	163.1	163.8	164.9	165.9	166.3	166.7	167.7
175°	163.5	163.2	162.9	163.5	163.5	163.8	164.4	165.1	164.8	165.1	165.4
177.5°	164.1	163.5	163.4	163.8	163.8	163.8	164.1	164.6	164.1	163.8	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331710-940

CATALOG NUMBER: SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	9.2	8.8	8.7	8.7	8.7	8.7	8.7	8.7
90°	10.1	9.5	10.1	10.4	10.4	10.4	10.4	10.4
92.5°	27.5	23.5	21.0	19.0	18.7	17.7	17.9	17.5
95°	82.6	63.3	50.1	43.2	39.1	36.6	35.6	35.9
97.5°	192.6	157.6	123.5	100.8	85.7	77.9	73.4	70.7
100°	287.7	248.6	205.5	167.3	141.2	127.6	118.5	112.8
102.5°	349.9	341.1	309.5	269.1	240.7	217.6	206.2	198.5
105°	382.8	418.4	422.5	412.1	392.5	373.0	359.4	355.1
107.5°	359.1	412.8	445.5	460.7	463.2	462.2	459.4	453.6
110°	338.7	395.1	435.4	461.3	474.8	480.8	483.7	483.3





TEST NUMBER: P331710-940

CATALOG NUMBER: SA2XXRDIP-C865D330U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	320.0	374.2	417.2	446.9	465.7	475.7	481.1	482.8
115°	297.1	345.6	386.9	419.4	441.8	456.2	464.4	467.3
117.5°	279.8	322.4	359.9	390.3	413.1	428.5	437.0	439.4
120°	271.3	310.3	343.8	372.4	394.5	409.3	418.4	421.6
122.5°	264.5	300.2	331.9	357.8	377.6	392.2	400.3	402.9
125°	254.6	287.0	314.8	338.4	356.7	368.6	376.5	379.1
127.5°	244.8	274.2	300.3	322.1	338.0	349.3	356.1	358.1
130°	238.5	265.6	290.5	311.3	326.7	337.4	343.8	346.3
132.5°	232.5	257.5	280.4	300.0	315.1	325.8	331.6	333.9
135°	224.0	244.8	265.6	283.2	296.8	307.2	312.9	314.1
137.5°	217.3	234.7	251.2	266.5	278.9	287.8	292.8	294.7
140°	212.9	228.1	242.6	256.5	266.5	274.7	279.5	281.3
142.5°	209.5	222.3	234.8	246.4	255.9	263.4	267.6	268.0
145°	204.5	214.9	224.6	233.8	241.3	246.7	249.9	250.7
147.5°	200.6	208.8	216.4	223.1	229.3	233.6	235.8	236.4
150°	197.9	204.8	211.4	217.0	221.8	225.6	227.5	227.8
152.5°	195.1	201.5	207.1	212.0	215.8	219.0	220.4	220.5
155°	191.3	196.3	201.0	204.5	207.9	210.2	211.4	210.8
157.5°	186.8	191.0	194.9	197.7	200.1	202.0	202.5	202.5
160°	184.0	187.4	190.9	193.1	195.4	196.9	197.2	197.2
162.5°	181.2	184.2	187.2	188.9	191.1	192.2	192.4	192.2
165°	177.1	179.2	181.5	182.7	184.0	185.3	185.3	184.9
167.5°	173.1	174.8	176.3	177.5	178.0	178.7	178.6	178.3
170°	171.1	172.0	173.3	173.9	174.2	175.1	174.9	174.2
172.5°	168.8	169.5	170.5	170.9	171.2	171.7	171.3	170.9
175°	166.4	166.7	167.0	167.3	167.3	167.6	167.3	166.7
177.5°	164.6	164.6	164.9	164.9	164.9	164.9	164.6	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8

(END OF REPORT)