

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331711-940

Luminaire Tested: **SA2XXRDIP-C865D530U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331711-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4829.1 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	94	90	95	91	88	85	80	78	75	70	68	66	60	59	58	53
2	93	86	80	75	87	81	76	72	71	67	64	62	59	57	54	52	50	46
3	86	77	70	64	80	72	66	61	64	59	55	56	52	49	49	46	44	40
4	79	69	61	55	74	65	58	53	57	52	48	51	47	43	44	41	39	36
5	73	62	54	48	68	58	51	46	52	47	42	46	42	38	41	37	35	32
6	68	56	48	43	63	53	46	41	47	42	38	42	38	34	37	34	31	28
7	63	51	43	38	59	48	41	37	43	38	34	39	34	31	34	31	28	26
8	59	47	39	34	55	44	38	33	40	34	30	36	31	28	32	28	26	23
9	55	43	36	31	52	41	34	30	37	31	28	33	29	26	30	26	23	21
10	51	40	33	28	48	38	31	27	34	29	25	31	27	23	28	24	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27493	27493	27493	27493
5°	30705	27665	24530	27665
10°	34067	27471	21263	27471
15°	35741	27067	16754	27067
20°	30986	26472	14496	26472
25°	20322	25655	12944	25655
30°	13679	24664	11714	24664
35°	11077	23416	10565	23416
40°	9851	22059	9778	22059
45°	8917	20466	8727	20466
50°	8116	18889	8083	18889
55°	7628	17140	7527	17140
60°	6381	15532	6307	15532
65°	5379	14105	6101	14105
70°	4971	12595	5755	12595
75°	4648	10967	5315	10967
80°	4296	9019	4733	9019
85°	3946	7114	4168	7114



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	3.3
10°-20°	449.8	9.3
20°-30°	579.6	12.0
30°-40°	550.8	11.4
40°-50°	471.8	9.8
50°-60°	359.3	7.4
60°-70°	227.1	4.7
70°-80°	113.4	2.3
80°-90°	31.1	0.6
90°-100°	21.5	0.4
100°-110°	78.7	1.6
110°-120°	210.3	4.4
120°-130°	347.1	7.2
130°-140°	369.2	7.6
140°-150°	343.1	7.1
150°-160°	275.9	5.7
160°-170°	177.8	3.7
170°-180°	61.2	1.3
0°-30°	1190.8	24.7
0°-40°	1741.6	36.1
0°-60°	2572.7	53.3
0°-90°	2944.4	61.0
90°-120°	310.4	6.4
90°-150°	1369.9	28.4
90°-180°	1885.0	39.0
0°-180°	4829.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1703	1703	1703	1703	1703	
5°	1894	1707	1514	1707	1894	187
15°	2138	1619	1002	1619	2138	577
25°	1141	1440	727	1440	1141	541
35°	562	1188	536	1188	562	360
45°	390	896	382	896	390	302
55°	271	609	267	609	271	238
65°	141	369	160	369	141	143
75°	74	176	85	176	74	79
85°	21	38	22	38	21	23
90°	13	0	13	0	13	7
95°	20	30	20	30	20	19
105°	35	141	35	141	35	37
115°	38	268	38	268	38	96
125°	398	378	398	378	398	344
135°	484	468	484	468	484	373
145°	551	543	551	543	551	345
155°	598	598	598	598	598	276
165°	629	630	629	630	629	177
175°	641	644	641	644	641	61
180°	643	643	643	643	643	



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1771.9	1773.3	1774.8	1771.4	1771.4	1768.6	1762.5	1757.7	1744.5	1742.6	1742.6
5°	1894.5	1893.3	1895.7	1888.0	1877.3	1875.0	1863.8	1849.0	1833.5	1816.4	1812.8
7.5°	2016.3	2014.6	2009.8	2008.6	2000.4	1982.5	1964.4	1945.2	1919.6	1894.6	1882.0
10°	2077.9	2097.4	2085.6	2064.8	2069.0	2041.2	2026.4	2001.0	1979.7	1942.4	1934.1
12.5°	2138.5	2146.2	2142.4	2130.7	2125.4	2106.0	2086.1	2064.0	2024.6	1991.2	1962.0
15°	2138.2	2149.5	2152.4	2148.9	2151.9	2150.7	2140.0	2121.6	2087.4	2050.7	2018.7
17.5°	1980.4	1988.2	2007.6	2020.7	2037.3	2072.3	2089.6	2096.3	2091.2	2070.3	2047.8
20°	1803.4	1790.4	1844.8	1872.6	1896.2	1955.4	2006.3	2025.9	2057.2	2056.6	2050.7
22.5°	1552.5	1555.6	1607.2	1640.2	1709.3	1768.4	1826.5	1900.0	1960.6	2000.7	2024.2
25°	1140.7	1163.2	1214.7	1259.6	1336.6	1446.6	1546.6	1662.6	1772.0	1858.4	1940.6
27.5°	856.8	858.4	899.2	940.8	986.4	1076.6	1202.5	1341.0	1497.0	1625.8	1773.9
30°	733.7	730.1	747.3	772.7	811.7	881.5	976.2	1112.3	1267.9	1462.0	1634.8
32.5°	646.6	646.8	659.7	678.5	711.0	758.0	822.9	933.4	1080.5	1271.2	1473.8
35°	562.0	561.5	571.0	584.5	598.2	628.3	672.7	730.7	831.9	1010.0	1217.0
37.5°	501.5	504.1	508.7	517.2	532.3	549.0	575.7	614.7	686.7	792.0	966.1
40°	467.4	468.6	475.1	482.2	491.1	504.1	526.0	557.3	610.0	694.0	821.2
42.5°	436.1	437.4	441.9	448.6	455.6	468.6	486.7	513.8	556.5	622.1	727.0
45°	390.5	390.5	394.7	397.6	405.3	417.1	431.9	454.4	483.9	532.5	602.4
47.5°	347.7	347.8	350.5	355.6	360.4	369.7	384.2	402.6	424.1	461.6	521.3
50°	323.1	323.6	325.4	329.6	332.5	340.8	352.0	368.0	390.5	419.5	469.2
52.5°	303.2	302.8	305.1	306.8	308.9	314.8	323.2	337.2	357.4	382.5	423.7
55°	271.0	268.6	272.2	275.1	276.9	279.3	284.0	292.8	310.0	331.4	362.1
57.5°	230.8	229.8	232.3	235.0	240.6	246.9	251.0	256.6	265.6	280.8	311.3
60°	197.6	197.6	203.0	204.7	211.2	219.5	227.8	232.6	241.4	251.5	273.9
62.5°	168.3	168.7	171.2	173.0	176.6	186.8	198.4	208.8	217.2	226.9	241.7
65°	140.8	142.0	142.0	143.2	145.5	147.9	152.7	161.0	175.8	189.3	200.5
67.5°	119.5	119.8	120.2	121.5	122.0	124.6	126.5	130.2	133.6	146.5	160.4
70°	105.3	107.1	106.5	107.7	108.3	109.4	111.8	113.6	119.0	121.9	130.2
72.5°	92.0	93.4	93.3	94.0	95.5	95.8	97.6	99.4	102.8	105.3	109.8
75°	74.5	73.9	74.5	75.7	76.3	77.0	77.0	79.3	81.1	83.5	86.4
77.5°	57.5	58.1	58.0	58.1	58.2	59.3	59.2	60.2	62.0	63.2	64.6
80°	46.2	46.7	46.2	46.7	47.3	47.9	47.3	47.9	49.7	50.9	50.9
82.5°	35.8	35.8	36.2	36.3	36.5	36.6	37.4	37.5	38.8	38.6	39.1
85°	21.3	20.7	20.7	20.7	21.3	21.8	21.3	21.3	21.8	21.8	21.8
87.5°	10.1	10.5	10.4	10.4	10.4	10.3	10.3	10.6	10.0	10.3	9.7
90°	12.6	12.4	12.1	11.9	11.8	11.4	10.9	10.3	9.8	9.3	8.5
92.5°	12.6	12.5	12.3	12.2	12.0	11.9	11.6	11.3	11.1	10.8	10.3
95°	20.0	20.2	20.2	20.3	20.4	20.2	19.7	19.2	18.6	18.2	17.4
97.5°	26.8	26.6	26.5	26.3	26.2	25.9	25.5	25.1	24.7	24.3	22.6
100°	31.2	30.9	30.8	30.6	30.3	29.9	29.0	28.2	27.4	26.5	24.8
102.5°	33.4	33.1	32.8	32.5	32.3	31.6	30.5	29.4	28.4	27.3	42.0
105°	35.4	35.0	34.5	34.2	33.7	32.9	31.8	30.7	29.5	28.4	56.6
107.5°	36.4	35.9	35.6	35.1	34.8	35.1	36.3	37.5	38.6	39.8	73.6
110°	36.7	36.4	35.9	35.5	35.1	40.0	50.4	60.7	71.1	81.4	111.3



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	37.1	36.8	36.5	36.1	35.8	54.5	92.2	129.9	167.6	205.5	212.8
115°	38.2	45.6	53.1	60.5	67.9	95.6	143.5	191.4	239.2	287.1	284.5
117.5°	155.8	180.3	204.7	229.2	253.7	271.7	283.3	294.9	306.5	318.0	316.3
120°	283.8	297.8	311.8	325.7	339.7	346.1	344.8	343.6	342.3	341.1	339.2
122.5°	354.2	357.0	359.6	362.4	365.1	366.0	365.3	364.5	363.8	363.1	361.1
125°	397.9	397.6	397.3	397.0	396.6	396.1	395.4	394.7	394.0	393.2	391.3
127.5°	425.4	425.3	425.3	425.3	425.2	424.6	423.6	422.5	421.4	420.4	418.9
130°	442.6	442.6	442.7	442.8	443.0	442.5	441.3	440.1	439.1	437.9	436.8
132.5°	459.3	459.4	459.5	459.6	459.7	459.3	458.3	457.4	456.4	455.4	454.2
135°	483.5	483.8	483.9	484.1	484.4	483.9	482.9	481.9	480.8	479.7	478.8
137.5°	505.6	506.0	506.2	506.6	506.9	506.7	505.6	504.6	503.6	502.6	501.5
140°	519.3	519.9	520.4	520.8	521.4	521.2	520.2	519.3	518.4	517.5	516.3
142.5°	532.7	533.2	533.8	534.3	534.8	534.7	533.8	533.0	532.1	531.3	529.9
145°	551.4	552.0	552.5	553.0	553.5	553.4	552.7	552.0	551.3	550.5	548.8
147.5°	567.9	568.4	568.8	569.3	569.6	569.6	569.1	568.6	568.0	567.5	565.7
150°	578.0	578.5	579.0	579.5	580.1	580.0	579.3	578.7	578.1	577.5	575.9
152.5°	586.6	587.2	587.9	588.6	589.2	589.3	588.7	588.1	587.5	586.8	585.2
155°	598.4	599.3	600.1	600.9	601.7	601.9	601.3	600.7	600.0	599.4	598.2
157.5°	609.3	610.1	610.9	611.7	612.6	612.6	611.9	611.2	610.5	609.8	608.9
160°	615.6	616.4	617.2	617.9	618.6	618.6	618.0	617.3	616.8	616.2	615.5
162.5°	620.9	621.8	622.7	623.6	624.5	624.6	623.8	623.1	622.4	621.7	621.2
165°	628.7	629.5	630.2	630.9	631.6	631.6	630.9	630.2	629.5	628.7	628.4
167.5°	633.6	634.5	635.5	636.4	637.4	637.5	636.8	636.0	635.3	634.5	634.3
170°	636.6	637.6	638.5	639.4	640.3	640.4	639.7	639.0	638.3	637.6	637.3
172.5°	638.8	639.8	640.7	641.7	642.6	642.7	641.9	641.2	640.5	639.8	639.5
175°	640.8	641.9	642.8	643.9	645.0	645.1	644.4	643.6	642.9	642.2	641.9
177.5°	642.0	642.7	643.5	644.3	645.0	645.1	644.5	643.9	643.4	642.7	642.7
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1743.5	1739.7	1736.4	1727.9	1723.6	1714.1	1712.7	1712.3	1700.0	1688.1	1684.8
5°	1803.4	1793.9	1779.7	1763.2	1746.0	1728.2	1716.4	1706.9	1683.3	1660.8	1647.8
7.5°	1863.8	1843.3	1818.9	1787.5	1761.4	1732.1	1710.2	1690.7	1657.2	1625.0	1603.3
10°	1908.7	1875.5	1843.0	1799.8	1766.1	1733.0	1702.2	1675.6	1637.7	1595.1	1565.0
12.5°	1936.6	1900.1	1855.3	1813.1	1769.4	1727.2	1686.1	1651.9	1607.4	1563.4	1527.5
15°	1974.3	1935.3	1880.9	1820.5	1764.3	1709.3	1662.0	1619.3	1561.4	1508.7	1464.9
17.5°	2005.3	1951.5	1893.1	1823.3	1758.2	1688.3	1627.3	1572.9	1508.3	1444.8	1393.2
20°	2015.2	1961.9	1894.5	1824.7	1747.8	1665.5	1599.8	1540.7	1471.4	1402.2	1343.1
22.5°	2009.0	1967.6	1892.6	1809.0	1730.3	1644.2	1570.0	1501.4	1424.6	1354.0	1285.3
25°	1967.3	1953.0	1882.0	1790.9	1701.0	1601.1	1515.2	1440.1	1352.5	1276.8	1202.2
27.5°	1869.9	1900.5	1856.5	1759.4	1659.5	1552.3	1455.8	1370.3	1279.4	1194.2	1119.9
30°	1776.2	1846.6	1827.7	1737.7	1625.9	1520.5	1412.3	1322.9	1225.9	1138.4	1065.0
32.5°	1647.9	1764.2	1782.7	1707.4	1591.8	1476.0	1362.6	1273.7	1172.4	1080.1	1008.6
35°	1443.7	1617.6	1697.5	1649.6	1533.6	1408.7	1291.6	1188.0	1086.3	995.1	924.2
37.5°	1200.0	1436.9	1570.0	1573.4	1467.0	1337.1	1209.6	1106.8	1002.6	913.2	836.3
40°	1041.9	1298.7	1472.0	1510.5	1420.6	1280.3	1151.4	1046.6	944.9	857.3	769.2
42.5°	899.9	1155.7	1368.9	1435.7	1364.2	1224.9	1095.6	986.1	887.2	804.3	714.3
45°	727.7	951.4	1186.2	1305.8	1266.1	1137.2	1000.5	896.3	803.4	731.9	645.5
47.5°	613.9	771.5	998.8	1160.5	1159.8	1042.1	907.6	807.9	721.7	654.6	584.7
50°	549.0	686.3	878.6	1062.0	1077.4	978.6	850.8	752.0	671.5	601.1	544.9
52.5°	490.8	604.0	776.9	952.7	996.5	910.9	786.9	695.7	617.6	552.9	504.7
55°	414.7	502.3	633.6	798.2	864.4	804.1	694.0	608.9	545.5	491.1	449.7
57.5°	350.9	416.5	521.9	654.3	731.6	693.6	602.8	533.6	479.4	430.2	397.4
60°	310.6	364.4	453.8	564.5	649.6	623.0	545.5	481.0	434.9	392.3	361.5
62.5°	272.8	319.1	395.6	485.4	563.5	552.5	489.2	435.1	394.7	355.8	329.8
65°	219.5	253.2	313.0	383.4	446.1	451.5	405.9	369.2	333.1	302.4	279.3
67.5°	174.8	196.8	238.9	298.2	345.2	361.9	334.1	306.1	277.5	253.7	233.7
70°	147.3	165.1	195.8	243.8	287.0	304.7	288.7	266.8	242.0	222.5	205.3
72.5°	119.4	136.7	159.3	194.6	231.6	250.7	245.2	229.4	209.3	193.1	176.9
75°	90.0	95.2	110.7	134.3	163.3	179.9	184.0	175.8	159.7	147.3	137.9
77.5°	66.5	69.7	77.0	89.4	108.4	123.1	129.2	128.2	117.3	110.0	101.2
80°	53.2	55.0	58.6	63.9	78.1	92.9	97.0	97.0	89.3	86.4	77.5
82.5°	40.5	41.7	43.9	46.8	53.5	66.3	71.0	72.0	67.1	63.2	56.2
85°	23.1	22.5	23.6	25.4	26.7	30.1	37.3	38.4	37.3	32.5	30.8
87.5°	9.5	9.9	9.7	9.0	9.3	9.5	11.7	13.8	12.1	11.0	10.3
90°	7.7	6.9	6.0	5.0	3.8	2.8	1.6	0.4	1.6	2.8	3.8
92.5°	10.0	9.5	9.2	9.0	9.1	9.2	9.3	9.4	9.3	9.2	9.1
95°	16.7	16.0	15.2	16.6	20.0	23.5	26.8	30.2	26.8	23.5	20.0
97.5°	21.0	19.3	17.6	21.6	31.2	40.8	50.4	60.0	50.4	40.8	31.2
100°	23.0	21.2	19.5	25.7	39.9	54.0	68.2	82.4	68.2	54.0	39.9
102.5°	56.7	71.4	86.1	95.0	97.9	100.9	104.0	106.9	104.0	100.9	97.9
105°	84.9	113.1	141.3	153.9	150.8	147.7	144.5	141.4	144.5	147.7	150.8
107.5°	107.5	141.3	175.1	190.8	188.3	185.8	183.3	180.8	183.3	185.8	188.3
110°	141.2	171.1	201.0	214.8	212.7	210.5	208.3	206.2	208.3	210.5	212.7



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	220.2	227.6	235.0	237.6	235.8	233.8	231.9	230.0	231.9	233.8	235.8
115°	282.0	279.4	276.8	274.6	272.9	271.1	269.3	267.6	269.3	271.1	272.9
117.5°	314.5	312.7	310.9	309.1	307.1	305.1	303.2	301.2	303.2	305.1	307.1
120°	337.4	335.6	333.7	332.0	330.4	328.9	327.3	325.7	327.3	328.9	330.4
122.5°	359.0	357.0	355.0	353.1	351.5	349.9	348.2	346.6	348.2	349.9	351.5
125°	389.3	387.4	385.4	383.7	382.4	381.0	379.7	378.4	379.7	381.0	382.4
127.5°	417.5	416.0	414.6	413.0	411.5	410.1	408.6	407.1	408.6	410.1	411.5
130°	435.6	434.5	433.4	431.9	430.3	428.6	427.0	425.3	427.0	428.6	430.3
132.5°	453.2	452.0	450.8	449.6	448.2	446.7	445.3	444.0	445.3	446.7	448.2
135°	478.0	477.0	476.1	474.7	473.1	471.4	469.8	468.1	469.8	471.4	473.1
137.5°	500.5	499.4	498.4	497.2	496.1	494.9	493.7	492.7	493.7	494.9	496.1
140°	515.2	514.1	512.9	511.9	511.1	510.3	509.4	508.6	509.4	510.3	511.1
142.5°	528.6	527.4	526.0	525.0	524.2	523.5	522.8	522.0	522.8	523.5	524.2
145°	547.0	545.3	543.5	542.7	542.8	542.9	543.0	543.1	543.0	542.9	542.8
147.5°	564.0	562.2	560.5	559.8	560.3	560.6	561.0	561.4	561.0	560.6	560.3
150°	574.2	572.6	570.9	570.4	571.1	571.9	572.6	573.3	572.6	571.9	571.1
152.5°	583.7	582.1	580.5	580.1	580.9	581.8	582.6	583.4	582.6	581.8	580.9
155°	596.9	595.7	594.4	594.2	595.2	596.1	597.1	598.0	597.1	596.1	595.2
157.5°	608.1	607.2	606.4	606.3	607.1	607.9	608.7	609.4	608.7	607.9	607.1
160°	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	615.5	614.9	614.3
162.5°	620.6	620.1	619.6	619.6	620.2	620.8	621.4	622.1	621.4	620.8	620.2
165°	628.0	627.8	627.5	627.6	628.2	628.8	629.5	630.1	629.5	628.8	628.2
167.5°	634.0	633.6	633.4	633.6	634.2	634.8	635.4	636.1	635.4	634.8	634.2
170°	637.1	636.9	636.7	636.9	637.6	638.2	638.8	639.4	638.8	638.2	637.6
172.5°	639.4	639.2	638.9	639.2	639.8	640.4	641.1	641.7	641.1	640.4	639.8
175°	641.8	641.6	641.4	641.6	642.4	643.1	643.8	644.5	643.8	643.1	642.4
177.5°	642.6	642.5	642.4	642.7	643.3	643.8	644.4	645.0	644.4	643.8	643.3
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1678.6	1675.3	1669.2	1659.7	1654.0	1644.1	1637.4	1641.3	1642.2	1641.3	1640.3
5°	1633.5	1621.1	1604.0	1587.4	1572.0	1555.5	1546.0	1541.9	1533.6	1528.8	1526.5
7.5°	1579.0	1557.6	1533.3	1504.5	1480.0	1454.3	1441.2	1434.7	1417.7	1408.5	1400.4
10°	1538.3	1504.6	1480.3	1442.4	1419.4	1385.6	1362.6	1363.2	1340.1	1327.0	1317.6
12.5°	1493.3	1456.3	1415.9	1381.9	1349.8	1322.7	1294.9	1283.6	1259.2	1246.6	1221.0
15°	1418.8	1375.6	1333.0	1286.8	1254.3	1212.3	1172.1	1122.9	1083.3	1049.0	1039.6
17.5°	1337.4	1283.9	1241.2	1187.0	1131.2	1060.6	1014.0	985.4	961.5	943.4	930.0
20°	1281.6	1227.1	1181.5	1099.9	1024.8	976.9	942.5	920.6	895.8	876.3	865.6
22.5°	1222.8	1166.0	1103.9	1012.8	954.2	915.8	885.2	860.1	843.2	828.0	818.2
25°	1139.5	1077.4	975.1	912.3	865.0	824.7	803.4	788.1	770.3	749.7	740.1
27.5°	1051.5	952.7	879.2	832.6	787.4	761.3	742.1	719.1	703.2	693.9	684.0
30°	985.7	886.9	829.5	778.6	746.6	717.6	695.2	682.2	666.8	650.9	644.4
32.5°	912.3	833.4	778.4	736.0	703.6	678.9	661.1	640.1	628.9	619.1	605.5
35°	821.2	761.4	711.1	676.9	646.1	626.0	605.3	592.8	572.7	564.5	559.1
37.5°	744.0	692.2	654.7	618.5	594.1	571.9	559.2	539.5	530.7	519.2	508.0
40°	700.5	649.6	613.6	584.0	556.8	540.2	524.2	508.3	495.3	489.9	476.3
42.5°	656.0	614.7	578.5	546.1	527.9	510.3	490.2	478.4	464.9	456.3	447.9
45°	594.6	557.9	527.2	500.5	480.5	462.1	449.1	429.5	421.9	404.7	397.6
47.5°	540.6	506.6	477.2	451.9	432.3	420.4	401.3	386.0	373.7	363.2	354.0
50°	502.3	473.9	445.5	423.0	405.3	388.2	368.6	360.9	342.0	336.6	331.4
52.5°	467.3	440.3	414.3	392.3	374.5	357.8	340.6	330.6	317.8	312.5	308.6
55°	418.3	392.3	367.4	347.9	330.1	313.0	302.4	289.9	284.0	279.8	275.1
57.5°	369.1	345.6	326.6	306.8	289.0	275.4	263.1	255.6	249.4	244.0	238.4
60°	337.9	315.3	298.2	279.8	261.5	250.3	240.8	231.9	224.8	216.5	214.2
62.5°	304.7	285.1	269.3	251.5	235.5	225.2	216.2	207.8	199.3	187.2	183.9
65°	259.1	243.8	227.2	212.4	198.2	188.2	175.1	165.7	162.1	161.0	160.3
67.5°	217.9	203.4	189.2	174.1	161.1	151.9	145.2	143.7	141.2	140.5	138.9
70°	190.5	176.9	162.7	148.5	136.1	134.3	132.0	129.6	126.6	125.5	124.2
72.5°	165.9	151.9	137.6	126.3	120.9	118.7	116.3	114.0	111.9	110.8	110.0
75°	127.2	114.2	104.7	100.6	97.6	95.9	92.3	90.5	89.3	87.6	86.9
77.5°	91.6	84.3	79.9	77.3	74.2	72.3	70.3	68.5	67.2	66.9	65.9
80°	69.8	66.3	63.3	59.7	58.6	56.2	55.6	53.9	54.4	52.7	52.7
82.5°	54.2	49.7	47.2	45.6	44.4	42.4	41.9	41.0	41.2	39.9	39.9
85°	27.8	26.7	25.4	24.3	24.3	22.5	23.1	22.5	22.5	21.3	20.7
87.5°	10.0	9.7	8.9	9.1	9.3	8.9	9.1	8.7	8.8	8.9	8.5
90°	5.0	6.0	6.9	7.7	8.5	9.3	9.8	10.3	10.9	11.4	11.8
92.5°	9.0	9.2	9.5	10.0	10.3	10.8	11.1	11.3	11.6	11.9	12.0
95°	16.6	15.2	16.0	16.7	17.4	18.2	18.6	19.2	19.7	20.2	20.4
97.5°	21.6	17.6	19.3	21.0	22.6	24.3	24.7	25.1	25.5	25.9	26.2
100°	25.7	19.5	21.2	23.0	24.8	26.5	27.4	28.2	29.0	29.9	30.3
102.5°	95.0	86.1	71.4	56.7	42.0	27.3	28.4	29.4	30.5	31.6	32.3
105°	153.9	141.3	113.1	84.9	56.6	28.4	29.5	30.7	31.8	32.9	33.7
107.5°	190.8	175.1	141.3	107.5	73.6	39.8	38.6	37.5	36.3	35.1	34.8
110°	214.8	201.0	171.1	141.2	111.3	81.4	71.1	60.7	50.4	40.0	35.1



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.6	235.0	227.6	220.2	212.8	205.5	167.6	129.9	92.2	54.5	35.8
115°	274.6	276.8	279.4	282.0	284.5	287.1	239.2	191.4	143.5	95.6	67.9
117.5°	309.1	310.9	312.7	314.5	316.3	318.0	306.5	294.9	283.3	271.7	253.7
120°	332.0	333.7	335.6	337.4	339.2	341.1	342.3	343.6	344.8	346.1	339.7
122.5°	353.1	355.0	357.0	359.0	361.1	363.1	363.8	364.5	365.3	366.0	365.1
125°	383.7	385.4	387.4	389.3	391.3	393.2	394.0	394.7	395.4	396.1	396.6
127.5°	413.0	414.6	416.0	417.5	418.9	420.4	421.4	422.5	423.6	424.6	425.2
130°	431.9	433.4	434.5	435.6	436.8	437.9	439.1	440.1	441.3	442.5	443.0
132.5°	449.6	450.8	452.0	453.2	454.2	455.4	456.4	457.4	458.3	459.3	459.7
135°	474.7	476.1	477.0	478.0	478.8	479.7	480.8	481.9	482.9	483.9	484.4
137.5°	497.2	498.4	499.4	500.5	501.5	502.6	503.6	504.6	505.6	506.7	506.9
140°	511.9	512.9	514.1	515.2	516.3	517.5	518.4	519.3	520.2	521.2	521.4
142.5°	525.0	526.0	527.4	528.6	529.9	531.3	532.1	533.0	533.8	534.7	534.8
145°	542.7	543.5	545.3	547.0	548.8	550.5	551.3	552.0	552.7	553.4	553.5
147.5°	559.8	560.5	562.2	564.0	565.7	567.5	568.0	568.6	569.1	569.6	569.6
150°	570.4	570.9	572.6	574.2	575.9	577.5	578.1	578.7	579.3	580.0	580.1
152.5°	580.1	580.5	582.1	583.7	585.2	586.8	587.5	588.1	588.7	589.3	589.2
155°	594.2	594.4	595.7	596.9	598.2	599.4	600.0	600.7	601.3	601.9	601.7
157.5°	606.3	606.4	607.2	608.1	608.9	609.8	610.5	611.2	611.9	612.6	612.6
160°	613.7	613.7	614.3	614.9	615.5	616.2	616.8	617.3	618.0	618.6	618.6
162.5°	619.6	619.6	620.1	620.6	621.2	621.7	622.4	623.1	623.8	624.6	624.5
165°	627.6	627.5	627.8	628.0	628.4	628.7	629.5	630.2	630.9	631.6	631.6
167.5°	633.6	633.4	633.6	634.0	634.3	634.5	635.3	636.0	636.8	637.5	637.4
170°	636.9	636.7	636.9	637.1	637.3	637.6	638.3	639.0	639.7	640.4	640.3
172.5°	639.2	638.9	639.2	639.4	639.5	639.8	640.5	641.2	641.9	642.7	642.6
175°	641.6	641.4	641.6	641.8	641.9	642.2	642.9	643.6	644.4	645.1	645.0
177.5°	642.7	642.4	642.5	642.6	642.7	642.7	643.4	643.9	644.5	645.1	645.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1635.1	1636.0	1634.6	1635.6	1634.6	1636.0	1635.1	1640.3	1641.3	1642.2	1641.3
5°	1523.5	1516.4	1515.2	1513.5	1515.2	1516.4	1523.5	1526.5	1528.8	1533.6	1541.9
7.5°	1390.3	1389.2	1386.3	1382.2	1386.3	1389.2	1390.3	1400.4	1408.5	1417.7	1434.7
10°	1304.6	1301.6	1301.1	1296.9	1301.1	1301.6	1304.6	1317.6	1327.0	1340.1	1363.2
12.5°	1204.3	1185.2	1183.2	1172.9	1183.2	1185.2	1204.3	1221.0	1246.6	1259.2	1283.6
15°	1025.4	1021.8	1010.0	1002.3	1010.0	1021.8	1025.4	1039.6	1049.0	1083.3	1122.9
17.5°	923.1	911.5	907.9	906.2	907.9	911.5	923.1	930.0	943.4	961.5	985.4
20°	857.3	846.7	844.9	843.7	844.9	846.7	857.3	865.6	876.3	895.8	920.6
22.5°	811.9	800.8	796.1	792.6	796.1	800.8	811.9	818.2	828.0	843.2	860.1
25°	734.2	730.1	727.7	726.6	727.7	730.1	734.2	740.1	749.7	770.3	788.1
27.5°	673.5	664.4	662.6	659.6	662.6	664.4	673.5	684.0	693.9	703.2	719.1
30°	639.0	636.1	631.9	628.3	631.9	636.1	639.0	644.4	650.9	666.8	682.2
32.5°	598.2	595.8	592.1	590.5	592.1	595.8	598.2	605.5	619.1	628.9	640.1
35°	553.2	544.9	541.4	536.0	541.4	544.9	553.2	559.1	564.5	572.7	592.8
37.5°	505.5	501.1	496.1	497.9	496.1	501.1	505.5	508.0	519.2	530.7	539.5
40°	468.6	465.7	464.5	463.9	464.5	465.7	468.6	476.3	489.9	495.3	508.3
42.5°	439.3	431.1	428.0	427.8	428.0	431.1	439.3	447.9	456.3	464.9	478.4
45°	394.7	386.9	381.7	382.2	381.7	386.9	394.7	397.6	404.7	421.9	429.5
47.5°	348.9	348.7	345.4	346.5	345.4	348.7	348.9	354.0	363.2	373.7	386.0
50°	327.2	323.6	321.3	321.8	321.3	323.6	327.2	331.4	336.6	342.0	360.9
52.5°	306.4	303.3	301.4	303.9	301.4	303.3	306.4	308.6	312.5	317.8	330.6
55°	272.2	268.6	268.0	267.4	268.0	268.6	272.2	275.1	279.8	284.0	289.9
57.5°	234.0	231.6	228.0	226.5	228.0	231.6	234.0	238.4	244.0	249.4	255.6
60°	206.5	201.8	195.8	195.3	195.8	201.8	206.5	214.2	216.5	224.8	231.9
62.5°	181.4	180.5	179.2	179.1	179.2	180.5	181.4	183.9	187.2	199.3	207.8
65°	159.2	158.5	159.2	159.7	159.2	158.5	159.2	160.3	161.0	162.1	165.7
67.5°	138.7	137.6	136.5	137.1	136.5	137.6	138.7	138.9	140.5	141.2	143.7
70°	123.1	122.4	121.9	121.9	121.9	122.4	123.1	124.2	125.5	126.6	129.6
72.5°	107.9	107.8	107.2	106.7	107.2	107.8	107.9	110.0	110.8	111.9	114.0
75°	86.4	85.2	85.2	85.2	85.2	85.2	86.4	86.9	87.6	89.3	90.5
77.5°	65.8	65.2	64.6	64.1	64.6	65.2	65.8	65.9	66.9	67.2	68.5
80°	52.1	51.5	50.9	50.9	50.9	51.5	52.1	52.7	52.7	54.4	53.9
82.5°	39.8	39.1	39.1	38.6	39.1	39.1	39.8	39.9	39.9	41.2	41.0
85°	21.3	21.8	21.3	22.5	21.3	21.8	21.3	20.7	21.3	22.5	22.5
87.5°	8.6	8.1	8.6	8.2	8.6	8.1	8.6	8.5	8.9	8.8	8.7
90°	11.9	12.1	12.4	12.6	12.4	12.1	11.9	11.8	11.4	10.9	10.3
92.5°	12.2	12.3	12.5	12.6	12.5	12.3	12.2	12.0	11.9	11.6	11.3
95°	20.3	20.2	20.2	20.0	20.2	20.2	20.3	20.4	20.2	19.7	19.2
97.5°	26.3	26.5	26.6	26.8	26.6	26.5	26.3	26.2	25.9	25.5	25.1
100°	30.6	30.8	30.9	31.2	30.9	30.8	30.6	30.3	29.9	29.0	28.2
102.5°	32.5	32.8	33.1	33.4	33.1	32.8	32.5	32.3	31.6	30.5	29.4
105°	34.2	34.5	35.0	35.4	35.0	34.5	34.2	33.7	32.9	31.8	30.7
107.5°	35.1	35.6	35.9	36.4	35.9	35.6	35.1	34.8	35.1	36.3	37.5
110°	35.5	35.9	36.4	36.7	36.4	35.9	35.5	35.1	40.0	50.4	60.7



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	36.1	36.5	36.8	37.1	36.8	36.5	36.1	35.8	54.5	92.2	129.9
115°	60.5	53.1	45.6	38.2	45.6	53.1	60.5	67.9	95.6	143.5	191.4
117.5°	229.2	204.7	180.3	155.8	180.3	204.7	229.2	253.7	271.7	283.3	294.9
120°	325.7	311.8	297.8	283.8	297.8	311.8	325.7	339.7	346.1	344.8	343.6
122.5°	362.4	359.6	357.0	354.2	357.0	359.6	362.4	365.1	366.0	365.3	364.5
125°	397.0	397.3	397.6	397.9	397.6	397.3	397.0	396.6	396.1	395.4	394.7
127.5°	425.3	425.3	425.3	425.4	425.3	425.3	425.3	425.2	424.6	423.6	422.5
130°	442.8	442.7	442.6	442.6	442.6	442.7	442.8	443.0	442.5	441.3	440.1
132.5°	459.6	459.5	459.4	459.3	459.4	459.5	459.6	459.7	459.3	458.3	457.4
135°	484.1	483.9	483.8	483.5	483.8	483.9	484.1	484.4	483.9	482.9	481.9
137.5°	506.6	506.2	506.0	505.6	506.0	506.2	506.6	506.9	506.7	505.6	504.6
140°	520.8	520.4	519.9	519.3	519.9	520.4	520.8	521.4	521.2	520.2	519.3
142.5°	534.3	533.8	533.2	532.7	533.2	533.8	534.3	534.8	534.7	533.8	533.0
145°	553.0	552.5	552.0	551.4	552.0	552.5	553.0	553.5	553.4	552.7	552.0
147.5°	569.3	568.8	568.4	567.9	568.4	568.8	569.3	569.6	569.6	569.1	568.6
150°	579.5	579.0	578.5	578.0	578.5	579.0	579.5	580.1	580.0	579.3	578.7
152.5°	588.6	587.9	587.2	586.6	587.2	587.9	588.6	589.2	589.3	588.7	588.1
155°	600.9	600.1	599.3	598.4	599.3	600.1	600.9	601.7	601.9	601.3	600.7
157.5°	611.7	610.9	610.1	609.3	610.1	610.9	611.7	612.6	612.6	611.9	611.2
160°	617.9	617.2	616.4	615.6	616.4	617.2	617.9	618.6	618.6	618.0	617.3
162.5°	623.6	622.7	621.8	620.9	621.8	622.7	623.6	624.5	624.6	623.8	623.1
165°	630.9	630.2	629.5	628.7	629.5	630.2	630.9	631.6	631.6	630.9	630.2
167.5°	636.4	635.5	634.5	633.6	634.5	635.5	636.4	637.4	637.5	636.8	636.0
170°	639.4	638.5	637.6	636.6	637.6	638.5	639.4	640.3	640.4	639.7	639.0
172.5°	641.7	640.7	639.8	638.8	639.8	640.7	641.7	642.6	642.7	641.9	641.2
175°	643.9	642.8	641.9	640.8	641.9	642.8	643.9	645.0	645.1	644.4	643.6
177.5°	644.3	643.5	642.7	642.0	642.7	643.5	644.3	645.0	645.1	644.5	643.9
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331711-940
 CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1637.4	1644.1	1654.0	1659.7	1669.2	1675.3	1678.6	1684.8	1688.1	1700.0	1712.3
5°	1546.0	1555.5	1572.0	1587.4	1604.0	1621.1	1633.5	1647.8	1660.8	1683.3	1706.9
7.5°	1441.2	1454.3	1480.0	1504.5	1533.3	1557.6	1579.0	1603.3	1625.0	1657.2	1690.7
10°	1362.6	1385.6	1419.4	1442.4	1480.3	1504.6	1538.3	1565.0	1595.1	1637.7	1675.6
12.5°	1294.9	1322.7	1349.8	1381.9	1415.9	1456.3	1493.3	1527.5	1563.4	1607.4	1651.9
15°	1172.1	1212.3	1254.3	1286.8	1333.0	1375.6	1418.8	1464.9	1508.7	1561.4	1619.3
17.5°	1014.0	1060.6	1131.2	1187.0	1241.2	1283.9	1337.4	1393.2	1444.8	1508.3	1572.9
20°	942.5	976.9	1024.8	1099.9	1181.5	1227.1	1281.6	1343.1	1402.2	1471.4	1540.7
22.5°	885.2	915.8	954.2	1012.8	1103.9	1166.0	1222.8	1285.3	1354.0	1424.6	1501.4
25°	803.4	824.7	865.0	912.3	975.1	1077.4	1139.5	1202.2	1276.8	1352.5	1440.1
27.5°	742.1	761.3	787.4	832.6	879.2	952.7	1051.5	1119.9	1194.2	1279.4	1370.3
30°	695.2	717.6	746.6	778.6	829.5	886.9	985.7	1065.0	1138.4	1225.9	1322.9
32.5°	661.1	678.9	703.6	736.0	778.4	833.4	912.3	1008.6	1080.1	1172.4	1273.7
35°	605.3	626.0	646.1	676.9	711.1	761.4	821.2	924.2	995.1	1086.3	1188.0
37.5°	559.2	571.9	594.1	618.5	654.7	692.2	744.0	836.3	913.2	1002.6	1106.8
40°	524.2	540.2	556.8	584.0	613.6	649.6	700.5	769.2	857.3	944.9	1046.6
42.5°	490.2	510.3	527.9	546.1	578.5	614.7	656.0	714.3	804.3	887.2	986.1
45°	449.1	462.1	480.5	500.5	527.2	557.9	594.6	645.5	731.9	803.4	896.3
47.5°	401.3	420.4	432.3	451.9	477.2	506.6	540.6	584.7	654.6	721.7	807.9
50°	368.6	388.2	405.3	423.0	445.5	473.9	502.3	544.9	601.1	671.5	752.0
52.5°	340.6	357.8	374.5	392.3	414.3	440.3	467.3	504.7	552.9	617.6	695.7
55°	302.4	313.0	330.1	347.9	367.4	392.3	418.3	449.7	491.1	545.5	608.9
57.5°	263.1	275.4	289.0	306.8	326.6	345.6	369.1	397.4	430.2	479.4	533.6
60°	240.8	250.3	261.5	279.8	298.2	315.3	337.9	361.5	392.3	434.9	481.0
62.5°	216.2	225.2	235.5	251.5	269.3	285.1	304.7	329.8	355.8	394.7	435.1
65°	175.1	188.2	198.2	212.4	227.2	243.8	259.1	279.3	302.4	333.1	369.2
67.5°	145.2	151.9	161.1	174.1	189.2	203.4	217.9	233.7	253.7	277.5	306.1
70°	132.0	134.3	136.1	148.5	162.7	176.9	190.5	205.3	222.5	242.0	266.8
72.5°	116.3	118.7	120.9	126.3	137.6	151.9	165.9	176.9	193.1	209.3	229.4
75°	92.3	95.9	97.6	100.6	104.7	114.2	127.2	137.9	147.3	159.7	175.8
77.5°	70.3	72.3	74.2	77.3	79.9	84.3	91.6	101.2	110.0	117.3	128.2
80°	55.6	56.2	58.6	59.7	63.3	66.3	69.8	77.5	86.4	89.3	97.0
82.5°	41.9	42.4	44.4	45.6	47.2	49.7	54.2	56.2	63.2	67.1	72.0
85°	23.1	22.5	24.3	24.3	25.4	26.7	27.8	30.8	32.5	37.3	38.4
87.5°	9.1	8.9	9.3	9.1	8.9	9.7	10.0	10.3	11.0	12.1	13.8
90°	9.8	9.3	8.5	7.7	6.9	6.0	5.0	3.8	2.8	1.6	0.4
92.5°	11.1	10.8	10.3	10.0	9.5	9.2	9.0	9.1	9.2	9.3	9.4
95°	18.6	18.2	17.4	16.7	16.0	15.2	16.6	20.0	23.5	26.8	30.2
97.5°	24.7	24.3	22.6	21.0	19.3	17.6	21.6	31.2	40.8	50.4	60.0
100°	27.4	26.5	24.8	23.0	21.2	19.5	25.7	39.9	54.0	68.2	82.4
102.5°	28.4	27.3	42.0	56.7	71.4	86.1	95.0	97.9	100.9	104.0	106.9
105°	29.5	28.4	56.6	84.9	113.1	141.3	153.9	150.8	147.7	144.5	141.4
107.5°	38.6	39.8	73.6	107.5	141.3	175.1	190.8	188.3	185.8	183.3	180.8
110°	71.1	81.4	111.3	141.2	171.1	201.0	214.8	212.7	210.5	208.3	206.2



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	167.6	205.5	212.8	220.2	227.6	235.0	237.6	235.8	233.8	231.9	230.0
115°	239.2	287.1	284.5	282.0	279.4	276.8	274.6	272.9	271.1	269.3	267.6
117.5°	306.5	318.0	316.3	314.5	312.7	310.9	309.1	307.1	305.1	303.2	301.2
120°	342.3	341.1	339.2	337.4	335.6	333.7	332.0	330.4	328.9	327.3	325.7
122.5°	363.8	363.1	361.1	359.0	357.0	355.0	353.1	351.5	349.9	348.2	346.6
125°	394.0	393.2	391.3	389.3	387.4	385.4	383.7	382.4	381.0	379.7	378.4
127.5°	421.4	420.4	418.9	417.5	416.0	414.6	413.0	411.5	410.1	408.6	407.1
130°	439.1	437.9	436.8	435.6	434.5	433.4	431.9	430.3	428.6	427.0	425.3
132.5°	456.4	455.4	454.2	453.2	452.0	450.8	449.6	448.2	446.7	445.3	444.0
135°	480.8	479.7	478.8	478.0	477.0	476.1	474.7	473.1	471.4	469.8	468.1
137.5°	503.6	502.6	501.5	500.5	499.4	498.4	497.2	496.1	494.9	493.7	492.7
140°	518.4	517.5	516.3	515.2	514.1	512.9	511.9	511.1	510.3	509.4	508.6
142.5°	532.1	531.3	529.9	528.6	527.4	526.0	525.0	524.2	523.5	522.8	522.0
145°	551.3	550.5	548.8	547.0	545.3	543.5	542.7	542.8	542.9	543.0	543.1
147.5°	568.0	567.5	565.7	564.0	562.2	560.5	559.8	560.3	560.6	561.0	561.4
150°	578.1	577.5	575.9	574.2	572.6	570.9	570.4	571.1	571.9	572.6	573.3
152.5°	587.5	586.8	585.2	583.7	582.1	580.5	580.1	580.9	581.8	582.6	583.4
155°	600.0	599.4	598.2	596.9	595.7	594.4	594.2	595.2	596.1	597.1	598.0
157.5°	610.5	609.8	608.9	608.1	607.2	606.4	606.3	607.1	607.9	608.7	609.4
160°	616.8	616.2	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2
162.5°	622.4	621.7	621.2	620.6	620.1	619.6	619.6	620.2	620.8	621.4	622.1
165°	629.5	628.7	628.4	628.0	627.8	627.5	627.6	628.2	628.8	629.5	630.1
167.5°	635.3	634.5	634.3	634.0	633.6	633.4	633.6	634.2	634.8	635.4	636.1
170°	638.3	637.6	637.3	637.1	636.9	636.7	636.9	637.6	638.2	638.8	639.4
172.5°	640.5	639.8	639.5	639.4	639.2	638.9	639.2	639.8	640.4	641.1	641.7
175°	642.9	642.2	641.9	641.8	641.6	641.4	641.6	642.4	643.1	643.8	644.5
177.5°	643.4	642.7	642.7	642.6	642.5	642.4	642.7	643.3	643.8	644.4	645.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1712.7	1714.1	1723.6	1727.9	1736.4	1739.7	1743.5	1742.6	1742.6	1744.5	1757.7
5°	1716.4	1728.2	1746.0	1763.2	1779.7	1793.9	1803.4	1812.8	1816.4	1833.5	1849.0
7.5°	1710.2	1732.1	1761.4	1787.5	1818.9	1843.3	1863.8	1882.0	1894.6	1919.6	1945.2
10°	1702.2	1733.0	1766.1	1799.8	1843.0	1875.5	1908.7	1934.1	1942.4	1979.7	2001.0
12.5°	1686.1	1727.2	1769.4	1813.1	1855.3	1900.1	1936.6	1962.0	1991.2	2024.6	2064.0
15°	1662.0	1709.3	1764.3	1820.5	1880.9	1935.3	1974.3	2018.7	2050.7	2087.4	2121.6
17.5°	1627.3	1688.3	1758.2	1823.3	1893.1	1951.5	2005.3	2047.8	2070.3	2091.2	2096.3
20°	1599.8	1665.5	1747.8	1824.7	1894.5	1961.9	2015.2	2050.7	2056.6	2057.2	2025.9
22.5°	1570.0	1644.2	1730.3	1809.0	1892.6	1967.6	2009.0	2024.2	2000.7	1960.6	1900.0
25°	1515.2	1601.1	1701.0	1790.9	1882.0	1953.0	1967.3	1940.6	1858.4	1772.0	1662.6
27.5°	1455.8	1552.3	1659.5	1759.4	1856.5	1900.5	1869.9	1773.9	1625.8	1497.0	1341.0
30°	1412.3	1520.5	1625.9	1737.7	1827.7	1846.6	1776.2	1634.8	1462.0	1267.9	1112.3
32.5°	1362.6	1476.0	1591.8	1707.4	1782.7	1764.2	1647.9	1473.8	1271.2	1080.5	933.4
35°	1291.6	1408.7	1533.6	1649.6	1697.5	1617.6	1443.7	1217.0	1010.0	831.9	730.7
37.5°	1209.6	1337.1	1467.0	1573.4	1570.0	1436.9	1200.0	966.1	792.0	686.7	614.7
40°	1151.4	1280.3	1420.6	1510.5	1472.0	1298.7	1041.9	821.2	694.0	610.0	557.3
42.5°	1095.6	1224.9	1364.2	1435.7	1368.9	1155.7	899.9	727.0	622.1	556.5	513.8
45°	1000.5	1137.2	1266.1	1305.8	1186.2	951.4	727.7	602.4	532.5	483.9	454.4
47.5°	907.6	1042.1	1159.8	1160.5	998.8	771.5	613.9	521.3	461.6	424.1	402.6
50°	850.8	978.6	1077.4	1062.0	878.6	686.3	549.0	469.2	419.5	390.5	368.0
52.5°	786.9	910.9	996.5	952.7	776.9	604.0	490.8	423.7	382.5	357.4	337.2
55°	694.0	804.1	864.4	798.2	633.6	502.3	414.7	362.1	331.4	310.0	292.8
57.5°	602.8	693.6	731.6	654.3	521.9	416.5	350.9	311.3	280.8	265.6	256.6
60°	545.5	623.0	649.6	564.5	453.8	364.4	310.6	273.9	251.5	241.4	232.6
62.5°	489.2	552.5	563.5	485.4	395.6	319.1	272.8	241.7	226.9	217.2	208.8
65°	405.9	451.5	446.1	383.4	313.0	253.2	219.5	200.5	189.3	175.8	161.0
67.5°	334.1	361.9	345.2	298.2	238.9	196.8	174.8	160.4	146.5	133.6	130.2
70°	288.7	304.7	287.0	243.8	195.8	165.1	147.3	130.2	121.9	119.0	113.6
72.5°	245.2	250.7	231.6	194.6	159.3	136.7	119.4	109.8	105.3	102.8	99.4
75°	184.0	179.9	163.3	134.3	110.7	95.2	90.0	86.4	83.5	81.1	79.3
77.5°	129.2	123.1	108.4	89.4	77.0	69.7	66.5	64.6	63.2	62.0	60.2
80°	97.0	92.9	78.1	63.9	58.6	55.0	53.2	50.9	50.9	49.7	47.9
82.5°	71.0	66.3	53.5	46.8	43.9	41.7	40.5	39.1	38.6	38.8	37.5
85°	37.3	30.1	26.7	25.4	23.6	22.5	23.1	21.8	21.8	21.8	21.3
87.5°	11.7	9.5	9.3	9.0	9.7	9.9	9.5	9.7	10.3	10.0	10.6
90°	1.6	2.8	3.8	5.0	6.0	6.9	7.7	8.5	9.3	9.8	10.3
92.5°	9.3	9.2	9.1	9.0	9.2	9.5	10.0	10.3	10.8	11.1	11.3
95°	26.8	23.5	20.0	16.6	15.2	16.0	16.7	17.4	18.2	18.6	19.2
97.5°	50.4	40.8	31.2	21.6	17.6	19.3	21.0	22.6	24.3	24.7	25.1
100°	68.2	54.0	39.9	25.7	19.5	21.2	23.0	24.8	26.5	27.4	28.2
102.5°	104.0	100.9	97.9	95.0	86.1	71.4	56.7	42.0	27.3	28.4	29.4
105°	144.5	147.7	150.8	153.9	141.3	113.1	84.9	56.6	28.4	29.5	30.7
107.5°	183.3	185.8	188.3	190.8	175.1	141.3	107.5	73.6	39.8	38.6	37.5
110°	208.3	210.5	212.7	214.8	201.0	171.1	141.2	111.3	81.4	71.1	60.7



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	231.9	233.8	235.8	237.6	235.0	227.6	220.2	212.8	205.5	167.6	129.9
115°	269.3	271.1	272.9	274.6	276.8	279.4	282.0	284.5	287.1	239.2	191.4
117.5°	303.2	305.1	307.1	309.1	310.9	312.7	314.5	316.3	318.0	306.5	294.9
120°	327.3	328.9	330.4	332.0	333.7	335.6	337.4	339.2	341.1	342.3	343.6
122.5°	348.2	349.9	351.5	353.1	355.0	357.0	359.0	361.1	363.1	363.8	364.5
125°	379.7	381.0	382.4	383.7	385.4	387.4	389.3	391.3	393.2	394.0	394.7
127.5°	408.6	410.1	411.5	413.0	414.6	416.0	417.5	418.9	420.4	421.4	422.5
130°	427.0	428.6	430.3	431.9	433.4	434.5	435.6	436.8	437.9	439.1	440.1
132.5°	445.3	446.7	448.2	449.6	450.8	452.0	453.2	454.2	455.4	456.4	457.4
135°	469.8	471.4	473.1	474.7	476.1	477.0	478.0	478.8	479.7	480.8	481.9
137.5°	493.7	494.9	496.1	497.2	498.4	499.4	500.5	501.5	502.6	503.6	504.6
140°	509.4	510.3	511.1	511.9	512.9	514.1	515.2	516.3	517.5	518.4	519.3
142.5°	522.8	523.5	524.2	525.0	526.0	527.4	528.6	529.9	531.3	532.1	533.0
145°	543.0	542.9	542.8	542.7	543.5	545.3	547.0	548.8	550.5	551.3	552.0
147.5°	561.0	560.6	560.3	559.8	560.5	562.2	564.0	565.7	567.5	568.0	568.6
150°	572.6	571.9	571.1	570.4	570.9	572.6	574.2	575.9	577.5	578.1	578.7
152.5°	582.6	581.8	580.9	580.1	580.5	582.1	583.7	585.2	586.8	587.5	588.1
155°	597.1	596.1	595.2	594.2	594.4	595.7	596.9	598.2	599.4	600.0	600.7
157.5°	608.7	607.9	607.1	606.3	606.4	607.2	608.1	608.9	609.8	610.5	611.2
160°	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	616.8	617.3
162.5°	621.4	620.8	620.2	619.6	619.6	620.1	620.6	621.2	621.7	622.4	623.1
165°	629.5	628.8	628.2	627.6	627.5	627.8	628.0	628.4	628.7	629.5	630.2
167.5°	635.4	634.8	634.2	633.6	633.4	633.6	634.0	634.3	634.5	635.3	636.0
170°	638.8	638.2	637.6	636.9	636.7	636.9	637.1	637.3	637.6	638.3	639.0
172.5°	641.1	640.4	639.8	639.2	638.9	639.2	639.4	639.5	639.8	640.5	641.2
175°	643.8	643.1	642.4	641.6	641.4	641.6	641.8	641.9	642.2	642.9	643.6
177.5°	644.4	643.8	643.3	642.7	642.4	642.5	642.6	642.7	642.7	643.4	643.9
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1762.5	1768.6	1771.4	1771.4	1774.8	1773.3	1771.9
5°	1863.8	1875.0	1877.3	1888.0	1895.7	1893.3	1894.5
7.5°	1964.4	1982.5	2000.4	2008.6	2009.8	2014.6	2016.3
10°	2026.4	2041.2	2069.0	2064.8	2085.6	2097.4	2077.9
12.5°	2086.1	2106.0	2125.4	2130.7	2142.4	2146.2	2138.5
15°	2140.0	2150.7	2151.9	2148.9	2152.4	2149.5	2138.2
17.5°	2089.6	2072.3	2037.3	2020.7	2007.6	1988.2	1980.4
20°	2006.3	1955.4	1896.2	1872.6	1844.8	1790.4	1803.4
22.5°	1826.5	1768.4	1709.3	1640.2	1607.2	1555.6	1552.5
25°	1546.6	1446.6	1336.6	1259.6	1214.7	1163.2	1140.7
27.5°	1202.5	1076.6	986.4	940.8	899.2	858.4	856.8
30°	976.2	881.5	811.7	772.7	747.3	730.1	733.7
32.5°	822.9	758.0	711.0	678.5	659.7	646.8	646.6
35°	672.7	628.3	598.2	584.5	571.0	561.5	562.0
37.5°	575.7	549.0	532.3	517.2	508.7	504.1	501.5
40°	526.0	504.1	491.1	482.2	475.1	468.6	467.4
42.5°	486.7	468.6	455.6	448.6	441.9	437.4	436.1
45°	431.9	417.1	405.3	397.6	394.7	390.5	390.5
47.5°	384.2	369.7	360.4	355.6	350.5	347.8	347.7
50°	352.0	340.8	332.5	329.6	325.4	323.6	323.1
52.5°	323.2	314.8	308.9	306.8	305.1	302.8	303.2
55°	284.0	279.3	276.9	275.1	272.2	268.6	271.0
57.5°	251.0	246.9	240.6	235.0	232.3	229.8	230.8
60°	227.8	219.5	211.2	204.7	203.0	197.6	197.6
62.5°	198.4	186.8	176.6	173.0	171.2	168.7	168.3
65°	152.7	147.9	145.5	143.2	142.0	142.0	140.8
67.5°	126.5	124.6	122.0	121.5	120.2	119.8	119.5
70°	111.8	109.4	108.3	107.7	106.5	107.1	105.3
72.5°	97.6	95.8	95.5	94.0	93.3	93.4	92.0
75°	77.0	77.0	76.3	75.7	74.5	73.9	74.5
77.5°	59.2	59.3	58.2	58.1	58.0	58.1	57.5
80°	47.3	47.9	47.3	46.7	46.2	46.7	46.2
82.5°	37.4	36.6	36.5	36.3	36.2	35.8	35.8
85°	21.3	21.8	21.3	20.7	20.7	20.7	21.3
87.5°	10.3	10.3	10.4	10.4	10.4	10.5	10.1
90°	10.9	11.4	11.8	11.9	12.1	12.4	12.6
92.5°	11.6	11.9	12.0	12.2	12.3	12.5	12.6
95°	19.7	20.2	20.4	20.3	20.2	20.2	20.0
97.5°	25.5	25.9	26.2	26.3	26.5	26.6	26.8
100°	29.0	29.9	30.3	30.6	30.8	30.9	31.2
102.5°	30.5	31.6	32.3	32.5	32.8	33.1	33.4
105°	31.8	32.9	33.7	34.2	34.5	35.0	35.4
107.5°	36.3	35.1	34.8	35.1	35.6	35.9	36.4
110°	50.4	40.0	35.1	35.5	35.9	36.4	36.7



TEST NUMBER: P331711-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	92.2	54.5	35.8	36.1	36.5	36.8	37.1
115°	143.5	95.6	67.9	60.5	53.1	45.6	38.2
117.5°	283.3	271.7	253.7	229.2	204.7	180.3	155.8
120°	344.8	346.1	339.7	325.7	311.8	297.8	283.8
122.5°	365.3	366.0	365.1	362.4	359.6	357.0	354.2
125°	395.4	396.1	396.6	397.0	397.3	397.6	397.9
127.5°	423.6	424.6	425.2	425.3	425.3	425.3	425.4
130°	441.3	442.5	443.0	442.8	442.7	442.6	442.6
132.5°	458.3	459.3	459.7	459.6	459.5	459.4	459.3
135°	482.9	483.9	484.4	484.1	483.9	483.8	483.5
137.5°	505.6	506.7	506.9	506.6	506.2	506.0	505.6
140°	520.2	521.2	521.4	520.8	520.4	519.9	519.3
142.5°	533.8	534.7	534.8	534.3	533.8	533.2	532.7
145°	552.7	553.4	553.5	553.0	552.5	552.0	551.4
147.5°	569.1	569.6	569.6	569.3	568.8	568.4	567.9
150°	579.3	580.0	580.1	579.5	579.0	578.5	578.0
152.5°	588.7	589.3	589.2	588.6	587.9	587.2	586.6
155°	601.3	601.9	601.7	600.9	600.1	599.3	598.4
157.5°	611.9	612.6	612.6	611.7	610.9	610.1	609.3
160°	618.0	618.6	618.6	617.9	617.2	616.4	615.6
162.5°	623.8	624.6	624.5	623.6	622.7	621.8	620.9
165°	630.9	631.6	631.6	630.9	630.2	629.5	628.7
167.5°	636.8	637.5	637.4	636.4	635.5	634.5	633.6
170°	639.7	640.4	640.3	639.4	638.5	637.6	636.6
172.5°	641.9	642.7	642.6	641.7	640.7	639.8	638.8
175°	644.4	645.1	645.0	643.9	642.8	641.9	640.8
177.5°	644.5	645.1	645.0	644.3	643.5	642.7	642.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1

(END OF REPORT)