

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331715-940

Luminaire Tested: **SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331715-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4376.5 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331715-940
CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331715-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53
2	92	85	79	74	86	80	75	70	70	66	63	62	59	56	53	51	49	45
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37	34
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33	30
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29	27
7	62	49	41	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24	22
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	20
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331715-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.8
10°-20°	336.0	7.7
20°-30°	471.9	10.8
30°-40°	514.6	11.8
40°-50°	473.1	10.8
50°-60°	371.6	8.5
60°-70°	242.3	5.5
70°-80°	124.9	2.9
80°-90°	34.8	0.8
90°-100°	38.2	0.9
100°-110°	118.6	2.7
110°-120°	202.7	4.6
120°-130°	266.6	6.1
130°-140°	299.2	6.8
140°-150°	293.4	6.7
150°-160°	246.1	5.6
160°-170°	163.2	3.7
170°-180°	57.0	1.3
0°-30°	930.3	21.3
0°-40°	1444.9	33.0
0°-60°	2289.6	52.3
0°-90°	2691.6	61.5
90°-120°	359.5	8.2
90°-150°	1218.6	27.8
90°-180°	1685.0	38.5
0°-180°	4376.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	0	7	18	17	17	3
95°	26	31	32	32	32	30
105°	109	111	112	113	113	115
115°	203	206	206	205	203	201
125°	296	300	299	298	297	264
135°	383	388	390	389	387	296
145°	465	468	471	472	470	290
155°	531	533	534	537	536	244
165°	578	578	578	581	579	163
175°	602	600	599	602	600	57
180°	602	602	602	602	602	



TEST NUMBER: P331715-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.2	13.8	12.4	11.0	9.6	9.2	9.6	10.2	10.6	11.1	10.9
90°	0.5	1.9	3.2	4.5	6.0	7.8	10.3	12.8	15.3	17.8	17.6
92.5°	9.1	10.1	11.1	12.0	13.0	13.8	14.4	15.0	15.6	16.1	16.2
95°	26.5	27.6	28.7	29.9	30.9	31.7	31.8	32.1	32.3	32.5	32.5
97.5°	48.3	49.3	50.3	51.3	52.3	53.0	53.4	53.9	54.3	54.8	54.8
100°	64.6	65.5	66.3	67.3	68.2	68.8	69.2	69.5	69.8	70.2	70.2
102.5°	81.7	82.4	83.1	83.8	84.5	85.2	85.6	86.0	86.4	86.9	86.9
105°	109.3	109.7	110.0	110.3	110.7	110.9	111.2	111.4	111.6	111.9	112.1
107.5°	137.2	137.7	138.2	138.7	139.2	139.5	139.5	139.5	139.5	139.5	139.6
110°	155.1	155.8	156.4	157.1	157.8	158.1	158.1	158.1	158.1	158.1	158.1



TEST NUMBER: P331715-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	174.6	175.3	175.9	176.6	177.4	177.6	177.5	177.5	177.4	177.3	177.0
115°	203.4	204.1	204.7	205.5	206.1	206.3	206.1	205.9	205.6	205.5	205.4
117.5°	232.1	233.0	233.9	234.8	235.7	235.9	235.2	234.5	233.9	233.3	233.0
120°	251.2	252.1	253.0	253.9	254.9	254.9	253.9	253.0	252.1	251.2	251.2
122.5°	268.7	269.7	270.9	272.0	273.0	273.2	272.6	272.0	271.3	270.7	270.5
125°	296.0	296.9	298.0	299.0	300.0	300.3	300.0	299.7	299.3	299.0	298.6
127.5°	322.4	323.8	325.0	326.4	327.6	328.1	327.7	327.3	326.9	326.5	326.0
130°	339.2	340.6	342.1	343.6	345.0	345.6	345.4	345.2	345.0	344.7	344.6
132.5°	357.8	359.1	360.3	361.5	362.7	363.3	363.4	363.4	363.5	363.5	363.0
135°	382.9	384.1	385.4	386.6	387.9	388.6	388.8	389.1	389.3	389.5	389.4
137.5°	409.2	410.3	411.3	412.3	413.3	413.9	414.3	414.6	414.8	415.1	415.0
140°	425.1	426.1	427.1	428.1	429.2	430.0	430.5	431.1	431.7	432.2	432.2
142.5°	441.4	442.4	443.4	444.4	445.4	446.1	446.6	446.9	447.3	447.6	447.7
145°	464.8	465.6	466.4	467.2	468.0	468.7	469.3	470.0	470.7	471.4	471.4
147.5°	485.6	486.5	487.5	488.5	489.4	490.1	490.5	491.0	491.4	492.0	492.1
150°	499.9	500.5	501.2	501.9	502.6	503.1	503.5	504.0	504.4	505.0	505.2
152.5°	512.5	513.2	513.8	514.5	515.1	515.8	516.3	516.8	517.4	518.0	518.4
155°	531.4	531.7	532.1	532.4	532.7	533.1	533.4	533.8	534.0	534.4	535.0
157.5°	547.5	547.8	548.0	548.2	548.5	548.7	548.8	549.1	549.3	549.5	550.3
160°	557.3	557.5	557.8	557.9	558.2	558.4	558.5	558.6	558.7	558.8	559.5
162.5°	566.2	566.3	566.3	566.4	566.4	566.5	566.6	566.8	566.9	566.9	567.8
165°	578.2	578.0	577.9	577.8	577.7	577.7	577.7	577.7	577.7	577.7	578.5
167.5°	588.1	587.8	587.5	587.1	586.7	586.6	586.6	586.6	586.5	586.5	587.3
170°	593.4	593.1	592.7	592.4	592.1	591.8	591.7	591.6	591.5	591.4	592.2
172.5°	597.1	596.7	596.4	596.0	595.8	595.5	595.4	595.3	595.1	595.0	595.8
175°	601.5	601.2	600.8	600.6	600.2	599.9	599.7	599.5	599.2	599.0	599.8
177.5°	603.4	603.1	602.8	602.5	602.3	602.1	601.9	601.7	601.5	601.4	601.9
180°	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5



TEST NUMBER: P331715-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	10.6	10.3	10.1	10.0	10.0	10.1	10.1	10.1
90°	17.4	17.1	16.9	16.9	16.9	17.0	17.2	17.3
92.5°	16.2	16.3	16.3	16.4	16.4	16.4	16.5	16.5
95°	32.5	32.5	32.5	32.5	32.2	32.0	31.7	31.6
97.5°	54.8	54.8	54.8	54.7	54.7	54.7	54.7	54.6
100°	70.2	70.2	70.2	70.1	70.0	69.9	69.8	69.6
102.5°	87.0	87.1	87.2	87.2	87.1	86.9	86.9	86.8
105°	112.4	112.5	112.8	112.9	112.9	112.9	112.9	112.9
107.5°	139.6	139.7	139.8	139.6	139.0	138.6	138.0	137.5
110°	158.1	158.1	158.1	158.0	157.7	157.3	156.9	156.6



TEST NUMBER: P331715-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	176.7	176.5	176.2	175.9	175.7	175.4	175.1	175.0
115°	205.2	205.1	205.0	204.7	204.4	204.1	203.8	203.4
117.5°	232.7	232.5	232.2	231.9	231.6	231.2	230.9	230.5
120°	251.2	251.2	251.2	251.0	250.7	250.4	250.0	249.7
122.5°	270.2	269.9	269.7	269.4	269.1	268.9	268.7	268.4
125°	298.3	298.0	297.7	297.4	297.3	297.2	297.0	296.9
127.5°	325.7	325.2	324.9	324.4	324.0	323.7	323.3	323.0
130°	344.3	344.1	343.8	343.5	343.0	342.6	342.1	341.7
132.5°	362.5	361.9	361.5	361.1	360.7	360.3	360.0	359.6
135°	389.3	389.1	389.1	388.8	388.5	388.2	387.8	387.4
137.5°	414.9	414.8	414.7	414.5	414.0	413.6	413.1	412.7
140°	432.2	432.2	432.2	432.0	431.5	431.1	430.6	430.2
142.5°	447.8	447.9	448.0	447.8	447.4	446.9	446.5	446.0
145°	471.6	471.7	471.8	471.6	471.2	470.7	470.3	469.8
147.5°	492.4	492.7	492.9	492.8	492.4	492.0	491.5	491.1
150°	505.6	506.0	506.3	506.3	506.0	505.6	505.2	505.0
152.5°	518.8	519.2	519.7	519.7	519.2	518.8	518.4	518.0
155°	535.6	536.1	536.7	536.8	536.5	536.1	535.7	535.5
157.5°	551.0	551.8	552.6	552.7	552.1	551.6	551.1	550.5
160°	560.2	560.9	561.5	561.7	561.2	560.8	560.3	559.8
162.5°	568.5	569.3	570.1	570.2	569.6	569.1	568.6	568.0
165°	579.3	580.1	580.8	580.9	580.3	579.8	579.3	578.6
167.5°	588.1	588.9	589.7	589.8	589.2	588.6	588.0	587.4
170°	593.0	593.8	594.5	594.6	593.9	593.3	592.5	591.9
172.5°	596.6	597.4	598.2	598.2	597.6	596.9	596.2	595.6
175°	600.6	601.4	602.2	602.3	601.5	600.8	600.2	599.5
177.5°	602.4	603.0	603.5	603.5	603.0	602.4	601.9	601.4
180°	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5

(END OF REPORT)