

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331304-935

Luminaire Tested: **SA2XXDIP-C485D725U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331304-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4079.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	45	39				39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				33
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				29
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				25
5	69	57	50	44	63	53	46	41	45	40	36	37	34	30	30	28	25	22				22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20				20
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18				18
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18	16				16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14				14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13508	13508	13508	13508
5°	15144	13598	12049	13598
10°	17354	13485	10427	13485
15°	19199	13237	9212	13237
20°	18907	12972	8399	12972
25°	17047	12618	7883	12618
30°	14087	12055	7506	12055
35°	10267	11466	7238	11466
40°	8201	10768	7088	10768
45°	7165	9965	6887	9965
50°	6737	9183	6752	9183
55°	6210	8391	6570	8391
60°	5690	7550	6290	7550
65°	5184	6793	6021	6793
70°	4707	6057	5618	6057
75°	4173	5234	4972	5234
80°	3589	4342	3998	4342
85°	3223	3223	2371	3223



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	2.0
10°-20°	231.6	5.7
20°-30°	336.2	8.2
30°-40°	354.8	8.7
40°-50°	314.1	7.7
50°-60°	250.7	6.1
60°-70°	170.4	4.2
70°-80°	87.4	2.1
80°-90°	24.2	0.6
90°-100°	50.5	1.2
100°-110°	157.0	3.8
110°-120°	268.3	6.6
120°-130°	352.8	8.6
130°-140°	396.0	9.7
140°-150°	388.3	9.5
150°-160°	325.7	8.0
160°-170°	216.0	5.3
170°-180°	75.5	1.9
0°-30°	647.5	15.9
0°-40°	1002.3	24.6
0°-60°	1567.1	38.4
0°-90°	1849.1	45.3
90°-120°	475.8	11.7
90°-150°	1612.8	39.5
90°-180°	2230.0	54.7
0°-180°	4079.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	837	837	837	837	837	
5°	934	839	743	839	934	93
15°	1149	792	551	792	1149	317
25°	957	708	442	708	957	432
35°	521	582	367	582	521	339
45°	314	436	302	436	314	247
55°	221	298	233	298	221	198
65°	136	178	158	178	136	135
75°	67	84	80	84	67	71
85°	17	17	13	17	17	20
90°	23	1	23	1	23	11
95°	42	35	42	35	42	47
105°	149	145	149	145	149	157
115°	269	269	269	269	269	266
125°	393	392	393	392	393	350
135°	513	507	513	507	513	395
145°	622	615	622	615	622	388
155°	709	703	709	703	709	326
165°	766	765	766	765	766	216
175°	794	796	794	796	794	75
180°	798	798	798	798	798	



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	875.3	875.6	876.0	871.9	871.4	871.4	867.8	864.7	861.1	856.2	856.7
5°	934.4	938.0	939.3	935.4	929.6	928.9	923.5	914.5	906.1	899.4	894.6
7.5°	1005.0	1006.4	1003.3	998.2	993.9	986.2	976.0	966.0	952.1	939.3	929.8
10°	1058.5	1060.5	1055.0	1047.6	1041.5	1032.5	1017.7	1002.5	984.3	966.6	952.4
12.5°	1099.2	1104.0	1096.9	1096.0	1085.5	1073.2	1055.5	1047.8	1022.1	997.5	982.2
15°	1148.6	1148.2	1148.9	1142.8	1135.1	1133.2	1114.5	1094.2	1057.9	1043.4	1018.3
17.5°	1134.3	1139.2	1141.4	1141.3	1141.2	1140.0	1133.9	1121.2	1102.9	1079.5	1050.6
20°	1100.4	1106.7	1107.8	1115.2	1119.3	1124.8	1127.0	1123.5	1112.2	1092.6	1067.6
22.5°	1047.8	1049.6	1052.7	1064.2	1073.2	1086.9	1094.1	1106.0	1101.6	1092.1	1071.2
25°	956.9	953.7	964.9	970.8	991.6	1013.5	1029.2	1046.6	1062.0	1071.4	1065.3
27.5°	847.7	842.9	859.8	875.1	892.1	915.8	940.3	969.3	993.4	1023.6	1034.0
30°	755.6	758.5	774.6	791.0	816.7	850.2	877.8	909.6	944.1	977.8	1001.3
32.5°	656.3	667.4	677.6	702.7	725.4	762.7	803.2	843.0	886.0	924.3	960.6
35°	520.9	533.7	547.9	566.3	598.1	635.1	674.6	728.3	786.9	839.2	882.4
37.5°	438.4	436.4	444.5	457.8	483.5	513.4	558.9	612.0	680.9	742.4	803.2
40°	389.1	387.8	393.6	405.8	425.4	447.3	487.2	533.7	597.8	673.0	745.4
42.5°	355.1	355.9	359.1	367.7	381.2	399.2	429.0	468.7	527.3	598.1	675.9
45°	313.8	316.1	319.6	323.8	331.5	346.3	363.0	391.3	437.6	496.8	573.3
47.5°	284.1	284.2	287.7	291.4	296.0	304.4	318.1	335.8	368.4	416.6	482.4
50°	268.2	265.9	268.5	271.4	276.2	282.0	291.0	307.7	329.6	368.5	423.4
52.5°	248.7	248.7	251.0	252.1	256.4	262.2	270.4	282.0	301.8	332.3	377.5
55°	220.6	222.2	223.5	225.4	229.3	233.4	239.9	247.6	263.0	285.9	319.3
57.5°	194.2	194.8	196.0	199.7	202.2	206.0	212.1	219.1	229.1	246.1	271.2
60°	176.2	176.2	178.7	180.4	183.6	187.4	192.3	199.1	208.0	221.9	242.1
62.5°	159.7	159.5	160.5	163.2	165.6	169.2	174.0	179.8	188.2	200.5	217.1
65°	135.7	135.1	137.0	137.6	140.2	143.7	147.6	153.7	160.5	169.4	184.3
67.5°	112.5	113.3	114.3	115.5	117.0	120.7	123.3	127.6	133.3	140.8	150.8
70°	99.7	99.7	99.7	100.7	102.5	104.5	107.1	110.6	116.1	122.5	131.5
72.5°	85.2	86.3	87.3	86.8	89.2	90.3	93.4	95.4	100.7	104.8	112.7
75°	66.9	66.9	66.9	68.4	69.5	70.4	72.3	74.3	76.9	82.0	86.2
77.5°	49.9	49.8	50.1	50.5	51.5	52.7	53.2	55.0	57.3	59.8	63.3
80°	38.6	39.3	39.5	40.2	40.2	40.8	41.2	43.4	45.0	46.7	48.9
82.5°	29.9	30.0	30.0	30.1	30.4	30.8	31.6	32.4	32.9	34.3	36.0
85°	17.4	17.0	17.0	17.7	17.4	17.4	18.0	18.7	18.7	18.9	20.0
87.5°	11.3	11.2	11.5	11.2	11.1	11.5	11.5	11.3	11.6	11.9	11.5
90°	22.9	22.7	22.6	22.5	22.3	22.4	22.6	23.0	23.2	23.6	20.2
92.5°	21.8	21.8	21.8	21.7	21.7	21.6	21.6	21.5	21.4	21.4	20.7
95°	41.8	42.0	42.4	42.6	43.0	43.0	43.0	43.0	43.0	43.0	42.8
97.5°	72.2	72.3	72.3	72.4	72.4	72.4	72.4	72.4	72.4	72.4	71.8
100°	92.2	92.4	92.5	92.6	92.8	92.9	92.9	92.9	92.9	92.9	92.4
102.5°	114.8	114.9	115.1	115.3	115.4	115.5	115.3	115.2	115.0	114.9	114.3
105°	149.4	149.4	149.4	149.4	149.4	149.3	149.0	148.7	148.4	148.1	147.7
107.5°	182.0	182.7	183.4	184.1	184.8	185.0	184.9	184.8	184.7	184.5	184.5
110°	207.2	207.8	208.2	208.6	209.1	209.3	209.3	209.3	209.3	209.3	209.3



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.5	231.9	232.1	232.5	232.8	233.2	233.5	233.8	234.3	234.6	234.7
115°	269.2	269.7	270.1	270.5	271.0	271.3	271.5	271.6	271.7	271.9	272.2
117.5°	305.1	305.6	306.0	306.5	306.9	307.3	307.7	308.1	308.4	308.8	309.6
120°	330.5	330.9	331.3	331.7	332.3	332.4	332.4	332.4	332.4	332.4	333.6
122.5°	355.2	355.5	355.9	356.2	356.5	356.9	357.2	357.6	357.9	358.3	359.1
125°	393.0	393.2	393.3	393.5	393.6	393.9	394.3	394.9	395.3	395.7	396.1
127.5°	427.5	428.0	428.4	429.0	429.4	429.9	430.4	431.0	431.5	432.0	432.6
130°	452.3	452.9	453.5	454.0	454.6	455.1	455.4	455.7	456.0	456.3	456.6
132.5°	476.0	476.4	476.9	477.3	477.9	478.5	479.1	479.7	480.4	481.0	481.0
135°	512.8	513.2	513.8	514.2	514.6	514.9	515.1	515.2	515.4	515.5	515.2
137.5°	546.2	546.8	547.4	548.0	548.6	549.0	549.1	549.2	549.3	549.4	549.1
140°	569.4	570.0	570.6	571.2	571.7	572.0	572.0	572.0	572.0	572.0	571.3
142.5°	590.4	591.0	591.5	592.1	592.7	593.0	592.9	592.7	592.6	592.5	592.0
145°	621.8	622.4	623.0	623.6	624.2	624.5	624.3	624.1	624.1	623.9	622.9
147.5°	650.0	650.6	651.1	651.7	652.3	652.4	652.0	651.7	651.3	651.1	650.5
150°	668.3	668.7	669.2	669.6	670.1	670.1	669.6	669.2	668.7	668.3	667.7
152.5°	685.5	686.0	686.6	687.3	687.8	687.8	687.3	686.6	686.0	685.5	684.8
155°	708.7	709.1	709.6	710.0	710.5	710.3	709.6	708.8	708.1	707.3	706.9
157.5°	728.6	729.3	730.0	730.7	731.4	731.3	730.3	729.3	728.2	727.2	726.9
160°	741.0	741.6	742.2	742.8	743.4	743.2	742.4	741.4	740.5	739.6	739.5
162.5°	751.7	752.4	753.2	753.9	754.6	754.5	753.5	752.4	751.4	750.4	750.3
165°	765.9	766.6	767.3	768.1	768.9	768.7	767.7	766.6	765.6	764.5	764.5
167.5°	777.5	778.3	779.0	779.8	780.6	780.4	779.4	778.3	777.3	776.2	776.3
170°	783.3	784.3	785.1	786.1	787.0	786.9	785.8	784.8	783.8	782.6	782.8
172.5°	788.2	789.1	790.0	790.9	791.8	791.7	790.7	789.6	788.6	787.6	787.7
175°	793.5	794.4	795.2	796.2	797.0	796.9	795.9	794.9	793.8	792.8	793.1
177.5°	795.9	796.6	797.3	798.1	798.7	798.7	798.1	797.3	796.6	795.9	796.1
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	858.5	856.4	855.1	850.6	846.4	842.3	841.0	841.5	835.9	830.5	828.2
5°	892.0	885.5	879.4	870.7	860.5	849.2	843.4	839.0	827.7	815.5	808.4
7.5°	922.0	912.7	901.0	884.7	869.7	852.0	840.7	830.8	814.2	797.0	786.5
10°	940.2	927.6	912.6	892.6	874.3	852.7	837.7	822.5	803.2	782.6	769.8
12.5°	955.9	939.0	924.1	898.5	876.8	849.9	832.0	810.7	790.4	765.9	753.3
15°	993.2	962.1	933.8	904.8	878.1	840.5	820.6	791.9	765.3	735.0	720.6
17.5°	1022.1	987.1	942.5	905.8	874.6	832.9	803.7	769.4	737.8	703.3	683.6
20°	1038.6	998.4	950.5	906.8	869.4	821.9	790.1	755.0	718.0	679.1	657.9
22.5°	1048.4	1006.2	958.7	902.9	859.2	812.9	772.8	734.4	696.9	655.0	632.7
25°	1051.5	1012.9	962.7	899.7	846.3	793.9	745.6	708.3	663.1	623.8	591.3
27.5°	1036.1	1008.5	960.3	893.6	831.5	770.2	716.4	674.2	626.3	583.8	551.0
30°	1017.4	1001.3	954.3	887.4	819.6	753.7	694.6	646.6	599.1	555.9	522.5
32.5°	988.3	984.8	943.6	878.7	807.0	732.9	671.7	623.2	570.5	528.1	496.3
35°	931.2	946.7	920.6	859.2	783.3	703.3	637.0	581.7	527.0	486.5	456.6
37.5°	854.7	893.0	886.2	830.5	751.2	671.0	597.8	540.0	487.9	447.0	417.7
40°	801.9	850.8	857.9	808.7	728.7	646.0	568.5	510.9	460.1	422.8	393.2
42.5°	745.4	802.5	821.9	782.5	704.0	619.7	542.3	482.7	432.4	396.1	369.9
45°	650.5	726.1	761.1	738.6	662.7	576.5	496.8	436.4	390.7	356.6	336.3
47.5°	561.8	644.4	691.6	683.5	616.8	531.5	452.7	394.7	350.3	323.0	304.9
50°	499.0	583.9	640.8	643.4	583.9	499.4	420.3	365.6	324.8	299.4	284.6
52.5°	444.5	525.6	587.6	601.2	547.2	465.9	391.2	336.8	300.8	277.5	264.2
55°	373.3	441.8	510.7	535.7	492.3	415.1	345.9	298.1	264.3	248.2	236.7
57.5°	310.4	367.5	431.0	458.7	432.0	365.9	301.1	259.5	232.1	218.0	209.1
60°	277.2	322.2	378.8	411.9	388.7	329.9	273.3	233.8	211.3	198.7	190.4
62.5°	246.3	286.2	334.0	364.3	351.7	296.2	245.6	210.6	191.2	179.4	173.4
65°	203.2	234.7	271.7	299.7	291.4	249.2	207.8	177.8	162.4	153.1	148.3
67.5°	167.3	190.1	215.8	240.2	233.5	203.6	170.4	147.1	135.5	127.5	124.7
70°	144.7	162.0	184.9	204.5	199.1	174.6	148.3	128.3	118.3	111.6	108.7
72.5°	123.1	137.3	154.8	170.8	167.1	146.8	124.8	109.8	102.1	95.9	93.5
75°	92.9	103.8	114.5	125.1	124.2	108.4	95.5	83.9	77.8	73.0	72.1
77.5°	68.6	74.7	82.0	88.3	86.5	77.5	67.4	60.8	56.3	53.0	52.5
80°	52.4	56.0	61.1	65.6	63.4	59.5	51.5	46.7	43.4	40.2	38.9
82.5°	38.0	41.6	44.6	47.1	45.4	41.8	36.8	33.5	31.6	29.4	28.8
85°	20.0	21.9	23.2	23.8	23.2	20.9	18.7	17.4	15.8	14.8	14.5
87.5°	11.1	10.4	9.8	9.8	8.7	8.4	6.9	5.8	5.9	6.0	5.9
90°	17.0	13.7	10.4	7.8	6.0	4.3	2.5	0.7	2.5	4.3	6.0
92.5°	19.8	19.0	18.3	17.2	15.9	14.6	13.3	12.0	13.3	14.6	15.9
95°	42.4	42.2	41.8	41.0	39.5	38.0	36.5	35.0	36.5	38.0	39.5
97.5°	71.3	70.7	70.2	69.2	67.8	66.6	65.3	64.0	65.3	66.6	67.8
100°	92.0	91.5	91.1	90.2	89.0	87.8	86.7	85.5	86.7	87.8	89.0
102.5°	113.8	113.2	112.7	111.9	111.0	110.0	109.0	108.1	109.0	110.0	111.0
105°	147.5	147.1	146.9	146.5	146.0	145.6	145.2	144.7	145.2	145.6	146.0
107.5°	184.5	184.5	184.5	184.2	183.6	182.9	182.3	181.6	182.3	182.9	183.6
110°	209.3	209.3	209.3	208.9	207.9	207.1	206.1	205.3	206.1	207.1	207.9



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	234.9	235.0	235.1	234.7	233.8	232.9	232.0	231.1	232.0	232.9	233.8
115°	272.5	272.8	273.1	272.8	271.9	271.0	270.1	269.2	270.1	271.0	271.9
117.5°	310.5	311.3	312.1	311.9	310.7	309.5	308.3	307.1	308.3	309.5	310.7
120°	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	333.6	334.8	336.0
122.5°	360.0	360.8	361.6	361.4	359.9	358.5	357.1	355.6	357.1	358.5	359.9
125°	396.6	397.1	397.5	397.1	395.7	394.3	393.0	391.7	393.0	394.3	395.7
127.5°	433.2	433.7	434.2	433.6	432.0	430.2	428.5	426.8	428.5	430.2	432.0
130°	456.8	457.2	457.4	456.7	454.7	452.8	450.8	448.9	450.8	452.8	454.7
132.5°	481.0	480.9	480.8	480.0	478.4	476.8	475.3	473.6	475.3	476.8	478.4
135°	514.9	514.6	514.3	513.3	511.7	510.1	508.4	506.8	508.4	510.1	511.7
137.5°	548.6	548.3	547.9	547.0	545.7	544.3	542.9	541.7	542.9	544.3	545.7
140°	570.6	569.8	569.0	568.0	566.6	565.3	564.0	562.7	564.0	565.3	566.6
142.5°	591.5	591.0	590.5	589.5	588.2	586.9	585.5	584.2	585.5	586.9	588.2
145°	622.1	621.2	620.3	619.3	618.3	617.3	616.1	615.1	616.1	617.3	618.3
147.5°	649.9	649.3	648.7	647.7	646.4	645.2	643.9	642.7	643.9	645.2	646.4
150°	667.1	666.5	665.9	665.1	664.3	663.3	662.5	661.6	662.5	663.3	664.3
152.5°	684.1	683.4	682.6	681.8	681.0	680.0	679.2	678.2	679.2	680.0	681.0
155°	706.5	705.9	705.5	705.1	704.6	704.2	703.7	703.3	703.7	704.2	704.6
157.5°	726.7	726.4	726.2	725.9	725.6	725.3	725.0	724.7	725.0	725.3	725.6
160°	739.3	739.2	739.0	738.8	738.5	738.2	737.9	737.6	737.9	738.2	738.5
162.5°	750.1	749.9	749.8	749.7	749.6	749.6	749.5	749.4	749.5	749.6	749.6
165°	764.5	764.5	764.5	764.6	764.7	764.9	765.1	765.2	765.1	764.9	764.7
167.5°	776.3	776.4	776.4	776.6	777.1	777.5	777.9	778.3	777.9	777.5	777.1
170°	783.0	783.2	783.3	783.6	784.0	784.5	785.0	785.4	785.0	784.5	784.0
172.5°	787.8	788.0	788.2	788.4	788.8	789.4	789.8	790.2	789.8	789.4	788.8
175°	793.4	793.7	794.0	794.4	794.8	795.2	795.7	796.2	795.7	795.2	794.8
177.5°	796.3	796.6	796.9	797.1	797.5	797.9	798.2	798.6	798.2	797.9	797.5
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	825.6	824.1	818.6	815.8	811.2	806.8	804.0	805.3	806.3	805.8	805.0
5°	801.9	795.8	786.5	778.4	772.7	762.1	757.6	755.4	753.4	751.1	748.9
7.5°	773.8	764.1	750.8	739.3	728.5	715.3	707.8	703.3	698.6	693.5	689.1
10°	753.7	740.2	726.1	710.0	697.2	685.2	674.6	667.5	661.1	655.0	650.5
12.5°	732.6	717.0	699.6	677.6	663.4	646.4	644.8	632.3	622.2	618.5	613.2
15°	699.0	677.2	655.0	629.0	617.7	602.3	592.6	583.0	574.3	568.2	566.5
17.5°	660.9	632.6	610.5	591.9	573.4	557.6	548.7	541.0	533.8	525.6	524.6
20°	631.8	607.4	583.3	566.9	547.9	531.8	520.9	513.2	507.0	502.2	498.1
22.5°	604.3	577.6	555.5	537.5	518.8	505.8	497.2	489.8	484.7	479.4	475.4
25°	560.2	539.2	515.1	494.9	479.4	471.1	464.0	457.5	454.3	450.8	446.3
27.5°	521.5	498.3	475.7	460.0	446.4	439.0	434.0	429.6	426.6	424.6	422.0
30°	494.2	470.7	453.1	437.6	426.4	419.0	415.8	413.2	409.7	408.4	407.1
32.5°	468.0	446.9	431.7	418.4	407.6	402.8	399.8	397.5	394.8	393.5	390.9
35°	430.8	413.2	398.4	391.0	382.3	378.2	375.9	372.6	370.1	368.9	368.5
37.5°	396.0	380.6	370.8	361.4	357.7	355.1	352.1	349.8	349.0	348.9	348.5
40°	373.3	360.8	352.1	344.4	342.8	338.9	336.3	334.4	334.4	334.8	334.4
42.5°	352.8	341.5	333.8	327.2	325.3	323.0	320.4	320.3	320.8	321.8	320.8
45°	321.6	313.5	308.1	304.8	301.3	299.0	298.7	299.7	300.0	300.3	301.3
47.5°	292.8	287.5	282.6	279.1	277.5	277.1	276.7	278.4	279.9	280.5	282.0
50°	275.9	269.8	265.6	263.4	262.1	261.4	262.1	264.0	265.3	266.9	267.9
52.5°	256.8	252.5	249.7	247.9	247.4	247.8	247.9	250.1	252.2	252.7	253.2
55°	230.6	227.3	226.7	223.8	225.1	224.7	226.4	227.6	229.5	231.5	231.9
57.5°	204.3	201.7	200.0	200.3	200.6	202.1	203.4	205.7	207.8	209.7	210.0
60°	186.8	185.5	184.6	184.6	185.2	187.2	188.7	191.0	192.3	193.6	194.5
62.5°	170.9	169.6	168.6	169.1	170.8	171.9	173.8	175.0	176.3	177.6	178.1
65°	145.7	145.0	146.0	146.6	147.0	148.5	150.8	151.8	153.1	153.7	155.9
67.5°	122.4	122.6	122.4	123.4	125.2	125.6	127.7	130.0	130.3	131.5	132.9
70°	106.8	107.4	108.1	108.7	110.3	110.9	112.5	113.5	114.8	115.7	116.8
72.5°	92.4	92.5	93.2	93.0	94.4	95.7	97.1	98.1	99.4	100.6	101.5
75°	71.0	71.0	71.7	72.1	73.6	75.3	74.9	75.6	76.9	78.2	78.8
77.5°	51.9	51.2	51.9	52.2	52.7	54.1	54.3	55.3	56.7	56.3	57.0
80°	39.5	38.6	39.5	39.9	39.9	41.5	41.5	42.1	43.0	42.1	43.0
82.5°	28.2	27.8	28.5	28.6	29.1	29.1	29.6	29.8	30.7	30.3	30.7
85°	14.1	13.9	14.1	13.9	14.1	14.5	14.5	14.1	14.1	14.8	13.9
87.5°	5.9	6.2	6.6	7.2	7.7	8.1	7.7	7.7	7.6	7.1	7.1
90°	7.8	10.4	13.7	17.0	20.2	23.6	23.2	23.0	22.6	22.4	22.3
92.5°	17.2	18.3	19.0	19.8	20.7	21.4	21.4	21.5	21.6	21.6	21.7
95°	41.0	41.8	42.2	42.4	42.8	43.0	43.0	43.0	43.0	43.0	43.0
97.5°	69.2	70.2	70.7	71.3	71.8	72.4	72.4	72.4	72.4	72.4	72.4
100°	90.2	91.1	91.5	92.0	92.4	92.9	92.9	92.9	92.9	92.9	92.8
102.5°	111.9	112.7	113.2	113.8	114.3	114.9	115.0	115.2	115.3	115.5	115.4
105°	146.5	146.9	147.1	147.5	147.7	148.1	148.4	148.7	149.0	149.3	149.4
107.5°	184.2	184.5	184.5	184.5	184.5	184.5	184.7	184.8	184.9	185.0	184.8
110°	208.9	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.1



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	234.7	235.1	235.0	234.9	234.7	234.6	234.3	233.8	233.5	233.2	232.8
115°	272.8	273.1	272.8	272.5	272.2	271.9	271.7	271.6	271.5	271.3	271.0
117.5°	311.9	312.1	311.3	310.5	309.6	308.8	308.4	308.1	307.7	307.3	306.9
120°	337.3	337.3	336.0	334.8	333.6	332.4	332.4	332.4	332.4	332.4	332.3
122.5°	361.4	361.6	360.8	360.0	359.1	358.3	357.9	357.6	357.2	356.9	356.5
125°	397.1	397.5	397.1	396.6	396.1	395.7	395.3	394.9	394.3	393.9	393.6
127.5°	433.6	434.2	433.7	433.2	432.6	432.0	431.5	431.0	430.4	429.9	429.4
130°	456.7	457.4	457.2	456.8	456.6	456.3	456.0	455.7	455.4	455.1	454.6
132.5°	480.0	480.8	480.9	481.0	481.0	481.0	480.4	479.7	479.1	478.5	477.9
135°	513.3	514.3	514.6	514.9	515.2	515.5	515.4	515.2	515.1	514.9	514.6
137.5°	547.0	547.9	548.3	548.6	549.1	549.4	549.3	549.2	549.1	549.0	548.6
140°	568.0	569.0	569.8	570.6	571.3	572.0	572.0	572.0	572.0	572.0	571.7
142.5°	589.5	590.5	591.0	591.5	592.0	592.5	592.6	592.7	592.9	593.0	592.7
145°	619.3	620.3	621.2	622.1	622.9	623.9	624.1	624.1	624.3	624.5	624.2
147.5°	647.7	648.7	649.3	649.9	650.5	651.1	651.3	651.7	652.0	652.4	652.3
150°	665.1	665.9	666.5	667.1	667.7	668.3	668.7	669.2	669.6	670.1	670.1
152.5°	681.8	682.6	683.4	684.1	684.8	685.5	686.0	686.6	687.3	687.8	687.8
155°	705.1	705.5	705.9	706.5	706.9	707.3	708.1	708.8	709.6	710.3	710.5
157.5°	725.9	726.2	726.4	726.7	726.9	727.2	728.2	729.3	730.3	731.3	731.4
160°	738.8	739.0	739.2	739.3	739.5	739.6	740.5	741.4	742.4	743.2	743.4
162.5°	749.7	749.8	749.9	750.1	750.3	750.4	751.4	752.4	753.5	754.5	754.6
165°	764.6	764.5	764.5	764.5	764.5	764.5	765.6	766.6	767.7	768.7	768.9
167.5°	776.6	776.4	776.4	776.3	776.3	776.2	777.3	778.3	779.4	780.4	780.6
170°	783.6	783.3	783.2	783.0	782.8	782.6	783.8	784.8	785.8	786.9	787.0
172.5°	788.4	788.2	788.0	787.8	787.7	787.6	788.6	789.6	790.7	791.7	791.8
175°	794.4	794.0	793.7	793.4	793.1	792.8	793.8	794.9	795.9	796.9	797.0
177.5°	797.1	796.9	796.6	796.3	796.1	795.9	796.6	797.3	798.1	798.7	798.7
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	802.5	801.9	801.9	799.6	801.9	801.9	802.5	805.0	805.8	806.3	805.3
5°	744.4	743.4	741.8	743.4	741.8	743.4	744.4	748.9	751.1	753.4	755.4
7.5°	687.0	683.1	682.5	678.7	682.5	683.1	687.0	689.1	693.5	698.6	703.3
10°	645.1	642.5	642.1	636.0	642.1	642.5	645.1	650.5	655.0	661.1	667.5
12.5°	613.1	606.9	608.2	604.7	608.2	606.9	613.1	613.2	618.5	622.2	632.3
15°	557.8	557.8	556.6	551.1	556.6	557.8	557.8	566.5	568.2	574.3	583.0
17.5°	518.2	517.5	514.4	516.0	514.4	517.5	518.2	524.6	525.6	533.8	541.0
20°	494.6	492.6	488.8	488.8	488.8	492.6	494.6	498.1	502.2	507.0	513.2
22.5°	472.2	472.0	468.0	469.2	468.0	472.0	472.2	475.4	479.4	484.7	489.8
25°	446.0	443.4	441.5	442.5	441.5	443.4	446.0	446.3	450.8	454.3	457.5
27.5°	421.2	419.7	419.7	417.0	419.7	419.7	421.2	422.0	424.6	426.6	429.6
30°	406.7	403.6	404.2	402.6	404.2	403.6	406.7	407.1	408.4	409.7	413.2
32.5°	390.3	389.2	388.5	387.1	388.5	389.2	390.3	390.9	393.5	394.8	397.5
35°	367.8	368.2	366.5	367.2	366.5	368.2	367.8	368.5	368.9	370.1	372.6
37.5°	348.3	349.3	348.5	348.7	348.5	349.3	348.3	348.5	348.9	349.0	349.8
40°	335.4	335.4	335.4	336.3	335.4	335.4	335.4	334.4	334.8	334.4	334.4
42.5°	323.0	322.5	322.0	321.9	322.0	322.5	323.0	320.8	321.8	320.8	320.3
45°	302.0	302.9	303.2	301.6	303.2	302.9	302.0	301.3	300.3	300.0	299.7
47.5°	282.8	282.9	282.8	284.2	282.8	282.9	282.8	282.0	280.5	279.9	278.4
50°	269.5	268.8	269.5	268.8	269.5	268.8	269.5	267.9	266.9	265.3	264.0
52.5°	255.3	255.5	255.0	254.9	255.0	255.5	255.3	253.2	252.7	252.2	250.1
55°	233.2	233.8	233.4	233.4	233.4	233.8	233.2	231.9	231.5	229.5	227.6
57.5°	210.2	210.8	211.2	209.7	211.2	210.8	210.2	210.0	209.7	207.8	205.7
60°	194.2	195.8	195.5	194.8	195.5	195.8	194.2	194.5	193.6	192.3	191.0
62.5°	179.5	180.1	180.0	179.9	180.0	180.1	179.5	178.1	177.6	176.3	175.0
65°	156.9	157.6	156.6	157.6	156.6	157.6	156.9	155.9	153.7	153.1	151.8
67.5°	132.5	132.8	133.5	133.9	133.5	132.8	132.5	132.9	131.5	130.3	130.0
70°	117.4	117.0	118.0	119.0	118.0	117.0	117.4	116.8	115.7	114.8	113.5
72.5°	101.4	102.1	101.8	102.5	101.8	102.1	101.4	101.5	100.6	99.4	98.1
75°	78.2	79.1	78.8	79.7	78.8	79.1	78.2	78.8	78.2	76.9	75.6
77.5°	56.5	56.6	56.5	57.0	56.5	56.6	56.5	57.0	56.3	56.7	55.3
80°	43.0	42.4	41.8	43.0	41.8	42.4	43.0	43.0	42.1	43.0	42.1
82.5°	30.0	30.4	29.7	29.7	29.7	30.4	30.0	30.7	30.3	30.7	29.8
85°	13.9	13.5	12.8	12.8	12.8	13.5	13.9	13.9	14.8	14.1	14.1
87.5°	7.1	6.8	6.9	6.6	6.9	6.8	7.1	7.1	7.1	7.6	7.7
90°	22.5	22.6	22.7	22.9	22.7	22.6	22.5	22.3	22.4	22.6	23.0
92.5°	21.7	21.8	21.8	21.8	21.8	21.8	21.7	21.7	21.6	21.6	21.5
95°	42.6	42.4	42.0	41.8	42.0	42.4	42.6	43.0	43.0	43.0	43.0
97.5°	72.4	72.3	72.3	72.2	72.3	72.3	72.4	72.4	72.4	72.4	72.4
100°	92.6	92.5	92.4	92.2	92.4	92.5	92.6	92.8	92.9	92.9	92.9
102.5°	115.3	115.1	114.9	114.8	114.9	115.1	115.3	115.4	115.5	115.3	115.2
105°	149.4	149.4	149.4	149.4	149.4	149.4	149.4	149.4	149.3	149.0	148.7
107.5°	184.1	183.4	182.7	182.0	182.7	183.4	184.1	184.8	185.0	184.9	184.8
110°	208.6	208.2	207.8	207.2	207.8	208.2	208.6	209.1	209.3	209.3	209.3



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	232.5	232.1	231.9	231.5	231.9	232.1	232.5	232.8	233.2	233.5	233.8
115°	270.5	270.1	269.7	269.2	269.7	270.1	270.5	271.0	271.3	271.5	271.6
117.5°	306.5	306.0	305.6	305.1	305.6	306.0	306.5	306.9	307.3	307.7	308.1
120°	331.7	331.3	330.9	330.5	330.9	331.3	331.7	332.3	332.4	332.4	332.4
122.5°	356.2	355.9	355.5	355.2	355.5	355.9	356.2	356.5	356.9	357.2	357.6
125°	393.5	393.3	393.2	393.0	393.2	393.3	393.5	393.6	393.9	394.3	394.9
127.5°	429.0	428.4	428.0	427.5	428.0	428.4	429.0	429.4	429.9	430.4	431.0
130°	454.0	453.5	452.9	452.3	452.9	453.5	454.0	454.6	455.1	455.4	455.7
132.5°	477.3	476.9	476.4	476.0	476.4	476.9	477.3	477.9	478.5	479.1	479.7
135°	514.2	513.8	513.2	512.8	513.2	513.8	514.2	514.6	514.9	515.1	515.2
137.5°	548.0	547.4	546.8	546.2	546.8	547.4	548.0	548.6	549.0	549.1	549.2
140°	571.2	570.6	570.0	569.4	570.0	570.6	571.2	571.7	572.0	572.0	572.0
142.5°	592.1	591.5	591.0	590.4	591.0	591.5	592.1	592.7	593.0	592.9	592.7
145°	623.6	623.0	622.4	621.8	622.4	623.0	623.6	624.2	624.5	624.3	624.1
147.5°	651.7	651.1	650.6	650.0	650.6	651.1	651.7	652.3	652.4	652.0	651.7
150°	669.6	669.2	668.7	668.3	668.7	669.2	669.6	670.1	670.1	669.6	669.2
152.5°	687.3	686.6	686.0	685.5	686.0	686.6	687.3	687.8	687.8	687.3	686.6
155°	710.0	709.6	709.1	708.7	709.1	709.6	710.0	710.5	710.3	709.6	708.8
157.5°	730.7	730.0	729.3	728.6	729.3	730.0	730.7	731.4	731.3	730.3	729.3
160°	742.8	742.2	741.6	741.0	741.6	742.2	742.8	743.4	743.2	742.4	741.4
162.5°	753.9	753.2	752.4	751.7	752.4	753.2	753.9	754.6	754.5	753.5	752.4
165°	768.1	767.3	766.6	765.9	766.6	767.3	768.1	768.9	768.7	767.7	766.6
167.5°	779.8	779.0	778.3	777.5	778.3	779.0	779.8	780.6	780.4	779.4	778.3
170°	786.1	785.1	784.3	783.3	784.3	785.1	786.1	787.0	786.9	785.8	784.8
172.5°	790.9	790.0	789.1	788.2	789.1	790.0	790.9	791.8	791.7	790.7	789.6
175°	796.2	795.2	794.4	793.5	794.4	795.2	796.2	797.0	796.9	795.9	794.9
177.5°	798.1	797.3	796.6	795.9	796.6	797.3	798.1	798.7	798.7	798.1	797.3
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	804.0	806.8	811.2	815.8	818.6	824.1	825.6	828.2	830.5	835.9	841.5
5°	757.6	762.1	772.7	778.4	786.5	795.8	801.9	808.4	815.5	827.7	839.0
7.5°	707.8	715.3	728.5	739.3	750.8	764.1	773.8	786.5	797.0	814.2	830.8
10°	674.6	685.2	697.2	710.0	726.1	740.2	753.7	769.8	782.6	803.2	822.5
12.5°	644.8	646.4	663.4	677.6	699.6	717.0	732.6	753.3	765.9	790.4	810.7
15°	592.6	602.3	617.7	629.0	655.0	677.2	699.0	720.6	735.0	765.3	791.9
17.5°	548.7	557.6	573.4	591.9	610.5	632.6	660.9	683.6	703.3	737.8	769.4
20°	520.9	531.8	547.9	566.9	583.3	607.4	631.8	657.9	679.1	718.0	755.0
22.5°	497.2	505.8	518.8	537.5	555.5	577.6	604.3	632.7	655.0	696.9	734.4
25°	464.0	471.1	479.4	494.9	515.1	539.2	560.2	591.3	623.8	663.1	708.3
27.5°	434.0	439.0	446.4	460.0	475.7	498.3	521.5	551.0	583.8	626.3	674.2
30°	415.8	419.0	426.4	437.6	453.1	470.7	494.2	522.5	555.9	599.1	646.6
32.5°	399.8	402.8	407.6	418.4	431.7	446.9	468.0	496.3	528.1	570.5	623.2
35°	375.9	378.2	382.3	391.0	398.4	413.2	430.8	456.6	486.5	527.0	581.7
37.5°	352.1	355.1	357.7	361.4	370.8	380.6	396.0	417.7	447.0	487.9	540.0
40°	336.3	338.9	342.8	344.4	352.1	360.8	373.3	393.2	422.8	460.1	510.9
42.5°	320.4	323.0	325.3	327.2	333.8	341.5	352.8	369.9	396.1	432.4	482.7
45°	298.7	299.0	301.3	304.8	308.1	313.5	321.6	336.3	356.6	390.7	436.4
47.5°	276.7	277.1	277.5	279.1	282.6	287.5	292.8	304.9	323.0	350.3	394.7
50°	262.1	261.4	262.1	263.4	265.6	269.8	275.9	284.6	299.4	324.8	365.6
52.5°	247.9	247.8	247.4	247.9	249.7	252.5	256.8	264.2	277.5	300.8	336.8
55°	226.4	224.7	225.1	223.8	226.7	227.3	230.6	236.7	248.2	264.3	298.1
57.5°	203.4	202.1	200.6	200.3	200.0	201.7	204.3	209.1	218.0	232.1	259.5
60°	188.7	187.2	185.2	184.6	184.6	185.5	186.8	190.4	198.7	211.3	233.8
62.5°	173.8	171.9	170.8	169.1	168.6	169.6	170.9	173.4	179.4	191.2	210.6
65°	150.8	148.5	147.0	146.6	146.0	145.0	145.7	148.3	153.1	162.4	177.8
67.5°	127.7	125.6	125.2	123.4	122.4	122.6	122.4	124.7	127.5	135.5	147.1
70°	112.5	110.9	110.3	108.7	108.1	107.4	106.8	108.7	111.6	118.3	128.3
72.5°	97.1	95.7	94.4	93.0	93.2	92.5	92.4	93.5	95.9	102.1	109.8
75°	74.9	75.3	73.6	72.1	71.7	71.0	71.0	72.1	73.0	77.8	83.9
77.5°	54.3	54.1	52.7	52.2	51.9	51.2	51.9	52.5	53.0	56.3	60.8
80°	41.5	41.5	39.9	39.9	39.5	38.6	39.5	38.9	40.2	43.4	46.7
82.5°	29.6	29.1	29.1	28.6	28.5	27.8	28.2	28.8	29.4	31.6	33.5
85°	14.5	14.5	14.1	13.9	14.1	13.9	14.1	14.5	14.8	15.8	17.4
87.5°	7.7	8.1	7.7	7.2	6.6	6.2	5.9	5.9	6.0	5.9	5.8
90°	23.2	23.6	20.2	17.0	13.7	10.4	7.8	6.0	4.3	2.5	0.7
92.5°	21.4	21.4	20.7	19.8	19.0	18.3	17.2	15.9	14.6	13.3	12.0
95°	43.0	43.0	42.8	42.4	42.2	41.8	41.0	39.5	38.0	36.5	35.0
97.5°	72.4	72.4	71.8	71.3	70.7	70.2	69.2	67.8	66.6	65.3	64.0
100°	92.9	92.9	92.4	92.0	91.5	91.1	90.2	89.0	87.8	86.7	85.5
102.5°	115.0	114.9	114.3	113.8	113.2	112.7	111.9	111.0	110.0	109.0	108.1
105°	148.4	148.1	147.7	147.5	147.1	146.9	146.5	146.0	145.6	145.2	144.7
107.5°	184.7	184.5	184.5	184.5	184.5	184.5	184.2	183.6	182.9	182.3	181.6
110°	209.3	209.3	209.3	209.3	209.3	209.3	208.9	207.9	207.1	206.1	205.3



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	234.3	234.6	234.7	234.9	235.0	235.1	234.7	233.8	232.9	232.0	231.1
115°	271.7	271.9	272.2	272.5	272.8	273.1	272.8	271.9	271.0	270.1	269.2
117.5°	308.4	308.8	309.6	310.5	311.3	312.1	311.9	310.7	309.5	308.3	307.1
120°	332.4	332.4	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4
122.5°	357.9	358.3	359.1	360.0	360.8	361.6	361.4	359.9	358.5	357.1	355.6
125°	395.3	395.7	396.1	396.6	397.1	397.5	397.1	395.7	394.3	393.0	391.7
127.5°	431.5	432.0	432.6	433.2	433.7	434.2	433.6	432.0	430.2	428.5	426.8
130°	456.0	456.3	456.6	456.8	457.2	457.4	456.7	454.7	452.8	450.8	448.9
132.5°	480.4	481.0	481.0	481.0	480.9	480.8	480.0	478.4	476.8	475.3	473.6
135°	515.4	515.5	515.2	514.9	514.6	514.3	513.3	511.7	510.1	508.4	506.8
137.5°	549.3	549.4	549.1	548.6	548.3	547.9	547.0	545.7	544.3	542.9	541.7
140°	572.0	572.0	571.3	570.6	569.8	569.0	568.0	566.6	565.3	564.0	562.7
142.5°	592.6	592.5	592.0	591.5	591.0	590.5	589.5	588.2	586.9	585.5	584.2
145°	624.1	623.9	622.9	622.1	621.2	620.3	619.3	618.3	617.3	616.1	615.1
147.5°	651.3	651.1	650.5	649.9	649.3	648.7	647.7	646.4	645.2	643.9	642.7
150°	668.7	668.3	667.7	667.1	666.5	665.9	665.1	664.3	663.3	662.5	661.6
152.5°	686.0	685.5	684.8	684.1	683.4	682.6	681.8	681.0	680.0	679.2	678.2
155°	708.1	707.3	706.9	706.5	705.9	705.5	705.1	704.6	704.2	703.7	703.3
157.5°	728.2	727.2	726.9	726.7	726.4	726.2	725.9	725.6	725.3	725.0	724.7
160°	740.5	739.6	739.5	739.3	739.2	739.0	738.8	738.5	738.2	737.9	737.6
162.5°	751.4	750.4	750.3	750.1	749.9	749.8	749.7	749.6	749.6	749.5	749.4
165°	765.6	764.5	764.5	764.5	764.5	764.5	764.6	764.7	764.9	765.1	765.2
167.5°	777.3	776.2	776.3	776.3	776.4	776.4	776.6	777.1	777.5	777.9	778.3
170°	783.8	782.6	782.8	783.0	783.2	783.3	783.6	784.0	784.5	785.0	785.4
172.5°	788.6	787.6	787.7	787.8	788.0	788.2	788.4	788.8	789.4	789.8	790.2
175°	793.8	792.8	793.1	793.4	793.7	794.0	794.4	794.8	795.2	795.7	796.2
177.5°	796.6	795.9	796.1	796.3	796.6	796.9	797.1	797.5	797.9	798.2	798.6
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	841.0	842.3	846.4	850.6	855.1	856.4	858.5	856.7	856.2	861.1	864.7
5°	843.4	849.2	860.5	870.7	879.4	885.5	892.0	894.6	899.4	906.1	914.5
7.5°	840.7	852.0	869.7	884.7	901.0	912.7	922.0	929.8	939.3	952.1	966.0
10°	837.7	852.7	874.3	892.6	912.6	927.6	940.2	952.4	966.6	984.3	1002.5
12.5°	832.0	849.9	876.8	898.5	924.1	939.0	955.9	982.2	997.5	1022.1	1047.8
15°	820.6	840.5	878.1	904.8	933.8	962.1	993.2	1018.3	1043.4	1057.9	1094.2
17.5°	803.7	832.9	874.6	905.8	942.5	987.1	1022.1	1050.6	1079.5	1102.9	1121.2
20°	790.1	821.9	869.4	906.8	950.5	998.4	1038.6	1067.6	1092.6	1112.2	1123.5
22.5°	772.8	812.9	859.2	902.9	958.7	1006.2	1048.4	1071.2	1092.1	1101.6	1106.0
25°	745.6	793.9	846.3	899.7	962.7	1012.9	1051.5	1065.3	1071.4	1062.0	1046.6
27.5°	716.4	770.2	831.5	893.6	960.3	1008.5	1036.1	1034.0	1023.6	993.4	969.3
30°	694.6	753.7	819.6	887.4	954.3	1001.3	1017.4	1001.3	977.8	944.1	909.6
32.5°	671.7	732.9	807.0	878.7	943.6	984.8	988.3	960.6	924.3	886.0	843.0
35°	637.0	703.3	783.3	859.2	920.6	946.7	931.2	882.4	839.2	786.9	728.3
37.5°	597.8	671.0	751.2	830.5	886.2	893.0	854.7	803.2	742.4	680.9	612.0
40°	568.5	646.0	728.7	808.7	857.9	850.8	801.9	745.4	673.0	597.8	533.7
42.5°	542.3	619.7	704.0	782.5	821.9	802.5	745.4	675.9	598.1	527.3	468.7
45°	496.8	576.5	662.7	738.6	761.1	726.1	650.5	573.3	496.8	437.6	391.3
47.5°	452.7	531.5	616.8	683.5	691.6	644.4	561.8	482.4	416.6	368.4	335.8
50°	420.3	499.4	583.9	643.4	640.8	583.9	499.0	423.4	368.5	329.6	307.7
52.5°	391.2	465.9	547.2	601.2	587.6	525.6	444.5	377.5	332.3	301.8	282.0
55°	345.9	415.1	492.3	535.7	510.7	441.8	373.3	319.3	285.9	263.0	247.6
57.5°	301.1	365.9	432.0	458.7	431.0	367.5	310.4	271.2	246.1	229.1	219.1
60°	273.3	329.9	388.7	411.9	378.8	322.2	277.2	242.1	221.9	208.0	199.1
62.5°	245.6	296.2	351.7	364.3	334.0	286.2	246.3	217.1	200.5	188.2	179.8
65°	207.8	249.2	291.4	299.7	271.7	234.7	203.2	184.3	169.4	160.5	153.7
67.5°	170.4	203.6	233.5	240.2	215.8	190.1	167.3	150.8	140.8	133.3	127.6
70°	148.3	174.6	199.1	204.5	184.9	162.0	144.7	131.5	122.5	116.1	110.6
72.5°	124.8	146.8	167.1	170.8	154.8	137.3	123.1	112.7	104.8	100.7	95.4
75°	95.5	108.4	124.2	125.1	114.5	103.8	92.9	86.2	82.0	76.9	74.3
77.5°	67.4	77.5	86.5	88.3	82.0	74.7	68.6	63.3	59.8	57.3	55.0
80°	51.5	59.5	63.4	65.6	61.1	56.0	52.4	48.9	46.7	45.0	43.4
82.5°	36.8	41.8	45.4	47.1	44.6	41.6	38.0	36.0	34.3	32.9	32.4
85°	18.7	20.9	23.2	23.8	23.2	21.9	20.0	20.0	18.9	18.7	18.7
87.5°	6.9	8.4	8.7	9.8	9.8	10.4	11.1	11.5	11.9	11.6	11.3
90°	2.5	4.3	6.0	7.8	10.4	13.7	17.0	20.2	23.6	23.2	23.0
92.5°	13.3	14.6	15.9	17.2	18.3	19.0	19.8	20.7	21.4	21.4	21.5
95°	36.5	38.0	39.5	41.0	41.8	42.2	42.4	42.8	43.0	43.0	43.0
97.5°	65.3	66.6	67.8	69.2	70.2	70.7	71.3	71.8	72.4	72.4	72.4
100°	86.7	87.8	89.0	90.2	91.1	91.5	92.0	92.4	92.9	92.9	92.9
102.5°	109.0	110.0	111.0	111.9	112.7	113.2	113.8	114.3	114.9	115.0	115.2
105°	145.2	145.6	146.0	146.5	146.9	147.1	147.5	147.7	148.1	148.4	148.7
107.5°	182.3	182.9	183.6	184.2	184.5	184.5	184.5	184.5	184.5	184.7	184.8
110°	206.1	207.1	207.9	208.9	209.3	209.3	209.3	209.3	209.3	209.3	209.3



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	232.0	232.9	233.8	234.7	235.1	235.0	234.9	234.7	234.6	234.3	233.8
115°	270.1	271.0	271.9	272.8	273.1	272.8	272.5	272.2	271.9	271.7	271.6
117.5°	308.3	309.5	310.7	311.9	312.1	311.3	310.5	309.6	308.8	308.4	308.1
120°	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	332.4	332.4
122.5°	357.1	358.5	359.9	361.4	361.6	360.8	360.0	359.1	358.3	357.9	357.6
125°	393.0	394.3	395.7	397.1	397.5	397.1	396.6	396.1	395.7	395.3	394.9
127.5°	428.5	430.2	432.0	433.6	434.2	433.7	433.2	432.6	432.0	431.5	431.0
130°	450.8	452.8	454.7	456.7	457.4	457.2	456.8	456.6	456.3	456.0	455.7
132.5°	475.3	476.8	478.4	480.0	480.8	480.9	481.0	481.0	481.0	480.4	479.7
135°	508.4	510.1	511.7	513.3	514.3	514.6	514.9	515.2	515.5	515.4	515.2
137.5°	542.9	544.3	545.7	547.0	547.9	548.3	548.6	549.1	549.4	549.3	549.2
140°	564.0	565.3	566.6	568.0	569.0	569.8	570.6	571.3	572.0	572.0	572.0
142.5°	585.5	586.9	588.2	589.5	590.5	591.0	591.5	592.0	592.5	592.6	592.7
145°	616.1	617.3	618.3	619.3	620.3	621.2	622.1	622.9	623.9	624.1	624.1
147.5°	643.9	645.2	646.4	647.7	648.7	649.3	649.9	650.5	651.1	651.3	651.7
150°	662.5	663.3	664.3	665.1	665.9	666.5	667.1	667.7	668.3	668.7	669.2
152.5°	679.2	680.0	681.0	681.8	682.6	683.4	684.1	684.8	685.5	686.0	686.6
155°	703.7	704.2	704.6	705.1	705.5	705.9	706.5	706.9	707.3	708.1	708.8
157.5°	725.0	725.3	725.6	725.9	726.2	726.4	726.7	726.9	727.2	728.2	729.3
160°	737.9	738.2	738.5	738.8	739.0	739.2	739.3	739.5	739.6	740.5	741.4
162.5°	749.5	749.6	749.6	749.7	749.8	749.9	750.1	750.3	750.4	751.4	752.4
165°	765.1	764.9	764.7	764.6	764.5	764.5	764.5	764.5	764.5	765.6	766.6
167.5°	777.9	777.5	777.1	776.6	776.4	776.4	776.3	776.3	776.2	777.3	778.3
170°	785.0	784.5	784.0	783.6	783.3	783.2	783.0	782.8	782.6	783.8	784.8
172.5°	789.8	789.4	788.8	788.4	788.2	788.0	787.8	787.7	787.6	788.6	789.6
175°	795.7	795.2	794.8	794.4	794.0	793.7	793.4	793.1	792.8	793.8	794.9
177.5°	798.2	797.9	797.5	797.1	796.9	796.6	796.3	796.1	795.9	796.6	797.3
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	867.8	871.4	871.4	871.9	876.0	875.6	875.3
5°	923.5	928.9	929.6	935.4	939.3	938.0	934.4
7.5°	976.0	986.2	993.9	998.2	1003.3	1006.4	1005.0
10°	1017.7	1032.5	1041.5	1047.6	1055.0	1060.5	1058.5
12.5°	1055.5	1073.2	1085.5	1096.0	1096.9	1104.0	1099.2
15°	1114.5	1133.2	1135.1	1142.8	1148.9	1148.2	1148.6
17.5°	1133.9	1140.0	1141.2	1141.3	1141.4	1139.2	1134.3
20°	1127.0	1124.8	1119.3	1115.2	1107.8	1106.7	1100.4
22.5°	1094.1	1086.9	1073.2	1064.2	1052.7	1049.6	1047.8
25°	1029.2	1013.5	991.6	970.8	964.9	953.7	956.9
27.5°	940.3	915.8	892.1	875.1	859.8	842.9	847.7
30°	877.8	850.2	816.7	791.0	774.6	758.5	755.6
32.5°	803.2	762.7	725.4	702.7	677.6	667.4	656.3
35°	674.6	635.1	598.1	566.3	547.9	533.7	520.9
37.5°	558.9	513.4	483.5	457.8	444.5	436.4	438.4
40°	487.2	447.3	425.4	405.8	393.6	387.8	389.1
42.5°	429.0	399.2	381.2	367.7	359.1	355.9	355.1
45°	363.0	346.3	331.5	323.8	319.6	316.1	313.8
47.5°	318.1	304.4	296.0	291.4	287.7	284.2	284.1
50°	291.0	282.0	276.2	271.4	268.5	265.9	268.2
52.5°	270.4	262.2	256.4	252.1	251.0	248.7	248.7
55°	239.9	233.4	229.3	225.4	223.5	222.2	220.6
57.5°	212.1	206.0	202.2	199.7	196.0	194.8	194.2
60°	192.3	187.4	183.6	180.4	178.7	176.2	176.2
62.5°	174.0	169.2	165.6	163.2	160.5	159.5	159.7
65°	147.6	143.7	140.2	137.6	137.0	135.1	135.7
67.5°	123.3	120.7	117.0	115.5	114.3	113.3	112.5
70°	107.1	104.5	102.5	100.7	99.7	99.7	99.7
72.5°	93.4	90.3	89.2	86.8	87.3	86.3	85.2
75°	72.3	70.4	69.5	68.4	66.9	66.9	66.9
77.5°	53.2	52.7	51.5	50.5	50.1	49.8	49.9
80°	41.2	40.8	40.2	40.2	39.5	39.3	38.6
82.5°	31.6	30.8	30.4	30.1	30.0	30.0	29.9
85°	18.0	17.4	17.4	17.7	17.0	17.0	17.4
87.5°	11.5	11.5	11.1	11.2	11.5	11.2	11.3
90°	22.6	22.4	22.3	22.5	22.6	22.7	22.9
92.5°	21.6	21.6	21.7	21.7	21.8	21.8	21.8
95°	43.0	43.0	43.0	42.6	42.4	42.0	41.8
97.5°	72.4	72.4	72.4	72.4	72.3	72.3	72.2
100°	92.9	92.9	92.8	92.6	92.5	92.4	92.2
102.5°	115.3	115.5	115.4	115.3	115.1	114.9	114.8
105°	149.0	149.3	149.4	149.4	149.4	149.4	149.4
107.5°	184.9	185.0	184.8	184.1	183.4	182.7	182.0
110°	209.3	209.3	209.1	208.6	208.2	207.8	207.2



TEST NUMBER: P331304-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.5	233.2	232.8	232.5	232.1	231.9	231.5
115°	271.5	271.3	271.0	270.5	270.1	269.7	269.2
117.5°	307.7	307.3	306.9	306.5	306.0	305.6	305.1
120°	332.4	332.4	332.3	331.7	331.3	330.9	330.5
122.5°	357.2	356.9	356.5	356.2	355.9	355.5	355.2
125°	394.3	393.9	393.6	393.5	393.3	393.2	393.0
127.5°	430.4	429.9	429.4	429.0	428.4	428.0	427.5
130°	455.4	455.1	454.6	454.0	453.5	452.9	452.3
132.5°	479.1	478.5	477.9	477.3	476.9	476.4	476.0
135°	515.1	514.9	514.6	514.2	513.8	513.2	512.8
137.5°	549.1	549.0	548.6	548.0	547.4	546.8	546.2
140°	572.0	572.0	571.7	571.2	570.6	570.0	569.4
142.5°	592.9	593.0	592.7	592.1	591.5	591.0	590.4
145°	624.3	624.5	624.2	623.6	623.0	622.4	621.8
147.5°	652.0	652.4	652.3	651.7	651.1	650.6	650.0
150°	669.6	670.1	670.1	669.6	669.2	668.7	668.3
152.5°	687.3	687.8	687.8	687.3	686.6	686.0	685.5
155°	709.6	710.3	710.5	710.0	709.6	709.1	708.7
157.5°	730.3	731.3	731.4	730.7	730.0	729.3	728.6
160°	742.4	743.2	743.4	742.8	742.2	741.6	741.0
162.5°	753.5	754.5	754.6	753.9	753.2	752.4	751.7
165°	767.7	768.7	768.9	768.1	767.3	766.6	765.9
167.5°	779.4	780.4	780.6	779.8	779.0	778.3	777.5
170°	785.8	786.9	787.0	786.1	785.1	784.3	783.3
172.5°	790.7	791.7	791.8	790.9	790.0	789.1	788.2
175°	795.9	796.9	797.0	796.2	795.2	794.4	793.5
177.5°	798.1	798.7	798.7	798.1	797.3	796.6	795.9
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5

(END OF REPORT)