

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331720-940

Luminaire Tested: **SA2XXRDIP-C865D725U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331720-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D725U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5274.7 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331720-940
CATALOG NUMBER: SA2XXRDIP-C865D725U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331720-940

CATALOG NUMBER: SA2XXRDIP-C865D725U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	42	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	31	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331720-940

CATALOG NUMBER: SA2XXRDIP-C865D725U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.3
10°-20°	336.0	6.4
20°-30°	471.9	8.9
30°-40°	514.6	9.8
40°-50°	473.1	9.0
50°-60°	371.6	7.0
60°-70°	242.3	4.6
70°-80°	124.9	2.4
80°-90°	34.6	0.7
90°-100°	29.4	0.6
100°-110°	107.8	2.0
110°-120°	288.3	5.5
120°-130°	475.8	9.0
130°-140°	506.0	9.6
140°-150°	470.3	8.9
150°-160°	378.1	7.2
160°-170°	243.7	4.6
170°-180°	83.9	1.6
0°-30°	930.3	17.6
0°-40°	1444.9	27.4
0°-60°	2289.6	43.4
0°-90°	2691.4	51.0
90°-120°	425.5	8.1
90°-150°	1877.7	35.6
90°-180°	2583.0	49.0
0°-180°	5274.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	1	8	13	16	17	4
95°	42	22	25	28	28	51
105°	194	202	39	46	48	207
115°	367	378	394	112	52	361
125°	519	527	539	543	545	462
135°	642	652	658	664	663	495
145°	744	744	755	759	756	465
155°	820	815	822	825	820	378
165°	864	860	862	866	862	244
175°	883	879	880	884	878	84
180°	882	882	882	882	882	



TEST NUMBER: P331720-940

CATALOG NUMBER: SA2XXRDIP-C865D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.2	13.9	12.6	11.1	9.8	9.2	9.5	9.6	9.9	10.2	10.1
90°	0.6	2.2	3.7	5.4	6.9	8.2	9.4	10.5	11.6	12.8	13.5
92.5°	12.8	12.8	12.6	12.5	12.3	12.6	13.1	13.6	14.3	14.8	15.2
95°	41.5	36.8	32.1	27.5	22.7	20.9	21.9	22.9	23.9	24.9	25.6
97.5°	82.3	69.1	55.9	42.7	29.5	24.1	26.4	28.7	31.0	33.3	33.9
100°	112.9	93.5	74.1	54.7	35.2	26.8	29.2	31.6	34.0	36.4	37.5
102.5°	146.6	142.5	138.4	134.3	130.1	118.0	97.8	77.7	57.5	37.4	38.9
105°	193.9	198.1	202.4	206.7	210.9	193.7	155.0	116.3	77.6	38.9	40.5
107.5°	247.9	251.3	254.8	258.2	261.6	240.1	193.7	147.3	100.9	54.5	52.9
110°	282.6	285.5	288.6	291.5	294.4	275.4	234.5	193.6	152.6	111.6	97.5



TEST NUMBER: P331720-940

CATALOG NUMBER: SA2XXRDIP-C865D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.2	317.9	320.5	323.2	325.7	322.0	311.9	301.8	291.7	281.5	229.9
115°	366.8	369.2	371.6	374.0	376.4	379.4	382.9	386.5	390.0	393.6	328.0
117.5°	412.9	415.5	418.2	420.9	423.6	426.1	428.6	431.1	433.5	436.0	420.1
120°	446.5	448.6	450.8	452.9	455.0	457.4	459.9	462.4	465.0	467.5	469.2
122.5°	475.1	477.3	479.6	481.8	484.0	486.5	489.4	492.1	494.9	497.7	498.6
125°	518.6	520.4	522.3	524.1	525.9	528.2	530.9	533.6	536.3	539.0	540.0
127.5°	558.0	560.1	562.1	564.1	566.1	568.2	570.2	572.2	574.3	576.2	577.7
130°	583.0	585.3	587.5	589.8	592.1	594.0	595.6	597.1	598.7	600.2	601.8
132.5°	608.5	610.5	612.4	614.3	616.3	618.0	619.6	621.1	622.7	624.2	625.5
135°	641.7	644.0	646.2	648.5	650.8	652.6	653.8	655.1	656.4	657.6	659.1
137.5°	675.3	676.8	678.4	680.0	681.6	683.1	684.6	686.0	687.4	688.9	690.3
140°	697.2	698.3	699.5	700.6	701.7	703.1	704.6	706.2	707.8	709.4	710.6
142.5°	715.6	716.6	717.6	718.6	719.6	721.0	722.8	724.6	726.4	728.2	729.3
145°	744.4	744.2	744.1	744.0	743.9	744.9	747.3	749.8	752.2	754.6	755.6
147.5°	769.5	769.0	768.5	767.9	767.4	768.3	770.7	773.0	775.4	777.8	778.6
150°	785.9	784.9	783.9	782.9	781.9	782.6	784.8	787.0	789.3	791.6	792.5
152.5°	799.6	798.5	797.5	796.3	795.2	795.8	797.9	800.0	802.2	804.3	805.2
155°	819.7	818.4	817.1	815.8	814.6	814.8	816.5	818.1	819.8	821.5	822.4
157.5°	835.4	834.3	833.2	832.1	831.1	831.1	832.3	833.5	834.6	835.9	836.9
160°	844.5	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	845.4
162.5°	852.7	851.9	851.0	850.2	849.3	849.3	850.0	850.7	851.5	852.2	853.2
165°	863.7	862.8	862.0	861.1	860.2	860.1	860.5	860.9	861.3	861.7	862.7
167.5°	871.8	871.0	870.1	869.3	868.4	868.2	868.6	869.0	869.4	869.8	870.8
170°	876.5	875.6	874.8	873.9	873.1	872.7	873.1	873.3	873.6	873.9	874.9
172.5°	879.5	878.6	877.8	876.9	876.1	875.8	876.1	876.4	876.6	876.9	878.0
175°	883.4	882.4	881.5	880.5	879.5	879.1	879.4	879.7	879.9	880.3	881.3
177.5°	884.1	883.3	882.5	881.7	880.9	880.6	880.7	880.8	880.9	881.0	881.8
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331720-940

CATALOG NUMBER: SA2XXRDIP-C865D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	10.0	9.9	9.8	9.8	9.9	10.0	10.0	10.1
90°	14.2	14.9	15.6	16.1	16.4	16.7	16.9	17.2
92.5°	15.5	15.9	16.2	16.6	16.7	16.9	17.0	17.2
95°	26.3	27.0	27.7	28.0	27.8	27.7	27.6	27.5
97.5°	34.4	35.0	35.6	35.9	36.1	36.3	36.5	36.6
100°	38.6	39.8	40.9	41.6	41.9	42.2	42.4	42.7
102.5°	40.3	41.8	43.2	44.2	44.6	45.0	45.4	45.8
105°	42.0	43.6	45.1	46.2	46.8	47.3	47.9	48.5
107.5°	51.3	49.7	48.2	47.6	48.2	48.8	49.3	49.8
110°	83.3	69.1	54.9	48.2	48.7	49.2	49.8	50.4



TEST NUMBER: P331720-940

CATALOG NUMBER: SA2XXRDIP-C865D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.2	126.4	74.7	49.0	49.6	50.0	50.5	50.9
115°	262.3	196.7	131.1	93.1	82.9	72.7	62.5	52.3
117.5°	404.2	388.3	372.4	347.7	314.1	280.6	247.1	213.6
120°	471.0	472.7	474.4	465.7	446.5	427.4	408.2	389.1
122.5°	499.7	500.7	501.8	500.4	496.7	492.9	489.3	485.5
125°	541.0	542.0	543.0	543.7	544.1	544.6	544.9	545.4
127.5°	579.2	580.6	582.0	582.8	582.9	583.0	583.1	583.2
130°	603.3	604.9	606.5	607.2	607.1	606.9	606.7	606.6
132.5°	626.9	628.2	629.5	630.2	630.0	629.9	629.7	629.5
135°	660.5	661.9	663.3	663.9	663.6	663.3	663.0	662.7
137.5°	691.7	693.0	694.5	694.9	694.5	693.9	693.5	692.9
140°	711.9	713.1	714.4	714.7	714.0	713.3	712.6	711.9
142.5°	730.5	731.6	732.8	733.1	732.4	731.6	730.9	730.2
145°	756.6	757.6	758.6	758.7	758.0	757.3	756.6	755.9
147.5°	779.3	780.1	780.8	780.9	780.2	779.6	779.1	778.5
150°	793.3	794.2	795.0	795.0	794.3	793.6	792.9	792.2
152.5°	806.0	806.9	807.8	807.7	806.8	805.8	804.9	804.0
155°	823.3	824.1	825.0	824.8	823.7	822.6	821.4	820.3
157.5°	837.8	838.7	839.7	839.6	838.6	837.4	836.3	835.3
160°	846.2	847.1	847.9	847.8	846.9	845.9	844.9	843.9
162.5°	854.1	855.1	856.0	856.0	854.7	853.5	852.3	851.0
165°	863.7	864.8	865.8	865.8	864.8	863.7	862.7	861.7
167.5°	871.8	872.8	873.8	873.6	872.4	871.1	869.8	868.5
170°	875.8	876.8	877.9	877.7	876.5	875.1	873.9	872.6
172.5°	879.0	879.9	880.9	880.7	879.5	878.2	876.9	875.7
175°	882.3	883.2	884.2	884.0	882.6	881.2	879.8	878.3
177.5°	882.6	883.4	884.2	884.1	883.1	882.1	881.0	880.0
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5

(END OF REPORT)