

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331368-935

Luminaire Tested: **SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331368-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6147.0 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331368-935  
CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18466	18466	18466	18466
5°	20702	18585	16470	18585
10°	23722	18433	14254	18433
15°	26242	18094	12593	18094
20°	25844	17732	11478	17732
25°	23302	17250	10774	17250
30°	19257	16479	10260	16479
35°	14034	15672	9895	15672
40°	11209	14720	9691	14720
45°	9796	13618	9412	13618
50°	9206	12552	9231	12552
55°	8487	11468	8982	11468
60°	7776	10317	8603	10317
65°	7087	9287	8225	9287
70°	6430	8280	7676	8280
75°	5702	7155	6800	7155
80°	4909	5923	5477	5923
85°	4409	4409	3260	4409



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.9	1.8
10°-20°	316.6	5.2
20°-30°	459.5	7.5
30°-40°	484.9	7.9
40°-50°	429.4	7.0
50°-60°	342.6	5.6
60°-70°	232.9	3.8
70°-80°	119.4	1.9
80°-90°	33.5	0.5
90°-100°	208.0	3.4
100°-110°	705.7	11.5
110°-120°	749.7	12.2
120°-130°	617.2	10.0
130°-140°	495.6	8.1
140°-150°	374.5	6.1
150°-160°	263.2	4.3
160°-170°	154.9	2.5
170°-180°	50.4	0.8
0°-30°	885.1	14.4
0°-40°	1370.0	22.3
0°-60°	2142.0	34.8
0°-90°	2527.8	41.1
90°-120°	1663.4	27.1
90°-150°	3150.7	51.3
90°-180°	3619.0	58.9
0°-180°	6147.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1144	1144	1144	1144	1144	
5°	1277	1147	1016	1147	1277	128
15°	1570	1082	753	1082	1570	433
25°	1308	968	605	968	1308	591
35°	712	795	502	795	712	463
45°	429	596	412	596	429	337
55°	302	407	319	407	302	270
65°	186	243	215	243	186	184
75°	91	115	109	115	91	98
85°	24	24	18	24	24	27
90°	33	1	33	1	33	19
95°	114	35	114	35	114	148
105°	1127	122	1127	122	1127	1091
115°	1483	215	1483	215	1483	1453
125°	1203	300	1203	300	1203	1087
135°	997	352	997	352	997	775
145°	796	402	796	402	796	506
155°	669	457	669	457	669	312
165°	587	498	587	498	587	168
175°	529	519	529	519	529	51
180°	520	520	520	520	520	



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1196.4	1196.7	1197.5	1191.8	1191.1	1191.1	1186.2	1182.0	1177.1	1170.4	1171.0
5°	1277.3	1282.1	1283.8	1278.6	1270.7	1269.8	1262.3	1250.0	1238.5	1229.3	1222.8
7.5°	1373.8	1375.7	1371.4	1364.4	1358.6	1348.1	1334.1	1320.5	1301.4	1283.9	1270.9
10°	1446.9	1449.6	1442.1	1432.0	1423.7	1411.4	1391.1	1370.5	1345.4	1321.2	1301.8
12.5°	1502.4	1509.0	1499.4	1498.1	1483.8	1466.9	1442.8	1432.4	1397.1	1363.4	1342.6
15°	1569.9	1569.5	1570.5	1562.1	1551.5	1548.9	1523.4	1495.7	1446.0	1426.2	1392.0
17.5°	1550.5	1557.1	1560.2	1560.1	1559.9	1558.2	1550.1	1532.6	1507.7	1475.6	1436.0
20°	1504.1	1512.9	1514.2	1524.3	1530.0	1537.5	1540.5	1535.7	1520.4	1493.5	1459.2
22.5°	1432.4	1434.8	1438.9	1454.7	1467.1	1485.7	1495.6	1511.8	1505.9	1492.8	1464.1
25°	1308.0	1303.6	1319.1	1326.9	1355.5	1385.3	1407.0	1430.6	1451.7	1464.5	1456.1
27.5°	1158.7	1152.2	1175.2	1196.2	1219.4	1251.8	1285.4	1325.0	1358.0	1399.2	1413.3
30°	1032.9	1036.8	1058.9	1081.2	1116.4	1162.1	1199.9	1243.5	1290.5	1336.6	1368.6
32.5°	897.2	912.4	926.3	960.6	991.5	1042.6	1097.9	1152.4	1211.0	1263.4	1313.1
35°	712.0	729.6	749.0	774.0	817.5	868.1	922.1	995.5	1075.6	1147.2	1206.1
37.5°	599.3	596.5	607.6	625.7	661.0	701.7	764.0	836.5	930.7	1014.9	1097.9
40°	531.8	530.0	538.0	554.7	581.5	611.4	665.9	729.6	817.1	919.9	1018.8
42.5°	485.4	486.5	490.9	502.7	521.0	545.6	586.4	640.7	720.7	817.6	923.9
45°	429.0	432.0	436.9	442.6	453.1	473.4	496.2	534.9	598.2	679.1	783.7
47.5°	388.4	388.5	393.4	398.4	404.7	416.0	434.7	458.9	503.6	569.5	659.4
50°	366.5	363.5	367.0	370.9	377.5	385.5	397.8	420.6	450.5	503.7	578.9
52.5°	339.8	339.9	343.1	344.6	350.5	358.3	369.6	385.5	412.5	454.1	515.9
55°	301.5	303.7	305.5	308.1	313.4	319.1	327.9	338.5	359.6	390.7	436.4
57.5°	265.4	266.1	267.9	272.9	276.3	281.5	289.9	299.5	313.2	336.3	370.7
60°	240.8	240.8	244.4	246.6	251.0	256.2	262.9	272.1	284.4	303.2	331.0
62.5°	218.3	218.0	219.4	223.0	226.4	231.3	237.9	245.7	257.3	274.1	296.9
65°	185.5	184.6	187.3	188.1	191.7	196.5	201.7	210.1	219.3	231.6	251.8
67.5°	153.9	154.9	156.3	158.0	159.9	165.0	168.5	174.4	182.2	192.4	206.1
70°	136.2	136.2	136.2	137.6	140.2	142.8	146.4	151.2	158.7	167.5	179.8
72.5°	116.6	118.0	119.3	118.6	121.9	123.5	127.7	130.4	137.6	143.2	154.1
75°	91.4	91.4	91.4	93.6	95.0	96.3	98.9	101.5	105.0	112.1	117.8
77.5°	68.2	68.0	68.4	69.0	70.4	72.0	72.8	75.2	78.4	81.6	86.5
80°	52.8	53.6	54.1	54.9	54.9	55.8	56.2	59.3	61.6	63.7	66.8
82.5°	40.8	41.0	41.1	41.2	41.6	42.1	43.2	44.3	45.0	46.8	49.2
85°	23.8	23.3	23.3	24.2	23.8	23.8	24.6	25.5	25.5	25.9	27.2
87.5°	15.8	15.8	16.1	15.8	15.8	15.9	15.5	15.6	16.1	16.6	16.8
90°	33.0	33.0	33.0	33.0	33.0	32.0	30.0	32.0	33.0	34.0	33.0
92.5°	55.4	57.0	56.2	59.4	60.2	66.4	74.8	87.2	109.9	130.0	128.2
95°	114.0	113.0	116.1	124.0	137.0	159.0	201.0	262.1	343.1	392.1	347.1
97.5°	224.5	232.8	247.5	272.1	319.9	392.1	500.3	611.5	702.1	669.3	504.1
100°	358.1	376.1	405.1	448.1	531.1	652.1	789.2	913.2	934.2	790.1	544.1
102.5°	630.2	654.5	690.8	764.1	854.4	982.6	1082.8	1110.9	1020.6	794.2	528.9
105°	1127.2	1141.3	1184.2	1246.2	1308.3	1341.3	1328.3	1215.2	1007.2	741.1	499.1
107.5°	1439.9	1458.4	1467.1	1470.5	1462.7	1414.3	1310.3	1140.1	919.4	684.3	484.3
110°	1534.3	1535.3	1526.3	1507.3	1464.3	1382.2	1254.2	1075.2	864.2	657.1	481.1



TEST NUMBER: P331368-935  
 CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1532.7	1527.3	1510.3	1478.5	1418.7	1324.6	1187.8	1016.0	825.8	639.6	481.9
115°	1483.3	1474.3	1448.3	1402.3	1331.3	1228.2	1097.3	943.2	778.2	620.1	486.1
117.5°	1395.1	1387.5	1360.0	1311.5	1239.1	1142.5	1023.6	888.4	748.1	610.7	493.3
120°	1338.3	1328.3	1299.2	1252.2	1182.2	1091.2	985.2	861.2	732.1	605.1	498.1
122.5°	1279.0	1270.7	1244.8	1198.6	1135.8	1053.6	953.2	839.6	718.5	601.9	503.7
125°	1203.2	1195.2	1170.3	1132.2	1074.2	999.2	911.2	808.1	699.1	596.2	512.1
127.5°	1136.9	1130.4	1108.8	1073.2	1022.6	953.4	870.4	777.1	681.1	592.7	520.7
130°	1099.2	1091.2	1071.3	1037.2	988.2	922.2	843.2	757.2	669.2	591.1	527.1
132.5°	1060.0	1052.8	1034.4	1000.4	952.2	890.2	817.6	738.0	659.5	590.3	533.5
135°	997.2	993.2	975.2	942.2	899.1	843.2	777.1	711.1	646.1	589.1	541.1
137.5°	935.6	929.6	913.8	885.4	846.2	797.4	744.9	689.7	636.7	588.9	547.9
140°	893.2	887.2	872.2	846.2	814.2	770.2	724.2	676.1	631.1	588.1	551.1
142.5°	850.8	849.5	836.2	812.5	782.1	745.4	705.8	665.0	625.5	588.1	553.5
145°	796.2	793.2	783.2	766.1	742.2	713.2	682.2	649.1	618.1	586.1	556.1
147.5°	750.4	748.6	741.8	728.1	708.3	687.2	663.0	637.0	610.5	582.6	556.9
150°	723.2	722.1	716.2	704.1	689.1	671.1	650.1	628.1	604.1	580.1	556.1
152.5°	699.9	699.7	695.3	684.9	673.1	657.5	639.7	619.3	598.5	576.1	554.5
155°	669.2	671.1	667.1	660.1	649.1	638.1	623.1	607.1	588.1	569.1	552.1
157.5°	642.9	642.9	641.1	635.3	627.5	618.9	606.3	592.9	578.3	561.9	547.5
160°	626.1	626.1	625.1	620.1	613.1	606.1	595.1	584.1	571.1	557.2	545.1
162.5°	610.1	610.9	609.9	606.5	599.5	594.1	584.7	575.3	564.7	553.1	542.7
165°	587.1	588.1	588.1	584.1	580.1	576.1	569.1	562.1	554.1	545.1	538.1
167.5°	565.9	567.1	567.3	565.1	563.4	559.7	554.9	549.5	543.7	538.1	533.5
170°	553.1	555.1	556.1	553.1	552.1	550.1	546.1	543.1	538.1	534.1	531.1
172.5°	542.7	543.9	544.9	543.5	542.5	541.3	538.1	535.9	532.5	529.3	527.9
175°	529.1	531.1	532.1	531.1	531.1	530.1	529.1	528.1	525.1	524.1	523.1
177.5°	520.9	522.5	523.3	523.3	523.3	523.3	522.5	522.5	520.9	520.1	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1173.5	1170.7	1169.0	1162.6	1157.0	1151.4	1149.6	1150.3	1142.6	1135.2	1132.0
5°	1219.3	1210.5	1202.1	1190.2	1176.2	1160.8	1152.9	1146.7	1131.4	1114.7	1105.0
7.5°	1260.2	1247.7	1231.6	1209.2	1188.8	1164.6	1149.2	1135.6	1113.0	1089.5	1075.0
10°	1285.2	1268.0	1247.3	1220.1	1195.1	1165.6	1145.0	1124.3	1097.9	1069.8	1052.2
12.5°	1306.7	1283.5	1263.2	1228.2	1198.6	1161.7	1137.2	1108.1	1080.4	1047.0	1029.8
15°	1357.7	1315.1	1276.3	1236.8	1200.3	1148.9	1121.7	1082.5	1046.0	1004.8	985.0
17.5°	1397.1	1349.3	1288.3	1238.0	1195.5	1138.6	1098.5	1051.7	1008.6	961.3	934.4
20°	1419.7	1364.7	1299.2	1239.5	1188.4	1123.4	1080.0	1032.0	981.5	928.2	899.2
22.5°	1433.0	1375.3	1310.5	1234.2	1174.4	1111.1	1056.4	1003.8	952.6	895.3	864.8
25°	1437.3	1384.5	1316.0	1229.8	1156.8	1085.2	1019.3	968.3	906.3	852.6	808.3
27.5°	1416.3	1378.5	1312.6	1221.5	1136.5	1052.7	979.3	921.5	856.1	797.9	753.3
30°	1390.7	1368.6	1304.5	1213.1	1120.3	1030.3	949.3	883.9	818.8	759.9	714.2
32.5°	1350.9	1346.2	1289.8	1201.1	1103.1	1001.8	918.1	851.9	779.8	721.9	678.4
35°	1272.9	1294.0	1258.4	1174.4	1070.7	961.2	870.7	795.1	720.4	665.0	624.1
37.5°	1168.3	1220.6	1211.3	1135.3	1026.9	917.1	817.2	738.1	666.9	611.1	570.9
40°	1096.1	1163.0	1172.7	1105.4	996.0	883.0	777.1	698.4	629.0	578.0	537.5
42.5°	1018.8	1096.9	1123.4	1069.5	962.2	847.1	741.2	659.7	591.0	541.4	505.6
45°	889.2	992.5	1040.3	1009.6	905.9	788.1	679.1	596.4	534.0	487.4	459.8
47.5°	767.9	880.8	945.2	934.4	843.2	726.5	618.8	539.5	478.7	441.5	416.7
50°	682.2	798.1	876.0	879.5	798.1	682.6	574.5	499.7	443.9	409.2	389.0
52.5°	607.6	718.3	803.2	821.8	747.9	636.9	534.8	460.4	411.2	379.3	361.2
55°	510.3	603.9	697.9	732.3	672.9	567.4	472.9	407.4	361.3	339.3	323.5
57.5°	424.2	502.3	589.2	627.1	590.5	500.2	411.6	354.7	317.3	298.0	285.9
60°	378.8	440.4	517.7	563.0	531.4	451.0	373.6	319.5	288.8	271.6	260.2
62.5°	336.7	391.2	456.6	498.0	480.8	404.9	335.6	287.9	261.3	245.2	237.0
65°	277.8	320.9	371.4	409.7	398.2	340.6	284.0	243.1	222.0	209.2	202.6
67.5°	228.8	259.8	294.9	328.4	319.2	278.4	232.9	201.0	185.3	174.4	170.4
70°	197.8	221.5	252.7	279.6	272.1	238.7	202.6	175.4	161.8	152.5	148.5
72.5°	168.2	187.8	211.5	233.5	228.4	200.7	170.7	150.1	139.6	131.0	127.8
75°	127.0	142.0	156.4	171.0	169.6	148.1	130.5	114.7	106.3	99.8	98.4
77.5°	93.8	102.1	112.0	120.6	118.2	105.9	92.1	83.1	76.9	72.5	71.8
80°	71.6	76.5	83.5	89.6	86.6	81.3	70.3	63.7	59.3	54.9	53.2
82.5°	51.9	56.8	61.0	64.3	62.0	57.1	50.3	45.8	43.1	40.2	39.4
85°	27.2	29.9	31.7	32.5	31.7	28.6	25.5	23.8	21.5	20.2	19.8
87.5°	15.9	14.6	13.5	13.7	12.2	11.8	9.6	7.9	8.2	8.6	8.4
90°	27.0	20.0	15.0	12.0	10.0	8.0	4.0	1.0	4.0	8.0	10.0
92.5°	99.8	68.0	45.4	36.0	29.2	24.8	17.6	12.2	17.6	24.8	29.2
95°	231.0	144.0	98.0	74.0	58.0	49.0	39.0	35.0	39.0	49.0	58.0
97.5°	311.3	190.0	132.2	105.0	86.6	73.0	62.4	57.0	62.4	73.0	86.6
100°	328.0	206.0	153.0	125.0	105.0	89.0	80.0	77.0	80.0	89.0	105.0
102.5°	328.9	220.4	171.4	143.4	122.6	106.6	97.6	95.4	97.6	106.6	122.6
105°	334.1	245.0	198.0	170.0	148.0	133.0	126.1	122.0	126.1	133.0	148.0
107.5°	347.8	270.3	224.6	196.5	174.6	160.8	154.0	150.8	154.0	160.8	174.6
110°	359.0	287.1	243.1	214.0	193.0	180.0	174.0	170.0	174.0	180.0	193.0





TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	371.1	303.1	260.6	230.8	210.6	198.5	191.7	187.6	191.7	198.5	210.6
115°	389.1	328.0	285.1	258.0	238.1	226.0	220.1	215.1	220.1	226.0	238.1
117.5°	408.3	351.0	311.3	283.3	264.1	253.5	247.5	243.5	247.5	253.5	264.1
120°	421.1	367.0	328.0	300.1	280.1	271.0	265.0	261.1	265.0	271.0	280.1
122.5°	432.3	382.3	345.7	316.8	296.9	287.1	281.0	277.8	281.0	287.1	296.9
125°	450.1	405.1	369.1	341.0	321.1	309.1	303.1	300.1	303.1	309.1	321.1
127.5°	466.7	426.3	391.2	362.5	343.3	330.1	321.7	317.6	321.7	330.1	343.3
130°	477.1	439.1	404.1	376.1	356.1	342.1	332.1	328.0	332.1	342.1	356.1
132.5°	487.5	450.3	416.9	388.9	368.1	353.3	342.5	337.7	342.5	353.3	368.1
135°	501.1	466.1	434.1	406.0	383.1	368.1	356.1	352.1	356.1	368.1	383.1
137.5°	511.5	478.9	447.3	421.3	398.5	382.5	370.5	365.7	370.5	382.5	398.5
140°	517.1	486.1	456.1	430.1	408.1	392.1	380.0	376.1	380.0	392.1	408.1
142.5°	521.9	491.7	462.5	438.1	416.9	400.9	389.7	386.5	389.7	400.9	416.9
145°	528.1	500.1	473.1	451.1	431.1	416.1	406.0	402.1	406.0	416.1	431.1
147.5°	531.5	506.9	481.5	461.9	445.3	431.4	421.9	418.9	421.9	431.4	445.3
150°	533.1	510.1	487.1	469.1	454.1	441.1	433.1	430.1	433.1	441.1	454.1
152.5°	533.9	513.3	492.7	476.3	462.1	450.6	442.7	441.3	442.7	450.6	462.1
155°	535.1	518.1	501.1	486.1	475.1	464.1	458.1	457.1	458.1	464.1	475.1
157.5°	535.1	521.5	507.1	494.5	485.7	476.1	471.3	470.3	471.3	476.1	485.7
160°	535.1	523.1	511.1	500.1	492.1	484.1	480.1	479.1	480.1	484.1	492.1
162.5°	534.3	523.9	513.5	504.9	497.7	491.3	487.3	487.9	487.3	491.3	497.7
165°	532.1	525.1	516.1	510.1	505.1	499.1	497.1	498.1	497.1	499.1	505.1
167.5°	530.7	524.9	518.3	514.5	510.9	507.1	505.3	506.5	505.3	507.1	510.9
170°	529.1	524.1	519.1	516.1	514.1	511.1	510.1	512.1	510.1	511.1	514.1
172.5°	526.7	523.3	519.9	517.7	516.5	513.5	514.1	515.3	514.1	513.5	516.5
175°	524.1	522.1	520.1	519.1	519.1	517.1	518.1	519.1	518.1	517.1	519.1
177.5°	522.5	520.9	520.1	520.1	520.1	518.5	519.3	520.9	519.3	518.5	520.1
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1128.5	1126.4	1119.0	1115.2	1108.8	1102.9	1099.0	1100.8	1102.2	1101.5	1100.4
5°	1096.1	1087.8	1075.0	1064.1	1056.2	1041.6	1035.5	1032.4	1029.8	1026.7	1023.6
7.5°	1057.7	1044.5	1026.2	1010.6	995.7	977.8	967.5	961.3	955.0	948.0	941.9
10°	1030.3	1011.8	992.5	970.4	952.9	936.6	922.1	912.5	903.7	895.4	889.2
12.5°	1001.4	980.2	956.2	926.2	906.8	883.6	881.3	864.3	850.6	845.4	838.2
15°	955.5	925.7	895.4	859.7	844.3	823.2	810.0	796.9	785.0	776.6	774.5
17.5°	903.4	864.7	834.6	809.0	783.8	762.2	750.0	739.4	729.7	718.5	717.0
20°	863.7	830.3	797.3	774.9	749.0	726.9	712.0	701.5	693.1	686.6	680.8
22.5°	826.0	789.5	759.3	734.8	709.2	691.5	679.7	669.5	662.5	655.2	649.9
25°	765.7	737.1	704.1	676.4	655.3	643.9	634.2	625.4	621.0	616.2	610.1
27.5°	712.8	681.1	650.2	628.8	610.3	600.1	593.2	587.3	583.2	580.3	576.9
30°	675.5	643.4	619.3	598.2	582.8	572.7	568.3	564.8	560.0	558.2	556.5
32.5°	639.7	610.8	590.1	571.8	557.2	550.5	546.5	543.4	539.6	537.8	534.3
35°	588.9	564.8	544.6	534.4	522.6	516.9	513.8	509.4	505.9	504.1	503.7
37.5°	541.2	520.2	507.0	494.0	489.0	485.4	481.2	478.2	477.2	476.9	476.5
40°	510.3	493.2	481.3	470.7	468.6	463.2	459.8	457.1	457.1	457.5	457.1
42.5°	482.2	466.7	456.3	447.2	444.6	441.4	437.9	437.7	438.5	440.0	438.5
45°	439.5	428.5	421.0	416.6	411.8	408.7	408.3	409.7	410.1	410.5	411.8
47.5°	400.3	393.0	386.2	381.4	379.3	378.8	378.2	380.6	382.6	383.4	385.5
50°	377.1	368.8	363.1	360.0	358.2	357.3	358.2	360.8	362.6	364.8	366.1
52.5°	351.1	345.2	341.2	338.9	338.2	338.7	338.9	341.9	344.7	345.4	346.1
55°	315.1	310.7	309.9	305.9	307.6	307.2	309.4	311.2	313.8	316.4	316.9
57.5°	279.3	275.8	273.4	273.7	274.2	276.2	278.0	281.1	284.0	286.7	287.0
60°	255.4	253.6	252.3	252.3	253.1	255.8	258.0	261.1	262.9	264.6	265.9
62.5°	233.6	231.8	230.5	231.2	233.5	235.1	237.6	239.3	241.0	242.8	243.4
65°	199.1	198.2	199.6	200.4	200.9	203.0	206.1	207.4	209.2	210.1	213.2
67.5°	167.4	167.6	167.4	168.6	171.2	171.7	174.6	177.6	178.0	179.7	181.7
70°	145.9	146.8	147.7	148.5	150.8	151.6	153.9	155.2	156.9	158.3	159.5
72.5°	126.2	126.4	127.3	127.1	129.0	130.9	132.8	134.1	135.8	137.5	138.8
75°	97.1	97.1	98.0	98.4	100.7	102.9	102.4	103.3	105.0	106.8	107.7
77.5°	70.9	70.0	70.9	71.4	72.1	74.0	74.3	75.5	77.5	76.9	77.9
80°	54.1	52.8	54.1	54.5	54.5	56.7	56.7	57.6	58.9	57.6	58.9
82.5°	38.6	38.0	38.9	39.0	39.7	39.8	40.6	40.7	42.0	41.4	42.0
85°	19.4	18.9	19.4	18.9	19.4	19.8	19.8	19.4	19.4	20.2	18.9
87.5°	8.4	8.6	9.3	10.7	11.5	11.4	10.8	10.6	10.2	9.9	10.2
90°	12.0	15.0	20.0	27.0	33.0	34.0	33.0	32.0	30.0	32.0	33.0
92.5°	36.0	45.4	68.0	99.8	128.2	130.0	109.9	87.2	74.8	66.4	60.2
95°	74.0	98.0	144.0	231.0	347.1	392.1	343.1	262.1	201.0	159.0	137.0
97.5°	105.0	132.2	190.0	311.3	504.1	669.3	702.1	611.5	500.3	392.1	319.9
100°	125.0	153.0	206.0	328.0	544.1	790.1	934.2	913.2	789.2	652.1	531.1
102.5°	143.4	171.4	220.4	328.9	528.9	794.2	1020.6	1110.9	1082.8	982.6	854.4
105°	170.0	198.0	245.0	334.1	499.1	741.1	1007.2	1215.2	1328.3	1341.3	1308.3
107.5°	196.5	224.6	270.3	347.8	484.3	684.3	919.4	1140.1	1310.3	1414.3	1462.7
110°	214.0	243.1	287.1	359.0	481.1	657.1	864.2	1075.2	1254.2	1382.2	1464.3



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.8	260.6	303.1	371.1	481.9	639.6	825.8	1016.0	1187.8	1324.6	1418.7
115°	258.0	285.1	328.0	389.1	486.1	620.1	778.2	943.2	1097.3	1228.2	1331.3
117.5°	283.3	311.3	351.0	408.3	493.3	610.7	748.1	888.4	1023.6	1142.5	1239.1
120°	300.1	328.0	367.0	421.1	498.1	605.1	732.1	861.2	985.2	1091.2	1182.2
122.5°	316.8	345.7	382.3	432.3	503.7	601.9	718.5	839.6	953.2	1053.6	1135.8
125°	341.0	369.1	405.1	450.1	512.1	596.2	699.1	808.1	911.2	999.2	1074.2
127.5°	362.5	391.2	426.3	466.7	520.7	592.7	681.1	777.1	870.4	953.4	1022.6
130°	376.1	404.1	439.1	477.1	527.1	591.1	669.2	757.2	843.2	922.2	988.2
132.5°	388.9	416.9	450.3	487.5	533.5	590.3	659.5	738.0	817.6	890.2	952.2
135°	406.0	434.1	466.1	501.1	541.1	589.1	646.1	711.1	777.1	843.2	899.1
137.5°	421.3	447.3	478.9	511.5	547.9	588.9	636.7	689.7	744.9	797.4	846.2
140°	430.1	456.1	486.1	517.1	551.1	588.1	631.1	676.1	724.2	770.2	814.2
142.5°	438.1	462.5	491.7	521.9	553.5	588.1	625.5	665.0	705.8	745.4	782.1
145°	451.1	473.1	500.1	528.1	556.1	586.1	618.1	649.1	682.2	713.2	742.2
147.5°	461.9	481.5	506.9	531.5	556.9	582.6	610.5	637.0	663.0	687.2	708.3
150°	469.1	487.1	510.1	533.1	556.1	580.1	604.1	628.1	650.1	671.1	689.1
152.5°	476.3	492.7	513.3	533.9	554.5	576.1	598.5	619.3	639.7	657.5	673.1
155°	486.1	501.1	518.1	535.1	552.1	569.1	588.1	607.1	623.1	638.1	649.1
157.5°	494.5	507.1	521.5	535.1	547.5	561.9	578.3	592.9	606.3	618.9	627.5
160°	500.1	511.1	523.1	535.1	545.1	557.2	571.1	584.1	595.1	606.1	613.1
162.5°	504.9	513.5	523.9	534.3	542.7	553.1	564.7	575.3	584.7	594.1	599.5
165°	510.1	516.1	525.1	532.1	538.1	545.1	554.1	562.1	569.1	576.1	580.1
167.5°	514.5	518.3	524.9	530.7	533.5	538.1	543.7	549.5	554.9	559.7	563.4
170°	516.1	519.1	524.1	529.1	531.1	534.1	538.1	543.1	546.1	550.1	552.1
172.5°	517.7	519.9	523.3	526.7	527.9	529.3	532.5	535.9	538.1	541.3	542.5
175°	519.1	520.1	522.1	524.1	523.1	524.1	525.1	528.1	529.1	530.1	531.1
177.5°	520.1	520.1	520.9	522.5	520.9	520.1	520.9	522.5	522.5	523.3	523.3
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1096.9	1096.1	1096.1	1093.0	1096.1	1096.1	1096.9	1100.4	1101.5	1102.2	1100.8
5°	1017.5	1016.2	1014.0	1016.2	1014.0	1016.2	1017.5	1023.6	1026.7	1029.8	1032.4
7.5°	939.0	933.8	933.0	927.7	933.0	933.8	939.0	941.9	948.0	955.0	961.3
10°	881.7	878.1	877.7	869.4	877.7	878.1	881.7	889.2	895.4	903.7	912.5
12.5°	838.1	829.7	831.3	826.5	831.3	829.7	838.1	838.2	845.4	850.6	864.3
15°	762.6	762.6	760.8	753.4	760.8	762.6	762.6	774.5	776.6	785.0	796.9
17.5°	708.3	707.5	703.3	705.3	703.3	707.5	708.3	717.0	718.5	729.7	739.4
20°	676.0	673.4	668.0	668.0	668.0	673.4	676.0	680.8	686.6	693.1	701.5
22.5°	645.4	645.2	639.6	641.4	639.6	645.2	645.4	649.9	655.2	662.5	669.5
25°	609.6	606.1	603.5	604.8	603.5	606.1	609.6	610.1	616.2	621.0	625.4
27.5°	575.7	573.8	573.6	570.0	573.6	573.8	575.7	576.9	580.3	583.2	587.3
30°	556.0	551.6	552.5	550.3	552.5	551.6	556.0	556.5	558.2	560.0	564.8
32.5°	533.5	531.9	531.1	529.2	531.1	531.9	533.5	534.3	537.8	539.6	543.4
35°	502.8	503.3	501.1	502.0	501.1	503.3	502.8	503.7	504.1	505.9	509.4
37.5°	476.0	477.4	476.4	476.6	476.4	477.4	476.0	476.5	476.9	477.2	478.2
40°	458.4	458.4	458.4	459.8	458.4	458.4	458.4	457.1	457.5	457.1	457.1
42.5°	441.5	440.8	440.1	440.1	440.1	440.8	441.5	438.5	440.0	438.5	437.7
45°	412.7	414.1	414.5	412.2	414.5	414.1	412.7	411.8	410.5	410.1	409.7
47.5°	386.6	386.8	386.6	388.6	386.6	386.8	386.6	385.5	383.4	382.6	380.6
50°	368.3	367.5	368.3	367.5	368.3	367.5	368.3	366.1	364.8	362.6	360.8
52.5°	349.0	349.1	348.6	348.4	348.6	349.1	349.0	346.1	345.4	344.7	341.9
55°	318.7	319.5	319.1	319.1	319.1	319.5	318.7	316.9	316.4	313.8	311.2
57.5°	287.3	288.1	288.7	286.7	288.7	288.1	287.3	287.0	286.7	284.0	281.1
60°	265.4	267.7	267.3	266.4	267.3	267.7	265.4	265.9	264.6	262.9	261.1
62.5°	245.5	246.2	246.2	246.0	246.2	246.2	245.5	243.4	242.8	241.0	239.3
65°	214.5	215.3	214.0	215.3	214.0	215.3	214.5	213.2	210.1	209.2	207.4
67.5°	181.2	181.4	182.4	183.0	182.4	181.4	181.2	181.7	179.7	178.0	177.6
70°	160.4	160.0	161.3	162.6	161.3	160.0	160.4	159.5	158.3	156.9	155.2
72.5°	138.6	139.6	139.1	140.1	139.1	139.6	138.6	138.8	137.5	135.8	134.1
75°	106.8	108.1	107.7	109.0	107.7	108.1	106.8	107.7	106.8	105.0	103.3
77.5°	77.1	77.3	77.1	77.9	77.1	77.3	77.1	77.9	76.9	77.5	75.5
80°	58.9	58.0	57.2	58.9	57.2	58.0	58.9	58.9	57.6	58.9	57.6
82.5°	41.0	41.5	40.6	40.6	40.6	41.5	41.0	42.0	41.4	42.0	40.7
85°	18.9	18.4	17.6	17.6	17.6	18.4	18.9	18.9	20.2	19.4	19.4
87.5°	10.2	9.7	9.7	9.4	9.7	9.7	10.2	10.2	9.9	10.2	10.6
90°	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0	32.0	30.0	32.0
92.5°	59.4	56.2	57.0	55.4	57.0	56.2	59.4	60.2	66.4	74.8	87.2
95°	124.0	116.1	113.0	114.0	113.0	116.1	124.0	137.0	159.0	201.0	262.1
97.5°	272.1	247.5	232.8	224.5	232.8	247.5	272.1	319.9	392.1	500.3	611.5
100°	448.1	405.1	376.1	358.1	376.1	405.1	448.1	531.1	652.1	789.2	913.2
102.5°	764.1	690.8	654.5	630.2	654.5	690.8	764.1	854.4	982.6	1082.8	1110.9
105°	1246.2	1184.2	1141.3	1127.2	1141.3	1184.2	1246.2	1308.3	1341.3	1328.3	1215.2
107.5°	1470.5	1467.1	1458.4	1439.9	1458.4	1467.1	1470.5	1462.7	1414.3	1310.3	1140.1
110°	1507.3	1526.3	1535.3	1534.3	1535.3	1526.3	1507.3	1464.3	1382.2	1254.2	1075.2



TEST NUMBER: P331368-935  
 CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1478.5	1510.3	1527.3	1532.7	1527.3	1510.3	1478.5	1418.7	1324.6	1187.8	1016.0
115°	1402.3	1448.3	1474.3	1483.3	1474.3	1448.3	1402.3	1331.3	1228.2	1097.3	943.2
117.5°	1311.5	1360.0	1387.5	1395.1	1387.5	1360.0	1311.5	1239.1	1142.5	1023.6	888.4
120°	1252.2	1299.2	1328.3	1338.3	1328.3	1299.2	1252.2	1182.2	1091.2	985.2	861.2
122.5°	1198.6	1244.8	1270.7	1279.0	1270.7	1244.8	1198.6	1135.8	1053.6	953.2	839.6
125°	1132.2	1170.3	1195.2	1203.2	1195.2	1170.3	1132.2	1074.2	999.2	911.2	808.1
127.5°	1073.2	1108.8	1130.4	1136.9	1130.4	1108.8	1073.2	1022.6	953.4	870.4	777.1
130°	1037.2	1071.3	1091.2	1099.2	1091.2	1071.3	1037.2	988.2	922.2	843.2	757.2
132.5°	1000.4	1034.4	1052.8	1060.0	1052.8	1034.4	1000.4	952.2	890.2	817.6	738.0
135°	942.2	975.2	993.2	997.2	993.2	975.2	942.2	899.1	843.2	777.1	711.1
137.5°	885.4	913.8	929.6	935.6	929.6	913.8	885.4	846.2	797.4	744.9	689.7
140°	846.2	872.2	887.2	893.2	887.2	872.2	846.2	814.2	770.2	724.2	676.1
142.5°	812.5	836.2	849.5	850.8	849.5	836.2	812.5	782.1	745.4	705.8	665.0
145°	766.1	783.2	793.2	796.2	793.2	783.2	766.1	742.2	713.2	682.2	649.1
147.5°	728.1	741.8	748.6	750.4	748.6	741.8	728.1	708.3	687.2	663.0	637.0
150°	704.1	716.2	722.1	723.2	722.1	716.2	704.1	689.1	671.1	650.1	628.1
152.5°	684.9	695.3	699.7	699.9	699.7	695.3	684.9	673.1	657.5	639.7	619.3
155°	660.1	667.1	671.1	669.2	671.1	667.1	660.1	649.1	638.1	623.1	607.1
157.5°	635.3	641.1	642.9	642.9	642.9	641.1	635.3	627.5	618.9	606.3	592.9
160°	620.1	625.1	626.1	626.1	626.1	625.1	620.1	613.1	606.1	595.1	584.1
162.5°	606.5	609.9	610.9	610.1	610.9	609.9	606.5	599.5	594.1	584.7	575.3
165°	584.1	588.1	588.1	587.1	588.1	588.1	584.1	580.1	576.1	569.1	562.1
167.5°	565.1	567.3	567.1	565.9	567.1	567.3	565.1	563.4	559.7	554.9	549.5
170°	553.1	556.1	555.1	553.1	555.1	556.1	553.1	552.1	550.1	546.1	543.1
172.5°	543.5	544.9	543.9	542.7	543.9	544.9	543.5	542.5	541.3	538.1	535.9
175°	531.1	532.1	531.1	529.1	531.1	532.1	531.1	531.1	530.1	529.1	528.1
177.5°	523.3	523.3	522.5	520.9	522.5	523.3	523.3	523.3	523.3	522.5	522.5
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1099.0	1102.9	1108.8	1115.2	1119.0	1126.4	1128.5	1132.0	1135.2	1142.6	1150.3
5°	1035.5	1041.6	1056.2	1064.1	1075.0	1087.8	1096.1	1105.0	1114.7	1131.4	1146.7
7.5°	967.5	977.8	995.7	1010.6	1026.2	1044.5	1057.7	1075.0	1089.5	1113.0	1135.6
10°	922.1	936.6	952.9	970.4	992.5	1011.8	1030.3	1052.2	1069.8	1097.9	1124.3
12.5°	881.3	883.6	906.8	926.2	956.2	980.2	1001.4	1029.8	1047.0	1080.4	1108.1
15°	810.0	823.2	844.3	859.7	895.4	925.7	955.5	985.0	1004.8	1046.0	1082.5
17.5°	750.0	762.2	783.8	809.0	834.6	864.7	903.4	934.4	961.3	1008.6	1051.7
20°	712.0	726.9	749.0	774.9	797.3	830.3	863.7	899.2	928.2	981.5	1032.0
22.5°	679.7	691.5	709.2	734.8	759.3	789.5	826.0	864.8	895.3	952.6	1003.8
25°	634.2	643.9	655.3	676.4	704.1	737.1	765.7	808.3	852.6	906.3	968.3
27.5°	593.2	600.1	610.3	628.8	650.2	681.1	712.8	753.3	797.9	856.1	921.5
30°	568.3	572.7	582.8	598.2	619.3	643.4	675.5	714.2	759.9	818.8	883.9
32.5°	546.5	550.5	557.2	571.8	590.1	610.8	639.7	678.4	721.9	779.8	851.9
35°	513.8	516.9	522.6	534.4	544.6	564.8	588.9	624.1	665.0	720.4	795.1
37.5°	481.2	485.4	489.0	494.0	507.0	520.2	541.2	570.9	611.1	666.9	738.1
40°	459.8	463.2	468.6	470.7	481.3	493.2	510.3	537.5	578.0	629.0	698.4
42.5°	437.9	441.4	444.6	447.2	456.3	466.7	482.2	505.6	541.4	591.0	659.7
45°	408.3	408.7	411.8	416.6	421.0	428.5	439.5	459.8	487.4	534.0	596.4
47.5°	378.2	378.8	379.3	381.4	386.2	393.0	400.3	416.7	441.5	478.7	539.5
50°	358.2	357.3	358.2	360.0	363.1	368.8	377.1	389.0	409.2	443.9	499.7
52.5°	338.9	338.7	338.2	338.9	341.2	345.2	351.1	361.2	379.3	411.2	460.4
55°	309.4	307.2	307.6	305.9	309.9	310.7	315.1	323.5	339.3	361.3	407.4
57.5°	278.0	276.2	274.2	273.7	273.4	275.8	279.3	285.9	298.0	317.3	354.7
60°	258.0	255.8	253.1	252.3	252.3	253.6	255.4	260.2	271.6	288.8	319.5
62.5°	237.6	235.1	233.5	231.2	230.5	231.8	233.6	237.0	245.2	261.3	287.9
65°	206.1	203.0	200.9	200.4	199.6	198.2	199.1	202.6	209.2	222.0	243.1
67.5°	174.6	171.7	171.2	168.6	167.4	167.6	167.4	170.4	174.4	185.3	201.0
70°	153.9	151.6	150.8	148.5	147.7	146.8	145.9	148.5	152.5	161.8	175.4
72.5°	132.8	130.9	129.0	127.1	127.3	126.4	126.2	127.8	131.0	139.6	150.1
75°	102.4	102.9	100.7	98.4	98.0	97.1	97.1	98.4	99.8	106.3	114.7
77.5°	74.3	74.0	72.1	71.4	70.9	70.0	70.9	71.8	72.5	76.9	83.1
80°	56.7	56.7	54.5	54.5	54.1	52.8	54.1	53.2	54.9	59.3	63.7
82.5°	40.6	39.8	39.7	39.0	38.9	38.0	38.6	39.4	40.2	43.1	45.8
85°	19.8	19.8	19.4	18.9	19.4	18.9	19.4	19.8	20.2	21.5	23.8
87.5°	10.8	11.4	11.5	10.7	9.3	8.6	8.4	8.4	8.6	8.2	7.9
90°	33.0	34.0	33.0	27.0	20.0	15.0	12.0	10.0	8.0	4.0	1.0
92.5°	109.9	130.0	128.2	99.8	68.0	45.4	36.0	29.2	24.8	17.6	12.2
95°	343.1	392.1	347.1	231.0	144.0	98.0	74.0	58.0	49.0	39.0	35.0
97.5°	702.1	669.3	504.1	311.3	190.0	132.2	105.0	86.6	73.0	62.4	57.0
100°	934.2	790.1	544.1	328.0	206.0	153.0	125.0	105.0	89.0	80.0	77.0
102.5°	1020.6	794.2	528.9	328.9	220.4	171.4	143.4	122.6	106.6	97.6	95.4
105°	1007.2	741.1	499.1	334.1	245.0	198.0	170.0	148.0	133.0	126.1	122.0
107.5°	919.4	684.3	484.3	347.8	270.3	224.6	196.5	174.6	160.8	154.0	150.8
110°	864.2	657.1	481.1	359.0	287.1	243.1	214.0	193.0	180.0	174.0	170.0



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	825.8	639.6	481.9	371.1	303.1	260.6	230.8	210.6	198.5	191.7	187.6
115°	778.2	620.1	486.1	389.1	328.0	285.1	258.0	238.1	226.0	220.1	215.1
117.5°	748.1	610.7	493.3	408.3	351.0	311.3	283.3	264.1	253.5	247.5	243.5
120°	732.1	605.1	498.1	421.1	367.0	328.0	300.1	280.1	271.0	265.0	261.1
122.5°	718.5	601.9	503.7	432.3	382.3	345.7	316.8	296.9	287.1	281.0	277.8
125°	699.1	596.2	512.1	450.1	405.1	369.1	341.0	321.1	309.1	303.1	300.1
127.5°	681.1	592.7	520.7	466.7	426.3	391.2	362.5	343.3	330.1	321.7	317.6
130°	669.2	591.1	527.1	477.1	439.1	404.1	376.1	356.1	342.1	332.1	328.0
132.5°	659.5	590.3	533.5	487.5	450.3	416.9	388.9	368.1	353.3	342.5	337.7
135°	646.1	589.1	541.1	501.1	466.1	434.1	406.0	383.1	368.1	356.1	352.1
137.5°	636.7	588.9	547.9	511.5	478.9	447.3	421.3	398.5	382.5	370.5	365.7
140°	631.1	588.1	551.1	517.1	486.1	456.1	430.1	408.1	392.1	380.0	376.1
142.5°	625.5	588.1	553.5	521.9	491.7	462.5	438.1	416.9	400.9	389.7	386.5
145°	618.1	586.1	556.1	528.1	500.1	473.1	451.1	431.1	416.1	406.0	402.1
147.5°	610.5	582.6	556.9	531.5	506.9	481.5	461.9	445.3	431.4	421.9	418.9
150°	604.1	580.1	556.1	533.1	510.1	487.1	469.1	454.1	441.1	433.1	430.1
152.5°	598.5	576.1	554.5	533.9	513.3	492.7	476.3	462.1	450.6	442.7	441.3
155°	588.1	569.1	552.1	535.1	518.1	501.1	486.1	475.1	464.1	458.1	457.1
157.5°	578.3	561.9	547.5	535.1	521.5	507.1	494.5	485.7	476.1	471.3	470.3
160°	571.1	557.2	545.1	535.1	523.1	511.1	500.1	492.1	484.1	480.1	479.1
162.5°	564.7	553.1	542.7	534.3	523.9	513.5	504.9	497.7	491.3	487.3	487.9
165°	554.1	545.1	538.1	532.1	525.1	516.1	510.1	505.1	499.1	497.1	498.1
167.5°	543.7	538.1	533.5	530.7	524.9	518.3	514.5	510.9	507.1	505.3	506.5
170°	538.1	534.1	531.1	529.1	524.1	519.1	516.1	514.1	511.1	510.1	512.1
172.5°	532.5	529.3	527.9	526.7	523.3	519.9	517.7	516.5	513.5	514.1	515.3
175°	525.1	524.1	523.1	524.1	522.1	520.1	519.1	519.1	517.1	518.1	519.1
177.5°	520.9	520.1	520.9	522.5	520.9	520.1	520.1	520.1	518.5	519.3	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331368-935  
 CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1149.6	1151.4	1157.0	1162.6	1169.0	1170.7	1173.5	1171.0	1170.4	1177.1	1182.0
5°	1152.9	1160.8	1176.2	1190.2	1202.1	1210.5	1219.3	1222.8	1229.3	1238.5	1250.0
7.5°	1149.2	1164.6	1188.8	1209.2	1231.6	1247.7	1260.2	1270.9	1283.9	1301.4	1320.5
10°	1145.0	1165.6	1195.1	1220.1	1247.3	1268.0	1285.2	1301.8	1321.2	1345.4	1370.5
12.5°	1137.2	1161.7	1198.6	1228.2	1263.2	1283.5	1306.7	1342.6	1363.4	1397.1	1432.4
15°	1121.7	1148.9	1200.3	1236.8	1276.3	1315.1	1357.7	1392.0	1426.2	1446.0	1495.7
17.5°	1098.5	1138.6	1195.5	1238.0	1288.3	1349.3	1397.1	1436.0	1475.6	1507.7	1532.6
20°	1080.0	1123.4	1188.4	1239.5	1299.2	1364.7	1419.7	1459.2	1493.5	1520.4	1535.7
22.5°	1056.4	1111.1	1174.4	1234.2	1310.5	1375.3	1433.0	1464.1	1492.8	1505.9	1511.8
25°	1019.3	1085.2	1156.8	1229.8	1316.0	1384.5	1437.3	1456.1	1464.5	1451.7	1430.6
27.5°	979.3	1052.7	1136.5	1221.5	1312.6	1378.5	1416.3	1413.3	1399.2	1358.0	1325.0
30°	949.3	1030.3	1120.3	1213.1	1304.5	1368.6	1390.7	1368.6	1336.6	1290.5	1243.5
32.5°	918.1	1001.8	1103.1	1201.1	1289.8	1346.2	1350.9	1313.1	1263.4	1211.0	1152.4
35°	870.7	961.2	1070.7	1174.4	1258.4	1294.0	1272.9	1206.1	1147.2	1075.6	995.5
37.5°	817.2	917.1	1026.9	1135.3	1211.3	1220.6	1168.3	1097.9	1014.9	930.7	836.5
40°	777.1	883.0	996.0	1105.4	1172.7	1163.0	1096.1	1018.8	919.9	817.1	729.6
42.5°	741.2	847.1	962.2	1069.5	1123.4	1096.9	1018.8	923.9	817.6	720.7	640.7
45°	679.1	788.1	905.9	1009.6	1040.3	992.5	889.2	783.7	679.1	598.2	534.9
47.5°	618.8	726.5	843.2	934.4	945.2	880.8	767.9	659.4	569.5	503.6	458.9
50°	574.5	682.6	798.1	879.5	876.0	798.1	682.2	578.9	503.7	450.5	420.6
52.5°	534.8	636.9	747.9	821.8	803.2	718.3	607.6	515.9	454.1	412.5	385.5
55°	472.9	567.4	672.9	732.3	697.9	603.9	510.3	436.4	390.7	359.6	338.5
57.5°	411.6	500.2	590.5	627.1	589.2	502.3	424.2	370.7	336.3	313.2	299.5
60°	373.6	451.0	531.4	563.0	517.7	440.4	378.8	331.0	303.2	284.4	272.1
62.5°	335.6	404.9	480.8	498.0	456.6	391.2	336.7	296.9	274.1	257.3	245.7
65°	284.0	340.6	398.2	409.7	371.4	320.9	277.8	251.8	231.6	219.3	210.1
67.5°	232.9	278.4	319.2	328.4	294.9	259.8	228.8	206.1	192.4	182.2	174.4
70°	202.6	238.7	272.1	279.6	252.7	221.5	197.8	179.8	167.5	158.7	151.2
72.5°	170.7	200.7	228.4	233.5	211.5	187.8	168.2	154.1	143.2	137.6	130.4
75°	130.5	148.1	169.6	171.0	156.4	142.0	127.0	117.8	112.1	105.0	101.5
77.5°	92.1	105.9	118.2	120.6	112.0	102.1	93.8	86.5	81.6	78.4	75.2
80°	70.3	81.3	86.6	89.6	83.5	76.5	71.6	66.8	63.7	61.6	59.3
82.5°	50.3	57.1	62.0	64.3	61.0	56.8	51.9	49.2	46.8	45.0	44.3
85°	25.5	28.6	31.7	32.5	31.7	29.9	27.2	27.2	25.9	25.5	25.5
87.5°	9.6	11.8	12.2	13.7	13.5	14.6	15.9	16.8	16.6	16.1	15.6
90°	4.0	8.0	10.0	12.0	15.0	20.0	27.0	33.0	34.0	33.0	32.0
92.5°	17.6	24.8	29.2	36.0	45.4	68.0	99.8	128.2	130.0	109.9	87.2
95°	39.0	49.0	58.0	74.0	98.0	144.0	231.0	347.1	392.1	343.1	262.1
97.5°	62.4	73.0	86.6	105.0	132.2	190.0	311.3	504.1	669.3	702.1	611.5
100°	80.0	89.0	105.0	125.0	153.0	206.0	328.0	544.1	790.1	934.2	913.2
102.5°	97.6	106.6	122.6	143.4	171.4	220.4	328.9	528.9	794.2	1020.6	1110.9
105°	126.1	133.0	148.0	170.0	198.0	245.0	334.1	499.1	741.1	1007.2	1215.2
107.5°	154.0	160.8	174.6	196.5	224.6	270.3	347.8	484.3	684.3	919.4	1140.1
110°	174.0	180.0	193.0	214.0	243.1	287.1	359.0	481.1	657.1	864.2	1075.2





TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	191.7	198.5	210.6	230.8	260.6	303.1	371.1	481.9	639.6	825.8	1016.0
115°	220.1	226.0	238.1	258.0	285.1	328.0	389.1	486.1	620.1	778.2	943.2
117.5°	247.5	253.5	264.1	283.3	311.3	351.0	408.3	493.3	610.7	748.1	888.4
120°	265.0	271.0	280.1	300.1	328.0	367.0	421.1	498.1	605.1	732.1	861.2
122.5°	281.0	287.1	296.9	316.8	345.7	382.3	432.3	503.7	601.9	718.5	839.6
125°	303.1	309.1	321.1	341.0	369.1	405.1	450.1	512.1	596.2	699.1	808.1
127.5°	321.7	330.1	343.3	362.5	391.2	426.3	466.7	520.7	592.7	681.1	777.1
130°	332.1	342.1	356.1	376.1	404.1	439.1	477.1	527.1	591.1	669.2	757.2
132.5°	342.5	353.3	368.1	388.9	416.9	450.3	487.5	533.5	590.3	659.5	738.0
135°	356.1	368.1	383.1	406.0	434.1	466.1	501.1	541.1	589.1	646.1	711.1
137.5°	370.5	382.5	398.5	421.3	447.3	478.9	511.5	547.9	588.9	636.7	689.7
140°	380.0	392.1	408.1	430.1	456.1	486.1	517.1	551.1	588.1	631.1	676.1
142.5°	389.7	400.9	416.9	438.1	462.5	491.7	521.9	553.5	588.1	625.5	665.0
145°	406.0	416.1	431.1	451.1	473.1	500.1	528.1	556.1	586.1	618.1	649.1
147.5°	421.9	431.4	445.3	461.9	481.5	506.9	531.5	556.9	582.6	610.5	637.0
150°	433.1	441.1	454.1	469.1	487.1	510.1	533.1	556.1	580.1	604.1	628.1
152.5°	442.7	450.6	462.1	476.3	492.7	513.3	533.9	554.5	576.1	598.5	619.3
155°	458.1	464.1	475.1	486.1	501.1	518.1	535.1	552.1	569.1	588.1	607.1
157.5°	471.3	476.1	485.7	494.5	507.1	521.5	535.1	547.5	561.9	578.3	592.9
160°	480.1	484.1	492.1	500.1	511.1	523.1	535.1	545.1	557.2	571.1	584.1
162.5°	487.3	491.3	497.7	504.9	513.5	523.9	534.3	542.7	553.1	564.7	575.3
165°	497.1	499.1	505.1	510.1	516.1	525.1	532.1	538.1	545.1	554.1	562.1
167.5°	505.3	507.1	510.9	514.5	518.3	524.9	530.7	533.5	538.1	543.7	549.5
170°	510.1	511.1	514.1	516.1	519.1	524.1	529.1	531.1	534.1	538.1	543.1
172.5°	514.1	513.5	516.5	517.7	519.9	523.3	526.7	527.9	529.3	532.5	535.9
175°	518.1	517.1	519.1	519.1	520.1	522.1	524.1	523.1	524.1	525.1	528.1
177.5°	519.3	518.5	520.1	520.1	520.1	520.9	522.5	520.9	520.1	520.9	522.5
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1186.2	1191.1	1191.1	1191.8	1197.5	1196.7	1196.4
5°	1262.3	1269.8	1270.7	1278.6	1283.8	1282.1	1277.3
7.5°	1334.1	1348.1	1358.6	1364.4	1371.4	1375.7	1373.8
10°	1391.1	1411.4	1423.7	1432.0	1442.1	1449.6	1446.9
12.5°	1442.8	1466.9	1483.8	1498.1	1499.4	1509.0	1502.4
15°	1523.4	1548.9	1551.5	1562.1	1570.5	1569.5	1569.9
17.5°	1550.1	1558.2	1559.9	1560.1	1560.2	1557.1	1550.5
20°	1540.5	1537.5	1530.0	1524.3	1514.2	1512.9	1504.1
22.5°	1495.6	1485.7	1467.1	1454.7	1438.9	1434.8	1432.4
25°	1407.0	1385.3	1355.5	1326.9	1319.1	1303.6	1308.0
27.5°	1285.4	1251.8	1219.4	1196.2	1175.2	1152.2	1158.7
30°	1199.9	1162.1	1116.4	1081.2	1058.9	1036.8	1032.9
32.5°	1097.9	1042.6	991.5	960.6	926.3	912.4	897.2
35°	922.1	868.1	817.5	774.0	749.0	729.6	712.0
37.5°	764.0	701.7	661.0	625.7	607.6	596.5	599.3
40°	665.9	611.4	581.5	554.7	538.0	530.0	531.8
42.5°	586.4	545.6	521.0	502.7	490.9	486.5	485.4
45°	496.2	473.4	453.1	442.6	436.9	432.0	429.0
47.5°	434.7	416.0	404.7	398.4	393.4	388.5	388.4
50°	397.8	385.5	377.5	370.9	367.0	363.5	366.5
52.5°	369.6	358.3	350.5	344.6	343.1	339.9	339.8
55°	327.9	319.1	313.4	308.1	305.5	303.7	301.5
57.5°	289.9	281.5	276.3	272.9	267.9	266.1	265.4
60°	262.9	256.2	251.0	246.6	244.4	240.8	240.8
62.5°	237.9	231.3	226.4	223.0	219.4	218.0	218.3
65°	201.7	196.5	191.7	188.1	187.3	184.6	185.5
67.5°	168.5	165.0	159.9	158.0	156.3	154.9	153.9
70°	146.4	142.8	140.2	137.6	136.2	136.2	136.2
72.5°	127.7	123.5	121.9	118.6	119.3	118.0	116.6
75°	98.9	96.3	95.0	93.6	91.4	91.4	91.4
77.5°	72.8	72.0	70.4	69.0	68.4	68.0	68.2
80°	56.2	55.8	54.9	54.9	54.1	53.6	52.8
82.5°	43.2	42.1	41.6	41.2	41.1	41.0	40.8
85°	24.6	23.8	23.8	24.2	23.3	23.3	23.8
87.5°	15.5	15.9	15.8	15.8	16.1	15.8	15.8
90°	30.0	32.0	33.0	33.0	33.0	33.0	33.0
92.5°	74.8	66.4	60.2	59.4	56.2	57.0	55.4
95°	201.0	159.0	137.0	124.0	116.1	113.0	114.0
97.5°	500.3	392.1	319.9	272.1	247.5	232.8	224.5
100°	789.2	652.1	531.1	448.1	405.1	376.1	358.1
102.5°	1082.8	982.6	854.4	764.1	690.8	654.5	630.2
105°	1328.3	1341.3	1308.3	1246.2	1184.2	1141.3	1127.2
107.5°	1310.3	1414.3	1462.7	1470.5	1467.1	1458.4	1439.9
110°	1254.2	1382.2	1464.3	1507.3	1526.3	1535.3	1534.3



TEST NUMBER: P331368-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1187.8	1324.6	1418.7	1478.5	1510.3	1527.3	1532.7
115°	1097.3	1228.2	1331.3	1402.3	1448.3	1474.3	1483.3
117.5°	1023.6	1142.5	1239.1	1311.5	1360.0	1387.5	1395.1
120°	985.2	1091.2	1182.2	1252.2	1299.2	1328.3	1338.3
122.5°	953.2	1053.6	1135.8	1198.6	1244.8	1270.7	1279.0
125°	911.2	999.2	1074.2	1132.2	1170.3	1195.2	1203.2
127.5°	870.4	953.4	1022.6	1073.2	1108.8	1130.4	1136.9
130°	843.2	922.2	988.2	1037.2	1071.3	1091.2	1099.2
132.5°	817.6	890.2	952.2	1000.4	1034.4	1052.8	1060.0
135°	777.1	843.2	899.1	942.2	975.2	993.2	997.2
137.5°	744.9	797.4	846.2	885.4	913.8	929.6	935.6
140°	724.2	770.2	814.2	846.2	872.2	887.2	893.2
142.5°	705.8	745.4	782.1	812.5	836.2	849.5	850.8
145°	682.2	713.2	742.2	766.1	783.2	793.2	796.2
147.5°	663.0	687.2	708.3	728.1	741.8	748.6	750.4
150°	650.1	671.1	689.1	704.1	716.2	722.1	723.2
152.5°	639.7	657.5	673.1	684.9	695.3	699.7	699.9
155°	623.1	638.1	649.1	660.1	667.1	671.1	669.2
157.5°	606.3	618.9	627.5	635.3	641.1	642.9	642.9
160°	595.1	606.1	613.1	620.1	625.1	626.1	626.1
162.5°	584.7	594.1	599.5	606.5	609.9	610.9	610.1
165°	569.1	576.1	580.1	584.1	588.1	588.1	587.1
167.5°	554.9	559.7	563.4	565.1	567.3	567.1	565.9
170°	546.1	550.1	552.1	553.1	556.1	555.1	553.1
172.5°	538.1	541.3	542.5	543.5	544.9	543.9	542.7
175°	529.1	530.1	531.1	531.1	532.1	531.1	529.1
177.5°	522.5	523.3	523.3	523.3	523.3	522.5	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1

(END OF REPORT)