

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331372-935

Luminaire Tested: **SA2XXDIP-C675D1080U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331372-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6035.6 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331372-935
CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331372-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	31	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14759	14759	14759
5°	14815	14603	14687
10°	14728	14454	14526
15°	14544	14265	14252
20°	14287	13984	13969
25°	14031	13639	13639
30°	13699	13323	13207
35°	13391	12942	12751
40°	13004	12560	12319
45°	12622	12184	11880
50°	12208	11788	11369
55°	11778	11333	10911
60°	11296	10785	10388
65°	10777	10243	9773
70°	10126	9583	9130
75°	9214	8827	8609
80°	8173	7922	7513
85°	6688	6354	5687



TEST NUMBER: P331372-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	1.4
10°-20°	241.9	4.0
20°-30°	355.5	5.9
30°-40°	412.9	6.8
40°-50°	412.5	6.8
50°-60°	359.7	6.0
60°-70°	266.0	4.4
70°-80°	150.6	2.5
80°-90°	43.6	0.7
90°-100°	42.2	0.7
100°-110°	154.7	2.6
110°-120°	413.6	6.9
120°-130°	682.8	11.3
130°-140°	726.1	12.0
140°-150°	674.9	11.2
150°-160°	542.6	9.0
160°-170°	349.7	5.8
170°-180°	120.4	2.0
0°-30°	683.3	11.3
0°-40°	1096.3	18.2
0°-60°	1868.5	31.0
0°-90°	2328.7	38.6
90°-120°	610.5	10.1
90°-150°	2694.3	44.6
90°-180°	3707.0	61.4
0°-180°	6035.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	914	910	901	907	906	87
15°	870	865	853	857	853	245
25°	788	780	766	767	766	362
35°	679	670	657	651	647	424
45°	553	546	534	524	520	426
55°	418	413	403	392	388	374
65°	282	277	268	260	256	279
75°	148	146	142	137	138	158
85°	36	35	34	32	31	41
90°	1	11	18	23	25	5
95°	60	31	36	40	39	73
105°	278	290	56	66	70	297
115°	526	542	565	161	75	518
125°	744	756	773	780	783	663
135°	921	935	944	952	951	711
145°	1068	1068	1083	1089	1085	668
155°	1176	1169	1179	1184	1177	542
165°	1239	1234	1237	1242	1237	350
175°	1268	1262	1263	1269	1260	121
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P331372-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	918.3	917.6	916.8	916.0	915.2	914.0	912.2	910.5	908.8	907.1	908.6
5°	914.1	913.3	912.6	911.8	911.0	909.6	907.4	905.3	903.1	901.0	902.5
7.5°	906.0	904.8	903.6	902.4	901.2	899.5	897.3	895.1	892.9	890.7	892.3
10°	898.3	896.9	895.5	894.1	892.9	891.0	888.6	886.3	883.9	881.6	883.1
12.5°	887.8	886.6	885.3	884.1	882.9	881.1	878.7	876.4	874.1	871.8	872.9
15°	870.1	869.0	867.8	866.7	865.5	863.6	861.1	858.5	856.0	853.4	854.3
17.5°	847.7	846.4	845.3	844.1	843.0	841.1	838.5	835.9	833.4	830.8	831.7
20°	831.5	830.3	829.1	827.9	826.8	824.8	822.1	819.4	816.7	813.9	814.5
22.5°	815.3	813.6	812.0	810.4	808.7	806.7	804.1	801.5	798.9	796.3	796.4
25°	787.6	786.0	784.5	782.8	781.3	778.9	775.5	772.2	768.9	765.6	765.9
27.5°	755.9	754.5	753.1	751.7	750.3	748.3	745.6	743.0	740.4	737.8	737.2
30°	734.8	733.2	731.7	730.1	728.6	726.3	723.4	720.5	717.6	714.6	714.0
32.5°	712.3	711.0	709.8	708.5	707.3	705.2	702.1	699.0	695.9	692.8	691.7
35°	679.4	677.5	675.5	673.6	671.6	669.1	666.0	662.8	659.7	656.6	655.4
37.5°	642.3	640.6	638.9	637.1	635.5	633.0	629.9	626.8	623.7	620.5	619.1
40°	617.0	615.4	613.9	612.3	610.8	608.5	605.3	602.2	599.1	595.9	594.2
42.5°	592.5	590.8	589.3	587.7	586.2	583.8	580.7	577.6	574.5	571.4	569.4
45°	552.8	551.5	550.1	548.8	547.4	545.3	542.3	539.4	536.5	533.6	531.4
47.5°	513.5	512.2	510.9	509.6	508.3	506.2	503.1	500.1	497.1	494.0	491.7
50°	486.0	485.1	484.1	483.1	482.2	480.3	477.6	474.8	472.1	469.3	466.7
52.5°	459.3	458.1	456.8	455.5	454.2	452.3	449.7	447.1	444.5	442.0	439.7
55°	418.4	417.2	416.0	414.8	413.7	411.9	409.6	407.3	404.9	402.6	400.2
57.5°	377.2	376.3	375.4	374.4	373.5	371.8	369.2	366.6	364.0	361.4	359.1
60°	349.8	349.0	348.3	347.5	346.7	344.9	342.2	339.5	336.7	334.0	331.8
62.5°	323.1	321.8	320.6	319.3	318.1	316.4	314.4	312.2	310.1	308.0	306.0
65°	282.1	280.9	279.8	278.6	277.4	275.9	274.0	272.0	270.0	268.1	266.3
67.5°	240.5	239.5	238.6	237.6	236.7	235.4	233.6	231.9	230.1	228.3	227.0
70°	214.5	213.7	212.9	212.2	211.4	210.1	208.3	206.6	204.8	203.0	201.6
72.5°	187.8	186.9	186.1	185.4	184.6	183.7	182.5	181.4	180.3	179.1	177.8
75°	147.7	147.2	146.9	146.5	146.1	145.4	144.5	143.4	142.5	141.5	140.3
77.5°	111.8	111.2	110.5	109.8	109.2	108.7	108.2	107.8	107.5	107.0	106.5
80°	87.9	87.7	87.5	87.3	87.1	86.8	86.4	86.0	85.7	85.2	84.6
82.5°	65.4	65.3	65.3	65.3	65.3	65.1	64.8	64.7	64.4	64.1	63.5
85°	36.1	35.8	35.6	35.5	35.2	35.0	34.9	34.7	34.4	34.3	33.7
87.5°	12.8	13.0	13.1	13.3	13.3	13.4	13.4	13.5	13.5	13.5	13.3
90°	0.9	3.2	5.4	7.7	9.9	11.8	13.4	15.1	16.7	18.3	19.3
92.5°	18.5	18.3	18.1	17.9	17.7	18.0	18.8	19.6	20.4	21.3	21.8
95°	59.5	52.8	46.1	39.3	32.6	30.0	31.4	32.9	34.3	35.7	36.7
97.5°	118.0	99.2	80.2	61.3	42.4	34.6	37.9	41.2	44.5	47.8	48.6
100°	162.0	134.1	106.2	78.4	50.5	38.3	41.8	45.3	48.7	52.2	53.8
102.5°	210.3	204.4	198.5	192.6	186.8	169.4	140.4	111.5	82.6	53.6	55.8
105°	278.3	284.4	290.4	296.5	302.6	277.9	222.4	166.9	111.3	55.8	58.0
107.5°	355.7	360.6	365.5	370.4	375.4	344.6	277.9	211.4	144.7	78.2	75.9
110°	405.4	409.7	414.1	418.3	422.6	395.3	336.5	277.8	219.0	160.1	139.8



TEST NUMBER: P331372-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	452.4	456.2	459.9	463.6	467.4	462.1	447.5	433.1	418.5	404.0	329.8
115°	526.3	529.8	533.2	536.7	540.1	544.4	549.5	554.6	559.6	564.7	470.5
117.5°	592.4	596.2	600.1	604.0	607.9	611.5	615.0	618.5	622.0	625.5	602.7
120°	640.7	643.8	646.8	649.9	652.9	656.3	660.0	663.6	667.3	670.9	673.3
122.5°	681.7	684.9	688.1	691.4	694.6	698.2	702.1	706.1	710.2	714.1	715.6
125°	744.2	746.7	749.4	752.1	754.7	757.9	761.8	765.7	769.6	773.4	774.8
127.5°	800.7	803.7	806.6	809.5	812.4	815.3	818.2	821.0	824.0	826.9	829.0
130°	836.5	839.8	843.1	846.4	849.5	852.3	854.5	856.8	859.0	861.3	863.5
132.5°	873.1	876.0	878.7	881.5	884.2	886.7	889.0	891.2	893.5	895.7	897.6
135°	920.8	924.0	927.3	930.6	933.8	936.3	938.1	940.0	941.8	943.7	945.7
137.5°	968.9	971.2	973.4	975.8	978.0	980.2	982.3	984.4	986.4	988.5	990.5
140°	1000.4	1002.0	1003.7	1005.3	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6
142.5°	1026.7	1028.2	1029.7	1031.1	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5
145°	1068.2	1067.9	1067.7	1067.6	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2
147.5°	1104.2	1103.5	1102.7	1101.9	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1
150°	1127.7	1126.2	1124.8	1123.3	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1
152.5°	1147.4	1145.8	1144.2	1142.6	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4
155°	1176.1	1174.3	1172.5	1170.6	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1
157.5°	1198.7	1197.1	1195.6	1194.0	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8
160°	1211.9	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1
162.5°	1223.6	1222.4	1221.1	1219.9	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2
165°	1239.3	1238.0	1236.8	1235.6	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9
167.5°	1251.0	1249.8	1248.5	1247.3	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5
170°	1257.6	1256.4	1255.2	1254.0	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3
172.5°	1262.0	1260.8	1259.6	1258.4	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7
175°	1267.7	1266.3	1264.8	1263.4	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6
177.5°	1268.6	1267.5	1266.3	1265.2	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331372-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	910.2	911.8	913.3	914.0	913.6	913.3	913.0	912.7
5°	904.0	905.6	907.1	907.8	907.4	907.0	906.6	906.2
7.5°	893.9	895.4	897.0	897.5	897.1	896.7	896.3	895.9
10°	884.7	886.3	887.9	888.3	887.8	887.2	886.6	886.0
12.5°	873.9	875.0	876.2	876.4	876.0	875.6	875.2	874.8
15°	855.1	855.8	856.6	856.5	855.5	854.5	853.6	852.6
17.5°	832.6	833.4	834.4	834.4	833.4	832.5	831.6	830.6
20°	815.1	815.7	816.2	816.1	815.4	814.6	813.8	813.0
22.5°	796.6	796.7	796.8	796.6	796.2	795.7	795.2	794.8
25°	766.4	766.7	767.2	767.2	766.7	766.4	765.9	765.6
27.5°	736.6	736.1	735.5	734.7	733.7	732.8	731.8	730.9
30°	713.4	712.8	712.2	711.5	710.8	710.0	709.2	708.4
32.5°	690.7	689.7	688.5	687.7	686.9	686.1	685.3	684.5
35°	654.3	653.1	651.9	650.8	649.9	648.8	647.9	646.9
37.5°	617.7	616.2	614.8	613.5	612.6	611.7	610.8	609.8
40°	592.5	590.6	588.9	587.6	586.9	586.1	585.3	584.5
42.5°	567.5	565.6	563.7	562.1	561.0	560.0	558.9	557.8
45°	529.3	527.1	525.0	523.5	522.7	521.9	521.2	520.3
47.5°	489.5	487.2	484.9	483.2	482.1	481.0	479.8	478.7
50°	463.9	461.2	458.4	456.6	455.6	454.6	453.7	452.6
52.5°	437.4	435.1	432.9	431.1	429.8	428.5	427.2	425.9
55°	397.9	395.5	393.2	391.5	390.5	389.6	388.6	387.6
57.5°	356.8	354.5	352.2	350.7	349.9	349.2	348.4	347.7
60°	329.7	327.5	325.4	324.1	323.5	322.9	322.3	321.7
62.5°	304.0	302.0	300.1	298.7	297.9	297.1	296.4	295.7
65°	264.6	262.8	261.1	259.7	258.7	257.7	256.8	255.8
67.5°	225.6	224.3	222.9	221.8	221.0	220.2	219.5	218.7
70°	200.3	199.0	197.6	196.5	195.7	194.9	194.2	193.4
72.5°	176.4	175.0	173.7	172.6	172.0	171.4	170.8	170.1
75°	139.1	138.0	136.8	136.5	136.8	137.2	137.6	138.0
77.5°	105.9	105.3	104.7	104.2	103.6	103.1	102.5	101.9
80°	84.1	83.5	82.9	82.4	82.1	81.6	81.3	80.8
82.5°	62.7	61.9	61.2	60.8	60.7	60.6	60.5	60.4
85°	33.1	32.5	31.9	31.5	31.3	31.2	31.0	30.7
87.5°	13.0	12.7	12.5	12.3	12.2	12.1	12.1	12.0
90°	20.3	21.4	22.4	23.1	23.5	23.9	24.3	24.7
92.5°	22.3	22.8	23.3	23.8	24.0	24.2	24.5	24.7
95°	37.7	38.7	39.8	40.2	40.0	39.8	39.5	39.3
97.5°	49.4	50.2	51.1	51.6	51.8	52.1	52.3	52.5
100°	55.4	57.1	58.7	59.7	60.1	60.5	61.0	61.3
102.5°	57.9	60.0	62.1	63.5	64.0	64.6	65.2	65.7
105°	60.3	62.5	64.7	66.3	67.2	67.9	68.7	69.6
107.5°	73.6	71.3	69.1	68.4	69.1	69.9	70.8	71.5
110°	119.5	99.2	78.8	69.1	69.8	70.7	71.5	72.3



TEST NUMBER: P331372-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.6	181.4	107.2	70.4	71.1	71.7	72.4	73.0
115°	376.3	282.2	188.0	133.6	119.0	104.4	89.7	75.1
117.5°	580.0	557.2	534.4	498.9	450.8	402.7	354.6	306.4
120°	675.8	678.2	680.7	668.1	640.7	613.2	585.7	558.4
122.5°	717.0	718.5	720.0	718.0	712.7	707.4	702.1	696.7
125°	776.3	777.7	779.1	780.2	780.8	781.4	782.0	782.6
127.5°	831.0	833.1	835.2	836.3	836.4	836.5	836.6	836.7
130°	865.7	868.0	870.2	871.2	871.1	870.8	870.6	870.5
132.5°	899.5	901.5	903.4	904.2	904.0	903.8	903.6	903.4
135°	947.7	949.8	951.7	952.6	952.2	951.7	951.4	951.0
137.5°	992.5	994.5	996.4	997.1	996.4	995.7	995.1	994.4
140°	1021.5	1023.3	1025.1	1025.5	1024.5	1023.5	1022.4	1021.5
142.5°	1048.2	1049.9	1051.5	1051.9	1050.9	1049.8	1048.9	1047.8
145°	1085.6	1087.0	1088.5	1088.6	1087.7	1086.7	1085.6	1084.6
147.5°	1118.2	1119.3	1120.3	1120.4	1119.6	1118.7	1117.8	1117.0
150°	1138.3	1139.5	1140.7	1140.8	1139.8	1138.8	1137.8	1136.8
152.5°	1156.6	1157.9	1159.1	1159.0	1157.6	1156.3	1154.9	1153.7
155°	1181.3	1182.6	1183.8	1183.5	1181.9	1180.3	1178.7	1177.1
157.5°	1202.1	1203.5	1204.9	1204.8	1203.2	1201.6	1200.1	1198.4
160°	1214.3	1215.5	1216.7	1216.6	1215.2	1213.8	1212.4	1210.9
162.5°	1225.5	1226.9	1228.4	1228.1	1226.4	1224.7	1222.9	1221.2
165°	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6
167.5°	1250.9	1252.3	1253.8	1253.5	1251.7	1249.9	1248.1	1246.2
170°	1256.8	1258.2	1259.6	1259.4	1257.6	1255.8	1254.0	1252.1
172.5°	1261.2	1262.6	1264.0	1263.9	1262.0	1260.2	1258.4	1256.5
175°	1265.9	1267.4	1268.8	1268.5	1266.4	1264.4	1262.4	1260.3
177.5°	1266.4	1267.6	1268.8	1268.6	1267.1	1265.7	1264.2	1262.7
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9

(END OF REPORT)