

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331357-935

Luminaire Tested: **SA2XXDIP-C675D925U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331357-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5710.5 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331357-935
CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	81	76	71	81	75	70	66	63	59	56	51	49	46	41	39	37	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32	28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	49	44	62	53	46	41	45	39	35	37	33	30	30	27	25	22
6	63	51	44	38	58	48	41	36	40	35	31	33	30	27	27	24	22	19
7	58	47	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	33	28	25	28	24	21	23	20	18	15
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	36	28	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18466	18466	18466	18466
5°	20702	18585	16470	18585
10°	23722	18433	14254	18433
15°	26242	18094	12593	18094
20°	25844	17732	11478	17732
25°	23302	17250	10774	17250
30°	19257	16479	10260	16479
35°	14034	15672	9895	15672
40°	11209	14720	9691	14720
45°	9796	13618	9412	13618
50°	9206	12552	9231	12552
55°	8487	11468	8982	11468
60°	7776	10317	8603	10317
65°	7087	9287	8225	9287
70°	6430	8280	7676	8280
75°	5702	7155	6800	7155
80°	4909	5923	5477	5923
85°	4409	4409	3260	4409



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	1.9
10°-20°	316.6	5.5
20°-30°	459.5	8.0
30°-40°	484.9	8.5
40°-50°	429.4	7.5
50°-60°	342.6	6.0
60°-70°	232.9	4.1
70°-80°	119.4	2.1
80°-90°	31.5	0.6
90°-100°	36.2	0.6
100°-110°	132.9	2.3
110°-120°	355.3	6.2
120°-130°	586.6	10.3
130°-140°	623.8	10.9
140°-150°	579.8	10.2
150°-160°	466.2	8.2
160°-170°	300.4	5.3
170°-180°	103.4	1.8
0°-30°	885.1	15.5
0°-40°	1370.0	24.0
0°-60°	2142.0	37.5
0°-90°	2525.8	44.2
90°-120°	524.5	9.2
90°-150°	2314.7	40.5
90°-180°	3185.0	55.8
0°-180°	5710.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1144	1144	1144	1144	1144	
5°	1277	1147	1016	1147	1277	128
15°	1570	1082	753	1082	1570	433
25°	1308	968	605	968	1308	591
35°	712	795	502	795	712	463
45°	429	596	412	596	429	337
55°	302	407	319	407	302	270
65°	186	243	215	243	186	184
75°	91	115	109	115	91	98
85°	24	24	18	24	24	27
90°	21	1	21	1	21	11
95°	34	51	34	51	34	32
105°	60	239	60	239	60	62
115°	64	452	64	452	64	162
125°	672	639	672	639	672	582
135°	817	791	817	791	817	630
145°	932	918	932	918	932	583
155°	1011	1010	1011	1010	1011	467
165°	1062	1065	1062	1065	1062	300
175°	1083	1089	1083	1089	1083	103
180°	1087	1087	1087	1087	1087	



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1196.4	1196.7	1197.5	1191.8	1191.1	1191.1	1186.2	1182.0	1177.1	1170.4	1171.0
5°	1277.3	1282.1	1283.8	1278.6	1270.7	1269.8	1262.3	1250.0	1238.5	1229.3	1222.8
7.5°	1373.8	1375.7	1371.4	1364.4	1358.6	1348.1	1334.1	1320.5	1301.4	1283.9	1270.9
10°	1446.9	1449.6	1442.1	1432.0	1423.7	1411.4	1391.1	1370.5	1345.4	1321.2	1301.8
12.5°	1502.4	1509.0	1499.4	1498.1	1483.8	1466.9	1442.8	1432.4	1397.1	1363.4	1342.6
15°	1569.9	1569.5	1570.5	1562.1	1551.5	1548.9	1523.4	1495.7	1446.0	1426.2	1392.0
17.5°	1550.5	1557.1	1560.2	1560.1	1559.9	1558.2	1550.1	1532.6	1507.7	1475.6	1436.0
20°	1504.1	1512.9	1514.2	1524.3	1530.0	1537.5	1540.5	1535.7	1520.4	1493.5	1459.2
22.5°	1432.4	1434.8	1438.9	1454.7	1467.1	1485.7	1495.6	1511.8	1505.9	1492.8	1464.1
25°	1308.0	1303.6	1319.1	1326.9	1355.5	1385.3	1407.0	1430.6	1451.7	1464.5	1456.1
27.5°	1158.7	1152.2	1175.2	1196.2	1219.4	1251.8	1285.4	1325.0	1358.0	1399.2	1413.3
30°	1032.9	1036.8	1058.9	1081.2	1116.4	1162.1	1199.9	1243.5	1290.5	1336.6	1368.6
32.5°	897.2	912.4	926.3	960.6	991.5	1042.6	1097.9	1152.4	1211.0	1263.4	1313.1
35°	712.0	729.6	749.0	774.0	817.5	868.1	922.1	995.5	1075.6	1147.2	1206.1
37.5°	599.3	596.5	607.6	625.7	661.0	701.7	764.0	836.5	930.7	1014.9	1097.9
40°	531.8	530.0	538.0	554.7	581.5	611.4	665.9	729.6	817.1	919.9	1018.8
42.5°	485.4	486.5	490.9	502.7	521.0	545.6	586.4	640.7	720.7	817.6	923.9
45°	429.0	432.0	436.9	442.6	453.1	473.4	496.2	534.9	598.2	679.1	783.7
47.5°	388.4	388.5	393.4	398.4	404.7	416.0	434.7	458.9	503.6	569.5	659.4
50°	366.5	363.5	367.0	370.9	377.5	385.5	397.8	420.6	450.5	503.7	578.9
52.5°	339.8	339.9	343.1	344.6	350.5	358.3	369.6	385.5	412.5	454.1	515.9
55°	301.5	303.7	305.5	308.1	313.4	319.1	327.9	338.5	359.6	390.7	436.4
57.5°	265.4	266.1	267.9	272.9	276.3	281.5	289.9	299.5	313.2	336.3	370.7
60°	240.8	240.8	244.4	246.6	251.0	256.2	262.9	272.1	284.4	303.2	331.0
62.5°	218.3	218.0	219.4	223.0	226.4	231.3	237.9	245.7	257.3	274.1	296.9
65°	185.5	184.6	187.3	188.1	191.7	196.5	201.7	210.1	219.3	231.6	251.8
67.5°	153.9	154.9	156.3	158.0	159.9	165.0	168.5	174.4	182.2	192.4	206.1
70°	136.2	136.2	136.2	137.6	140.2	142.8	146.4	151.2	158.7	167.5	179.8
72.5°	116.6	118.0	119.3	118.6	121.9	123.5	127.7	130.4	137.6	143.2	154.1
75°	91.4	91.4	91.4	93.6	95.0	96.3	98.9	101.5	105.0	112.1	117.8
77.5°	68.2	68.0	68.4	69.0	70.4	72.0	72.8	75.2	78.4	81.6	86.5
80°	52.8	53.6	54.1	54.9	54.9	55.8	56.2	59.3	61.6	63.7	66.8
82.5°	40.8	41.0	41.1	41.2	41.6	42.1	43.2	44.3	45.0	46.8	49.2
85°	23.8	23.3	23.3	24.2	23.8	23.8	24.6	25.5	25.5	25.9	27.2
87.5°	13.3	13.3	13.6	13.2	13.1	13.3	13.2	12.7	12.8	13.0	13.1
90°	21.3	20.9	20.5	20.1	19.8	19.2	18.3	17.5	16.6	15.8	14.3
92.5°	21.3	21.0	20.8	20.6	20.4	20.1	19.6	19.1	18.7	18.3	17.6
95°	33.8	34.0	34.2	34.4	34.5	34.2	33.3	32.4	31.5	30.7	29.4
97.5°	45.1	44.9	44.7	44.5	44.3	43.8	43.1	42.4	41.8	41.1	38.2
100°	52.7	52.3	52.0	51.7	51.3	50.5	49.0	47.6	46.2	44.9	41.8
102.5°	56.5	56.0	55.4	55.0	54.5	53.4	51.6	49.7	47.9	46.1	40.9
105°	59.8	59.1	58.4	57.7	57.0	55.6	53.7	51.8	49.9	48.0	45.7
107.5°	61.5	60.8	60.1	59.4	58.7	59.3	61.3	63.2	65.2	67.2	72.3
110°	62.2	61.4	60.7	60.0	59.3	67.7	85.2	102.6	120.1	137.6	188.1



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.8	62.2	61.6	61.0	60.5	92.1	155.8	219.6	283.4	347.1	359.6
115°	64.5	77.1	89.6	102.2	114.8	161.5	242.5	323.4	404.2	485.2	480.8
117.5°	263.3	304.6	345.9	387.3	428.6	459.1	478.7	498.3	517.8	537.4	534.4
120°	479.7	503.3	526.8	550.4	574.0	584.8	582.7	580.6	578.5	576.4	573.3
122.5°	598.6	603.1	607.7	612.3	616.9	618.5	617.3	616.0	614.8	613.5	610.1
125°	672.4	671.8	671.2	670.7	670.2	669.3	668.1	666.9	665.7	664.4	661.2
127.5°	718.8	718.8	718.7	718.6	718.4	717.6	715.7	713.9	712.1	710.4	707.9
130°	747.8	748.0	748.1	748.4	748.6	747.6	745.7	743.8	741.8	739.9	738.0
132.5°	776.1	776.3	776.4	776.6	776.8	776.1	774.5	772.8	771.2	769.5	767.6
135°	817.0	817.3	817.7	818.0	818.4	817.7	816.0	814.2	812.4	810.7	809.2
137.5°	854.3	854.9	855.5	856.1	856.7	856.1	854.4	852.6	850.9	849.3	847.5
140°	877.5	878.5	879.3	880.2	881.1	880.7	879.2	877.5	876.0	874.4	872.5
142.5°	900.2	901.1	902.0	902.8	903.7	903.4	902.0	900.5	899.1	897.7	895.5
145°	931.9	932.7	933.6	934.4	935.3	935.1	933.9	932.7	931.4	930.2	927.3
147.5°	959.7	960.4	961.1	961.8	962.6	962.5	961.6	960.7	959.8	958.9	956.0
150°	976.6	977.5	978.4	979.3	980.2	980.1	979.0	977.9	976.9	975.9	973.1
152.5°	991.1	992.3	993.4	994.5	995.7	995.7	994.7	993.7	992.6	991.6	988.9
155°	1011.2	1012.6	1014.0	1015.5	1016.8	1017.0	1016.0	1014.9	1013.8	1012.8	1010.7
157.5°	1029.7	1031.0	1032.3	1033.7	1035.1	1035.2	1034.0	1032.8	1031.7	1030.4	1029.0
160°	1040.3	1041.6	1042.8	1044.0	1045.3	1045.3	1044.3	1043.2	1042.2	1041.1	1040.1
162.5°	1049.1	1050.7	1052.1	1053.7	1055.2	1055.3	1054.1	1052.9	1051.7	1050.6	1049.6
165°	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2	1066.0	1064.8	1063.6	1062.4	1061.9
167.5°	1070.7	1072.3	1073.8	1075.4	1076.9	1077.2	1075.9	1074.7	1073.5	1072.3	1071.8
170°	1075.7	1077.3	1078.8	1080.5	1082.0	1082.2	1081.0	1079.8	1078.5	1077.3	1076.9
172.5°	1079.5	1081.1	1082.6	1084.2	1085.8	1086.0	1084.8	1083.5	1082.3	1081.1	1080.7
175°	1082.8	1084.5	1086.3	1088.0	1089.8	1090.0	1088.8	1087.6	1086.4	1085.1	1084.8
177.5°	1084.9	1086.1	1087.4	1088.6	1089.9	1090.0	1089.1	1088.0	1087.1	1086.1	1086.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1173.5	1170.7	1169.0	1162.6	1157.0	1151.4	1149.6	1150.3	1142.6	1135.2	1132.0
5°	1219.3	1210.5	1202.1	1190.2	1176.2	1160.8	1152.9	1146.7	1131.4	1114.7	1105.0
7.5°	1260.2	1247.7	1231.6	1209.2	1188.8	1164.6	1149.2	1135.6	1113.0	1089.5	1075.0
10°	1285.2	1268.0	1247.3	1220.1	1195.1	1165.6	1145.0	1124.3	1097.9	1069.8	1052.2
12.5°	1306.7	1283.5	1263.2	1228.2	1198.6	1161.7	1137.2	1108.1	1080.4	1047.0	1029.8
15°	1357.7	1315.1	1276.3	1236.8	1200.3	1148.9	1121.7	1082.5	1046.0	1004.8	985.0
17.5°	1397.1	1349.3	1288.3	1238.0	1195.5	1138.6	1098.5	1051.7	1008.6	961.3	934.4
20°	1419.7	1364.7	1299.2	1239.5	1188.4	1123.4	1080.0	1032.0	981.5	928.2	899.2
22.5°	1433.0	1375.3	1310.5	1234.2	1174.4	1111.1	1056.4	1003.8	952.6	895.3	864.8
25°	1437.3	1384.5	1316.0	1229.8	1156.8	1085.2	1019.3	968.3	906.3	852.6	808.3
27.5°	1416.3	1378.5	1312.6	1221.5	1136.5	1052.7	979.3	921.5	856.1	797.9	753.3
30°	1390.7	1368.6	1304.5	1213.1	1120.3	1030.3	949.3	883.9	818.8	759.9	714.2
32.5°	1350.9	1346.2	1289.8	1201.1	1103.1	1001.8	918.1	851.9	779.8	721.9	678.4
35°	1272.9	1294.0	1258.4	1174.4	1070.7	961.2	870.7	795.1	720.4	665.0	624.1
37.5°	1168.3	1220.6	1211.3	1135.3	1026.9	917.1	817.2	738.1	666.9	611.1	570.9
40°	1096.1	1163.0	1172.7	1105.4	996.0	883.0	777.1	698.4	629.0	578.0	537.5
42.5°	1018.8	1096.9	1123.4	1069.5	962.2	847.1	741.2	659.7	591.0	541.4	505.6
45°	889.2	992.5	1040.3	1009.6	905.9	788.1	679.1	596.4	534.0	487.4	459.8
47.5°	767.9	880.8	945.2	934.4	843.2	726.5	618.8	539.5	478.7	441.5	416.7
50°	682.2	798.1	876.0	879.5	798.1	682.6	574.5	499.7	443.9	409.2	389.0
52.5°	607.6	718.3	803.2	821.8	747.9	636.9	534.8	460.4	411.2	379.3	361.2
55°	510.3	603.9	697.9	732.3	672.9	567.4	472.9	407.4	361.3	339.3	323.5
57.5°	424.2	502.3	589.2	627.1	590.5	500.2	411.6	354.7	317.3	298.0	285.9
60°	378.8	440.4	517.7	563.0	531.4	451.0	373.6	319.5	288.8	271.6	260.2
62.5°	336.7	391.2	456.6	498.0	480.8	404.9	335.6	287.9	261.3	245.2	237.0
65°	277.8	320.9	371.4	409.7	398.2	340.6	284.0	243.1	222.0	209.2	202.6
67.5°	228.8	259.8	294.9	328.4	319.2	278.4	232.9	201.0	185.3	174.4	170.4
70°	197.8	221.5	252.7	279.6	272.1	238.7	202.6	175.4	161.8	152.5	148.5
72.5°	168.2	187.8	211.5	233.5	228.4	200.7	170.7	150.1	139.6	131.0	127.8
75°	127.0	142.0	156.4	171.0	169.6	148.1	130.5	114.7	106.3	99.8	98.4
77.5°	93.8	102.1	112.0	120.6	118.2	105.9	92.1	83.1	76.9	72.5	71.8
80°	71.6	76.5	83.5	89.6	86.6	81.3	70.3	63.7	59.3	54.9	53.2
82.5°	51.9	56.8	61.0	64.3	62.0	57.1	50.3	45.8	43.1	40.2	39.4
85°	27.2	29.9	31.7	32.5	31.7	28.6	25.5	23.8	21.5	20.2	19.8
87.5°	13.2	12.8	12.6	12.9	11.5	11.1	9.3	7.9	7.9	7.9	7.7
90°	12.9	11.5	10.2	8.4	6.5	4.6	2.7	0.8	2.7	4.6	6.5
92.5°	16.9	16.2	15.4	15.2	15.3	15.5	15.7	15.8	15.7	15.5	15.3
95°	28.2	27.0	25.7	28.1	33.8	39.6	45.4	51.1	45.4	39.6	33.8
97.5°	35.4	32.5	29.7	36.4	52.7	69.0	85.2	101.4	85.2	69.0	52.7
100°	38.9	35.9	33.0	43.4	67.3	91.3	115.2	139.2	115.2	91.3	67.3
102.5°	95.7	120.6	145.5	160.4	165.5	170.6	175.6	180.7	175.6	170.6	165.5
105°	143.4	191.1	238.8	260.0	254.8	249.5	244.3	239.0	244.3	249.5	254.8
107.5°	181.6	238.8	296.0	322.5	318.2	314.0	309.8	305.6	309.8	314.0	318.2
110°	238.6	289.1	339.6	363.0	359.4	355.7	352.1	348.4	352.1	355.7	359.4



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	372.0	384.5	397.0	401.6	398.4	395.1	391.8	388.6	391.8	395.1	398.4
115°	476.5	472.1	467.7	464.0	461.1	458.1	455.1	452.1	455.1	458.1	461.1
117.5°	531.4	528.4	525.4	522.2	518.9	515.6	512.2	508.9	512.2	515.6	518.9
120°	570.1	567.0	563.8	560.9	558.3	555.7	553.0	550.4	553.0	555.7	558.3
122.5°	606.7	603.2	599.8	596.7	593.9	591.2	588.4	585.7	588.4	591.2	593.9
125°	657.8	654.5	651.2	648.4	646.1	643.9	641.5	639.3	641.5	643.9	646.1
127.5°	705.4	702.9	700.4	697.9	695.4	692.9	690.4	687.9	690.4	692.9	695.4
130°	736.1	734.2	732.3	729.9	727.1	724.3	721.5	718.8	721.5	724.3	727.1
132.5°	765.7	763.8	761.8	759.7	757.3	754.9	752.5	750.2	752.5	754.9	757.3
135°	807.6	806.0	804.4	802.3	799.4	796.7	793.8	791.1	793.8	796.7	799.4
137.5°	845.7	843.9	842.1	840.2	838.3	836.4	834.4	832.4	834.4	836.4	838.3
140°	870.6	868.7	866.8	865.0	863.7	862.3	860.9	859.5	860.9	862.3	863.7
142.5°	893.3	891.0	888.9	887.2	885.9	884.7	883.4	882.1	883.4	884.7	885.9
145°	924.3	921.4	918.3	917.0	917.1	917.3	917.5	917.7	917.5	917.3	917.1
147.5°	953.0	950.0	947.1	946.0	946.7	947.4	948.0	948.6	948.0	947.4	946.7
150°	970.3	967.5	964.7	963.9	965.1	966.3	967.6	968.8	967.6	966.3	965.1
152.5°	986.3	983.6	980.9	980.3	981.7	983.0	984.4	985.8	984.4	983.0	981.7
155°	1008.7	1006.5	1004.4	1004.2	1005.7	1007.3	1008.9	1010.5	1008.9	1007.3	1005.7
157.5°	1027.5	1026.1	1024.6	1024.5	1025.8	1027.2	1028.5	1029.8	1028.5	1027.2	1025.8
160°	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1040.1	1039.1	1037.9
162.5°	1048.7	1047.8	1046.9	1047.0	1048.0	1049.1	1050.2	1051.2	1050.2	1049.1	1048.0
165°	1061.3	1060.8	1060.2	1060.5	1061.5	1062.6	1063.7	1064.7	1063.7	1062.6	1061.5
167.5°	1071.3	1070.8	1070.3	1070.6	1071.6	1072.7	1073.8	1074.8	1073.8	1072.7	1071.6
170°	1076.6	1076.2	1075.9	1076.2	1077.3	1078.3	1079.3	1080.5	1079.3	1078.3	1077.3
172.5°	1080.4	1080.0	1079.7	1080.0	1081.1	1082.1	1083.1	1084.2	1083.1	1082.1	1081.1
175°	1084.4	1084.1	1083.7	1084.2	1085.4	1086.7	1087.9	1089.1	1087.9	1086.7	1085.4
177.5°	1085.8	1085.7	1085.5	1086.0	1086.9	1088.0	1088.9	1089.9	1088.9	1088.0	1086.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1128.5	1126.4	1119.0	1115.2	1108.8	1102.9	1099.0	1100.8	1102.2	1101.5	1100.4
5°	1096.1	1087.8	1075.0	1064.1	1056.2	1041.6	1035.5	1032.4	1029.8	1026.7	1023.6
7.5°	1057.7	1044.5	1026.2	1010.6	995.7	977.8	967.5	961.3	955.0	948.0	941.9
10°	1030.3	1011.8	992.5	970.4	952.9	936.6	922.1	912.5	903.7	895.4	889.2
12.5°	1001.4	980.2	956.2	926.2	906.8	883.6	881.3	864.3	850.6	845.4	838.2
15°	955.5	925.7	895.4	859.7	844.3	823.2	810.0	796.9	785.0	776.6	774.5
17.5°	903.4	864.7	834.6	809.0	783.8	762.2	750.0	739.4	729.7	718.5	717.0
20°	863.7	830.3	797.3	774.9	749.0	726.9	712.0	701.5	693.1	686.6	680.8
22.5°	826.0	789.5	759.3	734.8	709.2	691.5	679.7	669.5	662.5	655.2	649.9
25°	765.7	737.1	704.1	676.4	655.3	643.9	634.2	625.4	621.0	616.2	610.1
27.5°	712.8	681.1	650.2	628.8	610.3	600.1	593.2	587.3	583.2	580.3	576.9
30°	675.5	643.4	619.3	598.2	582.8	572.7	568.3	564.8	560.0	558.2	556.5
32.5°	639.7	610.8	590.1	571.8	557.2	550.5	546.5	543.4	539.6	537.8	534.3
35°	588.9	564.8	544.6	534.4	522.6	516.9	513.8	509.4	505.9	504.1	503.7
37.5°	541.2	520.2	507.0	494.0	489.0	485.4	481.2	478.2	477.2	476.9	476.5
40°	510.3	493.2	481.3	470.7	468.6	463.2	459.8	457.1	457.1	457.5	457.1
42.5°	482.2	466.7	456.3	447.2	444.6	441.4	437.9	437.7	438.5	440.0	438.5
45°	439.5	428.5	421.0	416.6	411.8	408.7	408.3	409.7	410.1	410.5	411.8
47.5°	400.3	393.0	386.2	381.4	379.3	378.8	378.2	380.6	382.6	383.4	385.5
50°	377.1	368.8	363.1	360.0	358.2	357.3	358.2	360.8	362.6	364.8	366.1
52.5°	351.1	345.2	341.2	338.9	338.2	338.7	338.9	341.9	344.7	345.4	346.1
55°	315.1	310.7	309.9	305.9	307.6	307.2	309.4	311.2	313.8	316.4	316.9
57.5°	279.3	275.8	273.4	273.7	274.2	276.2	278.0	281.1	284.0	286.7	287.0
60°	255.4	253.6	252.3	252.3	253.1	255.8	258.0	261.1	262.9	264.6	265.9
62.5°	233.6	231.8	230.5	231.2	233.5	235.1	237.6	239.3	241.0	242.8	243.4
65°	199.1	198.2	199.6	200.4	200.9	203.0	206.1	207.4	209.2	210.1	213.2
67.5°	167.4	167.6	167.4	168.6	171.2	171.7	174.6	177.6	178.0	179.7	181.7
70°	145.9	146.8	147.7	148.5	150.8	151.6	153.9	155.2	156.9	158.3	159.5
72.5°	126.2	126.4	127.3	127.1	129.0	130.9	132.8	134.1	135.8	137.5	138.8
75°	97.1	97.1	98.0	98.4	100.7	102.9	102.4	103.3	105.0	106.8	107.7
77.5°	70.9	70.0	70.9	71.4	72.1	74.0	74.3	75.5	77.5	76.9	77.9
80°	54.1	52.8	54.1	54.5	54.5	56.7	56.7	57.6	58.9	57.6	58.9
82.5°	38.6	38.0	38.9	39.0	39.7	39.8	40.6	40.7	42.0	41.4	42.0
85°	19.4	18.9	19.4	18.9	19.4	19.8	19.8	19.4	19.4	20.2	18.9
87.5°	7.7	7.7	7.6	7.8	7.7	7.7	7.6	7.7	7.9	7.3	7.5
90°	8.4	10.2	11.5	12.9	14.3	15.8	16.6	17.5	18.3	19.2	19.8
92.5°	15.2	15.4	16.2	16.9	17.6	18.3	18.7	19.1	19.6	20.1	20.4
95°	28.1	25.7	27.0	28.2	29.4	30.7	31.5	32.4	33.3	34.2	34.5
97.5°	36.4	29.7	32.5	35.4	38.2	41.1	41.8	42.4	43.1	43.8	44.3
100°	43.4	33.0	35.9	38.9	41.8	44.9	46.2	47.6	49.0	50.5	51.3
102.5°	160.4	145.5	120.6	95.7	70.9	46.1	47.9	49.7	51.6	53.4	54.5
105°	260.0	238.8	191.1	143.4	95.7	48.0	49.9	51.8	53.7	55.6	57.0
107.5°	322.5	296.0	238.8	181.6	124.3	67.2	65.2	63.2	61.3	59.3	58.7
110°	363.0	339.6	289.1	238.6	188.1	137.6	120.1	102.6	85.2	67.7	59.3



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	401.6	397.0	384.5	372.0	359.6	347.1	283.4	219.6	155.8	92.1	60.5
115°	464.0	467.7	472.1	476.5	480.8	485.2	404.2	323.4	242.5	161.5	114.8
117.5°	522.2	525.4	528.4	531.4	534.4	537.4	517.8	498.3	478.7	459.1	428.6
120°	560.9	563.8	567.0	570.1	573.3	576.4	578.5	580.6	582.7	584.8	574.0
122.5°	596.7	599.8	603.2	606.7	610.1	613.5	614.8	616.0	617.3	618.5	616.9
125°	648.4	651.2	654.5	657.8	661.2	664.4	665.7	666.9	668.1	669.3	670.2
127.5°	697.9	700.4	702.9	705.4	707.9	710.4	712.1	713.9	715.7	717.6	718.4
130°	729.9	732.3	734.2	736.1	738.0	739.9	741.8	743.8	745.7	747.6	748.6
132.5°	759.7	761.8	763.8	765.7	767.6	769.5	771.2	772.8	774.5	776.1	776.8
135°	802.3	804.4	806.0	807.6	809.2	810.7	812.4	814.2	816.0	817.7	818.4
137.5°	840.2	842.1	843.9	845.7	847.5	849.3	850.9	852.6	854.4	856.1	856.7
140°	865.0	866.8	868.7	870.6	872.5	874.4	876.0	877.5	879.2	880.7	881.1
142.5°	887.2	888.9	891.0	893.3	895.5	897.7	899.1	900.5	902.0	903.4	903.7
145°	917.0	918.3	921.4	924.3	927.3	930.2	931.4	932.7	933.9	935.1	935.3
147.5°	946.0	947.1	950.0	953.0	956.0	958.9	959.8	960.7	961.6	962.5	962.6
150°	963.9	964.7	967.5	970.3	973.1	975.9	976.9	977.9	979.0	980.1	980.2
152.5°	980.3	980.9	983.6	986.3	988.9	991.6	992.6	993.7	994.7	995.7	995.7
155°	1004.2	1004.4	1006.5	1008.7	1010.7	1012.8	1013.8	1014.9	1016.0	1017.0	1016.8
157.5°	1024.5	1024.6	1026.1	1027.5	1029.0	1030.4	1031.7	1032.8	1034.0	1035.2	1035.1
160°	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1042.2	1043.2	1044.3	1045.3	1045.3
162.5°	1047.0	1046.9	1047.8	1048.7	1049.6	1050.6	1051.7	1052.9	1054.1	1055.3	1055.2
165°	1060.5	1060.2	1060.8	1061.3	1061.9	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2
167.5°	1070.6	1070.3	1070.8	1071.3	1071.8	1072.3	1073.5	1074.7	1075.9	1077.2	1076.9
170°	1076.2	1075.9	1076.2	1076.6	1076.9	1077.3	1078.5	1079.8	1081.0	1082.2	1082.0
172.5°	1080.0	1079.7	1080.0	1080.4	1080.7	1081.1	1082.3	1083.5	1084.8	1086.0	1085.8
175°	1084.2	1083.7	1084.1	1084.4	1084.8	1085.1	1086.4	1087.6	1088.8	1090.0	1089.8
177.5°	1086.0	1085.5	1085.7	1085.8	1086.0	1086.1	1087.1	1088.0	1089.1	1090.0	1089.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1096.9	1096.1	1096.1	1093.0	1096.1	1096.1	1096.9	1100.4	1101.5	1102.2	1100.8
5°	1017.5	1016.2	1014.0	1016.2	1014.0	1016.2	1017.5	1023.6	1026.7	1029.8	1032.4
7.5°	939.0	933.8	933.0	927.7	933.0	933.8	939.0	941.9	948.0	955.0	961.3
10°	881.7	878.1	877.7	869.4	877.7	878.1	881.7	889.2	895.4	903.7	912.5
12.5°	838.1	829.7	831.3	826.5	831.3	829.7	838.1	838.2	845.4	850.6	864.3
15°	762.6	762.6	760.8	753.4	760.8	762.6	762.6	774.5	776.6	785.0	796.9
17.5°	708.3	707.5	703.3	705.3	703.3	707.5	708.3	717.0	718.5	729.7	739.4
20°	676.0	673.4	668.0	668.0	668.0	673.4	676.0	680.8	686.6	693.1	701.5
22.5°	645.4	645.2	639.6	641.4	639.6	645.2	645.4	649.9	655.2	662.5	669.5
25°	609.6	606.1	603.5	604.8	603.5	606.1	609.6	610.1	616.2	621.0	625.4
27.5°	575.7	573.8	573.6	570.0	573.6	573.8	575.7	576.9	580.3	583.2	587.3
30°	556.0	551.6	552.5	550.3	552.5	551.6	556.0	556.5	558.2	560.0	564.8
32.5°	533.5	531.9	531.1	529.2	531.1	531.9	533.5	534.3	537.8	539.6	543.4
35°	502.8	503.3	501.1	502.0	501.1	503.3	502.8	503.7	504.1	505.9	509.4
37.5°	476.0	477.4	476.4	476.6	476.4	477.4	476.0	476.5	476.9	477.2	478.2
40°	458.4	458.4	458.4	459.8	458.4	458.4	458.4	457.1	457.5	457.1	457.1
42.5°	441.5	440.8	440.1	440.1	440.1	440.8	441.5	438.5	440.0	438.5	437.7
45°	412.7	414.1	414.5	412.2	414.5	414.1	412.7	411.8	410.5	410.1	409.7
47.5°	386.6	386.8	386.6	388.6	386.6	386.8	386.6	385.5	383.4	382.6	380.6
50°	368.3	367.5	368.3	367.5	368.3	367.5	368.3	366.1	364.8	362.6	360.8
52.5°	349.0	349.1	348.6	348.4	348.6	349.1	349.0	346.1	345.4	344.7	341.9
55°	318.7	319.5	319.1	319.1	319.1	319.5	318.7	316.9	316.4	313.8	311.2
57.5°	287.3	288.1	288.7	286.7	288.7	288.1	287.3	287.0	286.7	284.0	281.1
60°	265.4	267.7	267.3	266.4	267.3	267.7	265.4	265.9	264.6	262.9	261.1
62.5°	245.5	246.2	246.2	246.0	246.2	246.2	245.5	243.4	242.8	241.0	239.3
65°	214.5	215.3	214.0	215.3	214.0	215.3	214.5	213.2	210.1	209.2	207.4
67.5°	181.2	181.4	182.4	183.0	182.4	181.4	181.2	181.7	179.7	178.0	177.6
70°	160.4	160.0	161.3	162.6	161.3	160.0	160.4	159.5	158.3	156.9	155.2
72.5°	138.6	139.6	139.1	140.1	139.1	139.6	138.6	138.8	137.5	135.8	134.1
75°	106.8	108.1	107.7	109.0	107.7	108.1	106.8	107.7	106.8	105.0	103.3
77.5°	77.1	77.3	77.1	77.9	77.1	77.3	77.1	77.9	76.9	77.5	75.5
80°	58.9	58.0	57.2	58.9	57.2	58.0	58.9	58.9	57.6	58.9	57.6
82.5°	41.0	41.5	40.6	40.6	40.6	41.5	41.0	42.0	41.4	42.0	40.7
85°	18.9	18.4	17.6	17.6	17.6	18.4	18.9	18.9	20.2	19.4	19.4
87.5°	7.6	7.2	7.3	7.1	7.3	7.2	7.6	7.5	7.3	7.9	7.7
90°	20.1	20.5	20.9	21.3	20.9	20.5	20.1	19.8	19.2	18.3	17.5
92.5°	20.6	20.8	21.0	21.3	21.0	20.8	20.6	20.4	20.1	19.6	19.1
95°	34.4	34.2	34.0	33.8	34.0	34.2	34.4	34.5	34.2	33.3	32.4
97.5°	44.5	44.7	44.9	45.1	44.9	44.7	44.5	44.3	43.8	43.1	42.4
100°	51.7	52.0	52.3	52.7	52.3	52.0	51.7	51.3	50.5	49.0	47.6
102.5°	55.0	55.4	56.0	56.5	56.0	55.4	55.0	54.5	53.4	51.6	49.7
105°	57.7	58.4	59.1	59.8	59.1	58.4	57.7	57.0	55.6	53.7	51.8
107.5°	59.4	60.1	60.8	61.5	60.8	60.1	59.4	58.7	59.3	61.3	63.2
110°	60.0	60.7	61.4	62.2	61.4	60.7	60.0	59.3	67.7	85.2	102.6



TEST NUMBER: P331357-935
 CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	61.0	61.6	62.2	62.8	62.2	61.6	61.0	60.5	92.1	155.8	219.6
115°	102.2	89.6	77.1	64.5	77.1	89.6	102.2	114.8	161.5	242.5	323.4
117.5°	387.3	345.9	304.6	263.3	304.6	345.9	387.3	428.6	459.1	478.7	498.3
120°	550.4	526.8	503.3	479.7	503.3	526.8	550.4	574.0	584.8	582.7	580.6
122.5°	612.3	607.7	603.1	598.6	603.1	607.7	612.3	616.9	618.5	617.3	616.0
125°	670.7	671.2	671.8	672.4	671.8	671.2	670.7	670.2	669.3	668.1	666.9
127.5°	718.6	718.7	718.8	718.8	718.8	718.7	718.6	718.4	717.6	715.7	713.9
130°	748.4	748.1	748.0	747.8	748.0	748.1	748.4	748.6	747.6	745.7	743.8
132.5°	776.6	776.4	776.3	776.1	776.3	776.4	776.6	776.8	776.1	774.5	772.8
135°	818.0	817.7	817.3	817.0	817.3	817.7	818.0	818.4	817.7	816.0	814.2
137.5°	856.1	855.5	854.9	854.3	854.9	855.5	856.1	856.7	856.1	854.4	852.6
140°	880.2	879.3	878.5	877.5	878.5	879.3	880.2	881.1	880.7	879.2	877.5
142.5°	902.8	902.0	901.1	900.2	901.1	902.0	902.8	903.7	903.4	902.0	900.5
145°	934.4	933.6	932.7	931.9	932.7	933.6	934.4	935.3	935.1	933.9	932.7
147.5°	961.8	961.1	960.4	959.7	960.4	961.1	961.8	962.6	962.5	961.6	960.7
150°	979.3	978.4	977.5	976.6	977.5	978.4	979.3	980.2	980.1	979.0	977.9
152.5°	994.5	993.4	992.3	991.1	992.3	993.4	994.5	995.7	995.7	994.7	993.7
155°	1015.5	1014.0	1012.6	1011.2	1012.6	1014.0	1015.5	1016.8	1017.0	1016.0	1014.9
157.5°	1033.7	1032.3	1031.0	1029.7	1031.0	1032.3	1033.7	1035.1	1035.2	1034.0	1032.8
160°	1044.0	1042.8	1041.6	1040.3	1041.6	1042.8	1044.0	1045.3	1045.3	1044.3	1043.2
162.5°	1053.7	1052.1	1050.7	1049.1	1050.7	1052.1	1053.7	1055.2	1055.3	1054.1	1052.9
165°	1066.0	1064.8	1063.6	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2	1066.0	1064.8
167.5°	1075.4	1073.8	1072.3	1070.7	1072.3	1073.8	1075.4	1076.9	1077.2	1075.9	1074.7
170°	1080.5	1078.8	1077.3	1075.7	1077.3	1078.8	1080.5	1082.0	1082.2	1081.0	1079.8
172.5°	1084.2	1082.6	1081.1	1079.5	1081.1	1082.6	1084.2	1085.8	1086.0	1084.8	1083.5
175°	1088.0	1086.3	1084.5	1082.8	1084.5	1086.3	1088.0	1089.8	1090.0	1088.8	1087.6
177.5°	1088.6	1087.4	1086.1	1084.9	1086.1	1087.4	1088.6	1089.9	1090.0	1089.1	1088.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1099.0	1102.9	1108.8	1115.2	1119.0	1126.4	1128.5	1132.0	1135.2	1142.6	1150.3
5°	1035.5	1041.6	1056.2	1064.1	1075.0	1087.8	1096.1	1105.0	1114.7	1131.4	1146.7
7.5°	967.5	977.8	995.7	1010.6	1026.2	1044.5	1057.7	1075.0	1089.5	1113.0	1135.6
10°	922.1	936.6	952.9	970.4	992.5	1011.8	1030.3	1052.2	1069.8	1097.9	1124.3
12.5°	881.3	883.6	906.8	926.2	956.2	980.2	1001.4	1029.8	1047.0	1080.4	1108.1
15°	810.0	823.2	844.3	859.7	895.4	925.7	955.5	985.0	1004.8	1046.0	1082.5
17.5°	750.0	762.2	783.8	809.0	834.6	864.7	903.4	934.4	961.3	1008.6	1051.7
20°	712.0	726.9	749.0	774.9	797.3	830.3	863.7	899.2	928.2	981.5	1032.0
22.5°	679.7	691.5	709.2	734.8	759.3	789.5	826.0	864.8	895.3	952.6	1003.8
25°	634.2	643.9	655.3	676.4	704.1	737.1	765.7	808.3	852.6	906.3	968.3
27.5°	593.2	600.1	610.3	628.8	650.2	681.1	712.8	753.3	797.9	856.1	921.5
30°	568.3	572.7	582.8	598.2	619.3	643.4	675.5	714.2	759.9	818.8	883.9
32.5°	546.5	550.5	557.2	571.8	590.1	610.8	639.7	678.4	721.9	779.8	851.9
35°	513.8	516.9	522.6	534.4	544.6	564.8	588.9	624.1	665.0	720.4	795.1
37.5°	481.2	485.4	489.0	494.0	507.0	520.2	541.2	570.9	611.1	666.9	738.1
40°	459.8	463.2	468.6	470.7	481.3	493.2	510.3	537.5	578.0	629.0	698.4
42.5°	437.9	441.4	444.6	447.2	456.3	466.7	482.2	505.6	541.4	591.0	659.7
45°	408.3	408.7	411.8	416.6	421.0	428.5	439.5	459.8	487.4	534.0	596.4
47.5°	378.2	378.8	379.3	381.4	386.2	393.0	400.3	416.7	441.5	478.7	539.5
50°	358.2	357.3	358.2	360.0	363.1	368.8	377.1	389.0	409.2	443.9	499.7
52.5°	338.9	338.7	338.2	338.9	341.2	345.2	351.1	361.2	379.3	411.2	460.4
55°	309.4	307.2	307.6	305.9	309.9	310.7	315.1	323.5	339.3	361.3	407.4
57.5°	278.0	276.2	274.2	273.7	273.4	275.8	279.3	285.9	298.0	317.3	354.7
60°	258.0	255.8	253.1	252.3	252.3	253.6	255.4	260.2	271.6	288.8	319.5
62.5°	237.6	235.1	233.5	231.2	230.5	231.8	233.6	237.0	245.2	261.3	287.9
65°	206.1	203.0	200.9	200.4	199.6	198.2	199.1	202.6	209.2	222.0	243.1
67.5°	174.6	171.7	171.2	168.6	167.4	167.6	167.4	170.4	174.4	185.3	201.0
70°	153.9	151.6	150.8	148.5	147.7	146.8	145.9	148.5	152.5	161.8	175.4
72.5°	132.8	130.9	129.0	127.1	127.3	126.4	126.2	127.8	131.0	139.6	150.1
75°	102.4	102.9	100.7	98.4	98.0	97.1	97.1	98.4	99.8	106.3	114.7
77.5°	74.3	74.0	72.1	71.4	70.9	70.0	70.9	71.8	72.5	76.9	83.1
80°	56.7	56.7	54.5	54.5	54.1	52.8	54.1	53.2	54.9	59.3	63.7
82.5°	40.6	39.8	39.7	39.0	38.9	38.0	38.6	39.4	40.2	43.1	45.8
85°	19.8	19.8	19.4	18.9	19.4	18.9	19.4	19.8	20.2	21.5	23.8
87.5°	7.6	7.7	7.7	7.8	7.6	7.7	7.7	7.7	7.9	7.9	7.9
90°	16.6	15.8	14.3	12.9	11.5	10.2	8.4	6.5	4.6	2.7	0.8
92.5°	18.7	18.3	17.6	16.9	16.2	15.4	15.2	15.3	15.5	15.7	15.8
95°	31.5	30.7	29.4	28.2	27.0	25.7	28.1	33.8	39.6	45.4	51.1
97.5°	41.8	41.1	38.2	35.4	32.5	29.7	36.4	52.7	69.0	85.2	101.4
100°	46.2	44.9	41.8	38.9	35.9	33.0	43.4	67.3	91.3	115.2	139.2
102.5°	47.9	46.1	70.9	95.7	120.6	145.5	160.4	165.5	170.6	175.6	180.7
105°	49.9	48.0	95.7	143.4	191.1	238.8	260.0	254.8	249.5	244.3	239.0
107.5°	65.2	67.2	124.3	181.6	238.8	296.0	322.5	318.2	314.0	309.8	305.6
110°	120.1	137.6	188.1	238.6	289.1	339.6	363.0	359.4	355.7	352.1	348.4



TEST NUMBER: P331357-935
 CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.4	347.1	359.6	372.0	384.5	397.0	401.6	398.4	395.1	391.8	388.6
115°	404.2	485.2	480.8	476.5	472.1	467.7	464.0	461.1	458.1	455.1	452.1
117.5°	517.8	537.4	534.4	531.4	528.4	525.4	522.2	518.9	515.6	512.2	508.9
120°	578.5	576.4	573.3	570.1	567.0	563.8	560.9	558.3	555.7	553.0	550.4
122.5°	614.8	613.5	610.1	606.7	603.2	599.8	596.7	593.9	591.2	588.4	585.7
125°	665.7	664.4	661.2	657.8	654.5	651.2	648.4	646.1	643.9	641.5	639.3
127.5°	712.1	710.4	707.9	705.4	702.9	700.4	697.9	695.4	692.9	690.4	687.9
130°	741.8	739.9	738.0	736.1	734.2	732.3	729.9	727.1	724.3	721.5	718.8
132.5°	771.2	769.5	767.6	765.7	763.8	761.8	759.7	757.3	754.9	752.5	750.2
135°	812.4	810.7	809.2	807.6	806.0	804.4	802.3	799.4	796.7	793.8	791.1
137.5°	850.9	849.3	847.5	845.7	843.9	842.1	840.2	838.3	836.4	834.4	832.4
140°	876.0	874.4	872.5	870.6	868.7	866.8	865.0	863.7	862.3	860.9	859.5
142.5°	899.1	897.7	895.5	893.3	891.0	888.9	887.2	885.9	884.7	883.4	882.1
145°	931.4	930.2	927.3	924.3	921.4	918.3	917.0	917.1	917.3	917.5	917.7
147.5°	959.8	958.9	956.0	953.0	950.0	947.1	946.0	946.7	947.4	948.0	948.6
150°	976.9	975.9	973.1	970.3	967.5	964.7	963.9	965.1	966.3	967.6	968.8
152.5°	992.6	991.6	988.9	986.3	983.6	980.9	980.3	981.7	983.0	984.4	985.8
155°	1013.8	1012.8	1010.7	1008.7	1006.5	1004.4	1004.2	1005.7	1007.3	1008.9	1010.5
157.5°	1031.7	1030.4	1029.0	1027.5	1026.1	1024.6	1024.5	1025.8	1027.2	1028.5	1029.8
160°	1042.2	1041.1	1040.1	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1
162.5°	1051.7	1050.6	1049.6	1048.7	1047.8	1046.9	1047.0	1048.0	1049.1	1050.2	1051.2
165°	1063.6	1062.4	1061.9	1061.3	1060.8	1060.2	1060.5	1061.5	1062.6	1063.7	1064.7
167.5°	1073.5	1072.3	1071.8	1071.3	1070.8	1070.3	1070.6	1071.6	1072.7	1073.8	1074.8
170°	1078.5	1077.3	1076.9	1076.6	1076.2	1075.9	1076.2	1077.3	1078.3	1079.3	1080.5
172.5°	1082.3	1081.1	1080.7	1080.4	1080.0	1079.7	1080.0	1081.1	1082.1	1083.1	1084.2
175°	1086.4	1085.1	1084.8	1084.4	1084.1	1083.7	1084.2	1085.4	1086.7	1087.9	1089.1
177.5°	1087.1	1086.1	1086.0	1085.8	1085.7	1085.5	1086.0	1086.9	1088.0	1088.9	1089.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1149.6	1151.4	1157.0	1162.6	1169.0	1170.7	1173.5	1171.0	1170.4	1177.1	1182.0
5°	1152.9	1160.8	1176.2	1190.2	1202.1	1210.5	1219.3	1222.8	1229.3	1238.5	1250.0
7.5°	1149.2	1164.6	1188.8	1209.2	1231.6	1247.7	1260.2	1270.9	1283.9	1301.4	1320.5
10°	1145.0	1165.6	1195.1	1220.1	1247.3	1268.0	1285.2	1301.8	1321.2	1345.4	1370.5
12.5°	1137.2	1161.7	1198.6	1228.2	1263.2	1283.5	1306.7	1342.6	1363.4	1397.1	1432.4
15°	1121.7	1148.9	1200.3	1236.8	1276.3	1315.1	1357.7	1392.0	1426.2	1446.0	1495.7
17.5°	1098.5	1138.6	1195.5	1238.0	1288.3	1349.3	1397.1	1436.0	1475.6	1507.7	1532.6
20°	1080.0	1123.4	1188.4	1239.5	1299.2	1364.7	1419.7	1459.2	1493.5	1520.4	1535.7
22.5°	1056.4	1111.1	1174.4	1234.2	1310.5	1375.3	1433.0	1464.1	1492.8	1505.9	1511.8
25°	1019.3	1085.2	1156.8	1229.8	1316.0	1384.5	1437.3	1456.1	1464.5	1451.7	1430.6
27.5°	979.3	1052.7	1136.5	1221.5	1312.6	1378.5	1416.3	1413.3	1399.2	1358.0	1325.0
30°	949.3	1030.3	1120.3	1213.1	1304.5	1368.6	1390.7	1368.6	1336.6	1290.5	1243.5
32.5°	918.1	1001.8	1103.1	1201.1	1289.8	1346.2	1350.9	1313.1	1263.4	1211.0	1152.4
35°	870.7	961.2	1070.7	1174.4	1258.4	1294.0	1272.9	1206.1	1147.2	1075.6	995.5
37.5°	817.2	917.1	1026.9	1135.3	1211.3	1220.6	1168.3	1097.9	1014.9	930.7	836.5
40°	777.1	883.0	996.0	1105.4	1172.7	1163.0	1096.1	1018.8	919.9	817.1	729.6
42.5°	741.2	847.1	962.2	1069.5	1123.4	1096.9	1018.8	923.9	817.6	720.7	640.7
45°	679.1	788.1	905.9	1009.6	1040.3	992.5	889.2	783.7	679.1	598.2	534.9
47.5°	618.8	726.5	843.2	934.4	945.2	880.8	767.9	659.4	569.5	503.6	458.9
50°	574.5	682.6	798.1	879.5	876.0	798.1	682.2	578.9	503.7	450.5	420.6
52.5°	534.8	636.9	747.9	821.8	803.2	718.3	607.6	515.9	454.1	412.5	385.5
55°	472.9	567.4	672.9	732.3	697.9	603.9	510.3	436.4	390.7	359.6	338.5
57.5°	411.6	500.2	590.5	627.1	589.2	502.3	424.2	370.7	336.3	313.2	299.5
60°	373.6	451.0	531.4	563.0	517.7	440.4	378.8	331.0	303.2	284.4	272.1
62.5°	335.6	404.9	480.8	498.0	456.6	391.2	336.7	296.9	274.1	257.3	245.7
65°	284.0	340.6	398.2	409.7	371.4	320.9	277.8	251.8	231.6	219.3	210.1
67.5°	232.9	278.4	319.2	328.4	294.9	259.8	228.8	206.1	192.4	182.2	174.4
70°	202.6	238.7	272.1	279.6	252.7	221.5	197.8	179.8	167.5	158.7	151.2
72.5°	170.7	200.7	228.4	233.5	211.5	187.8	168.2	154.1	143.2	137.6	130.4
75°	130.5	148.1	169.6	171.0	156.4	142.0	127.0	117.8	112.1	105.0	101.5
77.5°	92.1	105.9	118.2	120.6	112.0	102.1	93.8	86.5	81.6	78.4	75.2
80°	70.3	81.3	86.6	89.6	83.5	76.5	71.6	66.8	63.7	61.6	59.3
82.5°	50.3	57.1	62.0	64.3	61.0	56.8	51.9	49.2	46.8	45.0	44.3
85°	25.5	28.6	31.7	32.5	31.7	29.9	27.2	27.2	25.9	25.5	25.5
87.5°	9.3	11.1	11.5	12.9	12.6	12.8	13.2	13.1	13.0	12.8	12.7
90°	2.7	4.6	6.5	8.4	10.2	11.5	12.9	14.3	15.8	16.6	17.5
92.5°	15.7	15.5	15.3	15.2	15.4	16.2	16.9	17.6	18.3	18.7	19.1
95°	45.4	39.6	33.8	28.1	25.7	27.0	28.2	29.4	30.7	31.5	32.4
97.5°	85.2	69.0	52.7	36.4	29.7	32.5	35.4	38.2	41.1	41.8	42.4
100°	115.2	91.3	67.3	43.4	33.0	35.9	38.9	41.8	44.9	46.2	47.6
102.5°	175.6	170.6	165.5	160.4	145.5	120.6	95.7	70.9	46.1	47.9	49.7
105°	244.3	249.5	254.8	260.0	238.8	191.1	143.4	95.7	48.0	49.9	51.8
107.5°	309.8	314.0	318.2	322.5	296.0	238.8	181.6	124.3	67.2	65.2	63.2
110°	352.1	355.7	359.4	363.0	339.6	289.1	238.6	188.1	137.6	120.1	102.6



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	391.8	395.1	398.4	401.6	397.0	384.5	372.0	359.6	347.1	283.4	219.6
115°	455.1	458.1	461.1	464.0	467.7	472.1	476.5	480.8	485.2	404.2	323.4
117.5°	512.2	515.6	518.9	522.2	525.4	528.4	531.4	534.4	537.4	517.8	498.3
120°	553.0	555.7	558.3	560.9	563.8	567.0	570.1	573.3	576.4	578.5	580.6
122.5°	588.4	591.2	593.9	596.7	599.8	603.2	606.7	610.1	613.5	614.8	616.0
125°	641.5	643.9	646.1	648.4	651.2	654.5	657.8	661.2	664.4	665.7	666.9
127.5°	690.4	692.9	695.4	697.9	700.4	702.9	705.4	707.9	710.4	712.1	713.9
130°	721.5	724.3	727.1	729.9	732.3	734.2	736.1	738.0	739.9	741.8	743.8
132.5°	752.5	754.9	757.3	759.7	761.8	763.8	765.7	767.6	769.5	771.2	772.8
135°	793.8	796.7	799.4	802.3	804.4	806.0	807.6	809.2	810.7	812.4	814.2
137.5°	834.4	836.4	838.3	840.2	842.1	843.9	845.7	847.5	849.3	850.9	852.6
140°	860.9	862.3	863.7	865.0	866.8	868.7	870.6	872.5	874.4	876.0	877.5
142.5°	883.4	884.7	885.9	887.2	888.9	891.0	893.3	895.5	897.7	899.1	900.5
145°	917.5	917.3	917.1	917.0	918.3	921.4	924.3	927.3	930.2	931.4	932.7
147.5°	948.0	947.4	946.7	946.0	947.1	950.0	953.0	956.0	958.9	959.8	960.7
150°	967.6	966.3	965.1	963.9	964.7	967.5	970.3	973.1	975.9	976.9	977.9
152.5°	984.4	983.0	981.7	980.3	980.9	983.6	986.3	988.9	991.6	992.6	993.7
155°	1008.9	1007.3	1005.7	1004.2	1004.4	1006.5	1008.7	1010.7	1012.8	1013.8	1014.9
157.5°	1028.5	1027.2	1025.8	1024.5	1024.6	1026.1	1027.5	1029.0	1030.4	1031.7	1032.8
160°	1040.1	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1042.2	1043.2
162.5°	1050.2	1049.1	1048.0	1047.0	1046.9	1047.8	1048.7	1049.6	1050.6	1051.7	1052.9
165°	1063.7	1062.6	1061.5	1060.5	1060.2	1060.8	1061.3	1061.9	1062.4	1063.6	1064.8
167.5°	1073.8	1072.7	1071.6	1070.6	1070.3	1070.8	1071.3	1071.8	1072.3	1073.5	1074.7
170°	1079.3	1078.3	1077.3	1076.2	1075.9	1076.2	1076.6	1076.9	1077.3	1078.5	1079.8
172.5°	1083.1	1082.1	1081.1	1080.0	1079.7	1080.0	1080.4	1080.7	1081.1	1082.3	1083.5
175°	1087.9	1086.7	1085.4	1084.2	1083.7	1084.1	1084.4	1084.8	1085.1	1086.4	1087.6
177.5°	1088.9	1088.0	1086.9	1086.0	1085.5	1085.7	1085.8	1086.0	1086.1	1087.1	1088.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331357-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1186.2	1191.1	1191.1	1191.8	1197.5	1196.7	1196.4
5°	1262.3	1269.8	1270.7	1278.6	1283.8	1282.1	1277.3
7.5°	1334.1	1348.1	1358.6	1364.4	1371.4	1375.7	1373.8
10°	1391.1	1411.4	1423.7	1432.0	1442.1	1449.6	1446.9
12.5°	1442.8	1466.9	1483.8	1498.1	1499.4	1509.0	1502.4
15°	1523.4	1548.9	1551.5	1562.1	1570.5	1569.5	1569.9
17.5°	1550.1	1558.2	1559.9	1560.1	1560.2	1557.1	1550.5
20°	1540.5	1537.5	1530.0	1524.3	1514.2	1512.9	1504.1
22.5°	1495.6	1485.7	1467.1	1454.7	1438.9	1434.8	1432.4
25°	1407.0	1385.3	1355.5	1326.9	1319.1	1303.6	1308.0
27.5°	1285.4	1251.8	1219.4	1196.2	1175.2	1152.2	1158.7
30°	1199.9	1162.1	1116.4	1081.2	1058.9	1036.8	1032.9
32.5°	1097.9	1042.6	991.5	960.6	926.3	912.4	897.2
35°	922.1	868.1	817.5	774.0	749.0	729.6	712.0
37.5°	764.0	701.7	661.0	625.7	607.6	596.5	599.3
40°	665.9	611.4	581.5	554.7	538.0	530.0	531.8
42.5°	586.4	545.6	521.0	502.7	490.9	486.5	485.4
45°	496.2	473.4	453.1	442.6	436.9	432.0	429.0
47.5°	434.7	416.0	404.7	398.4	393.4	388.5	388.4
50°	397.8	385.5	377.5	370.9	367.0	363.5	366.5
52.5°	369.6	358.3	350.5	344.6	343.1	339.9	339.8
55°	327.9	319.1	313.4	308.1	305.5	303.7	301.5
57.5°	289.9	281.5	276.3	272.9	267.9	266.1	265.4
60°	262.9	256.2	251.0	246.6	244.4	240.8	240.8
62.5°	237.9	231.3	226.4	223.0	219.4	218.0	218.3
65°	201.7	196.5	191.7	188.1	187.3	184.6	185.5
67.5°	168.5	165.0	159.9	158.0	156.3	154.9	153.9
70°	146.4	142.8	140.2	137.6	136.2	136.2	136.2
72.5°	127.7	123.5	121.9	118.6	119.3	118.0	116.6
75°	98.9	96.3	95.0	93.6	91.4	91.4	91.4
77.5°	72.8	72.0	70.4	69.0	68.4	68.0	68.2
80°	56.2	55.8	54.9	54.9	54.1	53.6	52.8
82.5°	43.2	42.1	41.6	41.2	41.1	41.0	40.8
85°	24.6	23.8	23.8	24.2	23.3	23.3	23.8
87.5°	13.2	13.3	13.1	13.2	13.6	13.3	13.3
90°	18.3	19.2	19.8	20.1	20.5	20.9	21.3
92.5°	19.6	20.1	20.4	20.6	20.8	21.0	21.3
95°	33.3	34.2	34.5	34.4	34.2	34.0	33.8
97.5°	43.1	43.8	44.3	44.5	44.7	44.9	45.1
100°	49.0	50.5	51.3	51.7	52.0	52.3	52.7
102.5°	51.6	53.4	54.5	55.0	55.4	56.0	56.5
105°	53.7	55.6	57.0	57.7	58.4	59.1	59.8
107.5°	61.3	59.3	58.7	59.4	60.1	60.8	61.5
110°	85.2	67.7	59.3	60.0	60.7	61.4	62.2



TEST NUMBER: P331357-935
 CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	155.8	92.1	60.5	61.0	61.6	62.2	62.8
115°	242.5	161.5	114.8	102.2	89.6	77.1	64.5
117.5°	478.7	459.1	428.6	387.3	345.9	304.6	263.3
120°	582.7	584.8	574.0	550.4	526.8	503.3	479.7
122.5°	617.3	618.5	616.9	612.3	607.7	603.1	598.6
125°	668.1	669.3	670.2	670.7	671.2	671.8	672.4
127.5°	715.7	717.6	718.4	718.6	718.7	718.8	718.8
130°	745.7	747.6	748.6	748.4	748.1	748.0	747.8
132.5°	774.5	776.1	776.8	776.6	776.4	776.3	776.1
135°	816.0	817.7	818.4	818.0	817.7	817.3	817.0
137.5°	854.4	856.1	856.7	856.1	855.5	854.9	854.3
140°	879.2	880.7	881.1	880.2	879.3	878.5	877.5
142.5°	902.0	903.4	903.7	902.8	902.0	901.1	900.2
145°	933.9	935.1	935.3	934.4	933.6	932.7	931.9
147.5°	961.6	962.5	962.6	961.8	961.1	960.4	959.7
150°	979.0	980.1	980.2	979.3	978.4	977.5	976.6
152.5°	994.7	995.7	995.7	994.5	993.4	992.3	991.1
155°	1016.0	1017.0	1016.8	1015.5	1014.0	1012.6	1011.2
157.5°	1034.0	1035.2	1035.1	1033.7	1032.3	1031.0	1029.7
160°	1044.3	1045.3	1045.3	1044.0	1042.8	1041.6	1040.3
162.5°	1054.1	1055.3	1055.2	1053.7	1052.1	1050.7	1049.1
165°	1066.0	1067.2	1067.2	1066.0	1064.8	1063.6	1062.4
167.5°	1075.9	1077.2	1076.9	1075.4	1073.8	1072.3	1070.7
170°	1081.0	1082.2	1082.0	1080.5	1078.8	1077.3	1075.7
172.5°	1084.8	1086.0	1085.8	1084.2	1082.6	1081.1	1079.5
175°	1088.8	1090.0	1089.8	1088.0	1086.3	1084.5	1082.8
177.5°	1089.1	1090.0	1089.9	1088.6	1087.4	1086.1	1084.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8

(END OF REPORT)