

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331358-935

Luminaire Tested: **SA2XXDIP-C675D925U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331358-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5374.2 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331358-935
CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18466	18466	18466	18466
5°	20702	18585	16470	18585
10°	23722	18433	14254	18433
15°	26242	18094	12593	18094
20°	25844	17732	11478	17732
25°	23302	17250	10774	17250
30°	19257	16479	10260	16479
35°	14034	15672	9895	15672
40°	11209	14720	9691	14720
45°	9796	13618	9412	13618
50°	9206	12552	9231	12552
55°	8487	11468	8982	11468
60°	7776	10317	8603	10317
65°	7087	9287	8225	9287
70°	6430	8280	7676	8280
75°	5702	7155	6800	7155
80°	4909	5923	5477	5923
85°	4409	4409	3260	4409



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	2.0
10°-20°	316.6	5.9
20°-30°	459.5	8.6
30°-40°	484.9	9.0
40°-50°	429.4	8.0
50°-60°	342.6	6.4
60°-70°	232.9	4.3
70°-80°	119.4	2.2
80°-90°	32.9	0.6
90°-100°	64.5	1.2
100°-110°	200.4	3.7
110°-120°	342.5	6.4
120°-130°	450.4	8.4
130°-140°	505.6	9.4
140°-150°	495.7	9.2
150°-160°	415.8	7.7
160°-170°	275.8	5.1
170°-180°	96.4	1.8
0°-30°	885.1	16.5
0°-40°	1370.0	25.5
0°-60°	2142.0	39.9
0°-90°	2527.2	47.0
90°-120°	607.4	11.3
90°-150°	2059.1	38.3
90°-180°	2847.0	53.0
0°-180°	5374.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1144	1144	1144	1144	1144	
5°	1277	1147	1016	1147	1277	128
15°	1570	1082	753	1082	1570	433
25°	1308	968	605	968	1308	591
35°	712	795	502	795	712	463
45°	429	596	412	596	429	337
55°	302	407	319	407	302	270
65°	186	243	215	243	186	184
75°	91	115	109	115	91	98
85°	24	24	18	24	24	27
90°	29	1	29	1	29	14
95°	53	45	53	45	53	59
105°	191	185	191	185	191	201
115°	344	344	344	344	344	339
125°	502	500	502	500	502	447
135°	655	647	655	647	655	504
145°	794	785	794	785	794	496
155°	905	898	905	898	905	416
165°	978	977	978	977	978	276
175°	1013	1016	1013	1016	1013	96
180°	1018	1018	1018	1018	1018	



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1196.4	1196.7	1197.5	1191.8	1191.1	1191.1	1186.2	1182.0	1177.1	1170.4	1171.0
5°	1277.3	1282.1	1283.8	1278.6	1270.7	1269.8	1262.3	1250.0	1238.5	1229.3	1222.8
7.5°	1373.8	1375.7	1371.4	1364.4	1358.6	1348.1	1334.1	1320.5	1301.4	1283.9	1270.9
10°	1446.9	1449.6	1442.1	1432.0	1423.7	1411.4	1391.1	1370.5	1345.4	1321.2	1301.8
12.5°	1502.4	1509.0	1499.4	1498.1	1483.8	1466.9	1442.8	1432.4	1397.1	1363.4	1342.6
15°	1569.9	1569.5	1570.5	1562.1	1551.5	1548.9	1523.4	1495.7	1446.0	1426.2	1392.0
17.5°	1550.5	1557.1	1560.2	1560.1	1559.9	1558.2	1550.1	1532.6	1507.7	1475.6	1436.0
20°	1504.1	1512.9	1514.2	1524.3	1530.0	1537.5	1540.5	1535.7	1520.4	1493.5	1459.2
22.5°	1432.4	1434.8	1438.9	1454.7	1467.1	1485.7	1495.6	1511.8	1505.9	1492.8	1464.1
25°	1308.0	1303.6	1319.1	1326.9	1355.5	1385.3	1407.0	1430.6	1451.7	1464.5	1456.1
27.5°	1158.7	1152.2	1175.2	1196.2	1219.4	1251.8	1285.4	1325.0	1358.0	1399.2	1413.3
30°	1032.9	1036.8	1058.9	1081.2	1116.4	1162.1	1199.9	1243.5	1290.5	1336.6	1368.6
32.5°	897.2	912.4	926.3	960.6	991.5	1042.6	1097.9	1152.4	1211.0	1263.4	1313.1
35°	712.0	729.6	749.0	774.0	817.5	868.1	922.1	995.5	1075.6	1147.2	1206.1
37.5°	599.3	596.5	607.6	625.7	661.0	701.7	764.0	836.5	930.7	1014.9	1097.9
40°	531.8	530.0	538.0	554.7	581.5	611.4	665.9	729.6	817.1	919.9	1018.8
42.5°	485.4	486.5	490.9	502.7	521.0	545.6	586.4	640.7	720.7	817.6	923.9
45°	429.0	432.0	436.9	442.6	453.1	473.4	496.2	534.9	598.2	679.1	783.7
47.5°	388.4	388.5	393.4	398.4	404.7	416.0	434.7	458.9	503.6	569.5	659.4
50°	366.5	363.5	367.0	370.9	377.5	385.5	397.8	420.6	450.5	503.7	578.9
52.5°	339.8	339.9	343.1	344.6	350.5	358.3	369.6	385.5	412.5	454.1	515.9
55°	301.5	303.7	305.5	308.1	313.4	319.1	327.9	338.5	359.6	390.7	436.4
57.5°	265.4	266.1	267.9	272.9	276.3	281.5	289.9	299.5	313.2	336.3	370.7
60°	240.8	240.8	244.4	246.6	251.0	256.2	262.9	272.1	284.4	303.2	331.0
62.5°	218.3	218.0	219.4	223.0	226.4	231.3	237.9	245.7	257.3	274.1	296.9
65°	185.5	184.6	187.3	188.1	191.7	196.5	201.7	210.1	219.3	231.6	251.8
67.5°	153.9	154.9	156.3	158.0	159.9	165.0	168.5	174.4	182.2	192.4	206.1
70°	136.2	136.2	136.2	137.6	140.2	142.8	146.4	151.2	158.7	167.5	179.8
72.5°	116.6	118.0	119.3	118.6	121.9	123.5	127.7	130.4	137.6	143.2	154.1
75°	91.4	91.4	91.4	93.6	95.0	96.3	98.9	101.5	105.0	112.1	117.8
77.5°	68.2	68.0	68.4	69.0	70.4	72.0	72.8	75.2	78.4	81.6	86.5
80°	52.8	53.6	54.1	54.9	54.9	55.8	56.2	59.3	61.6	63.7	66.8
82.5°	40.8	41.0	41.1	41.2	41.6	42.1	43.2	44.3	45.0	46.8	49.2
85°	23.8	23.3	23.3	24.2	23.8	23.8	24.6	25.5	25.5	25.9	27.2
87.5°	15.0	15.0	15.2	14.9	14.8	15.2	15.2	15.0	15.4	15.8	15.4
90°	29.2	29.0	28.8	28.7	28.4	28.6	28.9	29.3	29.7	30.0	25.8
92.5°	27.8	27.8	27.7	27.7	27.7	27.6	27.6	27.5	27.4	27.3	26.3
95°	53.3	53.6	54.1	54.4	54.8	55.0	55.0	55.0	55.0	55.0	54.6
97.5°	92.3	92.3	92.4	92.4	92.5	92.5	92.5	92.5	92.5	92.5	91.7
100°	117.7	117.9	118.1	118.3	118.5	118.6	118.6	118.6	118.6	118.6	118.0
102.5°	146.6	146.8	147.0	147.1	147.3	147.4	147.2	147.1	146.9	146.8	146.0
105°	190.7	190.7	190.7	190.7	190.7	190.5	190.2	189.8	189.4	189.0	188.6
107.5°	232.3	233.2	234.1	235.0	235.8	236.2	236.1	235.9	235.7	235.6	235.6
110°	264.7	265.2	265.8	266.4	266.9	267.3	267.3	267.3	267.3	267.3	267.3



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.6	296.0	296.4	296.9	297.2	297.7	298.2	298.6	299.1	299.5	299.7
115°	343.7	344.2	344.8	345.4	345.9	346.4	346.6	346.7	347.0	347.2	347.5
117.5°	389.6	390.1	390.7	391.3	391.8	392.4	392.9	393.3	393.7	394.3	395.3
120°	421.9	422.5	423.0	423.6	424.2	424.5	424.5	424.5	424.5	424.5	426.0
122.5°	453.5	453.9	454.3	454.8	455.2	455.6	456.1	456.5	457.0	457.4	458.6
125°	501.8	502.0	502.1	502.4	502.6	502.9	503.5	504.1	504.6	505.2	505.8
127.5°	545.8	546.4	547.0	547.6	548.2	548.9	549.6	550.3	551.0	551.6	552.3
130°	577.4	578.2	578.9	579.7	580.5	581.0	581.4	581.8	582.2	582.6	583.0
132.5°	607.7	608.3	608.9	609.5	610.1	610.8	611.7	612.5	613.4	614.2	614.1
135°	654.7	655.3	655.9	656.4	657.0	657.4	657.6	657.8	658.0	658.1	657.8
137.5°	697.3	698.1	698.9	699.6	700.4	700.9	701.0	701.2	701.4	701.5	701.0
140°	726.9	727.7	728.4	729.2	730.0	730.4	730.4	730.4	730.4	730.4	729.4
142.5°	753.7	754.5	755.3	756.0	756.8	757.1	756.9	756.8	756.6	756.5	755.8
145°	793.9	794.7	795.5	796.3	797.0	797.3	797.1	796.9	796.7	796.5	795.4
147.5°	829.8	830.6	831.3	832.1	832.8	832.9	832.5	832.1	831.6	831.2	830.4
150°	853.3	853.8	854.4	855.0	855.5	855.5	855.0	854.4	853.8	853.3	852.5
152.5°	875.2	876.0	876.7	877.4	878.1	878.1	877.4	876.7	876.0	875.2	874.3
155°	904.7	905.3	905.9	906.5	907.1	906.9	905.9	905.0	904.0	903.0	902.5
157.5°	930.2	931.1	932.0	933.0	933.8	933.7	932.4	931.1	929.8	928.5	928.2
160°	946.0	946.8	947.5	948.3	949.1	948.9	947.7	946.6	945.5	944.3	944.1
162.5°	959.8	960.7	961.6	962.5	963.5	963.2	961.9	960.6	959.3	958.0	957.9
165°	977.8	978.8	979.7	980.7	981.6	981.5	980.1	978.8	977.4	976.1	976.1
167.5°	992.6	993.6	994.5	995.6	996.5	996.3	995.1	993.7	992.4	991.0	991.1
170°	1000.1	1001.3	1002.5	1003.6	1004.7	1004.6	1003.3	1001.9	1000.7	999.3	999.4
172.5°	1006.3	1007.5	1008.7	1009.8	1010.9	1010.8	1009.5	1008.1	1006.9	1005.5	1005.6
175°	1013.1	1014.2	1015.3	1016.5	1017.6	1017.5	1016.2	1014.9	1013.5	1012.2	1012.5
177.5°	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2	1016.4
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1173.5	1170.7	1169.0	1162.6	1157.0	1151.4	1149.6	1150.3	1142.6	1135.2	1132.0
5°	1219.3	1210.5	1202.1	1190.2	1176.2	1160.8	1152.9	1146.7	1131.4	1114.7	1105.0
7.5°	1260.2	1247.7	1231.6	1209.2	1188.8	1164.6	1149.2	1135.6	1113.0	1089.5	1075.0
10°	1285.2	1268.0	1247.3	1220.1	1195.1	1165.6	1145.0	1124.3	1097.9	1069.8	1052.2
12.5°	1306.7	1283.5	1263.2	1228.2	1198.6	1161.7	1137.2	1108.1	1080.4	1047.0	1029.8
15°	1357.7	1315.1	1276.3	1236.8	1200.3	1148.9	1121.7	1082.5	1046.0	1004.8	985.0
17.5°	1397.1	1349.3	1288.3	1238.0	1195.5	1138.6	1098.5	1051.7	1008.6	961.3	934.4
20°	1419.7	1364.7	1299.2	1239.5	1188.4	1123.4	1080.0	1032.0	981.5	928.2	899.2
22.5°	1433.0	1375.3	1310.5	1234.2	1174.4	1111.1	1056.4	1003.8	952.6	895.3	864.8
25°	1437.3	1384.5	1316.0	1229.8	1156.8	1085.2	1019.3	968.3	906.3	852.6	808.3
27.5°	1416.3	1378.5	1312.6	1221.5	1136.5	1052.7	979.3	921.5	856.1	797.9	753.3
30°	1390.7	1368.6	1304.5	1213.1	1120.3	1030.3	949.3	883.9	818.8	759.9	714.2
32.5°	1350.9	1346.2	1289.8	1201.1	1103.1	1001.8	918.1	851.9	779.8	721.9	678.4
35°	1272.9	1294.0	1258.4	1174.4	1070.7	961.2	870.7	795.1	720.4	665.0	624.1
37.5°	1168.3	1220.6	1211.3	1135.3	1026.9	917.1	817.2	738.1	666.9	611.1	570.9
40°	1096.1	1163.0	1172.7	1105.4	996.0	883.0	777.1	698.4	629.0	578.0	537.5
42.5°	1018.8	1096.9	1123.4	1069.5	962.2	847.1	741.2	659.7	591.0	541.4	505.6
45°	889.2	992.5	1040.3	1009.6	905.9	788.1	679.1	596.4	534.0	487.4	459.8
47.5°	767.9	880.8	945.2	934.4	843.2	726.5	618.8	539.5	478.7	441.5	416.7
50°	682.2	798.1	876.0	879.5	798.1	682.6	574.5	499.7	443.9	409.2	389.0
52.5°	607.6	718.3	803.2	821.8	747.9	636.9	534.8	460.4	411.2	379.3	361.2
55°	510.3	603.9	697.9	732.3	672.9	567.4	472.9	407.4	361.3	339.3	323.5
57.5°	424.2	502.3	589.2	627.1	590.5	500.2	411.6	354.7	317.3	298.0	285.9
60°	378.8	440.4	517.7	563.0	531.4	451.0	373.6	319.5	288.8	271.6	260.2
62.5°	336.7	391.2	456.6	498.0	480.8	404.9	335.6	287.9	261.3	245.2	237.0
65°	277.8	320.9	371.4	409.7	398.2	340.6	284.0	243.1	222.0	209.2	202.6
67.5°	228.8	259.8	294.9	328.4	319.2	278.4	232.9	201.0	185.3	174.4	170.4
70°	197.8	221.5	252.7	279.6	272.1	238.7	202.6	175.4	161.8	152.5	148.5
72.5°	168.2	187.8	211.5	233.5	228.4	200.7	170.7	150.1	139.6	131.0	127.8
75°	127.0	142.0	156.4	171.0	169.6	148.1	130.5	114.7	106.3	99.8	98.4
77.5°	93.8	102.1	112.0	120.6	118.2	105.9	92.1	83.1	76.9	72.5	71.8
80°	71.6	76.5	83.5	89.6	86.6	81.3	70.3	63.7	59.3	54.9	53.2
82.5°	51.9	56.8	61.0	64.3	62.0	57.1	50.3	45.8	43.1	40.2	39.4
85°	27.2	29.9	31.7	32.5	31.7	28.6	25.5	23.8	21.5	20.2	19.8
87.5°	14.9	14.0	13.2	13.3	11.7	11.3	9.4	7.9	8.0	8.1	7.8
90°	21.7	17.5	13.3	10.0	7.7	5.4	3.2	0.9	3.2	5.4	7.7
92.5°	25.3	24.4	23.3	22.0	20.3	18.7	17.0	15.3	17.0	18.7	20.3
95°	54.2	53.8	53.5	52.3	50.4	48.5	46.6	44.7	46.6	48.5	50.4
97.5°	91.0	90.3	89.5	88.3	86.7	85.0	83.3	81.6	83.3	85.0	86.7
100°	117.4	116.8	116.3	115.2	113.7	112.2	110.6	109.1	110.6	112.2	113.7
102.5°	145.3	144.6	143.9	142.8	141.6	140.4	139.2	138.0	139.2	140.4	141.6
105°	188.3	187.9	187.5	187.0	186.5	185.9	185.3	184.8	185.3	185.9	186.5
107.5°	235.6	235.6	235.6	235.2	234.4	233.5	232.6	231.8	232.6	233.5	234.4
110°	267.3	267.3	267.3	266.7	265.5	264.3	263.2	262.1	263.2	264.3	265.5



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	299.8	300.0	300.1	299.6	298.5	297.4	296.2	295.1	296.2	297.4	298.5
115°	347.9	348.3	348.6	348.3	347.2	345.9	344.8	343.7	344.8	345.9	347.2
117.5°	396.3	397.4	398.5	398.3	396.7	395.2	393.6	392.2	393.6	395.2	396.7
120°	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5	426.0	427.5	429.0
122.5°	459.6	460.6	461.8	461.3	459.5	457.7	455.8	454.0	455.8	457.7	459.5
125°	506.4	507.0	507.6	507.0	505.2	503.5	501.8	500.1	501.8	503.5	505.2
127.5°	553.0	553.7	554.4	553.6	551.5	549.3	547.1	544.9	547.1	549.3	551.5
130°	583.3	583.7	584.1	583.1	580.6	578.1	575.6	573.1	575.6	578.1	580.6
132.5°	614.1	614.0	613.9	612.9	610.8	608.8	606.7	604.8	606.7	608.8	610.8
135°	657.4	657.0	656.7	655.4	653.3	651.2	649.1	647.0	649.1	651.2	653.3
137.5°	700.5	700.0	699.5	698.4	696.6	694.9	693.2	691.6	693.2	694.9	696.6
140°	728.4	727.5	726.5	725.2	723.5	721.8	720.1	718.3	720.1	721.8	723.5
142.5°	755.2	754.5	753.9	752.7	751.0	749.2	747.5	745.8	747.5	749.2	751.0
145°	794.2	793.1	791.9	790.7	789.4	788.0	786.7	785.3	786.7	788.0	789.4
147.5°	829.7	829.0	828.2	827.0	825.4	823.8	822.2	820.5	822.2	823.8	825.4
150°	851.7	850.9	850.2	849.2	848.1	846.9	845.8	844.6	845.8	846.9	848.1
152.5°	873.4	872.5	871.6	870.6	869.4	868.2	867.1	865.9	867.1	868.2	869.4
155°	901.9	901.4	900.8	900.2	899.7	899.1	898.5	897.9	898.5	899.1	899.7
157.5°	927.8	927.5	927.1	926.8	926.3	926.0	925.6	925.2	925.6	926.0	926.3
160°	943.9	943.7	943.6	943.2	942.9	942.5	942.1	941.8	942.1	942.5	942.9
162.5°	957.7	957.5	957.3	957.2	957.1	957.0	956.9	956.8	956.9	957.0	957.1
165°	976.1	976.1	976.1	976.2	976.4	976.5	976.8	977.0	976.8	976.5	976.4
167.5°	991.1	991.2	991.2	991.5	992.0	992.6	993.2	993.8	993.2	992.6	992.0
170°	999.7	999.9	1000.1	1000.4	1001.0	1001.6	1002.1	1002.7	1002.1	1001.6	1001.0
172.5°	1005.8	1006.1	1006.3	1006.6	1007.2	1007.8	1008.3	1008.9	1008.3	1007.8	1007.2
175°	1013.0	1013.3	1013.7	1014.2	1014.8	1015.3	1015.9	1016.5	1015.9	1015.3	1014.8
177.5°	1016.8	1017.0	1017.4	1017.7	1018.2	1018.6	1019.1	1019.6	1019.1	1018.6	1018.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1128.5	1126.4	1119.0	1115.2	1108.8	1102.9	1099.0	1100.8	1102.2	1101.5	1100.4
5°	1096.1	1087.8	1075.0	1064.1	1056.2	1041.6	1035.5	1032.4	1029.8	1026.7	1023.6
7.5°	1057.7	1044.5	1026.2	1010.6	995.7	977.8	967.5	961.3	955.0	948.0	941.9
10°	1030.3	1011.8	992.5	970.4	952.9	936.6	922.1	912.5	903.7	895.4	889.2
12.5°	1001.4	980.2	956.2	926.2	906.8	883.6	881.3	864.3	850.6	845.4	838.2
15°	955.5	925.7	895.4	859.7	844.3	823.2	810.0	796.9	785.0	776.6	774.5
17.5°	903.4	864.7	834.6	809.0	783.8	762.2	750.0	739.4	729.7	718.5	717.0
20°	863.7	830.3	797.3	774.9	749.0	726.9	712.0	701.5	693.1	686.6	680.8
22.5°	826.0	789.5	759.3	734.8	709.2	691.5	679.7	669.5	662.5	655.2	649.9
25°	765.7	737.1	704.1	676.4	655.3	643.9	634.2	625.4	621.0	616.2	610.1
27.5°	712.8	681.1	650.2	628.8	610.3	600.1	593.2	587.3	583.2	580.3	576.9
30°	675.5	643.4	619.3	598.2	582.8	572.7	568.3	564.8	560.0	558.2	556.5
32.5°	639.7	610.8	590.1	571.8	557.2	550.5	546.5	543.4	539.6	537.8	534.3
35°	588.9	564.8	544.6	534.4	522.6	516.9	513.8	509.4	505.9	504.1	503.7
37.5°	541.2	520.2	507.0	494.0	489.0	485.4	481.2	478.2	477.2	476.9	476.5
40°	510.3	493.2	481.3	470.7	468.6	463.2	459.8	457.1	457.1	457.5	457.1
42.5°	482.2	466.7	456.3	447.2	444.6	441.4	437.9	437.7	438.5	440.0	438.5
45°	439.5	428.5	421.0	416.6	411.8	408.7	408.3	409.7	410.1	410.5	411.8
47.5°	400.3	393.0	386.2	381.4	379.3	378.8	378.2	380.6	382.6	383.4	385.5
50°	377.1	368.8	363.1	360.0	358.2	357.3	358.2	360.8	362.6	364.8	366.1
52.5°	351.1	345.2	341.2	338.9	338.2	338.7	338.9	341.9	344.7	345.4	346.1
55°	315.1	310.7	309.9	305.9	307.6	307.2	309.4	311.2	313.8	316.4	316.9
57.5°	279.3	275.8	273.4	273.7	274.2	276.2	278.0	281.1	284.0	286.7	287.0
60°	255.4	253.6	252.3	252.3	253.1	255.8	258.0	261.1	262.9	264.6	265.9
62.5°	233.6	231.8	230.5	231.2	233.5	235.1	237.6	239.3	241.0	242.8	243.4
65°	199.1	198.2	199.6	200.4	200.9	203.0	206.1	207.4	209.2	210.1	213.2
67.5°	167.4	167.6	167.4	168.6	171.2	171.7	174.6	177.6	178.0	179.7	181.7
70°	145.9	146.8	147.7	148.5	150.8	151.6	153.9	155.2	156.9	158.3	159.5
72.5°	126.2	126.4	127.3	127.1	129.0	130.9	132.8	134.1	135.8	137.5	138.8
75°	97.1	97.1	98.0	98.4	100.7	102.9	102.4	103.3	105.0	106.8	107.7
77.5°	70.9	70.0	70.9	71.4	72.1	74.0	74.3	75.5	77.5	76.9	77.9
80°	54.1	52.8	54.1	54.5	54.5	56.7	56.7	57.6	58.9	57.6	58.9
82.5°	38.6	38.0	38.9	39.0	39.7	39.8	40.6	40.7	42.0	41.4	42.0
85°	19.4	18.9	19.4	18.9	19.4	19.8	19.8	19.4	19.4	20.2	18.9
87.5°	8.0	8.3	8.8	9.6	10.1	10.6	10.2	10.1	10.0	9.2	9.2
90°	10.0	13.3	17.5	21.7	25.8	30.0	29.7	29.3	28.9	28.6	28.4
92.5°	22.0	23.3	24.4	25.3	26.3	27.3	27.4	27.5	27.6	27.6	27.7
95°	52.3	53.5	53.8	54.2	54.6	55.0	55.0	55.0	55.0	55.0	54.8
97.5°	88.3	89.5	90.3	91.0	91.7	92.5	92.5	92.5	92.5	92.5	92.5
100°	115.2	116.3	116.8	117.4	118.0	118.6	118.6	118.6	118.6	118.6	118.5
102.5°	142.8	143.9	144.6	145.3	146.0	146.8	146.9	147.1	147.2	147.4	147.3
105°	187.0	187.5	187.9	188.3	188.6	189.0	189.4	189.8	190.2	190.5	190.7
107.5°	235.2	235.6	235.6	235.6	235.6	235.6	235.7	235.9	236.1	236.2	235.8
110°	266.7	267.3	267.3	267.3	267.3	267.3	267.3	267.3	267.3	267.3	266.9



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	299.6	300.1	300.0	299.8	299.7	299.5	299.1	298.6	298.2	297.7	297.2
115°	348.3	348.6	348.3	347.9	347.5	347.2	347.0	346.7	346.6	346.4	345.9
117.5°	398.3	398.5	397.4	396.3	395.3	394.3	393.7	393.3	392.9	392.4	391.8
120°	430.6	430.6	429.0	427.5	426.0	424.5	424.5	424.5	424.5	424.5	424.2
122.5°	461.3	461.8	460.6	459.6	458.6	457.4	457.0	456.5	456.1	455.6	455.2
125°	507.0	507.6	507.0	506.4	505.8	505.2	504.6	504.1	503.5	502.9	502.6
127.5°	553.6	554.4	553.7	553.0	552.3	551.6	551.0	550.3	549.6	548.9	548.2
130°	583.1	584.1	583.7	583.3	583.0	582.6	582.2	581.8	581.4	581.0	580.5
132.5°	612.9	613.9	614.0	614.1	614.1	614.2	613.4	612.5	611.7	610.8	610.1
135°	655.4	656.7	657.0	657.4	657.8	658.1	658.0	657.8	657.6	657.4	657.0
137.5°	698.4	699.5	700.0	700.5	701.0	701.5	701.4	701.2	701.0	700.9	700.4
140°	725.2	726.5	727.5	728.4	729.4	730.4	730.4	730.4	730.4	730.4	730.0
142.5°	752.7	753.9	754.5	755.2	755.8	756.5	756.6	756.8	756.9	757.1	756.8
145°	790.7	791.9	793.1	794.2	795.4	796.5	796.7	796.9	797.1	797.3	797.0
147.5°	827.0	828.2	829.0	829.7	830.4	831.2	831.6	832.1	832.5	832.9	832.8
150°	849.2	850.2	850.9	851.7	852.5	853.3	853.8	854.4	855.0	855.5	855.5
152.5°	870.6	871.6	872.5	873.4	874.3	875.2	876.0	876.7	877.4	878.1	878.1
155°	900.2	900.8	901.4	901.9	902.5	903.0	904.0	905.0	905.9	906.9	907.1
157.5°	926.8	927.1	927.5	927.8	928.2	928.5	929.8	931.1	932.4	933.7	933.8
160°	943.2	943.6	943.7	943.9	944.1	944.3	945.5	946.6	947.7	948.9	949.1
162.5°	957.2	957.3	957.5	957.7	957.9	958.0	959.3	960.6	961.9	963.2	963.5
165°	976.2	976.1	976.1	976.1	976.1	976.1	977.4	978.8	980.1	981.5	981.6
167.5°	991.5	991.2	991.2	991.1	991.1	991.0	992.4	993.7	995.1	996.3	996.5
170°	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7	1001.9	1003.3	1004.6	1004.7
172.5°	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9	1008.1	1009.5	1010.8	1010.9
175°	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5	1014.9	1016.2	1017.5	1017.6
177.5°	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1096.9	1096.1	1096.1	1093.0	1096.1	1096.1	1096.9	1100.4	1101.5	1102.2	1100.8
5°	1017.5	1016.2	1014.0	1016.2	1014.0	1016.2	1017.5	1023.6	1026.7	1029.8	1032.4
7.5°	939.0	933.8	933.0	927.7	933.0	933.8	939.0	941.9	948.0	955.0	961.3
10°	881.7	878.1	877.7	869.4	877.7	878.1	881.7	889.2	895.4	903.7	912.5
12.5°	838.1	829.7	831.3	826.5	831.3	829.7	838.1	838.2	845.4	850.6	864.3
15°	762.6	762.6	760.8	753.4	760.8	762.6	762.6	774.5	776.6	785.0	796.9
17.5°	708.3	707.5	703.3	705.3	703.3	707.5	708.3	717.0	718.5	729.7	739.4
20°	676.0	673.4	668.0	668.0	668.0	673.4	676.0	680.8	686.6	693.1	701.5
22.5°	645.4	645.2	639.6	641.4	639.6	645.2	645.4	649.9	655.2	662.5	669.5
25°	609.6	606.1	603.5	604.8	603.5	606.1	609.6	610.1	616.2	621.0	625.4
27.5°	575.7	573.8	573.6	570.0	573.6	573.8	575.7	576.9	580.3	583.2	587.3
30°	556.0	551.6	552.5	550.3	552.5	551.6	556.0	556.5	558.2	560.0	564.8
32.5°	533.5	531.9	531.1	529.2	531.1	531.9	533.5	534.3	537.8	539.6	543.4
35°	502.8	503.3	501.1	502.0	501.1	503.3	502.8	503.7	504.1	505.9	509.4
37.5°	476.0	477.4	476.4	476.6	476.4	477.4	476.0	476.5	476.9	477.2	478.2
40°	458.4	458.4	458.4	459.8	458.4	458.4	458.4	457.1	457.5	457.1	457.1
42.5°	441.5	440.8	440.1	440.1	440.1	440.8	441.5	438.5	440.0	438.5	437.7
45°	412.7	414.1	414.5	412.2	414.5	414.1	412.7	411.8	410.5	410.1	409.7
47.5°	386.6	386.8	386.6	388.6	386.6	386.8	386.6	385.5	383.4	382.6	380.6
50°	368.3	367.5	368.3	367.5	368.3	367.5	368.3	366.1	364.8	362.6	360.8
52.5°	349.0	349.1	348.6	348.4	348.6	349.1	349.0	346.1	345.4	344.7	341.9
55°	318.7	319.5	319.1	319.1	319.1	319.5	318.7	316.9	316.4	313.8	311.2
57.5°	287.3	288.1	288.7	286.7	288.7	288.1	287.3	287.0	286.7	284.0	281.1
60°	265.4	267.7	267.3	266.4	267.3	267.7	265.4	265.9	264.6	262.9	261.1
62.5°	245.5	246.2	246.2	246.0	246.2	246.2	245.5	243.4	242.8	241.0	239.3
65°	214.5	215.3	214.0	215.3	214.0	215.3	214.5	213.2	210.1	209.2	207.4
67.5°	181.2	181.4	182.4	183.0	182.4	181.4	181.2	181.7	179.7	178.0	177.6
70°	160.4	160.0	161.3	162.6	161.3	160.0	160.4	159.5	158.3	156.9	155.2
72.5°	138.6	139.6	139.1	140.1	139.1	139.6	138.6	138.8	137.5	135.8	134.1
75°	106.8	108.1	107.7	109.0	107.7	108.1	106.8	107.7	106.8	105.0	103.3
77.5°	77.1	77.3	77.1	77.9	77.1	77.3	77.1	77.9	76.9	77.5	75.5
80°	58.9	58.0	57.2	58.9	57.2	58.0	58.9	58.9	57.6	58.9	57.6
82.5°	41.0	41.5	40.6	40.6	40.6	41.5	41.0	42.0	41.4	42.0	40.7
85°	18.9	18.4	17.6	17.6	17.6	18.4	18.9	18.9	20.2	19.4	19.4
87.5°	9.2	9.0	9.0	8.7	9.0	9.0	9.2	9.2	9.2	10.0	10.1
90°	28.7	28.8	29.0	29.2	29.0	28.8	28.7	28.4	28.6	28.9	29.3
92.5°	27.7	27.7	27.8	27.8	27.8	27.7	27.7	27.7	27.6	27.6	27.5
95°	54.4	54.1	53.6	53.3	53.6	54.1	54.4	54.8	55.0	55.0	55.0
97.5°	92.4	92.4	92.3	92.3	92.3	92.4	92.4	92.5	92.5	92.5	92.5
100°	118.3	118.1	117.9	117.7	117.9	118.1	118.3	118.5	118.6	118.6	118.6
102.5°	147.1	147.0	146.8	146.6	146.8	147.0	147.1	147.3	147.4	147.2	147.1
105°	190.7	190.7	190.7	190.7	190.7	190.7	190.7	190.7	190.5	190.2	189.8
107.5°	235.0	234.1	233.2	232.3	233.2	234.1	235.0	235.8	236.2	236.1	235.9
110°	266.4	265.8	265.2	264.7	265.2	265.8	266.4	266.9	267.3	267.3	267.3



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	296.9	296.4	296.0	295.6	296.0	296.4	296.9	297.2	297.7	298.2	298.6
115°	345.4	344.8	344.2	343.7	344.2	344.8	345.4	345.9	346.4	346.6	346.7
117.5°	391.3	390.7	390.1	389.6	390.1	390.7	391.3	391.8	392.4	392.9	393.3
120°	423.6	423.0	422.5	421.9	422.5	423.0	423.6	424.2	424.5	424.5	424.5
122.5°	454.8	454.3	453.9	453.5	453.9	454.3	454.8	455.2	455.6	456.1	456.5
125°	502.4	502.1	502.0	501.8	502.0	502.1	502.4	502.6	502.9	503.5	504.1
127.5°	547.6	547.0	546.4	545.8	546.4	547.0	547.6	548.2	548.9	549.6	550.3
130°	579.7	578.9	578.2	577.4	578.2	578.9	579.7	580.5	581.0	581.4	581.8
132.5°	609.5	608.9	608.3	607.7	608.3	608.9	609.5	610.1	610.8	611.7	612.5
135°	656.4	655.9	655.3	654.7	655.3	655.9	656.4	657.0	657.4	657.6	657.8
137.5°	699.6	698.9	698.1	697.3	698.1	698.9	699.6	700.4	700.9	701.0	701.2
140°	729.2	728.4	727.7	726.9	727.7	728.4	729.2	730.0	730.4	730.4	730.4
142.5°	756.0	755.3	754.5	753.7	754.5	755.3	756.0	756.8	757.1	756.9	756.8
145°	796.3	795.5	794.7	793.9	794.7	795.5	796.3	797.0	797.3	797.1	796.9
147.5°	832.1	831.3	830.6	829.8	830.6	831.3	832.1	832.8	832.9	832.5	832.1
150°	855.0	854.4	853.8	853.3	853.8	854.4	855.0	855.5	855.5	855.0	854.4
152.5°	877.4	876.7	876.0	875.2	876.0	876.7	877.4	878.1	878.1	877.4	876.7
155°	906.5	905.9	905.3	904.7	905.3	905.9	906.5	907.1	906.9	905.9	905.0
157.5°	933.0	932.0	931.1	930.2	931.1	932.0	933.0	933.8	933.7	932.4	931.1
160°	948.3	947.5	946.8	946.0	946.8	947.5	948.3	949.1	948.9	947.7	946.6
162.5°	962.5	961.6	960.7	959.8	960.7	961.6	962.5	963.5	963.2	961.9	960.6
165°	980.7	979.7	978.8	977.8	978.8	979.7	980.7	981.6	981.5	980.1	978.8
167.5°	995.6	994.5	993.6	992.6	993.6	994.5	995.6	996.5	996.3	995.1	993.7
170°	1003.6	1002.5	1001.3	1000.1	1001.3	1002.5	1003.6	1004.7	1004.6	1003.3	1001.9
172.5°	1009.8	1008.7	1007.5	1006.3	1007.5	1008.7	1009.8	1010.9	1010.8	1009.5	1008.1
175°	1016.5	1015.3	1014.2	1013.1	1014.2	1015.3	1016.5	1017.6	1017.5	1016.2	1014.9
177.5°	1018.9	1018.0	1017.0	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1099.0	1102.9	1108.8	1115.2	1119.0	1126.4	1128.5	1132.0	1135.2	1142.6	1150.3
5°	1035.5	1041.6	1056.2	1064.1	1075.0	1087.8	1096.1	1105.0	1114.7	1131.4	1146.7
7.5°	967.5	977.8	995.7	1010.6	1026.2	1044.5	1057.7	1075.0	1089.5	1113.0	1135.6
10°	922.1	936.6	952.9	970.4	992.5	1011.8	1030.3	1052.2	1069.8	1097.9	1124.3
12.5°	881.3	883.6	906.8	926.2	956.2	980.2	1001.4	1029.8	1047.0	1080.4	1108.1
15°	810.0	823.2	844.3	859.7	895.4	925.7	955.5	985.0	1004.8	1046.0	1082.5
17.5°	750.0	762.2	783.8	809.0	834.6	864.7	903.4	934.4	961.3	1008.6	1051.7
20°	712.0	726.9	749.0	774.9	797.3	830.3	863.7	899.2	928.2	981.5	1032.0
22.5°	679.7	691.5	709.2	734.8	759.3	789.5	826.0	864.8	895.3	952.6	1003.8
25°	634.2	643.9	655.3	676.4	704.1	737.1	765.7	808.3	852.6	906.3	968.3
27.5°	593.2	600.1	610.3	628.8	650.2	681.1	712.8	753.3	797.9	856.1	921.5
30°	568.3	572.7	582.8	598.2	619.3	643.4	675.5	714.2	759.9	818.8	883.9
32.5°	546.5	550.5	557.2	571.8	590.1	610.8	639.7	678.4	721.9	779.8	851.9
35°	513.8	516.9	522.6	534.4	544.6	564.8	588.9	624.1	665.0	720.4	795.1
37.5°	481.2	485.4	489.0	494.0	507.0	520.2	541.2	570.9	611.1	666.9	738.1
40°	459.8	463.2	468.6	470.7	481.3	493.2	510.3	537.5	578.0	629.0	698.4
42.5°	437.9	441.4	444.6	447.2	456.3	466.7	482.2	505.6	541.4	591.0	659.7
45°	408.3	408.7	411.8	416.6	421.0	428.5	439.5	459.8	487.4	534.0	596.4
47.5°	378.2	378.8	379.3	381.4	386.2	393.0	400.3	416.7	441.5	478.7	539.5
50°	358.2	357.3	358.2	360.0	363.1	368.8	377.1	389.0	409.2	443.9	499.7
52.5°	338.9	338.7	338.2	338.9	341.2	345.2	351.1	361.2	379.3	411.2	460.4
55°	309.4	307.2	307.6	305.9	309.9	310.7	315.1	323.5	339.3	361.3	407.4
57.5°	278.0	276.2	274.2	273.7	273.4	275.8	279.3	285.9	298.0	317.3	354.7
60°	258.0	255.8	253.1	252.3	252.3	253.6	255.4	260.2	271.6	288.8	319.5
62.5°	237.6	235.1	233.5	231.2	230.5	231.8	233.6	237.0	245.2	261.3	287.9
65°	206.1	203.0	200.9	200.4	199.6	198.2	199.1	202.6	209.2	222.0	243.1
67.5°	174.6	171.7	171.2	168.6	167.4	167.6	167.4	170.4	174.4	185.3	201.0
70°	153.9	151.6	150.8	148.5	147.7	146.8	145.9	148.5	152.5	161.8	175.4
72.5°	132.8	130.9	129.0	127.1	127.3	126.4	126.2	127.8	131.0	139.6	150.1
75°	102.4	102.9	100.7	98.4	98.0	97.1	97.1	98.4	99.8	106.3	114.7
77.5°	74.3	74.0	72.1	71.4	70.9	70.0	70.9	71.8	72.5	76.9	83.1
80°	56.7	56.7	54.5	54.5	54.1	52.8	54.1	53.2	54.9	59.3	63.7
82.5°	40.6	39.8	39.7	39.0	38.9	38.0	38.6	39.4	40.2	43.1	45.8
85°	19.8	19.8	19.4	18.9	19.4	18.9	19.4	19.8	20.2	21.5	23.8
87.5°	10.2	10.6	10.1	9.6	8.8	8.3	8.0	7.8	8.1	8.0	7.9
90°	29.7	30.0	25.8	21.7	17.5	13.3	10.0	7.7	5.4	3.2	0.9
92.5°	27.4	27.3	26.3	25.3	24.4	23.3	22.0	20.3	18.7	17.0	15.3
95°	55.0	55.0	54.6	54.2	53.8	53.5	52.3	50.4	48.5	46.6	44.7
97.5°	92.5	92.5	91.7	91.0	90.3	89.5	88.3	86.7	85.0	83.3	81.6
100°	118.6	118.6	118.0	117.4	116.8	116.3	115.2	113.7	112.2	110.6	109.1
102.5°	146.9	146.8	146.0	145.3	144.6	143.9	142.8	141.6	140.4	139.2	138.0
105°	189.4	189.0	188.6	188.3	187.9	187.5	187.0	186.5	185.9	185.3	184.8
107.5°	235.7	235.6	235.6	235.6	235.6	235.6	235.2	234.4	233.5	232.6	231.8
110°	267.3	267.3	267.3	267.3	267.3	267.3	266.7	265.5	264.3	263.2	262.1



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	299.1	299.5	299.7	299.8	300.0	300.1	299.6	298.5	297.4	296.2	295.1
115°	347.0	347.2	347.5	347.9	348.3	348.6	348.3	347.2	345.9	344.8	343.7
117.5°	393.7	394.3	395.3	396.3	397.4	398.5	398.3	396.7	395.2	393.6	392.2
120°	424.5	424.5	426.0	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5
122.5°	457.0	457.4	458.6	459.6	460.6	461.8	461.3	459.5	457.7	455.8	454.0
125°	504.6	505.2	505.8	506.4	507.0	507.6	507.0	505.2	503.5	501.8	500.1
127.5°	551.0	551.6	552.3	553.0	553.7	554.4	553.6	551.5	549.3	547.1	544.9
130°	582.2	582.6	583.0	583.3	583.7	584.1	583.1	580.6	578.1	575.6	573.1
132.5°	613.4	614.2	614.1	614.1	614.0	613.9	612.9	610.8	608.8	606.7	604.8
135°	658.0	658.1	657.8	657.4	657.0	656.7	655.4	653.3	651.2	649.1	647.0
137.5°	701.4	701.5	701.0	700.5	700.0	699.5	698.4	696.6	694.9	693.2	691.6
140°	730.4	730.4	729.4	728.4	727.5	726.5	725.2	723.5	721.8	720.1	718.3
142.5°	756.6	756.5	755.8	755.2	754.5	753.9	752.7	751.0	749.2	747.5	745.8
145°	796.7	796.5	795.4	794.2	793.1	791.9	790.7	789.4	788.0	786.7	785.3
147.5°	831.6	831.2	830.4	829.7	829.0	828.2	827.0	825.4	823.8	822.2	820.5
150°	853.8	853.3	852.5	851.7	850.9	850.2	849.2	848.1	846.9	845.8	844.6
152.5°	876.0	875.2	874.3	873.4	872.5	871.6	870.6	869.4	868.2	867.1	865.9
155°	904.0	903.0	902.5	901.9	901.4	900.8	900.2	899.7	899.1	898.5	897.9
157.5°	929.8	928.5	928.2	927.8	927.5	927.1	926.8	926.3	926.0	925.6	925.2
160°	945.5	944.3	944.1	943.9	943.7	943.6	943.2	942.9	942.5	942.1	941.8
162.5°	959.3	958.0	957.9	957.7	957.5	957.3	957.2	957.1	957.0	956.9	956.8
165°	977.4	976.1	976.1	976.1	976.1	976.1	976.2	976.4	976.5	976.8	977.0
167.5°	992.4	991.0	991.1	991.1	991.2	991.2	991.5	992.0	992.6	993.2	993.8
170°	1000.7	999.3	999.4	999.7	999.9	1000.1	1000.4	1001.0	1001.6	1002.1	1002.7
172.5°	1006.9	1005.5	1005.6	1005.8	1006.1	1006.3	1006.6	1007.2	1007.8	1008.3	1008.9
175°	1013.5	1012.2	1012.5	1013.0	1013.3	1013.7	1014.2	1014.8	1015.3	1015.9	1016.5
177.5°	1017.0	1016.2	1016.4	1016.8	1017.0	1017.4	1017.7	1018.2	1018.6	1019.1	1019.6
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1149.6	1151.4	1157.0	1162.6	1169.0	1170.7	1173.5	1171.0	1170.4	1177.1	1182.0
5°	1152.9	1160.8	1176.2	1190.2	1202.1	1210.5	1219.3	1222.8	1229.3	1238.5	1250.0
7.5°	1149.2	1164.6	1188.8	1209.2	1231.6	1247.7	1260.2	1270.9	1283.9	1301.4	1320.5
10°	1145.0	1165.6	1195.1	1220.1	1247.3	1268.0	1285.2	1301.8	1321.2	1345.4	1370.5
12.5°	1137.2	1161.7	1198.6	1228.2	1263.2	1283.5	1306.7	1342.6	1363.4	1397.1	1432.4
15°	1121.7	1148.9	1200.3	1236.8	1276.3	1315.1	1357.7	1392.0	1426.2	1446.0	1495.7
17.5°	1098.5	1138.6	1195.5	1238.0	1288.3	1349.3	1397.1	1436.0	1475.6	1507.7	1532.6
20°	1080.0	1123.4	1188.4	1239.5	1299.2	1364.7	1419.7	1459.2	1493.5	1520.4	1535.7
22.5°	1056.4	1111.1	1174.4	1234.2	1310.5	1375.3	1433.0	1464.1	1492.8	1505.9	1511.8
25°	1019.3	1085.2	1156.8	1229.8	1316.0	1384.5	1437.3	1456.1	1464.5	1451.7	1430.6
27.5°	979.3	1052.7	1136.5	1221.5	1312.6	1378.5	1416.3	1413.3	1399.2	1358.0	1325.0
30°	949.3	1030.3	1120.3	1213.1	1304.5	1368.6	1390.7	1368.6	1336.6	1290.5	1243.5
32.5°	918.1	1001.8	1103.1	1201.1	1289.8	1346.2	1350.9	1313.1	1263.4	1211.0	1152.4
35°	870.7	961.2	1070.7	1174.4	1258.4	1294.0	1272.9	1206.1	1147.2	1075.6	995.5
37.5°	817.2	917.1	1026.9	1135.3	1211.3	1220.6	1168.3	1097.9	1014.9	930.7	836.5
40°	777.1	883.0	996.0	1105.4	1172.7	1163.0	1096.1	1018.8	919.9	817.1	729.6
42.5°	741.2	847.1	962.2	1069.5	1123.4	1096.9	1018.8	923.9	817.6	720.7	640.7
45°	679.1	788.1	905.9	1009.6	1040.3	992.5	889.2	783.7	679.1	598.2	534.9
47.5°	618.8	726.5	843.2	934.4	945.2	880.8	767.9	659.4	569.5	503.6	458.9
50°	574.5	682.6	798.1	879.5	876.0	798.1	682.2	578.9	503.7	450.5	420.6
52.5°	534.8	636.9	747.9	821.8	803.2	718.3	607.6	515.9	454.1	412.5	385.5
55°	472.9	567.4	672.9	732.3	697.9	603.9	510.3	436.4	390.7	359.6	338.5
57.5°	411.6	500.2	590.5	627.1	589.2	502.3	424.2	370.7	336.3	313.2	299.5
60°	373.6	451.0	531.4	563.0	517.7	440.4	378.8	331.0	303.2	284.4	272.1
62.5°	335.6	404.9	480.8	498.0	456.6	391.2	336.7	296.9	274.1	257.3	245.7
65°	284.0	340.6	398.2	409.7	371.4	320.9	277.8	251.8	231.6	219.3	210.1
67.5°	232.9	278.4	319.2	328.4	294.9	259.8	228.8	206.1	192.4	182.2	174.4
70°	202.6	238.7	272.1	279.6	252.7	221.5	197.8	179.8	167.5	158.7	151.2
72.5°	170.7	200.7	228.4	233.5	211.5	187.8	168.2	154.1	143.2	137.6	130.4
75°	130.5	148.1	169.6	171.0	156.4	142.0	127.0	117.8	112.1	105.0	101.5
77.5°	92.1	105.9	118.2	120.6	112.0	102.1	93.8	86.5	81.6	78.4	75.2
80°	70.3	81.3	86.6	89.6	83.5	76.5	71.6	66.8	63.7	61.6	59.3
82.5°	50.3	57.1	62.0	64.3	61.0	56.8	51.9	49.2	46.8	45.0	44.3
85°	25.5	28.6	31.7	32.5	31.7	29.9	27.2	27.2	25.9	25.5	25.5
87.5°	9.4	11.3	11.7	13.3	13.2	14.0	14.9	15.4	15.8	15.4	15.0
90°	3.2	5.4	7.7	10.0	13.3	17.5	21.7	25.8	30.0	29.7	29.3
92.5°	17.0	18.7	20.3	22.0	23.3	24.4	25.3	26.3	27.3	27.4	27.5
95°	46.6	48.5	50.4	52.3	53.5	53.8	54.2	54.6	55.0	55.0	55.0
97.5°	83.3	85.0	86.7	88.3	89.5	90.3	91.0	91.7	92.5	92.5	92.5
100°	110.6	112.2	113.7	115.2	116.3	116.8	117.4	118.0	118.6	118.6	118.6
102.5°	139.2	140.4	141.6	142.8	143.9	144.6	145.3	146.0	146.8	146.9	147.1
105°	185.3	185.9	186.5	187.0	187.5	187.9	188.3	188.6	189.0	189.4	189.8
107.5°	232.6	233.5	234.4	235.2	235.6	235.6	235.6	235.6	235.6	235.7	235.9
110°	263.2	264.3	265.5	266.7	267.3	267.3	267.3	267.3	267.3	267.3	267.3



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	296.2	297.4	298.5	299.6	300.1	300.0	299.8	299.7	299.5	299.1	298.6
115°	344.8	345.9	347.2	348.3	348.6	348.3	347.9	347.5	347.2	347.0	346.7
117.5°	393.6	395.2	396.7	398.3	398.5	397.4	396.3	395.3	394.3	393.7	393.3
120°	426.0	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5	424.5	424.5
122.5°	455.8	457.7	459.5	461.3	461.8	460.6	459.6	458.6	457.4	457.0	456.5
125°	501.8	503.5	505.2	507.0	507.6	507.0	506.4	505.8	505.2	504.6	504.1
127.5°	547.1	549.3	551.5	553.6	554.4	553.7	553.0	552.3	551.6	551.0	550.3
130°	575.6	578.1	580.6	583.1	584.1	583.7	583.3	583.0	582.6	582.2	581.8
132.5°	606.7	608.8	610.8	612.9	613.9	614.0	614.1	614.1	614.2	613.4	612.5
135°	649.1	651.2	653.3	655.4	656.7	657.0	657.4	657.8	658.1	658.0	657.8
137.5°	693.2	694.9	696.6	698.4	699.5	700.0	700.5	701.0	701.5	701.4	701.2
140°	720.1	721.8	723.5	725.2	726.5	727.5	728.4	729.4	730.4	730.4	730.4
142.5°	747.5	749.2	751.0	752.7	753.9	754.5	755.2	755.8	756.5	756.6	756.8
145°	786.7	788.0	789.4	790.7	791.9	793.1	794.2	795.4	796.5	796.7	796.9
147.5°	822.2	823.8	825.4	827.0	828.2	829.0	829.7	830.4	831.2	831.6	832.1
150°	845.8	846.9	848.1	849.2	850.2	850.9	851.7	852.5	853.3	853.8	854.4
152.5°	867.1	868.2	869.4	870.6	871.6	872.5	873.4	874.3	875.2	876.0	876.7
155°	898.5	899.1	899.7	900.2	900.8	901.4	901.9	902.5	903.0	904.0	905.0
157.5°	925.6	926.0	926.3	926.8	927.1	927.5	927.8	928.2	928.5	929.8	931.1
160°	942.1	942.5	942.9	943.2	943.6	943.7	943.9	944.1	944.3	945.5	946.6
162.5°	956.9	957.0	957.1	957.2	957.3	957.5	957.7	957.9	958.0	959.3	960.6
165°	976.8	976.5	976.4	976.2	976.1	976.1	976.1	976.1	976.1	977.4	978.8
167.5°	993.2	992.6	992.0	991.5	991.2	991.2	991.1	991.1	991.0	992.4	993.7
170°	1002.1	1001.6	1001.0	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7	1001.9
172.5°	1008.3	1007.8	1007.2	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9	1008.1
175°	1015.9	1015.3	1014.8	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5	1014.9
177.5°	1019.1	1018.6	1018.2	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0	1018.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1186.2	1191.1	1191.1	1191.8	1197.5	1196.7	1196.4
5°	1262.3	1269.8	1270.7	1278.6	1283.8	1282.1	1277.3
7.5°	1334.1	1348.1	1358.6	1364.4	1371.4	1375.7	1373.8
10°	1391.1	1411.4	1423.7	1432.0	1442.1	1449.6	1446.9
12.5°	1442.8	1466.9	1483.8	1498.1	1499.4	1509.0	1502.4
15°	1523.4	1548.9	1551.5	1562.1	1570.5	1569.5	1569.9
17.5°	1550.1	1558.2	1559.9	1560.1	1560.2	1557.1	1550.5
20°	1540.5	1537.5	1530.0	1524.3	1514.2	1512.9	1504.1
22.5°	1495.6	1485.7	1467.1	1454.7	1438.9	1434.8	1432.4
25°	1407.0	1385.3	1355.5	1326.9	1319.1	1303.6	1308.0
27.5°	1285.4	1251.8	1219.4	1196.2	1175.2	1152.2	1158.7
30°	1199.9	1162.1	1116.4	1081.2	1058.9	1036.8	1032.9
32.5°	1097.9	1042.6	991.5	960.6	926.3	912.4	897.2
35°	922.1	868.1	817.5	774.0	749.0	729.6	712.0
37.5°	764.0	701.7	661.0	625.7	607.6	596.5	599.3
40°	665.9	611.4	581.5	554.7	538.0	530.0	531.8
42.5°	586.4	545.6	521.0	502.7	490.9	486.5	485.4
45°	496.2	473.4	453.1	442.6	436.9	432.0	429.0
47.5°	434.7	416.0	404.7	398.4	393.4	388.5	388.4
50°	397.8	385.5	377.5	370.9	367.0	363.5	366.5
52.5°	369.6	358.3	350.5	344.6	343.1	339.9	339.8
55°	327.9	319.1	313.4	308.1	305.5	303.7	301.5
57.5°	289.9	281.5	276.3	272.9	267.9	266.1	265.4
60°	262.9	256.2	251.0	246.6	244.4	240.8	240.8
62.5°	237.9	231.3	226.4	223.0	219.4	218.0	218.3
65°	201.7	196.5	191.7	188.1	187.3	184.6	185.5
67.5°	168.5	165.0	159.9	158.0	156.3	154.9	153.9
70°	146.4	142.8	140.2	137.6	136.2	136.2	136.2
72.5°	127.7	123.5	121.9	118.6	119.3	118.0	116.6
75°	98.9	96.3	95.0	93.6	91.4	91.4	91.4
77.5°	72.8	72.0	70.4	69.0	68.4	68.0	68.2
80°	56.2	55.8	54.9	54.9	54.1	53.6	52.8
82.5°	43.2	42.1	41.6	41.2	41.1	41.0	40.8
85°	24.6	23.8	23.8	24.2	23.3	23.3	23.8
87.5°	15.2	15.2	14.8	14.9	15.2	15.0	15.0
90°	28.9	28.6	28.4	28.7	28.8	29.0	29.2
92.5°	27.6	27.6	27.7	27.7	27.7	27.8	27.8
95°	55.0	55.0	54.8	54.4	54.1	53.6	53.3
97.5°	92.5	92.5	92.5	92.4	92.4	92.3	92.3
100°	118.6	118.6	118.5	118.3	118.1	117.9	117.7
102.5°	147.2	147.4	147.3	147.1	147.0	146.8	146.6
105°	190.2	190.5	190.7	190.7	190.7	190.7	190.7
107.5°	236.1	236.2	235.8	235.0	234.1	233.2	232.3
110°	267.3	267.3	266.9	266.4	265.8	265.2	264.7



TEST NUMBER: P331358-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	298.2	297.7	297.2	296.9	296.4	296.0	295.6
115°	346.6	346.4	345.9	345.4	344.8	344.2	343.7
117.5°	392.9	392.4	391.8	391.3	390.7	390.1	389.6
120°	424.5	424.5	424.2	423.6	423.0	422.5	421.9
122.5°	456.1	455.6	455.2	454.8	454.3	453.9	453.5
125°	503.5	502.9	502.6	502.4	502.1	502.0	501.8
127.5°	549.6	548.9	548.2	547.6	547.0	546.4	545.8
130°	581.4	581.0	580.5	579.7	578.9	578.2	577.4
132.5°	611.7	610.8	610.1	609.5	608.9	608.3	607.7
135°	657.6	657.4	657.0	656.4	655.9	655.3	654.7
137.5°	701.0	700.9	700.4	699.6	698.9	698.1	697.3
140°	730.4	730.4	730.0	729.2	728.4	727.7	726.9
142.5°	756.9	757.1	756.8	756.0	755.3	754.5	753.7
145°	797.1	797.3	797.0	796.3	795.5	794.7	793.9
147.5°	832.5	832.9	832.8	832.1	831.3	830.6	829.8
150°	855.0	855.5	855.5	855.0	854.4	853.8	853.3
152.5°	877.4	878.1	878.1	877.4	876.7	876.0	875.2
155°	905.9	906.9	907.1	906.5	905.9	905.3	904.7
157.5°	932.4	933.7	933.8	933.0	932.0	931.1	930.2
160°	947.7	948.9	949.1	948.3	947.5	946.8	946.0
162.5°	961.9	963.2	963.5	962.5	961.6	960.7	959.8
165°	980.1	981.5	981.6	980.7	979.7	978.8	977.8
167.5°	995.1	996.3	996.5	995.6	994.5	993.6	992.6
170°	1003.3	1004.6	1004.7	1003.6	1002.5	1001.3	1000.1
172.5°	1009.5	1010.8	1010.9	1009.8	1008.7	1007.5	1006.3
175°	1016.2	1017.5	1017.6	1016.5	1015.3	1014.2	1013.1
177.5°	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2

(END OF REPORT)