

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331364-935

Luminaire Tested: **SA2XXDIP-C675D925U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331364-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D925U935-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5176.8 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331364-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331364-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	45	44	43	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14759	14759	14759
5°	14815	14603	14687
10°	14728	14454	14526
15°	14544	14265	14252
20°	14287	13984	13969
25°	14031	13639	13639
30°	13699	13323	13207
35°	13391	12942	12751
40°	13004	12560	12319
45°	12622	12184	11880
50°	12208	11788	11369
55°	11778	11333	10911
60°	11296	10785	10388
65°	10777	10243	9773
70°	10126	9583	9130
75°	9214	8827	8609
80°	8173	7922	7513
85°	6688	6354	5687



TEST NUMBER: P331364-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.0	1.7
10°-20°	241.9	4.7
20°-30°	355.5	6.9
30°-40°	412.9	8.0
40°-50°	412.5	8.0
50°-60°	359.7	6.9
60°-70°	266.0	5.1
70°-80°	150.6	2.9
80°-90°	44.6	0.9
90°-100°	64.5	1.2
100°-110°	200.4	3.9
110°-120°	342.5	6.6
120°-130°	450.4	8.7
130°-140°	505.6	9.8
140°-150°	495.7	9.6
150°-160°	415.8	8.0
160°-170°	275.8	5.3
170°-180°	96.4	1.9
0°-30°	683.3	13.2
0°-40°	1096.3	21.2
0°-60°	1868.5	36.1
0°-90°	2329.7	45.0
90°-120°	607.4	11.7
90°-150°	2059.1	39.8
90°-180°	2847.0	55.0
0°-180°	5176.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	914	910	901	907	906	87
15°	870	865	853	857	853	245
25°	788	780	766	767	766	362
35°	679	670	657	651	647	424
45°	553	546	534	524	520	426
55°	418	413	403	392	388	374
65°	282	277	268	260	256	279
75°	148	146	142	137	138	158
85°	36	35	34	32	31	41
90°	1	12	30	28	29	4
95°	45	53	55	55	53	51
105°	185	187	189	191	191	195
115°	344	348	347	346	344	340
125°	500	507	505	503	502	447
135°	647	656	658	657	655	500
145°	785	791	796	797	794	490
155°	898	900	903	907	905	413
165°	977	976	976	982	978	275
175°	1016	1014	1012	1018	1013	97
180°	1018	1018	1018	1018	1018	



TEST NUMBER: P331364-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	918.3	917.6	916.8	916.0	915.2	914.0	912.2	910.5	908.8	907.1	908.6
5°	914.1	913.3	912.6	911.8	911.0	909.6	907.4	905.3	903.1	901.0	902.5
7.5°	906.0	904.8	903.6	902.4	901.2	899.5	897.3	895.1	892.9	890.7	892.3
10°	898.3	896.9	895.5	894.1	892.9	891.0	888.6	886.3	883.9	881.6	883.1
12.5°	887.8	886.6	885.3	884.1	882.9	881.1	878.7	876.4	874.1	871.8	872.9
15°	870.1	869.0	867.8	866.7	865.5	863.6	861.1	858.5	856.0	853.4	854.3
17.5°	847.7	846.4	845.3	844.1	843.0	841.1	838.5	835.9	833.4	830.8	831.7
20°	831.5	830.3	829.1	827.9	826.8	824.8	822.1	819.4	816.7	813.9	814.5
22.5°	815.3	813.6	812.0	810.4	808.7	806.7	804.1	801.5	798.9	796.3	796.4
25°	787.6	786.0	784.5	782.8	781.3	778.9	775.5	772.2	768.9	765.6	765.9
27.5°	755.9	754.5	753.1	751.7	750.3	748.3	745.6	743.0	740.4	737.8	737.2
30°	734.8	733.2	731.7	730.1	728.6	726.3	723.4	720.5	717.6	714.6	714.0
32.5°	712.3	711.0	709.8	708.5	707.3	705.2	702.1	699.0	695.9	692.8	691.7
35°	679.4	677.5	675.5	673.6	671.6	669.1	666.0	662.8	659.7	656.6	655.4
37.5°	642.3	640.6	638.9	637.1	635.5	633.0	629.9	626.8	623.7	620.5	619.1
40°	617.0	615.4	613.9	612.3	610.8	608.5	605.3	602.2	599.1	595.9	594.2
42.5°	592.5	590.8	589.3	587.7	586.2	583.8	580.7	577.6	574.5	571.4	569.4
45°	552.8	551.5	550.1	548.8	547.4	545.3	542.3	539.4	536.5	533.6	531.4
47.5°	513.5	512.2	510.9	509.6	508.3	506.2	503.1	500.1	497.1	494.0	491.7
50°	486.0	485.1	484.1	483.1	482.2	480.3	477.6	474.8	472.1	469.3	466.7
52.5°	459.3	458.1	456.8	455.5	454.2	452.3	449.7	447.1	444.5	442.0	439.7
55°	418.4	417.2	416.0	414.8	413.7	411.9	409.6	407.3	404.9	402.6	400.2
57.5°	377.2	376.3	375.4	374.4	373.5	371.8	369.2	366.6	364.0	361.4	359.1
60°	349.8	349.0	348.3	347.5	346.7	344.9	342.2	339.5	336.7	334.0	331.8
62.5°	323.1	321.8	320.6	319.3	318.1	316.4	314.4	312.2	310.1	308.0	306.0
65°	282.1	280.9	279.8	278.6	277.4	275.9	274.0	272.0	270.0	268.1	266.3
67.5°	240.5	239.5	238.6	237.6	236.7	235.4	233.6	231.9	230.1	228.3	227.0
70°	214.5	213.7	212.9	212.2	211.4	210.1	208.3	206.6	204.8	203.0	201.6
72.5°	187.8	186.9	186.1	185.4	184.6	183.7	182.5	181.4	180.3	179.1	177.8
75°	147.7	147.2	146.9	146.5	146.1	145.4	144.5	143.4	142.5	141.5	140.3
77.5°	111.8	111.2	110.5	109.8	109.2	108.7	108.2	107.8	107.5	107.0	106.5
80°	87.9	87.7	87.5	87.3	87.1	86.8	86.4	86.0	85.7	85.2	84.6
82.5°	65.4	65.3	65.3	65.3	65.3	65.1	64.8	64.7	64.4	64.1	63.5
85°	36.1	35.8	35.6	35.5	35.2	35.0	34.9	34.7	34.4	34.3	33.7
87.5°	12.8	13.0	13.1	13.3	13.4	13.8	14.3	14.8	15.3	15.8	15.3
90°	0.9	3.2	5.4	7.7	10.0	13.3	17.5	21.7	25.8	30.0	29.7
92.5°	15.3	17.0	18.7	20.3	22.0	23.3	24.4	25.3	26.3	27.3	27.4
95°	44.7	46.6	48.5	50.4	52.3	53.5	53.8	54.2	54.6	55.0	55.0
97.5°	81.6	83.3	85.0	86.7	88.3	89.5	90.3	91.0	91.7	92.5	92.5
100°	109.1	110.6	112.2	113.7	115.2	116.3	116.8	117.4	118.0	118.6	118.6
102.5°	138.0	139.2	140.4	141.6	142.8	143.9	144.6	145.3	146.0	146.8	146.9
105°	184.8	185.3	185.9	186.5	187.0	187.5	187.9	188.3	188.6	189.0	189.4
107.5°	231.8	232.6	233.5	234.4	235.2	235.6	235.6	235.6	235.6	235.6	235.7
110°	262.1	263.2	264.3	265.5	266.7	267.3	267.3	267.3	267.3	267.3	267.3



TEST NUMBER: P331364-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.1	296.2	297.4	298.5	299.6	300.1	300.0	299.8	299.7	299.5	299.1
115°	343.7	344.8	345.9	347.2	348.3	348.6	348.3	347.9	347.5	347.2	347.0
117.5°	392.2	393.6	395.2	396.7	398.3	398.5	397.4	396.3	395.3	394.3	393.7
120°	424.5	426.0	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5	424.5
122.5°	454.0	455.8	457.7	459.5	461.3	461.8	460.6	459.6	458.6	457.4	457.0
125°	500.1	501.8	503.5	505.2	507.0	507.6	507.0	506.4	505.8	505.2	504.6
127.5°	544.9	547.1	549.3	551.5	553.6	554.4	553.7	553.0	552.3	551.6	551.0
130°	573.1	575.6	578.1	580.6	583.1	584.1	583.7	583.3	583.0	582.6	582.2
132.5°	604.8	606.7	608.8	610.8	612.9	613.9	614.0	614.1	614.1	614.2	613.4
135°	647.0	649.1	651.2	653.3	655.4	656.7	657.0	657.4	657.8	658.1	658.0
137.5°	691.6	693.2	694.9	696.6	698.4	699.5	700.0	700.5	701.0	701.5	701.4
140°	718.3	720.1	721.8	723.5	725.2	726.5	727.5	728.4	729.4	730.4	730.4
142.5°	745.8	747.5	749.2	751.0	752.7	753.9	754.5	755.2	755.8	756.5	756.6
145°	785.3	786.7	788.0	789.4	790.7	791.9	793.1	794.2	795.4	796.5	796.7
147.5°	820.5	822.2	823.8	825.4	827.0	828.2	829.0	829.7	830.4	831.2	831.6
150°	844.6	845.8	846.9	848.1	849.2	850.2	850.9	851.7	852.5	853.3	853.8
152.5°	865.9	867.1	868.2	869.4	870.6	871.6	872.5	873.4	874.3	875.2	876.0
155°	897.9	898.5	899.1	899.7	900.2	900.8	901.4	901.9	902.5	903.0	904.0
157.5°	925.2	925.6	926.0	926.3	926.8	927.1	927.5	927.8	928.2	928.5	929.8
160°	941.8	942.1	942.5	942.9	943.2	943.6	943.7	943.9	944.1	944.3	945.5
162.5°	956.8	956.9	957.0	957.1	957.2	957.3	957.5	957.7	957.9	958.0	959.3
165°	977.0	976.8	976.5	976.4	976.2	976.1	976.1	976.1	976.1	976.1	977.4
167.5°	993.8	993.2	992.6	992.0	991.5	991.2	991.2	991.1	991.1	991.0	992.4
170°	1002.7	1002.1	1001.6	1001.0	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7
172.5°	1008.9	1008.3	1007.8	1007.2	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9
175°	1016.5	1015.9	1015.3	1014.8	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5
177.5°	1019.6	1019.1	1018.6	1018.2	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331364-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	910.2	911.8	913.3	914.0	913.6	913.3	913.0	912.7
5°	904.0	905.6	907.1	907.8	907.4	907.0	906.6	906.2
7.5°	893.9	895.4	897.0	897.5	897.1	896.7	896.3	895.9
10°	884.7	886.3	887.9	888.3	887.8	887.2	886.6	886.0
12.5°	873.9	875.0	876.2	876.4	876.0	875.6	875.2	874.8
15°	855.1	855.8	856.6	856.5	855.5	854.5	853.6	852.6
17.5°	832.6	833.4	834.4	834.4	833.4	832.5	831.6	830.6
20°	815.1	815.7	816.2	816.1	815.4	814.6	813.8	813.0
22.5°	796.6	796.7	796.8	796.6	796.2	795.7	795.2	794.8
25°	766.4	766.7	767.2	767.2	766.7	766.4	765.9	765.6
27.5°	736.6	736.1	735.5	734.7	733.7	732.8	731.8	730.9
30°	713.4	712.8	712.2	711.5	710.8	710.0	709.2	708.4
32.5°	690.7	689.7	688.5	687.7	686.9	686.1	685.3	684.5
35°	654.3	653.1	651.9	650.8	649.9	648.8	647.9	646.9
37.5°	617.7	616.2	614.8	613.5	612.6	611.7	610.8	609.8
40°	592.5	590.6	588.9	587.6	586.9	586.1	585.3	584.5
42.5°	567.5	565.6	563.7	562.1	561.0	560.0	558.9	557.8
45°	529.3	527.1	525.0	523.5	522.7	521.9	521.2	520.3
47.5°	489.5	487.2	484.9	483.2	482.1	481.0	479.8	478.7
50°	463.9	461.2	458.4	456.6	455.6	454.6	453.7	452.6
52.5°	437.4	435.1	432.9	431.1	429.8	428.5	427.2	425.9
55°	397.9	395.5	393.2	391.5	390.5	389.6	388.6	387.6
57.5°	356.8	354.5	352.2	350.7	349.9	349.2	348.4	347.7
60°	329.7	327.5	325.4	324.1	323.5	322.9	322.3	321.7
62.5°	304.0	302.0	300.1	298.7	297.9	297.1	296.4	295.7
65°	264.6	262.8	261.1	259.7	258.7	257.7	256.8	255.8
67.5°	225.6	224.3	222.9	221.8	221.0	220.2	219.5	218.7
70°	200.3	199.0	197.6	196.5	195.7	194.9	194.2	193.4
72.5°	176.4	175.0	173.7	172.6	172.0	171.4	170.8	170.1
75°	139.1	138.0	136.8	136.5	136.8	137.2	137.6	138.0
77.5°	105.9	105.3	104.7	104.2	103.6	103.1	102.5	101.9
80°	84.1	83.5	82.9	82.4	82.1	81.6	81.3	80.8
82.5°	62.7	61.9	61.2	60.8	60.7	60.6	60.5	60.4
85°	33.1	32.5	31.9	31.5	31.3	31.2	31.0	30.7
87.5°	14.8	14.2	13.7	13.3	13.3	13.1	13.0	12.9
90°	29.3	28.9	28.6	28.4	28.7	28.8	29.0	29.2
92.5°	27.5	27.6	27.6	27.7	27.7	27.7	27.8	27.8
95°	55.0	55.0	55.0	54.8	54.4	54.1	53.6	53.3
97.5°	92.5	92.5	92.5	92.5	92.4	92.4	92.3	92.3
100°	118.6	118.6	118.6	118.5	118.3	118.1	117.9	117.7
102.5°	147.1	147.2	147.4	147.3	147.1	147.0	146.8	146.6
105°	189.8	190.2	190.5	190.7	190.7	190.7	190.7	190.7
107.5°	235.9	236.1	236.2	235.8	235.0	234.1	233.2	232.3
110°	267.3	267.3	267.3	266.9	266.4	265.8	265.2	264.7





TEST NUMBER: P331364-935

CATALOG NUMBER: SA2XXDIP-C675D925U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	298.6	298.2	297.7	297.2	296.9	296.4	296.0	295.6
115°	346.7	346.6	346.4	345.9	345.4	344.8	344.2	343.7
117.5°	393.3	392.9	392.4	391.8	391.3	390.7	390.1	389.6
120°	424.5	424.5	424.5	424.2	423.6	423.0	422.5	421.9
122.5°	456.5	456.1	455.6	455.2	454.8	454.3	453.9	453.5
125°	504.1	503.5	502.9	502.6	502.4	502.1	502.0	501.8
127.5°	550.3	549.6	548.9	548.2	547.6	547.0	546.4	545.8
130°	581.8	581.4	581.0	580.5	579.7	578.9	578.2	577.4
132.5°	612.5	611.7	610.8	610.1	609.5	608.9	608.3	607.7
135°	657.8	657.6	657.4	657.0	656.4	655.9	655.3	654.7
137.5°	701.2	701.0	700.9	700.4	699.6	698.9	698.1	697.3
140°	730.4	730.4	730.4	730.0	729.2	728.4	727.7	726.9
142.5°	756.8	756.9	757.1	756.8	756.0	755.3	754.5	753.7
145°	796.9	797.1	797.3	797.0	796.3	795.5	794.7	793.9
147.5°	832.1	832.5	832.9	832.8	832.1	831.3	830.6	829.8
150°	854.4	855.0	855.5	855.5	855.0	854.4	853.8	853.3
152.5°	876.7	877.4	878.1	878.1	877.4	876.7	876.0	875.2
155°	905.0	905.9	906.9	907.1	906.5	905.9	905.3	904.7
157.5°	931.1	932.4	933.7	933.8	933.0	932.0	931.1	930.2
160°	946.6	947.7	948.9	949.1	948.3	947.5	946.8	946.0
162.5°	960.6	961.9	963.2	963.5	962.5	961.6	960.7	959.8
165°	978.8	980.1	981.5	981.6	980.7	979.7	978.8	977.8
167.5°	993.7	995.1	996.3	996.5	995.6	994.5	993.6	992.6
170°	1001.9	1003.3	1004.6	1004.7	1003.6	1002.5	1001.3	1000.1
172.5°	1008.1	1009.5	1010.8	1010.9	1009.8	1008.7	1007.5	1006.3
175°	1014.9	1016.2	1017.5	1017.6	1016.5	1015.3	1014.2	1013.1
177.5°	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2

(END OF REPORT)