

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331411-935

Luminaire Tested: **SA2XXDIP-C865D1080U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331411-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6989.6 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331411-935  
CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				40	
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39				35	
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34				30	
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30				26	
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26				23	
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23				20	
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21				18	
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				16	
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17				15	
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16				14	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	24001	24001	24001	24001
5°	26909	24159	21409	24159
10°	30836	23961	18528	23961
15°	34111	23520	16368	23520
20°	33593	23048	14921	23048
25°	30289	22422	14004	22422
30°	25031	21420	13336	21420
35°	18242	20371	12861	20371
40°	14570	19134	12596	19134
45°	12732	17701	12237	17701
50°	11969	16317	11997	16317
55°	11032	14908	11674	14908
60°	10111	13411	11179	13411
65°	9211	12069	10693	12069
70°	8360	10763	9980	10763
75°	7411	9301	8840	9301
80°	6369	7699	7113	7699
85°	5706	5706	4224	5706



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.6	2.0
10°-20°	411.6	5.9
20°-30°	597.3	8.5
30°-40°	630.3	9.0
40°-50°	558.1	8.0
50°-60°	445.4	6.4
60°-70°	302.7	4.3
70°-80°	155.2	2.2
80°-90°	40.5	0.6
90°-100°	42.2	0.6
100°-110°	154.7	2.2
110°-120°	413.6	5.9
120°-130°	682.8	9.8
130°-140°	726.1	10.4
140°-150°	674.9	9.7
150°-160°	542.6	7.8
160°-170°	349.7	5.0
170°-180°	120.4	1.7
0°-30°	1150.5	16.5
0°-40°	1780.8	25.5
0°-60°	2784.3	39.8
0°-90°	3282.7	47.0
90°-120°	610.5	8.7
90°-150°	2694.3	38.5
90°-180°	3707.0	53.0
0°-180°	6989.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1486	1486	1486	1486	1486	
5°	1660	1491	1321	1491	1660	166
15°	2041	1407	979	1407	2041	563
25°	1700	1259	786	1259	1700	768
35°	926	1034	652	1034	926	602
45°	558	775	536	775	558	438
55°	392	530	415	530	392	351
65°	241	316	280	316	241	240
75°	119	149	142	149	119	127
85°	31	31	23	31	31	34
90°	25	1	25	1	25	12
95°	39	60	39	60	39	37
105°	70	278	70	278	70	72
115°	75	526	75	526	75	188
125°	783	744	783	744	783	677
135°	951	921	951	921	951	733
145°	1085	1068	1085	1068	1085	678
155°	1177	1176	1177	1176	1177	543
165°	1237	1239	1237	1239	1237	349
175°	1260	1268	1260	1268	1260	120
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1555.1	1555.6	1556.5	1549.2	1548.3	1548.3	1541.9	1536.4	1530.0	1521.3	1522.2
5°	1660.3	1666.6	1668.8	1662.0	1651.7	1650.5	1640.8	1624.8	1610.0	1597.9	1589.4
7.5°	1785.7	1788.2	1782.6	1773.6	1765.9	1752.2	1734.1	1716.5	1691.7	1669.0	1652.0
10°	1880.8	1884.2	1874.5	1861.3	1850.5	1834.4	1808.2	1781.3	1748.8	1717.4	1692.2
12.5°	1953.0	1961.4	1949.0	1947.2	1928.6	1906.7	1875.4	1861.8	1816.0	1772.2	1745.2
15°	2040.7	2040.1	2041.3	2030.4	2016.7	2013.3	1980.2	1944.2	1879.6	1853.9	1809.4
17.5°	2015.3	2024.0	2028.1	2027.9	2027.6	2025.4	2014.8	1992.1	1959.7	1918.0	1866.6
20°	1955.1	1966.4	1968.2	1981.3	1988.7	1998.5	2002.4	1996.1	1976.2	1941.3	1896.8
22.5°	1861.8	1865.0	1870.4	1890.8	1906.9	1931.3	1944.0	1965.1	1957.4	1940.4	1903.2
25°	1700.2	1694.5	1714.5	1724.8	1762.0	1800.8	1828.8	1859.6	1887.1	1903.6	1892.7
27.5°	1506.2	1497.6	1527.6	1554.9	1585.0	1627.1	1670.8	1722.3	1765.1	1818.7	1837.1
30°	1342.6	1347.7	1376.3	1405.4	1451.1	1510.5	1559.7	1616.3	1677.4	1737.3	1779.1
32.5°	1166.1	1185.9	1204.0	1248.6	1288.9	1355.1	1427.1	1497.9	1574.1	1642.3	1706.8
35°	925.5	948.4	973.5	1006.1	1062.6	1128.3	1198.6	1294.0	1398.0	1491.2	1567.7
37.5°	779.0	775.4	789.8	813.3	859.1	912.1	993.1	1087.4	1209.7	1319.1	1427.1
40°	691.3	689.0	699.3	721.0	755.9	794.7	865.6	948.4	1062.0	1195.8	1324.3
42.5°	630.9	632.3	638.0	653.3	677.3	709.2	762.2	832.8	936.9	1062.7	1200.9
45°	557.6	561.6	567.9	575.3	589.0	615.3	645.0	695.3	777.6	882.7	1018.6
47.5°	504.8	504.9	511.3	517.8	526.0	540.8	565.0	596.6	654.6	740.2	857.1
50°	476.5	472.5	477.1	482.2	490.8	501.0	517.0	546.7	585.6	654.7	752.4
52.5°	441.8	441.9	446.0	447.9	455.6	465.9	480.4	501.0	536.2	590.3	670.6
55°	391.9	394.8	397.1	400.5	407.3	414.7	426.2	439.9	467.4	507.9	567.3
57.5°	345.1	345.9	348.3	354.8	359.1	366.0	376.9	389.3	407.1	437.1	481.8
60°	313.1	313.1	317.6	320.5	326.2	333.0	341.6	353.6	369.6	394.2	430.2
62.5°	283.9	283.4	285.2	289.9	294.2	300.7	309.2	319.3	334.4	356.3	385.9
65°	241.1	240.0	243.4	244.5	249.1	255.4	262.3	273.1	285.1	301.1	327.4
67.5°	199.9	201.3	203.2	205.3	207.8	214.5	219.0	226.7	236.9	250.1	267.9
70°	177.1	177.1	177.1	178.8	182.3	185.7	190.3	196.6	206.2	217.7	233.7
72.5°	151.5	153.3	155.2	154.1	158.5	160.6	166.0	169.5	178.8	186.1	200.3
75°	118.8	118.8	118.8	121.7	123.4	125.1	128.5	132.0	136.6	145.7	153.1
77.5°	88.7	88.4	89.0	89.7	91.5	93.6	94.6	97.7	101.9	106.2	112.4
80°	68.5	69.7	70.3	71.4	71.4	72.6	73.1	77.1	80.0	82.8	86.9
82.5°	53.0	53.2	53.4	53.6	54.1	54.8	56.2	57.5	58.5	60.9	64.0
85°	30.8	30.3	30.3	31.4	30.8	30.8	32.0	33.1	33.1	33.7	35.4
87.5°	16.8	16.7	17.1	16.6	16.5	16.8	16.6	15.9	16.2	16.4	16.6
90°	24.7	24.3	23.9	23.5	23.1	22.4	21.4	20.3	19.3	18.3	16.7
92.5°	24.7	24.5	24.2	24.0	23.8	23.3	22.8	22.3	21.8	21.3	20.4
95°	39.3	39.5	39.8	40.0	40.2	39.8	38.7	37.7	36.7	35.7	34.3
97.5°	52.5	52.3	52.1	51.8	51.6	51.1	50.2	49.4	48.6	47.8	44.5
100°	61.3	61.0	60.5	60.1	59.7	58.7	57.1	55.4	53.8	52.2	48.7
102.5°	65.7	65.2	64.6	64.0	63.5	62.1	60.0	57.9	55.8	53.6	48.6
105°	69.6	68.7	67.9	67.2	66.3	64.7	62.5	60.3	58.0	55.8	48.7
107.5°	71.5	70.8	69.9	69.1	68.4	69.1	71.3	73.6	75.9	78.2	144.7
110°	72.3	71.5	70.7	69.8	69.1	78.8	99.2	119.5	139.8	160.1	219.0



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	73.0	72.4	71.7	71.1	70.4	107.2	181.4	255.6	329.8	404.0	418.5
115°	75.1	89.7	104.4	119.0	133.6	188.0	282.2	376.3	470.5	564.7	559.6
117.5°	306.4	354.6	402.7	450.8	498.9	534.4	557.2	580.0	602.7	625.5	622.0
120°	558.4	585.7	613.2	640.7	668.1	680.7	678.2	675.8	673.3	670.9	667.3
122.5°	696.7	702.1	707.4	712.7	718.0	720.0	718.5	717.0	715.6	714.1	710.2
125°	782.6	782.0	781.4	780.8	780.2	779.1	777.7	776.3	774.8	773.4	769.6
127.5°	836.7	836.6	836.5	836.4	836.3	835.2	833.1	831.0	829.0	826.9	824.0
130°	870.5	870.6	870.8	871.1	871.2	870.2	868.0	865.7	863.5	861.3	859.0
132.5°	903.4	903.6	903.8	904.0	904.2	903.4	901.5	899.5	897.6	895.7	893.5
135°	951.0	951.4	951.7	952.2	952.6	951.7	949.8	947.7	945.7	943.7	941.8
137.5°	994.4	995.1	995.7	996.4	997.1	996.4	994.5	992.5	990.5	988.5	986.4
140°	1021.5	1022.4	1023.5	1024.5	1025.5	1025.1	1023.3	1021.5	1019.6	1017.8	1015.5
142.5°	1047.8	1048.9	1049.8	1050.9	1051.9	1051.5	1049.9	1048.2	1046.5	1044.9	1042.3
145°	1084.6	1085.6	1086.7	1087.7	1088.6	1088.5	1087.0	1085.6	1084.2	1082.8	1079.3
147.5°	1117.0	1117.8	1118.7	1119.6	1120.4	1120.3	1119.3	1118.2	1117.1	1116.1	1112.7
150°	1136.8	1137.8	1138.8	1139.8	1140.8	1140.7	1139.5	1138.3	1137.1	1135.8	1132.6
152.5°	1153.7	1154.9	1156.3	1157.6	1159.0	1159.1	1157.9	1156.6	1155.4	1154.2	1151.1
155°	1177.1	1178.7	1180.3	1181.9	1183.5	1183.8	1182.6	1181.3	1180.1	1178.9	1176.5
157.5°	1198.4	1200.1	1201.6	1203.2	1204.8	1204.9	1203.5	1202.1	1200.8	1199.4	1197.7
160°	1210.9	1212.4	1213.8	1215.2	1216.6	1216.7	1215.5	1214.3	1213.1	1211.9	1210.7
162.5°	1221.2	1222.9	1224.7	1226.4	1228.1	1228.4	1226.9	1225.5	1224.2	1222.8	1221.8
165°	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6	1236.0
167.5°	1246.2	1248.1	1249.9	1251.7	1253.5	1253.8	1252.3	1250.9	1249.5	1248.1	1247.5
170°	1252.1	1254.0	1255.8	1257.6	1259.4	1259.6	1258.2	1256.8	1255.3	1254.0	1253.5
172.5°	1256.5	1258.4	1260.2	1262.0	1263.9	1264.0	1262.6	1261.2	1259.7	1258.4	1257.9
175°	1260.3	1262.4	1264.4	1266.4	1268.5	1268.8	1267.4	1265.9	1264.6	1263.1	1262.7
177.5°	1262.7	1264.2	1265.7	1267.1	1268.6	1268.8	1267.6	1266.4	1265.3	1264.2	1264.0
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1525.4	1521.7	1519.5	1511.2	1503.9	1496.6	1494.4	1495.2	1485.2	1475.6	1471.4
5°	1584.8	1573.4	1562.5	1547.1	1528.9	1508.8	1498.6	1490.6	1470.6	1448.9	1436.3
7.5°	1638.1	1621.7	1600.9	1571.8	1545.2	1513.7	1493.7	1476.0	1446.8	1416.2	1397.4
10°	1670.5	1648.2	1621.3	1586.0	1553.4	1515.1	1488.2	1461.5	1427.1	1390.6	1367.7
12.5°	1698.4	1668.4	1641.9	1596.5	1558.0	1510.1	1478.3	1440.4	1404.3	1360.9	1338.5
15°	1764.8	1709.3	1659.1	1607.7	1560.2	1493.4	1458.0	1407.1	1359.7	1306.1	1280.3
17.5°	1816.1	1753.9	1674.6	1609.3	1553.9	1480.0	1428.0	1367.0	1311.0	1249.6	1214.6
20°	1845.4	1773.9	1688.8	1611.1	1544.8	1460.3	1403.7	1341.4	1275.7	1206.6	1168.9
22.5°	1862.7	1787.6	1703.4	1604.2	1526.6	1444.2	1373.1	1304.8	1238.3	1163.6	1124.1
25°	1868.2	1799.7	1710.5	1598.5	1503.7	1410.6	1324.9	1258.6	1178.0	1108.4	1050.7
27.5°	1841.0	1791.8	1706.2	1587.8	1477.3	1368.4	1272.9	1197.8	1112.8	1037.2	979.1
30°	1807.7	1779.1	1695.7	1576.8	1456.3	1339.2	1234.1	1148.9	1064.4	987.8	928.4
32.5°	1756.0	1749.8	1676.5	1561.3	1433.9	1302.2	1193.3	1107.3	1013.7	938.4	881.8
35°	1654.5	1682.0	1635.6	1526.6	1391.7	1249.5	1131.8	1033.5	936.4	864.4	811.2
37.5°	1518.5	1586.7	1574.5	1475.7	1334.8	1192.1	1062.2	959.5	866.9	794.3	742.1
40°	1424.9	1511.7	1524.2	1436.8	1294.6	1147.8	1010.1	907.8	817.5	751.3	698.7
42.5°	1324.3	1425.7	1460.3	1390.3	1250.7	1101.1	963.5	857.6	768.2	703.8	657.1
45°	1155.8	1290.0	1352.3	1312.3	1177.5	1024.3	882.7	775.2	694.1	633.6	597.6
47.5°	998.2	1144.9	1228.6	1214.5	1096.0	944.3	804.3	701.2	622.2	573.9	541.7
50°	886.7	1037.5	1138.6	1143.2	1037.5	887.3	746.7	649.6	577.0	531.9	505.6
52.5°	789.8	933.8	1044.0	1068.2	972.2	827.9	695.1	598.4	534.5	493.0	469.5
55°	663.3	785.0	907.2	951.8	874.7	737.5	614.8	529.6	469.6	441.1	420.5
57.5°	551.5	652.9	765.8	815.0	767.5	650.1	534.9	461.1	412.3	387.4	371.6
60°	492.5	572.5	673.0	731.8	690.7	586.2	485.6	415.3	375.4	353.1	338.2
62.5°	437.6	508.5	593.5	647.3	624.9	526.3	436.3	374.2	339.7	318.8	308.1
65°	361.1	417.1	482.8	532.4	517.6	442.7	369.1	315.9	288.5	271.9	263.4
67.5°	297.3	337.8	383.3	426.9	414.9	361.9	302.6	261.3	240.9	226.6	221.4
70°	257.1	287.9	328.5	363.3	353.6	310.2	263.4	228.0	210.3	198.3	193.1
72.5°	218.7	244.1	275.0	303.5	297.0	260.9	221.8	195.0	181.4	170.4	166.2
75°	165.1	184.5	203.4	222.2	220.5	192.5	169.7	149.1	138.3	129.7	127.9
77.5°	121.9	132.8	145.6	156.8	153.7	137.7	119.8	108.0	100.0	94.3	93.3
80°	93.2	99.4	108.6	116.6	112.5	105.7	91.4	82.8	77.1	71.4	69.1
82.5°	67.5	73.8	79.3	83.6	80.6	74.1	65.3	59.5	56.1	52.2	51.3
85°	35.4	38.8	41.2	42.3	41.2	37.1	33.1	30.8	28.0	26.3	25.7
87.5°	16.7	16.4	16.1	16.6	14.8	14.3	12.1	10.2	10.2	10.2	9.7
90°	15.1	13.4	11.8	9.9	7.7	5.4	3.2	0.9	3.2	5.4	7.7
92.5°	19.6	18.8	18.0	17.7	17.9	18.1	18.3	18.5	18.3	18.1	17.9
95°	32.9	31.4	30.0	32.6	39.3	46.1	52.8	59.5	52.8	46.1	39.3
97.5°	41.2	37.9	34.6	42.4	61.3	80.2	99.2	118.0	99.2	80.2	61.3
100°	45.3	41.8	38.3	50.5	78.4	106.2	134.1	162.0	134.1	106.2	78.4
102.5°	111.5	140.4	169.4	186.8	192.6	198.5	204.4	210.3	204.4	198.5	192.6
105°	166.9	222.4	277.9	302.6	296.5	290.4	284.4	278.3	284.4	290.4	296.5
107.5°	211.4	277.9	344.6	375.4	370.4	365.5	360.6	355.7	360.6	365.5	370.4
110°	277.8	336.5	395.3	422.6	418.3	414.1	409.7	405.4	409.7	414.1	418.3





TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	433.1	447.5	462.1	467.4	463.6	459.9	456.2	452.4	456.2	459.9	463.6
115°	554.6	549.5	544.4	540.1	536.7	533.2	529.8	526.3	529.8	533.2	536.7
117.5°	618.5	615.0	611.5	607.9	604.0	600.1	596.2	592.4	596.2	600.1	604.0
120°	663.6	660.0	656.3	652.9	649.9	646.8	643.8	640.7	643.8	646.8	649.9
122.5°	706.1	702.1	698.2	694.6	691.4	688.1	684.9	681.7	684.9	688.1	691.4
125°	765.7	761.8	757.9	754.7	752.1	749.4	746.7	744.2	746.7	749.4	752.1
127.5°	821.0	818.2	815.3	812.4	809.5	806.6	803.7	800.7	803.7	806.6	809.5
130°	856.8	854.5	852.3	849.5	846.4	843.1	839.8	836.5	839.8	843.1	846.4
132.5°	891.2	889.0	886.7	884.2	881.5	878.7	876.0	873.1	876.0	878.7	881.5
135°	940.0	938.1	936.3	933.8	930.6	927.3	924.0	920.8	924.0	927.3	930.6
137.5°	984.4	982.3	980.2	978.0	975.8	973.4	971.2	968.9	971.2	973.4	975.8
140°	1013.3	1011.1	1008.8	1006.9	1005.3	1003.7	1002.0	1000.4	1002.0	1003.7	1005.3
142.5°	1039.7	1037.2	1034.7	1032.6	1031.1	1029.7	1028.2	1026.7	1028.2	1029.7	1031.1
145°	1075.8	1072.4	1068.9	1067.3	1067.6	1067.7	1067.9	1068.2	1067.9	1067.7	1067.6
147.5°	1109.2	1105.9	1102.4	1101.1	1101.9	1102.7	1103.5	1104.2	1103.5	1102.7	1101.9
150°	1129.4	1126.1	1122.8	1122.0	1123.3	1124.8	1126.2	1127.7	1126.2	1124.8	1123.3
152.5°	1148.0	1144.9	1141.8	1141.1	1142.6	1144.2	1145.8	1147.4	1145.8	1144.2	1142.6
155°	1174.0	1171.6	1169.2	1168.8	1170.6	1172.5	1174.3	1176.1	1174.3	1172.5	1170.6
157.5°	1195.9	1194.3	1192.6	1192.5	1194.0	1195.6	1197.1	1198.7	1197.1	1195.6	1194.0
160°	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1210.7	1209.4	1208.2
162.5°	1220.7	1219.6	1218.6	1218.7	1219.9	1221.1	1222.4	1223.6	1222.4	1221.1	1219.9
165°	1235.4	1234.7	1234.1	1234.4	1235.6	1236.8	1238.0	1239.3	1238.0	1236.8	1235.6
167.5°	1246.9	1246.4	1245.8	1246.1	1247.3	1248.5	1249.8	1251.0	1249.8	1248.5	1247.3
170°	1253.1	1252.8	1252.3	1252.8	1254.0	1255.2	1256.4	1257.6	1256.4	1255.2	1254.0
172.5°	1257.5	1257.1	1256.7	1257.1	1258.4	1259.6	1260.8	1262.0	1260.8	1259.6	1258.4
175°	1262.3	1261.9	1261.5	1262.0	1263.4	1264.8	1266.3	1267.7	1266.3	1264.8	1263.4
177.5°	1263.9	1263.7	1263.5	1264.0	1265.2	1266.3	1267.5	1268.6	1267.5	1266.3	1265.2
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1466.9	1464.1	1454.6	1449.6	1441.3	1433.6	1428.5	1430.8	1432.6	1431.7	1430.4
5°	1424.9	1414.0	1397.4	1383.1	1372.9	1354.0	1346.0	1342.0	1338.6	1334.6	1330.6
7.5°	1374.8	1357.7	1333.9	1313.5	1294.3	1270.9	1257.6	1249.6	1241.4	1232.3	1224.3
10°	1339.2	1315.2	1290.0	1261.5	1238.6	1217.5	1198.6	1186.0	1174.7	1163.7	1155.8
12.5°	1301.7	1274.0	1242.9	1203.9	1178.7	1148.5	1145.6	1123.4	1105.6	1098.9	1089.5
15°	1242.1	1203.2	1163.7	1117.5	1097.5	1070.1	1052.9	1035.8	1020.4	1009.5	1006.7
17.5°	1174.3	1124.0	1084.8	1051.5	1018.7	990.7	974.9	961.2	948.5	934.0	932.0
20°	1122.7	1079.2	1036.4	1007.2	973.5	944.9	925.5	911.8	901.0	892.4	884.9
22.5°	1073.8	1026.2	987.0	955.1	921.9	898.8	883.5	870.2	861.2	851.7	844.7
25°	995.2	958.1	915.2	879.3	851.8	837.0	824.4	813.0	807.3	801.0	793.0
27.5°	926.5	885.3	845.2	817.3	793.2	780.1	771.2	763.4	758.0	754.3	749.8
30°	878.1	836.4	804.9	777.6	757.6	744.4	738.7	734.2	727.9	725.6	723.3
32.5°	831.5	793.9	767.1	743.3	724.2	715.7	710.4	706.3	701.4	699.0	694.5
35°	765.6	734.2	707.8	694.7	679.3	671.8	667.9	662.2	657.5	655.3	654.7
37.5°	703.5	676.2	658.9	642.0	635.5	630.9	625.5	621.6	620.2	619.8	619.3
40°	663.3	641.0	625.6	611.9	609.0	602.2	597.6	594.2	594.2	594.8	594.2
42.5°	626.7	606.7	593.1	581.3	577.9	573.9	569.3	569.0	570.0	571.9	570.0
45°	571.3	557.1	547.3	541.6	535.3	531.3	530.7	532.4	533.0	533.6	535.3
47.5°	520.4	510.8	502.0	495.8	493.0	492.3	491.6	494.6	497.4	498.4	501.0
50°	490.2	479.3	471.9	467.9	465.6	464.5	465.6	469.1	471.3	474.2	475.9
52.5°	456.3	448.7	443.6	440.5	439.5	440.2	440.5	444.4	448.1	449.0	449.9
55°	409.7	403.9	402.8	397.6	399.9	399.3	402.2	404.5	407.9	411.4	411.9
57.5°	363.0	358.4	355.3	355.9	356.5	359.0	361.4	365.4	369.1	372.7	373.1
60°	331.9	329.7	328.0	328.0	329.1	332.5	335.4	339.3	341.6	344.0	345.6
62.5°	303.6	301.4	299.6	300.5	303.5	305.6	308.8	311.0	313.3	315.6	316.4
65°	258.8	257.7	259.4	260.5	261.1	264.0	267.9	269.7	271.9	273.1	277.1
67.5°	217.6	217.7	217.6	219.1	222.5	223.2	227.0	230.9	231.4	233.6	236.2
70°	189.7	190.8	192.0	193.1	196.0	197.1	199.9	201.6	204.0	205.7	207.4
72.5°	164.1	164.3	165.5	165.2	167.6	170.1	172.5	174.3	176.5	178.7	180.4
75°	126.2	126.2	127.4	127.9	130.9	133.7	133.1	134.2	136.6	138.8	140.0
77.5°	92.2	90.9	92.2	92.8	93.7	96.1	96.5	98.2	100.7	100.0	101.3
80°	70.3	68.5	70.3	70.9	70.9	73.7	73.7	74.8	76.5	74.8	76.5
82.5°	50.2	49.3	50.6	50.7	51.7	51.7	52.7	52.9	54.6	53.8	54.6
85°	25.1	24.5	25.1	24.5	25.1	25.7	25.7	25.1	25.1	26.3	24.5
87.5°	9.7	9.6	9.6	9.9	9.7	9.6	9.4	9.6	9.7	9.0	9.2
90°	9.9	11.8	13.4	15.1	16.7	18.3	19.3	20.3	21.4	22.4	23.1
92.5°	17.7	18.0	18.8	19.6	20.4	21.3	21.8	22.3	22.8	23.3	23.8
95°	32.6	30.0	31.4	32.9	34.3	35.7	36.7	37.7	38.7	39.8	40.2
97.5°	42.4	34.6	37.9	41.2	44.5	47.8	48.6	49.4	50.2	51.1	51.6
100°	50.5	38.3	41.8	45.3	48.7	52.2	53.8	55.4	57.1	58.7	59.7
102.5°	186.8	169.4	140.4	111.5	82.6	53.6	55.8	57.9	60.0	62.1	63.5
105°	302.6	277.9	222.4	166.9	111.3	55.8	58.0	60.3	62.5	64.7	66.3
107.5°	375.4	344.6	277.9	211.4	144.7	78.2	75.9	73.6	71.3	69.1	68.4
110°	422.6	395.3	336.5	277.8	219.0	160.1	139.8	119.5	99.2	78.8	69.1



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	467.4	462.1	447.5	433.1	418.5	404.0	329.8	255.6	181.4	107.2	70.4
115°	540.1	544.4	549.5	554.6	559.6	564.7	470.5	376.3	282.2	188.0	133.6
117.5°	607.9	611.5	615.0	618.5	622.0	625.5	602.7	580.0	557.2	534.4	498.9
120°	652.9	656.3	660.0	663.6	667.3	670.9	673.3	675.8	678.2	680.7	668.1
122.5°	694.6	698.2	702.1	706.1	710.2	714.1	715.6	717.0	718.5	720.0	718.0
125°	754.7	757.9	761.8	765.7	769.6	773.4	774.8	776.3	777.7	779.1	780.2
127.5°	812.4	815.3	818.2	821.0	824.0	826.9	829.0	831.0	833.1	835.2	836.3
130°	849.5	852.3	854.5	856.8	859.0	861.3	863.5	865.7	868.0	870.2	871.2
132.5°	884.2	886.7	889.0	891.2	893.5	895.7	897.6	899.5	901.5	903.4	904.2
135°	933.8	936.3	938.1	940.0	941.8	943.7	945.7	947.7	949.8	951.7	952.6
137.5°	978.0	980.2	982.3	984.4	986.4	988.5	990.5	992.5	994.5	996.4	997.1
140°	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6	1021.5	1023.3	1025.1	1025.5
142.5°	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5	1048.2	1049.9	1051.5	1051.9
145°	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2	1085.6	1087.0	1088.5	1088.6
147.5°	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1	1118.2	1119.3	1120.3	1120.4
150°	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1	1138.3	1139.5	1140.7	1140.8
152.5°	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4	1156.6	1157.9	1159.1	1159.0
155°	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1	1181.3	1182.6	1183.8	1183.5
157.5°	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8	1202.1	1203.5	1204.9	1204.8
160°	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1	1214.3	1215.5	1216.7	1216.6
162.5°	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2	1225.5	1226.9	1228.4	1228.1
165°	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3
167.5°	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5	1250.9	1252.3	1253.8	1253.5
170°	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3	1256.8	1258.2	1259.6	1259.4
172.5°	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7	1261.2	1262.6	1264.0	1263.9
175°	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6	1265.9	1267.4	1268.8	1268.5
177.5°	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3	1266.4	1267.6	1268.8	1268.6
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1425.7	1424.9	1424.9	1420.7	1424.9	1424.9	1425.7	1430.4	1431.7	1432.6	1430.8
5°	1322.6	1320.9	1318.0	1320.9	1318.0	1320.9	1322.6	1330.6	1334.6	1338.6	1342.0
7.5°	1220.6	1213.7	1212.6	1205.9	1212.6	1213.7	1220.6	1224.3	1232.3	1241.4	1249.6
10°	1146.1	1141.5	1140.9	1130.1	1140.9	1141.5	1146.1	1155.8	1163.7	1174.7	1186.0
12.5°	1089.4	1078.4	1080.6	1074.3	1080.6	1078.4	1089.4	1089.5	1098.9	1105.6	1123.4
15°	991.3	991.3	988.9	979.2	988.9	991.3	991.3	1006.7	1009.5	1020.4	1035.8
17.5°	920.8	919.5	914.1	916.9	914.1	919.5	920.8	932.0	934.0	948.5	961.2
20°	878.7	875.3	868.4	868.4	868.4	875.3	878.7	884.9	892.4	901.0	911.8
22.5°	839.0	838.7	831.4	833.6	831.4	838.7	839.0	844.7	851.7	861.2	870.2
25°	792.4	787.8	784.5	786.1	784.5	787.8	792.4	793.0	801.0	807.3	813.0
27.5°	748.3	745.8	745.5	740.9	745.5	745.8	748.3	749.8	754.3	758.0	763.4
30°	722.7	717.0	718.2	715.3	718.2	717.0	722.7	723.3	725.6	727.9	734.2
32.5°	693.4	691.4	690.3	687.9	690.3	691.4	693.4	694.5	699.0	701.4	706.3
35°	653.6	654.2	651.3	652.5	651.3	654.2	653.6	654.7	655.3	657.5	662.2
37.5°	618.7	620.5	619.2	619.6	619.2	620.5	618.7	619.3	619.8	620.2	621.6
40°	595.9	595.9	595.9	597.6	595.9	595.9	595.9	594.2	594.8	594.2	594.2
42.5°	573.9	573.0	572.1	572.0	572.1	573.0	573.9	570.0	571.9	570.0	569.0
45°	536.5	538.2	538.7	535.9	538.7	538.2	536.5	535.3	533.6	533.0	532.4
47.5°	502.6	502.7	502.6	505.1	502.6	502.7	502.6	501.0	498.4	497.4	494.6
50°	478.8	477.6	478.8	477.6	478.8	477.6	478.8	475.9	474.2	471.3	469.1
52.5°	453.7	453.8	453.1	453.0	453.1	453.8	453.7	449.9	449.0	448.1	444.4
55°	414.2	415.3	414.7	414.7	414.7	415.3	414.2	411.9	411.4	407.9	404.5
57.5°	373.4	374.4	375.2	372.7	375.2	374.4	373.4	373.1	372.7	369.1	365.4
60°	345.1	347.9	347.3	346.2	347.3	347.9	345.1	345.6	344.0	341.6	339.3
62.5°	319.0	320.0	319.9	319.7	319.9	320.0	319.0	316.4	315.6	313.3	311.0
65°	278.8	279.9	278.2	279.9	278.2	279.9	278.8	277.1	273.1	271.9	269.7
67.5°	235.5	235.8	237.1	237.9	237.1	235.8	235.5	236.2	233.6	231.4	230.9
70°	208.5	207.9	209.7	211.4	209.7	207.9	208.5	207.4	205.7	204.0	201.6
72.5°	180.2	181.4	180.9	182.1	180.9	181.4	180.2	180.4	178.7	176.5	174.3
75°	138.8	140.5	140.0	141.7	140.0	140.5	138.8	140.0	138.8	136.6	134.2
77.5°	100.3	100.6	100.3	101.3	100.3	100.6	100.3	101.3	100.0	100.7	98.2
80°	76.5	75.4	74.3	76.5	74.3	75.4	76.5	76.5	74.8	76.5	74.8
82.5°	53.2	53.9	52.8	52.8	52.8	53.9	53.2	54.6	53.8	54.6	52.9
85°	24.5	24.0	22.8	22.8	22.8	24.0	24.5	24.5	26.3	25.1	25.1
87.5°	9.3	8.9	9.0	8.6	9.0	8.9	9.3	9.2	9.0	9.7	9.6
90°	23.5	23.9	24.3	24.7	24.3	23.9	23.5	23.1	22.4	21.4	20.3
92.5°	24.0	24.2	24.5	24.7	24.5	24.2	24.0	23.8	23.3	22.8	22.3
95°	40.0	39.8	39.5	39.3	39.5	39.8	40.0	40.2	39.8	38.7	37.7
97.5°	51.8	52.1	52.3	52.5	52.3	52.1	51.8	51.6	51.1	50.2	49.4
100°	60.1	60.5	61.0	61.3	61.0	60.5	60.1	59.7	58.7	57.1	55.4
102.5°	64.0	64.6	65.2	65.7	65.2	64.6	64.0	63.5	62.1	60.0	57.9
105°	67.2	67.9	68.7	69.6	68.7	67.9	67.2	66.3	64.7	62.5	60.3
107.5°	69.1	69.9	70.8	71.5	70.8	69.9	69.1	68.4	69.1	71.3	73.6
110°	69.8	70.7	71.5	72.3	71.5	70.7	69.8	69.1	78.8	99.2	119.5



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	71.1	71.7	72.4	73.0	72.4	71.7	71.1	70.4	107.2	181.4	255.6
115°	119.0	104.4	89.7	75.1	89.7	104.4	119.0	133.6	188.0	282.2	376.3
117.5°	450.8	402.7	354.6	306.4	354.6	402.7	450.8	498.9	534.4	557.2	580.0
120°	640.7	613.2	585.7	558.4	585.7	613.2	640.7	668.1	680.7	678.2	675.8
122.5°	712.7	707.4	702.1	696.7	702.1	707.4	712.7	718.0	720.0	718.5	717.0
125°	780.8	781.4	782.0	782.6	782.0	781.4	780.8	780.2	779.1	777.7	776.3
127.5°	836.4	836.5	836.6	836.7	836.6	836.5	836.4	836.3	835.2	833.1	831.0
130°	871.1	870.8	870.6	870.5	870.6	870.8	871.1	871.2	870.2	868.0	865.7
132.5°	904.0	903.8	903.6	903.4	903.6	903.8	904.0	904.2	903.4	901.5	899.5
135°	952.2	951.7	951.4	951.0	951.4	951.7	952.2	952.6	951.7	949.8	947.7
137.5°	996.4	995.7	995.1	994.4	995.1	995.7	996.4	997.1	996.4	994.5	992.5
140°	1024.5	1023.5	1022.4	1021.5	1022.4	1023.5	1024.5	1025.5	1025.1	1023.3	1021.5
142.5°	1050.9	1049.8	1048.9	1047.8	1048.9	1049.8	1050.9	1051.9	1051.5	1049.9	1048.2
145°	1087.7	1086.7	1085.6	1084.6	1085.6	1086.7	1087.7	1088.6	1088.5	1087.0	1085.6
147.5°	1119.6	1118.7	1117.8	1117.0	1117.8	1118.7	1119.6	1120.4	1120.3	1119.3	1118.2
150°	1139.8	1138.8	1137.8	1136.8	1137.8	1138.8	1139.8	1140.8	1140.7	1139.5	1138.3
152.5°	1157.6	1156.3	1154.9	1153.7	1154.9	1156.3	1157.6	1159.0	1159.1	1157.9	1156.6
155°	1181.9	1180.3	1178.7	1177.1	1178.7	1180.3	1181.9	1183.5	1183.8	1182.6	1181.3
157.5°	1203.2	1201.6	1200.1	1198.4	1200.1	1201.6	1203.2	1204.8	1204.9	1203.5	1202.1
160°	1215.2	1213.8	1212.4	1210.9	1212.4	1213.8	1215.2	1216.6	1216.7	1215.5	1214.3
162.5°	1226.4	1224.7	1222.9	1221.2	1222.9	1224.7	1226.4	1228.1	1228.4	1226.9	1225.5
165°	1240.8	1239.4	1237.9	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4
167.5°	1251.7	1249.9	1248.1	1246.2	1248.1	1249.9	1251.7	1253.5	1253.8	1252.3	1250.9
170°	1257.6	1255.8	1254.0	1252.1	1254.0	1255.8	1257.6	1259.4	1259.6	1258.2	1256.8
172.5°	1262.0	1260.2	1258.4	1256.5	1258.4	1260.2	1262.0	1263.9	1264.0	1262.6	1261.2
175°	1266.4	1264.4	1262.4	1260.3	1262.4	1264.4	1266.4	1268.5	1268.8	1267.4	1265.9
177.5°	1267.1	1265.7	1264.2	1262.7	1264.2	1265.7	1267.1	1268.6	1268.8	1267.6	1266.4
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1428.5	1433.6	1441.3	1449.6	1454.6	1464.1	1466.9	1471.4	1475.6	1485.2	1495.2
5°	1346.0	1354.0	1372.9	1383.1	1397.4	1414.0	1424.9	1436.3	1448.9	1470.6	1490.6
7.5°	1257.6	1270.9	1294.3	1313.5	1333.9	1357.7	1374.8	1397.4	1416.2	1446.8	1476.0
10°	1198.6	1217.5	1238.6	1261.5	1290.0	1315.2	1339.2	1367.7	1390.6	1427.1	1461.5
12.5°	1145.6	1148.5	1178.7	1203.9	1242.9	1274.0	1301.7	1338.5	1360.9	1404.3	1440.4
15°	1052.9	1070.1	1097.5	1117.5	1163.7	1203.2	1242.1	1280.3	1306.1	1359.7	1407.1
17.5°	974.9	990.7	1018.7	1051.5	1084.8	1124.0	1174.3	1214.6	1249.6	1311.0	1367.0
20°	925.5	944.9	973.5	1007.2	1036.4	1079.2	1122.7	1168.9	1206.6	1275.7	1341.4
22.5°	883.5	898.8	921.9	955.1	987.0	1026.2	1073.8	1124.1	1163.6	1238.3	1304.8
25°	824.4	837.0	851.8	879.3	915.2	958.1	995.2	1050.7	1108.4	1178.0	1258.6
27.5°	771.2	780.1	793.2	817.3	845.2	885.3	926.5	979.1	1037.2	1112.8	1197.8
30°	738.7	744.4	757.6	777.6	804.9	836.4	878.1	928.4	987.8	1064.4	1148.9
32.5°	710.4	715.7	724.2	743.3	767.1	793.9	831.5	881.8	938.4	1013.7	1107.3
35°	667.9	671.8	679.3	694.7	707.8	734.2	765.6	811.2	864.4	936.4	1033.5
37.5°	625.5	630.9	635.5	642.0	658.9	676.2	703.5	742.1	794.3	866.9	959.5
40°	597.6	602.2	609.0	611.9	625.6	641.0	663.3	698.7	751.3	817.5	907.8
42.5°	569.3	573.9	577.9	581.3	593.1	606.7	626.7	657.1	703.8	768.2	857.6
45°	530.7	531.3	535.3	541.6	547.3	557.1	571.3	597.6	633.6	694.1	775.2
47.5°	491.6	492.3	493.0	495.8	502.0	510.8	520.4	541.7	573.9	622.2	701.2
50°	465.6	464.5	465.6	467.9	471.9	479.3	490.2	505.6	531.9	577.0	649.6
52.5°	440.5	440.2	439.5	440.5	443.6	448.7	456.3	469.5	493.0	534.5	598.4
55°	402.2	399.3	399.9	397.6	402.8	403.9	409.7	420.5	441.1	469.6	529.6
57.5°	361.4	359.0	356.5	355.9	355.3	358.4	363.0	371.6	387.4	412.3	461.1
60°	335.4	332.5	329.1	328.0	328.0	329.7	331.9	338.2	353.1	375.4	415.3
62.5°	308.8	305.6	303.5	300.5	299.6	301.4	303.6	308.1	318.8	339.7	374.2
65°	267.9	264.0	261.1	260.5	259.4	257.7	258.8	263.4	271.9	288.5	315.9
67.5°	227.0	223.2	222.5	219.1	217.6	217.7	217.6	221.4	226.6	240.9	261.3
70°	199.9	197.1	196.0	193.1	192.0	190.8	189.7	193.1	198.3	210.3	228.0
72.5°	172.5	170.1	167.6	165.2	165.5	164.3	164.1	166.2	170.4	181.4	195.0
75°	133.1	133.7	130.9	127.9	127.4	126.2	126.2	127.9	129.7	138.3	149.1
77.5°	96.5	96.1	93.7	92.8	92.2	90.9	92.2	93.3	94.3	100.0	108.0
80°	73.7	73.7	70.9	70.9	70.3	68.5	70.3	69.1	71.4	77.1	82.8
82.5°	52.7	51.7	51.7	50.7	50.6	49.3	50.2	51.3	52.2	56.1	59.5
85°	25.7	25.7	25.1	24.5	25.1	24.5	25.1	25.7	26.3	28.0	30.8
87.5°	9.4	9.6	9.7	9.9	9.6	9.6	9.7	9.7	10.2	10.2	10.2
90°	19.3	18.3	16.7	15.1	13.4	11.8	9.9	7.7	5.4	3.2	0.9
92.5°	21.8	21.3	20.4	19.6	18.8	18.0	17.7	17.9	18.1	18.3	18.5
95°	36.7	35.7	34.3	32.9	31.4	30.0	32.6	39.3	46.1	52.8	59.5
97.5°	48.6	47.8	44.5	41.2	37.9	34.6	42.4	61.3	80.2	99.2	118.0
100°	53.8	52.2	48.7	45.3	41.8	38.3	50.5	78.4	106.2	134.1	162.0
102.5°	55.8	53.6	82.6	111.5	140.4	169.4	186.8	192.6	198.5	204.4	210.3
105°	58.0	55.8	111.3	166.9	222.4	277.9	302.6	296.5	290.4	284.4	278.3
107.5°	75.9	78.2	144.7	211.4	277.9	344.6	375.4	370.4	365.5	360.6	355.7
110°	139.8	160.1	219.0	277.8	336.5	395.3	422.6	418.3	414.1	409.7	405.4



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.8	404.0	418.5	433.1	447.5	462.1	467.4	463.6	459.9	456.2	452.4
115°	470.5	564.7	559.6	554.6	549.5	544.4	540.1	536.7	533.2	529.8	526.3
117.5°	602.7	625.5	622.0	618.5	615.0	611.5	607.9	604.0	600.1	596.2	592.4
120°	673.3	670.9	667.3	663.6	660.0	656.3	652.9	649.9	646.8	643.8	640.7
122.5°	715.6	714.1	710.2	706.1	702.1	698.2	694.6	691.4	688.1	684.9	681.7
125°	774.8	773.4	769.6	765.7	761.8	757.9	754.7	752.1	749.4	746.7	744.2
127.5°	829.0	826.9	824.0	821.0	818.2	815.3	812.4	809.5	806.6	803.7	800.7
130°	863.5	861.3	859.0	856.8	854.5	852.3	849.5	846.4	843.1	839.8	836.5
132.5°	897.6	895.7	893.5	891.2	889.0	886.7	884.2	881.5	878.7	876.0	873.1
135°	945.7	943.7	941.8	940.0	938.1	936.3	933.8	930.6	927.3	924.0	920.8
137.5°	990.5	988.5	986.4	984.4	982.3	980.2	978.0	975.8	973.4	971.2	968.9
140°	1019.6	1017.8	1015.5	1013.3	1011.1	1008.8	1006.9	1005.3	1003.7	1002.0	1000.4
142.5°	1046.5	1044.9	1042.3	1039.7	1037.2	1034.7	1032.6	1031.1	1029.7	1028.2	1026.7
145°	1084.2	1082.8	1079.3	1075.8	1072.4	1068.9	1067.3	1067.6	1067.7	1067.9	1068.2
147.5°	1117.1	1116.1	1112.7	1109.2	1105.9	1102.4	1101.1	1101.9	1102.7	1103.5	1104.2
150°	1137.1	1135.8	1132.6	1129.4	1126.1	1122.8	1122.0	1123.3	1124.8	1126.2	1127.7
152.5°	1155.4	1154.2	1151.1	1148.0	1144.9	1141.8	1141.1	1142.6	1144.2	1145.8	1147.4
155°	1180.1	1178.9	1176.5	1174.0	1171.6	1169.2	1168.8	1170.6	1172.5	1174.3	1176.1
157.5°	1200.8	1199.4	1197.7	1195.9	1194.3	1192.6	1192.5	1194.0	1195.6	1197.1	1198.7
160°	1213.1	1211.9	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9
162.5°	1224.2	1222.8	1221.8	1220.7	1219.6	1218.6	1218.7	1219.9	1221.1	1222.4	1223.6
165°	1237.9	1236.6	1236.0	1235.4	1234.7	1234.1	1234.4	1235.6	1236.8	1238.0	1239.3
167.5°	1249.5	1248.1	1247.5	1246.9	1246.4	1245.8	1246.1	1247.3	1248.5	1249.8	1251.0
170°	1255.3	1254.0	1253.5	1253.1	1252.8	1252.3	1252.8	1254.0	1255.2	1256.4	1257.6
172.5°	1259.7	1258.4	1257.9	1257.5	1257.1	1256.7	1257.1	1258.4	1259.6	1260.8	1262.0
175°	1264.6	1263.1	1262.7	1262.3	1261.9	1261.5	1262.0	1263.4	1264.8	1266.3	1267.7
177.5°	1265.3	1264.2	1264.0	1263.9	1263.7	1263.5	1264.0	1265.2	1266.3	1267.5	1268.6
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1494.4	1496.6	1503.9	1511.2	1519.5	1521.7	1525.4	1522.2	1521.3	1530.0	1536.4
5°	1498.6	1508.8	1528.9	1547.1	1562.5	1573.4	1584.8	1589.4	1597.9	1610.0	1624.8
7.5°	1493.7	1513.7	1545.2	1571.8	1600.9	1621.7	1638.1	1652.0	1669.0	1691.7	1716.5
10°	1488.2	1515.1	1553.4	1586.0	1621.3	1648.2	1670.5	1692.2	1717.4	1748.8	1781.3
12.5°	1478.3	1510.1	1558.0	1596.5	1641.9	1668.4	1698.4	1745.2	1772.2	1816.0	1861.8
15°	1458.0	1493.4	1560.2	1607.7	1659.1	1709.3	1764.8	1809.4	1853.9	1879.6	1944.2
17.5°	1428.0	1480.0	1553.9	1609.3	1674.6	1753.9	1816.1	1866.6	1918.0	1959.7	1992.1
20°	1403.7	1460.3	1544.8	1611.1	1688.8	1773.9	1845.4	1896.8	1941.3	1976.2	1996.1
22.5°	1373.1	1444.2	1526.6	1604.2	1703.4	1787.6	1862.7	1903.2	1940.4	1957.4	1965.1
25°	1324.9	1410.6	1503.7	1598.5	1710.5	1799.7	1868.2	1892.7	1903.6	1887.1	1859.6
27.5°	1272.9	1368.4	1477.3	1587.8	1706.2	1791.8	1841.0	1837.1	1818.7	1765.1	1722.3
30°	1234.1	1339.2	1456.3	1576.8	1695.7	1779.1	1807.7	1779.1	1737.3	1677.4	1616.3
32.5°	1193.3	1302.2	1433.9	1561.3	1676.5	1749.8	1756.0	1706.8	1642.3	1574.1	1497.9
35°	1131.8	1249.5	1391.7	1526.6	1635.6	1682.0	1654.5	1567.7	1491.2	1398.0	1294.0
37.5°	1062.2	1192.1	1334.8	1475.7	1574.5	1586.7	1518.5	1427.1	1319.1	1209.7	1087.4
40°	1010.1	1147.8	1294.6	1436.8	1524.2	1511.7	1424.9	1324.3	1195.8	1062.0	948.4
42.5°	963.5	1101.1	1250.7	1390.3	1460.3	1425.7	1324.3	1200.9	1062.7	936.9	832.8
45°	882.7	1024.3	1177.5	1312.3	1352.3	1290.0	1155.8	1018.6	882.7	777.6	695.3
47.5°	804.3	944.3	1096.0	1214.5	1228.6	1144.9	998.2	857.1	740.2	654.6	596.6
50°	746.7	887.3	1037.5	1143.2	1138.6	1037.5	886.7	752.4	654.7	585.6	546.7
52.5°	695.1	827.9	972.2	1068.2	1044.0	933.8	789.8	670.6	590.3	536.2	501.0
55°	614.8	737.5	874.7	951.8	907.2	785.0	663.3	567.3	507.9	467.4	439.9
57.5°	534.9	650.1	767.5	815.0	765.8	652.9	551.5	481.8	437.1	407.1	389.3
60°	485.6	586.2	690.7	731.8	673.0	572.5	492.5	430.2	394.2	369.6	353.6
62.5°	436.3	526.3	624.9	647.3	593.5	508.5	437.6	385.9	356.3	334.4	319.3
65°	369.1	442.7	517.6	532.4	482.8	417.1	361.1	327.4	301.1	285.1	273.1
67.5°	302.6	361.9	414.9	426.9	383.3	337.8	297.3	267.9	250.1	236.9	226.7
70°	263.4	310.2	353.6	363.3	328.5	287.9	257.1	233.7	217.7	206.2	196.6
72.5°	221.8	260.9	297.0	303.5	275.0	244.1	218.7	200.3	186.1	178.8	169.5
75°	169.7	192.5	220.5	222.2	203.4	184.5	165.1	153.1	145.7	136.6	132.0
77.5°	119.8	137.7	153.7	156.8	145.6	132.8	121.9	112.4	106.2	101.9	97.7
80°	91.4	105.7	112.5	116.6	108.6	99.4	93.2	86.9	82.8	80.0	77.1
82.5°	65.3	74.1	80.6	83.6	79.3	73.8	67.5	64.0	60.9	58.5	57.5
85°	33.1	37.1	41.2	42.3	41.2	38.8	35.4	35.4	33.7	33.1	33.1
87.5°	12.1	14.3	14.8	16.6	16.1	16.4	16.7	16.6	16.4	16.2	15.9
90°	3.2	5.4	7.7	9.9	11.8	13.4	15.1	16.7	18.3	19.3	20.3
92.5°	18.3	18.1	17.9	17.7	18.0	18.8	19.6	20.4	21.3	21.8	22.3
95°	52.8	46.1	39.3	32.6	30.0	31.4	32.9	34.3	35.7	36.7	37.7
97.5°	99.2	80.2	61.3	42.4	34.6	37.9	41.2	44.5	47.8	48.6	49.4
100°	134.1	106.2	78.4	50.5	38.3	41.8	45.3	48.7	52.2	53.8	55.4
102.5°	204.4	198.5	192.6	186.8	169.4	140.4	111.5	82.6	53.6	55.8	57.9
105°	284.4	290.4	296.5	302.6	277.9	222.4	166.9	111.3	55.8	58.0	60.3
107.5°	360.6	365.5	370.4	375.4	344.6	277.9	211.4	144.7	78.2	75.9	73.6
110°	409.7	414.1	418.3	422.6	395.3	336.5	277.8	219.0	160.1	139.8	119.5





TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	456.2	459.9	463.6	467.4	462.1	447.5	433.1	418.5	404.0	329.8	255.6
115°	529.8	533.2	536.7	540.1	544.4	549.5	554.6	559.6	564.7	470.5	376.3
117.5°	596.2	600.1	604.0	607.9	611.5	615.0	618.5	622.0	625.5	602.7	580.0
120°	643.8	646.8	649.9	652.9	656.3	660.0	663.6	667.3	670.9	673.3	675.8
122.5°	684.9	688.1	691.4	694.6	698.2	702.1	706.1	710.2	714.1	715.6	717.0
125°	746.7	749.4	752.1	754.7	757.9	761.8	765.7	769.6	773.4	774.8	776.3
127.5°	803.7	806.6	809.5	812.4	815.3	818.2	821.0	824.0	826.9	829.0	831.0
130°	839.8	843.1	846.4	849.5	852.3	854.5	856.8	859.0	861.3	863.5	865.7
132.5°	876.0	878.7	881.5	884.2	886.7	889.0	891.2	893.5	895.7	897.6	899.5
135°	924.0	927.3	930.6	933.8	936.3	938.1	940.0	941.8	943.7	945.7	947.7
137.5°	971.2	973.4	975.8	978.0	980.2	982.3	984.4	986.4	988.5	990.5	992.5
140°	1002.0	1003.7	1005.3	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6	1021.5
142.5°	1028.2	1029.7	1031.1	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5	1048.2
145°	1067.9	1067.7	1067.6	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2	1085.6
147.5°	1103.5	1102.7	1101.9	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1	1118.2
150°	1126.2	1124.8	1123.3	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1	1138.3
152.5°	1145.8	1144.2	1142.6	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4	1156.6
155°	1174.3	1172.5	1170.6	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1	1181.3
157.5°	1197.1	1195.6	1194.0	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8	1202.1
160°	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1	1214.3
162.5°	1222.4	1221.1	1219.9	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2	1225.5
165°	1238.0	1236.8	1235.6	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9	1239.4
167.5°	1249.8	1248.5	1247.3	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5	1250.9
170°	1256.4	1255.2	1254.0	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3	1256.8
172.5°	1260.8	1259.6	1258.4	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7	1261.2
175°	1266.3	1264.8	1263.4	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6	1265.9
177.5°	1267.5	1266.3	1265.2	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3	1266.4
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1541.9	1548.3	1548.3	1549.2	1556.5	1555.6	1555.1
5°	1640.8	1650.5	1651.7	1662.0	1668.8	1666.6	1660.3
7.5°	1734.1	1752.2	1765.9	1773.6	1782.6	1788.2	1785.7
10°	1808.2	1834.4	1850.5	1861.3	1874.5	1884.2	1880.8
12.5°	1875.4	1906.7	1928.6	1947.2	1949.0	1961.4	1953.0
15°	1980.2	2013.3	2016.7	2030.4	2041.3	2040.1	2040.7
17.5°	2014.8	2025.4	2027.6	2027.9	2028.1	2024.0	2015.3
20°	2002.4	1998.5	1988.7	1981.3	1968.2	1966.4	1955.1
22.5°	1944.0	1931.3	1906.9	1890.8	1870.4	1865.0	1861.8
25°	1828.8	1800.8	1762.0	1724.8	1714.5	1694.5	1700.2
27.5°	1670.8	1627.1	1585.0	1554.9	1527.6	1497.6	1506.2
30°	1559.7	1510.5	1451.1	1405.4	1376.3	1347.7	1342.6
32.5°	1427.1	1355.1	1288.9	1248.6	1204.0	1185.9	1166.1
35°	1198.6	1128.3	1062.6	1006.1	973.5	948.4	925.5
37.5°	993.1	912.1	859.1	813.3	789.8	775.4	779.0
40°	865.6	794.7	755.9	721.0	699.3	689.0	691.3
42.5°	762.2	709.2	677.3	653.3	638.0	632.3	630.9
45°	645.0	615.3	589.0	575.3	567.9	561.6	557.6
47.5°	565.0	540.8	526.0	517.8	511.3	504.9	504.8
50°	517.0	501.0	490.8	482.2	477.1	472.5	476.5
52.5°	480.4	465.9	455.6	447.9	446.0	441.9	441.8
55°	426.2	414.7	407.3	400.5	397.1	394.8	391.9
57.5°	376.9	366.0	359.1	354.8	348.3	345.9	345.1
60°	341.6	333.0	326.2	320.5	317.6	313.1	313.1
62.5°	309.2	300.7	294.2	289.9	285.2	283.4	283.9
65°	262.3	255.4	249.1	244.5	243.4	240.0	241.1
67.5°	219.0	214.5	207.8	205.3	203.2	201.3	199.9
70°	190.3	185.7	182.3	178.8	177.1	177.1	177.1
72.5°	166.0	160.6	158.5	154.1	155.2	153.3	151.5
75°	128.5	125.1	123.4	121.7	118.8	118.8	118.8
77.5°	94.6	93.6	91.5	89.7	89.0	88.4	88.7
80°	73.1	72.6	71.4	71.4	70.3	69.7	68.5
82.5°	56.2	54.8	54.1	53.6	53.4	53.2	53.0
85°	32.0	30.8	30.8	31.4	30.3	30.3	30.8
87.5°	16.6	16.8	16.5	16.6	17.1	16.7	16.8
90°	21.4	22.4	23.1	23.5	23.9	24.3	24.7
92.5°	22.8	23.3	23.8	24.0	24.2	24.5	24.7
95°	38.7	39.8	40.2	40.0	39.8	39.5	39.3
97.5°	50.2	51.1	51.6	51.8	52.1	52.3	52.5
100°	57.1	58.7	59.7	60.1	60.5	61.0	61.3
102.5°	60.0	62.1	63.5	64.0	64.6	65.2	65.7
105°	62.5	64.7	66.3	67.2	67.9	68.7	69.6
107.5°	71.3	69.1	68.4	69.1	69.9	70.8	71.5
110°	99.2	78.8	69.1	69.8	70.7	71.5	72.3



TEST NUMBER: P331411-935

CATALOG NUMBER: SA2XXDIP-C865D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	181.4	107.2	70.4	71.1	71.7	72.4	73.0
115°	282.2	188.0	133.6	119.0	104.4	89.7	75.1
117.5°	557.2	534.4	498.9	450.8	402.7	354.6	306.4
120°	678.2	680.7	668.1	640.7	613.2	585.7	558.4
122.5°	718.5	720.0	718.0	712.7	707.4	702.1	696.7
125°	777.7	779.1	780.2	780.8	781.4	782.0	782.6
127.5°	833.1	835.2	836.3	836.4	836.5	836.6	836.7
130°	868.0	870.2	871.2	871.1	870.8	870.6	870.5
132.5°	901.5	903.4	904.2	904.0	903.8	903.6	903.4
135°	949.8	951.7	952.6	952.2	951.7	951.4	951.0
137.5°	994.5	996.4	997.1	996.4	995.7	995.1	994.4
140°	1023.3	1025.1	1025.5	1024.5	1023.5	1022.4	1021.5
142.5°	1049.9	1051.5	1051.9	1050.9	1049.8	1048.9	1047.8
145°	1087.0	1088.5	1088.6	1087.7	1086.7	1085.6	1084.6
147.5°	1119.3	1120.3	1120.4	1119.6	1118.7	1117.8	1117.0
150°	1139.5	1140.7	1140.8	1139.8	1138.8	1137.8	1136.8
152.5°	1157.9	1159.1	1159.0	1157.6	1156.3	1154.9	1153.7
155°	1182.6	1183.8	1183.5	1181.9	1180.3	1178.7	1177.1
157.5°	1203.5	1204.9	1204.8	1203.2	1201.6	1200.1	1198.4
160°	1215.5	1216.7	1216.6	1215.2	1213.8	1212.4	1210.9
162.5°	1226.9	1228.4	1228.1	1226.4	1224.7	1222.9	1221.2
165°	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6
167.5°	1252.3	1253.8	1253.5	1251.7	1249.9	1248.1	1246.2
170°	1258.2	1259.6	1259.4	1257.6	1255.8	1254.0	1252.1
172.5°	1262.6	1264.0	1263.9	1262.0	1260.2	1258.4	1256.5
175°	1267.4	1268.8	1268.5	1266.4	1264.4	1262.4	1260.3
177.5°	1267.6	1268.8	1268.6	1267.1	1265.7	1264.2	1262.7
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9

(END OF REPORT)